


REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1238	C	ELECTRONIC FILE RENAMED	HYO	2/14/02	DJC	2/14/02	DJC	2/14/02
1808	D	Updated	JWM	7/24/06	HO	7/24/06	HO	7/24/06

NOTES:

1. UL FILE #E94521
2. CSA FILE #LR62645-66
3. FINISH: Putty
4. Circuitry: Single Stage
5. UL 1449 Clamping Level: 330 Volts
6. Max. Surge Current: 13,000 Amps
7. Noise Reduction 40dB
8. Response Time: less that 1 nanosecond



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
TOLERANCES UNLESS OTHERWISE SPECIFIED,
.X ±0.015
.XX ±0.010
.XXX ±0.005

DRAWN BY:	DATE:
R.D.	5/3/96
CHECKED BY:	DATE:
APPROVED BY:	DATE:

DRAWING TITLE: Computer Grade Surge Protector			
SIZE A	DWG. NO. SSC66F	ELECTRONIC FILE 66N7712.DWG	REV D
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	