





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F008.DWG



REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1789	A	Released	DCM	12/5/06	JN	2/14/08	JN	2/14/08
1959	B	Shell Plate was Zinc	JN	2/14/08	JN	2/14/08	JN	2/14/08



PANEL CUTOUT



SPECIFICATION:

- 1. Shell: Steel, Tin-Plated
- 2. Contact: Brass, Stamped Gold 5u" Min.- Plated over Nickel
- 3. Insulator: PBT & Fiber-Glass Reinforced, Blue Color
- 4. Current Rating: 5 Amps
- 5. Dielectric Strength: 1000 V for One Minute
- 6. Insulator Resistance: 1000M? Min. at 500 V DC
- 7. Temperature: -50°C to +105°C

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Dan McVicker	12/5/06
CHECKED BY:	DATE:
Jason Nash	2/14/08
APPROVED BY:	DATE:
Jason Nash	2/14/08

DRAWING TITLE: D-Sub Cover, Metallized Plastic, 37 Pin, 45 Degree Ext			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC15400	79K4983.dwg	B
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	