


| DCP # | REV | DESCRIPTION | DRAWN | DATE | CHECKD | DATE | APPRVD | DATE |
|-------|-----|-------------|-------|----------|--------|----------|--------|----------|
| 2070 | A | Released | JN | 09-03-09 | JWM | 09-03-09 | JWM | 09-03-09 |
| | | | | | | | | |



Specification

1. Rated Voltage: 9VDC
2. Operating Voltage: 7 ~ 12VDC
3. Max. Rated Current: 15mA at 9VDC
4. Resonant Frequency: 3.3 ± 0.5 KHz
5. Min. Sound Pressure Level: 88dB at 9VDC/30cm
6. Tone Nature: Continuous
7. Case Material: PC
8. Operating Temperature: -20~+80°C
9. Store Temperature: -30~+100°C
10. Weight: 8g

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY: Jason Nash DATE: 09-03-09
CHECKED BY: Jason Nash DATE: 09-03-09
APPROVED BY: Jason Nash DATE: 09-03-09

DRAWING TITLE: Piezo Buzzer & Transducer
SIZE: DWG. NO: ELECTRONIC FILE: REV:
A MCKPI-G2312-3961 25R0632.dwg A
SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1