


REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1815		Released	jwm	2/28/08	JN	08/17/08	JN	08/17/08



SPECIFICATIONS

- CONNECTOR: 6 POSITION, 4 CONDUCTOR
- LEAD WIRE: 26 AWG, 7 STRAND
- LEAD WIRE COLORS: BLACK, RED, GREEN, YELLOW
- SPRING WIRE: 0.018 INCH DIAMETER, PHOSPHOROUS BRONZE ALLOY
- HOUSING MATERIAL: ABS AND POLYCARBONATE
- COLOR: ALMOND
- HARDWARE: (1) FOAM PAD, (2) #6-3/4 SCREWS

- INSULATION RESISTANCE: ≥ 500 MEGOHMS
- DIELECTRIC STRENGTH: 500 V AC RMS, 60 Hz
- CONTACT RESISTANCE: ≤ 15 MILLIOHMS
- CURRENT RATING: 1½ AMPS
- RETENTION FORCE: 76 N (17 lbs)
- CRIMPING STRENGTH: 2.0 Kg (4.4 lbs)

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	2/28/08
CHECKED BY:	DATE:
Jason Nash	09/17/08
APPROVED BY:	DATE:
Jason Nash	09/17/08

DRAWING TITLE: MODULAR SURFACE JACK, 4 CONDUCTORS, ALMOND			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC22182	26M8145.dwg	A
SCALE: NTS	U.O.M.: INCHES	SHEET: 1 OF 1	