




REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2075	A	RELEASED	LG	30-09-08	JN	30-09-08	JN	30-09-08



Mfg. p/n	A (mm)	A (inch)
MB220-500M02	10	0.394
MB220-500M03	15	0.591
MB220-500M04	20	0.788
MB220-500M05	25	0.985
MB220-500M06	30	1.182
MB220-500M08	40	1.576
MB220-500M10	50	1.97
MB220-500M12	60	2.364



SPECIFICATIONS	UL	VDE
Rated Voltage	AC 300V	
Rated Current	10A	
Wire Size	24~12AWG	0.2~4mm ²
Housing Material	Polyamide66(UL94V-0)	
Cage Clamp	Steel, Ni Plated	
Terminal	Brass, Tin plated	
Spring	Stainless strip steel	
Screw Size	M2.6, Steel, Ni plated	
Operating Temperature	-40°C to +105°C	
Torque	3.5 lb-inch	
PCB Hole Diameter	1.5mm	

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
LG	30-09-08
CHECKED BY:	DATE:
JN	30-09-08
APPROVED BY:	DATE:
JN	30-09-08

DRAWING TITLE: Euro Type Terminal Block			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	Ta-1196	Ta-1196.dwg	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	