





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
809	A	RELEASED	JWM	3/19/03	HO	3/19/03	DJC	3/19/03



RECOMMENDED CRIMP DIE: .068



RECOMMENDED CRIMP DIE: .255



RECOMMENDED STRIPPING DIMENSIONS

SPECIFICATIONS:

IMPEDANCE: 75 Ohms
 FREQUENCY RANGE: 0-1 GHz
 VOLTAGE RATING: 500 Vrms
 DIELECTRIC WITHSTANDING VOLTAGE: 1500 Vrms
 (D) FOR RG-59, 59A, 59B, 62, 62A, 62C/U: ALPHA9059, 9062, 9830, 9840, 9845; BELDEN 8221, 8241, 9169, 9204, 9228; CANARE LV-61S; CommScope 5555, 5560, 5563
 (D1) FOR BELDEN1426A, 1505A, 8212, 8241F, 9100, 9110, 9165, 9171, 9240, 9259, 9265, 9274, 9275, 9659, YR2393D; CommScope 5553, 5565, 55525550, 5567, 5571

#	DESCRIPTION	QTY	MATRL	FINISH
1	COUPLING NUT	1	BRASS	NICKEL, 100 μ inch
2	BODY	1	BRASS	NICKEL, 100 μ inch
3	INSULATOR	1	DELTRIN	---
4	GASKET	1	RUBBER	RED
5	RETAINING RING	1	BRASS	NICKEL, 100 μ inch
6	SPRING	1	SK5	NICKEL, 100 μ inch
7	WASHER	1	BRASS	NICKEL, 100 μ inch
8	PIN	1	BRASS	GOLD, 3 μ inch
9	FERRULE	1	BRASS	NICKEL, 100 μ inch

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	3/19/03
CHECKED BY:	DATE:
Hisham Odish	3/19/03
APPROVED BY:	DATE:
Daniel Carey	3/19/03

DRAWING TITLE: BNC Plug. 75 Ohm, Crimp			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC11204	34C5609.dwg	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	