




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F008.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DATE	CHECKD	DATE	APPRVD	DATE
1934	A	Released	08/08/08	JWM	08/08/08	JWM	08/08/08

DOC. NO. SPC-F008 \* Effective 7/8/02 \* DCP No. 1308



Notes:

1. New Product Shall Be Reference to Bellcore GR-326 Standard.
2. Insertion Loss  $\leq 0.2\text{dB}$  Typical (1300nm)
3. Return Loss  $\geq 55\text{dB}$  (1310nm)
4. Cable Marking:  
 Baycon: Plus Corning SMF-28 Optical Fiber Cable DFNR(L) E201648 04/2005 \*\*\*\*\*  
 Key Marking: Plus Corning SMF-28 Optical Fiber Cable DFNR(L) E201648 04/2005 \*\*\*\*\*

SPC Type No.	Length (Meters)
SPC22996	1
SPC22999	4
SPC23001	8
SPC23002	10

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jason Nash	08/08/08
CHECKED BY:	DATE:
JWM	08/08/08
APPROVED BY:	DATE:
JWM	08/08/08

DRAWING TITLE:		SCALE:	
Duplex Optic Fiber Cable, 9/125, LC to LC		NTS	
SIZE	DWG. NO.	U.O.M.: INCHES [mm]	
A	Ta-923		

ELECTRONIC FILE	REV
Ta-923.DWG	A