


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1262	A	RELEASED	HO	12/27/02	LS	12/27/02	DJC	12/27/02
1885	B	UPDATED TO ROHS COMPLIANT	EO	02/04/06	HO	2/6/06	HO	2/6/06

Absolute Maximum Ratings:

- Collector-Base Voltage, $V_{CB0} = 180V$
- Collector-Emitter Voltage, $V_{CE0} = 160V$
- Emitter-Base Voltage, $V_{EB0} = 6V$
- Continuous Collector Current, $I_C = 600mA$
- Total Device Dissipation ($T_A = +25^{\circ}C$), $P_D = 625mW$
Derate above $25^{\circ}C = 5mW/^{\circ}C$
- Total Device Dissipation ($T_C = +25^{\circ}C$), $P_D = 1.5W$
Derate above $25^{\circ}C = 12mW/^{\circ}C$
- Operating Junction Temperature Range, $T_J = -55^{\circ}C \sim +150^{\circ}C$
- Storage Temperature Range, $T_{stg} = -55^{\circ}C \sim +150^{\circ}C$
- Thermal Resistance, Junction to Case, $R_{thJC} = 83.3^{\circ}C/W$
- Thermal Resistance, Junction to Ambient (Note 1), $R_{thJA} = 200^{\circ}C/W$


RoHS
Compliant

DIM.	MIN.	MAX.
A	4.32	5.33
B	4.45	5.20
C	3.18	4.19
D	0.41	0.55
E	0.35	0.50
F	5°	
G	1.14	1.40
H	1.14	1.53
K	12.70	—



- 1 COLLECTOR
- 2 BASE
- 3 EMITTER

Electrical Characteristics: ($T_A = +25^{\circ}C$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Max	Unit
-----------	--------	-----------------	-----	-----	------

OFF Characteristics

Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = 100\mu A$, $I_E = 0$	180	—	V
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 1.0mA$, $I_B = 0$, Note 2	160	—	V
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = 10\mu A$, $I_C = 0$	6	—	V
Collector Cut-Off Current	I_{CBO}	$V_{CB} = 120V$, $I_E = 0$	—	50	nA
		$V_{CB} = 120V$, $I_E = 0$, $T_A = +100^{\circ}C$	—	50	uA
Emitter Cut-Off Current	I_{EBO}	$V_{EB} = 4V$, $I_C = 0$	—	50	nA

ON Characteristics (Note 2)


DC Current Gain	h_{FE}	$V_{CE} = 5V$, $I_C = 1.0mA$	80	—	—
		$V_{CE} = 5V$, $I_C = 10mA$	80	250	—
		$V_{CE} = 5V$, $I_C = 50mA$	30	—	—
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 10mA$, $I_B = 1.0mA$	—	0.15	V
		$I_C = 50mA$, $I_B = 5.0mA$	—	0.2	V
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 10mA$, $I_B = 1.0mA$	—	1	V
		$I_C = 50mA$, $I_B = 5.0mA$	—	1	V

Small-Signal Characteristics



Current Gain-Bandwidth Product	f_T	$V_{CE} = 10V$, $I_C = 10mA$, $f = 100MHz$	100	300	MHz
Output Capacitance	C_{obo}	$V_{CB} = 10V$, $I_E = 0$, $f = 1MHz$	—	6	pF
Input Capacitance	C_{ibo}	$V_{BE} = 0.5V$, $I_C = 0$, $f = 1MHz$	—	20	pF
Small-Signal Current Gain	h_{fe}	$V_{CE} = 10V$, $I_C = 1mA$, $f = 1kHz$	50	200	—
Noise Figure	NF	$V_{CE} = 5V$, $I_C = 250\mu A$, $f = 1kHz$, $R_S = 1k\Omega$	—	8	dB

Notes:

- R_{thJA} is measured with the device soldered into a typical printed circuit board.
- Pulse Test: Pulse Width = $300\mu s$, Duty Cycle = 2%.



SECTION A-A



Bottom View

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	HISHAM ODISH	12/27/02	TRANSISTOR, BIPOLAR, TO-92, NPN			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	LUIS SERBIA	12/27/02	A	2N5551	35C0727.DWG	B
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: MILLIMETERS	SHEET: 1 OF 1
	DANIEL CAREY	12/27/02				

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.