
All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:			DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
XXX	A	RELEASED	Amudha	26-11-08	Suresh	27-11-08	JN	12/12/08

RoHS Compliant



STRAIN RELIEF SHOWN AS ILLUSTRATION ONLY

ITEM	DESCRIPTION	MATERIAL	FINISH
4	CABLE	-	-
3	TUBING	**HEAT SHRINK	BLACK
2	STRAIN RELIEF	POLYVINYL CHLORIDE	BLACK
1	7-16 DIN M CRIMP	BRASS	SILVER

**DUAL WALL POLYOLEFIN

Manufacturer Part Number	Length	Cable Type	Strain Relief
SPC29121	12	RG-58A/U	Yes
SPC29122	24	RG-58A/U	Yes
SPC29123	36	RG-58A/U	Yes
SPC29124	48	RG-58A/U	Yes
SPC29125	60	RG-58A/U	Yes
SPC29126	72	RG-58A/U	Yes
SPC29127	12	RG-58C/U	Yes
SPC29128	24	RG-58C/U	Yes
SPC29129	36	RG-58C/U	Yes
SPC29130	48	RG-58C/U	Yes
SPC29131	60	RG-58C/U	Yes
SPC29132	72	RG-58C/U	Yes
SPC29140	12	RG-223/U	No
SPC29141	12	RG-223/U	No
SPC29142	36	RG-223/U	No
SPC29143	48	RG-223/U	No
SPC29144	60	RG-223/U	No
SPC29145	72	RG-223/U	No
SPC29146	12	RG-213/U	No
SPC29147	24	RG-213/U	No

Disclaimer:
All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.

SPC TECHNOLOGY

Unless otherwise specified, Dimensions are for references purposes only.

Drawn By:	Date:
Amudha	26-11-08
Checked By:	Date:
Suresh	27-11-08
Approved By:	Date:
Jason Nash	12/12/08

Drawing Title: 7-16 DIN MALE CRIMP TO 7-16 DIN MALE CRIMP

Size:	Dwg. No	Electronic File	Rev
A	TA-1024	TA-1024.dwg	A

Scale: NTS | U.O.M.: Inches (mm) | Sheet: 1 of 2

All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:			DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
XXX	A	RELEASED	Amudha	26-11-08	Suresh	27-11-08	JN	12/12/08

RoHS Compliant

Manufacturer Part Number	Length	Cable Type	Strain Relief
SPC29148	36	RG-213/U	No
SPC29149	48	RG-213/U	No
SPC29150	60	RG-213/U	No
SPC29151	72	RG-213/U	No
SPC29152	12	LMR-400	No
SPC29153	24	LMR-400	No
SPC29154	36	LMR-400	No
SPC29155	48	LMR-400	No
SPC29156	60	LMR-400	No
SPC29157	72	LMR-400	No
SPC29158	12	BELDEN 9913	No
SPC29159	24	BELDEN 9913	No
SPC29160	36	BELDEN 9913	No
SPC29161	48	BELDEN 9913	No
SPC29162	60	BELDEN 9913	No
SPC29163	72	BELDEN 9913	No
SPC29164	12	LMR-195	No
SPC29165	24	LMR-195	No
SPC29166	36	LMR-195	No
SPC29167	48	LMR-195	No
SPC29168	60	LMR-195	No
SPC29169	72	LMR-195	No
SPC29242	12	RG-142B/U	No
SPC29243	24	RG-142B/U	No
SPC29244	36	RG-142B/U	No
SPC29245	48	RG-142B/U	No
SPC29246	60	RG-142B/U	No
SPC29247	72	RG-142B/U	No
SPC29251	12	RG-8/X	No
SPC29252	24	RG-8/X	No
SPC29253	36	RG-8/X	No
SPC29254	48	RG-8/X	No
SPC29255	60	RG-8/X	No
SPC29256	72	RG-8/X	No
SPC29257	24	LMR-240	No
SPC29258	24	LMR-240	No
SPC29259	36	LMR-240	No
SPC29260	48	LMR-240	No
SPC29261	60	LMR-240	No
SPC29262	72	LMR-240	No
SPC29263	12	LMR-240 ULTRAFLEX	No
SPC29264	24	LMR-240 ULTRAFLEX	No
SPC29265	36	LMR-240 ULTRAFLEX	No
SPC29266	48	LMR-240 ULTRAFLEX	No
SPC29267	60	LMR-240 ULTRAFLEX	No
SPC29268	72	LMR-240 ULTRAFLEX	No

Disclaimer:
All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.

SPC TECHNOLOGY

Unless otherwise specified, Dimensions are for references purposes only.

Drawn By:	Date:
Amudha	26-11-08
Checked By:	Date:
Suresh	27-11-08
Approved By:	Date:
Jason Nash	12/12/08

Drawing Title: 7-16 DIN MALE CRIMP TO 7-16 DIN MALE CRIMP

Size:	Dwg. No	Electronic File	Rev
A	TA-1024	TA-1024.dwg	A

Scale: NTS | U.O.M.: Inches (mm) | Sheet: 2 of 2