


REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2000	A	Released	JN	11/18/08	JWM	11/18/08	JWM	11/18/08





Specifications:

- Rated current: 15Amp AC300V
- Insulation withstands volt: AC2000V min
- Insulation resistance: >2000MΩ at DC500V
- Operating Temperature: -40°C to +120°C
- Wire range: 14~22 AWG
- Screw Torque: 12 lb-in



Item	Material	Plating/Finish
1	Insulating Body, PBT (UL94V-0)	Black
2	Terminal, Brass	Tin Plated
3	Screw, Steel	Ni plated



Mfg. P/N	Number of Poles	A (mm)	B (mm)
MC24351	4	39.2	28.5
MC24352	6	58.2	47.5
MC24353	8	77.2	66.5
MC24354	10	96.2	85.5

Unit of Measure: mm

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jason Nash	11/18/08
CHECKED BY:	DATE:
JWM	11/18/08
APPROVED BY:	DATE:
JWM	11/18/08

DRAWING TITLE: Barrier Terminal Block			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	Ta-1160	Ta-1160.dwg	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	