



SPC
TECHNOLOGY



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			JAG	01-08-10	MRD	05-08-10	XXX	16-08-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398



Specifications

Volts	Amps	Watts	MSCP	Filament	Life-HRS
13	0.58	7.54	6	C-2R	750

Dimensions : Inches

Part Number Table

Description	Part Number
G-6 Double Contact Bayonet Base Lamp	90

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

DRAWN BY:

JAG

DATE:

01-08-10

DRAWING TITLE:

G-6 Double Contact Bayonet Base Lamp

CHECKED BY:

MRD

DATE:

05-08-10

SIZE DWG. NO.

XXX

XXX

ELECTRONIC FILE

96F7943

REV

A

APPROVED BY:

XXX

DATE:

16-08-10

SCALE: NTS

XXX

U.O.M.: INCHES [mm]

XXX

SHEET:

1

OF

1