



All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:			DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
XXX	A	RELEASED	Ilvya	27-11-08	Suresh	27-11-08	JN	12/12/08



STRAIN RELIEF SHOWN AS ILLUSTRATION ONLY



ITEM	DESCRIPTION	MATERIAL	FINISH
5	CABLE	-	-
4	TUBING	**HEAT SHRINK	BLACK
3	STRAIN RELIEF	POLYVINYL CHLORIDE	BLACK
2	N F CRIMP BULK	BRASS	NICKEL
1	N MALE CRIMP	BRASS	NICKEL

****DUAL WALL POLYOLEFIN**

SUGGESTED MOUNTING CONFIGURATION

Manufacturer Part Number	Length	Cable Type	Strain Relief
SPC25655	12	RG-58C/U	Yes
SPC25656	24	RG-58C/U	Yes
SPC25657	36	RG-58C/U	Yes
SPC25658	48	RG-58C/U	Yes
SPC25659	60	RG-58C/U	Yes
SPC25660	72	RG-58C/U	Yes
SPC25661	12	RG-142B/U	No
SPC25662	24	RG-142B/U	No
SPC25663	36	RG-142B/U	No
SPC25664	48	RG-142B/U	No

Disclaimer:

All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.



SPC TECHNOLOGY

Drawing Title:
N MALE CRIMP TO N FEMALE CRIMP BULKHEAD

Size: A	Dwg. No: TA-996	Electronic File: TA-996.dwg	Rev: A
---------	-----------------	-----------------------------	--------

Scale: NTS	U.O.M.: Inches (mm)	Sheet: 1 of 2
------------	---------------------	---------------

Unless otherwise specified, Dimensions are for references purposes only.

Drawn By: Ilvya	Date: 27-11-08
Checked By: Suresh	Date: 27-11-08
Approved By: Jason Nash	Date: 12/12/08

All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:			DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
XXX	A	RELEASED	Ilvya	27-11-08	Suresh	27-11-08	JN	12/12/08



Manufacturer Part Number	Length	Cable Type	Strain Relief
SPC25665	60	RG-142B/U	No
SPC25666	72	RG-142B/U	No
SPC25667	12	RG-223/U	No
SPC25668	24	RG-223/U	No
SPC25669	36	RG-223/U	No
SPC25670	48	RG-223/U	No
SPC25671	60	RG-223/U	No
SPC25672	72	RG-223/U	No
SPC25673	12	RG-316/U	No
SPC25674	24	RG-316/U	No
SPC25675	36	RG-316/U	No
SPC25676	48	RG-316/U	No
SPC25677	60	RG-316/U	No
SPC25678	72	RG-316/U	No
SPC27849	12	RG-58A/U	Yes
SPC27850	24	RG-58A/U	Yes
SPC27851	36	RG-58A/U	Yes
SPC27852	48	RG-58A/U	Yes
SPC27853	60	RG-58A/U	Yes
SPC27854	72	RG-58A/U	Yes
SPC27855	12	LMR-100	No
SPC27856	24	LMR-100	No
SPC27857	36	LMR-100	No
SPC27858	48	LMR-100	No
SPC27859	60	LMR-100	No
SPC27860	72	LMR-100	No
SPC27861	12	LMR-195	No
SPC27862	24	LMR-195	No
SPC27863	36	LMR-195	No
SPC27864	48	LMR-195	No
SPC27865	60	LMR-195	No
SPC27866	72	LMR-195	No
SPC27867	12	RG-400/U	No
SPC27868	24	RG-400/U	No
SPC27869	36	RG-400/U	No
SPC27870	48	RG-400/U	No
SPC27871	60	RG-400/U	No
SPC27872	72	RG-400/U	No
SPC27873	12	RG-188A/U	No
SPC27874	24	RG-188A/U	No
SPC27875	36	RG-188A/U	No
SPC27876	48	RG-188A/U	No
SPC27877	60	RG-188A/U	No
SPC27878	72	RG-188A/U	No

Disclaimer:

All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.



SPC TECHNOLOGY

Unless otherwise specified, Dimensions are for references purposes only.	Drawn By:	Date:	Drawing Title:			
	Ilvya	27-11-08	N MALE CRIMP TO N FEMALE CRIMP BULKHEAD			
	Checked By:	Date:	Size:	Dwg. No	Electronic File	Rev
	Suresh	27-11-08	A	TA-996	TA-996.dwg	A
Approved By:	Date:	Scale: NTS		U.O.M.: Inches (mm)	Sheet: 2 of 2	
Jason Nash	12/12/08					