


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISONS		DOC. NO.	SPC-F005	* Effective:	12/21/98	* DCP No:	680	
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
615	A	Released	JMM	6/16/00	JC	7/31/00	DJC	8/2/00



- Notes:
1. 2 Switch Positions: x1/x10
 2. Attenuation: x1/x10
 3. Input Resistance: 1MΩ (x1); 10MΩ (x10)
 4. Input Capacitance: 46pF (x1); 18pF (x10)
 5. Band Width (MHz): 15 (x1); 60 (x10)
 6. Risetime (ns): 27 (x1); 5.8 (x10)
 7. Max. Input (VDC + AC Max): 600
 8. Compensation: (pF) 10..35
 9. Length: 47.2 [1.2 meters]
 10. Meets IEC61010-2-031 CAT I 600V

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.		DRAWING TITLE: Switchable Oscilloscope Probe Kit	
DRAWN BY: Jeff McVicker	DATE: 6/16/00	SIZE: A	DWG. NO.: 76-109
CHECKED BY: John Cole	DATE: 7/31/00	SCALE: NTS	ELECTRONIC FILE: 84N2151.dwg
APPROVED BY: Daniel Carey	DATE: 8/2/00		REV: A