


© COPYRIGHT 1997 BY SPC TECHNOLOGY. ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS		DOC. NO. SPC-FD05, Total Pages: 2
DCP #	REV	Effective: 7/15/97, DCP No: 229 Supersedes DCP No: 103
162	A	RELEASED J.W.M. 1/9/98 J.C. 2/4/98 B.B. 2/5/98
888	B	UK Listing was Swadded J.W.M. 2/17/00 J.C. 2/17/00 J.C. 2/17/00



Max. Rating: 10A.250VAC  
 Contact Resistance: <10milliohms  
 Insulation Breakdown: >10<sup>3</sup> Megohms  
 A.C. Breakdown: Pole-Pole 6.5KV. Poles-Accessible Parts 6.5KV.  
 Operating Temperature: -40°C to +70°C  
 Withdrawl Force: 10N(Min). 50N(Max)  
 Materials:  
 Moulding: Nylon. Flammability Rating UL94V-0  
 Contacts: Brass Nickel Plated.

**DISCLAIMER**  
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL OBTAIN THE SERVICES OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



**SPC TECHNOLOGY**



Canada

USA

UK

DRAWN BY:		DATE:	DRAWING TITLE:	
Jeff McVicker		1/9/98	Rewirable Plug Assembly	
CHECKED BY:		DATE:	SIZE	DWG. NO.
JOHN COLE		2/4/98	A	2161
APPROVED BY:		DATE:	SCALE:	U.O.M.: Millimeters
BRETT BRAATZ		2/5/98	NTS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE SHOWN FOR REFERENCE ONLY!			ELECTRONIC FILE	REV
			92N4164.dwg	B
			SHEET: 1	OF 1