
ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS								
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
948	A	RELEASED	HO	3/27/02	JWM	3/27/02	DJC	3/27/02

DOC. NO. SPC-FD05 * Effective: 12/21/98 * DCP No: 680



Specifications:

1. Volts: 24 VAC, 28 VDC
2. Current: 13 ~ 15 mA
3. Lens Color: Water Clear
4. Typical Useful Life: 20,000 ~ 40,000 hours
5. Replaces Incandescent Types: 327, 376, 385, 387

SPC Type No.	Emitted Color	Wave Length peack (nm)	Luminous Intensity Typical: (mcd) (see Note)	Viewing Angle
SPC10550	White	mixed	1207	60°
SPC10551	Red	635	2000	50°
SPC10552	Green	520	3400	45°
SPC10553	Yellow	590	1300	30°

Note: mcd rating are prior to basing of product

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
HISHAM ODISH	3/27/02
CHECKED BY:	DATE:
JEFF MCVICKER	3/27/02
APPROVED BY:	DATE:
DANIEL CAREY	3/27/02

SPC TECHNOLOGY

DRAWING TITLE: LED, Single Contact Midget Flanged Base

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-511	TA-511.DWG	A

SCALE: NTS | U.O.M.: Millimeters | SHEET: 1 OF 1

SPC-FD05.DWG