




SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS		DOC. NO.	Effective: 7/8/02		DCP No:			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			AMD	01-08-10	JAG	05-08-10	XXX	17-08-10



Specifications:

Electrical:

Contact rating : 6A @ 125VAC, 3A @ 250VAC
 Contact resistance : 30 milliohms maximum
 Insulation resistance : 1,000 megohms minimum At 500 VDC
 Dielectric strength : 1,000 VRMS

Mechanical:

Life : 10,000 Cycles


Environmental:

Operating temperature : -30°C to +85°C

Circuit	Switching Type
SPST	ON-OFF

Part Number Table

Description	Part Number
Pull Chain Switch	SPC21175



Dimensions : Inches (mm)

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	AMD	DATE:	02-08-10
CHECKED BY:	JAG	DATE:	05-08-10
APPROVED BY:	XXX	DATE:	17-08-10

DRAWING TITLE:		Pull Chain Switch	
SIZE	DWG. NO.	ELECTRONIC FILE	REV
XXX	XXX	34C4458	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1