



SPC
TECHNOLOGY


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			VEE	06-08-10	JAG	11-08-10	XXX	20-08-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398



Specifications:

Electrical:

Contact rating : 15A at 125VAC, 10A at 250VAC
 Contact resistance : 30 milliohms maximum
 Insulation resistance : 1,000 Megohms minimum at 500 VDC
 Dielectric strength : 1,000 VRMS

Mechanical:

Life : 10,000 Cycles

Environmental:





Operating temperature : -30°C to +85°C

Material:

Housing : Nylon 6/6, UL94V-0 - Black
 Actuator : Polycarbonate - Black
 Contact/terminals : Copper alloy, silver plated

Part Number Table

Description	Part Number
Rocker Switch - DPST - ON/OFF	SPC21179



Dimensions : Inches (mm)

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

VEE

DATE:

06-08-10

DRAWING TITLE:

Rocker Switch - DPST - ON/OFF

CHECKED BY:

JAG

DATE:

11-0-10

ELECTRONIC FILE

34C4463

APPROVED BY:

XXX

REV

A

DATE:

20-08-10

SCALE:

NTS

U.O.M.: INCHES [mm]

XXX

SHEET:

1 OF 1

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.