


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS		DOC. NO. SPC-F005	* Effective: 12/21/98	* DCP No: 680				
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
B		Revised and Redrawn	JWM	1/8/93				
1210	C	Renamed - was 3-881-*	JWM	7/26/01	JC	8/30/01	JC	8/30/01



MOUNTING HOLE LAYOUT

PART NUMBER	COLOR
3-881-BK	BLACK
3-881-GR	GREEN
3-881-R	RED
3-881-W	WHITE
3-881-Y	YELLOW

- NOTES:**
- MATERIAL: BRASS PER QQ-B-626D
STUD: SILVER
FINISH: SILVER
 - INSULATING MATERIAL: NYLON
66 PER ASTM D4066
THUMB NUT: NYLON 66 PER
ASTM D4066
 - HARDWARE: GOLD PLATED NUTS
 - PANEL THICKNESS: UP TO .281" [7.14 MM]
 - CURRENT RATING: 15 AMPS
 - FLAMMABILITY: UL94V-2 SELF-EXTINGUISHING
 - CONTINUOUS USE TEMPERATURE:
-40°F (-40°C) TO 185°F (85°C)
 - BREAKDOWN VOLTAGE: 5700 Vrms MINIMUM
 - STUD-TO-PANEL CAP.: 3.3 pF NOMINAL
 - CONTACT RESISTANCE: N.A.
 - FEATURES TURRET TERMINAL
OF INSTALLATION
 - HAS A CAPTIVE THUMB NUT
 - INSULATED BODY IS FLATTENED TO PREVENT
TURNING.
 - WEIGHT: .015 LBS.
 - BODY THREAD STRIPPING TORQUE:
6.0 IN. LBS [7.0 KG CM]

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



DRAWING TITLE: **Binding Posts (Standard)**

Tolerances Unless Otherwise Specified:		DRAWING TITLE:	
X = ±.015	DATE: 1/8/93	SIZE:	DWG. NO. TA-377
.XX = ±.010	DATE: 1/15/93	A	ELECTRONIC FILE TA-377.dwg
.XXX = ±.005	DATE: 1/19/93	SCALE: NTS	SHEET: 1 OF 1
APPROVED BY: J Liska			