



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1868	A	RELEASED	EYO	11/08/05	HO	11/17/05	JWM	11/17/05



RoHS Compliant




Specifications:

- Material
Coating: Conformal Silicone Ceramic.
Core: Ceramic
Terminals: solder-coated copper clad axial lead.
- Derating Linearly from 100% @ +25°C to 0% @ +275°C.
- Power Rating: Based on 25°C free air rating.
- Overload:
 - > 5W: 5 times rated wattage for 5 seconds.
 - ≤ 5W: 10 times rated wattage for 5 seconds.
- Temperature Coefficient:
 - >1Ω: ±90 ppm/°C
 - 1Ω ~ 9.99Ω: ±50 ppm/°C
 - ≤10Ω: ±20 pmm°/C

Multicomp Type No.	Resistance (Ω) ±1%	Wattage (W)	L	W	D	A
MC14693	0.10	1	0.437	1.500	0.125	0.0201
MC14694	0.13					
MC14695	0.15					
MC14696	0.33					
MC14697	0.50					
MC14698	1.00	3	0.593	1.500	0.218	0.032
MC14699	2.00					
MC14700	3.00					
MC14701	4.00					
MC14702	5.00					
MC14703	10.00	5	0.937	1.500	0.343	0.0403
MC14704	15.00					
MC14705	20.00					
MC14706	25.00					
MC14707	33.00					
MC14708	40.00	5	0.937	1.500	0.343	0.0403
MC14709	50.00					
MC14710	100.00					
MC14711	250.00					
MC14712	500.00					

Wattage Derating Chart



DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED,
 .XX ±0.125
 .XXX ±0.062
 .XXXX ±0.0005

DRAWN BY:	DATE:
EKLAS ODISH	11/08/05
CHECKED BY:	DATE:
HISHAM ODISH	11/17/05
APPROVED BY:	DATE:
JEFF MCVICKER	11/17/05

DRAWING TITLE: RoHS Compliant Axial Lead Wirewound Resistors, Silicon, 1%			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-684	TA-684.DWG	A
SCALE: NTS		U.O.M.: INCHES	SHEET: 1 OF 1