


All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:			DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
xxx	A	RELEASED	Amudha	26-11-08	Suresh	27-11-08	JN	12/12/08



STRAIN RELIEF SHOWN AS ILLUSTRATION ONLY

Manufacturer Part Number	Length	Cable Type	Strain Relief
SPC26366	12	RG-8A/U	No
SPC26367	24	RG-8A/U	No
SPC26368	36	RG-8A/U	No
SPC26369	48	RG-8A/U	No
SPC26370	60	RG-8A/U	No
SPC26371	72	RG-8A/U	No
SPC26372	12	RG-58C/U	Yes
SPC26374	24	RG-58C/U	Yes
SPC20877	36	RG-58C/U	Yes
77362CPS	48	RG-58C/U	Yes
SPC26379	60	RG-58C/U	Yes
SPC26381	72	RG-58C/U	Yes
SPC26383	12	RG-59B/U	No
SPC26384	24	RG-59B/U	No
SPC26385	36	RG-59B/U	No
SPC26386	48	RG-59B/U	No
SPC26387	60	RG-59B/U	No
SPC26388	72	RG-59B/U	No
SPC29005	12	RG-213/U	No
SPC29006	24	RG-213/U	No
SPC29007	36	RG-213/U	No
SPC29008	48	RG-213/U	No
SPC29009	60	RG-213/U	No
SPC29010	72	RG-213/U	No
SPC29011	12	RG-58A/U	Yes
SPC29012	24	RG-58A/U	Yes
SPC29013	36	RG-58A/U	Yes
SPC29014	48	RG-58A/U	Yes
SPC29015	60	RG-58A/U	Yes
SPC29016	72	RG-58A/U	Yes
SPC29017	12	LMR-195	No
SPC29018	24	LMR-195	No

ITEM	DESCRIPTION	MATERIAL	FINISH
4	CABLE		
3	TUBING	**HEAT SHRINK	BLACK
2	STRAIN RELIEF	POLYVINYL CHLORIDE	BLACK
1	UHF MALE CRIMP	BRASS	NICKEL

**DUAL WALL POLYOLEFIN

Disclaimer:

All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.



SPC TECHNOLOGY

Unless otherwise specified, Dimensions are for references purposes only.	Drawn By:	Date:	Drawing Title:		
	Amudha	26-11-08	UHF MALE CRIMP TO UHF MALE CRIMP		
	Checked By:	Date:	Size:	Dwg. No	Electronic File
	Suresh	27-11-08	A	TA-1023	TA-1023.dwg
Approved By:	Date:	Scale:	U.O.M.:	Sheet:	
Jason Nash	12/12/08	NTS	Inches (mm)	1 of 2	

All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:			DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
xxx	A	RELEASE II	Amudha	26-11-08	Suresh	27-11-08	JN	12/12/08



Manufacturer Part Number	Length	Cable Type	Strain Relief
SPC29019	36	LMR-195	No
SPC29020	48	LMR-195	No
SPC29021	60	LMR-195	No
SPC29022	72	LMR-195	No
SPC29023	12	RG-62A/U	No
SPC29024	24	RG-62A/U	No
SPC29025	36	RG-62A/U	No
SPC29026	48	RG-62A/U	No
SPC29027	60	RG-62A/U	No
SPC29028	72	RG-62A/U	No
SPC29029	12	RG-8/X	No
SPC29030	24	RG-8/X	No
SPC29031	36	RG-8/X	No
SPC29032	48	RG-8/X	No
SPC29033	60	RG-8/X	No
SPC29034	72	RG-8/X	No
SPC29035	12	LMR-240	No
SPC29036	24	LMR-240	No
SPC29037	36	LMR-240	No
SPC29038	48	LMR-240	No
SPC29039	60	LMR-240	No
SPC29040	72	LMR-240	No
SPC29041	12	BELDEN 9913	No
SPC29042	24	BELDEN 9913	No
SPC29043	36	BELDEN 9913	No
SPC29044	48	BELDEN 9913	No
SPC29045	60	BELDEN 9913	No
SPC29046	72	BELDEN 9913	No
SPC29047	12	LMR-400	No
SPC29048	24	LMR-400	No
SPC29049	36	LMR-400	No
SPC29050	48	LMR-400	No
SPC29051	60	LMR-400	No
SPC29052	72	LMR-400	No
SPC29053	12	RG-55A/U	No
SPC29054	24	RG-55A/U	No
SPC29055	36	RG-55A/U	No
SPC29056	48	RG-55A/U	No
SPC29057	60	RG-55A/U	No
SPC29058	72	RG-55A/U	No
SPC29059	12	RG-142/U	No
SPC29060	24	RG-142/U	No
SPC29061	36	RG-142/U	No
SPC29062	48	RG-142/U	No
SPC29063	60	RG-142/U	No
SPC29064	72	RG-142/U	No
SPC29065	12	RG-223/U	No
SPC29066	24	RG-223/U	No
SPC29067	36	RG-223/U	No
SPC29068	48	RG-223/U	No
SPC29069	60	RG-223/U	No
SPC29070	72	RG-223/U	No
SPC29071	12	RG-400/U	No
SPC29072	24	RG-400/U	No
SPC29073	36	RG-400/U	No
SPC29074	48	RG-400/U	No
SPC29075	60	RG-400/U	No
SPC29076	72	RG-400/U	No
SPC29077	12	RG-214/U	No
SPC29078	24	RG-214/U	No
SPC29079	36	RG-214/U	No
SPC29080	48	RG-214/U	No
SPC29081	60	RG-214/U	No
SPC29082	72	RG-214/U	No
SPC29083	12	BELDEN 9913F	No
SPC29084	24	BELDEN 9913F	No
SPC29085	36	BELDEN 9913F	No
SPC29086	48	BELDEN 9913F	No
SPC29087	60	BELDEN 9913F	No
SPC29088	72	BELDEN 9913F	No

Disclaimer:

All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.



SPC TECHNOLOGY

Drawing Title:

UHF MALE CRIMP TO UHF MALE CRIMP

Size: A	Dwg. No TA-1023	Electronic File TA-1023.dwg	Rev A
---------	-----------------	-----------------------------	-------

Scale: NTS U.O.M.: Inches (mm) Sheet: 2 of 2

Unless otherwise specified, Dimensions are for references purposes only.

Drawn By: Amudha	Date: 26-11-08
Checked By: Suresh	Date: 27-11-08
Approved By: Jason Nash	Date: 12/12/08