


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.



RoHS Compliant

| REVISIONS | | Doc. No. SPC-F005 | Effective 12/21/08 | Doc No 890 | | | | |
|-----------|-----|-------------------|--------------------|------------|--------|----------|--------|----------|
| DCP # | REV | DESCRIPTION | DRAWN | DATE | CHECKD | DATE | APPRVD | DATE |
| 1950 | C | Released | JJM | 10/09/08 | JJM | 10/09/08 | JJM | 10/09/08 |

| SPC Type No. | Screw Size | Inside Diameter | | Outside Diameter | | Thickness | | | |
|--------------|------------|-----------------|-----------|------------------|-----------|-----------|------|------|------|
| | | Basic | Tolerance | Basic | Tolerance | Basic | Max | Min | |
| SPC21883 | 4 | .125 | .008 | .312 | .008 | .005 | .032 | .040 | .025 |
| SPC21884 | 6 | .156 | .008 | .375 | .015 | .005 | .049 | .065 | .036 |
| SPC21885 | 8 | .188 | .008 | .438 | .015 | .005 | .049 | .065 | .036 |
| SPC21886 | 10 | .219 | .008 | .500 | .015 | .005 | .049 | .065 | .036 |
| SPC21887 | 1/4 | .281 | .015 | .625 | .015 | .005 | .065 | .080 | .051 |



MATERIAL: Steel, Nickel Plated

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

| | | | |
|--------------|------------|-------|----------|
| DRAWN BY: | Jason Nash | DATE: | 10/09/08 |
| CHECKED BY: | JJM | DATE: | 10/09/08 |
| APPROVED BY: | JJM | DATE: | 10/09/08 |



SPC TECHNOLOGY

FLAT STEEL WASHER

| | | | | | |
|----------------|-------------------|-----------------|------------|--------|--------|
| DRAWING TITLE: | FLAT STEEL WASHER | ELECTRONIC FILE | TA-955.DWG | REV | A |
| SIZE | A | DWG. NO. | TA-955 | | |
| SCALE: | NTS | U.O.M.: | INCHES | SHEET: | 1 OF 1 |