



Master Components Selector Guide

Including Former Catalyst, PulseCore and CMD Devices



ON Semiconductor Master Components Selector Guide

AC–DC Controllers and Regulators, Amplifiers and Comparators, Analog Switches, Bipolar Transistors, Clock and Data Distribution, Clock Generation, Custom, DC–DC Controllers, Converters, and Regulators, Digital Potentiometers, Diodes, Drivers, DSP Systems, EMI/RFI Filters, IGBTs and FETs, Interfaces, Memory, Rectifiers, Standard Logic, Thermal Management, Thyristors, Voltage and Current Management

SG388/D
Rev. 11, May–2010



ON Semiconductor®

© SCILLC, 2010
Previous Edition © 2009
“All Rights Reserved”

AnyLevel, DPP, EASY SWITCHER, ECLinPS, ECLinPS Lite, ECLinPS MAX, ECLinPS Plus, EpiBase, FASTMOS, FLEXMOS, From-the-Socket-to-the-Pocket, FULLPAK, GigaComm, HDPlus, ICePAK, LDD, MECL, MEGAHERTZ, MHTL, MicroIntegration, MicroLeadless, MiniGate, MiniMOS, MiniMOSORB, Multi-Pak, NOCAP, ON-Demand, PInPAK, PMode, PowerBase, POWERSENSE, POWERTAP, PureEdge, QCP, Quake, SLEEPMODE, SMARTDISCRETES, SMART HotPlug, SMARTswitch, Soft-Skip, SUPERBRIDGES, SuperLock, ThermalTrak, Thermopad, Thermowatt, TIMING SAFE, TMOS Stylized, TOCCATA, Toccata Plus[†], TOCCATA PLUS, μ Cool, uCool, Unibloc, VPower, Zurium and Z-Switch are trademarks of Semiconductor Components Industries, LLC (SCILLC).

A/M/I, AMI, AMI SEMICONDUCTOR, AMIS, ASTRIC, BelaSigna[†], BELASIGNA, CATALYST, C.MD DESIGN, dBCOOL[†], DBCOOL, EMI-LATOR, Ezairo[†], EZAIRO, FPGASIC, FREEPROM, GreenPoint, LUXGUARD, MOSORB, NETRANS, Orela[†], ORELA, PICOGUARD, PRAETORIAN, PULSECORE, QUAD-MODE, SENSEFET, SignaKlara[†], SIGNAKLARA, SURMETIC, TMOS, TMOS & Design Device, UNIWATT, XLARRAY, XPRESSARRAY, XTREMOS, and XTREMEESD are registered trademarks of Semiconductor Components Industries, LLC (SCILLC).

All brand names and product names appearing in this document are registered trademarks or trademarks of their respective holders.

ON Semiconductor and **ON** are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

Table of Contents

	Page		Page
AC–DC Controllers and Regulators	5	Clock and Data Distribution	75
Off–Line Controllers	8	Arithmetic Functions	78
Flyback / Forward Fixed Frequency	9	Adders/Subtractors	78
Flyback Variable Frequency	11	Counters	78
Push–Pull / Half–Bridge Controllers	12	Dividers	79
UC384X Type	13	Magnitude Comparators	80
Off–Line Regulators	14	Prescalers	80
Power Factor Controllers	16	Buffers	81
Interleaved PFC	17	Clock Drivers	81
Variable Frequency / Critical Conduction Mode	17	Crosspoint Switches	84
Fixed Frequency / Continuous Conduction Mode	17	Flip–Flops	84
Fixed Frequency / Discontinuous Conduction Mode	18	Latches and Registers	86
Single Stage	18	Logic Gates	87
Secondary Side Controllers	18	Multiplexers	89
Amplifiers and Comparators	19	Receivers/Drivers	91
Single Operational Amplifiers	22	Serial/Parallel Converters	93
Dual Operational Amplifiers	24	Skew Managers	93
Quad Operational Amplifiers	26	Translators	94
Single Comparators	28	Clock Generation	97
Dual Comparators	28	Crystal Oscillators	100
Quad Comparators	29	Phase/Frequency Detectors	101
Audio Amplifiers	30	PLL Clock Generators	102
Transconductance Amplifiers	30	Spread Spectrum EMI Reduction Clocks	103
Video Amplifiers	31	VCOs	105
Companders	31	Zero Delay Buffers	105
Analog Switches	33	Custom	107
Audio Switches	36	Digital ASICs	110
Data Switches	37	Standard Cell Product Families	110
Signal Switches	37	Structured ASIC Product Families	110
Video Switches	40	Custom Foundry Services	110
Bipolar Transistors	41	DC–DC Controllers, Converters, and Regulators	111
Bipolar Power Transistors	44	DC–DC Switching Non–Isolated	114
Discrete Transistors	45	Step–Down Switching Regulators – Internal Switch	115
Darlington Transistors	50	Multi–Topology (Step–Up, Step–Down, Inverting) Switching Regulators – Internal Switch	117
Audio	52	Step–Down Switching Controllers – External Switch	118
Electronic Lamp Ballasts	54	Step–Up Switching Controllers – External Switch	118
Small–Signal Bipolar Transistors	55	Charge Pumps	119
General–Purpose Transistors	55	DC–DC Switching Isolated	120
General–Purpose Multiple Transistors	60	Flyback Fixed Frequency Converters	120
Low Noise and Good h_{FE} Linearity	61	DC–DC Switching, Computing	121
Darlington Transistors	61	Linear Voltage Regulators	123
High Current Transistors	62	Standard Linear Voltage Regulators	123
High Voltage Transistors	64	Multi–Market Low Dropout Linear Voltage Regulators	124
RF Transistors	65	Single Output Low Dropout Linear Voltage Regulators	126
Switching Transistors	65	Multiple Output Low Dropout Linear Voltage Regulators	128
Multiple Switching Transistors	66	Automotive Linear Voltage Regulators	129
Digital Transistors (Bias Resistor Transistors)	67	Single Automotive Linear Voltage Regulators	130
Dual Digital Transistors (Bias Resistor Transistors)	69		
Combinational Digital Transistors (Bias Resistor Transistors)	70		
Complex Digital Transistors	72		
Low Saturation Voltage Transistors	73		
Load Switch Transistors	74		

	Page
Dual Automotive Linear Voltage Regulators	132
Battery Charge Controllers	132
Digital Potentiometers	133
Digitally Programmable Potentiometers	136
Diodes	147
Tuning and Switching Diodes	
Abrupt Junction Tuning Diodes	150
Hyper-Abrupt Junction Tuning Diodes	150
Schottky Diodes	151
Pin Switching Diodes	154
General Purpose Signal & Switching Diodes	155
Zener Diodes – Regulation in Axial Leads	157
Zener Diodes – Regulation in Surface Mount	159
Dual Zeners – Duals in Surface Mount	165
TVS Diodes – In Axial Leads	168
TVS Diodes – In Surface Mount	171
ESD Protection Diodes	183
TVS/ESD Protection	198
Drivers	211
Display/LED Drivers	214
Load/Relay Drivers	
Load Drivers – Darlington Transistors Arrays	217
Relay Drivers	217
MOSFET/IGBT Drivers	218
Motor Drivers	219
DSP Systems	221
Audio DSP Systems	224
EMI/RFI Filters	225
Audio Filters	228
Data Filters	228
RC Parallel Interface Filters	230
LC Parallel Interface Filters	231
Application Specific Filters	231
IGBTs and FETs	233
IGBTs	236
JFETS	237
High-Frequency Amplifiers	237
Switches and Choppers	237
MOSFETs	238
Protected MOSFETs	250
Interfaces	251
Data Transmitters and Transceivers	254
HART and MAU	254
LIN and CAN Transceivers	254
EIA Transceivers	255
I/O Expanders	256
Modulators/Demodulators	256
Sensor Interfaces	256
SMART and SIM Card Interfaces	257
Memory	259
Serial SRAM	262


	Page
Parallel SRAM	262
Serial EEPROM	263
Parallel EEPROM	265
Flash	265
NVRAM	265
Rectifiers	267
Application Specific Rectifiers	270
Low V_F Schottky	270
Low Leakage Schottky	271
High Voltage Schottky	271
MEGAHERTZ™	271
UltraSoft Rectifiers	271
Energy Rated Rectifiers	271
SCHOTTKY Rectifiers	272
Surface Mount Schottky	272
Axial Lead Schottky	275
TO-220 Type Schottky	276
TO-218 Types and TO-247 Schottky	278
UltraSoft Rectifiers	278
Ultrafast Rectifiers	279
Surface Mount Ultrafast	279
Axial Lead Ultrafast	280
TO-220 Type Ultrafast	281
TO-218 Types and TO-247 Ultrafast	281
Fast Recovery Rectifiers/General Purpose Rectifiers	282
Standard Logic	283
Arithmetic Functions	286
Buffers	287
Bus Switches	291
Flip-Flops	292
Inverters	294
Latches and Registers	297
Logic Gates	299
Multiplexers	304
Multivibrators	305
Transceivers	306
Translators	307
Thermal Management	309
Fan Controllers	312
Temperature Sensors	313
Thyristors	315
Silicon Controlled Rectifiers (SCRs)	318
TRIACs (Bidirectional Devices)	321
Thyristor Surge Protection	325
Thyristor and Transistor Triggers	328
Voltage and Current Management	329
Current Protection	332
Voltage Protection	332
Voltage References	333
Voltage Supervisors	334
Index	335
NOTE: The Tape & Reel Specification information has been moved to its own publication. Please see ON Semiconductor brochure, BRD8011/D, for information on Tape & Reel.	

AC-DC Controllers and Regulators

AC–DC Controllers and Regulators

Table of Contents

	Page
Off–Line Controllers	8
Flyback / Forward Fixed Frequency	9
Flyback Variable Frequency	11
Push–Pull / Half–Bridge Controllers	12
UC384X Type	13
Off–Line Regulators	14
Power Factor Controllers	16
Interleaved PFC	17
Variable Frequency / Critical Conduction Mode ...	17
Fixed Frequency / Continuous Conduction Mode .	17
Fixed Frequency / Discontinuous Conduction Mode	18
Single Stage	18
Secondary Side Controllers	18



ON Semiconductor Selector Guide – AC-DC Controllers and Regulators

FLYBACK / FORWARD FIXED FREQUENCY

Device	Control Mode	Switching Freq (kHz)	Freq Jittering (%)	Standby Mode Technique	Min HV Startup Limit (V)	Dynamic Self Supply (mA)	Under-voltage Lock-Out (V)	Short Circuit Protection	Over Power Compensation	Brown-Out Protection	Latch	Soft-Start (ms)	Max V _{CC} (V)	Drive Capability Source/Sink (mA)	Temp (°C)	Packages	Additional Features
CS51021A	Current Mode	Adjustable	N/A	NO	NO	NO	YES	YES	NO	NO	Via the Latch / Demag	Adj	20	1,000	-40 to +85	SO-16	Bidirectional Synchronization
CS51022A	Current Mode	Adjustable	N/A	NO	NO	NO	YES	YES	NO	NO	Via the Latch / Demag	Adj	20	1,000	-40 to +85	TSSOP-16, SO-16	100 µA Max Sleep Current
CS51221	Voltage Mode	Adjustable	N/A	NO	NO	NO	YES	YES	NO	NO	Via the Latch / Demag	Adj	15	1,000	-40 to +85	SO-16	
CS5124	Current Mode	400	N/A	NO	NO	NO	YES	YES	NO	NO	NO	Adj	20	200	-40 to +105	SO-8	
MC33023	Voltage or Current	Adjustable	N/A	NO	NO	NO	YES	YES	NO	NO	NO	Adj	30	200	-40 to +105	SO-16 WB	
MC34023	Voltage or Current	Adjustable	N/A	NO	NO	NO	YES	YES	NO	NO	NO	Adj	30	200	0 to +70	PDIP-16	
MC33060A	Voltage Mode	200	N/A	NO	NO	NO	YES	YES	NO	NO	NO	Adj	42	200	-40 to +85	SO-14, PDIP-14	
MC34060A	Voltage Mode	200	N/A	NO	NO	NO	YES	YES	NO	NO	NO	Adj	42	200	0 to +70	SO-14, PDIP-14	
NCP1200	Current Mode	100, 40, 60	±0.7	Adj Skip Mode	30	4	N/A	When DSS is used	NO	NO	NO	NO	16	250 / 250	-25 to +125	SO-8, PDIP-8	Limited Duty Cycle to 50%
NCP1203	Current Mode	100, 40, 60	N/A	Adj Skip Mode	30	NO	7.8 to 12.8 Typ.	NO	NO	NO	NO	NO	16	250	-40 to +125	SO-8, PDIP-8	
NCP1216A	Current Mode	133, 100, 65	±4	Adj Skip Mode	30	8	NO	When DSS is used	NO	NO	NO	1.00	16	500	0 to +125	SO-8, PDIP-7	Limited Duty Cycle to 50%
NCP1216	Current Mode	133, 100, 65	±4	Adj Skip Mode	30	8	NO	When DSS is used	NO	NO	NO	NO	16	500	0 to +125	SO-8, PDIP-7	
NCP1217A	Current Mode	133, 100, 65	N/A	Adj Skip Mode	30	NO	7.6 to 12.8 Typ.	NO	NO	NO	Via the Latch / Demag	1.00	16	500	0 to +125	SO-8, PDIP-7	Limited Duty Cycle to 50%
NCP1217	Current Mode	133, 100, 65	N/A	Adj Skip Mode	30	NO	7.6 to 12.8 Typ.	NO	NO	NO	Via the Latch / Demag	NO	16	500	0 to +125	SO-8, PDIP-7	
NCP1219	Current Mode	65, 100	±7.5	Adj. Skip Mode	20	12.8	9.4 to 12.7	YES	NO	NO	Via the Latch / Demag	4.8	20	500 / 800	-40 to +125	SO-7	HV Startup up to 500V
NCP1230	Current Mode	133, 100, 65	±6.4	Adj Skip Mode	20	NO	7.7 to 12.6 Typ.	YES	NO	NO	Via the Latch / Demag	2.50	18	500 / 800	-40 to +125	SO-8, PDIP-7	

ON Semiconductor Selector Guide – AC-DC Controllers and Regulators

FLYBACK / FORWARD FIXED FREQUENCY (CONTINUED)

Device	Control Mode	Switching Freq (kHz)	Freq Jittering (%)	Standby Mode Technique	Min HV Startup Limit (V)	Dynamic Self Supply (mA)	Under-voltage Lock-Out (V)	Short Circuit Protection	Over Power Compensation	Brown-Out Protection	Latch	Soft-Start (ms)	Max V _{CC} (V)	Drive Capability Source/Sink (mA)	Temp (°C)	Packages	Additional Features
NCP1237/ NCP1238	Current Mode	65, 100, 133	± 6	Freq. Foldback and Soft-Skip	60	8	9.5 to 12 Typ	NO	YES	YES	YES	4	28	1000 / 1000	-40 to +125	SO-7	HV Startup up to 500V
NCP1218	Current Mode	65	± 7.5	Adj. Skip Mode	20	13	9.5 to 12.6 Typ	YES	NO	NO	Vias the Latch / Demag	4	20	500 / 800	-40 to +125	SO-7	HV Startup up to 500V
NCP1252	Current Mode	Up to 500	± 5	Skip Mode	N/A	NO	9 to 10 Typ	YES	NO	YES	YES	Adj	28	500 / 800	-25 to +125	SO-8	
NCP1271	Current Mode	65, 100	± 7.5	Adj. Skip Mode with Transient Load Detection	20	NO	12.6 to 20 Typ.	YES	NO	NO	Via the Latch / Demag	4	20	500 / 800	-40 to +125	SO-7	
NCP1288	Current Mode	65, 100, 133	± 6	Freq. Foldback and Soft-Skip	60	NO	10.5 to 16 Typ	NO	YES	YES	YES	4	28	1000 / 1000	-40 to +125	SO-7	HV Startup up to 500V
NCP1562	Voltage Mode	230	N/A	NO	NO	NO	7 to 10.3 Typ.	NO	NO	NO	Line UV/OV detectors	Adj	20	1000 / 2000	-40 to +125	SO-16	HV Startup up to 100V

ON Semiconductor Selector Guide – AC-DC Controllers and Regulators

FLYBACK VARIABLE FREQUENCY

Device	Control Mode	Freq Clamp Max On Time (µs)	Freq Clamp Min Off Time (µs)	Standby Mode Tech- nique	Min HV Start- Up Lim- it (V)	Dynamic Self Supply (mA)	Under- voltage Lock- Out (V)	Short Circuit Protec- tion	Over Power Com- pensation	Brown- Out Protec- tion	Latch	Soft- Start (ms)	Max VCC (V)	Drive Capability Source/Sink (mA)	Temp (°C)	Pack- ages
MC33067	Voltage Mode	Adj	Adj	NO	NO	NO	9 to 16 Typ.	YES	NO	NO	NO	Adj	20	200 / 200	-40 to +85	SO-16, PDIP-16
MC34067	Voltage Mode	Adj	Adj	NO	NO	NO	9 to 16 Typ.	YES	NO	NO	NO	Adj	20	200 / 200	0 to +70	SO-16, PDIP-16
MC33064	Current Mode	NO	6.9	Freq Clamp	40	NO	7.6 to 15 Typ.	NO	NO	NO	NO	NO	16	220 / 600	-25 to +125	SO-8, SO-16
NCP1207A NCP1207 /B	Current Mode	NO	8 (A Version) 4.5 (B Version)	Adj Skip Mode	40	7	9.8 to 10.4 Typ.	YES	NO	NO	Via the Latch / Demag	1	16	500 / 500	-40 to +125	SO-8, PDIP-8
NCP1308	Current Mode	NO	10	Adj Skip Mode	40	7	9.8 to 12 Typ.	YES	NO	NO	Fixed on the VCC	1	16	500 / 500	0 to +125	SO-8
NCP1337	Current Mode	67	35	Soft- Ripple Mode	55	9.5	10 to 12 Typ.	YES	YES	YES	Via the Latch / Demag	4	20	500 / 500	0 to +125	SO-7, PDIP-7
NCP1338	Current Mode	67	35	Soft- Ripple Mode	55	9.5	10 to 12 Typ.	YES	YES	YES	Via the Latch / Demag	4	20	500 / 500	0 to +125	SO-7, PDIP-7
NCP1351	Current Mode	Fixed Ton	Variable Toff	Adj Skip Mode	NO	NO	8.5 to 15 Typ.	YES	NO	NO	NO	NO	20	300 / 150	0 to +125	SO-8, PDIP-8
NCP1377	Current Mode	NO	3.8	Adj Skip Mode	40	NO	7.6 to 12.8 Typ.	NO	NO	NO	Via the Latch / Demag	1	16	500 / 500	0 to +125	SO-7, PDIP-7
NCP1379/ NCP1380	Current Mode	NO	NO	Freq. Foldback	NO	NO	9 to 17 Typ.	YES	YES	YES	A&C Versions	3.8	28	500 / 800	-40 to +125	SO-8
NCP1381	Current Mode	45	8	Adj Skip Mode	NO	NO	10 to 15 Typ.	YES	YES	YES	Via the Latch / Demag	5	20	500 / 800	0 to +125	SO-14
NCP1382	Current Mode	45	8	Adj Skip Mode	NO	NO	10 to 15 Typ.	YES	YES	YES	Via the Latch / Demag	5	20	500 / 800	0 to +125	SO-14

ON Semiconductor Selector Guide – AC-DC Controllers and Regulators


PUSH-PULL / HALF-BRIDGE CONTROLLERS

Device	Control Mode	Switching Freq (kHz)	Standby Mode Technique	Max Duty Cycle (%)	Under-voltage Lock-Out (V)	Short Circuit Protection	Latch	Internal Ref Voltage (V)	Enable Capability	Soft-Start (ms)	Max V _{oc} (V)	Drive Capability Source/Sink (mA)	Temp (°C)	Packages	Additional Features
MC33025	Voltage & Current mode	1000	NO	45	9.2 & 4.2	YES	NO	5.1	NO	Adj	30	200 / 200	-40 to +105	SO-16, PDIP-16	
MC34025	Voltage & Current mode	1000	NO	45	9.2 & 4.2	YES	NO	5.1	NO	Adj	30	200 / 200	0 to +70	SO-16, PDIP-16	
NCP1392	Current	250	NO	50	9	NO	NO	3.5	YES	Adj	16 Clamped	500 / 1000	-40 to +125	SO-8	Brown-Out Protection
NCP1393	Current	250	NO	50	9	NO	YES	3.5	NO	Adj	16 Clamped	500 / 1000	-40 to +125	SO-8	Brown-Out Protection
NCP1395	Voltage	1000	Adj Skip Mode	52	9.3	NO	YES	2	YES	Adj	20	180/180	0 to +125	SO-16, PDIP-16	
NCP1396	Voltage	500	Skip Cycle Possible (A)	50	9.5	NO	YES	2	YES	Adj	20	500 / 1000	-40 to +125	SO-15	
NCP1397	Voltage	500	Skip Cycle Possible	50	9.5	YES	YES	2	YES	Adj	20	500 / 1000	-40 to +125	SO-15	
SG3525A	Voltage	400	NO	49	7	NO	NO	5.1	YES	Adj	40	400 / 400	0 to +70	SO-16, PDIP-16	
TL494	Voltage	200	NO	48	6.43	NO	NO	5	NO	Adj	40	500 / 500	40 to +125 0 to +70 -40 to +85	SO-16, PDIP-16	
TL594	Voltage	300	NO	50	5.2	NO	NO	5	NO	Adj	42	500 / 500	-40 to +85	SO-16, PDIP-16, TSSOP-16	

ON Semiconductor Selector Guide – AC-DC Controllers and Regulators

UC384X TYPE


Device	Control Mode	Switching Freq (kHz)	Standby Mode Technique	Max Duty Cycle (%)	Undervoltage Lock-out (V)	Short Circuit Protection	Latch	Internal Ref Voltage (V)	Soft-Start (ms)	Max V _{CC} (V)	Drive Capability Source/Sink (mA)	Temp (°C)	Packages
UC2842B	Current Mode	52	NO	96	10 to 16 Typ.	YES	N/A	5	NO	30	200 / 200	-25 to +85	SO-14, SO-8, PDIP-8
UC2843B	Current Mode	52	NO	96	7.6 to 8.5 Typ.	YES	N/A	5	NO	30	200 / 200	-25 to +85	SO-14, SO-8, PDIP-8
UC2844B	Current Mode	52	NO	48	10 to 16 Typ.	YES	N/A	5	NO	30	200 / 200	-25 to +85	SO-14, SO-8, PDIP-8
UC2845B	Current Mode	52	NO	48	7.6 to 8.5 Typ.	YES	N/A	5	NO	30	200 / 200	-25 to +85	SO-14, SO-8, PDIP-8
UC3842B	Current Mode	52	NO	96	10 to 16 Typ.	YES	N/A	5	NO	30	200 / 200	0 to +70	SO-14, SO-8, PDIP-8
UC3843B	Current Mode	52	NO	96	7.6 to 8.5 Typ.	YES	N/A	5	NO	30	200 / 200	0 to +70	SO-14, SO-8, PDIP-8
UC3844B	Current Mode	52	NO	50	10 to 16 Typ.	YES	N/A	5	NO	25	200 / 200	0 to +70	SO-14, SO-8, PDIP-8
UC3845B	Current Mode	52	NO	50	7.6 to 8.5 Typ.	YES	N/A	5	NO	25	200 / 200	0 to +70	SO-14, SO-8, PDIP-8
UC3842BV	Current Mode	52	NO	96	10 to 16 Typ.	YES	N/A	5	YES	30	200 / 200	-40 to +105	SO-14, SO-8
UC3843BV	Current Mode	52	NO	96	7.6 to 8.5 Typ.	YES	N/A	5	YES	30	200 / 200	-40 to +105	SO-14, SO-8
UC3844BV	Current Mode	52	NO	50	10 to 16 Typ.	YES	N/A	5	YES	25	200 / 200	-40 to +105	SO-14, SO-8
UC3845BV	Current Mode	52	NO	50	7.6 to 8.5 Typ.	YES	N/A	5	YES	25	200 / 200	-40 to +105	SO-14, SO-8



ON Semiconductor Selector Guide – AC-DC Controllers and Regulators

OFF-LINE REGULATORS

Device	Control Mode	Switching Freq (kHz)	Freq Jittering (%)	Standby Mode Technique	R _{DS(on)} Typ (Ω)	Max Break-down Voltage (V)	Max Internal Current Set Point (mA)	Min HV Startup Limit (V)	Dynamic Self Supply (mA)	Under-voltage Lock-out (V)	Short Circuit Protection	Over Power Compensation	Brown-Out Protection	Latch	Temp (°C)	Pack-ages	Com ments
MC33363	Voltage Mode	285	N/A	NO	14	700	400	9	NO	9.5 to 15.2 Typ.	NO	NO	NO	NO	-25 to +150	SO-16, PDIP-16	
NCP1010	Current Mode	65, 100, 130	± 3.3	Skip Mode	22	700	100	30	8.5	7.5 to 8.5 Typ.	When DSS is used	NO	NO	YES	0 to +125	PDIP-7, SOT-223	
NCP1011	Current Mode	65, 100, 130	± 3.3	Skip Mode	22	700	250, 450	30	8.5	7.5 to 8.5 Typ.	When DSS is used	NO	NO	YES	0 to +125	PDIP-7, SMT, SOT-223	
NCP1012	Current Mode	65, 100, 130	± 3.3	Skip Mode	11	700	250	30	8	7.5 to 8.5 Typ.	When DSS is used	NO	NO	YES	0 to +125	PDIP-7, SMT, SOT-223	
NCP1013	Current Mode	65, 100, 130	± 3.3	Skip Mode	11	700	350	30	8	7.5 to 8.5 Typ.	When DSS is used	NO	NO	YES	0 to +125	PDIP-7, SOT-223	
NCP1014	Current Mode	65, 100, 130	± 3.3	Skip Mode	11	700	450	30	8	7.5 to 8.5 Typ.	When DSS is used	NO	NO	YES	0 to +125	PDIP-7, SMT, SOT-223	
NCP1015	Current Mode	65, 100	± 3.3	Skip Mode	11	700	450	30	8	7.5 to 8.5 Typ.	When DSS is Used	No	No	Yes	0 to +125	PDIP-7, SOT-223	
NCP1027	Current Mode	65, 100	± 6.0	Skip Mode	5.6	700	800	30	N/A	7.2 to 8.5 Typ.	YES	YES	YES	YES	0 to +125	PDIP-7	
NCP1028	Current Mode	65, 100	± 6.0	Skip Mode	5.6	700	800	30	N/A	7.2 to 8.5 Typ.	YES	YES	YES	YES	0 to +125	PDIP-7	No OVP on V _{CC} Pin
NCP1050	Gated Oscillator	45.5, 103, 140	± 5.0	Skip Mode	30	700	100	20	6.3	7.5 to 8.5 Typ.	YES	NO	NO	YES	-40 to +150	PDIP-7, SOT-223	
NCP1051	Gated Oscillator	45.5, 103, 140	± 5.0	Skip Mode	30	700	200	20	6.3	7.5 to 8.5 Typ.	YES	NO	NO	YES	-40 to +150	PDIP-7, SOT-223	
NCP1052	Gated Oscillator	45.5, 103, 140	± 5.0	Skip Mode	30	700	300	20	6.3	7.5 to 8.5 Typ.	YES	NO	NO	YES	-40 to +150	PDIP-7, SOT-223	
NCP1053	Gated Oscillator	45.5, 103, 140	± 5.0	Skip Mode	15	700	400	20	6.3	7.5 to 8.5 Typ.	YES	NO	NO	YES	-40 to +150	PDIP-7, SOT-223	
NCP1054	Gated Oscillator	45.5, 103, 140	± 5.0	Skip Mode	15	700	530	20	6.3	7.5 to 8.5 Typ.	YES	NO	NO	YES	-40 to +150	PDIP-7, SOT-223	
NCP1055	Gated Oscillator	45.5, 103, 140	± 5.0	Skip Mode	15	700	680	20	6.3	7.5 to 8.5 Typ.	YES	NO	NO	YES	-40 to +150	PDIP-7, SOT-223	



ON Semiconductor Selector Guide – AC-DC Controllers and Regulators

INTERLEAVED PFC

Device	Control Mode	Topology	Freq Clamp Freq Max (kHz)	Under Voltage Lock-Out (V)	Max Startup Consumption (mA)	Over Power Limitation	Current Limit Detection	Brown-out Protection	Latch	Under (Output) Voltage Protection	In-Rush Detection	Enable Capability	Main PWM Turn On Signal	Max V _{CC} (V)	Drive Capability Source/Sink (mA)	Temp (°C)	Pack-ages
NCP1631	Voltage Mode	Boost	500	10 to 11.85 Typ.	100	YES	Current Sensing	YES	Fixed	Fixed	YES	YES	YES	20	500 / 800	-40 to +125	SO-16

VARIABLE FREQUENCY / CRITICAL CONDUCTION MODE

Device	Control Mode	Topology	Freq Clamp Freq Max (kHz)	Min HV Startup Limit (V)	Under Voltage Lock-Out (V)	Max Startup Consumption (µA)	Current Limit Detection	Latch	Under Voltage Protection	Enable Capability	Max V _{CC} (V)	Drive Capability Source/Sink (mA)	Temp (°C)	Packages
MC33262	Current Mode	Boost	NO	N/A	8 to 13 Typ.	400	Current Sensing	Fixed	NO	YES	30	500 / 500	-40 to +105	SO-8, PDIP-8
MC34262	Current Mode	Boost	NO	N/A	8 to 13 Typ.	400	Current Sensing	Fixed	NO	YES	30	500 / 500	0 to +85	SO-8, PDIP-8
MC33368	Current Mode	Boost	YES	YES	8.5 to 13 Typ.	N/A	Current Sensing	Fixed	NO	YES	16	1000 / 1000	-25 to +125	SO-16
NCP1606	Voltage Mode	Boost	600	N/A	9.5 to 12 Typ.	50	Current Sensing	Program- mable	Fixed	YES	20	500 / 800	-40 to +125	SO-8, PDIP-8
NCP1607	Voltage Mode	Boost	600	N/A	9.5 to 12 Typ.	50	Current Sensing	Program- mable	Fixed	YES	20	500 / 800	-40 to +125	SO-8
NCP1608	Voltage Mode	Boost	600	N/A	9.5 to 12 Typ.	50	Current Sensing	Program- mable	Fixed	YES	20	500 / 800	-40 to +125	SO-8

FIXED FREQUENCY / CONTINUOUS CONDUCTION MODE

Device	Control Mode	Topology	Switching Freq (kHz)	Under Voltage Lock-Out (V)	Max Startup Consumption (µA)	Over Power Limitation	Current Limit Detection	Brown Out Protection	Latch	Under (Output) Voltage Protection	In-Rush Detection	Enable Capability	Max V _{CC} (V)	Drive Capability Source/Sink (mA)	Temp (°C)	Pack-ages
NCP1650	Average Current Mode	Boost	Adjustable 25 to 250	10 to 10.5 Typ.	80	NO	Negative Current Sensing	YES	Fixed	NO	NO	YES	20	1500 / 1500	-40 to +125	SO-16
NCP1653	Average Current Mode or Peak Current Mode	Boost and Follower Boost	67, 100	8.7 to 13.25 Typ.	50	YES	Program- mable Negative Current Sensing	NO	Fixed	Fixed	YES	YES	18	1000 / 1000	-40 to +125	SO-8, PDIP-8
NCP1654	Average Current Mode	Boost	65, 133, 200	9 to 13.75 9 to 10.5	150	YES	Current Sensing	YES	YES	YES	YES	YES	25	1500 / 1500	-40 to +125	SO-8

ON Semiconductor Selector Guide – AC-DC Controllers and Regulators

FIXED FREQUENCY / DISCONTINUOUS CONDUCTION MODE

Device	Control Mode	Topology	Switching Freq (kHz)	Min HV Startup Limit (V)	Under Voltage Lock-Out (V)	Startup Consumption (μ A)	Current Limit Detection	Latch	Under (Output) Voltage Protection	In-Rush Detection	Main PWM Turn On Signal	Enable Capability	Max V_{CC} (V)	Drive Capability Source/Sink (mA)	Temp ($^{\circ}$ C)	Pack-ages
NCP1601	Voltage Mode	Boost	up to 405	N/A	9 to 13.75 Typ. 9 to 10.5 Typ.	40	Negative Current Sensing	Fixed	Fixed	YES	N/A	YES	18	500 / 800	-40 to +125	SO-8, PDIP-8
NCP1605 NCP1605A	Voltage Mode	Boost	up to 250	N/A	9 to 15, 9 to 10.5 (A Version)	N/A	Current Sensing	Fixed	Fixed	YES	YES	YES	20	500 / 800	0 to +125	SO-16

SINGLE STAGE

Device	Control Mode	Topology	Switching Freq (kHz)	Min HV Startup Limit (V)	Standby Mode Technique	Under Voltage Lock-Out (V)	Max Startup Consumption (mA)	Current Limit Detection	Under (Output) Voltage Protection	Enable Capability	Max V_{CC} (V)	Drive Capability Source/Sink (mA)	In-Rush Detection	Temp ($^{\circ}$ C)	Pack-ages
NCP1651	Average Current Mode	Boost	Adjustable 25 to 250	17	N/A	9.8 to 10.8 Typ.	5.5	Current Sensing	YES	YES	18	1500 / 1500	N/A	-40 to +125	SO-16
NCP1652	Average Current Mode	Boost	100	40	Adj Skip Mode	11 to 14 Typ.	100	Current Sensing	YES	YES	20	300 / 700	N/A	-40 to +125	SO-16

SECONDARY SIDE CONTROLLERS

Device	IC Operating Voltage	Converter Input Voltage	Output Voltage	Output Driver	Freq.	Temp. (T_A)	Features	Package
CS5101	ULVO: 7.0/8.0 V Max: 45 V	V_{gate} max: 75 V)	$(V_{REF} = 2.0 V)$	1.5 A	SYNC	-40 to +85 $^{\circ}$ C	<ul style="list-style-type: none"> Voltage mode Configured as either buck or boost with external NFET Externally programmable overcurrent protection 5.0 V 2% reference pin 	DIP-14
NCP4303	Max: 30 V	-	12 V (A Version) 6 V (B Version)	5 A / 2.5 A	Up to 500 kHz	-40 to +125	<ul style="list-style-type: none"> Synchronous rectification driver Adjustable minimum ON and OFF times Parasitic inductance compensation Can be used in CCM, DCM, and QR flyback applications as well as LLC applications 	SO-8
NCP4330	Max: 45 V	-	-	-	-	-40 to +125 $^{\circ}$ C	<ul style="list-style-type: none"> Bootstrap for N-MOSFET High Side Drive 	SO-8

Amplifiers and Comparators

Amplifiers and Comparators

Table of Contents

	Page
Single Operational Amplifiers	22
Dual Operational Amplifiers	24
Quad Operational Amplifiers	26
Single Comparators	28
Dual Comparators	28
Quad Comparators	29
Audio Amplifiers	30
Transconductance Amplifiers	30
Video Amplifiers	31
Compandors	31

SINGLE OPERATIONAL AMPLIFIERS

Device Name	V _{CC} (min) (V)	V _{CC} (max) (V)	G _{BW} (typ) (MHz)	Slew Rate (typ) (V/μs)	V _{IO} (max @ 25°C, V _S = 5.0 V) (mV)	I _B (typ) (nA)	I _D (typ) (mA)	Temp Range (°C)	CMR (typ) (dB)	e _n (typical) (nV/√Hz) @ f = 1.0 kHz	Number of Channels	Supply Type	Package	Description
LM201A	±3.0	±22	1.0	0.5	2.0	30	1.8	-25 to +85	96	-	1	Split	DIP-8, SO-8	General Purpose, Precision Non Compensated
LM201AV	±3.0	±22	1.0	0.5	2.0	30	1.8	-40 to +105	96	-	1	Split	DIP-8, SO-8	General Purpose, Precision Non Compensated
LM301A	±3.0	±18	1.0	0.5	7.5	70	1.8	0 to +70	90	-	1	Split	DIP-8, SO-8	General Purpose, Precision Non Compensated
LMV321	2.5	5.5	1	1.0	9	1	140	-40 to +85	65	50	1	Single	SC-70, TSOP-5	Low Voltage, Rail-to-Rail
LMV931	1.8	5	1.5	0.48	6	1	90	-40 to +125	70	50	1	Single	SC-70	Low Voltage, Rail-to-Rail
LMV981	1.8	5	1.5	0.48	6.0	1	0.21	-40 to +125	70	50	1	Single, Split	ULLGA-8	Low Power, Rail-to-Rail
MC33071	3.0 or ±1.5	44	4.5	13	5.0	100	1.6	-40 to +85	97	32	1	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, *Av = -1.0
MC33071A	3.0 or ±1.5	44	4.5	13	3.0	100	1.6	-40 to +85	97	32	1	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, *Av = -1.0
MC33171	3.0 or ±1.5	44 or ±22	1.8	2.1	5.0	20	0.18	-40 to +85	90	32	1	Single, Split	DIP-8, SO-8	Low Power, Single Supply, Two Voltage Ranges
MC33201	1.8 or ±0.9	12	2.2	1.0	6.0	80	0.9	-40 to +105	90	20	1	Single, Split	DIP-8, SO-8	Low Voltage, Rail-to-Rail
MC33201V	1.8 or ±0.9	12	2.2	1.0	6.0	80	0.9	-55 to +125	90	20	1	Single, Split	DIP-8, SO-8	Low Voltage, Rail-to-Rail, Extended Temp. Range
MC33501	1.0 or ±0.5	7.0 or ±3.5	4 @ V _S = 5	3.0	5.0	0.04 pA	1.2 @ V _S = 1 V	-40 to +105	75	30	1	Single, Split	TSOP-5	One Volt SMARTMOS™, Rail-to-Rail
MC33503	1.0 or ±0.5	7.0 or ±3.5	4 @ V _S = 5	3.0	5.0	0.04 pA	1.2 @ V _S = 1 V	-40 to +105	75	30	1	Single, Split	TSOP-5	One Volt SMARTMOS, Rail-to-Rail

SINGLE OPERATIONAL AMPLIFIERS (continued)

Device Name	V _{cc} (min) (V)	V _{cc} (max) (V)	GBW (typ) (MHz)	Slew Rate (typ) (V/μs)	V _{io} (max @ 25°C, V _s = 5.0 V) (mV)	I _{IB} (typ) (nA)	I _D (typ) (mA)	Temp Range (°C)	CMR (typ) (dB)	e _n (typical) (nV/√Hz) @ f = 1.0 kHz	Number of Channels	Supply Type	Package	Description
MC34071	3.0 or ±1.5	44	4.5	13	5.0	100	1.6	0 to +70	97	32	1	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, *Av = -1.0
MC34071A	3.0 or ±1.5	44	4.5	13	3.0	100	1.6	0 to +70	97	32	1	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, *Av = -1.0
NCS2001	0.9 or ±0.45	7.0 or ±3.5	1.4	1.6	6.0	10 pA	0.80	-40 to +105	70	100	1	Single, Split	TSOP-5, SC70-5	One Volt, CMOS Rail-to-Rail
NCS2002	0.9 or ±0.45	7.0 or ±3.5	0.8	1.2	6.0	10 pA	0.80	-40 to +105	82	100	1	Single, Split	TSOP-6	One Volt, CMOS Rail-to-Rail with Enable
NCS7101	1.8 or ±0.9	10 or ±5.0	1.0	1.2	7.0	1.0 pA	1.1	-40 to +85	65 (min)	140	1	Single, Split	TSOP-5	Low Voltage, Rail-to-Rail
NCV2002	0.9 or ±0.45	7.0 or ±3.5	0.8	1.2	6.0	10 pA	0.80	-40 to +125	82	100	1	Single, Split	TSOP-6	One Volt, CMOS Rail-to-Rail with Enable
NE5230	±0.9 or 1.8	±7.5 or 15	0.6	0.25	3.0	40	0.6	0 to +70	95	30	1	Single, Split	SO-8, PDIP-8	Single Low Voltage Op Amp
NE5534	±3.0	±20	10	13	4.0	500	4.0	0 to +70	100	4.0	1	Single, Split	SO-8, PDIP-8	Single Low Noise Op Amp
NE5534A	±3.0	±20	10	13	4.0	500	4.0	0 to +70	100	3.5	1	Single, Split	SO-8, PDIP-8	Single Low Noise Op Amp
SA5230	±0.9 or 1.8	±7.5 or 15	0.6	0.25	3.0	40	0.6	-40 to +85	95	30	1	Single, Split	SO-8, PDIP-8	Single Low Voltage Op Amp
SA5534	±3.0	±20	10	13	4.0	500	4.0	-40 to +85	100	4.0	1	Single, Split	PDIP-8	Single Low Noise Op Amp
SA5534A	±3.0	±20	10	13	4.0	500	4.0	-40 to +85	100	3.5	1	Single, Split	SO-8, PDIP-8	Single Low Noise Op Amp
SE5534	±3.0	±20	10	13	2.0	400	4.0	-55 to +125	100	4.0	1	Single, Split	PDIP-8	Single Low Noise Op Amp
SE5534A	±3.0	±20	10	13	2.0	400	4.0	-55 to +125	100	3.5	1	Single, Split	PDIP-8	Single Low Noise Op Amp

DUAL OPERATIONAL AMPLIFIERS

Device Name	V _{CC} (min) (V)	V _{CC} (max) (V)	G _{BW} (typ) (MHz)	Slew Rate (typ) (V/μs)	V _{IO} (max @ 25°C, V _S = 5.0 V) (mV)	I _{IB} (typ) (nA)	I _D * (typ) (mA)	Temp Range (°C)	CMR (typ) (dB)	e _n (typical) (nV/√Hz) @ f = 1.0 kHz	Number of Channels	Supply Type	Package	Description
LM258	3.0 or ±1.5	32 or ±18	1.0	0.6	5.0	45	0.7	-25 to +85	85	-	2	Single, Split	DIP-8, SO-8, Micro8	Low Noise
LM358	3.0 or ±1.5	32 or ±18	1.0	0.6	7.0	45	0.7	0 to +70	70	-	2	Single, Split	DIP-8, SO-8, Micro8	Low Noise
LMV358	2.7	5	1	1	9.0	1	140	-40 to +85	65	50	2	Single	Micro8, SOIC-8	Low Voltage, Rail-to-Rail
LM833	±2.5	36	15	7.0	5.0	300	4.0	-40 to +85	100	4.5	2	Single, Split	DIP-8, SO-8	Low Noise
LM2904	3.0 or ±1.5	26 or ±13	1.0	0.6	7.0	45	0.7	-40 to +105	70	-	2	Single, Split	DIP-8, SO-8, Micro8	Low Power
LM2904V	3.0 or ±1.5	26 or ±13	1.0	0.6	7.0	45	0.7	-40 to +125	70	-	2	Single, Split	DIP-8, SO-8, Micro8	Low Power
MC33072	3.0 or ±1.5	44 or ±22	4.5	13	5.0	100	3.2	-40 to +85	97	32	2	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, *Av = -1.0
MC33072A	3.0 or ±1.5	44 or ±22	4.5	13	3.0	100	3.2	-40 to +85	97	32	2	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, *Av = -1.0
MC33077	±2.5	±18	37	11	1 @ V _S = ±15 V	280	3.5	-40 to +85	107	4.4	2	Split	DIP-8, SO-8	Low Noise
MC33078	±5.0	±18	16	7.0	2.0	300	4.1	-40 to +85	100	4.5	2	Split	DIP-8, SO-8	Low Noise
MC33172	3.0 or ±1.5	44 or ±22	1.8	2.1	5.0	20	0.36	-40 to +85	90	32	2	Single, Split	DIP-8, SO-8	Low Power, Single Supply, Two Voltage Ranges
MC33172V	3.0 or ±1.5	44 or ±22	1.8	2.1	5.0	20	0.36	-40 to +105	90	32	2	Single, Split	SO-8	Low Power, Single Supply, Two Voltage Ranges, Extended Temp. Range
MC33178	±2.0	±18	5.0	2.0	3.0	100	0.85	-40 to +85	110	7.5	2	Split	DIP-8, SO-8	High Output Current, Low Power, Low Noise

*I_D typical for total device (all channels)

DUAL OPERATIONAL AMPLIFIERS (continued)

Device Name	V _{CC} (min) (V)	V _{CC} (max) (V)	GBW (typ) (MHz)	Slew Rate (typ) (V/μs)	V _{IO} (max @ 25°C, V _S = 5.0 V) (mV)	I _B (typ) (nA)	I _B * (typ) (mA)	Temp Range (°C)	CMR (typ) (dB)	e _n (typical) (nV/√Hz) @ f = 1.0 kHz	Number of Channels	Supply Type	Package	Description
MC33202	1.8 or ±0.9	12 or ±6	2.2	1.0	8.0	80	1.8	-40 to +105	90	20	2	Single, Split	DIP-8, SO-8, Micro8™	Low Voltage, Rail-to-Rail
MC33202V	1.8 or ±0.9	12 or ±6	2.2	1.0	8.0	80	1.8	-55 to +125	90	20	2	Single, Split	DIP-8, SO-8	Low Voltage, Rail-to-Rail, Extended Temp. Range
MC33272A	3.0 or ±1.5	36 or ±18	24	10	1 @ V _S = ±15 V 2 @ V _S = 5.0 V	300	4.30	-40 to +85	100	18	2	Single, Split	DIP-8, SO-8	Single Supply, High SR, Low Input Offset Voltage
MC33502	1.0	7.0	5.0	3.0	5.0	0.04 pA	3.3	-40 to +105	75	30	2	Single, Split	DIP-8, SO-8	One Volt SMARTMOS, Rail-to-Rail
MC34072	3.0 or ±1.5	44 or ±22	4.5	13	5.0	100	3.2	0 to +70	97	32	2	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, *Av = -1.0
MC34072A	3.0 or ±1.5	44 or ±22	4.5	13	3.0	100	3.2	0 to +70	97	32	2	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, *Av = -1.0
MC34072V	3.0 or ±1.5	44 or ±22	4.5	13	5.0	100	3.2	-40 to +125	97	32	2	Single, Split	DIP-8, SO-8	High SR, Wide BW, Single Supply, Extended Temp. Range, *Av = -1.0
NE592	-8.0	+8.0	90	-	-	9.0 μA	18	0 to +70	86	-	2	-	SO-8, 14 PDIP-8, 14	Video Amplifier
NE5532/A	±3.0	±20	10	9.0	4.0 @ ±15 V	200	8.0	0 to +70	100	8.0	2	Split	DIP-8, SO-8, SO-16W	Low Noise
SA5532	±3.0	±20	10	9.0	4.0 @ ±15 V	200	8.0	-40 to +85	100	8.0	2	Split	DIP-8	Low Noise
SE5532/A	±3.0	±20	10	9.0	2.0 @ ±15 V	200	8.0	-55 to 125	100	8.0	2	Split	DIP-8, SO-8	Low Noise
TCA0372	5.0 or ±2.5	40 or ±20	1.4	1.4	15 @ ±15 V	100	5.0	-40 to +125	90	22	2	Single, Split	SOP (12+2+2) DIP-8, DIP-16	Power, High Current
TCA0372B	5.0 or ±2.5	40 or ±20	1.4	1.4	15 @ ±15 V	100	5.0	-40 to +125	90	22	2	Single, Split	DIP-8, SO-16W	Power, High Current

*I_B typical for total device (all channels)

QUAD OPERATIONAL AMPLIFIERS

Device Name	V _{CC} (min) (V)	V _{CC} (max) (V)	G _{BW} (typ) (MHz)	Slew Rate (typ) (V/μs)	V _{IO} (max @ 25°C, V _S = 5.0 V) (mV)	I _B (typ) (nA)	I _D * (typ) (mA)	Temp Range (°C)	CMR (typ) (dB)	e _n (typical) (nV/√Hz) @ f = 1.0 kHz	Number of Channels	Supply Type	Package	Description
LM224	3.0 ±1.5	32 ±16	1.0	0.6	5.0	90	-	-25 to +85	85	-	4	Single, Split	DIP-14, SO-14	Low Power
LM324	3.0 ±1.5	32 ±16	1.0	0.6	7.0	90	-	0 to +70	70	-	4	Single, Split	DIP-14, SO-14	Low Power
LMV324	2.5	5.5	1.0	1.0	9.0	1	140	-40 to +85	65	50	4	Single	SO-14, TSSOP-14	Low Voltage, Rail-to-Rail
LM324A	3.0 ±1.5	32 ±16	1.0	0.6	3.0	45	0.7	0 to +70	70	-	4	Single, Split	DIP-14, SO-14	Low Power
LMV824	2.5	5	5.0	2.0	3.5	245	1.3	-40 to +85	90	7.5	4	Single, Split	SO-14, TSSOP-14	Low Power, Rail-to-Rail
LM2902	3.0 ±1.5	26 ±13	1.0	0.6	7.0	90	-	-40 to +105	70	-	4	Single, Split	DIP-14, SO-14	Low Power
LM2902V	3.0 ±1.5	26 ±13	1.0	0.6	7.0	90	-	-40 to +125	70	-	4	Single, Split	DIP-14, SO-14	Low Power, Extended Temp. Range
MC3303	3.0 ±1.5	36 ±18	1.0	0.6	8.0	200	2.8	-40 to +85	90	-	4	Single, Split	DIP-14, SO-14	Low Power
MC33074	3.0 or ±1.5	44 or ±22	4.5	13	5.0	100	6.4	-40 to +85	97	32	4	Single, Split	DIP-14, SO-14, TSSOP-14	High SR, Wide BW, Single Supply, *AV = -1.0
MC33074A	3.0 or ±1.5	44 or ±22	4.5	13	3.0	100	6.4	-40 to +85	97	32	4	Single, Split	DIP-14, SO-14, TSSOP-14	High SR, Wide BW, Single Supply, *AV = -1.0
MC33079	±5.0	±18	16	7.0	2.5	300	8.4	-40 to +85	100	4.5	4	Split	DIP-14, SO-14	Low Noise
MC33174	3.0 or ±1.5	44 or ±22	1.8	2.1	5.0	20	0.72	-40 to +85	90	32	4	Single, Split	DIP-14, SO-14, TSSOP-14	Low Power, Single Supply, Two Voltage Ranges
MC33174V	3.0 or ±1.5	44 or ±22	1.8	2.1	5.0	20	0.72	-40 to +105	90	32	4	Single, Split	DIP-14, SO-14	Low Power, Single Supply, Two Voltage Ranges, Extended Temp. Range
MC33179	±2.0	±18	5.0	2.0	3.0	100	1.7	-40 to +85	110	7.5	4	Split	DIP-14, SO-14	High Output Current, Low Power, Low Noise

*I_D typical for total device (all channels)

QUAD OPERATIONAL AMPLIFIERS (continued)

Device Name	V _{CC} (min) (V)	V _{CC} (max) (V)	GBW (typ) (MHz)	Slew Rate (typ) (V/ μ s)	V _{IO} (max @ 25°C, V _S = 5.0 V) (mV)	I _{IB} (typ) (nA)	I _D * (typ) (mA)	Temp Range (°C)	CMR (typ) (dB)	e _n (typical) (nV/ \sqrt Hz) @ f = 1.0 kHz	Number of Channels	Supply Type	Package	Description
MC33204	1.8 or ± 0.9	12 or ± 6.0	2.2	1.0	10	80	3.6	-40 to +105	90	20	4	Single, Split	DIP-14, SO-14, TSSOP-14	Low Voltage, Rail-to-Rail
MC33204V	1.8 or ± 0.9	12 or ± 6.0	2.2	1.0	10	80	3.6	-55 to +125	90	20	4	Single, Split	DIP-14, SO-14	Low Voltage, Rail-to-Rail, Extended Temp. Range
MC33274A	3.0 or ± 1.5	36 or ± 18	24	10	1.0 @ V _S = ± 15 V 2.0 @ V _S = 5.0 V	300	8.6	-40 to +85	100	18	4	Single, Split	DIP-14, SO-14	Single Supply, High SR, Low Input Offset Voltage
MC3403	3.0 ± 1.5	36 ± 18	1.0	0.6	10	200	2.8	0 to +70	90	-	4	Single, Split	DIP-14, SO-14	Low Power
MC34074	3.0 or ± 1.5	44 or ± 22	4.5	13	5.0	100	6.4	0 to +70	97	32	4	Single, Split	DIP-14, SO-14	High SR, Wide BW, Single Supply, *AV = -1.0
MC34074A	3.0 or ± 1.5	44 or ± 22	4.5	13	3.0	100	6.4	0 to +70	97	32	4	Single, Split	DIP-14, SO-14	High SR, Wide BW, Single Supply, *AV = -1.0
MC34074V	3.0 or ± 1.5	44 or ± 22	4.5	13	5.0	100	6.4	-40 to +125	97	32	4	Single, Split	DIP-14, SO-14	High SR, Wide BW, Single Supply, *AV = -1.0
NCV33274A	3.0 or ± 1.5	36 or ± 18	24	10	3.5 @ V _S = ± 15 V 2.0 @ V _S = ± 5.0 V	300	8.6	-40 to +125	100	18	4	Single, Split	DIP-14, SO-14	Single Supply, High SR, Low Input Offset Voltage

*I_D typical for total device (all channels)

SINGLE COMPARATORS

Device Name	V _{CC} (min)	V _{CC} (max)	V _{IO} (max) (mV)	I _{IO} (max) (nA)	I _{IB} (typ) (nA)	I _q * (typ) (mA)	Temp Range (°C)	Response Time (ns)	Supply Type	Number of Channels	Package	Description
LM211	5.0 or ±2.5	36 or ±15	3.0	10	45	2.4	-25 to +85	200	Single, Split	1	SO-8	Highly Flexible Voltage
LM311	5.0 or ±2.5	36 or ±15	7.5	50	45	2.4	0 to +70	200	Single, Split	1	SO-8, DIP-8	Highly Flexible Voltage
LMV331	2.7	5	9	< 1	< 1	0.06	-40 to +85	600	Single, Split	1	SC-70, TSOP-5	Low Voltage CMOS
NCS2200	0.85 or ±0.425	6.0 or ±3.0	+8.0	-	1.0 pA	10	-40 to +105	700	Single, Split	1	SOT-23-5, DFN-6	Low Voltage CMOS
NCS2201	0.85 or ±0.425	6.0 or ±3.0	+8.0	-	1.0 pA	10	-40 to +105	700	Single, Split	1	SOT-23-6	Low Voltage CMOS with Enable
NCS2202	0.85 or ±0.425	6.0 or ±3.0	+8.0	-	1.0 pA	10	-40 to +105	700	Single, Split	1	SOT-23-5	Low Voltage CMOS
NCS2203	0.85 or ±0.425	6.0 or ±3.0	+8.0	-	1.0 pA	10	-40 to +105	700	Single, Split	1	SOT-23-6	Low Voltage CMOS with Enable

DUAL COMPARATORS

Device Name	V _{CC} (min)	V _{CC} (max)	V _{IO} (max) (mV)	I _{IO} (max) (nA)	I _{IB} (typ) (nA)	I _q * (typ) (mA)	Temp Range (°C)	Response Time (ns)	Supply Type	Number of Channels	Package	Description
LM293	2.0 or ±1.0	36 or ±18	5.0	50	25	0.4	-25 to +85	1300	Single, Split	2	SO-8	Low Offset Voltage
LM393	2.0 or ±1.0	36 or ±18	5.0	50	25	0.4	0 to +70	1300	Single, Split	2	SO-8, DIP-8	Low Offset Voltage
LMV393	2.7	5	9	< 1	< 1	0.1	-40 to +85	600	Single, Split	2	Micro8, SO-8, UDFN-8	Low Voltage CMOS
LM2903	2.0 or ±1.0	36 or ±18	7.0	50	25	0.4	-40 to +105	1500	Single, Split	2	SO-8, DIP-8	Low Offset Voltage
LM2903V	2.0 or ±1.0	36 or ±18	7.0	50	25	0.4	-40 to +125	1500	Single, Split	2	SO-8, DIP-8	Low Offset Voltage

*I_q typical for total device (all channels)

QUAD COMPARATORS

Device Name	V _{cc} (min)	V _{cc} (max)	V _{io} (max) (mV)	I _o (max) (nA)	I _B (typ) (nA)	I _q * (typ) (mA)	Temp Range (°C)	Response Time (ns)	Supply Type	Number of Channels	Package	Description
LM239	3.0 or ±1.5	36 or ±18	5.0	50	25	0.8	-25 to +85	1300	Single, Split	4	SO-14, DIP-14	TTL and CMOS Compatible
LM339	3.0 or ±1.5	36 or ±18	5.0	50	25	0.8	0 to +70	1300	Single, Split	4	SO-14, DIP-14	TTL and CMOS Compatible
LMV339	2.7	5	9	< 1	< 1	0.17	-40 to +85	600	Single, Split	4	SO-14, TSSOP-14	Low Voltage CMOS
LM2901	3.0 or ±1.5	36 or ±18	7.0	50	25	0.8	-40 to +105	1300	Single, Split	4	SO-14, DIP-14	TTL and CMOS Compatible
LM2901V	3.0 or ±1.5	36 or ±18	7.0	50	25	0.8	-40 to +125	1300	Single, Split	4	SO-14, DIP-14	TTL and CMOS Compatible
MC3302	3.0 or ±1.5	30 or ±15	20	100	25	0.8	-40 to +85	1300	Single, Split	4	SO-14, DIP-14	TTL and CMOS Compatible

*I_q typical for total device (all channels)

AUDIO AMPLIFIERS

Product	Class	Output	Efficiency Typ (%)	t _{on} Typ (ms)	THD + N Typ (%)	I _Q Typ (mA)	I _{SD} Typ (mA)	Package
NCP2809	AB	-	63	285	-	1.5	10	Micro-10, UDFN-10
NCP2811	AB	-	-	1	0.01	6	10	TSSOP-14, Flip-Chip-12, WQFN-12
NCP2820	D	Differential	-	-	0.05	2.2	300	Flip-Chip-9, DFN-8
NCP2823	-	BTL	92	-	-	-	-	Flip-Chip-9
NCP2830	D	BTL	89	0.2	0.03	7	10	UQFN-20
NCP2890	AB	BTL	63	285	0.02	1.5	10	Flip-Chip-9, Micro8™
NCP2892	AB	BTL	63	90	0.01	1.5	10	Flip-Chip-9
NCP2990	AB	BTL	63	70	0.01	1.7	10	Flip-Chip-9
NCP2991	AB	BTL	64	30	0.015	1.8	20	Flip-Chip-9
NCP4894	AB	Differential	64	140	0.01	1.9	20	Micro-10, Flip-Chip-9, DFN-10
NCS2211	AB	BTL	63	0.001	0.2	20	1000	SOIC-8, DFN-9
NLMD5820	D	Differential	87	0	0.05	2.2	300	UDFN-16

TRANSCONDUCTANCE AMPLIFIERS

Device Name	Channels	V _{CC} (typ) (V)	T _A (min) (°C)	T _A (max) (°C)	g _M (typ) (μmho)	V _{IO} (typ) (mV)	I _{IB} (typ) (μA)	S _R (typ) (V/μs)	B _W (typ) (MHz)	e _n (typ) (pA/Hz)	THD (typ) (%)	Package
AU5517	2	44	-40	+125	9600	0.4	0.4	50	2	25	0.5	SOIC-16
NE5517A	2	44	0	+70	9600	0.4	0.4	50	2	25	0.5	PDIP-16
NE5517	2	44	0	+70	9600	0.4	0.4	50	2	25	0.5	SOIC-16, PDIP-16

VIDEO AMPLIFIERS

Device Name	Channels	Filter Order	V _{CC} (V)	I _{CC} (mA)	G (dB)	B _w (MHz)	Attenuation (dB)	ΔG _D (ns)	Temperature Range (°C)	Package
NCS2566	6	6	5	60	6 ± 0.2	/34	50 @ 27 MHz; 43 @ 74.25 MHz	10 for HD; 20 for SD	-40 to +85	TSSOP-20
NCS2554	4	6	5	40	6 ± 0.2		50 @ 27 MHz	20	-40 to +85	TSSOP-14
NCS2564	4	6	5	40	6 ± 0.2	8/34	50 @ 27 MHz; 43 @ 74.25 MHz	10 for HD; 20 for SD	-40 to +85	TSSOP-14
NCS2553	3	6	5	23	6 ± 0.2	9	45 @ 27 MHz	27 for SD	-40 to +85	SOIC-8
NCS2563	3	6	5	22	6 ± 0.2	33	36 @ 74.25 MHz	6 for HD	-40 to +85	SOIC-8
NCS2561	1	2	2.7 – 3.3	6	6 ± 0.2	9.3	22 @ 27 MHz	15 for SD	-40 to +125	SC-88
NE592D14	1	-	8	18	100	90	-	-	0 to +70	SOIC-14
NE592D8	1	-	8	18	400	40	-	-	0 to +70	SOIC-8
NE592N14	1	-	8	18	100	90	-	-	0 to +70	PDIP-14
NE592N8	1	-	8	18	400	40	-	-	0 to +70	PDIP-8

COMPANDORS

Device Name	Channels	V _{CC} (min) (V)	V _{CC} (max) (V)	I _{CC} (max) (V)	THD (typ) (%)	e _n (typ) (μV)	V _{REF} (V)	T _A (min) (°C)	T _A (max) (°C)	Package
NE570	2	6	24	4.3	0.3	20	1.8	0	70	SO-16 WB
SA571	2	6	18	4.3	0.5	20	1.8	-40	85	SO-16 WB, PDIP-16
SA572D	2	6	22	6.3	0.05	6	2.5	-40	85	SO-16 WB, TSSOP-16, PDIP-16
SA575D	2	3	7	4.2	0.12	6		-40	85	SOIC-20 WB, TSSOP-20, PDIP-20

Analog Switches

Analog Switches

Table of Contents

	Page
Audio Switches	36
Data Switches	37
Signal Switches	37
Video Switches	40

ON Semiconductor Selector Guide – Analog Switches

AUDIO SWITCHES

Device	Configuration	THD (%)	R _{on} Max (Ω)	I _{lkg} Max (μA)	V _{CC} Min (V)	V _{CC} Max (V)	Packages
NLAS3699B	Dual DPDT	0.01	0.75	1	1.65	4.5	QFN-16
NLAS3699	Dual DPDT	0.01	0.75	1	1.65	3.6	QFN-16
NLAS3799BL	Dual DPDT	0.042	0.4	1	1.65	4.3	WQFN-16
NLAS3799B	Dual DPDT	0.042	0.4	1	1.65	4.3	UQFN-16, WQFN-16
NLAS3799L	Dual DPDT	0.042	0.5	1	1.65	3.6	WQFN-16
NLAS3799	Dual DPDT	0.042	0.5	1	1.65	3.6	WQFN-16
NLAS3899B	Dual DPDT	0.007	4	1	1.65	4.3	WQFN-16
NLAS4157	SPDT	0.012	1	1	1.65	5.5	SC-88/SC70-6/SOT-363
NLAS4684	Dual SPDT	0.14	0.5	1	1.8	5.5	DFN-10, FLIP-CHIP-10, Micro-10
NLAS4783B	Triple SPDT	0.008	1.2	1	1.65	4.5	QFN-16
NLAS4783	Triple SPDT	0.008	1.2	1	1.65	3.6	QFN-16
NLAS5113	SPST	0.08	1.1	2	1.65	4.5	UDFN-6, SC-88
NLAS5123	SPDT	0.012	1	1	1.65	5.5	UDFN-6, WDFN-6
NLAS5157	SPDT	0.02	0.5	1	1.65	4.3	UDFN-6
NLAS5213A	Dual SPST	-	1.3	1	1.65	4.5	UDFN-8, US-8
NLAS5213B	Dual SPST	-	1.3	1	1.65	4.5	UDFN-8, US-8
NLAS52231	Dual SPDT	0.03	0.5	1	1.65	4.5	UQFN-10
NLAS5223BL	Dual SPDT	0.08	0.5	1	1.65	4.5	WQFN-10
NLAS5223B	Dual SPDT	0.08	0.5	1	1.65	4.5	UQFN-10, WQFN-10
NLAS5223	Dual SPDT	0.12	0.5	1	1.65	3.6	WQFN-10
NLMD5820	Amp+DPST	0.08	0.5	2	1.65	4.2	UDFN-16
NS5S1153	DPDT	0.01	4.6	35	2.7	5.0	UQFN-10

DATA SWITCHES

Device	Data Type	Configuration	C _{on} Typ (pF)	Bandwidth Typ (MHz)	R _{on} Max (Ω)	I _{lkg} Max (μA)	V _{cc} Min (V)	V _{cc} Max (V)	Packages
NLAS3899B	SIM	Dual DPDT	20	280	4	1	1.65	4.3	WQFN-16
NLAS4717EP	USB	DPDT	38	90	4.5	1	1.8	5.5	WQFN-10, FLIP-CHIP-10
NLAS4717	USB	DPDT	110	40	4.5	1	1.8	5.5	FLIP-CHIP-10, Micro-10
NLAS7213	USB HS	DPST	5	1100	10	1	1.65	4.5	UQFN-8
NLAS7222A	USB HS	DPDT	7	500	9	1	3	3.6	UQFN-10, WQFN-10
NLAS7222B	USB HS	DPDT	8	500	8	1	1.65	4.5	UQFN-10
NLAS7222C	USB HS	DPDT	10	500	8	1	1.65	4.5	UQFN-10
NLAS7223B	USB HS	DPDT	7.5	900	7.5	1	1.65	4.5	UQFN-10
NLAS7223C	USB HS	DPDT	7.5	900	7.5	1	1.65	4.5	UQFN-10
NLAS8252	USB	DP3T	16	200	6	1	1.65	4.5	UQFN-12
NLAS7242	USB	DPDT	7.5	900	7.5	1	1.65	4.5	UQFN-10
NS5S1153	USB/Audio	DPDT	6.9	900	4.6	35	2.7	5.0	UQFN-10

SIGNAL SWITCHES

Device	Configuration	Number of Elements	Channels	r _{on} Max (Ω)	I _{lkg} Max (μA)	V _{cc} Min (V)	V _{cc} Max (V)	Package
MC14016B	Quad SPST	4	1	660	0.1	3	18	PDIP-14, SOIC-14
MC14051B	SP8T	1	8	500	0.1	3	18	PDIP-16, SOEIAJ-16, SOIC-16, TSSOP-16
MC14052B	DP4T	2	4	500	0.1	3	18	PDIP-16, SOEIAJ-16, SOIC-16, TSSOP-16
MC14053B	Triple SPDT	3	2	500	0.1	3	18	PDIP-16, SOEIAJ-16, SOIC-16, TSSOP-16
MC14066B	Quad SPST	4	1	500	0.1	3	18	PDIP-14, SOEIAJ-14, SOIC-14, TSSOP-14
MC14067B	SP16T	1	16	500	0.1	3	18	SOIC-24
MC14551B	4PDT	4	2	500	0.1	3	18	PDIP-16, SOEIAJ-16, SOIC-16
MC74HC4051A	SP8T	1	8	190	0.2	2	12	PDIP-16, SO-16 WB, SOEIAJ-16, SOIC-16, TSSOP-16
MC74HC4067A	SP16T	1	16	250	0.1	2	6	TSSOP-24, SOIC-24
MC74HC4052A	DP4T	2	4	190	0.1	2	12	PDIP-16, SO-16 WB, SOEIAJ-16, SOIC-16, TSSOP-16

ON Semiconductor Selector Guide – Analog Switches

SIGNAL SWITCHES

Device	Configuration	Number of Elements	Channels	r_{on} Max (Ω)	I_{lkg} Max (μA)	V_{cc} Min (V)	V_{cc} Max (V)	Package
MC74HC4053A	Triple SPDT	3	2	190	0.1	2	12	PDIP-16, SO-16 WB, SOEIAJ-16, SOIC-16, TSSOP-16
MC74HC4066A	Quad SPST	4	1	120	0.1	2	12	PDIP-14, SOEIAJ-14, SOIC-14, TSSOP-14
MC74HC4316A	Quad SPST	4	1	160	0.1	2	6	PDIP-16, SOEIAJ-16, SOIC-16
MC74HC4851A	SP8T	1	8	550	0.1	2	6	PDIP-16, SO-16 WB, SOIC-16, TSSOP-16
MC74HC4852	DP4T	2	4	550	0.1	2	6	PDIP-16, SO-16 WB, SOIC-16, TSSOP-16
M74HCT4051A	SP8T	1	8	160		4.5	5.5	TSSOP-16, SOIC-16
M74HCT4052A	DP4T	2	4	160		4.5	5.5	TSSOP-16, SOIC-16
M74HCT4053A	Triple SPDT	2	4	160		4.5	5.5	TSSOP-16, SOIC-16
M74HCT4851A	SP8T	1	8	550		4.5	5.5	TSSOP-16, SOIC-16
MC74HCT4851A	SP8T	1	8	550		4.5	5.5	TSSOP-16, SOIC-16
MC74HCT4852A	DP4T	2	4	550		4.5	5.5	TSSOP-16, SOIC-16
MC74LVX4066	Quad SPST	4	1	25	0.1	2	6	SOEIAJ-14, SOIC-14, TSSOP-14
MC74LVX8051	SP8T	1	8	30	0.2	2	6	SOEIAJ-16, SOIC-16, TSSOP-16
MC74LVX8053	Triple SPDT	3	2	30	0.1	2	6	SOEIAJ-16, SOIC-16, TSSOP-16
MC74LVXT4066	Quad SPST	4	1	25	0.1	2	5.5	SOEIAJ-14, SOIC-14, TSSOP-14
MC74LVXT8051	SP8T	1	8	30	0.1	2	6	SOEIAJ-16, SOIC-16, TSSOP-16
MC74LVXT8053	Triple SPDT	3	2	30	0.1	2	6	SOEIAJ-16, SOIC-16, TSSOP-16
MC74VHC1G66	Single SPST	1	1	45	0.1	2	5.5	UDFN-6, SC-88A, SC-70-5, TSOP-5 / SOT23-5
MC74VHC1GT66	Single SPST	1	1	45	0.1	2	5.5	SC-88A, SC-70-5, TSOP-5 / SOT23-5
MC74VHC4051	SP8T	1	8	160	0.1	2	6	SOEIAJ-16, SOIC-16, TSSOP-16
MC74VHC4066	Quad SPST	4	1	120	0.1	2	12	SOEIAJ-14, SOIC-14, TSSOP-14
NL7WB66	Dual SPST	2	1	11	0.1	1.65	5.5	US-8
NLAS1053	Single SPDT	1	2	28	1	2	5.5	US-8
NLAS2066	Dual SPST	2	1	11	0.1	1.65	5.5	US-8
NLAS3158	Dual SPDT	2	2	6	1	1.65	5.5	DFN-12
NLAS323	Dual SPST	2	1	30	0.1	2	5.5	US-8
NLAS324	Dual SPST	2	1	30	0.1	2	5.5	US-8

SIGNAL SWITCHES

Device	Configuration	Number of Elements	Channels	r_{on} Max (Ω)	I_{lk} Max (μA)	V_{CC} Min (V)	V_{CC} Max (V)	Package
NLAS325	Dual SPST	2	1	30	0.2	2	5.5	US-8
NLAS3799	Dual DPDT	4	2	0.5	1	1.65	3.6	QFN-16
NLAS3899B	Dual DPDT	4	2	4	1	1.65	4.3	QFN-16
NLAS4051	SP8T	1	8	37	0.1	2.5	5.5	SOIC-16, TSSOP-16
NLAS4051S	SP8T	1	8	26	0.1	2.5	5.5	TSSOP-16
NLAS4053	Triple SPDT	3	2	37	0.1	2.5	5.5	SOIC-16, TSSOP-16
NLAS44599	Dual DPDT	4	2	30	0.2	2	5.5	QFN-16
NLAS4501	Single SPST	1	1	30	0.1	2	5.5	SC-88A, SC-70-5, TSOP-5 / SOT23-5
NLAS4599	Single SPDT	1	2	30	0.1	2	5.5	SC-88/SC70-6, TSOP-6
NLAS4717EP	Dual SPDT	2	2	4.5	1	1.8	5.5	FLIP-CHIP-10, WQFN-10
NLAS5113	SPST	1	1	1.1	2	1.65	4.5	UDFN-6, SC-88/SC-70-6
NLAS5123	Single SPDT	1	2	1	1	1.65	5.5	UDFN-6, WDFN-6
NLAS5223L	Dual SPDT	2	2	0.5	1	1.65	3.6	WQFN-10
NLAS5223	Dual SPDT	2	2	0.5	1	1.65	3.6	WQFN-10
NLAS9431	Dual DPDT	4	2	30	0.2	2	5.5	QFN-16
NLASB3157	Single SPDT	1	2	7	1	1.65	5.5	SC-88/SC-70-6, WDFN-6
NLAST4051	SP8T	1	8	37	0.1	2.5	5.5	TSSOP-16
NLAST4053	Triple SPDT	3	2	26	1	2.5	5.5	TSSOP-16
NLAST44599	Dual DPDT	4	2	30	0.2	2	5.5	QFN-16
NLAST4501	Single SPST	1	1	30	0.1	2	5.5	SC-88A, SC-70-5, TSOP-5 / SOT23-5
NLAST4599	Single SPDT	1	2	30	0.1	2	5.5	SC-88/SC-70-6, TSOP-6
NLAST9431	Dual DPDT	4	2	30	0.2	2	5.5	QFN-16
N55B1G384	Single SPST	1	1	7	1	2	5.5	SC-88A, SC-70-5, TSOP-5 / SOT23-5
N55B1G385	Single SPST	1	1	7	1	2	5.5	SC-88A, SC-70-5, TSOP-5 / SOT23-5

ON Semiconductor Selector Guide – Analog Switches

VIDEO SWITCHES

Device	Number of Inputs	Number of Outputs	B _w Typ (MHz)	I _{cch} Typ (mA)	V _{cc} Min (V)	V _{cc} Max (V)	T _A Min (°C)	T _A Max (°C)	Package
NCS6415	8	6	20	30	8	11	0	70	SOIC-20
NCS6416	6	6	15	30	4.75	5.25	0	70	SOIC-20
NCS6433	4	8	570		4	5.5	-40	85	TSSOP-16, SOIC-16

Bipolar Transistors









Bipolar Transistors

Table of Contents

	Page
Bipolar Power Transistors	44
Discrete Transistors	45
Darlington Transistors	50
Audio	52
Electronic Lamp Ballasts	54
Small-Signal Bipolar Transistors	55
General-Purpose Transistors	55
General-Purpose Multiple Transistors	60
Low Noise and Good h_{FE} Linearity	61
Darlington Transistors	61
High Current Transistors	62
High Voltage Transistors	64
RF Transistors	65
Switching Transistors	65
Multiple Switching Transistors	66
Digital Transistors (Bias Resistor Transistors)	67
Dual Digital Transistors	
(Bias Resistor Transistors)	69
Combinational Digital Transistors	
(Bias Resistor Transistors)	70
Complex Digital Transistors	72
Low Saturation Voltage Transistors	73
Load Switch Transistors	74

BIPOLAR TRANSISTORS SELECTOR GUIDE

SELECTION BY PACKAGE


Package	I_C Range (Amps)	V_{CE} Range (Volts)	P_D (Watts)
 SOT-223	0.5–3.0	30–300	2.75–3.0
 DPAK	0.5–10	25–450	12.5–25
 D ² PAK	6.0–10	80–350	50–75
 DPAK	0.5–10	25–450	12.5–25
 TO-225AA	0.3–5.0	25–500	12.5–50
 TO-220AB	0.5–15	32–400	30–150
 Isolated TO-220	1.0–10	60–450	28–45
 TO-218	10–25	60–350	80–150
 TO-247	8.0–30	150–250	100–200
 TO-3P	15–20	150–260	150–200
 TO-264	15–20	250–350	200–250
 TO-264 5-Lead	15	260	200
 TO-3 (TO-204AA) 40 Mil Pins	4.0–30	40–250	115–250
 TO-3 (TO-204AE) 60 Mil Pins	40–60	60–250	150–300

DISCRETE TRANSISTORS

I _C Cont Amps Max	V _{CEO(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	f _T MHz Min	P _D (Case) Watts @ 25°C	Package	
		NPN	PNP						
0.5	300		MMJT350T1	30/240	0.05	30	2.75	 SOT-223	
2.0	100	NSS1C201MZ4	NSS1C200MZ4	120/360	0.5	100	2.0		
3.0	40		NJT4030P	200/400	1.0	160 typ	2.0		
		NJT4031N		200/400	1.0	215	2.0		
	40	NSS40301MZ4	NSS40300MZ4	200/500	1.0	150	2.0		
6.0	60	NSS60601MZ4	NSS60600MZ4	120/360	1.0	100	2.0		
0.5	300	MJD340T4	MJD350T4	30/240	0.05	30	15	 DPAK	
1.0	250	MJD47T4		30/150	0.3	10	15		
	350		MJD5731T4	10 min	1.0	10	15		
	400	MJD50T4		30/150	0.3	10	15		
2.0	50	NJD2873T4		40 min	2.0	30	12.5		
3.0	40	MJD31T4	MJD32T4	10 min	1.0	3.0	15		
	100	MJD31CT4	MJD32CT4	10 min	1.0	3.0	15		
4.0	45		MJD148T4	50 min	2.0	3.0	20		
	100	MJD243T4	MJD253T4	40/180	0.2	40	12.5		
5.0	25	MJD200T4	MJD210T4	45/180	2.0	65	12.5		
6.0	100	MJD41CT4	MJD42CT4	15/75	3.0	3.0	20		
8.0	80	MJD44H11T4	MJD45H11T4	40 min	4.0	50 typ	20		
10	60	MJD3055T4	MJD2955T4	20/100	4.0	2.0	20		
6.0	100	MJB41CT4	MJB42CT4	15/75	3.0	3.0	65	 D²PAK	
8.0	80	MJB44H11T4	MJB45H11T4	40/100	4.0	40	50		
0.3	350	MJE3439		40/160	0.02	15	15	 TO-225AA	
0.5	200	MJE344		30/300	0.05	15	20.8		
	250	2N5655		30/250	0.1	10	20		
	300	MJE340	MJE350	30/240	0.05	30	20.8		
	350		2N5657		30/250	0.1	10		20
			BD159		30/240	0.05	30		20
1.0	40	2N4921	2N4918	20/100	0.5	3.0	30		
	60	2N4922	2N4919	20/100	0.5	3.0	30		
	80	2N4923	2N4920	20/100	0.5	3.0	30		
1.5	45	BD135	BD136	40/250	0.15	50	12.5		
	60	BD137	BD138	40/250	0.15	50	12.5		
	80	BD139	BD140	40/250	0.15	50	12.5		
2.0	45		BD234	25 min	1.0	3.0	25		
	80	BD237		25 min	1.0	3.0	25		
3.0	40	MJE180	MJE170	50/250	0.1	50	12.5		
	60	MJE181	MJE171	50/250	0.1	50	12.5		
	80		BD179	BD180	40/250	0.15	3.0		25
			MJE182	MJE172	50/250	0.1	50	12.5	

†Style 3.

DISCRETE TRANSISTORS (continued)

I _C Cont Amps Max	V _{CEO(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	f _T MHz Min	P _D (Case) Watts @ 25°C	Package
		NPN	PNP					
4.0	32	BD435	BD436	50 min	2.0	3.0	36	 TO-225AA
			MJE371	40 min	1.0	3.0	40	
	40	2N5190		25 min	1.5	2.0	40	
		BD437	BD438	40 min	2.0	3.0	36	
	60	BD439	BD440	25 min	2.0	3.0	36	
		BD787	BD788	20 min	2.0	50	15	
		2N5191	2N5194	25/100	1.5	2.0	40	
	80	2N5192	2N5195	25/100	1.5	2.0	40	
BD441		BD442	15 min	2.0	3.0	36		
100	MJE243	MJE253	40/120	0.2	40	15		
5.0	25	MJE200	MJE210	45/180	2.0	65	15	
1.0	60	TIP29A		15/75	1.0	3.0	30	 TO-220AB
		TIP29B		15/75	1.0	3.0	30	
	80	TIP29C	TIP30C	15/75	1.0	3.0	30	
	250	TIP47		30/150	0.3	10	40	
		TIP48	MJE5730	30/150	0.3	10	40	
	350		MJE5731	30/150	0.3	10	40	
	375		MJE5731A	30/150	0.3	10	40	
	400	TIP50		30/150	0.3	10	40	
2.0	450/1000	BUX85		30	0.1	4.0	50	
		MJE18002		14/34	0.2	12 typ	40	
3.0	40	TIP31	TIP32	25 min	1.0	3.0	40	
		TIP31A	TIP32A	25 min	1.0	3.0	40	
	80		BD242B	25 min	1.0	3.0	40	
		TIP31B	TIP32B	25 min	1.0	3.0	40	
	100	BD241C	BD242C	25 min	1.0	3.0	40	
		TIP31C	TIP32C	25 min	1.0	3.0	40	
4.0	80	D44C12	D45C12	40/120	0.2	40 typ	30	
		MJE15034	MJE15035	10 min	2.0	30	50	
	400/700	MJE13005		6/30	3.0	4.0	60	
	500/800	BUH50		10 typ	2.0	4.0	50	
5.0	400/700	BUL45		14/34	0.3	12 typ	75	
		BUL45D2*		22 min	0.8	13 typ	75	
	450/1000	MJE18004		14/34	0.3	13	75	

NOTE: When two voltages are given, the format is V_{CEO(sus)}/V_{CES}.

*D2 suffix indicates transistor with built-in C-E freewheeling diode and antisaturation network.

DISCRETE TRANSISTORS (continued)



I _C Cont Amps Max	V _{CEO(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	f _T MHz Min	P _D (Case) Watts @ 25°C	Package
		NPN	PNP					
6.0	40		TIP42	15/75	3.0	3.0	65	
	60	TIP41A	TIP42A	15/75	3.0	3.0	65	
	80	TIP41B	TIP42B	15/75	3.0	3.0	65	
			BD244B	15 min	3.0	3.0	65	
	100	BD243C	BD244C	15 min	3.0	3.0	65	
		TIP41C	TIP42C	15/75	3.0	3.0	65	
	450/1000	MJE18006		14/34	0.5	14 typ	100	
7.0	30	2N6288	2N6111	30/150	3.0	4.0	40	
	50		2N6109	30/150	2.5	4.0	40	
	70	2N6292	2N6107	30/150	2.0	4.0	40	
	200	BU406		30 min	1.5	10	60	
8.0	120	MJE15028	MJE15029	20 min	4.0	30	50	
	150	MJE15030	MJE15031	20 min	4.0	30	50	
	250	MJE15032	MJE15033	10 min	2.0	30	50	
	300		MJE5850	15 min	2.0	30 typ	80	
	350		MJE5851	15 min	2.0	30 typ	80	
			MJE5852	15 min	2.0	30 typ	80	
	450/1000	MJE13007		5/30	5.0	14 typ	80	
450/1000	MJE18008		16/34	1.0	13 typ	125		
10	60	D44H8	D45H8	40 min	4.0	3.0	50	
		MJE3055T	MJE2955T	20/70	4.0	3.0	75	
	80	BD809	BD810	15 min	4.0	1.5	90	
		D44H11	D45H11	40 min	4.0	50 typ	50	
	400/700	BUH100		6.0 min	10	23 typ	100	
12	90	BUV26		12 min	12	30 typ	85	
	120	BUV27		12 min	8.0	30 typ	70	
	400/700	MJE13009		6/30	8.0	4.0	100	
15	60	2N6487	2N6490	20/150	5.0	5.0	75	
	80	2N6488	2N6491	20/150	5.0	5.0	75	
		D44VH10	D45VH10	20 min	4.0	50 typ	83	
	400/700	BUH150		4.0 min	20	23 typ	150	



TO-220AB

NOTE: When two voltages are given, the format is V_{CEO(sus)}/V_{CES}.

DISCRETE TRANSISTORS (continued)

I _C Cont Amps Max	V _{CE0(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	f _T MHz Min	P _D (Case) Watts @ 25°C	Package
		NPN	PNP					
1.0	250	MJF47		30/150	0.3	10	28	 Isolated TO-220
3.0	100	MJF31C	MJF32C	10 min	1.0	3.0	28	
5.0	450/1000	MJF18004		14/34	0.3	13 typ	35	
8.0	150	MJF15030	MJF15031	40 min	3.0	30	35	
	450/1000	MJF18008		16/34	1.0	13 typ	45	
10	60	MJF3055	MJF2955	20/100	4.0	2.0	40	
	80	MJF44H11	MJF45H11	40/100	4.0	40	35	
10	100	TIP33C		20/100	3.0	3.0	80	 TO-218
15	60	TIP3055	TIP2955	5 min	10	2.5	80	
16	160	MJE4343	MJE4353	15 min	8.0	1.0	125	
25	60	TIP35A	TIP36A	15/75	15	3.0	125	
	100	TIP35C	TIP36C	15/75	15	3.0	125	
8.0	150	MJW21192	MJW21191	15 min	8.0	4.0	100	 TO-247
15	260	MJW0281A	MJW0302A	75/150	3.0	30	150	
		MJW3281A	MJW1302A	75/150	4.0	30	200	
16	250	MJW21194	MJW21193	20/60	8.0	4.0	200	
		MJW21196	MJW21195	20/60	8.0	4.0	200	
30	450/1000	MJW18020		14/35	3.0	13 typ	250	
15	260	NJW0281	NJW0302	75/150	3.0	30	150	 TO-3P
	260	NJW3281	NJW1302	75/150	4.0	30	200	
16	250	NJW21194	NJW21193	20/60	8.0	4.0	200	
15	260	MJL3281A	MJL1302A	75/150	4.0	30	200	 TO-264
	350	MJL4281A	MJL4302A	80/250	5.0	35	230	
16	250	MJL21194	MJL21193	25/75	8.0	4.0	200	
		MJL21196	MJL21195	25/75	8.0	4.0	200	
15	260	NJL0281D	NJL0302D	75/150	3.0	30	180	 TO-264 (5-Lead)
	260	NJL3281D	NJL1302D	75/150	4.0	30	200	
	350	NJL4281D	NJL4302D	75/150	5.0	30	250	
16	250	NJL21194D	NJL21193D	25/75	8.0	4.0	200	
10	140	2N3442		20/70	4.0	3.0	117	
15	60	2N3055	MJ2955	20/70	4.0	2.5	115	 TO-3 (TO-204AA)
		2N3055A		20/70	4.0	0.8	115	
	120	MJ15015	MJ15016	20/70	4.0	1.0	180	
	140	MJ15001	MJ15002	25/150	4.0	2.0	200	

NOTE: When two voltages are given, the format is V_{CE0(sus)}/V_{CES}.

DISCRETE TRANSISTORS (continued)


I _C Cont Amps Max	V _{CEO(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	f _T MHz Min	P _D (Case) Watts @ 25°C	Package
		NPN	PNP					
16	140	2N3773		15/60	8.0	4.0	150	 TO-3 (TO-204AA)
	200		MJ15023	15/60	8.0	5.0	250	
	250	MJ15024	MJ15025	15/60	8.0	5.0	250	
		MJ21194	MJ21193	25/75	8.0	4.0	250	
		MJ21196	MJ21195	25/75	8.0	4.0	250	
20	60	2N3772		15/60	10	2.0	150	
	90	2N5038		20/100	12	60	140	
	140	MJ15003	MJ15004	25/150	5.0	2.0	250	
25	60	2N5885	2N5883	20/100	10	4.0	200	
	80	2N5886	2N5884	20/100	10	4.0	200	
	100	2N6338		30/120	10	40	200	
	150	2N6341		30/120	10	40	200	
30	40	2N3771		15/60	15	2.0	150	
	60	2N5302		15/60	15	2.0	200	
	100	MJ802	MJ4502	25/100	7.5	2.0	200	
40	200	BUV21		10 min	25	8.0	150	 TO-3 (TO-204AE)
	250	BUV22		10 min	20	8.0	250	
50	80	2N5686	2N5684	15/60	25	2.0	300	
60	80	MJ14002		15/100	50	3.0	300	

DARLINGTON TRANSISTORS

I _C Cont Amps Max	V _{CEO(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	f _T MHz Min	P _D (Case) Watts @ 25°C	Package
		NPN	PNP					
2.0	100	MJD112T4	MJD117T4	1000 min	2.0	25	20	 DPAK
4.0	80	MJD6039T4		1k/2k	2.0	25	20	
	350	NJD35N04		2000 min	2.0	90	45	
8.0	100	MJD122T4	MJD127T4	1k/2k	4.0	4	20	
	120		MJD128T4	1k/2k	4.0	4	20	
10	80	MJD44E3T4		1k min	5.0		20	
10	350	BUB323Z		500/3400	5.0	2.0	75	 D²PAK
2.0	100	MJE270†	MJE271†	1.5k min	0.12	6.0	15	 TO-225AA
4.0	40		2N6034	25 min	1.5	2.0	40	
	45	BD675	BD676	750	1.5	3.0	40	
60		BD675A	BD676A	750	2.0	3.0	40	
		BD677	BD678	750 min	1.5		40	
	BD677A	BD678A	750 min	2.0		40		
	MJE800	MJE700	750 min	1.5	1.0	40		
80		2N6038	2N6035	750/18k	2.0	25	40	
		BD679	BD680	750 min	1.5		40	
	BD679A	BD680A	750 min	2.0		40		
	MJE802	MJE702	750 min	1.5	1.0	40		
	MJE803	MJE703	750 min	2.0	1.0	40		
100		2N6039	2N6036	750/18k	2.0	25	40	
100		BD681	BD682	750 min	1.5		40	
2.0	60	TIP110	TIP115	500 min	2.0	25	50	 TO-220AB
	80	TIP111	TIP116	500 min	2.0	25	50	
	100	TIP112	TIP117	500 min	2.0	25	50	
5.0	60	TIP120	TIP125	1k min	3.0	4.0	65	
	80	TIP121	TIP126	1k min	3.0	4.0	65	
	100	TIP122	TIP127	1k min	3.0	4.0	75	
8.0	60	2N6043	2N6040	1k/10k	4.0	4.0	75	
		TIP100		1k/20k	3.0	4.0	80	
	80	BDX53B	BDX54B	750 min	3.0	4.0	60	
		TIP101	TIP106	1k/20k	3.0	4.0	80	
		TIP131		1k/15k	4.0		70	
	100	TIP132		1k/15k	4.0		70	
		2N6045	2N6042	1k/10k	3.0	4.0	75	
		BDX53C	BDX54C	750 min	3.0			
TIP102		TIP107	1k/20k	3.0	4.0	80		
400		MJE5742		200 min	4.0		80	



NOTE: When two voltages are given, the format is V_{CEO(sus)}/V_{CES}.
 †Style 3.

DARLINGTON TRANSISTORS (continued)

I _C Cont Amps Max	V _{CEO(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	f _T MHz Min	P _D (Case) Watts @ 25°C	Package
		NPN	PNP					
10	60	2N6387	2N6667	1k/20k	5.0	20	65	 TO-220AB
	80	BDX33B	BDX34B	750 min	3.0	3.0	70	
		2N6388		1k/20k	5.0	20	65	
	100	BDX33C	BDX34C	750 min	3.0	3.0	70	
15	80		BDW46	1k min	5.0	4.0	85	
	100	BDW42	BDW47	1k min	5.0	4.0	85	
5.0	100	MJF122	MJF127	2000 min	3.0	4.0	28	 Isolated TO-220
10	100	MJF6388		3k/20k	3.0	20	40	
10	60	TIP140		500 min	10	4.0	125	 TO-218
		TIP141		500 min	10	4.0	125	
	100	BDV65B	BDV64B	1k min	5.0		125	
		TIP142	TIP147	500 min	10	4.0	125	
	350	BU323Z		500/3400	5.0		150	
15	150		MJH11017	400/15k	10	3.0	150	
	200	MJH11020	MJH11019	400/15k	10	3.0	150	
	250	MJH11022	MJH11021	400/15k	10	3.0	150	
20	100	MJH6284	MJH6287	750/18k	10	4.0	125	
12	100		2N6052	750/18k	6.0	4.0	150	 TO-3 (TO-204AA)
15	250	MJ11022	MJ11021	100 min	15	3.0	175	
20	80		2N6286	750/18k	10	4.0	160	
	100	2N6284	2N6287	750/18k	10	4.0	160	
30	60	MJ11012		1k min	20	4.0	200	
	120	MJ11016	MJ11015	1k min	20	4.0	200	
	250	MJ11022	MJ11021	400/15k	10	3.0	200	
50	60	MJ11028		400 min	50		300	 TO-3 (TO-204AE)
	90	MJ11030		400 min	50		300	
	120	MJ11032	MJ11033	400 min	50		300	

Audio

GENERAL DESIGN CURVES FOR POWER AUDIO OUTPUT STAGES



Another important parameter that must be considered before selecting the output transistors is the safe-operating area these devices must withstand. For a complete discussion see Application Note AN485.

RECOMMENDED POWER TRANSISTORS FOR AUDIO/SERVO LOADS

RMS Power Output	NPN	PNP	Package	P_D Watts @ 25°C	V_{CEO}	I_C Max	h_{FE}		f_T MHz Typ
							Min/Max	@ I_C Amps	
To 25 W	MJE15030	MJE15031	TO-220	50	150	8.0	20 min	4.0	30
	MJE15032	MJE15033	TO-220	50	250	8.0	50 min	1.0	30
25 to 50 W	MJE15034	MJE15035	TO-220	50	350	4.0	50 min	1.0	30
50 to 100 W	MJ15003	MJ15004	TO-3	150	140	20	25/150	5.0	3.0
	MJ15015	MJ15016	TO-3	180	120	15	20/70	4.0	3.0
Over 100 W	MJW21192	MJW21191	TO-3	100	150	8.0	15 min	4.0	4.0
	NJW0281	NJW0302	TO-3P	150	260	15	75/150	3.0	30
	NJL0281D	NJL0302D	TO-264 (5-Lead)	180	260	15	75/150	3.0	30
	MJL21194	MJL21193	TO-264	200	250	16	25/75	8.0	4.0
	MJL21196	MJL21195	TO-264	200	250	16	25/75	8.0	4.0
	MJW21194	MJW21193	TO-247	200	250	16	20/60	8.0	4.0
	NJW21194	NJW21193	TO-3P	200	250	16	20/60	8.0	4.0
	MJW21196	MJW21195	TO-247	200	250	16	25/60	8.0	4.0
	MJL3281A	MJL1302A	TO-264	200	260	15	75/150	5.0	30

RECOMMENDED POWER TRANSISTORS FOR AUDIO/SERVO LOADS (continued)

RMS Power Output	NPN	PNP	Package	P _D Watts @ 25°C	V _{CEO}	I _C Max	h _{FE}		f _T MHz Typ
							Min/Max	@ I _C Amps	
Over 100 W	MJW3281A	MJW1302A	TO-247	200	260	15	75/150	5.0	30
	NJW3281	NJW1302	TO-3P	200	260	15	75/150	5.0	30
	MJL4281A	MJL4302A	TO-264	200	350	15	80/200	5.0	35
	NJL3281D	NJL1302D	TO-264 (5-Lead)	200	260	15	75/150	7.0	30
	NJL4281D	NJL4302D	TO-264 (5-Lead)	250	350	15	75/150	5.0	30
	MJ15024	MJ15025	TO-3	250	250	16	15/60	8.0	4.0
	MJ21194	MJ21193	TO-3	250	250	16	25/75	8.0	4.0

The Power Transistors shown are provided for reference only and show device capability. The final choice of the Power Transistors used is left to the circuit designer and depends upon the particular safe-operating area required and the mounting and heat sinking configuration used.

Bipolar Power Transistors for Electronic Lamp Ballasts

I _C Cont Amps Max	V _{CEO(sus)} Volts Min	V _{CES} Volts Min	Device Type	I _C Operating Amps	h _{FE} min @ I _C Operating V _{CE} = 1.0 V	Inductive Switching @ I _C Operating t _{si} /t _{fi} Max (μs)	P _D (Case) Watts @ 25°C	Package
2.0	450	1000	MJE18002	1.0	6.0	2.75/0.175	50	 TO-220AB
4.0	500	800	BUH50	2.0	8.0 typ	2.75/0.15	50	
5.0	400	700	BUL45	2.0	7.0	3.8/0.17	75	
		700	BUL45D2*	2.0	10	2.25/0.015	75	
	450	1000	MJE18004	2.0	6.0	2.5/0.175	75	
6.0	450	1000	MJE18006	3.0	6.0	3.2/0.15	100	
8.0	450	1000	MJE18008	4.5	6.0	3.2/0.15	125	
10	400	700	BUH100	5.0	10 typ	3.5/0.15	100	
15	400	700	BUH150	10	8.0 typ	2.75/0.175	150	

Isolated TO-220

I _C Cont Amps Max	V _{CEO(sus)} Volts Min	V _{CES} Volts Min	Device Type	I _C Operating Amps	h _{FE} min @ I _C Operating V _{CE} = 1.0 V	Inductive Switching @ I _C Operating t _{si} /t _{fi} Max (μs)	P _D (Case) Watts @ 25°C	Package
5.0	450	1000	MJF18004	2.0	6.0	2.5/0.175	35	 Isolated TO-220
8.0	450	1000	MJF18008	4.5	6.0	3.2/0.15	45	

BUH-Series are specified for Halogen applications.

*D2 suffix indicates transistor with built-in C-E freewheeling diode and antisaturation network.

†Style 3.

The isolated TO-220 is UL RECOGNIZED for its isolation feature and has been evaluated to 3500 volts RMS. Actual isolation rating depends on specific mounting position and maintaining required strike and creepage distances.

BIPOLAR TRANSISTORS
GENERAL-PURPOSE TRANSISTORS

NPN	PNP	V _{(BR)CEO}	I _C mA Max	h _{FE}		f _T MHz Min	NF dB Max	Package	
				Min	Max				
MPS8099	–	80	500	100	300	150	–	 <p>TO-226AA, TO-92 Case 29-11</p>	
MPSA06	MPSA56	80	500	100	–	100	–		
BC639	–	80	1000	40	160	60	0.5		
BC639-16	–	80	1000	100	250	60	0.5		
–	BC640-016	80	500	100	250	–	–		
BC546B	–	65	100	180	450	150	10		
MPSA05	MPSA55	60	500	100	–	100	–		
–	MPS2907A	60	600	100	300	200	–		
MPS651	MPS751	60	2000	75	–	75	0.5		
BC637	–	60	500	40	160	–	0.5		
–	2N5087	50	50	250	800	40	2.0		
–	BC307B	45	100	200	460	150	10		
BC337	–	45	800	100	630	210 (Typ)	–		
BC337-25	BC327-25	45	800	160	400	260 (Typ)	–		
BC337-40	BC327-40	45	800	250	630	260 (Typ)	–		
BC550C	–	45	100	380	800	250 (Typ)	2.5		
BC547B	BC557B	45	100	180	450	150	10		
–	BC557C	45	100	380	800	150	10		
MPS2222A	–	40	600	100	300	300	–		
PN2222A	–	40	600	100	300	300	4		
2N4401	2N4403	40	600	100	300	200	–		
–	MPS6652	40	1000	50	–	100	–		
2N3904	2N3906	40	200	100	300	250	5.0		
BC548C	–	30	100	420	800	300	10		 <p>TO-226AA, TO-92 Case 29-11</p>
BC549C	–	30	100	420	800	–	–		
MPS2222	–	30	600	100	300	250	–		
2N5088	–	30	50	350	–	50	3.0		
2N5089	–	25	50	450	–	50	2.0		
2N4124	–	25	200	120	360	300	–		
MPS4124	–	25	200	120	360	170	5.0		
MPS5172	–	25	100	100	500	–	–		
–	BC369	20	1000	60	–	65	0.5		
MPSW06	MPSW56	80	500	80	–	50	–	 <p>TO-226AE (1-WATT) TO-92 Case 29-10</p>	
MPSW05	–	60	500	60	–	50	250		
MPSW01A	MPSW51A	40	1000	50	–	50	–		
MPSW01	MPSW51	30	1000	50	–	50	–		
MPS6726	–	30	1000	50	250	–	–		

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

GENERAL-PURPOSE TRANSISTORS (continued)

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package
				Min	Max			
MMBT5550L	–	140	600	60	250	–	–	 <p>TO-236AB, SOT-23 Case 318-08</p>
–	BSS63L	100	100	30	–	50	–0.25	
BSS64L	–	80	100	20	–	60	0.15	
MMBTA06L	MMBTA56L	80	500	100	–	100	–	
MMBT8099L	–	80	500	100	300	150	–	
BC846AL	–	65	100	110	220	100	10	
BC846BL	–	65	100	200	450	100	10	
–	BC856AL	65	100	125	250	100	10	
–	BC856BL	65	100	220	475	100	10	
–	MMBT2907AL	60	600	100	300	200	–	
MMBT2484L	–	60	50	250	–	–	3.0	
MMBTA05L	–	60	500	100	–	100	–	
–	MMBTA55L	60	500	100	–	50	–	
MMBT6428L	–	50	200	250	–	100	3.0 (Typ)	
–	MMBT5087L	50	50	250	–	40	2.0	
MMBT6429L	–	45	200	500	–	100	3.0 (Typ)	
BC817-16L	–	45	500	100	250	100	–	
BC817-25L	–	45	500	160	400	100	–	
BC817-40L	–	45	500	250	600	100	–	
–	BC807-16L	45	500	100	250	100	–	
–	BC807-25L	45	500	160	400	100	–	
–	BC807-40L	45	500	250	600	100	–	
BC847AL	–	45	100	110	220	100	10	
BC847BL	–	45	100	200	450	100	10	
BC847CL	–	45	100	420	800	100	10	
BC850BL	–	45	100	200	450	100	4.0	
BC850CL	–	45	100	420	800	100	4.0	
–	BC857AL	45	100	125	250	100	10	
–	BC857BL	45	100	220	475	100	10	
–	BC857CL	45	100	420	800	100	10	
–	BCW68GL	45	800	120	400	100	10	
–	BCW70L	45	100	215	500	–	10	
BCW72L	–	45	100	200	450	300	10	
–	BCX17L	45	500	100	600	–	–	
BCX19L	–	45	500	100	600	–	–	
MMBT2222AL	–	40	600	100	300	300	4.0	
MMBT3904L	–	40	200	100	300	200	5.0	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

GENERAL-PURPOSE TRANSISTORS (continued)

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package	
				Min	Max				
-	MMBT3906L	40	200	100	300	250	4.0	 TO-236AB, SOT-23 Case 318-08	
MMBT4401L	-	40	600	100	300	250	-		
-	MMBT4403L	40	600	100	300	200	-		
MMBT3416L	-	40	100	75	225	-	-		
-	MMBT470L	40	100	40	400	125	-		
-	BCW30L	32	100	215	500	-	10		
BCW32L	-	32	100	200	450	-	10		
BCW65AL	-	32	800	100	250	100	10		
BCW65CL	-	32	100	250	630	100	10		
BC848AL	-	30	100	110	220	100	10		
BC848BL	-	30	100	200	450	100	10		
BC848CL	-	30	100	420	800	100	10		
BC849BL	-	30	100	200	450	100	4.0		
BC849CL	-	30	100	420	800	100	4.0		
MMBT489L	-	30	1000	300	900	100	-		
-	MMBT589L	30	1000	100	300	100	-		
-	BC858AL	30	100	125	250	100	10		
-	BC858BL	30	100	220	475	100	10		
-	BC858CL	30	100	420	800	100	10		
MMBT5088L	-	30	50	300	900	5	3.0		
MMBT2222L	-	30	600	100	300	250	4.0		
MMBT6521L	-	25	100	300	600	-	-		
MMBT5089L	-	25	50	400	1200	50	2.0		
MMBT4124L	-	25	200	120	360	300	5.0		
BC818-40L	-	25	500	250	600	100	-		
-	MMBT4126L	25	200	120	300	250	4.0		
-	BC808-25L	25	500	160	400	100	-		
BCW33L	-	20	100	420	800	-	10		
MSD601-R	-	50	100	210	340	-	-		 SC-59 Case 318D-04
MSD602-R	-	50	500	120	240	-	-		
MSC2712G	-	50	100	200	400	-	-		
-	MSA1162G	50	100	200	400	-	-		
-	MSA1162Y	50	100	120	240	-	-		
-	MSB710-R	50	500	120	240	-	-		
-	MSB709-R	45	100	210	340	-	-		
MSD1328-R	-	20	500	200	350	-	-		

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

GENERAL-PURPOSE TRANSISTORS (continued)

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package
				Min	Max			
<i>MMBTA06W</i>	<i>MMBTA56W</i>	80	500	100	–	100	–	 SC-70, SOT-323 Case 419-04
<i>BC846BW</i>	–	65	100	200	450	100	10	
–	<i>BC856BW</i>	65	100	220	475	100	10	
–	<i>MMBT2907AW</i>	60	600	100	–	200	–	
<i>MSD1819A-R</i>	–	50	100	210	340	–	–	
<i>BC847AW</i>	–	45	100	110	220	100	10	
<i>BC847BW</i>	–	45	100	200	450	100	10	
<i>BC847CW</i>	–	45	100	420	800	100	4.0	
–	<i>BC857BW</i>	45	100	220	475	100	10	
–	<i>BC857CW</i>	45	100	420	800	100	10	
–	<i>MSB1218A-R</i>	45	100	210	340	–	–	
MMBT4401W	–	40	600	100	300	250	–	
–	MMBT4403W	40	600	100	300	200	–	
<i>MMBT2222AW</i>	–	40	600	100	300	300	4.0	
<i>MMBT3904W</i>	–	40	200	100	300	300	5.0	
–	<i>MMBT3906W</i>	40	200	100	300	250	4.0	
<i>BC848BW</i>	–	30	100	200	450	100	10	
<i>BC848CW</i>	–	30	100	420	800	100	4.0	
–	<i>BC858AW</i>	30	100	110	220	100	10	
–	<i>BC858BW</i>	30	100	200	450	100	10	
<i>2SC4617</i>	–	50	100	120	560	180 (Typ)	–	 SOT-416, SC-75, SC-90 Case 463-01
–	<i>2SA1774</i>	50	100	120	560	140 (Typ)	–	
<i>BC847BT</i>	–	45	100	200	450	100	10	
<i>BC847CT</i>	–	45	100	420	800	100	4.0	
–	<i>BC857BT</i>	45	100	220	475	100	10	
<i>MMBT3904T</i>	–	40	200	100	300	300	5.0	
–	<i>MMBT3906T</i>	40	200	100	300	250	4.0	
<i>MMBT2222AT</i>	–	40	600	100	300	300	4.0	
MMBT5551M3	–	160	60	80	250	–	–	 SOT-723 Case 631AA-01
BC846BM3	–	65	100	200	450	100	10	
–	MMBT2907AM3	60	600	100	300	200	–	
2SC5658M3	–	50	100	120	560	180 (Typ)	–	
–	2SA2029M3	50	100	120	560	140 (Typ)	–	
–	2SC5658RM3	50	100	215	375	180 (Typ)	–	
–	NS2029M3	50	100	120	560	100	–	
–	BC856BM3	45	100	220	475	100	10	
BC847BM3	–	45	100	200	450	100	10	
–	MMBT4403M3	40	600	100	300	200	–	
MMBT4401M3	–	40	600	100	300	250	–	
MMBT2222AM3	–	40	600	100	300	300	4	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

GENERAL-PURPOSE TRANSISTORS (continued)

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package
				Min	Max			
NST846BF3	–	65	100	200	450	100	10	 SOT-1123 Case 524AA
–	NST856BF3	65	100	200	475	100	10	
NST847BF3	–	45	100	200	450	100	10	
–	NST857BF3	45	100	200	475	100	10	
NST3904F3	–	40	200	100	300	200	5	
–	NST3906F3	40	200	100	300	250	4	
NST848BF3	–	30	100	200	450	100	10	
<i>BCP56</i>	<i>BCP53</i>	80	1000	40	250	50 (Typ)	–	 SOT-223 Case 318E-04
<i>BCP56-10</i>	<i>BCP53-10</i>	80	1000	63	160	50 (Typ)	–	
<i>BCP56-16</i>	<i>BCP53-16</i>	80	1000	100	250	50 (Typ)	–	
–	<i>PZT2907A</i>	60	600	100	300	200	–	
<i>PZT651</i>	<i>PZT751</i>	60	2000	75	–	75	–	
<i>PZT2222A</i>	–	40	600	100	300	300	–	
<i>BCP68</i>	<i>BCP69</i>	25	1000	85	375	60 (Typ)	–	
–	MMBT2131	30	700	150	–	–	–	 SC-74 Case 318F-05
–	MBT35200M	35	2000	100	400	100	–	 TSOP-6 SINGLE Case 318G-02
NST489AM	–	30	3000	300	900	200	–	
–	NSL12AW	12	2000	100	300	100	–	 SC-88, SOT-363 Case 419B-02

Devices listed in ***bold italic*** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

GENERAL-PURPOSE MULTIPLE TRANSISTORS

Device	Type	V _{(BR)CEO}	I _C mA Max	h _{FE}		f _T MHz Min	NF dB Max	Package	
				Min	Max				
<i>BC846BDW1</i>	Dual NPN	65	100	200	450	100	10	 SC-88, SOT-363 Case 419B-02	
<i>BC856BDW1</i>	Dual PNP	65	100	220	475	100	10		
<i>BC846BPDW1</i>	Dual Complementary	65	100	200	475	100	10		
<i>BC847BDW1</i>	Dual NPN	45	100	200	290	100	10		
<i>BC847CDW1</i>	Dual NPN	45	100	420	520	100	4.0		
<i>BC857BDW1</i>	Dual PNP	45	100	220	290	100	10		
<i>BC857CDW1</i>	Dual PNP	45	100	420	520	100	10		
<i>BC847BPDW1</i>	Dual Complementary	45	100	200	290	100	10		
<i>MBT3904DW1</i>	Dual NPN	40	200	100	300	300	5.0		
<i>MBT3906DW1</i>	Dual PNP	40	200	100	300	250	4.0		
<i>MBT3946DW1</i>	Dual Complementary	40	200	100	300	250	5.0/4.0		
<i>MBT2222ADW1</i>	Dual NPN	40	600	100	300	300	4.0		
MBT6429DW1	Dual NPN	45	200	500	1250	100	-		
NST45011MW6	Dual Matched NPN	45	100	200	500	100	10		
UMZ1N	Dual Complementary	50	200	200	400	114 (Typ)	-		
<i>BC848CDW1</i>	Dual NPN	30	100	420	250	100	4.0	 SOT-563 Case 463A-01	
<i>BC848CPDW1</i>	Dual Complementary	30	100	420	520	100	4.0/10		
<i>BC847CDXV6</i>	NPN	45	100	420	520	100	-		
EMT1DXV6	Dual PNP	60	100	120	560	140 (Typ)	-		
EMX1DXV6	Dual NPN	50	100	120	560	180 (Typ)	-		
EMX2DXV6	Dual NPN	50	100	120	560	180 (Typ)	-		
EMZ1DXV6	Complementary	60	100	120	560	140 (Typ)	-		
<i>BC847BPDXV6</i>	Complementary	45	100	200	290	100	-		
<i>NST3904DXV6</i>	Dual NPN	40	200	100	300	300	-		
<i>NST3906DXV6</i>	Dual PNP	40	200	100	300	250	-		
<i>NST3946DXV6</i>	Complementary	40	200	100	300	250	-		
<i>NST30010MXV6</i>	Matched Dual PNP	30	100	420	520	100	-		
<i>BC858CDXV6</i>	Dual PNP	30	100	420	520	100	-		
NST3904DP6	Dual NPN	40	200	100	300	200	5		 SOT-963 Case 527AA
NST3906DP6	Dual PNP	40	200	100	300	250	4		
NST3946DP6	Dual Complementary	40	200	100	300	200	5		
NST847BDP6	Dual NPN	45	100	200	450	100	10		
NST847BPDP6	Dual Complementary	45	100	200	450	100	10		
NST857BDP6	Dual PNP	45	100	200	475	100	10		
NST45010MW6	Matched Dual PNP	45	100	220	475	100	10		
HN1B01FDW1	Complementary	50	200	200	400	-	-	 SC-74 Case 318F-05	
<i>NSS40301MD</i>	Matched Dual NPN	40	3000	200	500	150	-	 8 1 SOIC-8 Case 751 STYLE 16	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

LOW NOISE AND GOOD h_{FE} LINEARITY

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package
				Min	Max			
–	2N5087	50	50	250	800	40	2.0	 TO-226AA, TO-92 Case 29-11 (Note 1)
BC550C	–	45	100	380	800	250 (Typ)	2.5	
2N5088	–	30	50	350	–	50	3.0	
2N5089	–	25	50	450	–	50	2.0	
MMBT2484L	–	60	50	250	–	–	3.0	 TO-236AB, SOT-23 Case 318-08
MMBT6428L	–	50	200	250	–	100	3.0 (Typ)	
–	MMBT5087L	50	50	250	–	40	2.0	
MMBT6429L	–	45	200	500	–	100	3.0 (Typ)	
MMBT5088L	–	30	50	300	900	5	3.0	
MMBT5089L	–	25	50	400	–	50	2.0	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

1. N_F : Noise Figure at $R_S = 2.0\text{ k}\Omega$, $I_C = 200\text{ }\mu\text{A}$, $V_{CE} = 5.0\text{ Volts}$. $f = 30\text{ Hz to }15\text{ kHz}$.

DARLINGTON TRANSISTORS

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package
				Min	Max			
MPSW45A	–	50	1000	25K	150K	100	1.5	 TO-226AE (1-WATT) TO-92 Case 29-10
MPSW45	–	40	1000	25K	150K	100	1.5	
MPSA29	–	100	500	10K	–	125	1.5	 TO-226AA, TO-92 Case 29-11
BC373	–	80	1000	10K	160K	100	1.1	
MPSA27	–	60	500	10K	–	–	1.5	
2N6427	–	40	500	20K	200K	–	1.5	
2N6426	–	40	500	30K	300K	125	1.5	
MPSA14	–	30	500	20K	–	125	1.5	
MPSA13	–	30	500	10K	–	125	1.5	
BC517	–	30	1000	30K	–	200 (Typ)	1.0	
MMBT6427L	–	40	500	20000	200000	–	10	 TO-236AB, SOT-23 Case 318-08
MMBTA14L	MMBTA64L	30	300	20K	–	125	–	
MMBTA13L	–	30	300	10000	–	125	–	
–	MMBTA63L	30	500	10000	–	125	–	
BSP52	–	80	1000	2000	–	–	–	 SOT-223 Case 318E-04

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

HIGH CURRENT TRANSISTORS (≥ 500 mA)

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package
				Min	Max			
BC639	–	80	500	40	160	60	0.5	 <p>TO-226AA, TO-92 Case 29-11</p>
BC639-16	–	80	1000	100	250	60	0.5	
MPS8099	–	80	500	100	300	150	–	
MPSA06	MPSA56	80	500	100	–	100	–	
MPS651	MPS751	60	2000	75	–	75	0.5	
BC637	–	60	500	40	160	–	0.5	
MPSA05	MPSA55	60	500	100	–	100	–	
–	MPS2907A	60	600	100	300	200	–	
BC337	–	45	800	100	630	210 (Typ)	–	
BC337-25	BC327-25	45	800	160	400	260 (Typ)	–	
BC337-40	BC327-40	45	800	250	630	260 (Typ)	–	
MPS650	–	40	2000	40	–	75	–	
MPS2222A	–	40	600	100	300	300	–	
2N4401	2N4403	40	600	100	300	200	–	
P2N2222A	–	40	600	100	300	300	–	
PN2222A	–	40	600	100	300	300	–	
–	MPS6652	40	1000	50	–	100	–	
MPS2222	–	30	600	100	300	250	–	
–	BC369	20	1000	60	–	65	0.5	
MPSW06	MPSW56	80	500	80	–	50	–	
MPSW05	–	60	500	60	–	50	250	
–	2SA1020	50	2000	70	240	100	–	
MPSW01A	MPSW51A	40	1000	50	–	50	–	
MPSW01	MPSW51	30	1000	50	–	50	–	
MPS6726	–	30	1000	50	250	–	–	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

HIGH CURRENT TRANSISTORS (≥ 500 mA) (continued)

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package
				Min	Max			
MMBT5550L	–	140	600	60	250	–	–	 TO-236AB, SOT-23 Case 318-08
MMBTA06L	MMBTA56L	80	500	100	–	100	–	
MMBT8099L	–	80	500	100	300	150	–	
–	MMBT2907AL	60	600	100	300	200	–	
MMBTA05L	–	60	500	100	–	100	–	
–	MMBTA55L	60	500	100	–	50	–	
–	BCW68GL	45	800	120	400	100	10	
BCW66GL	–	45	800	160	400	100	10	
–	BCX17L	45	500	100	600	–	–	
BCX19L	–	45	500	100	600	–	–	
MMBT2222AL	–	40	600	100	300	300	4.0	
MMBT4401L	–	40	600	100	300	250	–	
–	MMBT4403L	40	600	100	300	200	–	
BCW65AL	–	32	800	100	250	100	10	
MMBT2222L	–	30	600	100	300	250	4.0	
BCP56	BCP53	80	1000	40	250	50 (Typ)	–	 SOT-223 Case 318E-04
BCP56-10	BCP53-10	80	1000	63	160	50 (Typ)	–	
BCP56-16	BCP53-16	80	1000	100	250	50 (Typ)	–	
–	PZT2907A	60	600	100	300	200	–	
PZT651	PZT751	60	2000	75	–	75	–	
PZT2222A	–	40	600	100	300	300	–	
BCP68	BCP69	25	1000	85	375	60 (Typ)	–	
MMBT2222AT	–	40	600	100	300	300	4.0	 SOT-416, SC-75, SC-90 Case 463-01
–	MMBT2907AW	60	600	100	–	200	–	 SC-70, SOT-323 Case 419-04
MMBT2222AW	–	40	600	100	300	300	4.0	
–	MSB92ASW	300	500	120	200	50	–	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

HIGH VOLTAGE TRANSISTORS (> 100 V)

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	NF dB Max	Package
				Min	Max			
<i>MPSW42</i>	–	300	50	40	–	50	0.5	 TO-226AE (1-WATT) TO-92 Case 29-10
–	<i>MPSW92</i>	300	50	25	–	50	0.5	
<i>2N5551</i>	–	160	600	80	250	100	8.0	
–	<i>2N5401</i>	150	600	60	240	100	8.0	
MPSA44	–	400	300	50	200	–	–	 TO-226AA, TO-92 Case 29-11
–	<i>2N6520</i>	350	500	30	200	40	–	
<i>MPSA42</i>	–	300	50	40	–	50	0.5	
–	<i>MPSA92</i>	300	50	40	–	50	0.5	
2N5550	–	140	600	60	250	100	10	
<i>MMBT6517L</i>	–	350	100	15	–	40	–	 TO-236AB, SOT-23 Case 318-08
–	<i>MMBT6520L</i>	350	500	15	–	40	–	
<i>MMBTA42L</i>	–	300	50	40	–	50	–	
–	<i>MMBTA92L</i>	300	50	25	–	50	–	
<i>MMBT5551L</i>	–	160	600	80	250	–	–	
–	<i>MMBT5401L</i>	150	500	50	–	100	8.0	
MMBT5550L	–	140	600	60	250	–	–	 SOT-223 Case 318E-04
<i>BSP19A</i>	–	350	100	40	–	70	–	
<i>PZTA42</i>	<i>PZTA92</i>	300	50	40	–	50	–	
–	PZTA96S	450	50	50	150	–	–	
–	<i>BSP16</i>	300	100	30	120	15	–	 SC-70, SOT-323 Case 419-04
<i>BF720</i>	<i>BF721</i>	250	100	50	–	60	–	
<i>MSD42W</i>	–	300	150	40	–	–	–	
–	<i>MSB92W</i>	300	50	25	–	50	–	
–	<i>MSB92AW</i>	300	50	120	200	50	–	
–	MSB92ASW	300	50	120	200	50	–	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

RF TRANSISTORS

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	Cap pF Max	Package
				Min	Max			
<i>MPSH10</i>	–	25	–	60	–	650	$C_{RB} = 0.65$	 TO-226AA, TO-92 Case 29-11
<i>MMBTH10L</i>	–	25	–	60	–	650	$C_{CB} = 0.7$	 TO-236AB, SOT-23 Case 318-08
<i>MMBTH10-4L</i>	–	25	–	120	240	800	$C_{CB} = 0.7$	
MMBT918L	–	15	50	20	–	600	$C_{OBO} = 1.7$	
BSV52L	–	12	100	40	120	400	–	
MMBTH10M3	–	25	–	60	–	650	$C_{CB} = 0.7$	 SOT-723 Case 631AA-01

Devices listed in ***bold italic*** are ON Semiconductor preferred devices.

SWITCHING TRANSISTORS

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	T_{off} ns Max	Package
				Min	Max			
–	<i>MPS2907A</i>	60	600	100	300	200	110	 TO-226AA, TO-92 Case 29-11
<i>2N4401</i>	<i>2N4403</i>	40	600	100	300	200	–	
<i>2N3904</i>	<i>2N3906</i>	40	200	100	300	250	300	
P2N2222A	–	40	600	100	300	300	285	
<i>MPS2222A</i>	–	40	600	100	300	300	285	
–	<i>MMBT2907AL</i>	60	600	100	300	200	100	 TO-236AB, SOT-23 Case 318-08
<i>MMBT2222AL</i>	–	40	600	100	300	300	285	
<i>MMBT3904L</i>	–	40	200	100	300	300	250	
–	<i>MMBT3906L</i>	40	200	100	300	250	300	
<i>MMBT4401L</i>	–	40	600	100	300	250	255	
–	<i>MMBT4403L</i>	40	600	100	300	200	255	
<i>MMBT2369L</i>	–	15	200	40	120	–	18	
<i>MMBT2369AL</i>	–	15	200	40	120	–	18	

Devices listed in ***bold italic*** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

SWITCHING TRANSISTORS

NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	T_{off} ns Max	Package
				Min	Max			
–	MMBT2907AW	60	600	100	300	200	100	 SC-70, SOT-323 Case 419-04
MMBT3904W	–	40	200	100	300	300	250	
–	MMBT3906W	40	200	100	300	250	300	
MMBT2222AW	–	40	600	100	300	300	285	
MMBT4401W	–	40	600	100	300	250	255	
–	MMBT4403W	40	600	100	300	200	255	
MMBT3904T	–	40	200	100	300	300	250	 SOT-416, SC-75, SC-90 Case 463-01
–	MMBT3906T	40	200	100	300	250	300	
MMBT2222AT	–	40	600	100	300	300	285	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

MULTIPLE SWITCHING TRANSISTORS


Device	Type	$V_{(BR)CEO}$	I_C mA Max	h_{FE}		f_T MHz Min	T_{off} ns Max	Package
				Min	Max			
MBT3904DW1	Dual NPN	40	200	100	300	300	250	 SC-88, SOT-363 Case 419B-02
MBT3906DW1	Dual PNP	40	200	100	300	250	300	
MBT3946DW1	Dual Complementary	40	200	100	300	250	250/300	
MBT2222ADW1	Dual NPN	40	600	100	300	300	285	
HN1B01FDW1	Dual Complementary	50	200	200	400	–	–	 SC-74 Case 318F-05

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

DIGITAL TRANSISTORS (BIAS RESISTOR TRANSISTORS)

These devices include bias resistors on the semiconductor chip with the transistor. See the BRT diagram for orientation of resistors.




NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE} Min	R_1 Ω	R_2 Ω	Package
<i>MUN2211</i>	<i>MUN2111</i>	50	100	35	10K	10K	 SC-59 Case 318D-04
<i>MUN2212</i>	<i>MUN2112</i>	50	100	60	22K	22K	
<i>MUN2213</i>	<i>MUN2113</i>	50	100	80	47K	47K	
<i>MUN2214</i>	<i>MUN2114</i>	50	100	80	10K	47K	
<i>MUN2215</i>		50	100	160	10K	∞	
<i>MUN2216</i>		50	100	160	4.7K	∞	
<i>MUN2230</i>		50	100	3.0	1.0K	1.0K	
<i>MUN2232</i>		50	100	15	4.7K	4.7K	
<i>MUN2233</i>		50	100	80	4.7K	47K	
<i>MUN2234</i>		50	100	80	22K	47K	
<i>MUN2237</i>		50	100	80	47K	22K	
<i>MUN2240</i>	-	50	100	160	47K	∞	
<i>MMUN2211L</i>	<i>MMUN2111L</i>	50	100	35	10K	10K	 TO-236AB, SOT-23 Case 318-08
<i>MMUN2212L</i>	<i>MMUN2112L</i>	50	100	60	22K	22K	
<i>MMUN2213L</i>	<i>MMUN2113L</i>	50	100	80	47K	47K	
<i>MMUN2214L</i>	<i>MMUN2114L</i>	50	100	80	10K	47K	
<i>MMUN2215L</i>	<i>MMUN2115L</i>	50	100	160	10K	∞	
<i>MMUN2216L</i>	<i>MMUN2116L</i>	50	100	160	4.7K	∞	
<i>MMUN2231L</i>		50	100	8.0	2.2K	2.2K	
<i>MMUN2232L</i>	<i>MMUN2132L</i>	50	100	15	4.7K	4.7K	
<i>MMUN2233L</i>	<i>MMUN2133L</i>	50	100	80	4.7K	47K	
<i>MMUN2234L</i>		50	100	80	22K	47K	
<i>MMUN2238L</i>	-	50	100	160	2.2K	∞	
<i>MUN5211</i>	<i>MUN5111</i>	50	100	35	10K	10K	
<i>MUN5212</i>	<i>MUN5112</i>	50	100	60	22K	22K	
<i>MUN5213</i>	<i>MUN5113</i>	50	100	80	47K	47K	
<i>MUN5214</i>	<i>MUN5114</i>	50	100	80	10K	47K	
<i>MUN5215</i>		50	100	160	10K	∞	
<i>MUN5230</i>		50	100	3.0	1.0K	1.0K	
	<i>MUN5131</i>	50	100	8.0	2.2K	2.2K	
<i>MUN5232</i>	<i>MUN5132</i>	50	100	15	4.7K	4.7K	
<i>MUN5233</i>	<i>MUN5133</i>	50	100	80	4.7K	47K	
<i>MUN5235</i>	<i>MUN5135</i>	50	100	80	2.2K	47K	


Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

DIGITAL TRANSISTORS (BIAS RESISTOR TRANSISTORS) (continued)

These devices include bias resistors on the semiconductor chip with the transistor. See the BRT diagram for orientation of resistors.




NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE} Min	R1 Ω	R2 Ω	Package
<i>DTC114EE</i>	<i>DTA114EE</i>	50	100	35	10k	10k	 SOT-416, SC-75, SC-90 Case 463-01
<i>DTC124EE</i>		50	100	60	22k	22k	
<i>DTC144EE</i>	<i>DTA144EE</i>	50	100	80	47k	47k	
<i>DTC114YE</i>	<i>DTA114YE</i>	50	100	80	10k	47k	
<i>DTC114TE</i>	<i>DTA114TE</i>	50	100	160	10k	∞	
<i>DTC143EE</i>	<i>DTA143EE</i>	50	100	15	4.7k	4.7k	
<i>DTC143ZE</i>	<i>DTA143ZE</i>	50	100	80	4.7k	4.7k	
<i>DTC124XE</i>	–	50	100	80	22k	47k	
<i>DTC123JE</i>		50	100	80	2.2k	47k	
<i>DTC115EE</i>	<i>DTA115EE</i>	50	100	80	100k	100k	
<i>DTC114EM3</i>	<i>DTA114EM3</i>	50	100	35	10k	10k	 SOT-723 Case 631AA-01
<i>DTC124EM3</i>	<i>DTA124EM3</i>	50	100	60	22k	22k	
<i>DTC144EM3</i>	<i>DTA144EM3</i>	50	100	80	47k	47k	
<i>DTC114YM3</i>	<i>DTA114YM3</i>	50	100	80	10k	47k	
<i>DTC114TM3</i>	<i>DTA114TM3</i>	50	100	160	10k	∞	
<i>DTC143TM3</i>	<i>DTA143TM3</i>	50	100	160	4.7k	∞	
<i>DTC123EM3</i>	<i>DTA123EM3</i>	50	100	8.0	2.2k	2.2k	
<i>DTC143EM3</i>	<i>DTA143EM3</i>	50	100	15	4.7k	4.7k	
<i>DTC143ZM3</i>	<i>DTA143ZM3</i>	50	100	80	4.7k	4.7k	
<i>DTC124XM3</i>	<i>DTA124XM3</i>	50	100	80	22k	47k	
<i>DTC123JM3</i>		50	100	80	2.2k	47k	
<i>DTC115EM3</i>	<i>DTA115EM3</i>	50	100	80	100k	100k	
<i>DTC144WM3</i>	<i>DTA144WM3</i>	50	100	80	47k	22k	
<i>DTC144TM3</i>	<i>DTA144TM3</i>	50	100	160	47k	∞	
<i>NSBC143EF3</i>	<i>NSBA143EF3</i>	50	100	15	4.7k	4.7k	 SOT-1123 Case 524AA
<i>NSBC114EF</i>	<i>NSBA114EF3</i>	50	100	35	10k	10k	
<i>NSBC124EF3</i>	<i>NSBA124EF3</i>	50	100	60	22k	22k	
<i>NSBC144EF3</i>	<i>NSBA144EF3</i>	50	100	80	47k	47k	
<i>NSBC123JF3</i>	<i>NSBA123JF3</i>	50	100	80	2.2k	47k	
<i>NSBC143ZF3</i>	<i>NSBA143ZF3</i>	50	100	80	4.7k	47k	
<i>NSBC144WF3</i>	<i>NSBA144WF3</i>	50	100	80	47k	22k	
<i>NSBC123TF3</i>	<i>NSBA123TF3</i>	50	100	160	2.2k	∞	
<i>NSBC114TF3</i>	<i>NSBA114TF3</i>	50	100	160	10k	∞	
<i>NSBC115TF3</i>	<i>NSBA115TF3</i>	50	100	160	100k	∞	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

DUAL DIGITAL TRANSISTORS (BIAS RESISTOR TRANSISTORS)

These devices include bias resistors on the semiconductor chip with the transistor. See the BRT diagram for orientation of resistors.




NPN	PNP	$V_{(BR)CEO}$	I_C mA Max	h_{FE} Min	R_1 Ω	R_2 Ω	Package
<i>MUN5211DW1</i>	<i>MUN5111DW1</i>	50	100	35	10k	10k	 SC-88, SOT-363 Duals Case 419B-02
<i>MUN5212DW1</i>		50	100	60	22k	22k	
<i>MUN5213DW1</i>	<i>MUN5113DW1</i>	50	100	80	47k	47k	
<i>MUN5214DW1</i>	<i>MUN5114DW1</i>	50	100	80	10k	47k	
<i>MUN5215DW1</i>	<i>MUN5115DW1</i>	50	100	160	10k	∞	
<i>MUN5216DW1</i>	<i>MUN5116DW1</i>	50	100	160	4.7k	∞	
<i>MUN5230DW1</i>		50	100	3.0	1.0k	1.0k	
<i>MUN5232DW1</i>		50	100	15	4.7k	4.7k	
<i>MUN5233DW1</i>	<i>MUN5133DW1</i>	50	100	80	4.7k	47k	
<i>MUN5235DW1</i>	<i>MUN5135DW1</i>	50	100	80	2.2k	47k	
<i>MUN5237DW1</i>		50	100	80	47k	22k	
NSBC114EDXV6	NSBA114EDXV6	50	100	35	10k	10k	 SOT-563 Duals Case 463A-01
NSBC124EDXV6		50	100	60	22k	22k	
NSBC144EDXV6	NSBA144EDXV6	50	100	80	47k	47k	
NSBC114YDXV6	NSBA114YDXV6	50	100	80	10k	10k	
NSBC114TDXV6		50	100	160	10k	–	
NSBC143ZDXV6		50	100	80	4.7k	4.7k	
	NSBA123JDXV6	50	100	80	2.2k	47k	
NSBC115EDXV6	NSBA115EDXV6	50	100	80	100k	100k	 SOT-963 Case 527AA
NSBC143EDP6	NSBA143EDP6	50	100	15	4.7k	4.7k	
NSBC114EDP6	NSBA114EDP6	50	100	35	10k	10k	
NSBC124EDP6	NSBA124EDP6	50	100	60	22k	22k	
NSBC114YDP6	NSBA114YDP6	50	100	80	10k	47k	
NSBC123JDP6	NSBA123JDP6	50	100	80	2.2k	47k	
NSBC143ZDP6	NSBA143ZDP6	50	100	80	4.7k	47k	
NSBC144EDP6	NSBA144EDP6	50	100	80	47k	47k	
NSBC144WDP6	NSBA144WDP6	50	100	80	47k	22k	
NSBC114TDP6	NSBA114TDP6	50	100	160	10k	∞	
NSBC115TDP6	NSBA115TDP6	50	100	160	100k	∞	
NSBC123TDP6	NSBA123TDP6	50	100	160	2.2k	∞	

BIPOLAR TRANSISTORS

DUAL DIGITAL TRANSISTORS (BIAS RESISTOR TRANSISTORS)

These devices include bias resistors on the semiconductor chip with the transistor. See the BRT diagram for orientation of resistors.




NPN	PNP	V_{(BR)CEO}	I_C mA Max	h_{FE} Min	R₁ Ω	R₂ Ω	Package
NSBC114YF3	NSBA114YF3	45	100	80	10k	47k	 SOT-1123 Case 524AA
IMH20TR1	–	15	600	100	2.2k	–	 SC-74 Case 318F-05

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

COMBINATIONAL DIGITAL TRANSISTORS (BIAS RESISTOR TRANSISTORS)

These devices include bias resistors on the semiconductor chip with the transistor. See the BRT diagram for orientation of resistors.




Device	Type	V_{(BR)CEO}	I_C mA Max	h_{FE} Min	Q₁	Q₂	Package
MUN5311DW1	Dual Complementary	50	100	35	MUN5211	MUN5111	 SC-88, SOT-363 Case 419B-02
MUN5312DW1		50	100	60	MUN5212	MUN5112	
MUN5313DW1		50	100	80	MUN5213	MUN5113	
MUN5314DW1		50	100	80	MUN5214	MUN5114	
MUN5315DW1		50	100	160	MUN5215	MUN5115	
MUN5316DW1		50	100	160	MUN5216	MUN5116	
MUN5330DW1		50	100	3.0	MUN5230	MUN5130	
MUN5333DW1		50	100	80	MUN5233	MUN5133	
MUN5334DW1		50	100	80	22k/47k	22k/47k	
MUN5335DW1		50	100	80	MUN5235	MUN5135	
NSB4904DW1		50	100	80	22k/47k	22k/47k	
UMC3N	Dual Common Base Collector	50	100	35	4.7k/10k	47k/47k	 SC-88A, SOT-353 SC70-5 Case 419A-02
UMC5N		50	100	20	47k/∞	47k/∞	
NSB1706DMW5	Dual Common Emitter	50	100	80	4.7k/47k	4.7k/47k	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

COMBINATIONAL DIGITAL TRANSISTORS (BIAS RESISTOR TRANSISTORS)

These devices include bias resistors on the semiconductor chip with the transistor. See the BRT diagram for orientation of resistors.




Device	Type	$V_{(BR)CEO}$	I_C mA Max	h_{FE} Min	Q1	Q2	Package		
EMC3DXV5	Dual Common Base Collector	50	100	35	10k/10k	10k/10k	 SOT-553 Case 463B-01		
EMC4DXV5		50	100	80	10k/47k	4.7k/47k			
EMC5DXV5		50	100	35	4.7k/10k	4.7k/47k			
EMG2DXV5	Dual Common Base, Common Emitter	50	100	80	4.7k/47k	4.7k/47k			
NSTB1002DXV5	Dual Common Base Collector	40	100	100	47k/47k	47k/47k		 SOT-563 Case 463A-01	
NSTB1005DXV5		50	100	80	47k/47k	47k/47k			
NSB1010XV5		50	100	–	4.7k/4.7k	10k/10k			
EMD4DXV6	Dual Complementary	50	100	80	10k/47k	47k/47k			 SOT-563 Case 463A-01
EMD5DXV6		50	100	20	4.7k/10k	47k/47k			
NSBC114EPDXV6		50	100	35	10k/10k	10k/10k			
NSBC114YPDXV6		50	100	80	10k/47k	10k/47k			
NSBC123JPDXV6		50	100	80	2.2k/47k	2.2k/47k			
NSBC124EPDXV6		50	100	60	22k/22k	22k/22k			
NSBC143TPDXV6		50	100	160	4.7k/∞	4.7k/∞			
NSBC143ZPDXV6		50	100	80	4.7k/47k	4.7k/47k			
NSBC144EPDXV6		50	100	80	47k/47k	47k/47k			
NSB1011XV6	Dual NPN	50	100	–	2.2k/47k	10k/10k			

Devices listed in ***bold italic*** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

COMBINATIONAL DIGITAL TRANSISTORS (BIAS RESISTOR TRANSISTORS) (continued)

These devices include bias resistors on the semiconductor chip with the transistor. See the BRT diagram for orientation of resistors.




Device	Type	$V_{(BR)CEO}$	I_C mA Max	h_{FE} Min	Q1	Q2	Package
<i>NSBC114EPD6</i>	Dual Complementary	50	100	35	10k/10k	10k/10k	 SOT-963 Case
<i>NSBC114YPDP6</i>		50	100	80	10k/47k	10k/47k	
<i>NSBC123JPDP6</i>		50	100	80	2.2k/47k	2.2k/47k	
<i>NSBC143ZPDP6</i>		50	100	80	4.7k/47k	4.7k/47k	
<i>NSBC144EPDP6</i>		50	100	80	47k/47k	47k/47k	
<i>NSBC115TPDP6</i>		50	100	160	100k/∞	100k/∞	

Devices listed in ***bold italic*** are ON Semiconductor preferred devices.

COMPLEX DIGITAL TRANSISTORS

These devices include bias resistors on the semiconductor chip with the transistor. See the BRT diagram for orientation of resistors.




Device	Switching Transistor				Digital Transistor			Package
	$V_{(BR)CEO}$ V	I_C (mA) Max	h_{FE}		h_{FE} Min	R1 Ω	R2 Ω	
			Min	Max				
<i>EMF5XV6</i>	12	500	270	680	80	47K	47K	 SOT-563 Case 463A-01
<i>EMF18XV6</i>	60	100	120	560	80	47K	47K	

Devices listed in ***bold italic*** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

LOW SATURATION VOLTAGE TRANSISTORS

NPN	PNP	$V_{(BR)CEO}$	I_C DC A Max	I_C Peak A Max	h_{FE} @ 1.0 A		f_t MHz Min	$V_{CE(sat)}$ @ 1.0 A Max	Package
					Min	Max			
NSS1C201L	-	100	2	3	120	360	100	0.09	 TO-236AB, SOT-23 Case 318-08 STYLE 6
-	NSS1C200L	100	2	3	120	360	120	0.115	
NSS60201L	-	60	2	4	200	500	150	0.070	
-	NSS60200L	60	2	4	200	500	150	0.095	
NSS40201L	-	40	2	4	200	500	150	0.060	
-	NSS40200L	40	2	4	200	500	150	0.090	
NSS30101L	-	30	1	2	100	500	100	0.200	
-	NSS30100L	30	1	2	100	500	100	0.300	
NSS20201L	-	20	2	4	200	500	150	0.050	
-	NSS20200L	20	2	4	200	500	150	0.080	
NSS12201L	-	12	2	4	200	500	150	0.055	
-	NSS12200L	12	2	4	200	500	150	0.080	
NSS20101J	-	20	1	2	200	500	350	0.22	 SC-89 Case 463A-01
-	NSS12100M3	12	1	3	120			0.41	 SOT-723 Case 631AA-01
NSS30071MR6	-	30	0.7	2	150	500	100	0.250	 SC-74 Case 318F-05 STYLE 2
-	NSS30070MR6	30	0.7	2	150	500	100	0.250	
-	NSS35200MR6	35	2	5	100	400	100	0.150	 TSOP-6 Single Case 318G-02 STYLE 6
NSS30201MR6	-	30	2	5	200	900	100	0.150	
NSS20201MR6	-	20	2	5	200	900	100	0.150	
-	NSS20300MR6	20	3	5	100	400	100	0.150	
NSS40601CF8	-	40	6	6	225	500	100	0.065	 ChipFET™ Case 1206A-03 STYLE 4
-	NSS40600CF8	40	6	6	220	500	100	0.065	
-	NSS35200CF8	35	2	7	100	400	100	0.150	
NSS20601CF8	-	20	6	6	250	500	100	0.050	
NSS12601CF8	-	12	6	6	250	500	100	0.050	
NSS40501UW3	-	40	5	6	250	500	100	0.045	 WDFN3 Case 506AU-01
-	NSS40500UW3	40	5	6	250	500	100	0.080	
NSS20501UW3	-	20	5	6	250	500	100	0.045	
-	NSS20500UW3	20	5	7	250	500	100	0.090	
NSS12501UW3	-	12	5	6	250	500	100	0.045	
-	NSS12500UW3	12	5	6	250	500	100	0.070	
NSS12100UW3	-	12	1	2	200	400	200	0.44	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

BIPOLAR TRANSISTORS

LOW SATURATION VOLTAGE TRANSISTORS (continued)

NPN	PNP	$V_{(BR)CEO}$	I_C DC A Max	I_C Peak A Max	h_{FE} @ 1.0 A		f_t MHz Min	$V_{CE(sat)}$ @ 1.0 A Max	Package
					Min	Max			
-	NSS40200UW6	40	2	4	150	500	100	0.120	 WDFN6 Case 506AS-01
-	NSS12200W	12	2	3	100	300	100	0.290	 SC-88, SOT-363 Case 419B-02 STYLE 20
-	NSS12100XV6	12	1	2	200	500	150	0.280	 SOT-563 Case 463A-01
NJD2873	-	50	2	3	120	360	65	0.300	 DPAK Case 369C-01
NSS1C201MZ4	-	100	2	3	120	360	100	0.100	 SOT-223 Case 318E-04
-	NSS1C200MZ4	100	2	3	120	360	120	0.125	
NSS40301MZ4	-	40	3	5	200	500	150	0.045	
-	NSS40300MZ4	40	3	5	200	500	150	0.050	
NSS60601MZ4	-	60	6	12	120	360	100	0.060	
-	NSS60600MZ4	60	6	12	120	360	100	0.065	
-	NSB9435	30	3	5	125	500	110	0.210	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

LOW SATURATION VOLTAGE MULTIPLE TRANSISTORS

Device	Type	$V_{(BR)CEO}$	I_C DC	I_C Peak	h_{FE}		f_t	$V_{CE(sat)}$	Package
					Min	Max			
NSS40301MD	Matched Dual NPN	40	3	6	200		100	0.05	 8 1 SOIC-8 Case 751
NSS40300DD	Dual PNP	40	3	6	220		100	0.095	
NSS40300MD	Matched Dual PNP	40	3	6	220		100	0.095	
NSS40302PD	Dual Complementary	40	3	6	200		100	0.06	

LOAD SWITCH TRANSISTORS (Low Saturation Voltage Transistors with BRT Driver)

NPN	PNP	$V_{(BR)CEO}$	I_C DC A Max	I_C Peak A Max	h_{FE} @ 1.0 A		f_t MHz Min	$V_{CE(sat)}$ @ 0.1 A Max	Package
					Min	Max			
-	EMF5XV6	50	0.1	0.5	270	680	-	0.250	 SOT-563 Case 463A-01
-	EMF18XV6	50	0.1	0.5	120	560	-	0.400	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

Clock and Data Distribution

Clock and Data Distribution

Table of Contents

	Page
Arithmetic Functions	78
Adders/Subtractors	78
Counters	78
Dividers	79
Magnitude Comparators	80
Prescalers	80
Buffers	81
Clock Drivers	81
Crosspoint Switches	84
Flip-Flops	84
Latches and Registers	86
Logic Gates	87
Multiplexers	89
Receivers/Drivers	91
Serial/Parallel Converters	93
Skew Management	93
Translators	94

**ARITHMETIC FUNCTIONS
ADDERS/SUBTRACTORS**

Device	Type	V _{CC} Typ (V)	Input Level	Output Level	t _{pd} Typ (ns)	t _R & t _F Max (ps)	Package
MC10H180	Dual 2-Bit Adder/Subtractor	-5.2	ECL	ECL	1.8	2100	PDIP-16, PLCC-20

COUNTERS

Device	Type	V _{CC} Typ (V)	Input Level	Output Level	f _{Max} Typ (MHz)	t _{pd} Typ (ns)	t _R & t _F Max (ps)	Package
MC100EP016A	8-Bit Synchronous Binary Up Counter	3.3	ECL, CML	ECL	1400	0.55	320	QFN-32, LQFP-32
MC10EP016	8-Bit Synchronous Binary Up Counter	3.3	ECL, CML	ECL	900	0.5	220	LQFP-32
MC100E016	8-Bit Synchronous Binary Up Counter	5	ECL	ECL	900	0.775	700	PLCC-28
MC10E016	8-Bit Synchronous Binary Up Counter	5	ECL	ECL	900	0.775	800	PLCC-28
MC10H016	4-Bit Binary Counter	5	ECL	ECL	200	1.8	21	PDIP-16, PLCC-20
MC100E136	6-Bit Universal Up/Down Counter	5	ECL	ECL	650	1.15	600	PLCC-28
MC10E136	6-Bit Universal Up/Down Counter	5	ECL	ECL	650	1.15	600	PLCC-28
MC10H136	Universal Hexadecimal Counter	5	ECL	ECL	250	1.5	2400	PDIP-16, PLCC-20
MC100E137	8-Bit Ripple Counter	5	ECL	ECL	2200	2.9	600	PLCC-28
MC10E137	8-Bit Ripple Counter	5	ECL	ECL	2200	2.9	600	PLCC-28

**ARITHMETIC FUNCTIONS (continued)
DIVIDERS**

Device	Input Level	Output Level	Type	V _{CC} Typ (V)	f _{Max} Typ (MHz)	t _{pd} Typ (ns)	t _R & t _F Max (ps)	Package
NB6L239	ECL, CML, LVDS, CMOS	ECL	Dual Bank ÷ 1/2/4/8, ÷ 2/4/8/16	2.5	3000	0.47	120	QFN-16
NB6N239S	ECL, CML, LVDS, CMOS	LVDS	Dual Bank ÷ 1/2/4/8, ÷ 2/4/8/16	3.3	3000	0.665	190	QFN-16
NB7N017M	ECL, CML, LVDS, CMOS	CML	8 Bit Dual Modulus Divider	3.3	3500	0.5	65	QFN-52
MC100LVEP34	ECL, CML, LVDS	ECL	÷ 2, ÷ 4, ÷ 8	3.3	2800	0.7	250	TSSOP-16, SOIC-16
MC100LVEL34	ECL, CML, LVDS	ECL	÷ 2, ÷ 4, ÷ 8	3.3	1500	0.7	400	TSSOP-16, SOIC-16
MC100EL34	ECL	ECL	÷ 2, ÷ 4, ÷ 8	5	1100	1	52.5	SOIC-16
MC100EL34	ECL	ECL	÷ 2, ÷ 4, ÷ 8	5	1100	1	52.5	SOIC-16
MC100LVEL37	ECL, LVDS	ECL	1:4 ÷ 1/÷ 2	3.3	1000	0.7	550	SOIC-20
MC100LVEL38	ECL	ECL	÷ 2, ÷ 4/6	3.3	1000	0.9	550	SOIC-20
MC100EL38	ECL	ECL	÷ 2, ÷ 4/6	5	1200	0.9	550	SOIC-20
MC100EP139	ECL, CML	ECL	÷ 2/4, ÷ 4/5/6	3.3	1000	0.75	275	TSSOP-20, SOIC-20, QFN-20
MC100EP139	ECL, CML	ECL	÷ 2/4, ÷ 4/5/6	3.3	1000	0.75	275	TSSOP-20, SOIC-20
MC100LVEL39	ECL, LVDS	ECL	÷ 2/4, ÷ 4/6	3.3	1000	0.9	550	SOIC-20
MC100EL39	ECL	ECL	÷ 2/4, ÷ 4/6	5	1200	0.9	550	SOIC-20
NB7L32M	ECL, CML, LVDS	CML	÷ 2	2.5	14000	0.155	45	QFN-16
MC100EP32	ECL, CML	ECL	÷ 2	3.3	4000	0.35	170	TSSOP-8, SOIC-8, DFN-8
MC100EP32	ECL, CML	ECL	÷ 2	3.3	4000	0.35	170	TSSOP-8, SOIC-8, DFN-8
MC100LVEL32	ECL, LVDS	ECL	÷ 2	3.3	2600	0.51	320	TSSOP-8, SOIC-8, DFN-8
MC100EL32	ECL	ECL	÷ 2	5	3000	0.51	350	TSSOP-8, SOIC-8
MC100EL32	ECL	ECL	÷ 2	5	3000	0.51	350	TSSOP-8, SOIC-8
MC100EP33	ECL, CML	ECL	÷ 4	3.3	4000	0.32	180	TSSOP-8, SOIC-8, DFN-8
MC100EP33	ECL, CML	ECL	÷ 4	3.3	4000	0.32	180	TSSOP-8, SOIC-8, DFN-8
MC100LVEL33	ECL, LVDS	ECL	÷ 4	3.3	4000	0.63	320	TSSOP-8, SOIC-8, DFN-8
MC100EL33	ECL	ECL	÷ 4	5	4200	0.65	350	TSSOP-8, SOIC-8
MC100EL33	ECL	ECL	÷ 4	5	4000	0.65	350	TSSOP-8, SOIC-8

ARITHMETIC FUNCTIONS (continued)
MAGNITUDE COMPARATORS

Device	Input Level	Output Level	Type	V _{cc} Typ (V)	f _{Max} Typ (MHz)	t _{pd} Typ (ns)	t _R & t _F Max (ps)	Package
MC10E166	ECL	ECL	9-Bit	5	1100	0.85	800	PLCC-20
MC10H166	ECL	ECL	5-Bit	5		2	1600	PDIP-16, PLCC-20

PRESCALERS

Device	Input Level	Output Level	Type	V _{cc} Typ (V)	f _{Max} Typ (MHz)	Package
MC12026A	ECL	ECL	1.1 GHz Dual Modulus Prescaler	5	1100	SOIC-8
MC12080	ECL	ECL	1.1 GHz Prescaler	5	1100	SOIC-8
MC12093	ECL	ECL	1.1 GHz Prescaler, ÷ 2, ÷ 4, ÷ 8	3.3	1100	SOIC-8, DFN-8
MC12095	ECL	ECL	2.5 GHz Prescaler	3.3	3000	SOIC-8

BUFFERS

Device	V _{cc} Typ (V)	Input Level	Output Level	Output Level	t _{pd} Typ (ns)	t _{skew(OO)} Max (ps)	t _r & t _f Max (ps)	Package
MC100LVEL12	3.3	ECL, CML	ECL	LVECL/LVPECL	0.445		550	TSSOP-8, SOIC-8, DFN-8
MC100EL12	5	ECL	ECL	ECL/PECL	0.29		550	TSSOP-8, SOIC-8
MC10EL12	5	ECL	ECL	ECL/PECL	0.29		550	TSSOP-8, SOIC-8
MC100E112	5	ECL	ECL	ECL/PECL	0.4	40	700	PLCC-28
MC10E112	5	ECL	ECL	ECL/PECL	0.4	40	700	PLCC-28
MC10E122	5	ECL	ECL	S.E.	0.35	75	800	PLCC-28
MC10H123	5	ECL	ECL	ECL/PECL	1.5		1700	PDIP-16, PLCC-20
MC10H188	5	ECL	ECL	ECL/PECL	1.3		2400	PDIP-16, PLCC-20, SOEIAJ-16
MC10H189	5	ECL	ECL	MECL	1.3		2400	PDIP-16, PLCC-20, SOEIAJ-16
NB4N316M	3.3	ECL, CML, CMOS, LVDS	CML	CML	0.55	20	300	TSSOP-8
NB4N527S	3.3	ECL, CML, CMOS, LVDS, HSTL	LVDS	LVDS	0.275	50	300	QFN-16
NB4N855S	3.3	ECL, CML, CMOS, LVDS, HSTL	LVDS	LVDS	0.47	25	140	Micro-10

CLOCK DRIVERS

Product	Outputs Per	Channels	Input Level	Output Level	V _{cc} Typ (V)	f _{max} Typ (MHz)	t _{skew(OO)} Max (ps)	t _{jitter} Typ (ps)	t _r & t _f Max (ps)	Package
MC100E210	4+5	2	ECL	ECL	5	700	75	0.2	600	PLCC-28
MC100LVE210	4+5	2	ECL	ECL	3.3	700	75	0.2	600	PLCC-28
NB100LVEP224	24	1	ECL	ECL	2.5	1000	40	5	300	LQFP-64
NB100EP223	22	1	ECL, HSTL	HSTL	3.3	500	25	0.2	700	LQFP-64
NB4N121K	21	1	ECL, CML, CMOS, LVDS	HCSL	3.3	200	50	1	340	QFN-52
NB100LVEP221	20	1	ECL/PECL/HSTL	ECL	2.5	1000	20	1	300	QFN-52, LQFP-52
MC100LVE222	15	1	ECL	ECL	3.3	1500	50	0.2	600	LQFP-52
NB100LVEP222	15	1	CML, LVPECL, LVDS	ECL	2.5	1000	20	0.2	160	QFN-52, LQFP-52
MC100LVEP111	10	1	ECL, HSTL	ECL	2.5	3000	25	0.2	200	QFN-32, LQFP-32
NB4N111K	10	1	ECL, CML, LVDS	HCSL	3.3	400	100	1	700	QFN-32
NB7L111M	10	1	ECL, CML, CMOS, LVDS	CML	2.5	5500	20	0.2	75	QFN-52
MC100E111	9	1	ECL	ECL	5	800	50	0.2	600	PLCC-28
MC100EP809	9	1	ECL, CML, LVDS, HSTL	HSTL	3.3	750	15	1.4	600	LQFP-32
MC100H641	9	1	ECL	TTL	5	65	350		1700	PLCC-28
MC100LVE111	9	1	ECL	ECL	3.3	1500	20	0.2	600	PLCC-28

ON Semiconductor Selector Guide – Clock and Data Distribution

CLOCK DRIVERS

Product	Outputs Per	Channels	Input Level	Output Level	V _{CC} Typ (V)	f _{max} Typ (MHz)	t _{skew(OO)} Max (ps)	t _{jitter} Typ (ps)	t _R & t _F Max (ps)	Package
MC10E111	9	1	ECL	ECL	5	800	50	0.2	600	PLCC-28
MC10E411	9	1	ECL	ECL	5	1000	50	0.2	600	PLCC-28
MC10H641	9	1	ECL	ECL	5	65	350		1700	PLCC-28
MC10H645	9	1	TTL	TTL	5		650		2500	PLCC-28
MC100E310	8	1	ECL	ECL	5	900	50	0.2	600	PLCC-28
MC100H640	8	1	ECL	TTL	5	135	500		2500	PLCC-28
MC100H641	8	1	ECL	TTL	5	80	350		1700	PLCC-28
MC100H642	8	1	ECL	TTL	5	100	500		2500	PLCC-28
MC100H643	8	1	ECL	TTL	5	80	500		1200	PLCC-28
MC100H646	8	1	ECL	TTL	5	80	350		1500	PLCC-28
MC100LVE310	8	1	ECL	ECL	3.3	1000	50	1.5	600	PLCC-28
MC10H640	8	1	ECL	TTL	5		500		2500	PLCC-28
MC10H642	8	1	ECL	TTL	5	100	500		2500	PLCC-28
MC10H643	8	1	ECL	TTL	5	80	500		1200	PLCC-28
MC10H646	8	1	ECL	TTL	5	80	350		1500	PLCC-28
MC100E211	6	1	ECL	ECL	5	700	75	0.2	400	PLCC-28
MC10E211	6	1	ECL	ECL	5	700	75	0.2	400	PLCC-28
NB7VQ1006M	6	1	ECL, CML, LVDS	CML	1.8	7500	1	0.2	65	QFN-24
MC100EL14	5	1	ECL	ECL	5	1000	50	0.2	500	SOIC-20
MC100EP14	5	1	ECL, HSTL	ECL	3.3	2000	45	0.2	270	TSSOP-20
MC100EP210S	5	2	ECL, LVDS	LVDS	3.3	1000	20	0.2	225	QFN-32, LQFP-32
MC100LVEL14	5	1	ECL	ECL	3.3	1000	50	0.2	500	SOIC-20
MC100LVEP14	5	1	ECL, HSTL	ECL	2.5	2000	25	0.2	250	TSSOP-20
MC100LVEP210	5	2	ECL, HSTL	ECL	2.5	3000	20	0.2	270	QFN-32, LQFP-32
NBSG14	5	1	ECL, CML, CMOS, LVDS	RSECL	2.5	12000	15	0.5	55	QFN-16, BGA-16
MC100EL15	4	1	ECL	ECL	5	1000	50	0.2	575	SOIC-16
MC10EL15	4	1	ECL	ECL	5	1000	50	0.2	575	SOIC-16
NB3L553	4	1	CMOS	CMOS	2.5	200	50		1000	SOIC-8, DFN-8
NB3N2304NZ	4	1	CMOS	CMOS	3.3	140	100		1500	TSSOP-8, DFN-8
NB3N551	4	1	CMOS	CMOS	3.3	180	160	2	1	SOIC-8, DFN-8
NB6HQ14M	4	1	CML, ECL, LVDS	CML	2.5	5000	3	0.2	0.03	QFN-16
NB6L14M	4	1	ECL, CML, CMOS, LVDS	CML	2.5	3000	20	0.2	150	QFN-16

CLOCK DRIVERS

Product	Outputs Per	Channels	Input Level	Output Level	V _{CC} Typ (V)	f _{max} Typ (MHz)	t _{skew(OO)} Max (ps)	t _{jitter} Typ (ps)	t _R & t _F Max (ps)	Package
NB6L14	4	1	ECL, CML, CMOS, LVDS	ECL	2.5	3000	20	0.2	225	QFN-16
NB6N14S	4	1	ECL, CML, CMOS, LVDS	LVDS	3.3	2000	20	0.5	190	QFN-16
NB7HQ14M	4	1	CML, ECL, LVDS	CML	2.5	7000	15	0.2	45	QFN-16
NB7L14M	4	1	ECL, CML, CMOS, LVDS	CML	2.5	8000	15	0.5	60	QFN-16
MC100EL13	3	2	ECL	ECL	5	1000	50	0.2	500	SOIC-20
MC100LVEL13	3	2	ECL	ECL	3.3	1000	50	0.2	500	SOIC-20
NB4L6254	3	2	ECL, CML, CMOS, LVDS	ECL	2.5	3000	50	0.3	300	LQFP-32
MC100EL11	2	1	ECL	ECL	5	2000	5	0.2	350	SOIC-8, TSSOP-8
MC100EP11	2	1	ECL	ECL	3.3	3000	20	0.2	180	SOIC-8, TSSOP-8, DFN-8
MC100LVEL11	2	1	ECL	ECL	3.3	1000	20	0.2	180	SOIC-8, TSSOP-8, DFN-8
MC100LVEP11	2	1	ECL, CML, LVDS	ECL	2.5	3000	20	0.2	180	SOIC-8, TSSOP-8, DFN-8
MC10EL11	2	1	ECL	ECL	5	2000	5	0.2	350	SOIC-8, TSSOP-8
MC10EP11	2	1	ECL	ECL	3.3	3000	20	0.2	180	SOIC-8, TSSOP-8
MC10LVEP11	2	1	ECL	ECL	2.5	3000	20	0.2	180	SOIC-8, TSSOP-8
NB4L339	2	1	ECL, CML, LVDS	ECL	2.5	700	60	0.5	250	QFN-32
NB4N11M	2	1	ECL, CML, CMOS, LVDS	CML	3.3	2500	25	1	300	TSSOP-8
NB6L11	2	1	ECL, CML, CMOS, LVDS	ECL	2.5	6000	15	0.2	120	SOIC-8, TSSOP-8
NB6L11M	2	1	ECL, CML, CMOS, LVDS	CML	2.5	4000	15	0.15	120	QFN-16
NB6L11S	2	1	ECL, CML, CMOS, LVDS	LVDS	2.5	2000	25	0.5	170	QFN-16
NB6L572M	2	1	CML, ECL, LVDS	CML	2.5, 3.3	6000	15	0.2	50	QFN-32
NB6L611	2	1	ECL, CML, CMOS, LVDS	ECL	2.5	3000	15	0.2	200	QFN-16
NB6LQ572M	2	1	CML, ECL, LVDS	CML	2.5, 3.3	6000	15	0.2	50	QFN-32
NB6N11S	2	1	ECL, CML, CMOS, LVDS	LVDS	3.3	2000	30	0.5	120	QFN-16
NB7L11M	2	1	ECL, CML, CMOS, LVDS	CML	2.5	8000	15	0.2	60	QFN-16
NBSG11	2	1	ECL, CML, CMOS, LVDS	RSECL	2.5	12000	15	0.5	30	QFN-16, BGA-16
NB4N855S	1	1	ECL, CML, CMOS, LVDS, HSTL, SSTL	LVDS	3.3	1500	25	0.5	140	Micro-10
NB7L585R	6	1	CML, ECL, LVDS	RSECL	2.5	7000	20	0.2	70	QFN-32

CROSSPOINT SWITCHES

Device	V _{CC} Typ (V)	Input Level	Output Level	f _{Max} Max (V)	t _{Jitter} Max (ps)	t _{skew} Max (ps)	t _{pd} Max (ps)	Package
NBSG72A	2.5 / 1.8	ECL, CML, LVDS	ECL (with OLS)	7	1.5	25	255	QFN-16
NB7V72M	2.5 / 1.9	ECL, CML, LVDS	CML	5	0.8	30		QFN-16
NB4N840M	3.3	CML	CML	3.5	0.5	25	340	QFN-32
NB4L6254	2.5	CML, ECL, CMOS, LVDS	ECL	3	0.8	60	610	LQFP-32
NB4L858M	2.5	ECL, CML	CML	3	0.5	12	450	LQFP-32
NB6L72M	2.5	ECL, CML, CMOS, LVDS	CML	3	0.5	20	480	QFN-16
NB6L72	2.5	ECL, CML, CMOS, LVDS	ECL	3	1.0	20	525	QFN-16
NB4L7210	2.5	ECL, CML, CMOS, LVDS	ECL	1	0.19	10	875	QFN-52

FLIP-FLOPS

Device	Type	V _{CC} Typ (V)	Input Level	Output Level	f _{Toggle} Typ (MHz)	t _{pd} Typ (ns)	t _{su} Min (ns)	t _h Min (ns)	t _{Jitter} Typ (ps)	t _R & t _F Max (ps)	Package
MC100EP29	D-Type	3.3	ECL, CML	ECL	3000	0.42	0.1	0.1	0.2	300	TSSOP-20, QFN-20
MC10EP29	D-Type	3.3	ECL, CML	ECL	3000	0.42	0.1	0.1	0.2	300	TSSOP-20, QFN-20
MC100LVEL29	D-Type	3.3	ECL, LVDS	ECL	1100	0.58	0	0.1	1	550	SOIC-20
MC100EL29	D-Type	5	ECL	ECL	1100	0.58	0	0.1	1	550	SOIC-20
MC100LVEL30	D-Type	3.3	ECL	ECL	1200	0.45	0.15	0.2	1	550	SOIC-20
MC100EL30	D-Type	5	ECL	ECL	1200	0.45	0.15	0.2	1	550	SOIC-20
MC100EP31	D-Type	3.3	ECL, CML	ECL	3000	0.34	0.1	0.15	0.2	200	TSSOP-8, SOIC-8, DFN-8
MC10EP31	D-Type	3.3	ECL, CML	ECL	3000	0.34	0.1	0.15	0.2	200	TSSOP-8, SOIC-8
MC100LVEL31	D-Type	3.3	ECL	ECL	2900	0.475	0.15	0.25	1	320	TSSOP-8, SOIC-8
MC100EL31	D-Type	5	ECL	ECL	2800	0.475	0.15	0.25	1	350	TSSOP-8, SOIC-8
MC100EL31	D-Type	5	ECL	ECL	2800	0.475	0.15	0.25	1	350	TSSOP-8, SOIC-8
MC100EP51	D-Type	3.3	ECL, CML	ECL	3000	0.37	0.1	0.1	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC10EP51	D-Type	3.3	ECL, CML	ECL	3000	0.375	0.1	0.1	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC100LVEL51	D-Type	3.3	ECL	ECL	2800	0.475	0.15	0.25	1	320	TSSOP-8, SOIC-8, DFN-8
MC100EL51	D-Type	5	ECL	ECL	2800	0.475	0.15	0.25	1	350	TSSOP-8, SOIC-8
MC100EL51	D-Type	5	ECL	ECL	2800	0.475	0.15	0.25	1	350	TSSOP-8, SOIC-8

FLIP-FLOPS

Device	Type	V _{cc} Typ (V)	Input Level	Output Level	f _{Toggle} Typ (MHz)	t _{pd} Typ (ns)	t _{su} Min (ns)	t _h Min (ns)	t _{jitter} Typ (ps)	t _R & t _F Max (ps)	Package
NB4L52	D-Type	2.5	ECL, CML, CMOS, LVDS	ECL	4000	0.33	0.1	0.05	1	200	QFN-16
MC100EP52	D-Type	3.3	ECL, CML	ECL	4000	0.33	0.05	0	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC100EP52	D-Type	3.3	ECL, CML	ECL	4000	0.33	0.05	0	1	180	TSSOP-8, SOIC-8, DFN-8
MC100EL52	D-Type	5	ECL	ECL	2800	0.365	0.125	0.15	1	350	TSSOP-8, SOIC-8
MC100EL52	D-Type	5	ECL	ECL	2800	0.365	0.125	0.15	1	350	TSSOP-8, SOIC-8
NBSG53A	D-Type	2.5	ECL, CML, CMOS, LVDS	200, 400, 600, 800 mV	10000	0.215	0.03	0.025	0.5	60	QFN-16, BGA-16
MC100EP131	D-Type	3.3	ECL, CML	ECL	3000	0.46	0.12	0.12	0.2	290	QFN-32, LQFP-32
MC100EP131	D-Type	3.3	ECL, CML	ECL	3000	0.46	0.12	0.12	0.2	290	QFN-32, LQFP-32
MC100E131	D-Type	5	ECL	ECL	1100	0.5	0.15	0.175	1	480	PLCC-28
MC100E131	D-Type	5	ECL	ECL	1100	0.5	0.15	0.175	1	480	PLCC-28
MC10H131	D-Type	5	ECL	ECL	250	1	0.7	0.8		2000	PDIP-16, PLCC-20, SOE/AJ-16
MC10H176	D-Type	5	ECL	ECL	250	1.7	1.5	0.9		1900	PDIP-16, PLCC-20, SOE/AJ-16
MC10H186	D-Type	5	ECL	ECL	250	1.7	1.5	1		2600	PDIP-16, PLCC-20
MC100E431	D-Type	5	ECL	ECL	1100	0.6	0.2	0.2	1	650	PLCC-28
MC10E431	D-Type	5	ECL	ECL	1100	0.6	0.2	0.2	1	650	PLCC-28
MC100EP35	JK-Type	3.3	ECL, CML	ECL	3000	0.41	0.15	0.15	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC10EP35	JK-Type	3.3	ECL, CML	ECL	3000	0.41	0.15	0.15	0.2	180	TSSOP-8, SOIC-8
MC100EL35	JK-Type	5	ECL	ECL	2200	0.525	0.15	0.25	1	350	TSSOP-8, SOIC-8
MC10EL35	JK-Type	5	ECL	ECL	2200	0.525	0.15	0.25	1	350	TSSOP-8, SOIC-8
MC10H135	JK-Type	5	ECL	ECL	250	1.5	1.5	1		2200	PDIP-16, PLCC-20, SOE/AJ-16

LATCHES AND REGISTERS

Device	V _{cc} Typ (V)	Input Level	Output Level	Type	Bits	t _{pd} Typ (ns)	t _{su} Min (ns)	t _h Min (ns)	t _{rec} Typ (ns)	t _{jitter} Typ (ps)	t _r & t _f Max (ps)	Package
MC10H130	5	ECL	ECL	Latch	2	1	2.2	0.7			1700	PDIP-16, PLCC-20
MC100E150	5	ECL	ECL	Latch	6	0.8	0.2	0.2	0.75	1	450	PLCC-28
MC10E150	5	ECL	ECL	Latch	6	0.8	0.2	0.2	0.75	1	450	PLCC-28
MC100E175	5	ECL	ECL	Latch	9	0.6	0.275	0.175	0.85	1	800	PLCC-28
MC10E175	5	ECL	ECL	Latch	9	0.6	0.275	0.175	0.85	1	800	PLCC-28
MC10H175	5	ECL	ECL	Latch	5	1.2	1.5	0.8			1900	PDIP-16, PLCC-20, SOEIAJ-16
MC100E143	5	ECL	ECL	Register	9	0.8	0.05	0.3	0.9	1	800	PLCC-28
MC10E143	5	ECL	ECL	Register	9	0.8	0.05	0.3	0.9	1	800	PLCC-28
MC100E151	5	ECL	ECL	Register	6	0.65	0.15	0.35	0.75	1	450	PLCC-28
MC10E151	5	ECL	ECL	Register	6	0.65	0.15	0.35	0.75	1	450	PLCC-28
MC100EP451	3.3	ECL _{CMIL}	ECL	Register	6	0.45	0.08	0.08	0.25	0.2	260	QFN-32, LQFP-32
MC10EP451	3.3	ECL _{CMIL}	ECL	Register	6	0.45	0.08	0.08	0.25	0.2	260	QFN-32, LQFP-32
MC100E451	5	ECL	ECL	Register	6	0.65	0.15	0.35	0.75	1	800	PLCC-28
MC10E451	5	ECL	ECL	Register	6	0.65	0.15	0.35	0.75	1	800	PLCC-28
MC100E452	5	ECL	ECL	Register	5	0.6	0.175	0.225	0.75	1	650	PLCC-28
MC10E452	5	ECL	ECL	Register	5	0.6	0.175	0.225	0.75	1	650	PLCC-28
MC10E141	5	ECL	ECL	Shift Register	8	0.75	0.175	0.2	0.9	1	800	PLCC-28
MC10H141	5	ECL	ECL	Shift Register	4	1.5	1.5	1			2400	PDIP-16, PLCC-20
MC100EP142	3.3	ECL _{CMIL}	ECL	Shift Register	9	0.675	0.05	0.1	0.8	1	275	QFN-32, LQFP-32
MC10EP142	3.3	ECL _{CMIL}	ECL	Shift Register	9	0.675	0.05	0.1	0.8	1	275	QFN-32, LQFP-32
MC100E142	5	ECL	ECL	Shift Register	9	0.8	0.05	0.3	0.9	1	800	PLCC-28
MC10E142	5	ECL	ECL	Shift Register	9	0.8	0.05	0.3	0.9	1	800	PLCC-28
MC100E241	5	ECL	ECL	Shift Register	8	0.75	0.175	0.2	0.9	1	800	PLCC-28

LOGIC GATES

Device	V _{cc} Typ (V)	Input Level	Output Level	Type	Channels	f _{Toggle} Max (MHz)	t _{pd} Typ (ns)	t _{glitter} Typ (ps)	t _R & t _F Max (ps)	Package
NB7L86M	2.5	ECL, CML, LVDS, CMOS	ECL	SmartGate	1	8000	0.09	0.2	60	QFN-16
NBSG86A	2.375-3.465	ECL, CML, CMOS, LVDS	200, 400, 600, 800 mV	SmartGate	1	8000	0.165	0.5	65	BGA-16, QFN-16
MC10H104	5	ECL	ECL	AND	4		1		1700	PDIP-16, PLCC-20, SOEIAJ-16
MC100E104	5	ECL	ECL	AND/NAND	5	2000	0.385	1	700	PLCC-28
MC100E404	5	ECL	ECL	AND/NAND	4	2000	0.475	1	400	PLCC-28
MC100EL04	5	ECL	ECL	AND/NAND	1	2000	0.24	1	350	TSSOP-8, SOIC-8
MC100EL05	5	ECL	ECL	AND/NAND	1	2000	0.275	1	350	TSSOP-8, SOIC-8
MC100EP05	3.3	ECL, CML	ECL	AND/NAND	1	3000	0.22	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC100EP105	3.3	ECL, CML	ECL	AND/NAND	1	3000	0.22	0.2	180	QFN-32, LQFP-32
MC100LVEL05	3.3	ECL, CML, LVDS	ECL	AND/NAND	1	2000	0.34	1	320	TSSOP-8, SOIC-8
MC100LVEP05	2.5	ECL	ECL	AND/NAND		3000	0.22	0.2	200	TSSOP-8
MC10E104	5	ECL	ECL	AND/NAND	5	700	0.385	1	700	PLCC-28
MC10E404	5	ECL	ECL	AND/NAND	4	700	0.475	1	400	PLCC-28
MC10EL04	5	ECL	ECL	AND/NAND	1	2000	0.24	1	350	TSSOP-8, SOIC-8
MC10EL05	5	ECL	ECL	AND/NAND	1	2000	0.275	1	350	TSSOP-8, SOIC-8
MC10EP05	3.3	ECL, CML	ECL	AND/NAND	1	3000	0.22	0.2	180	TSSOP-8, SOIC-8
MC10EP105	3.3	ECL, CML	ECL	AND/NAND	1	3000	0.22	0.2	180	QFN-32, LQFP-32
MC10H100	5	ECL	ECL	NOR	4		1		2100	PDIP-16, SOEIAJ-16
MC10H102	5	ECL	ECL	NOR	4		1		1600	PDIP-16, PLCC-20, SOEIAJ-16
MC10H106	5	ECL	ECL	NOR	3		1		1800	PDIP-16, PLCC-20, SOEIAJ-16
MC10H211	5	ECL	ECL	NOR	2		1		2200	PDIP-16, PLCC-20, SOEIAJ-16
MC10H103	5	ECL	ECL	OR	4		1		1800	PDIP-16, PLCC-20, SOEIAJ-16
MC10H210	5	ECL	ECL	OR	2		1		1900	PDIP-16, PLCC-20, SOEIAJ-16
MC100E101	5	ECL	ECL	OR/NOR	4	2000	0.35	1	575	PLCC-28
MC100EL01	5	ECL	ECL	OR/NOR	1	2000	0.23	1	235	TSSOP-8, SOIC-8
MC100EP01	3.3	ECL, CML	ECL	OR/NOR	1	3000	0.27	0.2	180	TSSOP-8, SOIC-8, DFN-8

LOGIC GATES

Device	V _{cc} Typ (V)	Input Level	Output Level	Type	Channels	f _{Toggle} Max (MHz)	t _{pd} Typ (ns)	t _{glitter} Typ (ps)	t _R & t _F Max (ps)	Package
MC100EP101	3.3	ECL, CML	ECL	OR/NOR	4	3000	0.3	0.2	220	QFN-32, LQFP-32
MC100LVEL01	3.3	ECL	ECL	OR/NOR	1	2000	0.37	1	320	TSSOP-8, SOIC-8
MC10E101	5	ECL	ECL	OR/NOR	4	700	0.35	1	575	PLCC-28
MC10EL01	5	ECL	ECL	OR/NOR	1	2000	0.23	1	235	TSSOP-8, SOIC-8
MC10EP01	3.3	ECL, CML	ECL	OR/NOR	1	3000	0.27	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC10EP101	3.3	ECL, CML	ECL	OR/NOR	4	3000	0.3	0.2	220	QFN-32, LQFP-32
MC10H101	5	ECL	ECL	OR/NOR	4		1		2200	PDIP-16, PLCC-20, SOEIAJ-16
MC10H105	5	ECL	ECL	OR/NOR	3		1		1600	PDIP-16, PLCC-20, SOEIAJ-16
MC10H109	5	ECL	ECL	OR/NOR	2		1		2100	PDIP-16, PLCC-20, SOEIAJ-16
MC10H209	5	ECL	ECL	OR/NOR	2		0.75		1500	PLCC-20, SOEIAJ-16
MC10H117	5	ECL	ECL	OR-AND/OR-AND INV	2		1		1600	PDIP-16, PLCC-20, SOEIAJ-16
MC10H121	5	ECL	ECL	OR-AND/OR-AND INV	4		1		1800	PDIP-16, PLCC-20, SOEIAJ-16
MC10H113	5	ECL	ECL	XOR	4		1.3		1900	PDIP-16, PLCC-20, SOEIAJ-16
MC100E107	5	ECL	ECL	XOR/XNOR	5	2000	0.41	1	700	PLCC-28
MC100EL07	5	ECL	ECL	XOR/XNOR	1	2000	0.26	1	225	TSSOP-8, SOIC-8, DFN-8
MC100EP08	3.3	ECL, CML	ECL	XOR/XNOR	1	3000	0.25	0.2	180	TSSOP-8, SOIC-8
MC10E107	5	ECL	ECL	XOR/XNOR	5	700	0.41	1	700	PLCC-28
MC10EL07	5	ECL	ECL	XOR/XNOR	1	2000	0.26	1	225	TSSOP-8, SOIC-8
MC10EP08	3.3	ECL, CML	ECL	XOR/XNOR	1	3000	0.25	0.2	180	TSSOP-8, SOIC-8
MC10H107	5	ECL	ECL	XOR/XNOR	3		1		1600	PDIP-16, PLCC-20, SOEIAJ-16

MULTIPLEXERS

Device	V _{cc} Typ (V)	Input Level	Output Level	Mux Ratio	Channels	f _{toggle} Typ (MHz)	t _{pd} Typ (ns)	t _{skew(OO)} Max (ps)	t _{jitter} Typ (ps)	t _r & t _f Max (ps)	Package
MC100EL58	5	ECL	ECL	2:1	1	1500	0.23		1	350	TSSOP-8, SOIC-8
MC100EP58	3.3	ECL, CML	ECL	2:1	1	3000	0.31		0.2	180	TSSOP-8, SOIC-8
MC100LVEL58	3.3	ECL	ECL	2:1	1	1500	0.44		1	320	TSSOP-8, SOIC-8, DFN-8
MC10EL58	5	ECL	ECL	2:1	1	1500	0.23		1	350	TSSOP-8, SOIC-8
MC10EP58	3.3	ECL, CML	ECL	2:1	1	3000	0.31		0.2	180	TSSOP-8, SOIC-8
NB7L86M	2.5	ECL, CML, CMOS, LVDS	CML	2:1	1	8000	0.09		0.2	60	QFN-16
NBSG86A	2.5	ECL, CML, CMOS, LVDS	200, 400, 600, 800 mV	2:1	1	8000	0.165	20	0.5	65	BGA-16, QFN-16
MC100EL56	5	ECL	ECL	2:1	2	1000	0.58	80	1	540	SOIC-20
MC100EP56	3.3	ECL, CML	ECL	2:1	2	3000	0.36	100	0.2	180	TSSOP-20, SOIC-20, QFN-20
MC100LVEL56	3.3	ECL, LVDS	ECL	2:1	2	1000	0.44	80	3	540	SOIC-20
MC10EP56	5	ECL, CML	ECL	2:1	2	3000	0.475	100	0.2	200	TSSOP-20, QFN-20
NB100LVEP56	2.5	ECL, CML	ECL	2:1	2	2500	0.7	50	0.2	170	TSSOP-20, QFN-24
MC100E457	5	ECL	ECL	2:1	3	1000	0.475	40	1	500	PLCC-28
MC100EL59	5	ECL	ECL	2:1	3	1000	0.5	100	1	540	SOIC-20
MC100LVEL59	3.3	ECL	ECL	2:1	3	1000	0.5	100	1	540	SOIC-20
MC10E457	5	ECL	ECL	2:1	3	1000	0.475	40	1	500	PLCC-28
MC100E157	5	ECL	ECL	2:1	4	1000	0.38	70	1	650	PLCC-28
MC10E157	5	ECL	ECL	2:1	4	1100	0.38	70	1	650	PLCC-28
MC10H158	5	ECL	ECL	2:1	4		1.5			2200	PDIP-16, PLCC-20, SOEIAJ-16
MC10H159	5	ECL	ECL	2:1	4		1.5			2200	PLCC-20, SOEIAJ-16
MC100E158	5	ECL	ECL	2:1	5	1000	0.385	60	1	650	PLCC-28
MC10E154	5	ECL	ECL	2:1	5	1100	0.5	50	1	800	PLCC-28
MC10E158	5	ECL	ECL	2:1	5	1100	0.385	60	1	650	PLCC-28
MC10E155	5	ECL	ECL	2:1	6	1100	0.5	75	1	800	PLCC-28
MC10E167	5	ECL	ECL	2:1	6	1400	0.65	75	1	800	PLCC-28

MULTIPLXERS

Device	V _{cc} Typ (V)	Input Level	Output Level	Mux Ratio	Channels	f _{Toggle} Typ (MHz)	t _{pd} Typ (ns)	t _{skew(OO)} Max (ps)	t _{jitter} Typ (ps)	t _{tr} & t _{tf} Max (ps)	Package
NB4N7132	3.3	ECL, CML, LVDS	ECL	2:1		750	0.375		25	175	TSSOP-28
MC100EL57	5	ECL	ECL	4:1	1	1000	0.56	100	1	375	SOIC-16
MC100EP57	3.3	ECL, CML	ECL	4:1	1	3000	0.475	200	0.2	200	TSSOP-20, QFN-20
MC100EL57	5	ECL	ECL	4:1	1	1000	0.56	100	1	375	SOIC-16
MC100EP57	3.3	ECL, CML	ECL	4:1	1	3000	0.475	200	0.2	200	TSSOP-20, QFN-20
MC10H174	5	ECL	ECL	4:1	2		1.5			1600	PDIP-16, PLCC-20, SOEIAJ-16
MC100E171	5	ECL	ECL	4:1	3	1000	0.48	60	1	650	PLCC-28
MC10E156	5	ECL	ECL	4:1	3	1100	0.6	50	1	700	PLCC-28
MC10E171	5	ECL	ECL	4:1	3	1400	0.48	60	1	650	PLCC-28
MC10H164	5	ECL	ECL	8:1	1		1			1600	PDIP-16, PLCC-20, SOEIAJ-16
MC100E163	5	ECL	ECL	8:1	2	1000	0.55	40	1	575	PLCC-28
MC10E163	5	ECL	ECL	8:1	2	1100	0.55	40	1	575	PLCC-28
MC100E164	5	ECL	ECL	16:1	1	1000	0.6	50	1	550	PLCC-28
MC100LVE164	3.3	ECL	ECL	16:1	1	1000	0.6	50	1	550	LQFP-32
MC10E164	5	ECL	ECL	16:1	1	1100	0.6	50	1	550	PLCC-28
MC10H172	5	ECL	ECL		2		2			1800	PDIP-16, PLCC-20
NB4N1158	3.3	ECL, CMOS	ECL		3	1500	0.375		10	150	TSSOP-28
NB7L572	2.5	ECL, CML, CMOS	ECL								QFN-32
MC10H161	5	ECL	ECL	3 Bit to 1 of 8 Decode	1		1			1800	PDIP-16, PLCC-20, SOEIAJ-16
MC10H162	5	ECL	ECL	3 Bit to 1 of 8 decode	1		1			1900	PDIP-16, PLCC-20, SOEIAJ-16
MC10H165	5	ECL	ECL	8 Bit Priority Encode	1		2.2			2400	PDIP-16, PLCC-20
MC10H171	5	ECL	ECL	BIN 1:4 Decode	2		2			1800	PDIP-16, PLCC-20

RECEIVERS/DRIVERS

Device	Type	V _{cc} Typ (V)	Input Level	Output Level	f _{roggle} Max (MHz)	t _{pd} Typ (ns)	t _{jitter} Typ (ps)	t _R & t _F Max (ps)	Package
MC10EL89	Coaxial Cable Driver	5	ECL	2x ECL	1500	0.35		455	TSSOP-8, SOIC-8
MC10EP89	Coaxial Cable Driver	3.3	ECL, CML	2x ECL	2000	0.31		350	TSSOP-8, SOIC-8, DFN-8
MC10SX1189	Fibre Channel Coaxial Cable Driver	5	ECL	2x ECL	2500	0.425		250	SOIC-16
MC10SX1190	Fibre Channel Coaxial Cable Driver	3.3	ECL	2x ECL		0.425		250	TSSOP-20
MC10SX1130	LED Driver	5	ECL	LED	400	1.4		1260	SOIC-16
NBSG16	Signal Driver	2.5	ECL, TTL, CMLS, CML, LVDS	RSECL	12000	0.12	0.3	65	BGA-16, QFN-16
NBSG16M	Signal Driver	2.5	ECL, TTL, CMLS, CML, LVDS	CML	10000	0.12	0.2	53	QFN-16
NBSG16VS	Signal Driver	2.5	ECL, TTL, CMLS, CML, LVDS	RSECL	12000	0.125	0.8	55	BGA-16, QFN-16
NB6L16	Signal Driver	2.5	LVDS, ECL, CML, CMOS, TTL	ECL	6000	0.13	0.2	120	TSSOP-8, SOIC-8
NB4L16M	Signal Driver	2.5	TTL, CMOS, LVDS, ECL, CML	CML	3500	0.265	0.2	90	QFN-16
MC100LVEP16	Signal Driver	3.3	ECL, CML, LVDS	ECL	4000	0.24	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC10LVEP16	Signal Driver	2.5	ECL, CML, LVDS	ECL	4000	0.24	0.2	180	TSSOP-8, SOIC-8
MC100EP16	Signal Driver	3.3	ECL, CML	ECL	4000	0.22	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC10EP16	Signal Driver	3.3	ECL, CML	ECL	4000	0.22	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC100LVEL16	Signal Driver	3.3	ECL, LVDS	ECL	2000	0.3	0.2	320	TSSOP-8, SOIC-8, DFN-8
MC100EL16	Signal Driver	5	ECL	ECL	2000	0.25	0.2	350	TSSOP-8, SOIC-8
MC10EL16	Signal Driver	5	ECL	ECL	2000	0.25	0.2	350	TSSOP-8, SOIC-8
MC100EP16F	Signal Driver	3.3	ECL, CML	ECL	3000	0.3	0.2	100	TSSOP-8, SOIC-8
MC100EP16T	Signal Driver	3.3	ECL, CML	ECL	3000	0.22	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC10EP16T	Signal Driver	3.3	ECL, CML	ECL	3000	0.22	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC100EP16VA	Signal Driver	3.3	ECL, CML	ECL	3000	0.27	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC10EP16VA	Signal Driver	3.3	ECL, CML	ECL	3000	0.27	0.2	180	TSSOP-8, SOIC-8, DFN-8
MC100EP16VB	Signal Driver	3.3	ECL, CML	ECL	3000	0.3	0.2	240	TSSOP-8, SOIC-8
MC100EP16VC	Signal Driver	3.3	ECL, CML	ECL	3000	0.38	0.2	240	TSSOP-8, SOIC-8, DFN-8
MC100EP16VS	Signal Driver	3.3	ECL, CML	ECL	4000	0.22	0.2	180	TSSOP-8, SOIC-8
MC100EP16VT	Signal Driver	3.3	ECL, CML	ECL	4000	0.3	0.2	180	TSSOP-8, SOIC-8, DFN-8
NB100LVEP17	Signal Driver	2.5	ECL, CML, LVDS	ECL	2500	0.25	0.5	240	TSSOP-20, QFN-24

RECEIVERS/DRIVERS

Device	Type	V _{cc} Typ (V)	Input Level	Output Level	f _{Toggle} Max (MHz)	t _{pd} Typ (ns)	t _{Jitter} Typ (ps)	t _R & t _F Max (ps)	Package
MC100EP17	Signal Driver	3.3	ECL, CML	ECL	3000	0.22	0.2	230	TSSOP-20, SOIC-20, QFN-20
MC10EP17	Signal Driver	3.3	ECL, CML	ECL	3000	0.22	0.2	230	TSSOP-20, SOIC-20, QFN-20
MC100LVEL17	Signal Driver	3.3	ECL, LVDS	ECL	2000	0.425	0.2	550	SOIC-20
MC100EL17	Signal Driver	5	ECL	ECL	2000	0.425	0.2	550	SOIC-20
MC10H115	Signal Driver	5	ECL	ECL		1		1500	PDIP-16, PLCC-20, SOEIAJ-16
MC100EP116	Signal Driver	3.3	ECL, CML	ECL	3000	0.26	0.2	240	QFN-32, LQFP-32
MC10EP116	Signal Driver	3.3	ECL	ECL	3000	0.26	0.2	240	LQFP-32
MC100E116	Signal Driver	5	ECL	ECL	1200	0.3	0.2	575	PLCC-28
MC10E116	Signal Driver	5	ECL	ECL	800	0.3	0.2	575	PLCC-28
MC10H116	Signal Driver	5	ECL	ECL		1		1600	PDIP-16, SOIC-16, PLCC-20, SOEIAJ-16
NB7L216	Signal Driver	2.5	CMOS, TTL, LVDS, ECL, CML	RSECL	12000	0.18	0.1	45	QFN-16
NB4N316M	Signal Driver	3.3	CML, ECL, LVDS, CMOS, TTL	CML		0.55		300	TSSOP-8
MC10H330	Signal Driver	5	ECL	ECL		1.5		2000	PLCC-28
MC10H332	Signal Driver	5	ECL	ECL		1.5		2000	PDIP-20, PLCC-20
MC10H334	Signal Driver	5	ECL	ECL		1.6		2200	PLCC-20
MC100E416	Signal Driver	5	ECL	ECL	2000	0.35	0.2	350	PLCC-28
MC10E416	Signal Driver	5	ECL	ECL	2000	0.35	0.2	350	PLCC-28
MC100H680	Signal Driver	5	ECL	TTL		3.2		3400	PLCC-28
MC10H680	Signal Driver	5	ECL	TTL		3.2		3400	PLCC-28
NB4N855S	Signal Driver	3.3	LVDS, CML, ECL, HSTL, SSTL, CMOS, TTL	LVDS		0.47	0.5	140	Micro-10
NB7VQ1006M	Signal Driver	1.8	CML, ECL, LVDS	CML	7500	0.225	0.2	65	QFN-24

SERIAL/PARALLEL CONVERTERS

Device	V _{cc} Typ (V)	Input Level	Output Level	Type	Bits	f _{dr} Typ (Gb/sec)	t _{pd} Typ (ns)	t _{su} Min (ns)	t _h Min (ns)	t _{jitter} Typ (ps)	t _r & t _f Max (ps)	Package
MC100EP445	3.3	ECL, CML	ECL	Serial/Parallel	8	2.5	1.3	-0.4	0.6	0.2	300	QFN-32, LQFP-32
MC10EP445	3.3	ECL, CML	ECL	Serial/Parallel	8	2.5	1.3	-0.4	0.6	0.2	300	LQFP-32
MC100E445	5	ECL	ECL	Serial/Parallel	4	2.0	1.8	-0.25	0.3	1	350	PLCC-28
MC10E445	5	ECL	ECL	Serial/Parallel	4	2.0	1.8	-0.25	0.3	1	350	PLCC-28
MC100EP446	3.3	ECL, CML	ECL	Parallel/Serial	8	3.4	0.8	-0.45	-0.6	0.2	170	QFN-32, LQFP-32
MC10EP446	3.3	ECL, CML	ECL	Parallel/Serial	8	3.4	0.8	-0.45	-0.6	0.2	170	QFN-32, LQFP-32
MC100E446	5	ECL	ECL	Parallel/Serial	4	1.6	1.2	-0.45	0.65	1	350	PLCC-28
MC10E446	5	ECL	ECL	Serial/Parallel	4	2.0	1.8	-0.25	0.3	1	350	PLCC-28

SKEW MANAGEMENT

Device	V _{cc} Typ (V)	Input Level	Output Level	f _{max} Typ (MHz)	t _{d(prog)} Min (ns)	t _{d(prog)} Max (ns)	t _{d(step)} Typ (ps)	t _{jitter} Typ (ps)	t _r & t _f Max (ps)	Package
MC100E195	5	ECL, CML	ECL	1000	2.05	2.6	20	5	325	PLCC-28
MC100E196	5	ECL, CML	ECL	1000	2.05	2.6	20	5	325	PLCC-28
MC100EP195B	3.3	ECL, CML, LVDS	ECL	1200	2.2	12	10	3	300	QFN-32, LQFP-32
MC100EP195	3.3	ECL, CML	ECL	1200	2.2	12.2	10	3	300	QFN-32, LQFP-32
MC100EP196B	3.3	ECL, CML, LVDS	ECL	1200	8.95	12.11	11	1.2	165	QFN-32, LQFP-32
MC100EP196	3.3	ECL, CML	ECL	1200	2.2	12.2	10	3	210	LQFP-32
MC10E195	3.3	ECL, CML	ECL	1000	2.05	2.6	20	5	325	PLCC-28
MC10E196	3.3	ECL, CML	ECL	1000	2.05	2.6	20	5	325	PLCC-28
MC10EP195	3.3	ECL, CML	ECL	1200	2.2	12.2	10	3	300	QFN-32, LQFP-32
NB6L295M	2.5	ECL, CML	CML	1500	6.2	6.2	11	2.4	150	QFN-24

ON Semiconductor Selector Guide – Clock and Data Distribution

TRANSLATORS

Device	V _{cc} Typ (V)	Input Level	Output Level	Channels	f _{max} Typ (MHz)	t _{pd} Typ (ns)	t _r & t _f Max (ps)	Package
MC100EPT20	3.3	CMOS	ECL	1	1000	0.37	180	TSSOP-8, SOIC-8, DFN-8
MC100EPT20	3.3	CMOS	ECL	1	1000	0.37	180	TSSOP-8, SOIC-8, DFN-8
MC100LVELT20	3.3	CMOS	ECL	1	1000	0.37	180	SOIC-8
MC100ELT20	5	CMOS	ECL	1	100	1.2	1500	TSSOP-8, SOIC-8
MC100ELT20	5	CMOS	ECL	1	100	1.2	1500	TSSOP-8, SOIC-8
MC100EPT21	3.3	ECL, CML, LVDS	TTL	1	350	1.4	500	TSSOP-8, SOIC-8, DFN-8
MC100ELT21	5	ECL, CML	TTL	1	100	3.5	750	TSSOP-8, SOIC-8
MC100ELT21	5	ECL, CML	TTL	1	100	3.5	750	TSSOP-8, SOIC-8
MC100EPT22	3.3	TTL, CMOS	ECL	2	1100	0.42	220	TSSOP-8, SOIC-8, DFN-8
MC100LVELT22	3.3	TTL, CMOS	ECL	2	2000	0.35	500	TSSOP-8, SOIC-8
MC100ELT22	5	TTL	ECL	2	100	1.2	1600	TSSOP-8, SOIC-8
MC100ELT22	5	TTL	ECL	2	100	1.2	1600	TSSOP-8, SOIC-8
MC100EPT23	3.3	ECL, CML, LVDS	TTL	2	350	1.5	600	TSSOP-8, SOIC-8, DFN-8
MC100LVELT23	3.3	CML, PECL, LVDS	TTL	2	180	1.7	600	TSSOP-8, SOIC-8, DFN-8
MC100ELT23	5	ECL, CML	TTL	2	100	3.5	1600	TSSOP-8, SOIC-8
NB100ELT23L	3.3	ECL, CML, LVDS	TTL	2	275	2.1	1300	TSSOP-8, SOIC-8
MC100EPT24	3.3	TTL, CMOS	LVNECL	1	1000	0.53	180	TSSOP-8, SOIC-8, DFN-8
MC100ELT24	5	TTL	NECL	1	400	0.95	1250	TSSOP-8, SOIC-8
MC100ELT24	5	TTL	NECL	1	400	0.95	1250	TSSOP-8, SOIC-8
MC100EPT25	3.3	LVNECL/NECL	TTL	1	275	1.1	1100	TSSOP-8, SOIC-8, DFN-8
MC100ELT25	5	NECL	TTL	1	100	2.6	2300	TSSOP-8, SOIC-8
MC100EPT26	3.3	ECL, LVDS	TTL	1	275	1.5	900	TSSOP-8, SOIC-8, DFN-8
MC100ELT28	5	TTL, ECL	ECL, TTL	2	100	1.2	1500	TSSOP-8, SOIC-8
MC100ELT28	5	TTL, ECL	ECL, TTL	2	100	1.2	1500	TSSOP-8, SOIC-8
MC100EP90	3.3	LVNECL/NECL	LVPECL, PECL	3	3000	0.26	180	TSSOP-20
MC100EL90	5	LVNECL/NECL	PECL	3	650	0.5	500	SOIC-20
NB100LVEP91	2.5	HSTL, CML, LVDS, ECL	LVNECL/NECL	3	2500	0.43	250	QFN-24, SOIC-20
MC100EP91	3.3	LVDS, HSTL, ECL, CML, TTL	NECL	3	2	0.55	150	QFN-24, SOIC-20
MC100EL91	5	ECL	NECL	3		0.67	400	SOIC-20

TRANSLATORS

Device	V _{cc} Typ (V)	Input Level	Output Level	Channels	f _{max} Typ (MHz)	t _{pd} Typ (ns)	t _r & t _f Max (ps)	Package
MC100LVEL90	3.3	LVNECL, NECL	ECL	3	650	0.5	500	SOIC-20
MC100LVEL91	3.3	ECL	LVNECL	3	600	0.62	580	SOIC-20
MC100LVEL92	3.3	ECL	LVPECL	3	600	0.61	580	SOIC-20
MC10EP90	3.3	LVNECL/NECL	LVPECL/PECL	3	3000	0.26	180	TSSOP-20
MC100EPT622	3.3	LVTTTL/LVCMOS	PECL	10	1500	0.45	250	QFN-32, LQFP-32
MC10H124	5	TTL	NECL	4			1600	PDIP-16, PLCC-20, SOEIAJ-16
MC10H125	5	NECL	TTL	4			1200	PDIP-16, PLCC-20, SOEIAJ-16
MC10H350	5	PECL	TTL	4		3.5	1600	PDIP-16, PLCC-20, SOEIAJ-16
MC10H351	5	TTL/NMOS	PECL	4		1.3	2000	PDIP-20, PLCC-20, SOEIAJ-20
MC10H352	5	CMOS	PECL	4		1.3	2000	PDIP-20, PLCC-20
MC10H424	5	TTL	ECL	4		1.5	2000	PDIP-16, PLCC-20
MC100H600	5	TTL	ECL	1		2300	1500	PLCC-28
MC10H600	5	TTL	ECL	1			1500	PLCC-28
MC100H601	5	ECL	TTL	1		3.45	3000	PLCC-28
MC10H601	5	ECL	TTL	1		3.45	3000	PLCC-28
MC100H602	5	TTL	ECL	1		2.5	1500	PLCC-28
MC10H602	5	TTL	ECL	1			1500	PLCC-28
MC100H603	5	ECL	TTL	1			3000	PLCC-28
MC10H603	5	ECL	TTL	1			3000	PLCC-28
MC100H604	5	TTL	ECL	6			2000	PLCC-28
MC10H604	5	TTL	ECL	6			2000	PLCC-28
MC100H605	5	ECL	TTL	6		5.2	1500	PLCC-28
MC10H605	5	ECL	TTL	6		5.2	1500	PLCC-28
MC100H606	5	TTL	ECL	6		3	2000	PLCC-28
MC10H606	5	TTL	ECL	6			2000	PLCC-28
MC100H607	5	PECL	TTL	6			2000	PLCC-28
MC10H607	5	ECL	TTL	6			2000	PLCC-28

Clock Generation

Clock Generation

Table of Contents

	Page
Crystal Oscillators	100
Phase/Frequency Detectors	101
PLL Clock Generators	102
Spread Spectrum EMI Reduction Clocks	103
VCOs	105
Zero Delay Buffers	105

ON Semiconductor Selector Guide – Clock Management

CRYSTAL OSCILLATORS

Device	V _{DD} Typ (V)	Input	Output Level	f _{CLKOUT1} Typ (MHz)	f _{CLKOUT2} Typ (MHz)	Δf (± PPM)	t _{Jitter(Φ)} Typ (ps)	t _R & t _F Typ (ps)	t _R & t _F Max (ps)	Duty Cycle Min (%)	Duty Cycle Typ (%)	Duty Cycle Max (%)	Package
NBXDBA009	3.3	Crystal, CMOS	ECL	75	150	50	0.4	250	400	48	50	52	CLCC-6
NBXDBA012	3.3	Crystal, CMOS	ECL	106.25	212.5	50	0.4	250	400	48	50	52	CLCC-6
NBXDBA014	3.3	Crystal, CMOS	ECL	62.5	125	50	0.4	380	620	48	50	52	CLCC-6
NBXDBA015	3.3	Crystal, CMOS	ECL	200	206.9	50	0.4	250	400	48	50	52	CLCC-6
NBXDBA017	3.3	Crystal, CMOS	ECL	156.25	312.5	50	0.4	250	400	48	50	52	CLCC-6
NBXDBA018	3.3	Crystal, CMOS	ECL	155.52	311.04	50	0.4	250	400	48	50	52	CLCC-6
NBXDBA019	3.3	Crystal, CMOS	ECL	125	250	50	0.4	250	400	48	50	52	CLCC-6
NBXDBB017	3.3	Crystal, CMOS	ECL	156.25	312.5	20	0.4	250	400	48	50	52	CLCC-6
NBXDBB018	3.3	Crystal, CMOS	ECL	155.52	311.04	20	0.4	250	400	48	50	52	CLCC-6
NBXDDA016	3.3	Crystal, CMOS	ECL	133.33	137.93	50	0.4	160	300	48	50	52	CLCC-6
NBXDPA012	2.5 - 3.3	CMOS	LVDS	106.25	212.5	50	0.4	115	400	48	50	52	CLCC-6
NBXDPA017	2.5 - 3.3	CMOS	LVDS	156.25	312.5	50	0.4	115	400	48	50	52	CLCC-6
NBXDPA018	2.5 - 3.3	CMOS	LVDS	155.52	311.04	50	0.5	115	400	48	50	52	CLCC-6
NBXDPA019	2.5 - 3.3	CMOS	LVDS	125	250	50	0.5	115	400	48	50	52	CLCC-6
NBXHBA017	3.3	Crystal, CMOS	ECL	156.25	-	50	0.4	250	400	48	50	52	CLCC-6
NBXHBA019	3.3	Crystal, CMOS	ECL	125	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA007	3.3	Crystal, CMOS	ECL	240	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA008	3.3	Crystal, CMOS	ECL	161.1328	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA010	3.3	Crystal, CMOS	ECL	100	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA017	3.3	Crystal, CMOS	ECL	312.5	-	50	0.4	250	400	48	50	52	CLCC-6

CRYSTAL OSCILLATORS

Device	V _{DD} Typ (V)	Input	Output Level	f _{CLKOUT1} Typ (MHz)	f _{CLKOUT2} Typ (MHz)	Δf (± PPM)	t _{Jitter(Φ)} Typ (ps)	t _R & t _F Typ (ps)	t _R & t _F Max (ps)	Duty Cycle Min (%)	Duty Cycle Typ (%)	Duty Cycle Max (%)	Package
NBXSBA019	3.3	Crystal, CMOS	ECL	250	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA020	3.3	Crystal, CMOS	ECL	280	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA021	3.3	Crystal, CMOS	ECL	266.667	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA022	3.3	Crystal, CMOS	ECL	187.5	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA023	3.3	Crystal, CMOS	ECL	400	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA024	2.5 - 3.3	CMOS	ECL	622.08	-	50	0.5	250	400	45	50	55	CLCC-6
NBXSBA025	2.5 - 3.3	CMOS	ECL	425	-	50	0.5	250	400	48	50	52	CLCC-6
NBXSBA030	2.5 - 3.3	CMOS	ECL	175	-	50	0.5	250	400	48	50	52	CLCC-6
NBXSBA031	2.5 - 3.3	CMOS	ECL	340	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA045	2.5 - 3.3	CMOS	ECL	345	-	50	0.4	250	400	48	50	52	CLCC-6
NBXSBA046	2.5 - 3.3	CMOS	ECL	172.5	-	50	0.5	250	400	48	50	52	CLCC-6
NBXSPA008	2.5 - 3.3	CMOS	LVDS	161.1328	-	50	0.5	115	400	48	50	52	CLCC-6
NBXSPA022	2.5 - 3.3	CMOS	LVDS	187.5	-	50	0.4	115	400	48	50	52	CLCC-6

PHASE/FREQUENCY DETECTORS

Device	V _{CC} Typ (V)	Input Level	Output Level	f _{Toggle} Max (MHz)	t _{pd} Typ (ns)	t _{Jitter} Typ (ps)	t _R & t _F Max (ps)	Package
MC100EP140	3.3	ECL, CML	ECL	2000	0.475	0.2	200	SOIC-8
MC100EP40	3.3	ECL, CML	ECL	2000	0.55	0.2	150	TSSOP-20
MC100LVEL40	3.3	ECL, CML	ECL	250	1.35	0.2	475	SOIC-20
MCH12140	5	ECL, CML	ECL	800	0.44	0.2	350	SOIC-8
MCK12140	5	ECL, CML	ECL	800	0.44	0.2	350	SOIC-8
NB3N5573	3.3	ECL, CML	ECL	200	-	1.5	700	TSSOP-16

ON Semiconductor Selector Guide – Clock Management

PLL CLOCK GENERATORS

Device	V _{CC} Typ (V)	Input	Output Level	f _{Max} Min (MHz)	f _{Max} Max (MHz)	t _{Lock} Max (ms)	t _{Jitter} Typ (ps)	t _{su} Min (ns)	t _h Min (ns)	t _r & t _f Min (ps)	t _r & t _f Max (ps)	Package
NB3N3001	3.3	Crystal	ECL	Not Used	106.25 or 212.5 Typ	1	0.3	-	-	275	600	TSSOP-8
NB3N3002	3.3	Crystal, CMOS	HCSL	25	200	1	2	-	-	175	700	TSSOP-16
NB3N3011	3.3	Crystal	ECL	96	120	1	0.29	-	-	275	600	TSSOP-8
NB3N502	3	Crystal, CMOS	CMOS	10	190	1	15	-	-	1000	1000	SOIC-8
NB3N508S	3.3	Crystal, CMOS	LVDS	Not Used	216	2	88 dBc/Hz @ 1 KHz	-	-	380	500	TSSOP-16
NB4N441	3.3	Crystal, CMOS	CMOS	12.5	425	5	3.5	20	-	175	425	QFN-24
NB4N507A	3.3	Crystal, CMOS	ECL	50	200	1	10	-	-	50	70	SOIC-16
NBC12429A	3.3	Crystal, CMOS	ECL, CMOS	25	400	10	20	20	20	175	425	QFN-32, LQFP-32, PLCC-28
NBC12429	3.3	Crystal, CMOS	ECL, CMOS	25	400	10	20	20	20	175	425	LQFP-32, PLCC-28
NBC12430A	3.3	Crystal, CMOS	ECL, CMOS	50	800	10	20	20	20	175	425	QFN-32, LQFP-32, PLCC-28
NBC12430	3.3	Crystal, CMOS	ECL, CMOS	50	800	10	20	20	20	175	425	LQFP-32, PLCC-28
NBC12439A	3.3	Crystal, CMOS	ECL, CMOS	50	800	10	20	20	20	175	425	QFN-32, LQFP-32, PLCC-28
NBC12439	3.3	Crystal, CMOS	ECL, CMOS	50	800	10	20	20	20	175	425	LQFP-32, PLCC-28

SPREAD SPECTRUM EMI REDUCTION CLOCKS

Product	V _{DD} Typ (V)	f _{in} Typ (MHz)	f _{out} Typ (MHz)	Deviation Type	Features	T _A Min (°C)	T _A Max (°C)	Package
ASM3I2579AF-06OR	3.3	13	30	±1	SSON	-40	85	TSOP-6
ASM3I2669AF-06OR	2.5, 3.3	6-12, 6-13	6-12, 6-13	±1	PDB	-40	85	TSOP-6
ASM3I2779AF-06OR	2.5, 3.3	13-30	13-30	±1	PDB	-40	85	TSOP-6
ASM3P1819NF-08SR	3.3	20-40	20-40	-1.25	-	0	70	SOIC-8
ASM3P2107AF-08SR	5	12-22	12-22	Down	-	0	70	SOIC-8
ASM3P2108AF-08SR	5	25-45	25-45	-1.3	-	0	70	SOIC-8
ASM3P2111BG-08SR	3.3	25	48, 66	-1.7 @ 66.66 MHz	-	0	70	SOIC-8
ASM3P2180AF-08SR	3.3	6-30	6-30	Selectable Down	-	0	70	SOIC-8
ASM3P2180AF-08ST	3.3	6-30	6-30	Selectable Down	-	0	70	SOIC-8
ASM3P2274AF-06OR	2.5, 3.3	12-30	48-120	-1.5	PDB	0	70	TSOP-6
ASM3P2474AF-06OR	3.3	13-30	13-30, 26-60	-1.5	-	0	70	TSOP-6
ASM3P2598AF-06OR	2.5, 3.3	60-120	60-120	±1.5	SSON	0	70	TSOP-6
ASM3P2669AF-06OR	2.5, 3.3	6-12, 6-13	6-12, 6-13	±1	PDB	0	70	TSOP-6
ASM3P2760AF-06OR	2.5, 3.3	6-12, 6-13	6-12, 6-13	±0.65	PDB	0	70	TSOP-6
ASM3P2775AF-06OR	3.3	13-30	13-30	±1.8	PDB	0	70	TSOP-6
ASM3P2779AF-06OR	2.5, 3.3	13-30	13-30	±1	PDB	0	70	TSOP-6
ASM3P2780AF-06OR	2.5, 3.3	30-50	30-50	±0.75	PDB	0	70	TSOP-6
ASM3P2863AG-08SR	2.5	25	48, 50	±1	-	0	70	SOIC-8
ASM3P2863AF-06OR	2.5, 3.3	6-12, 6-13	6-12, 6-13	±0.5	REFOUT	0	70	TSOP-6
ASM3P2872AF-06OR	2.5, 3.3	13-30	13-30	-1.25	REFOUT	0	70	TSOP-6
P1708CF-08SR	3.3	50-110	50-110	Selectable Center Spread	SSON/OFF	0	70	SOIC-8
P1708CF-08TR	3.3	50-110	50-110	Selectable Center Spread	SSON/OFF	0	70	TSSOP-8
P1727AF-08SR	3.3	20-40	20-40	Selectable ±0.625% to -3.50%	-	0	70	SOIC-8
P3P18S19BF-08SR	3.3	20-40	20-40	-1.25% to -1.75%	Spread Deviation Selection	0	70	SOIC-8
P3P18S19BF-08ST	3.3	20-40	20-40	-1.25% to -1.75%	Spread Deviation Selection	0	70	SOIC-8
P3P73U00AG-08-ST	2.5, 3.3	10-60, 10-70	10-60, 10-70	Analog	MR Selection	0	70	SOIC-8
P3P73U00AG-08-TT	2.5, 3.3	10-60, 10-70	10-60, 10-70	Analog	MR Selection	0	70	TSSOP-8
P3P73U00AG-08CR	2.5, 3.3	10-60, 10-70	10-60, 10-70	Analog	MR Selection	0	70	WDFN-8
P3P73U00AG-08SR	2.5, 3.3	10-60, 10-70	10-60, 10-70	Analog	MR Selection	0	70	SOIC-8

SPREAD SPECTRUM EMI REDUCTION CLOCKS

Product	V _{DD} Typ (V)	f _{in} Typ (MHz)	f _{out} Typ (MHz)	Deviation Type	Features	T _A Min (°C)	T _A Max (°C)	Package
P3P73Z01BWG-08CR	2.5, 3.3	12-150, 15-175	12-150, 15-175	Analog	Analog Delay Control	0	70	WDFN-8
P3P73Z01BWG-08TR	2.5, 3.3	12-150, 15-175	12-150, 15-175	Analog	Analog Delay Control	0	70	TSSOP-8
P3P73Z01BWG-08TT	2.5, 3.3	12-150, 15-175	12-150, 15-175	Analog	Analog Delay Control	0	70	TSSOP-8
PCS3P2042BG-08TR	3.3	30-110	30-110	±0.23 to ±1.89	SSON/OFF	0	70	TSSOP-8
PCS3P2042BG-08TT	3.3	30-110	30-110	±0.23 to ±1.89	SSON/OFF	0	70	TSSOP-8
PCS3P2537AG-08CR	3.3	18-36	18-36	-0.25	SSON	0	70	WDFN-8
PCS3P25811AG08SR	3.3	4-32	4-32	-0.5 to -3.0, ±0.3 to ±1.4	-	0	70	SOIC-8
PCS3P7303AG-08CR	2.5, 3.3	10-70, 10-80	10-70, 10-80	Analog	-	0	70	WDFN-8
PCS3P7303AG-08TR	2.5, 3.3	10-70, 10-80	10-70, 10-80	Analog	-	0	70	TSSOP-8
PCS3P7303AG-08TT	2.5, 3.3	10-70, 10-80	10-70, 10-80	Analog	-	0	70	TSSOP-8
PCS3P73U00AG08TR	2.5, 3.3	10-60, 10-70	10-60, 10-70	Analog	MR Selection	0	70	TSSOP-8
PCS3P8504AG-08CR	2.5, 3.3	15-40, 15-50	15-40, 15-50	Analog	MR Selection	0	70	WDFN-8
PCS3PS550AG-08CR	2.5, 3.3	18-36	18-36	±0.4 to ±2.5	PDB	0	70	WDFN-8

VCOs

Device	Input Level	Output Level	Description	f _{Max} Typ (MHz)	V _{CC} Max (V)	Duty Cycle (%)	Package
FS6128-04	CMOS	CMOS	VCXO Clock Generator, 27 MHz Output	27	3.6	50	SOIC-14
FS6128-07	CMOS	CMOS	VCXO Clock Generator, 27 MHz Output	27	3.6	50	SOIC-14
FS6131	CMOS	CMOS	I2C Programmable 1-PLL Clock	230	5.5	50	SOIC-14
FS6370	CMOS	CMOS	EE Programmable 3-PLL Clock	150	5.5	50	SOIC-14
FS6377	CMOS	CMOS	I2C Programmable 3-PLL Clock	150	5.5	50	SOIC-14
FS7140	CMOS	CMOS	I2C Programmable 1-PLL Clock	300	3.6	50	SOIC-14, SSOP-16
FS7145	CMOS	CMOS	I2C Programmable 1-PLL Clock	300	3.6	50	SOIC-14
MC100EL1648	LRC tank	ECL	5 V ECL Voltage Controlled Oscillator	1100	5.5	50	SOIC-8, TSSOP-8, SOEIAJ-14, DFN-8
MC14046B	CMOS	CMOS	Phase Locked Loop	-	18	-	SOIC-16, SOEIAJ-16, PDIP-16
MC74HC4046A	CMOS	CMOS	Phase Locked Loop	-	6	-	SOIC-16, TSSOP-16, SOEIAJ-16, PDIP-16

ZERO DELAY BUFFERS

Device	Input Level	Output Level	Outputs Per	V _{DD} Typ (V)	t _{skew} Max (ps)	F Max (MHz)	t _{jitter} Max (ps)	Package
NB2304A	CMOS	CMOS	4	3.3	200	133.3	100	SOIC-8
NB2305A	CMOS	CMOS	5	3.3	250	133.3	200	SOIC-8, TSSOP-8
NB2308A	CMOS	CMOS	8	3.3	200	133.3	100	SOIC-16, TSSOP-16
NB2309A	CMOS	CMOS	9	3.3	250	133.3	200	SOIC-16, TSSOP-16

Custom

Custom

Table of Contents

	Page
Digital ASICs	110
Standard Cell Product Families	110
Structured ASIC Product Families	110
Custom Foundry Services	110

DIGITAL ASICs
STANDARD CELL PRODUCT FAMILIES

Product	Core Voltage	I/O Voltage	I/O Types	System Performance	Memory	Clock Management	FPGA Conversion Targets	Handling	Flow	Package Options
0.5 μm (SC5)	5 V	5 V, 3.3 V	PCI, TTL, LVTTL	75 MHz	SRAM, DPRAM, ROM	PPL	Legacy FPGAs/PLDs	Domestic fabrication, ITAR	QML	Full package offering
0.35 μm (SC3)	3.3 V / 2.5 V	5 V, 3.3 V, 5 V Tolerant	PCI, GTL, HSTL, SSTL, LVPECL, USB1.1	100 MHz	SRAM, DPRAM, ROM	DLL, PLL	XC4000XL, FLEX®, Spartan® XL, MAX®	Domestic fabrication, ITAR	QML	Full package offering
0.18 μm (ONC18)	1.8 V	3.3 V, 2.5 V, 1.8 V, 3.3 V / 5 V Tolerant	PCI, HSTL, SSTL, LVDS	266 MHz	SRAM, DPRAM, ROM	DLL, PLL	Virtex®-E, APEX™-E, Virtex II, Spartan IIE	Domestic fabrication, ITAR	QML	Full package offering
0.11 μm (SP110)	1.2 V	3.3 V, 2.5 V, 1.8 V, 1.5 V, 3.3 V Tolerant	PCI, PCI-X, GTL, HSTL, SSTL, LVPECL, LVDS	450 MHz	SRAM, DPRAM, ROM	DLL, PLL	Virtex-4, Spartan-3, APEX-II, Stratix®-II, Cyclone®	Domestic fabrication, ITAR	QML	Full package offering

STRUCTURED ASIC PRODUCT FAMILIES

Product	Core Voltage	I/O Voltage	I/O Types	System Performance	Memory	Clock Management	FPGA Conversion Targets	Handling	Flow	Package Options
XPressArray®-II (150 nm)	1.5 V	3.3 V, 2.5 V, 1.8 V, 1.5 V	PCI, PCI-X, GTL, HSTL, SSTL2, LVPECL, LVDS	210 MHz	SRAM, DPRAM, ROM	DLL, PPL	Virtex-4, Spartan-3, APEX-II, Stratix-II, Cyclone	TSMC-ON hybrid domestic process, ITAR	QML	Exclusive flip chip

CUSTOM FOUNDRY SERVICES


Process Name	Min Drawn Poly (μ)	No. Metal Layers	Wafer Size (in)	Maximum Operating Voltage (V)	Metal 1 Pitch	NVM	Linear Cap	N-Channel DMOS	P-Channel DMOS	BI-polars	Trans Char	Other Devices
ONC18G/R	0.18	4-6	8	3.3	0.46	Y	MIM	-	-	-	Salicide	Resistors
ONC25	0.25	2-5	8	5	0.64	Y	MIM	-	-	Y	Salicide	Misc.
ONBCD25	0.25	2-5	8	40	0.64	Y	MIM	Y	-	Y	Salicide	Misc.
C3/D3	0.35	3-5	8	5	1.10	Y	PIP	-	-	-	Salicide	Resistors
I3T25	0.35	3-5	8	18	1.00	Y	MIM	Y	Y	Y	Salicide	Resistors
I3T50	0.35	3-5	6	40	1.00	Y	MIM	Y	Y	Y	Salicide	Misc.
I3T80	0.35	3-5	6	80	1.00	Y	MIM	Y	Y	Y	Salicide	Misc.
C5	0.6	2,3	8	20	1.50	Y	PIP	Y	Y	-	Poly	Misc.
I2T30 (E)	0.7	2,3	6	30	2.80	-	PIP	Y	Y	Y	Poly	Misc.
I2T100	0.7	2,3	6	100	2.80	-	PIP	Y	Y	Y	Poly	Misc

DC-DC Controllers, Converters, and Regulators

DC–DC Controllers, Converters, and Regulators

Table of Contents

	Page
DC–DC Switching Non–Isolated	114
Step–Down Switching Regulators –	
Internal Switch	115
Multi–Topology (Step–Up, Step–Down, Inverting)	
Switching Regulators – Internal Switch	117
Step–Down Switching Controllers –	
External Switch	118
Step–Up Switching Controllers –	
External Switch	118
Charge Pumps	119
DC–DC Switching Isolated	120
Flyback Fixed Frequency Converters	120
DC–DC Switching, Computing	121
Linear Voltage Regulators	123
Standard Linear Voltage Regulators	123
Multi–Market Low Dropout Linear	
Voltage Regulators	124
Single Output Low Dropout Linear Voltage	
Regulators	126
Multiple Output Low Dropout Linear Voltage	
Regulators	128
Automotive Linear Voltage Regulators	129
Single Automotive Linear Voltage Regulators ..	130
Dual Automotive Linear Voltage Regulators ...	132
Battery Charge Controllers	132



*Coming Soon.

STEP-DOWN SWITCHING REGULATORS – INTERNAL SWITCH

Device	V _{IN} (V)		V _{OUT} Options (Adj Range)	I _{OUT} (A)	F _{SW} (kHz)	Mode	Enable	Soft-Start	Comments	Temp Range (°C)	Package
	Min	Max									
NCP3102	4.5	13.2	Down to 0.8 V	10 A	275	Voltage	✓	✓	Highly integrated 10 A output	-40 to +85	QFN-40
NCP3101	4.5	13.2	Down to 0.8 V	6.0 A	275	Voltage	✓	✓	Highly integrated 6 A output	-40 to +85	QFN-40
MC33167	7.0	40	Down to 5.0 V	5.0 A	72	Voltage			Large 5.0 A output capability	-40 to +85	D2PAK / TO-220
MC34167	7.0	40	Down to 5.0 V	5.0 A	72	Voltage			Standby Mode < 36 µA	0 to +70	D2PAK / TO-220
MC33166	7.5	40	Down to 5.0 V	3.0 A	72	Voltage			Internal thermal shutdown	-40 to +85	D2PAK / TO-220
MC34166	7.5	40	Down to 5.0 V	3.0 A	72	Voltage			Cycle-by-Cycle current limit	0 to +70	D2PAK / TO-220
LM2576	4.75	40	3.3, 5, 12, 15, Adj(1.23 to 37 V)	3.0 A	52	Voltage	✓		No external compensation required	-40 to +125	D2PAK / TO-220
NCP3121/ NCP3123	4.5	13.2	Down to 0.8 V	3.0/3.0 A	200-750 200-2200	Voltage	✓	✓	Auto tracking and sequencing; 180° Out-of-phase operation	-40 to +85	QFN-32
NCP3120/ NCP3122	4.5	13.2	Down to 0.8 V	2.0/2.0 A	200 - 750 200-2200	Voltage	✓	✓	Auto tracking and sequencing; 180° Out-of-phase operation	-40 to +85	QFN-32
NCP5252	4.5	13.2	Down to 0.6 V	2.0 A	333 - 1000	-	✓	✓	FPWM mode	-40 to +85	QFN-16
NCP1592	2.7	5.5	0.9 - 3.3 V	1.6	2250	Current	✓	✓	Dual buck auto PFM/PWM. Synchronous rectification.		Thin DFN-10
CS5171	2.7	30	1.276 to 40 V	1.5 A	280	Current	✓	✓	LT1372/1373 Compatible	-40 to +85	SO-8
CS5172	2.7	30	-2.5 to 40 V	1.5 A	280	Current	✓	✓	Flyback & SEPIC	-40 to +85	SO-8
CS5173	2.7	30	1.276 to 40 V	1.5 A	560	Current	✓	✓	Easy External Synchronization	-40 to +85	SO-8
CS5174	2.7	30	-2.5 to 40 V	1.5 A	560	Current	✓	✓	Negative feedback polarity	-40 to +85	SO-8
CS51411	4.5	40	Down to 1.276 V	1.5 A	260	Voltage	✓	✓	Sync capability; Pin- Compatible with LT1375 and LT1376	-40 to +85	SO-8 / DFN-8
CS51412	4.5	40	Down to 1.276 V	1.5 A	260	Voltage	✓	✓	External Bias; Pin- Compatible with LT1375 and LT1376	-40 to +85	SO-8 / DFN-8
CS51413	4.5	40	Down to 1.276 V	1.5 A	520	Voltage	✓	✓	Sync capability; Pin- Compatible with LT1375 and LT1376	-40 to +85	SO-8 / DFN-8
CS51414	4.5	40	Down to 1.276 V	1.5 A	520	Voltage	✓	✓	External Bias; Pin- Compatible with LT1375 and LT1376	-40 to +85	SO-8 / DFN-8
NCP1595A	4.0	5.5	Down to 0.8 V	1.5 A	1200	Current	✓	✓	Internal compensation; Synchronous Rectification	0 to +85	DFN-6
NCP5030	2.7	5.5	2.2-5.5 V	1.2 A	1000	Current	✓	✓	Buck/ Boost Converter - can supply either regulated current or regulated output voltage	-40 to +85	DFN-12
LM2575	4.75	40	3.3, 5, 12, 15, Adj(1.23 to 37 V)	1.0 A	52	Voltage	✓		No external compensation required	-40 to +125	D2PAK / TO-220
NCP1599	2.7	5.5	Adj(0.9-3.3 V)	1.0 A	1700	Current	✓	✓	Auto PWM/ PFM mode. Synchronous Rectification	-40 to +85	Thin SOT-23-5, Thin DFN-6
LM2574	4.75	40	3.3, 5, 12, 15, Adj(1.23 to 37 V)	0.5 A	52	Voltage	✓		No external compensation required	-40 to +125	D2PAK / TO-220
NCP1422	1.0	5.0	1.5-5.0 V	800 mA	1200	Current	✓	✓	PFM mode. Synchronous Rectification, True-cutoff, Low-battery detect	-40 to +85	DFN-10
NCP1421	1.0	5.0	1.5-5.0 V	600 mA	1200	Current	✓	✓	PFM Sync-rect. True-cutoff, Low-battery detect	-40 to +85	Micro8™
NCP1521B	2.7	5.5	0.9 - 3.3 V	600 mA	1500	Current	✓	✓	Auto PWM/ PFM mode. Synchronous Rectification	-40 to +85	Thin SOT-23-5, Thin DFN-6
NCP1522B	2.7	5.5	0.9 - 3.3 V	600 mA	3000	Voltage	✓	✓	Auto PWM/ PFM mode. Synchronous Rectification	-40 to +85	Thin SOT-23-5, Thin DFN-6

ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators

STEP-DOWN SWITCHING REGULATORS – INTERNAL SWITCH (CONTINUED)

Device	V _{IN} (V)		V _{OUT} Options (Adj Range)	I _{OUT} (A)	F _{SW} (kHz)	Mode	Enable	Soft-Start	Comments	Temp Range (°C)	Package
	Min	Max									
NCP1523B	2.7	5.5	0.9 – 3.3 V	600 mA	3000	Voltage	✓	✓	PWM mode. Synchronous Rectification	-40 to +85	Micro-Bump-8
NCP1423	0.8	V _{OUT}	1.8 – 5.5 V	400 mA	600	Current	✓	✓	PFM mode. Synchronous Rectification, True-cutoff, Low-battery detect	-40 to +85	Micro-10
NCP1410	1.0	5.5	V _{IN} to 5.5 V	250 mA	600	Current	✓		PFM mode. Synchronous Rectification, Low-battery detect	-40 to +85	Micro8™
NCP1402	0.8	5.5	1.8 – 5.0 V	200 mA	180	Voltage	✓	✓	PFM mode	-40 to +85	Thin SOT-23-5
NCP1400	0.8	5.5	1.9 – 5.0 V	100 mA	180	Voltage	✓	✓	PWM mode	-40 to +85	Thin SOT-23-5
NCP1403	1.2	5.5	up to 15 V	50 mA	300	Current	✓	✓	PFM mode	-40 to +85	Thin SOT-23-5
NCP1406	1.4	5.5	up to 25 V	50 mA	1000	Current	✓	✓	PFM mode	-40 to +85	Thin SOT-23-5
LM2594	4.75	40	3.3, 5, 12, 15 Adj (1.23 to 37 V)	0.5 A	52	Voltage	✓		No external compensation required	-40 to +125	D2PAK, TO-220
LM2595	4.75	40	3.3, 5, 12, 15 Adj (1.23 to 37 V)	1.0 A	52	Voltage	✓		No external compensation required	-40 to +125	D2PAK, TO-220
NCP3127	4.5	13.2	Down to 0.8 V	2.0 A	350	Voltage			High Efficiency	-40 to +85	SO-8
LM2596	4.75	40	3.3, 5, 12, 15 Adj (1.23 to 37 V)	3.0 A	52	Voltage	✓		No external compensation required	-40 to +125	D2PAK, TO-220
NCP3126	4.5	13.2	Down to 0.8 V	3.0 A	350	Voltage	✓	✓	High Efficiency	-40 to +85	SO-8
NCP3125	4.5	13.2	Down to 0.8 V	4.0 A	350	Voltage	✓	✓	High Efficiency	-40 to +85	SO-8

MULTI-TOPOLOGY (STEP-UP, STEP-DOWN, INVERTING) SWITCHING REGULATORS – INTERNAL SWITCH

Device	V _{IN} (V)		V _{OUT} Options (Adj Range)	I _{OUT} (A)	F _{sw} (kHz)	Enable	Mode	Step- Up	Step- Down	Step-Up/ Step- Down	Inv	Comments	Temp Range (°C)	Package
	Min	Max												
MC34063	3.0	40	Down to 1.25 V	1.5	up to 100	✓	Hysteresis	✓	✓	✓	✓	Simple and flexible regulator	0 to +70	SO-8 / PDIP-8
MC33063	3.0	40	Down to 1.25 V	1.5	up to 100	✓	Hysteresis	✓	✓	✓	✓	Minimal number of external components	-40 to +85	SO-8 / PDIP-8
NCP3063/ NCP3063B	3.0	40	Down to 1.25 V	1.5	up to 250	✓	Hysteresis	✓	✓	✓	✓	Higher F _{sw} for optimized size and efficiency. NCP3064 includes ENABLE.	-40 to +85	PDIP/SO-8/ DFN-8/PDIP-8
NCP3064	3.0	40	Down to 1.25 V	1.5	up to 250	✓	Hysteresis	✓	✓	✓	✓	Higher F _{sw} for optimized size and efficiency. NCP3064 includes ENABLE.	-40 to +85	PDIP/SO-8/ DFN-8/PDIP-8
NCP3065	3.0	40	Down to 0.2 V	1.5	up to 250	✓	Hysteresis	✓	✓	✓	✓	Driver for HB-LED/constant current source. NCP3066 includes ENABLE.	-40 to +85	DFN-8 / SO-8 / PDIP-8
NCP3066	3.0	40	Down to 0.2 V	1.5	up to 250	✓	Hysteresis	✓	✓	✓	✓	Driver for HB-LED/constant current source. NCP3066 includes ENABLE.	-40 to +85	DFN-8 / SO-8 / PDIP-8
CS5171	2.7	30	1.276 to 40 V	1.5	280		Current	✓			✓	LT1372/1373 Compatible	-40 to +85	SO-8
CS5172	2.7	30	-2.5 to 40 V	1.5	280		Current	✓			✓	Flyback and SEPIC	-40 to +85	SO-8
CS5173	2.7	30	1.276 to 40 V	1.5	560		Current	✓			✓	Easy External Synchronization	-40 to +85	SO-8
CS5174	2.7	30	-2.5 to 40 V	1.5	560		Current	✓			✓	Negative feedback polarity	-40 to +85	SO-8
MC34166	7.5	40	Down to 5.0 V	3.0	72		Voltage		✓		✓	Cycle-by-Cycle current limit	0 to +70	D2PAK / TO-220
MC33166	7.5	40	Down to 5.0 V	3.0	72		Voltage		✓		✓	Internal thermal shutdown	-40 to +85	D2PAK / TO-220
MC34163	2.5	40	Down to 1.25 V	3.4	up to 100	✓	Hysteresis	✓	✓	✓	✓	Simple & Flexible regulator	0 to +70	SO-16W / PDIP
MC33163	2.5	40	Down to 1.25 V	3.4	up to 100	✓	Hysteresis	✓	✓	✓	✓	Minimal number of external components	-40 to +85	SO-16W / PDIP
NCP3163	2.5	40	Down to 1.25 V	3.4	up to 300	✓	Hysteresis	✓	✓	✓	✓	Higher F _{sw} for optimized size and efficiency	-40 to +85	SO-16WEP
MC34167	7.0	40	Down to 5.0 V	5.0	72		Voltage		✓		✓	Large 5.0A output capability	0 to +70	D2PAK/TO-220
MC33167	7.0	40	Down to 5.0 V	5.0	72		Voltage		✓		✓	Standby Mode < 36 μA	-40 to +85	D2PAK/TO-220

ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators
STEP-DOWN SWITCHING CONTROLLERS – EXTERNAL SWITCH

Device	V _{IN} (V)		V _{OUT} Options (Adj Range)	V _{OUT} Accuracy	F _{SW} (kHz)	Mode	Enable	Soft-Start	Synchronous	Comments	Temp Range (°C)	Package
	Min	Max										
CS51031	4.5	16	Down to 1.25 V	2%	200 – 700	Hysteresis		✓		No compensation required ; PFET	-40 to +85	SO-8
CS51033	3.3	5.0	Down to 1.25 V	2%	200 – 700	Hysteresis		✓		No compensation required ; PFET	-40 to +85	SO-8
SG3525	8.0	35	Down to 5.1 V	1%	100 – 400	Voltage	✓	✓		Flexible configurations	0 to +70	SO-16W
NCP1034	8.0	100	Down to 1.25 V	1.5%	25 – 500	Voltage	✓	✓	✓	1 A Gate Drive, Sync	-40 to +125	SOIC-16
NCP1587	4.5	13.2	Down to 0.8 V	1.5%	250 – 300	Voltage	✓	✓	✓	0.7 A gate driver; Short Circuit Protection	-40 to +85	SO-8
NCP1571	2.0	12	Down to 0.980 V	1.0%	200	Voltage	✓	✓	✓	12 V bias supply	0 to +125	SO-8
NCP1575	2.0	12	Down to 0.980 V	1.0%	200 – 500	Voltage	✓	✓	✓	12 V bias supply	0 to +125	SO-8
NCP3011	4.7	28	Down to 0.8 V	1.0%	400	Voltage	✓	✓	✓	External +1.25 V Ref PG, Sync	-40 to +85	TSSOP-14
NCP3020	4.7	28	Down to 0.6 V	1.0%	300/600	Voltage	-	✓	✓	Integrated Diode	-40 to +85	SO-8

DUAL STEP-DOWN SWITCHING CONTROLLERS – EXTERNAL SWITCH

Device	V _{IN} (V)		V _{OUT} Options (Adj Range)	V _{OUT} Accuracy	F _{SW} (kHz)	Mode	Enable	Soft-Start	Synchronous	Comments	Temp Range (°C)	Package
	Min	Max										
NCP5422	10.8	13.2	Down to 1.0 V	2.0%	150 – 600	Voltage	✓	✓	✓	Hiccup mode overcurrent protection	0 to +70	SO-16
NCP5425	4.6	13.2	Down to 0.8 V	1.0%	150 – 750	Voltage	✓	✓	✓	1.5 A peak drive capability	0 to +125	TSSOP-20
TL494	7.0	40	0.3 V Ext Adj	5.0%	Up to 200	Voltage				Buck, boost, forward, flyback	-40 to +125	SOIC-16, PDIP-16
TL594	7.0	40	0.3 V Ext Adj	1.5%	Up to 300	Voltage				Buck, boost, forward, flyback	-40 to +85	SOIC-16, PDIP-16, TSSOP-16


STEP-UP SWITCHING CONTROLLERS – EXTERNAL SWITCH

Device	V _{IN} (V)		V _{OUT} Options (Adj Range)	V _{OUT} Accuracy	F _{SW} (kHz)	Mode	Enable	Soft-Start	Synchronous	Comments	Temp Range (°C)	Package
	Min	Max										
NCP1450	0.9	5.5	1.8–5.0 V (Factory Prefixed)	2.5%	180	Voltage	✓	✓		PFM mode	-40 to +85	Thin SOT-23-5

ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators

CHARGE PUMPS

Device	V _{in} Typ (V)	V _{out} Typ (V)	I _{out} Typ (mA)	I _{cc} Max (μA)	f _{osc} Typ (kHz)	Shutdown Pin	Package
CAT3200TDL-GT3	2.7 to 4.5	5	100	-	2000	Yes	TSOT-23
CAT3200ZJ-GT3	2.7 to 4.5	2.7 to 6 (adj)	100	-	2000	Yes	MSOP-8
CAT660ELA	3.0 to 5.5	-	100	-	80	No	PDIP-8
CAT660EVA	3.0 to 5.5	-	100	-	80	No	SOIC-8
CAT660EVA-T3	3.0 to 5.5	-	100	-	80	No	SOIC-8
CAT661ELA	3.0 to 5.5	-	100	-	135	No	PDIP-8
CAT661EVA	3.0 to 5.5	-	100	-	135	No	SOIC-8
CAT661EVA-T3	3.0 to 5.5	-	100	-	135	No	SOIC-8
MAX1720EUTG	1.15 to 5.5	-V _{in} or 2 V _{in}	90	90	12	Yes	TSOP-6
NOPT729SN35T1G	1.15 to 5.5	-V _{in} or 2 V _{in}	50	20	35	Yes	TSOP-6




FLYBACK FIXED FREQUENCY CONVERTERS

Device	V _{IN} (V)		V _{OUT} Options (Adj Range)	V _{OUT} Accuracy	F _{sw} (kHz)	Mode	Enable	Soft-Start	Synchronous	Comments	Temp Range (°C)	Package
	Min	Max										
NCP1030	10	200	2.5 up to V _{IN}	2%	up to 1000	Voltage Mode	✓	✓		PoE applications: Integrated Switch	-40 to +125	Micro8™
NCP1031	10	200	2.5 up to V _{IN}	2%	up to 1000	Voltage Mode	✓	✓		PoE applications: Integrated Switch	-40 to +125	SO-8, DFN-8

Please see Flyback/Forward Fixed Frequency Controllers Table Page 9.

ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators




ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators


DC-DC SWITCHING, COMPUTING

Device	Description	Phases	Mode	V _{CC} Min (V)	V _{CC} Max (V)	f _{sw} Typ (kHz)	Package
ADP3290	VR11.1 4-Phase Solution	2/3/4	Current/Voltage Mode	6	14.5	100 – 1000	LFCSP-40
ADP3293	VR11.1 8-Bit, Programmable 2- to 3-Phase Synchronous Buck Controller	2/3	Current/Voltage Mode	6	14.5	100 – 1000	LFCSP-40
ADP4000	6-Phase VR11.1 Controller with PMBus	4/5/6	Current/Voltage Mode	4.7	5.75	250 – 9000	LFCSP-48
ADP4100	6-Phase VR11.1 Controller	4/5/6	Current/Voltage Mode	4.7	5.75	250 – 9000	LFCSP-48
NCP1587	Buck Controller	1	Voltage Mode	4.5	13.2	250 – 300	SOIC-8
NCP1587A	Buck Controller	1	Voltage Mode	4.5	13.2	180 – 220	SOIC-8
NCP5208	DDR-III Termination Regulator	1	Voltage Mode	1.7	5.5	–	SOIC-8
NCP5210	3-in-1 DDR Memory Controller	1	Voltage Mode	4.5	13.2	250	DFN-20
NCP5386	1/2 Phase Controller	1/2	Current/Voltage Mode	4.75	7	100 – 1000	QFN-32
NCP5392	VR11.1 4 Phase Controller	2/3/4	Current/Voltage Mode	4.75	5.25	100 – 10000	QFN-40


ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators



ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators



ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators



ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators

SINGLE OUTPUT LOW DROPOUT LINEAR VOLTAGE REGULATORS

Device	I _{out} (mA)	Dropout* (Typ, mV)	I _q ** (Typ, μ A)	PSRR*** (dB)	Absolute Max Input Voltage (V)	Package(s)-Pins	V _{out} V	Features
NCP698	150	370	2.5	-	6	SC82AB-4	1.3, 1.5, 1.8, 2.5, 2.8, 3.0, 3.3, 3.5, 5	Enable, Ultra Low I _q
NCP699	150	320	40	55	6	SOT-23-5	1.3, 1.4, 1.5, 1.8, 2.5, 2.8, 3, 3.1, 3.3, 5 V	Enable
NCP5426	150	150	120	70 (@ 30 mA)	12	SOT-23-5	1.3 V	Enable, Vibrator driver
NCP584	200	100	3.5	75	6.5	SOT-23-5	0.9, 1.2, 1.5, 1.8, 2.5, 2.6, 2.8, 3, 3.1, 3.3 V	Enable, Tri-mode
MC33275	300	260	125	75	13	SO-8, DPAK-3, SOT-223-3, 4x4 DFN-8	2.5, 3, 3.3, 5 V	Tight line & load Reg.
MC33375	300	260	125	75	13	SO-8, SOT-223-3	1.8, 2.5, 3, 3.3, 5 V	Enable
NCP585	300	230	3.5	75 (@ 50 mA)	6.5	SOT-23-5, HSON-6	0.9, 1.0, 1.2, 1.25, 1.5, 1.8, 2.5, 2.8, 3, 3.3 V	Enable, Tri-mode
NCP2860	300	150	355	70	6	Micro8	Adj, 2.77 V	Low noise, Enable, Flag
NCP603	300	157	145	62	6.5	TSOP-5	Adj, 1.3, 1.5, 1.8, 2.8, 3, 3.3, 3.5, 5 V	Enable
NCP5500	500	230	300	75 (@ 100 mA)	18	DPAK-5, SO-8	Adj, 1.5, 3.3, 5 V	Enable, low noise
NCP5501	500	230	300	75 (@ 100 mA)	18	DPAK-3	1.5, 3.3, 5 V	Low noise
NCP3334	500	340 (max)	190 (max)	75	16	SO-8	Adj	Enable, High accuracy
NCP3335A	500	340 (max)	190 (max)	75	16	Micro8, 3x3 DFN-10	Adj, 1.5, 1.8, 2.5, 2.8, 2.85, 3.0, 3.3, 5 V	Enable, Ultra High accuracy
NCP605	500	170	145 (@ 500mA)	62	6.5	3x3.3 DFN-6	Adj, 1.5, 1.8, 2.5, 2.8, 3.0, 3.3, 5 V	Enhanced ESD protection
NCP606	500	170	145 (@ 500mA)	62	6.5	3x3.3 DFN-6	Adj, 1.5, 1.8, 2.5, 2.8, 3.0, 3.3, 5 V	Enable, Enhanced ESD protection
MC33269	800	1.1 V	5.5 mA	55	20	SO-8, DPAK-3, SOT-223-3, TO-220-3	Adj, 3.3, 5, 12 V	Current limit protection
MC34268	800	950 (@ 490 mA)	3.0 mA	55 (min)	15	SO-8, DPAK-3, SOT-223-3	2.85 V	SCSI-2 Active Terminator
NCP1117	1.0 A	1.07 V (@ 800 mA)	3.6 mA	64 (@ 500 mA)	20	DPAK-3, SOT-223-3	Adj, 1.5, 1.8, 1.9, 2, 2.5, 2.85, 3.3, 5, 12 V	Current limit protection
NCP5661	1.0 A	1.0 V	1.3 mA (@ 1 A)	70	18	DPAK-5, 3x3.3 DFN-6	Adj, 1.2, 1.5, 1.8, 2.5, 2.8, 3.0, 3.3 V	Enable, fast transient, flag
NCP565	1.5 A	900	1.5 mA (@ 1.5 A)	85	18	D2PAK-3/5, SOT-223-3, 3x3.3 DFN-6	Adj, 1.2, 1.5, 2.8, 3.0, 3.3 V	Fast transient, Ultra High PSRR

Bold Denotes NEW Products, Packages, and/or Voltage Options

Contact an ON Semiconductor Sales Representative for other voltage options or for automotive grade regulators.

2. These electrical characteristics are determined by an external MOSFET used in conjunction with the LDO controller.

*Voltage dropout was measured at full load for $V_{out} = 3.3$ V where applicable unless noted.

** I_q was measured at 0 or 0.1 mA load unless noted

**** PSRR was measured at $f = 120$ Hz for $V_{out} = 3.3$ @ full load unless otherwise noted.

SINGLE OUTPUT LOW DROPOUT LINEAR VOLTAGE REGULATORS (CONTINUED)

Device	I _{out} (mA)	Dropout* (Typ. mV)	I _q ** (Typ. μA)	PSRR**** (dB)	Absolute Max Input Voltage (V)	Package(s)–Pins	V _{out}	Features
NCP566	1.5 A	900	1.5 mA (@ 1.5 A)	85	9	SOT–223–3	1.2, 1.8, 2.5 V	Fast transient, Ultra High PSRR
NCP1086	1.5 A	1.05 V	5 mA (@ 10 mA)	80	7	D2PAK–3, TO–220–3, SOT–223–3	Adj, 3.3 V	Fast transient, Ultra High Accuracy
NCP5662	2.0 A	1.0 V	1.3 mA (@ 2 A)	70	18	D2PAK–5, 4x4 DFN–8	Adj, 1.2, 1.5, 1.8, 2.5, 2.8, 3.0, 3.3 V	Enable, fast transient, flag
CS5253/CS5253B	3.0 A	400	–	80	13	D2PAK–5	Adj, 2.5 V	Control, Sense, Ultra High PSRR
NCP630	3.0 A	1.0 V	0.4 mA (@ 300 mA)	88	12	D2PAK–5	Adj, 3.47 V	Enable, Fast transient, Ultra High PSRR
NCP631	3.0 A	1.0 V	0.4 mA (@ 300 mA)	76	9	D2PAK–5	3.47 V	Enable, Soft–Start
NCP5663	3.0 A	1.0 V	1.3 mA (@ 3 A)	70	18	D2PAK–5	Adj, 1.5, 1.8 V	Enable, fast transient, flag
NCP5666	3.0 A	1.0 V	1.8 mA (@ 3 A)	70	18	D2PAK–5	2.5, 5 V	Enable, Fast transient
NCP5667	3.0 A	1.0 V	2.4 mA (@ 3 A)	70	18	D2PAK–3	5 V	Enhanced ESD protection
NCP102 (Controller)	Note 2	Note 2	1.4 mA (@ V _{cc} = 5 V)	50 (min)	15	TSOP–6	Adj down to 0.8 V	Enable, MLCC and POSCAP Compatible
NCP3520 (Controller)	Note 2	Note 2	1.25 mA	72	7	Micro8	1.2 V	Controller, Enable, NRCS
NCP3521 (Controller)	Note 2	Note 2	1.25 mA	72	7	Micro8	1.5 V	Controller, Enable, NRCS

Bold Denotes NEW Products, Packages, and/or Voltage Options

Contact an ON Semiconductor Sales Representative for other voltage options or for automotive grade regulators.

2. These electrical characteristics are determined by an external MOSFET used in conjunction with the LDO controller.

*Voltage dropout was measured at full load for V_{out} = 3.3 V where applicable unless noted.

** I_q was measured at 0 or 0.1 mA load unless noted

**** PSRR was measured at f = 120 Hz for V_{out} = 3.3 @ full load unless otherwise noted.

ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators

MULTIPLE OUTPUT LOW DROPOUT LINEAR VOLTAGE REGULATORS


Device	I _{out} (mA)	Dropout* (Typ. mV)	I _q ** (Typ)	Max Input Voltage (V)	Package	V _{out}	Features
MC33567 (Dual Controller)	Note 3	Note 3	6.3 mA	12.5	SO-8	1.8/1.5, 2.5/2.5, 2.3/1.2 V	Controller, Enable, Undervoltage detection
NCP4672 (Dual)	30, 80	150, --- (@ 20mA)	1.0 mA	18	SO-8	3.5/1.8 V	Programmable delay, Reset
MC33762 (Dual)	80, 80	160, 160	180	12	Micro8	2.5/2.5, 2.8/2.8, 3/3 V	Enable, Fast off to on, low noise
NCP4523 (Triple)	150, 80, 80	220, 160, 160	210	7	SSOP-8	2.8/2.8/2.8, 3/3/3, 2.35/2.8/2.8 V	Tight line & load Reg., High PSSR
MC33765 (5 Outputs)	30, 40, 50, 150, 60	110, 110, 110, 170, 110	470	5.3	TSSOP-16	5 x 2.8 V	Enable, Byp Pin, Ultra Low noise
NCP5504 (Dual)	250, 250	250, 250	370	18	DPAK-5	3.3 / Adj V	Low noise, High PSSR
NCP590 (Dual)	300, 300	165, 165	115	5.5	2x2 DFN-8	Combinations ranging from 0.8 to 5V	Enable, Ultra High Accuracy, Ultra Low Dropout

3. These electrical characteristics are determined by an external MOSFET used in conjunction with the LDO controller.

*Voltage dropout was measured at full load for V_{out} = 3.3 V where applicable unless noted.

** I_q was measured at 0 or 0.1 mA load unless noted

ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators



ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators

SINGLE AUTOMOTIVE LINEAR VOLTAGE REGULATORS

Device	Output Voltage (V)	Tolerance	Output Current	Dropout (Max)	Sleepmode Current (Max)	Quiescent Current (Max) @ Low Load (Load)	Enable	Reset (♦♦ = Adjustable)	Delay	Early Warning Flag/Monitor	Watchdog	Wakeup	Current Limit	Overvoltage	Overtemperature	Peak Transient	Packages
NCV8184	Tracking	±3 mV	70 mA	0.6 V	20 µA	70 µA (100 µA)	♦						♦		♦	42 V	DPAK-5, SOIC-8, SOIC-8 ePad
NCV553	5	±3%	80 mA	0.8 V	-	6 µA (1 mA)							♦		♦	12 V	SC-82
CS8101	5	±2%	100 mA	0.6 V	50 µA	140 µA (100 µA)	♦	♦					♦	♦	♦	60 V	SOIC-8, SOIC-20 Fused
CS8151	5	±2%	100 mA	0.6 V	-	750 µA (200 µA)		♦	♦		♦		♦	♦	♦	74 V	SOIC-14, SOIC-16, D2PAK-7
NCV317L	Adj	±4%	100 mA	1.9 V (Typ)	-	-							♦		♦	40 V	SOIC-8, TO-92
NCV2931	Adj, 5	±5%	100 mA	0.6 V	1 mA	1 mA (10 mA)	♦						♦	♦	♦	60 V	SOIC-8, D2PAK-3, DPAK-3
NCV2931A	Adj, 5	±3.8%	100 mA	0.6 V	1 mA	1 mA (10 mA)	♦						♦	♦	♦	60 V	SOIC-8, SOT-223, DPAK-3
NCV2951	Adj, 5	±2.4%	100 mA	0.45 V	-	120 µA (100 µA)	♦	♦					♦		♦	32 V	SOIC-8
NCV2951A	Adj, 3.3, 5	±1.5%	100 mA	0.45 V	-	120 µA (100 µA)	♦	♦					♦		♦	32 V	SOIC-8
NCV4949	5	±2%	100 mA	0.5 V	-	260 µA (300 µA)		♦	♦				♦		♦	40 V	SOIC-20, SOIC-8, SOIC-8 ePad
NCV612	1.5, 1.8, 2.5, 2.7, 2.8, 3.0, 3.1, 3.3, 5.0	±3%	100 mA	0.3 V	1 µA	90 µA (1 mA)	♦						♦		♦	6 V	SC-70
NCV662	1.5, 1.8, 2.5, 2.7, 2.8, 3.0, 3.3, 5.0	±4%	100 mA	0.3 V	1 µA	6 µA (1 mA)	♦						♦		♦	6 V	SC-82
NCV663	1.5, 1.8, 2.5, 2.7, 2.8, 3.0, 3.3, 5.0	±4%	100 mA	0.3 V	-	6 µA (1 mA)							♦		♦	6 V	SC-82
NCV78LxxA	5, 8, 12, 15, 24	±4%	100 mA	1.7 V (Typ)	-	-							♦		♦	30 V	SOIC-8, TO-92
NCV551	1.4, 1.5, 1.8, 2.5, 2.7, 2.8, 3.0, 3.1, 3.2, 3.3, 5	±3%	150 mA	0.22 V	1 µA	8 µA (1 mA)	♦						♦		♦	12 V	TSOP-5
NCV4264	3.3, 5	±2%	150 mA	0.5 V	-	400 µA (1 mA)							♦		♦	45 V	SOT-223
NCV4264-2	3.3, 5	±2%	150 mA	0.5 V	-	70 µA (100 µA)							♦		♦	45 V	SOT-223
NCV4269	5	±2%	150 mA	0.5 V	-	250 µA (1 mA)		♦♦	♦	♦			♦		♦	60 V	SOIC-8, SOIC-8 ePad, SOIC-20 Fused, SOIC-14 Fused
NCV4279	5	±2%	150 mA	0.5 V	-	250 µA (1 mA)		♦♦	♦	♦			♦		♦	60 V	SOIC-8, SOIC-14 Fused
NCV4299	3.3, 5	±2%	150 mA	0.5 V	1 µA	105 µA (1 mA)	♦	♦♦	♦	♦			♦		♦	60 V	SOIC-8, SOIC-14 Fused
NCV8501	Adj, 2.5, 3.3, 5, 8, 10	±2%	150 mA	0.6 V	30 µA	75 µA (100 µA)	♦	♦	♦	♦			♦		♦	60 V	SOIC-8, SOIC-16 ePad
NCV8502	Adj, 2.5, 3.3, 5, 8, 10	±2%	150 mA	0.6 V	-	75 µA (100 µA)		♦♦	♦	♦			♦		♦	60 V	SOIC-8, SOIC-16 ePad
NCV8512	5	±2%	150 mA	0.6 V	-	200 µA (100 µA)		♦♦	♦	♦			♦		♦	60 V	SOIC-16 ePad

NOTE: All devices in this table are AEC-Qualified and PPAP-Capable. Contact ON Semiconductor for details. * See datasheet for details.

ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators

SINGLE AUTOMOTIVE LINEAR VOLTAGE REGULATORS (CONTINUED)

Device	Output Voltage (V)	Tolerance	Output Current	Dropout (Max)	Sleepmode Current (Max)	Quiescent Current (Max) @ Low Load (Load)	Enable	Reset (♦♦ = Adjustable)	Delay	Early Warning Flag/Monitor	Watchdog	Wakeup	Current Limit	Overvoltage	Overtemperature	Peak Transient	Packages
NCV8560	Adj, 1.3, 1.5, 1.8, 2.5, 2.8, 3.0, 3.3, 3.5, 5.0	±2%	150 mA	0.125 V	1 µA	180 µA (150 mA)	♦						♦		♦	6 V	DFN-6 8x3, TSOP-5
NCV8660	3.3, 5	±2%	150 mA	0.6 V	-	40 µA (150 mA)		♦					♦		♦	40 V	SOIC-8 Fused, DPAK-5
NCV8664	3.3, 5	±2%	150 mA	0.6 V	-	30 µA (100 µA)							♦		♦	45 V	SOIC-8 Fused, DPAK-3, SOT-223
NCV8665	5	±2%	150 mA	0.6 V	-	40 µA (100 µA)		♦					♦		♦	45 V	SOIC-8 Fused, D2PAK-5
CS8182	Tracking	±5 mV	200 mA	0.6 V	55 µA	150 µA (100 µA)	♦						♦		♦	45 V	DPAK-5, D2PAK-5, SOIC-8 Fused
NCV8508	5	±3%	250 mA	0.9 V	-	150 µA (150 mA)		♦				♦	♦		♦	60 V	D2PAK-7, SOIC-16 Fused, SOIC-8 ePad
NCV8518A	5	±2%	250 mA	0.75 V	1 µA	150 µA (150 mA)	♦	♦				♦	♦		♦	45 V	SOIC-8 ePad, SOIC-16 ePad
NCV33275	3.3, 5	±2%	300 mA	0.5 V	-	200 µA (0 µA)							♦		♦	13 V	SOT-223
NCV33375	1.8	±2%	300 mA	0.5 V	4 µA	200 µA (0 µA)	♦						♦		♦	13 V	SOT-223
NCV8674	5, 12	±2%	350 mA	0.6 V	-	38 µA (100 µA)							♦		♦	45 V	D2PAK-3
NCV8675	3.3, 5	±2%	350 mA	0.6 V	-	50 µA (100 µA)							♦		♦	45 V	D2PAK-5
NCV8503	Adj, 2.5, 3.3, 5	±2%	400 mA	0.6 V	1 µA	350 µA (100 µA)	♦	♦♦					♦		♦	60 V	SOIC-16 ePad
NCV8504	Adj, 2.5, 3.3, 5	±2%	400 mA	0.6 V	-	150 µA (100 µA)		♦♦					♦		♦	60 V	SOIC-16 ePad
NCV8505	Adj, 2.5, 3.3, 5	±2%	400 mA	0.6 V	1 µA	350 µA (100 µA)	♦	♦					♦		♦	60 V	D2PAK-7
NCV8506	Adj, 2.5, 3.3, 5	±2%	400 mA	0.6 V	-	150 µA (100 µA)		♦					♦		♦	60 V	D2PAK-7
NCV4274	2.5, 3.3, 5	±4%	400 mA	0.5 V	-	250 µA (1 mA)							♦		♦	60 V	DPAK-3, D2PAK-3, SOT-223
NCV4274A	2.5, 3.3, 5	±2%	400 mA	0.5 V	-	250 µA (1 mA)							♦		♦	60 V	DPAK-3, D2PAK-3, SOT-223
NCV4276	Adj, 1.8, 2.5, 3.3, 5	±4%	400 mA	0.5 V	10 µA	220 µA (1 mA)	♦						♦		♦	45 V	DPAK-5, D2PAK-5
NCV4276A	Adj, 3.3, 5	±2%	400 mA	0.5 V	10 µA	220 µA (1 mA)	♦						♦		♦	45 V	DPAK-5, D2PAK-5
NCV4275A	3.3, 5	±2%	450 mA	0.5 V	-	200 µA (1 mA)		♦					♦		♦	45 V	DPAK-5, D2PAK-5
NCV317M	Adj	±4%	500 mA	2.2 V (Typ)	-	-							♦		♦	40 V	DPAK-3
NCV5500	Adj, 1.5, 3.3, 5	±4.9%	500 mA	0.7 V	50 µA	500 µA (100 µA)	♦						♦		♦	18 V	SOIC-8, DPAK-5
NCV5501	1.5, 3.3, 5	±4.9%	500 mA	0.7 V	-	500 µA (100 µA)							♦		♦	18 V	DPAK-3
NCV78Mxx	5, 8, 12, 15	±4%	500 mA	*	-	*							♦		♦	35 V	TO-220, DPAK-3
NCV78MxxA	5	±5%	500 mA	*	-	*							♦		♦	35 V	DPAK-3
NCV8141	5	±3%	500 mA	1.5 V	50 µA	*	♦	♦					♦		♦	60 V	D2PAK-7
NCV8535	Adj, 1.5, 1.8, 2.5, 2.8, 2.85, 3.0, 3.3, 5	±1.5%	500 mA	0.34 V	1 µA	190 µA (100 µA)	♦						♦		♦	16 V	DFN-10 3x3

NOTE: All devices in this table are AEC-Qualified and PPAP-Capable. Contact ON Semiconductor for details. * See datasheet for details.

ON Semiconductor Selector Guide – DC-DC Controllers, Converters, and Regulators

SINGLE AUTOMOTIVE LINEAR VOLTAGE REGULATORS (CONTINUED)

Device	Output Voltage (V)	Tolerance	Output Current	Dropout (Max)	Sleepmode Current (Max)	Quiescent Current (Max) @ Low Load (Load)	Enable	Reset (♦♦ = Adjustable)	Delay	Early Warning Flag/Monitor	Watchdog	Current Limit	Overvoltage	Overtemperature	Peak Transient	Packages
CS8126	5	±3%	750 mA	0.6 V	-	-	♦	♦	♦			♦	♦	♦	60 V	D2PAK-7
CS8129	5	±3%	750 mA	0.6 V	-	-	♦	♦	♦			♦	♦	♦	60 V	SOIC-16
NCV33269	Adj. 3.3, 5, 12	±2%	800 mA	1.35 V	-	-						♦		♦	20 V	DPAK-3
NCV78xxA	5, 12	±4%	1 A	*	-	-						♦		♦	35 V	D2PAK-3, TO-220
NCV78xx	5, 8, 12, 15	5%	1 A	*	-	-						♦		♦	35 V	TO-220, DPAK-3, D2PAK-3
NCV5661	Adj. 1.2, 1.5, 1.8, 2.5, 2.8, 3.0, 3.3	±2%	1 A	1.3 V	300 µA	-	♦	♦				♦		♦	18 V	DPAK-5, DFN-6 3x3
NCV1117	Adj. 1.5, 1.8, 2, 2.5, 3.3, 5, 12	±2%	1 A	1.2 V	-	-						♦		♦	20 V	DPAK-3, SOT-223
NCV317	Adj.	±4%	1.5 A	2.25 V Typ	-	-						♦		♦	40 V	TO-220, D2PAK-3
NCV565	Adj.	±3%	1.5 A	1.3 V	-	-						♦		♦	18 V	D2PAK-5
NCV5662	Adj. 1.5	±2%	2 A	1.3 V	300 µA	-	♦	♦				♦		♦	18 V	D2PAK-5
NCV5663	Adj. 1.5	±2%	3 A	1.3 V	300 µA	-	♦	♦				♦		♦	18 V	D2PAK-5

NOTE: All devices in this table are AEC-Qualified and PPAP-Capable. Contact ON Semiconductor for details. * See datasheet for details.

DUAL AUTOMOTIVE LINEAR VOLTAGE REGULATORS

Device	Output Voltage	Tolerance	Output Current	Dropout (Max)	Sleepmode Current (Max)	Quiescent Current (Max) @ Low Load (Load)	Enable	Reset	Delay	Sequenced	Current Limit	Overvoltage	Overtemperature	Peak Transient	Package(s)
CS8361	5 V Tracking	±2% 25 mV	100 mA 250 mA	0.6 V 0.7 V	200 µA	200 µA (300 µA)	♦	♦			♦	♦	♦	60 V	D2PAK-7, SOIC-16 Fused
NCV8509	5.0, 5.0, 3.3 V 2.6, 2.5, 1.8 V	±2% ±2%	115 mA 100 mA	0.6 V -	-	175 µA (200 µA)		♦	♦	♦	♦		♦	50 V	SOIC-16 ePad
NCV5504	Adj. 3.3 V	±2% ±2%	250 mA 250 mA	0.4 V 0.4 V	-	450 µA (0 µA)					♦		♦	18 V	DPAK-5

NOTE: All devices in this table are AEC-Qualified and PPAP-Capable. Contact ON Semiconductor for details.

BATTERY CHARGE CONTROLLER

Device	Description	Type	Number of Cells Charged	V _{CC} Min (V)	V _{CC} Max (V)	I _D Max (µA)	Features	Packages
M/C33341	Power Supply Battery Charger Regulation Control Circuit	-	Flexible	2.3	15	-	CCCV	SOIC-8, PDIP-8
NCP1855B	One-Cell Lithium-ion/Polymer Battery Charger	Li-Ion/Polymer	1	2.8	-	3	CCCV	DFN-10

Digital Potentiometers

Digital Potentiometers

Table of Contents

	Page
Digitally Programmable Potentiometers	136

ON Semiconductor Selector Guide – Digital Potentiometers

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (k Ω)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5120SDI-10	1	16	Potentiometer	Up/Down	10	VCC	No	5.5	SC-70
CAT5120TBI-10	1	16	Potentiometer	Up/Down	10	VCC	No	5.5	SOT-23
CAT5121SDI-10	1	16	Rheostat	Up/Down	10	VCC	No	5.5	SC-70
CAT5121TBI-10	1	16	Rheostat	Up/Down	10	VCC	No	5.5	SOT-23
CAT5122SDI-10	1	16	Rheostat	Up/Down	10	VCC	No	5.5	SC-70
CAT5122TBI-10	1	16	Rheostat	Up/Down	10	VCC	No	5.5	SOT-23
CAT5120SDI-50	1	16	Potentiometer	Up/Down	50	VCC	No	5.5	SC-70
CAT5120TBI-50	1	16	Potentiometer	Up/Down	50	VCC	No	5.5	SOT-23
CAT5121SDI-50	1	16	Rheostat	Up/Down	50	VCC	No	5.5	SC-70
CAT5121TBI-50	1	16	Rheostat	Up/Down	50	VCC	No	5.5	SOT-23
CAT5110SDI-10	1	32	Potentiometer	Up/Down	10	VCC	No	5.5	SC-70
CAT5110TBI-10	1	32	Potentiometer	Up/Down	10	VCC	No	5.5	SOT-23
CAT5112LI-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	PDIP-8
CAT5112VI-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	SOIC-8
CAT5112YI-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	TSSOP-8
CAT5112ZI-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	MSOP-8
CAT5114LI-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	PDIP-8
CAT5114VI-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	SOIC 8
CAT5114VP2I-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	TDFN-8
CAT5114YI-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	TSSOP-8
CAT5114ZD7I10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	TDFN-8
CAT5114ZI-10	1	32	Potentiometer	Up/Down	10	VCC	Yes	6	MSOP-8
CAT5115LI-10	1	32	Potentiometer	Up/Down	10	VCC	No	6	PDIP-8
CAT5115VI-10	1	32	Potentiometer	Up/Down	10	VCC	No	6	SOIC 8
CAT5115YI-10	1	32	Potentiometer	Up/Down	10	VCC	No	6	TSSOP-8
CAT5115ZI-10	1	32	Potentiometer	Up/Down	10	VCC	No	6	MSOP-8

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (kΩ)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5115ZI10	1	32	Potentiometer	Up/Down	10	VCC	No	6	MSOP-8
CAT5126VP2I10	1	32	Potentiometer	Up/Down	10	VCC	OTP	5.5	TDFN-8
CAT5126ZI-10	1	32	Potentiometer	Up/Down	10	VCC	OTP	5.5	MSOP-8
CAT5128TBI-10	1	32	Potentiometer	Up/Down	10	VCC	No	5.5	SOT-23
CAT5118SDI-10	1	32	Rheostat	Up/Down	10	VCC	No	5.5	SC-70
CAT5118TBI-10	1	32	Rheostat	Up/Down	10	VCC	No	5.5	SOT-23
CAT5119SDI-10	1	32	Rheostat	Up/Down	10	VCC	No	5.5	SC-70
CAT5119TBI-10	1	32	Rheostat	Up/Down	10	VCC	No	5.5	SOT-23
CAT5123TBI-10	1	32	Rheostat	Up/Down	10	VCC	No	5.5	SOT-23
CAT5125TBI-10	1	32	Rheostat	Up/Down	10	VCC	No	5.5	SOT-23
CAT5127ZD7I10	1	32	Rheostat	Up/Down	10	VCC	Yes	5.5	TDFN-8
CAT5127ZI-10	1	32	Rheostat	Up/Down	10	VCC	Yes	5.5	MSOP-8
CAT5127ZI10	1	32	Rheostat	Up/Down	10	VCC	Yes	5.5	MSOP-8
CAT5129TDI-10	1	32	Rheostat	Up/Down	10	VCC	Yes	5.5	TSOT-23
CAT5110SDI-50	1	32	Potentiometer	Up/Down	50	VCC	No	5.5	SC-70
CAT5110TBI-50	1	32	Potentiometer	Up/Down	50	VCC	No	5.5	SOT-23
CAT5112LI-50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	PDIP-8
CAT5112VI-50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	SOIC-8
CAT5112YI-50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	TSSOP-8
CAT5112ZI-50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	MSOP-8
CAT5114LI-50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	PDIP-8
CAT5114VI-50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	SOIC 8
CAT5114VP2I50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	TDFN-8
CAT5114YI-50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	TSSOP-8
CAT5114ZD7I50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	TDFN-8
CAT5114ZI-50	1	32	Potentiometer	Up/Down	50	VCC	Yes	6	MSOP-8
CAT5115LI-50	1	32	Potentiometer	Up/Down	50	VCC	No	6	PDIP-8

ON Semiconductor Selector Guide – Digital Potentiometers

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (k Ω)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5115VI-50	1	32	Potentiometer	Up/Down	50	VCC	No	6	SOIC 8
CAT5115YI-50	1	32	Potentiometer	Up/Down	50	VCC	No	6	TSSOP-8
CAT5115ZI-50	1	32	Potentiometer	Up/Down	50	VCC	No	6	MSOP-8
CAT5115ZI50	1	32	Potentiometer	Up/Down	50	VCC	No	6	MSOP-8
CAT5126ZI-50	1	32	Potentiometer	Up/Down	50	VCC	OTP	5.5	MSOP-8
CAT5128TBI-50	1	32	Potentiometer	Up/Down	50	VCC	No	5.5	SOT-23
CAT5118SDI-50	1	32	Rheostat	Up/Down	50	VCC	No	5.5	SC-70
CAT5118TBI-50	1	32	Rheostat	Up/Down	50	VCC	No	5.5	SOT-23
CAT5119SDI-50	1	32	Rheostat	Up/Down	50	VCC	No	5.5	SC-70
CAT5119TBI-50	1	32	Rheostat	Up/Down	50	VCC	No	5.5	SOT-23
CAT5124TBI-50	1	32	Rheostat	Up/Down	50	VCC	No	5.5	SOT-23
CAT5110SDI-00	1	32	Potentiometer	Up/Down	100	VCC	No	5.5	SC-70
CAT5110TBI-00	1	32	Potentiometer	Up/Down	100	VCC	No	5.5	SOT-23
CAT5112LI-00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	PDIP-8
CAT5112VI-00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	SOIC-8
CAT5112YI-00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	TSSOP-8
CAT5114LI-00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	PDIP-8
CAT5114VI-00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	SOIC 8
CAT5114VP2I00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	TDFN-8
CAT5114YI-00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	TSSOP-8
CAT5114ZD7I00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	TDFN-8
CAT5114ZI-00	1	32	Potentiometer	Up/Down	100	VCC	Yes	6	MSOP-8
CAT5115LI-00	1	32	Potentiometer	Up/Down	100	VCC	No	6	PDIP-8
CAT5115VI-00	1	32	Potentiometer	Up/Down	100	VCC	No	6	SOIC 8
CAT5115YI-00	1	32	Potentiometer	Up/Down	100	VCC	No	6	TSSOP-8
CAT5115ZI-00	1	32	Potentiometer	Up/Down	100	VCC	No	6	MSOP-8
CAT5115ZI00	1	32	Potentiometer	Up/Down	100	VCC	No	6	MSOP-8

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (k Ω)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5126ZI-00	1	32	Potentiometer	Up/Down	100	VCC	OTP	5.5	MSOP-8
CAT5118SDI-00	1	32	Rheostat	Up/Down	100	VCC	No	5.5	SC-70
CAT5118TBI-00	1	32	Rheostat	Up/Down	100	VCC	No	5.5	SOT-23
CAT5119SDI-00	1	32	Rheostat	Up/Down	100	VCC	No	5.5	SC-70
CAT5119TBI-00	1	32	Rheostat	Up/Down	100	VCC	No	5.5	SOT-23
CAT5113LI-01	1	100	Potentiometer	Up/Down	1	VCC	Yes	6	PDIP-8
CAT5113VI-01	1	100	Potentiometer	Up/Down	1	VCC	Yes	6	SOIC-8
CAT5113YI-01	1	100	Potentiometer	Up/Down	1	VCC	Yes	6	TSSOP-8
CAT5113ZI-01	1	100	Potentiometer	Up/Down	1	VCC	Yes	6	MSOP-8
CAT5113ZI01	1	100	Potentiometer	Up/Down	1	VCC	Yes	6	MSOP-8
CAT5111LI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	PDIP-8
CAT5111VI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	SOIC-8
CAT5111VI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	SOIC-8
CAT5111YI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	TSSOP-8
CAT5111YI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	TSSOP-8
CAT5111ZI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	MSOP-8
CAT5111ZI10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	MSOP-8
CAT5113LI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	PDIP-8
CAT5113VI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	SOIC-8
CAT5113YI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	TSSOP-8
CAT5113ZI-10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	MSOP-8
CAT5113ZI10	1	100	Potentiometer	Up/Down	10	VCC	Yes	6	MSOP-8
CAT5116LI	1	100	Potentiometer	Up/Down	32	VCC	Yes	5.5	PDIP-8
CAT5116VI	1	100	Potentiometer	Up/Down	32	VCC	Yes	5.5	SOIC-8
CAT5116YI	1	100	Potentiometer	Up/Down	32	VCC	Yes	5.5	TSSOP-8
CAT5116ZI	1	100	Potentiometer	Up/Down	32	VCC	Yes	5.5	MSOP-8
CAT5111LI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	PDIP-8

ON Semiconductor Selector Guide – Digital Potentiometers

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (k Ω)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5111VI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	SOIC-8
CAT5111VI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	SOIC-8
CAT5111YI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	TSSOP-8
CAT5111YI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	TSSOP-8
CAT5111ZI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	MSOP-8
CAT5111ZI50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	MSOP-8
CAT5113LI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	PDIP-8
CAT5113VI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	SOIC-8
CAT5113YI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	TSSOP-8
CAT5113ZI-50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	MSOP-8
CAT5113ZI50	1	100	Potentiometer	Up/Down	50	VCC	Yes	6	MSOP-8
CAT5111LI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	PDIP-8
CAT5111VI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	SOIC-8
CAT5111YI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	TSSOP-8
CAT5111YI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	TSSOP-8
CAT5111ZI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	MSOP-8
CAT5111ZI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	MSOP-8
CAT5111ZI00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	MSOP-8
CAT5113LI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	PDIP-8
CAT5113VI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	SOIC-8
CAT5113YI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	TSSOP-8
CAT5113ZI-00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	MSOP-8
CAT5113ZI00	1	100	Potentiometer	Up/Down	100	VCC	Yes	6	MSOP-8
CAT5132ZI-10	1	128	Potentiometer	I ² C	10	16	Yes	5.5	MSOP-10
CAT5133ZI-10	1	128	Potentiometer	Up/Down	10	16	Yes	5.5	MSOP-10
CAT5132ZI-50	1	128	Potentiometer	I ² C	50	16	Yes	5.5	MSOP-10

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (kΩ)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5132ZI-00	1	128	Potentiometer	I ² C	100	16	Yes	5.5	MSOP-10
CAT5140ZI-50	1	256	Potentiometer	I ² C	50	VCC	Yes	5.5	MSOP-8
CAT5171TBI-50	1	256	Potentiometer	I ² C	50	VCC	No	5.5	SOT-23
CAT5172TBI-50	1	256	Potentiometer	SPI	50	VCC	No	5.5	SOT-23
CAT5140ZI-00	1	256	Potentiometer	I ² C	100	VCC	Yes	5.5	MSOP-8
CAT5172TBI-00	1	256	Potentiometer	SPI	100	VCC	No	5.5	SOT-23
CAT5221WI-25	2	64	Potentiometer	I ² C	2.5	VCC	Yes	6	SOIC-20
CAT5221WI25	2	64	Potentiometer	I ² C	2.5	VCC	Yes	6	SOIC-20
CAT5221YI-25	2	64	Potentiometer	I ² C	2.5	VCC	Yes	6	TSSOP-20
CAT5221YI25	2	64	Potentiometer	I ² C	2.5	VCC	Yes	6	TSSOP-20
CAT5411WI-25	2	64	Potentiometer	SPI	2.5	VCC	Yes	6	SOIC-24
CAT5411WI25	2	64	Potentiometer	SPI	2.5	VCC	Yes	6	SOIC-24
CAT5411YI-25	2	64	Potentiometer	SPI	2.5	VCC	Yes	6	TSSOP-24
CAT5411YI25	2	64	Potentiometer	SPI	2.5	VCC	Yes	6	TSSOP-24
CAT5419WI-25	2	64	Potentiometer	I ² C	2.5	VCC	Yes	6	SOIC-24
CAT5419WI25	2	64	Potentiometer	I ² C	2.5	VCC	Yes	6	SOIC-24
CAT5419YI-25	2	64	Potentiometer	I ² C	2.5	VCC	Yes	6	TSSOP-24
CAT5419YI25	2	64	Potentiometer	I ² C	2.5	VCC	Yes	6	TSSOP-24
CAT5221WI-10	2	64	Potentiometer	I ² C	10	VCC	Yes	6	SOIC-20
CAT5221WI10	2	64	Potentiometer	I ² C	10	VCC	Yes	6	SOIC-20
CAT5221YI-10	2	64	Potentiometer	I ² C	10	VCC	Yes	6	TSSOP-20
CAT5221YI10	2	64	Potentiometer	I ² C	10	VCC	Yes	6	TSSOP-20
CAT5411WI-10	2	64	Potentiometer	SPI	10	VCC	Yes	6	SOIC-24
CAT5411WI10	2	64	Potentiometer	SPI	10	VCC	Yes	6	SOIC-24
CAT5411YI-10	2	64	Potentiometer	SPI	10	VCC	Yes	6	TSSOP-24
CAT5411YI10	2	64	Potentiometer	SPI	10	VCC	Yes	6	TSSOP-24
CAT5419WI-10	2	64	Potentiometer	I ² C	10	VCC	Yes	6	SOIC-24

ON Semiconductor Selector Guide – Digital Potentiometers

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (k Ω)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5419YI-10	2	64	Potentiometer	I ² C	10	VCC	Yes	6	TSSOP-24
CAT5419YI10	2	64	Potentiometer	I ² C	10	VCC	Yes	6	TSSOP-24
CAT5221WI-50	2	64	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-20
CAT5221WI50	2	64	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-20
CAT5221YI-50	2	64	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-20
CAT5221YI50	2	64	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-20
CAT5411WI-50	2	64	Potentiometer	SPI	50	VCC	Yes	6	SOIC-24
CAT5411WI50	2	64	Potentiometer	SPI	50	VCC	Yes	6	SOIC-24
CAT5411YI-50	2	64	Potentiometer	SPI	50	VCC	Yes	6	TSSOP-24
CAT5411YI50	2	64	Potentiometer	SPI	50	VCC	Yes	6	TSSOP-24
CAT5419WI-50	2	64	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-24
CAT5419WI50	2	64	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-24
CAT5419YI-50	2	64	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-24
CAT5419YI50	2	64	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-24
CAT5221WI-00	2	64	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-20
CAT5221WI00	2	64	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-20
CAT5221YI-00	2	64	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-20
CAT5221YI00	2	64	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-20
CAT5411WI-00	2	64	Potentiometer	SPI	100	VCC	Yes	6	SOIC-24
CAT5411WI00	2	64	Potentiometer	SPI	100	VCC	Yes	6	SOIC-24
CAT5411YI-00	2	64	Potentiometer	SPI	100	VCC	Yes	6	TSSOP-24
CAT5411YI00	2	64	Potentiometer	SPI	100	VCC	Yes	6	TSSOP-24
CAT5419WI-00	2	64	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-24
CAT5419WI00	2	64	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-24
CAT5419YI-00	2	64	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-24
CAT5419YI00	2	64	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-24
CAT5261WI-50	2	256	Potentiometer	SPI	50	VCC	Yes	6	SOIC-24

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (kΩ)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5261WI50	2	256	Potentiometer	SPI	50	VCC	Yes	6	SOIC-24
CAT5261YI-50	2	256	Potentiometer	SPI	50	VCC	Yes	6	TSSOP-24
CAT5261YI50	2	256	Potentiometer	SPI	50	VCC	Yes	6	TSSOP-24
CAT5269WI-50	2	256	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-24
CAT5269WI50	2	256	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-24
CAT5269YI50	2	256	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-24
CAT5270YI-50	2	256	Potentiometer	I ² C	50	VCC	No	6	TSSOP-14
CAT5271ZI-50	2	256	Potentiometer	I ² C	50	VCC	No	6.5	MSOP-10
CAT5261WI-00	2	256	Potentiometer	SPI	100	VCC	Yes	6	SOIC-24
CAT5261WI00	2	256	Potentiometer	SPI	100	VCC	Yes	6	SOIC-24
CAT5261YI-00	2	256	Potentiometer	SPI	100	VCC	Yes	6	TSSOP-24
CAT5261YI00	2	256	Potentiometer	SPI	100	VCC	Yes	6	TSSOP-24
CAT5269WI-00	2	256	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-24
CAT5269WI00	2	256	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-24
CAT5269YI-00	2	256	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-24
CAT5269YI00	2	256	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-24
CAT5270YI-00	2	256	Potentiometer	I ² C	100	VCC	No	6.5	MSOP-10
CAT5241WI-25	4	64	Potentiometer	I ² C	2.5	VCC	Yes	6	SOIC-20
CAT5241WI25	4	64	Potentiometer	I ² C	2.5	VCC	Yes	6	SOIC-20
CAT5241YI-25	4	64	Potentiometer	I ² C	2.5	VCC	Yes	6	TSSOP-20
CAT5241YI25	4	64	Potentiometer	I ² C	2.5	VCC	Yes	6	TSSOP-20
CAT5401WI-25	4	64	Potentiometer	SPI	2.5	VCC	Yes	6	SOIC-24
CAT5401WI25	4	64	Potentiometer	SPI	2.5	VCC	Yes	6	SOIC-24
CAT5401YI-25	4	64	Potentiometer	SPI	2.5	VCC	Yes	6	TSSOP-24
CAT5401YI25	4	64	Potentiometer	SPI	2.5	VCC	Yes	6	TSSOP-24
CAT5409WI-25	4	64	Potentiometer	I ² C	2.5	VCC	Yes	6	SOIC-24

ON Semiconductor Selector Guide – Digital Potentiometers

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (k Ω)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5409YI-25	4	64	Potentiometer	I ² C	2.5	VCC	Yes	6	TSSOP-24
CAT5409YI25	4	64	Potentiometer	I ² C	2.5	VCC	Yes	6	TSSOP-24
CAT5241WI-10	4	64	Potentiometer	I ² C	10	VCC	Yes	6	SOIC-20
CAT5241WI10	4	64	Potentiometer	I ² C	10	VCC	Yes	6	SOIC-20
CAT5241YI-10	4	64	Potentiometer	I ² C	10	VCC	Yes	6	TSSOP-20
CAT5241YI10	4	64	Potentiometer	I ² C	10	VCC	Yes	6	TSSOP-20
CAT5401WI-10	4	64	Potentiometer	SPI	10	VCC	Yes	6	SOIC-24
CAT5401WI10	4	64	Potentiometer	SPI	10	VCC	Yes	6	SOIC-24
CAT5401YI-10	4	64	Potentiometer	SPI	10	VCC	Yes	6	TSSOP-24
CAT5401YI10	4	64	Potentiometer	SPI	10	VCC	Yes	6	TSSOP-24
CAT5409WI-10	4	64	Potentiometer	I ² C	10	VCC	Yes	6	SOIC-24
CAT5409WI10	4	64	Potentiometer	I ² C	10	VCC	Yes	6	SOIC-24
CAT5409YI-10	4	64	Potentiometer	I ² C	10	VCC	Yes	6	TSSOP-24
CAT5409YI10	4	64	Potentiometer	I ² C	10	VCC	Yes	6	TSSOP-24
CAT5241WI-50	4	64	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-20
CAT5241WI50	4	64	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-20
CAT5241YI-50	4	64	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-20
CAT5241YI50	4	64	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-20
CAT5401WI-50	4	64	Potentiometer	SPI	50	VCC	Yes	6	SOIC-24
CAT5401WI50	4	64	Potentiometer	SPI	50	VCC	Yes	6	SOIC-24
CAT5401YI-50	4	64	Potentiometer	SPI	50	VCC	Yes	6	TSSOP-24
CAT5401YI50	4	64	Potentiometer	SPI	50	VCC	Yes	6	TSSOP-24
CAT5409WI-50	4	64	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-24
CAT5409WI50	4	64	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-24
CAT5409YI-50	4	64	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-24
CAT5409YI50	4	64	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-24
CAT5241WI-00	4	64	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-20

DIGITALLY PROGRAMMABLE POTENTIOMETERS

Product	# of Pots	# of Taps	Type	Control Interface	Resistance Typ (kΩ)	V _H Max (V)	Wiper Position Memory	V _{DD} Max (V)	Package
CAT5241WI00	4	64	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-20
CAT5241YI-00	4	64	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-20
CAT5241YI00	4	64	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-20
CAT5401WI-00	4	64	Potentiometer	SPI	100	VCC	Yes	6	SOIC-24
CAT5401WI00	4	64	Potentiometer	SPI	100	VCC	Yes	6	SOIC-24
CAT5401YI-00	4	64	Potentiometer	SPI	100	VCC	Yes	6	TSSOP-24
CAT5401YI00	4	64	Potentiometer	SPI	100	VCC	Yes	6	TSSOP-24
CAT5409WI-00	4	64	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-24
CAT5409WI00	4	64	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-24
CAT5409YI-00	4	64	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-24
CAT5409YI00	4	64	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-24
CAT5251WI-50	4	256	Potentiometer	SPI	50	VCC	Yes	6	SOIC-24
CAT5251WI50	4	256	Potentiometer	SPI	50	VCC	Yes	6	SOIC-24
CAT5251YI-50	4	256	Potentiometer	SPI	50	VCC	Yes	6	TSSOP-24
CAT5251YI50	4	256	Potentiometer	SPI	50	VCC	Yes	6	TSSOP-24
CAT5259WI-50	4	256	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-24
CAT5259WI50	4	256	Potentiometer	I ² C	50	VCC	Yes	6	SOIC-24
CAT5259YI-50	4	256	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-24
CAT5259YI50	4	256	Potentiometer	I ² C	50	VCC	Yes	6	TSSOP-24
CAT5251WI-00	4	256	Potentiometer	SPI	100	VCC	Yes	6	SOIC-24
CAT5251WI00	4	256	Potentiometer	SPI	100	VCC	Yes	6	SOIC-24
CAT5251YI-00	4	256	Potentiometer	SPI	100	VCC	Yes	6	TSSOP-24
CAT5251YI00	4	256	Potentiometer	SPI	100	VCC	Yes	6	TSSOP-24
CAT5259WI-00	4	256	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-24
CAT5259WI00	4	256	Potentiometer	I ² C	100	VCC	Yes	6	SOIC-24
CAT5259YI-00	4	256	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-24
CAT5259YI00	4	256	Potentiometer	I ² C	100	VCC	Yes	6	TSSOP-24

Diodes

Diodes

Table of Contents

	Page
Tuning and Switching Diodes	
Abrupt Junction Tuning Diodes	150
Hyper–Abrupt Junction Tuning Diodes	150
Schottky Diodes	151
Pin Switching Diodes	154
General Purpose Signal & Switching Diodes	155
Zener Diodes – Regulation in Axial Leads	157
Zener Diodes – Regulation in Surface Mount	159
Dual Zeners – Surface Mount	165
TVS Diodes – In Axial Leads	168
TVS Diodes – In Surface Mount	171
ESD Protection Diodes	183
TVS/ESD Protection	198

TUNING AND SWITCHING DIODES

ABRUPT JUNCTION TUNING DIODES

Device	V _R Volts	C _T @ V _R = 4.0 V, 1.0 MHz			Cap Ratio Min	Q @ 4.0 V 50 MHz Typ	Package
		pF Min	pF Nominal	pF Max			
MV2105	30	13.5	15	16.5	2.5	400	 TO-226AC, TO-92 2-Lead Case 182-06
MMBV2105L	30	13.5	15	16.5	2.5	400	 TO-236AB, SOT-23 Case 318-08
MMBV3102L	30	20	–	25	4.5	200	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

HYPER-ABRUPT JUNCTION TUNING DIODES

Device	V _R Volts	C _T (f = 1.0 MHz)			Cap Ratio			Q 3.0 V Min	Type	Package
		pF Min	pF Max	Volts	Min	Max	Volts			
MMBV105GL	30	1.5	2.8	25	4.0	6.5	3.0/25	200	Single	 TO-236AB, SOT-23 Case 318-08
MMBV609L	20	26	32	3.0	1.8	2.4	3/8	250	Dual Common Cathode	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

TUNING AND SWITCHING DIODES (continued)

SCHOTTKY DIODES

Device	V _R Volts	C _T @ V		V _F Volts Max	I _R @ V		Type	Package
		pF Max	Volts		nA Max	Volts		
<i>MBD301</i>	30	1.5	15	0.6	200	25	Single	 TO-226AC, TO-92 2-Lead Case 182-06
<i>MMSD701</i>	70	1.0	20	1.0	200	35	Single	 SOD-123 Case 425-04
<i>BAT54</i>	30	10	1.0	0.4	2000	25	Single	
<i>MMSD301</i>	30	1.5	15	0.6	200	25	Single	
<i>MMDL770</i>	70	1.0	20	1.0	200	35	Single	 SOD-323 Case 477-02
<i>BAT54H</i>	30	10	1.0	0.4	2000	25	Single	
<i>MMDL301</i>	30	1.5	15	0.6	200	25	Single	
NSR0240H	40	–	–	0.71	550	10	Single	
NSR0340H	40	–	–	0.59	1000	10	Single	
NSR1020MW2	20	29	5	0.44	40000	10	Single	
NSRLV20MW2	20	29	5	0.27	50000	10	Single	
<i>RB751V40</i>	30	2.5	1.0	0.37	500	30	Single	
<i>MMDL101</i>	7.0	1.0	0	0.6	250	3.0	Single	
<i>NSR0320MW2</i>	20	29	5.0	0.27	50000	15	Single	
<i>BAS70L</i>	70	2.0	0	0.75	100	50	Single	 TO-236AB, SOT-23 Case 318-08
<i>BAS70-04L</i>	70	2.0	0	0.75	100	50	Dual Series	
<i>MMBD701L</i>	70	1.0	20	1.0	200	35	Single	
<i>BAS40L</i>	40	5.0	1.0	0.5	1000	25	Single	
<i>BAS40-04L</i>	40	5.0	1.0	0.5	1000	25	Dual Series	
<i>BAS40-06L</i>	40	5.0	1.0	0.5	1000	25	Dual Common Anode	
BAT54CL	30	10	1.0	0.4	2000	25	Dual Common Cathode	
<i>BAT54L</i>	30	10	1.0	0.4	2000	25	Single	
<i>BAT54AL</i>	30	10	1.0	0.4	2000	25	Dual Common Anode	
<i>BAT54SL</i>	30	10	1.0	0.4	2000	25	Dual Series	
<i>MMBD301L</i>	30	1.5	15	0.6	200	25	Single	
MMBD452L	30	1.5	15	0.6	200	25	Dual Series	
<i>MMBD101L</i>	7.0	1.0	0	0.6	250	3.0	Single	
<i>MMBD352L</i>	7.0	1.0	0	0.6	250	3.0	Dual Series	
<i>MMBD353L</i>	7.0	1.0	0	0.6	250	3.0	Dual Series	
<i>MMBD354L</i>	7.0	1.0	0	0.6	250	3.0	Dual Common Cathode	
<i>MMBD355L</i>	7.0	1.0	0	0.6	250	3.0	Dual Common Anode	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

TUNING AND SWITCHING DIODES (continued)

SCHOTTKY DIODES (continued)

Device	V _R Volts	C _T @ V		V _F Volts Max	I _R @ V		Type	Package
		pF Max	Volts		nA Max	Volts		
MMBD770	70	1.0	20	1.0	200	35	Single	 SC-70, SOT-323 Case 419-04
BAT54AW	30	10	1.0	0.4	2000	25	Dual Common Anode	
BAT54CW	30	10	1.0	0.4	2000	25	Dual Common Cathode	
BAT54W	30	10	1.0	0.4	2000	25	Single	
BAT54SW	30	10	1.0	0.4	2000	25	Dual Series	
MMBD330	30	1.5	15	0.6	200	25	Single	
MMBD717L	20	2.5	1.0	0.37	1000	10	Dual Common Anode	
MMBD352W	7.0	1.0	0	0.6	250	3.0	Dual Series	
BAT54CT	30	10	1.0	0.4	2000	25	Dual Common Cathode	 SOT-416, SC-75, SC-90 Case 463-01
MBD770DW	70	1.0	0	0.5	200	35	Dual Isolated	 SC-88, SOT-363 Case 419B-02
MBD54DW	30	1.0	0	0.32	2000	25	Dual Isolated	
MBD330DW	30	1.5	0	0.4	200	25	Dual Isolated	
NSR0320XV6	23	35	5.0	0.27	50000	15	Single	 SOT-563 Case 463A-01
BAT54CXV3	30	10	1.0	0.4	2000	25	Dual Common Cathode	 SC-89 Case 463C-03
NSR0240V2	40	–	–	0.39	2000	25	Single	 SOD-523 Case 502-01
NSR0340V2	40	–	–	0.35	3000	25	Single	
RB751S40	40	2.5	1.0	0.37	500	30	Single	
BAT54XV2	30	10	1.0	0.4	2000	25	Single	
NSRLL30XV2	30	–	–	0.60	1000	10	Single	
RB520S30	30	–	–	0.5	1000	10	Single	
RB521S30	30	–	–	0.6	30000	10	Single	
NSR0520V2	20	–	–	0.32	30000	10	Single	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

TUNING AND SWITCHING DIODES (continued)

SCHOTTKY DIODES (continued)

Device	V _R Volts	C _T @ V		V _F Max Volts	I _R @ V		Type	Package
		pF Max	Volts		nA Max	Volts		
NSR0230M2	30	–	–	0.325	10000	10	Single	 SOD-723 Case 509AA
NSR30CM3	30	10	1.0	0.8	2.0	25	Dual Common Cathode	 SOT-723 Case 631AA-01
MMBD301M3	30	1.5	15	0.6	200	25	Single	
BAT54M3	30	10	1	0.4	2000	25	Single	
NSR0130P2	30	–	–	0.385	350	10	Single	 SOD-923 Case 514AA-01
NSR0140P2	40	2.5	1.0	0.350	500	30	Single	
NSR0170P2	70	–	–	0.64	90	50	Single	
NSR0240P2	40	–	–	0.5	5000	40	Single	
NSR0340P2	40	–	–	0.56	5000	10	Single	
NSR0530P2	30	–	–	0.46	10000	10	Single	
NSR0620P2	20	–	–	0.52	10000	10	Single	
NSR0230P2	20	–	–	0.325	10000	10	Single	
NSR20F30NX	30	–	–	0.480	20000	10	Single	
NSR20F20NX	20	–	–	0.490	30000	10	Single	
NSR10F40NX	40	–	–	0.490	10000	10	Single	 DSN2 (0502) Case 152AD-01
NSR10F30NX	30	–	–	0.480	20000	10	Single	
NSR10F20NX	20	–	–	0.460	20000	10	Single	
NSR05F40NX	40	–	–	0.44	15000	10	Single	 DSN2 (0402) Case 152AC-01
NSR05F30NX	30	–	–	0.430	15000	10	Single	
NSR05F20NX	20	–	–	0.430	15000	10	Single	
NSR02L30NX	30	–	–	0.4	200	10	Single	 DSN2 (0201) Case 152AA-01
NSR02F30NX	30	–	–	0.37	7000	10	Single	
NSR01L30NX	30	–	–	0.4	200	10	Single	
NSR01F30NX	30	–	–	0.37	700	10	Single	

Devices listed in ***bold italic*** are ON Semiconductor preferred devices.

TUNING AND SWITCHING DIODES (continued)

PIN SWITCHING DIODES

Device	V _R Volts Min	C _T @ V		Resistance Ω Max	I _R μA Max	Type	Package
		pF Max	Volts				
MMBV3700L	200	1.0	20	1.0	0.1	Single	 TO-236AB, SOT-23 Case 318-08
<i>MMBV3401L</i>	35	1.0	20	0.7	0.1	Single	
<i>MMVL3401</i>	35	1.0	20	0.7	0.1	Single	 SOD-323 Case 477-02

Devices listed in ***bold italic*** are ON Semiconductor preferred devices.

TUNING AND SWITCHING DIODES (continued)

GENERAL PURPOSE SIGNAL AND SWITCHING DIODES

Device	V _R Min Volts	I _R Max μA	V _F		C _T Max pF	t _{rr} Max ns	Type	Package
			Min Volts	Max Volts				
BAV23CL	250	0.1	–	1.25	5	150	Dual Common Cathode	 TO-236AB, SOT-23 Case 318-08
BAS21L	250	0.1	–	1.0	5.0	50	Single	
BAS21SL	250	0.1	–	1.0	5.0	50	Dual Series	
MMBD914L	100	5.0	–	1.0	4.0	4.0	Single	
BAS16L	75	1.0	–	1.0	2.0	6.0	Single	
MMBD6050L	70	0.1	0.85	1.1	2.5	4.0	Single	
BAL99L	70	2.5	–	1.0	1.5	6.0	Single	
BAS116L	75	0.005	–	0.9	2.0	3000	Single	
MMBD7000L	100	1.0	0.75	1.1	1.5	4.0	Dual Series	
MMBD2836L	75	0.1	–	1.0	4.0	4.0	Dual Common Anode	
MMBD2838L	75	0.1	–	1.0	4.0	4.0	Dual Common Cathode	
BAV70L	70	5.0	–	1.0	1.5	6.0	Dual Common Cathode	
BAV99L	70	2.5	–	1.0	1.5	4.0	Dual Series	
BAW56L	70	2.5	–	1.0	2.0	6.0	Dual Common Anode	
MMBD6100L	70	0.1	0.85	1.1	2.5	4.0	Dual Common Cathode	
BAV74L	50	0.1	–	1.0	2.0	4.0	Dual Common Cathode	
MMBD2835L	35	0.1	–	1.0	4.0	4.0	Dual Common Anode	
MMBD2837L	35	0.1	–	1.0	4.0	4.0	Dual Common Cathode	
BAV199L	70	0.005	–	0.9	2.0	3000	Dual Series	
BAS20L	200	0.1	–	1.0	5.0	50	Single	
BAS19L	120	0.1	–	1.0	5.0	50	Single	
M1MA151K	40	0.1	–	1.2	2.0	3.0	Single	 SC-59 Case 318D-04
M1MA152K	80	0.1	–	1.2	2.0	3.0	Single	
M1MA151WA	40	0.1	–	1.2	15	10	Dual Common Anode	
M1MA151WK	40	0.1	–	1.2	2.0	3.0	Dual Common Cathode	
M1MA152WA	80	0.1	–	1.2	15	10	Dual Common Anode	
M1MA152WK	80	0.1	–	1.2	2.0	3.0	Dual Common Cathode	
BAS16W	75	1.0	–	1.25	2.0	6.0	Single	 SC-70, SOT-323 Case 419-04
M1MA141K	40	0.1	–	1.2	2.0	3.0	Single	
M1MA142WK	80	0.1	–	1.2	2.0	3.0	Dual Common Cathode	
M1MA142WA	80	0.1	–	1.2	15	10	Dual Common Anode	
BAW56W	70	2.5	–	1.0	2.0	6.0	Dual Common Anode	
BAV70W	70	5.0	–	1.0	1.5	6.0	Dual Common Cathode	
BAV99W	70	2.5	–	1.0	1.5	6.0	Dual Series	
BAV99RW	70	2.5	–	1.0	1.5	6.0	Dual Series	
M1MA141WA	40	0.1	–	1.2	15	10	Dual Common Anode	
MMSD914	100	5.0	–	1.0	4.0	4.0	Single	 SOD-123 Case 425-04
MMSD103	250	100	–	1.0	5.0	50	Single	
MMSD4148	100	5.0	–	1.0	4.0	4.0	Single	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

TUNING AND SWITCHING DIODES (continued)

GENERAL PURPOSE SIGNAL AND SWITCHING DIODES

Device	V _R Min Volts	I _R Max μA	V _F		C _T Max pF	t _{rr} Max ns	Type	Package
			Min Volts	Max Volts				
BAS16H	75	1.0	–	1.0	2.0	6.0	Single	 SOD-323 Case 477-02
BAS20H	200	0.1			5.0	50	Single	
BAS21AH	250	0.04	–	1.0	5.0	50	Single	
BAS21H	250	0.1	–	1.0	5.0	50	Single	
MMDL914	100	5.0	–	1.0	4.0	4.0	Single	
MMDL6050	70	0.1	0.85	1.1	2.5	4.0	Single	
BAS16T	75	1.0	–	1.0	2.0	6.0	Single	 SOT-416, SC-75, SC-90 Case 463-01
DA121T	80	1.0			2.0	6.0	Single	
DAP222	80	0.1	–	1.2	3.5	4.0	Dual Common Anode	
BAW56T	70	2.5	–	1.0	2.0	6.0	Dual Common Anode	
DAN222	80	0.1	–	1.2	3.5	4.0	Dual Common Cathode	
BAV70T	70	5.0	–	1.0	1.5	6.0	Dual Common Cathode	
HN2D02FUTW1	85	0.1	–	1.2	2.0	3.0	Triple Isolated	 SC-88 Case 419B-02
BAS21DW5	250	0.1	–	1.0	5.0	50	Dual Isolated	 SC-88A Case 419A-02
1SS400	100	0.1	–	1.2	3.0	4.0	Single	 SOD-523 Case 502-01
BAS16XV2	75	1.0	–	1.0	2.0	6.0	Single	
NSD914XV2	100	–	–	1.0	4.0	4.0	Single	
NSDEMP11XV6	70	0.01	–	1.2	3.5	4.0	Two Dual Common Anode	 SOT-563 Case 463A-01
BAS16DXV6	75	0.001	–	1.25	2.0	6.0	Dual Isolated	
BAV70M3	75	2.5	–	1.25	1.5	6	Dual Common Cathode	 SOT-723 Case 631AA-01
BAW56M3	75	2.5	–	1.25	2	6	Dual Common ANode	
DAN222M3	80	0.1	–	1.2	3.5	4.0	Dual Common Cathode	
DAP222M3	80	0.1	–	1.2	3.5	4.0	Dual Common Anode	
BAS21M3	250	0.1	–	1.25	5	50	Single	
NSD16F3	75	1	–	1.25	2	6	Single	
NSD914F3	100	5	–	1	4	4	Single	 SOT-1123 Case 631AA-01

Devices listed in **bold italic** are ON Semiconductor preferred devices.

ZENER DIODES – REGULATION IN AXIAL LEADS

Axial Leaded – 3, 5 W

Nominal Zener Breakdown Voltage	3 Watt Cathode = Polarity Band	5 Watt Cathode = Polarity Band
Volts	 <p>Plastic Surmetic 30 Case 59-10 (DO-41)</p>	 <p>Plastic Surmetic 40 Case 17</p>
3.3	1N5913B	1N5333B
3.6		1N5334B
3.9		1N5335B
4.3		1N5336B
4.7	1N5917B	1N5337B
5.1		1N5338B
5.6	1N5919B	1N5339B
6.0		1N5340B
6.2	1N5920B	1N5341B
6.8	1N5921B	1N5342B
7.5		1N5343B
8.2	1N5923B	1N5344B
8.7		1N5345B
9.1	1N5924B	1N5346B
10	1N5925B	1N5347B
11		1N5348B
12	1N5927B	1N5349B
13		1N5350B
14		1N5351B
15	1N5929B	1N5352B
16		1N5353B
17		1N5354B
18	1N5931B	1N5355B
19		1N5356B
20	1N5932B	1N5357B
22		1N5358B
24	1N5934B	1N5359B

ZENER DIODES – REGULATION IN AXIAL LEADS (continued)

Axial Leaded – 3, 5 W

Nominal Zener Breakdown Voltage	3 Watt Cathode = Polarity Band	5 Watt Cathode = Polarity Band
Volts	 Plastic Surmetic 30 Case 59-10 (DO-41)	 Plastic Surmetic 40 Case 17
25		1N5360B
27	1N5935B	1N5361B
28		1N5362B
30		1N5363B
33	1N5937B	1N5364B
36	1N5938B	1N5365B
39		1N5366B
43	1N5940B	1N5367B
47	1N5941B	1N5368B
51	1N5942B	1N5369B
56		1N5370B
60		1N5371B
62		1N5372B
68		1N5373B
75	1N5946B	1N5374B
82		1N5375B
87		
91	1N5948B	1N5377B
100		1N5378B
110		
120		1N5380B
130		1N5381B
140		
150	1N5953B	1N5383B
160		1N5384B
170		
180	1N5955B	1N5386B
190		1N5387
200	1N5956B	1N5388B



ZENER DIODES – REGULATION IN SURFACE MOUNT

Surface Mount Packages – 200 mW

Nominal Zener Breakdown Voltage	Standard Tolerance SOD-923	Tight Tolerance SOD-923	Standard Tolerance SOD-523	Tight Tolerance SOD-523	Standard Tolerance SOD-323	Tight Tolerance SOD-323
Volts	 Case 514AB	 Case 514AB	 Case 502	 Case 502	 Case 477 Style 1	 Case 477 Style 1
2.4	NZ9F2V4	NZ9F2V4S	MM5Z2V4	MM5Z2V4S	MM3Z2V4	
2.7	NZ9F2V7	NZ9F2V7S	MM5Z2V7		MM3Z2V7	
3.0	NZ9F3V0	NZ9F3V0S	MM5Z3V0		MM3Z3V0	
3.3	NZ9F3V3	NZ9F3V3S	MM5Z3V3		MM3Z3V3	MM3Z3V3S
3.6	NZ9F3V6	NZ9F3V6S	MM5Z3V6		MM3Z3V6	
3.9	NZ9F3V9	NZ9F3V9S			MM3Z3V9	MM3Z3V9S
4.3	NZ9F4V3	NZ9F4V3S			MM3Z4V3	MM3Z4V3S
4.7	NZ9F4V7	NZ9F4V7S	MM5Z4V7	MM5Z4V7S	MM3Z4V7	MM3Z4V7S
5.1	NZ9F5V1	NZ9F5V1S	MM5Z5V1	MM5Z5V1S	MM3Z5V1	MM3Z5V1S
5.6	NZ9F5V6	NZ9F5V6S	MM5Z5V6	MM5Z5V6S	MM3Z5V6	MM3Z5V6S
6.2	NZ9F6V2	NZ9F6V2S	MM5Z6V2	MM5Z6V2S	MM3Z6V2	MM3Z6V2S
6.8	NZ9F6V8	NZ9F6V8S	MM5Z6V8	MM5Z6V8S	MM3Z6V8	MM3Z6V8S
7.5	NZ9F7V5	NZ9F7V5S	MM5Z7V5		MM3Z7V5	MM3Z7V5S
8.2	NZ9F8V2	NZ9F8V2S	MM5Z8V2	MM5Z8V2S	MM3Z8V2	MM3Z8V2S
9.1	NZ9F9V1	NZ9F9V1S	MM5Z9V1	MM5Z9V1S	MM3Z9V1	MM3Z9V1S
10	NZ9F10V	NZ9F10VS	MM5Z10V		MM3Z10V	MM3Z10VS
11	NZ9F11V	NZ9F11VS			MM3Z11V	
12	NZ9F12V	NZ9F12VS	MM5Z12V		MM3Z12V	MM3Z12VS
13	NZ9F13V	NZ9F13VS			MM3Z13V	
15	NZ9F15V	NZ9F15VS	MM5Z15V		MM3Z15V	MM3Z15VS
16	NZ9F16V	NZ9F16VS	MM5Z16V		MM3Z16V	MM3Z16VS
18	NZ9F18V	NS9F18VS	MM5Z18V		MM3Z18V	MM3Z18VS
20	NZ9F20V		MM5Z20V		MM3Z20V	
22	NZ9F22V				MM3Z22V	MM3Z22VS
24	NZ9F24V		MM5Z24V		MM3Z24V	
27			MM5Z27V		MM3Z27V	MM3Z27VS
30			MM5Z30V			
36			MM5Z36V		MM3Z36V	MM3Z33VS
39					MM3Z39V	
43					MM3Z43V	





ZENER DIODES – REGULATION IN SURFACE MOUNT (continued)

Surface Mount Packages – 225 mW

Nominal Zener Breakdown Voltage	Standard Tolerance SOT-23	Tight Tolerance SOT-23	Standard Tolerance SOT-23	Energy Rated SOT-23
Volts	 Case 318	 Case 318	 Case 318	 Case 318
2.4	BZX84C2V4L		MMBZ5221BL	
2.5			MMBZ5222BL	
2.7	BZX84C2V7L		MMBZ5223BL	
3.0	BZX84C3V0L		MMBZ5225BL	
3.3	BZX84C3V3L		MMBZ5226BL	
3.6	BZX84C3V6L		MMBZ5227BL	
3.9	BZX84C3V9L		MMBZ5228BL	
4.3	BZX84C4V3L		MMBZ5229BL	
4.7	BZX84C4V7L		MMBZ5230BL	
5.1	BZX84C5V1L	BZX84B5V1L	MMBZ5231BL	MMBZ5231EL
5.6	BZX84C5V6L	BZX84B5V6L	MMBZ5232BL	MMBZ5232EL
6.0			MMBZ5233BL	
6.2	BZX84C6V2L	BZX84B6V2L	MMBZ5234BL	MMBZ5234EL
6.8	BZX84C6V8L	BZX84B6V8L	MMBZ5235BL	
7.5	BZX84C7V5L	BZX84B7V5L	MMBZ5236BL	
8.2	BZX84C8V2L	BZX84B8V2L	MMBZ5237BL	MMBZ5237EL
8.7			MMBZ5238BL	
9.1	BZX84C9V1L	BZX84B9V1L	MMBZ5239BL	MMBZ5239EL
10	BZX84C10L		MMBZ5240BL	MMBZ5240EL
11	BZX84C11L		MMBZ5241BL	
12	BZX84C12L	BZX84B12L	MMBZ5242BL	MMBZ5242EL
13	BZX84C13L		MMBZ5243BL	MMBZ5243EL
14			MMBZ5244BL	
15	BZX84C15L	BZX84B15L	MMBZ5245BL	MMBZ5245EL
16	BZX84C16L	BZX84B16L	MMBZ5246BL	MMBZ5246EL
17			MMBZ5247BL	
18	BZX84C18L	BZX84B18L	MMBZ5248BL	MMBZ5248EL
19			MMBZ5249BL	
20	BZX84C20L		MMBZ5250BL	MMBZ5250EL
22	BZX84C22L	BZX84B22L	MMBZ5251BL	
24	BZX84C24L	BZX84B24L	MMBZ5252BL	MMBZ5252EL
25			MMBZ5253BL	MMBZ5253EL
27	BZX84C27L		MMBZ5254BL	
28			MMBZ5255BL	
30	BZX84C30L		MMBZ5256BL	
33	BZX84C33L		MMBZ5257BL	MMBZ5257EL
36	BZX84C36L		MMBZ5258BL	
39	BZX84C39L		MMBZ5259BL	

ZENER DIODES – REGULATION IN SURFACE MOUNT (continued)

Surface Mount Packages – 225 mW

Nominal Zener Breakdown Voltage	Standard Tolerance SOT-23	Tight Tolerance SOT-23	Standard Tolerance SOT-23	Energy Rated SOT-23
Volts	 Case 318	 Case 318	 Case 318	 Case 318
43	BZX84C43L		MMBZ5260BL	
47	BZX84C47L		MMBZ5261BL	MMBZ5261EL
51	BZX84C51L			
56	BZX84C56L		MMBZ5263BL	
60			MMBZ5264BL	
62	BZX84C62L			
68	BZX84C68L			
75	BZX84C75L			
82			MMBZ5268BL	
91			MMBZ5270BL	

ZENER DIODES – REGULATION IN SURFACE MOUNT (continued)

Surface Mount Packages – 500 mW

Nominal Zener Breakdown Voltage	Standard Tolerance SOD-123	Standard Tolerance SOD-123	Standard Tolerance SOD-123	Energy Rated SOD-123
Volts	 Case 425	 Case 425	 Case 425	 Case 425
1.8		MMSZ4678		
2.0		MMSZ4679		
2.2		MMSZ4680		
2.4	MMSZ2V4	MMSZ4681	MMSZ5221B	MMSZ5221E
2.5			MMSZ5222B	
2.7	MMSZ2V7	MMSZ4682	MMSZ5223B	MMSZ5223E
3.0	MMSZ3V0	MMSZ4683	MMSZ5225B	
3.3	MMSZ3V3	MMSZ4684	MMSZ5226B	MMSZ5226E
3.6	MMSZ3V6	MMSZ4685	MMSZ5227B	
3.9	MMSZ3V9	MMSZ4686	MMSZ5228B	
4.3	MMSZ4V3	MMSZ4687	MMSZ5229B	
4.7	MMSZ4V7	MMSZ4688	MMSZ5230B	
5.1	MMSZ5V1	MMSZ4689	MMSZ5231B	
5.6	MMSZ5V6	MMSZ4690	MMSZ5232B	
6.0			MMSZ5233B	
6.2	MMSZ6V2	MMSZ4691	MMSZ5234B	
6.8	MMSZ6V8	MMSZ4692	MMSZ5235B	MMSZ5235E
7.5	MMSZ7V5	MMSZ4693	MMSZ5236B	
8.2	MMSZ8V2	MMSZ4694	MMSZ5237B	MMSZ5237E
8.7			MMSZ5238B	
9.1	MMSZ9V1	MMSZ4696	MMSZ5239B	
10	MMSZ10	MMSZ4697	MMSZ5240B	MMSZ5240E
11	MMSZ11	MMSZ4698	MMSZ5241B	
12	MMSZ12	MMSZ4699	MMSZ5242B	MMSZ5242E
13	MMSZ13	MMSZ4700	MMSZ5243B	
14		MMSZ4701	MMSZ5244B	MMSZ5244E
15	MMSZ15	MMSZ4702	MMSZ5245B	MMSZ5245E
16	MMSZ16	MMSZ4703	MMSZ5246B	MMSZ5246E
17		MMSZ4704	MMSZ5247B	
18	MMSZ18	MMSZ4705	MMSZ5248B	MMSZ5248E
19		MMSZ4706	MMSZ5249B	
20	MMSZ20	MMSZ4707	MMSZ5250B	MMSZ5250E
22	MMSZ22	MMSZ4708	MMSZ5251B	MMSZ5251E
24	MMSZ24	MMSZ4709	MMSZ5252B	MMSZ5252E
25		MMSZ4710	MMSZ5253B	

ZENER DIODES – REGULATION IN SURFACE MOUNT (continued)

Surface Mount Packages – 500 mW (continued)

Nominal Zener Breakdown Voltage	Standard Tolerance SOD-123	Standard Tolerance SOD-123	Standard Tolerance SOD-123	Energy Rated SOD-123
Volts	 Case 425	 Case 425	 Case 425	 Case 425
27	MMSZ27	MMSZ4711	MMSZ5254B	MMSZ5254E
28	MMSZ30		MMSZ5255B	
30		MMSZ4713	MMSZ5256B	MMSZ5256E
33	MMSZ33	MMSZ4714	MMSZ5257B	MMSZ5257E
36	MMSZ36	MMSZ4715	MMSZ5258B	
39	MMSZ39		MMSZ5259B	MMSZ5259E
43	MMSZ43	MMSZ4717	MMSZ5260B	
47	MMSZ47		MMSZ5261B	
51	MMSZ51		MMSZ5262B	
56	MMSZ56		MMSZ5263B	
60			MMSZ5264B	
62			MMSZ5265B	
68			MMSZ5266B	
75			MMSZ5267B	
82			MMSZ5268B	
87				
91			MMSZ5270B	
100				
110			MMSZ5272B	

ZENER DIODES – REGULATION IN SURFACE MOUNT (continued)

Surface Mount Packages – 1.5, 3 W

Nominal Zener Breakdown Voltage	1.5 Watt SMA	3 Watt SMB
Volts	 Plastic Case 403B Cathode = Notch	 Plastic Case 403A
3.3	1SMA5913B	1SMB5913B
3.6	1SMA5914B	1SMB5914B
3.9	1SMA5915B	1SMB5915B
4.3	1SMA5916B	1SMB5916B
4.7	1SMA5917B	1SMB5917B
5.1	1SMA5918B	1SMB5918B
5.6	1SMA5919B	1SMB5919B
6.2	1SMA5920B	1SMB5920B
6.8	1SMA5921B	1SMB5921B
7.5	1SMA5922B	1SMB5922B
8.2	1SMA5923B	1SMB5923B
9.1	1SMA5924B	1SMB5924B
10	1SMA5925B	1SMB5925B
11		1SMB5926B
12	1SMA5927B	1SMB5927B
13	1SMA5928B	1SMB5928B
15	1SMA5929B	1SMB5929B
16	1SMA5930B	1SMB5930B
18	1SMA5931B	1SMB5931B
20	1SMA5932B	1SMB5932B
22	1SMA5933B	1SMB5933B
24	1SMA5934B	1SMB5934B
27	1SMA5935B	1SMB5935B
30	1SMA5936B	1SMB5936B
33	1SMA5937B	1SMB5937B
36	1SMA5938B	1SMB5938B
39	1SMA5939B	1SMB5939B
43	1SMA5940B	1SMB5940B
47	1SMA5941B	1SMB5941B
51	1SMA5942B	1SMB5942B
56	1SMA5943B	1SMB5943B
62		1SMB5944B
68	1SMA5945B	1SMB5945B
75		1SMB5946B

ZENER DIODES – REGULATION IN SURFACE MOUNT (continued)

Surface Mount Packages – 1.5, 3 W (continued)

Nominal Zener Breakdown Voltage	1.5 Watt	3 Watt
	SMA	SMB
Volts	 Plastic Case 403B Cathode = Notch	 Plastic Case 403A
82		1SMB5947B
91		1SMB5948B
100		1SMB5949B
120		1SMB5951B
130		1SMB5952B
150		1SMB5953B
160		1SMB5954B
180		1SMB5955B
200		1SMB5956B



DUAL ZENERS – DUALS IN SURFACE MOUNT

MMBZ15VDLT1 – Common Cathode Series

SOT-23 Dual Common Cathode Zener; 40 W Peak Power (10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Bidirectional (Circuit tied to Pins 1 and 2)

Device	Breakdown Voltage			Reverse Voltage Working Peak V _{RWM} (V)	Reverse Leakage Current I _R (nA)	Reverse Surge Current I _{PP} (A)	Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Temperature Coefficient of V _{BR} (mV/°C)	
	V _{BR} (Note 1) (V)								
	Min	Nom	Max						
 <p style="text-align: center;">CASE 318-08 TO-236AB LOW PROFILE SOT-23</p> 									
MMBZ15VDL	14.3	15	15.8	1.0	12.8	100	1.9	21.2	12
MMBZ27VCL	25.65	27	28.35	1.0	22	50	1.0	38	26

1. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

DUAL ZENERS – SURFACE MOUNT (continued)


MMBZ5V6ALT1 – Common Anode Series

SOT-23 Dual Common Anode Zener; 24 W Peak Power (10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Unidirectional (Circuit tied to Pins 1 and 3 or Pins 2 and 3)

(V_F = 0.9 V Max @ I_F = 10 mA)

Device	Breakdown Voltage			@ I _T (mA)	Max Reverse Leakage Current		Max Zener Impedance (Note 3)			Max Reverse Surge Current I _{PP} (A)	Max Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Max Temp Coefficient of V _{BR} (mV/°C)
	V _{BR} (Note 2) (V)				I _R @ V _R (μA) (V)	Z _{ZT} @ I _{ZT} (Ω) (mA)	Z _{ZK} @ I _{ZK} (Ω) (mA)					
	Min	Nom	Max									
 <p style="text-align: center;">CASE 318-08 STYLE 12 LOW PROFILE SOT-23 PLASTIC</p> 												
MMBZ5V6AL	5.32	5.6	5.88	20	5.0	3.0	11	1600	0.25	3.0	8.0	1.26
MMBZ6V2AL	5.89	6.2	6.51	1.0	0.5	3.0	–	–	–	2.76	8.7	2.80
MMBZ6V8AL	6.46	6.8	7.14	1.0	0.5	4.5	–	–	–	2.5	9.6	3.40
MMBZ9V1AL	8.65	9.1	9.56	1.0	0.3	6.0	–	–	–	1.7	14	7.50

2. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

3. Z_{ZT} and Z_{ZK} are measured by dividing the AC voltage drop across the device by the AC current supplied. The specified limits are I_{Z(AC)} = 0.1 I_{Z(DC)}, with AC frequency = 1 kHz.



MMBZ5V6ALT1 – Common Anode Series

SOT-23 Dual Common Anode Zener; 40 W Peak Power (10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Unidirectional (Circuit tied to Pins 1 and 3 or Pins 2 and 3)

(V_F = 0.9 V Max @ I_F = 10 mA)

Device	Breakdown Voltage			@ I _T (mA)	Reverse Voltage Working Peak V _{RWM} (V)	Max Reverse Leakage Current I _R (nA)	Max Reverse Surge Current I _{PP} (A)	Max Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Maximum Temperature Coefficient of V _{BR} (mV/°C)
	V _{BR} (Note 4) (V)								
	Min	Nom	Max						
 <p style="text-align: center;">CASE 318-08 STYLE 12 LOW PROFILE SOT-23 PLASTIC</p> 									
MMBZ12VAL	11.40	12	12.60	1.0	8.5	200	2.35	17	7.50
MMBZ15VAL	14.25	15	15.75	1.0	12.0	50	1.9	21	12.30
MMBZ18VAL	17.10	18	18.90	1.0	14.5	50	1.6	25	15.30
MMBZ20VAL	19.00	20	21.00	1.0	17.0	50	1.4	28	17.20
MMBZ27VAL	25.65	27	28.35	1.0	22.0	50	1.0	40	24.30
MMBZ33VAL	31.35	33	34.65	1.0	26.0	50	0.87	46	30.40

4. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.


DUAL ZENERS – SURFACE MOUNT (continued)

MMBZ27VCW – Common Cathode Series

SC-70 Dual Common Cathode Zener; 40 W Peak Power (10 x 1000 μs)

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Bidirectional (Circuit tied to Pins 1 and 2)

Device	Breakdown Voltage				Reverse Voltage Working Peak V_{RWM} (V)	Reverse Leakage Current I_R (nA)	Reverse Surge Current I_{PP} (A)	Reverse Voltage @ I_{PP} (Clamping Voltage) V_C (V)	Temperature Coefficient of V_{BR} (mV/°C)
	V_{BR} (Note 1) (V)			@ I_T (mA)					
	Min	Nom	Max						
 CASE 419-04 SC-70 									
MMBZ27VCL	25.65	27	28.35	1.0	22	50	1.0	38	26

1. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

MMBZ27VAW – Common Anode Series

SC-70 Dual Common Anode Zener; 40 W Peak Power (10 x 1000 μs)

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Bidirectional (Circuit Tied to Pins 1 and 2)

Device	Breakdown Voltage				Reverse Leakage Current I_R @ V_R (μA) (V)	Reverse Surge Current I_{PP} (A)	Reverse Voltage @ I_{PP} (Clamping Voltage) V_C (V)	Temp Coefficient of V_{BR} (mV/°C)	
	V_{BR} (Note 2) (V)			@ I_T (mA)					
	Min	Nom	Max						
 CASE 419-04 SC-70 									
MMBZ27VAW	25.65	27	28.35	1.0	50	22	1.0	40	24.3


2. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

TVS – IN AXIAL LEADS

Peak Power Dissipation, 500 W @ 1 ms Surge (10 x 1000 μs) Case 59 (MiniMOSORB™)



CASE 59 (MiniMOSORB™)
PLASTIC
Cathode = Polarity Band



Surge Current Characteristics


ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted) $V_F = 3.5\text{ V Max}$, $I_F = 35\text{ A Pulse}$

Working Peak Reverse Voltage V_{RWM} (V) (Note 1)	Device	Breakdown Voltage			Maximum Reverse Leakage @ V_{RWM} I_R (μA)	Maximum Reverse Surge Current I_{RSM} (A) (Note 3)	Maximum Reverse Voltage @ I_{RSM} (Clamping Voltage) V_{RSM} (V)
		V_{BR} (V)		@ I_T Pulse (mA)			
		Min (Note 2)	Max				
5	SA5.0A	6.4	7	10	600	54.3	9.2
6	SA6.0A	6.67	7.37	10	600	48.5	10.3
7	SA7.0A	7.78	8.6	10	150	41.7	12
10	SA10A	11.1	12.3	1	1	29.4	17
12	SA12A	13.3	14.7	1	1	25.1	19.9
13	SA13A	14.4	15.9	1	1	23.2	21.5
15	SA15A	16.7	18.5	1	1	20.6	24.4
16	SA16A	17.8	19.7	1	1	19.2	26
17	SA17A	18.9	20.9	1	1	18.1	27.6
18	SA18A	20	22.1	1	1	17.2	29.2
20	SA20A	22.2	24.5	1	1	15.4	32.4
24	SA24A	26.7	29.5	1	1	12.8	38.9
26	SA26A	28.9	31.9	1	1	11.9	42.1
28	SA28A	31.1	34.4	1	1	11	45.4
30	SA30A	33.3	36.8	1	1	10.3	48.4
33	SA33A	36.7	40.6	1	1	9.4	53.3
36	SA36A	40	44.2	1	1	8.6	58.1


1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C .
3. 10 x 1000 μs exponential decay surge waveform.

TVS – IN AXIAL LEADS (continued)

Peak Power Dissipation, 600 W @ 1 ms Surge (10 x 1000 μs) Case 17 – SURMETIC® 40 (continued)



**CASE 17
PLASTIC**
Cathode = Polarity Band





ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted) $V_F = 3.5\text{ V Max}$, $I_F = 50\text{ A Pulse}$ (except bidirectional devices).

Breakdown Voltage (Note 2)		Device	Working Peak Reverse Voltage V_{RWM} (V) (Note 1)	Maximum Reverse Leakage @ V_{RWM} I_R (μA)	Maximum Reverse Surge Current I_{RSM} (A) (Note 3)	Maximum Reverse Voltage @ I_{RSM} (Clamping Voltage) V_{RSM} (V)
V_{BR} (V)	@ I_T Pulse (mA)					
Nom						
6.8	10	P6KE6.8A	5.8	1000	57	10.5
7.5	10	P6KE7.5A	6.4	500	53	11.3
10	1	P6KE10A	8.55	10	41	14.5
12	1	P6KE12A	10.2	5	36	16.7
13	1	P6KE13A	11.1	5	33	18.2
15	1	P6KE15A	12.8	5	28	21.2
16	1	P6KE16A	13.6	5	27	22.5
18	1	P6KE18A	15.3	5	24	25.2
20	1	P6KE20A	17.1	5	22	27.7
22	1	P6KE22A	18.8	5	20	30.6
24	1	P6KE24A	20.5	5	18	33.2
27	1	P6KE27A	23.1	5	16	37.5
30	1	P6KE30A	25.6	5	14.4	41.4
33	1	P6KE33A	28.2	5	13.2	45.7
36	1	P6KE36A	30.8	5	12	49.9
39	1	P6KE39A	33.3	5	11.2	53.9
43	1	P6KE43A	36.8	5	10.1	59.3
47	1	P6KE47A	40.2	5	9.3	64.8
51	1	P6KE51A	43.6	5	8.6	70.1
56	1	P6KE56A	47.8	5	7.8	77
62	1	P6KE62A	53	5	7.1	85
68	1	P6KE68A	58.1	5	6.5	92
75	1	P6KE75A	64.1	5	5.8	103
82	1	P6KE82A	70.1	5	5.3	113
100	1	P6KE100A	85.5	5	4.4	137
150	1	P6KE150A	128	5	2.9	207
160	1	P6KE160A	136	5	2.7	219
180	1	P6KE180A	154	5	2.4	246
200	1	P6KE200A	171	5	2.2	274

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C .
3. $10 \times 1000\ \mu\text{s}$ exponential decay surge waveform.

TVS – IN AXIAL LEADS (continued)

Peak Power Dissipation, 1500 W @ 1 ms Surge (10 x 1000 μs) Case 41A – MOSORB



ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted) $V_F = 3.5\text{ V Max}$, $I_F = 100\text{ A Pulse}$


Breakdown Voltage (Note 2)		JEDEC Device	Device	Working Peak Reverse Voltage V_{RWM} (V) (Note 1)	Maximum Reverse Leakage @ V_{RWM} I_R (μA)	Maximum Reverse Surge Current I_{RSM} (A) (Note 3)	Maximum Reverse Voltage @ I_{RSM} (Clamping Voltage) V_{RSM} (V)
V_{BR} V	@ I_T Pulse (mA)						
Nom							
6.8	10	1N6267A	1.5KE6.8A	5.8	1000	143	10.5
7.5	10		1.5KE7.5A	6.4	500	132	11.3
8.2	10		1.5KE8.2A	7.02	200	124	12.1
10	1	1N6271A	1.5KE10A	8.55	10	103	14.5
11	1		1.5KE11A	9.4	5	96	15.6
12	1		1.5KE12A	10.2	5	90	16.7
13	1	1N6274A	1.5KE13A	11.1	5	82	18.2
15	1	1N6275A	1.5KE15A	12.8	5	71	21.2
16	1	1N6276A	1.5KE16A	13.6	5	67	22.5
18	1	1N6277A	1.5KE18A	15.3	5	59.5	25.2
20	1	1N6278A	1.5KE20A	17.1	5	54	27.7
22	1	1N6279A		18.8	5	49	30.6
24	1	1N6280A	1.5KE24A	20.5	5	45	33.2
27	1	1N6281A	1.5KE27A	23.1	5	40	37.5
30	1	1N6282A	1.5KE30A	25.6	5	36	41.4
33	1	1N6283A	1.5KE33A	28.2	5	33	45.7
36	1	1N6284A	1.5KE36A	30.8	5	30	49.9
39	1	1N6285A	1.5KE39A	33.3	5	28	53.9
43	1	1N6286A	1.5KE43A	36.8	5	25.3	59.3
47	1	1N6287A	1.5KE47A	40.2	5	23.2	64.8
51	1	1N6288A	1.5KE51A	43.6	5	21.4	70.1
56	1	1N6289A	1.5KE56A	47.8	5	19.5	77
62	1	1N6290A	1.5KE62A	53	5	17.7	85
68	1	1N6291A	1.5KE68A	58.1	5	16.3	92
75	1	1N6292A	1.5KE75A	64.1	5	14.6	103
82	1		1.5KE82A	70.1	5	13.3	113
91	1	1N6294A	1.5KE91A	77.8	5	12	125
100	1	1N6295A		85.5	5	11	137

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C .
3. $10 \times 1000\ \mu\text{s}$ exponential decay surge waveform.

TVS – IN SURFACE MOUNT

1PMT Series Unidirectional Overvoltage Transient Suppressors, 200 W Peak Power @ 1 ms Surge
(10 x 1000 μs)

ELECTRICAL CHARACTERISTICS ($T_L = 30^\circ\text{C}$ unless otherwise noted) ($V_F = 1.25\text{ V @ }200\text{ mA}$)


Device	Marking	V_{RWM} (V)	V_{BR} @ I_T (V) (Note 2)			I_T	I_R @ V_{RWM}	V_C @ I_{PP}	I_{PP} (A)
		(Note 1)	Min	Nom	Max	(mA)	(μA)	(V)	(Note 3)
 <p>POWERMITE® CASE 457 PLASTIC</p>		 <p>Surge Current Characteristics</p>							
1PMT5.0A	MKE	5.0	6.4	6.7	7.0	10	800	9.2	19
1PMT7.0A	MKM	7.0	7.78	8.2	8.6	10	500	12	14.6
1PMT12A	MLE	12	13.3	14	14.7	1.0	5.0	19.9	8.8
1PMT16A	MLP	16	17.8	18.75	19.7	1.0	5.0	26	7.0
1PMT22A	MLX	22	24.4	25.6	26.9	1.0	5.0	35.5	4.9
1PMT26A	MME	26	28.9	30.4	31.9	1.0	5.0	42.1	4.2
1PMT33A	MMM	33	36.7	38.7	40.6	1.0	5.0	53.3	3.3

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C .
3. 10 x 1000 μs exponential decay surge waveform.

TVS – IN SURFACE MOUNT (continued)

SMF Series Unidirectional Overvoltage Transient Suppressors, 200 W Peak Power @ 1 ms Surge
(10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_L = 30°C unless otherwise noted) (V_F = 1.25 V @ 200 mA)


Device	Marking	V _{RWM} (V)	V _{BR} @ I _T (V) (Note 2)			I _T	I _R @ V _{RWM}	V _C @ I _{PP}	I _{PP} (A)
		(Note 1)	Min	Nom	Max	(mA)	(μA)	(V)	(Note 3)
 <p>SOD-123FL CASE 498 PLASTIC</p>		 <p>Surge Current Characteristics</p>							
SMF5.0A	KE	5.0	6.4	6.7	7.0	10	400	9.2	16.3
SMF6.0A	KG	6.0	6.67	7.02	7.37	10	400	10.3	14.6
SMF7.0A	KM	7.0	7.78	8.2	8.6	10	100	12	12.5
SMF7.5A	KP	7.5	8.33	8.77	9.21	1.0	50	12.9	11.6
SMF8.0A	KR	8.0	8.89	9.36	9.83	1.0	25	13.6	11
SMF9.0A	KV	9.0	10	10.55	11.1	1.0	5.0	15.4	9.7
SMF10A	KX	10	11.1	11.7	12.3	1.0	2.5	17	8.8
SMF11A	KZ	11	12.2	12.85	13.5	1.0	2.5	18.2	8.2
SMF12A	LE	12	13.3	14	14.7	1.0	2.5	19.9	7.5
SMF13A	LG	13	14.4	15.15	15.9	1.0	1.0	21.5	7.0
SMF14A	LK	14	15.6	16.4	17.2	1.0	1.0	23.2	6.5
SMF15A	LM	15	16.7	17.6	18.5	1.0	1.0	24.4	6.1
SMF18A	LT	18	20	21	22.1	1.0	1.0	29.2	5.1
SMF20A	LV	20	22.2	23.35	24.5	1.0	1.0	32.4	4.6
SMF22A	LX	22	24.4	25.6	26.9	1.0	1.0	35.5	4.2
SMF24A	LZ	24	26.7	28.1	29.5	1.0	1.0	38.9	3.9
SMF26A	ME	26	28.9	30.4	31.9	1.0	1.0	42.1	3.6
SMF28A	MG	28	31.1	32.8	34.4	1.0	1.0	45.4	3.3
SMF30A	MK	30	33.3	35.1	36.8	1.0	1.0	48.4	3.1
SMF33A	MM	33	36.7	38.7	40.6	1.0	1.0	53.3	2.8
SMF36A	MP	36	40	42.1	44.2	1.0	1.0	58.1	2.6

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C.
3. 10 x 1000 μs exponential decay surge waveform. TVS – in Surface Mount (continued)

TVS – IN SURFACE MOUNT (continued)

1SMA Series Unidirectional Overvoltage Transient Suppressors; 400 W Peak Power @ 1 ms Surge
(10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted) (V_F = 3.5 Volts @ I_F = 40 A for all types) (Note 4)


Device	Working Peak Reverse Voltage V _{RWM} (V) (Note 1)	Breakdown Voltage		Maximum Reverse Voltage @ I _{RSM} (Clamping Voltage) V _C (V)	Maximum Reverse Surge Current I _{PP} (A) (Note 3)	Maximum Reverse Leakage @ V _{RWM} I _R (μA)	Device Marking
		V _{BR} (V) (Min) (Note 2)	I _T mA				
 <p>SMA CASE 403B PLASTIC</p>  <p>Surge Current Characteristics</p>							
1SMA5.0A	5.0	6.4	10	9.2	43.5	400	QE
1SMA6.0A	6.0	6.67	10	10.3	38.8	400	QG
1SMA6.5A	6.5	7.22	10	11.2	35.7	250	QK
1SMA8.0A	8.0	8.89	1	13.6	29.4	25	QR
1SMA8.5A	8.5	9.44	1	14.4	27.8	5.0	QT
1SMA9.0A	9.0	10	1	15.4	26.0	2.5	QV
1SMA10A	10	11.1	1	17.0	23.5	2.5	QX
1SMA11A	11	12.2	1	18.2	22.0	2.5	QZ
1SMA12A	12	13.3	1	19.9	20.1	2.5	RE
1SMA13A	13	14.4	1	21.5	18.6	2.5	RG
1SMA15A	15	16.7	1	24.4	16.4	2.5	RM
1SMA16A	16	17.8	1	26.0	15.4	2.5	RP
1SMA17A	17	18.9	1	27.6	14.5	2.5	RR
1SMA18A	18	20	1	29.2	13.7	2.5	RT
1SMA20A	20	22.2	1	32.4	12.3	2.5	RV
1SMA22A	22	24.4	1	35.5	11.3	2.5	RX
1SMA24A	24	26.7	1	38.9	10.3	2.5	RZ
1SMA26A	26	28.9	1	42.1	9.5	2.5	SE
1SMA28A	28	31.1	1	45.4	8.8	2.5	SG
1SMA30A	30	33.3	1	48.4	8.3	2.5	SK
1SMA33A	33	36.7	1	53.3	7.5	2.5	SM
1SMA36A	36	40	1	58.1	6.9	2.5	SP
1SMA40A	40	44.4	1	64.5	6.2	2.5	SR
1SMA43A	43	47.8	1	69.4	5.8	2.5	ST
1SMA45A	45	50	1	72.2	5.5	2.5	SV
1SMA48A	48	53.3	1	77.4	5.2	2.5	SX
1SMA54A	54	60	1	87.1	4.6	2.5	TE
1SMA58A	58	64.4	1	93.6	4.8	2.5	TG
1SMA70A	70	77.8	1	113.0	3.5	2.5	TP

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C.
3. 10 x 1000 μs exponential decay surge waveform.
4. 1/2 sine wave (or equivalent square pulse, PW = 8.3 ms, duty cycle = 4 pulses per minute).

TVS – IN SURFACE MOUNT (continued)

1SMA Series Bidirectional Zener Overvoltage Transient Suppressors; 400 W Peak Power @ 1 ms Surge (10 x 1000 μs)


ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Device	Working Peak Reverse Voltage V _{RWM} (V) (Note 1)	Breakdown Voltage		Maximum Reverse Voltage @ I _{RSM} (Clamping Voltage) V _C (V)	Maximum Reverse Surge Current I _{PP} (A) (Note 3)	Maximum Reverse Leakage @ V _{RWM} I _R (μA)	Device Marking
		V _{BR} (V) (Min) (Note 2)	I _T mA				
 <p style="text-align: center;">SMA CASE 403B PLASTIC</p> <div style="float: right;">  <p style="text-align: center;">Surge Current Characteristics</p> </div>							
1SMA10CA	10	11.1	1	17.0	23.5	2.5	QXC
1SMA12CA	12	13.3	1	19.9	20.1 ¹	2.5	REC
1SMA13CA	13	14.4	1	21.5	18.6	2.5	RGC
1SMA15CA	15	16.7	1	24.4	16.4	2.5	RMC
1SMA16CA	16	17.8	1	26.0	15.4	2.5	RPC
1SMA18CA	18	20	1	29.2	13.7	2.5	RTC
1SMA20CA	20	22.2	1	32.4	12.3	2.5	RVC
1SMA24CA	24	26.7	1	38.9	10.3	2.5	RZC
1SMA26CA	26	28.9	1	42.1	9.5	2.5	SEC
1SMA28CA	28	31.1	1	45.4	8.8	2.5	SGC
1SMA30CA	30	33.3	1	48.4	8.3	2.5	SKC
1SMA33CA	33	36.7	1	53.3	7.5	2.5	SMC
1SMA36CA	36	40	1	58.1	6.9	2.5	SPC
1SMA40CA	40	44.4	1	64.5	6.2	2.5	SRC
1SMA48CA	48	53.3	1	77.4	5.2	2.5	SXC
1SMA58CA	58	64.4	1	93.6	4.3	2.5	TGC
1SMA60CA	60	66.7	1	96.8	4.1	2.5	TKC
1SMA70CA	70	77.8	1	113.0	3.5	2.5	TPC
1SMA78CA	78	86.7	1	126.0	3.2	2.5	TSC

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C.
3. 10 x 1000 μs exponential decay surge waveform.

TVS – IN SURFACE MOUNT (continued)

1SMB Series Unidirectional Overvoltage Transient Suppressors; 600 W Peak Power @ 1 ms Surge
(10 x 1000 μ s)ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted) ($V_F = 3.5\text{ V Max @ } I_F = 30\text{ A}$) (Note 4)


Device	Working Peak Reverse Voltage V_{RWM} (Vo) (Note 1)	Breakdown Voltage		Maximum Clamping Voltage $V_C @ I_{pp}$ (V)	Peak Pulse Current I_{pp} (A) (Note 3)	Maximum Reverse Leakage @ V_R I_R (μ A)	Device Marking
		$V_{BR} @ I_T$ (V) (Min) (Note 2)	mA				
 <p>SMB CASE 403A PLASTIC</p>  <p>Surge Current Characteristics</p>							
1SMB5.0A	5.0	6.40	10	9.2	65.2	800	KE
1SMB6.0A	6.0	6.67	10	10.3	58.3	800	KG
1SMB6.5A	6.5	7.22	10	11.2	53.6	500	KK
1SMB7.0A	7.0	7.78	10	12.0	50.0	200	KM
1SMB7.5A	7.5	8.33	1.0	12.9	46.5	100	KP
1SMB8.0A	8.0	8.89	1.0	13.6	44.1	50	KR
1SMB8.5A	8.5	9.44	1.0	14.4	41.7	10	KT
1SMB9.0A	9.0	10.0	1.0	15.4	39.0	5.0	KV
1SMB10A	10	11.1	1.0	17.0	35.3	5.0	KX
1SMB11A	11	12.2	1.0	18.2	33.0	5.0	KZ
1SMB12A	12	13.3	1.0	19.9	30.2	5.0	LE
1SMB13A	13	14.4	1.0	21.5	27.9	5.0	LG
1SMB14A	14	15.6	1.0	23.2	25.8	5.0	LK
1SMB15A	15	16.7	1.0	24.4	24.0	5.0	LM
1SMB16A	16	17.8	1.0	26.0	23.1	5.0	LP
1SMB17A	17	18.9	1.0	27.6	21.7	5.0	LR
1SMB18A	18	20.0	1.0	29.2	20.5	5.0	LT
1SMB20A	20	22.2	1.0	32.4	18.5	5.0	LV
1SMB22A	22	24.4	1.0	35.5	16.9	5.0	LX
1SMB24A	24	26.7	1.0	38.9	15.4	5.0	LZ
1SMB26A	26	28.9	1.0	42.1	14.2	5.0	ME
1SMB28A	28	31.1	1.0	45.4	13.2	5.0	MG
1SMB30A	30	33.3	1.0	48.4	12.4	5.0	MK
1SMB33A	33	36.7	1.0	53.3	11.3	5.0	MM
1SMB36A	36	40.0	1.0	58.1	10.3	5.0	MP
1SMB40A	40	44.4	1.0	64.5	9.3	5.0	MR
1SMB43A	43	47.8	1.0	69.4	8.6	5.0	MT
1SMB45A	45	50.0	1.0	72.7	8.3	5.0	MV
1SMB48A	48	53.3	1.0	77.4	7.7	5.0	MX
1SMB51A	51	56.7	1.0	82.4	7.3	5.0	MZ
1SMB54A	54	60.0	1.0	87.1	6.9	5.0	NE
1SMB58A	58	64.4	1.0	93.6	6.4	5.0	NG
1SMB60A	60	66.7	1.0	96.8	6.2	5.0	NK
1SMB64A	64	71.1	1.0	103	5.8	5.0	NM
1SMB70A	70	77.8	1.0	113	5.3	5.0	NP
1SMB75A	75	83.3	1.0	121	4.9	5.0	NR
1SMB85A	85	94.4	1.0	137	4.4	5.0	NV
1SMB90A	90	100	1.0	146	4.1	5.0	NX
1SMB100A	100	111	1.0	162	3.7	5.0	NZ

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C .
3. $10 \times 1000\ \mu\text{s}$ exponential decay surge waveform.
4. 1/2 sine wave (or equivalent square pulse, $PW = 8.3\text{ ms}$, duty cycle = 4 pulses per minute).

TVS – IN SURFACE MOUNT (continued)

1SMB Series Unidirectional Overvoltage Transient Suppressors; 600 W Peak Power @ 1 ms Surge
(10 x 1000 μs) (continued)

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted) ($V_F = 3.5\text{ V Max @ } I_F = 30\text{ A}$) (Note 4)


Device	Working Peak Reverse Voltage V_{RWM} (V) (Note 1)	Breakdown Voltage		Maximum Clamping Voltage $V_C @ I_{pp}$ (V)	Peak Pulse Current I_{pp} (A) (Note 3)	Maximum Reverse Leakage @ V_R I_R (μA)	Device Marking
		$V_{BR} @ I_T$ (V) (Min) (Note 2)	mA				
 <p>SMB CASE 403A PLASTIC</p>  <p>Surge Current Characteristics</p>							
1SMB110A	110	122	1.0	177	3.4	5.0	PE
1SMB120A	120	133	1.0	193	3.1	5.0	PG
1SMB130A	130	144	1.0	209	2.9	5.0	PK
1SMB150A	150	167	1.0	243	2.5	5.0	PM
1SMB160A	160	178	1.0	259	2.3	5.0	PP
1SMB170A	170	189	1.0	275	2.2	5.0	PR

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C .
3. 10 x 1000 μs exponential decay surge waveform.
4. 1/2 sine wave (or equivalent square pulse, PW = 8.3 ms, duty cycle = 4 pulses per minute).

TVS – IN SURFACE MOUNT (continued)

1SMB Series Bidirectional Overvoltage Transient Suppressors; 600 W Peak Power @ 1 ms Surge
(10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted).


Device	Working Peak Reverse Voltage V _{RWM} (V) (Note 1)	Breakdown Voltage		Maximum Clamping Voltage V _C @ I _{pp} (V)	Peak Pulse Current I _{pp} (A) (Note 3)	Maximum Reverse Leakage @ V _R I _R (μA)	Device Marking
		V _{BR} @ I _T (V) (Min) (Note 2)	(mA)				
 <p>SMB CASE 403A PLASTIC</p>  <p>Surge Current Characteristics</p>							
1SMB10CA	10	11.1	1.0	17.0	35.3	5.0	KXC
1SMB11CA	11	12.2	1.0	18.2	33.0	5.0	KZC
1SMB12CA	12	13.3	1.0	19.9	30.2	5.0	LEC
1SMB13CA	13	14.4	1.0	21.5	27.9	5.0	LGC
1SMB14CA	14	15.6	1.0	23.2	25.8	5.0	LKC
1SMB15CA	15	16.7	1.0	24.4	24.0	5.0	LMC
1SMB16CA	16	17.8	1.0	26.0	23.1	5.0	LPC
1SMB17CA	17	18.9	1.0	27.6	21.7	5.0	LRC
1SMB18CA	18	20.0	1.0	29.2	20.5	5.0	LTC
1SMB20CA	20	22.2	1.0	32.4	18.5	5.0	LVC
1SMB22CA	22	24.4	1.0	35.5	16.9	5.0	LXC
1SMB24CA	24	26.7	1.0	38.9	15.4	5.0	LZC
1SMB26CA	26	28.9	1.0	42.1	14.2	5.0	MEC
1SMB28CA	28	31.1	1.0	45.4	13.2	5.0	MGC
1SMB30CA	30	33.3	1.0	48.4	12.4	5.0	MKC
1SMB33CA	33	36.7	1.0	53.3	11.3	5.0	MMC
1SMB36CA	36	40.0	1.0	58.1	10.3	5.0	MPC
1SMB40CA	40	44.4	1.0	64.5	9.3	5.0	MRC
1SMB43CA	43	47.8	1.0	69.4	8.6	5.0	MTC
1SMB45CA	45	50.0	1.0	72.7	8.3	5.0	MVC
1SMB48CA	48	53.3	1.0	77.4	7.7	5.0	MXC
1SMB51CA	51	56.7	1.0	82.4	7.3	5.0	MZC
1SMB54CA	54	60.0	1.0	87.1	6.9	5.0	NEC
1SMB58CA	58	64.4	1.0	93.6	6.4	5.0	NGC
1SMB60CA	60	66.7	1.0	96.8	6.2	5.0	NKC
1SMB64CA	64	71.1	1.0	103	5.8	5.0	NMC
1SMB75CA	75	83.3	1.0	121	4.9	5.0	NRC

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C.
3. 10 x 1000 μs exponential decay surge waveform.

TVS – IN SURFACE MOUNT (continued)

P6SMB Series Unidirectional Overvoltage Transient Suppressors; 600 W Peak Power @ 1 ms Surge
(10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted) (V_F = 3.5 V Max, I_F = 50 A for all types) (Note 4)


Device	Breakdown Voltage				Working Peak Reverse Voltage V _{RWM} (V) (Note 1)	Maximum Reverse Leakage @ V _{RWM} I _R (μA)	Maximum Reverse Surge Current I _{PP} (A) (Note 3)	Maximum Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Temperature Coefficient of V _{BR} %/°C	Device Marking
	V _{BR} @ I _T (V) (Note 2)									
	Min	Nom	Max	(mA)						
 SMB CASE 403A PLASTIC										
										
P6SMB6.8A	6.45	6.8	7.14	10	5.8	1000	57	10.5	0.057	6V8A
P6SMB7.5A	7.13	7.5	7.88	10	6.4	500	53	11.3	0.061	7V5A
P6SMB8.2A	7.79	8.2	8.61	10	7.02	200	50	12.1	0.065	8V2A
P6SMB9.1A	8.65	9.1	9.55	1	7.78	50	45	13.4	0.068	9V1A
P6SMB10A	9.5	10	10.5	1	8.55	10	41	14.5	0.073	10A
P6SMB12A	11.4	12	12.6	1	10.2	5	36	16.7	0.078	12A
P6SMB13A	12.4	13	13.7	1	11.1	5	33	18.2	0.081	13A
P6SMB15A	14.3	15	15.8	1	12.8	5	28	21.2	0.084	15A
P6SMB16A	15.2	16	16.8	1	13.6	5	27	22.5	0.086	16A
P6SMB18A	17.1	18	18.9	1	15.3	5	24	25.2	0.088	18A
P6SMB20A	19	20	21	1	17.1	5	22	27.7	0.09	20A
P6SMB22A	20.9	22	23.1	1	18.8	5	20	30.6	0.092	22A
P6SMB24A	22.8	24	25.2	1	20.5	5	18	33.2	0.094	24A
P6SMB27A	25.7	27	28.4	1	23.1	5	16	37.5	0.096	27A
P6SMB30A	28.5	30	31.5	1	25.6	5	14.4	41.4	0.097	30A
P6SMB33A	31.4	33	34.7	1	28.2	5	13.2	45.7	0.098	33A
P6SMB36A	34.2	36	37.8	1	30.8	5	12	49.9	0.099	36A
P6SMB39A	37.1	39	41	1	33.3	5	11.2	53.9	0.1	39A
P6SMB43A	40.9	43	45.2	1	36.8	5	10.1	59.3	0.101	43A
P6SMB47A	44.7	47	49.4	1	40.2	5	9.3	64.8	0.101	47A
P6SMB51A	48.5	51	53.6	1	43.6	5	8.6	70.1	0.102	51A
P6SMB56A	53.2	56	58.8	1	47.8	5	7.8	77	0.103	56A
P6SMB62A	58.9	62	65.1	1	53	5	7.1	85	0.104	62A
P6SMB68A	64.6	68	71.4	1	58.1	5	6.5	92	0.104	68A
P6SMB75A	71.3	75	78.8	1	64.1	5	5.8	103	0.105	75A
P6SMB82A	77.9	82	86.1	1	70.1	5	5.3	113	0.105	82A
P6SMB91A	86.5	91	95.5	1	77.8	5	4.8	125	0.106	91A
P6SMB100A	95	100	105	1	85.5	5	4.4	137	0.106	100A
P6SMB120A	114	120	126	1	102	5	3.6	165	0.107	120A
P6SMB130A	124	130	137	1	111	5	3.3	179	0.107	130A
P6SMB150A	143	150	158	1	128	5	2.9	207	0.108	150A
P6SMB160A	152	160	168	1	136	5	2.7	219	0.108	160A
P6SMB180A	171	180	189	1	154	5	2.4	246	0.108	180A
P6SMB200A	190	200	210	1	171	5	2.2	274	0.108	200A

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C.
3. 10 x 1000 μs exponential decay surge waveform.
4. 1/2 sine wave (or equivalent square pulse, PW = 8.3 ms, duty cycle = 4 pulses per minute).

TVS – IN SURFACE MOUNT (continued)

P6SMB Series Bidirectional Overvoltage Transient Suppressors; 600 W Peak Power @ 1 ms Surge
(10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)


Device	Breakdown Voltage				Working Peak Reverse Voltage V _{RWM} Volts (Note 1)	Maximum Reverse Leakage I _R @ V _{RWM} μA	Maximum Reverse Surge Current I _{PP} Amps (Note 3)	Maximum Reverse Voltage @ I _{PP} (Clamping Voltage) V _C Volts	Temperature Coefficient of V _{BR} %/°C	Device Marking
	V _{BR} @ I _T Volts (Note 2)									
	Min	Nom	Max	mA						
 <p>SMB CASE 403A PLASTIC</p>  <p>Surge Current Characteristics</p>										
P6SMB11CA P6SMB12CA	10.5 11.4	11 12	11.6 12.6	1 1	9.4 10.2	5 5	38 36	15.6 16.7	0.075 0.078	11C 12C
P6SMB15CA P6SMB16CA P6SMB18CA P6SMB20CA	14.3 15.2 17.1 19	15 16 18 20	15.8 16.8 18.9 21	1 1 1 1	12.8 13.6 15.3 17.1	5 5 5 5	28 27 24 22	21.2 22.5 25.2 27.7	0.084 0.086 0.088 0.09	15C 16C 18C 20C
P6SMB22CA P6SMB24CA P6SMB27CA P6SMB30CA	20.9 22.8 25.7 28.5	22 24 27 30	23.1 25.2 28.4 31.5	1 1 1 1	18.8 20.5 23.1 25.6	5 5 5 5	20 18 16 14.4	30.6 33.2 37.5 41.4	0.092 0.094 0.096 0.097	22C 24C 27C 30C
P6SMB33CA P6SMB36CA P6SMB39CA P6SMB43CA	31.4 34.2 37.1 40.9	33 36 39 43	34.7 37.8 41 45.2	1 1 1 1	28.2 30.8 33.3 36.8	5 5 5 5	13.2 12 11.2 10.1	45.7 49.9 53.9 59.3	0.098 0.099 0.1 0.101	33C 36C 39C 43C
P6SMB47CA P6SMB51CA P6SMB56CA P6SMB62CA	44.7 48.5 53.2 58.9	47 51 56 62	49.4 53.6 58.8 65.1	1 1 1 1	40.2 43.6 47.8 53	5 5 5 5	9.3 8.6 7.8 7.1	64.8 70.1 77 85	0.101 0.102 0.103 0.104	47C 51C 56C 62C
P6SMB68CA P6SMB82CA	64.6 77.9	68 82	71.4 86.1	1 1	58.1 70.1	5 5	6.5 5.3	92 113	0.104 0.105	68C 82C

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C.
3. 10 x 1000 μs exponential decay surge waveform.

TVS – IN SURFACE MOUNT (continued)

SMBJ12AON Series Bidirectional Overvoltage Transient Suppressors; 600 W Peak Power @ 1 ms Surge (10 x 1000 μs)

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)


Device	Breakdown Voltage				Working Peak Reverse Voltage V_{RWM} Volts (Note 1)	Maximum Reverse Leakage @ V_{RWM} I_R μA	Maximum Reverse Surge Current I_{PP} Amps (Note 3)	Maximum Reverse Voltage @ I_{PP} (Clamping Voltage) V_C Volts
	V_{BR} @ I_T Volts (Note 2)							
	Min	Nom	Max	mA				
 <p>SMB CASE 403A PLASTIC</p>					 <p>Surge Current Characteristics</p>			
SMBJ12AON	13.2	13.75	14.3	1	12	5	17.5	15.6

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C .
3. 10 x 1000 μs exponential decay surge waveform.

TVS – IN SURFACE MOUNT (continued)

1SMC Series Unidirectional Overvoltage Transient Suppressors; 1500 W Peak Power @ 1 ms Surge (10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted) (V_F = 3.5 V Max @ I_F = 100 A) (Note 4)


Device	Working Peak Reverse Voltage V _R Volts (Note 1)	Breakdown Voltage		Maximum Clamping Voltage V _C @ I _{pp} Volts	Peak Pulse Current I _{pp} Amps (Note 3)	Maximum Reverse Leakage @ V _R I _R μA	Device Marking
		V _{BR} @ I _T					
		Volts (Min) (Note 2)	mA				
 <p>SMC CASE 403B PLASTIC</p>  <p>Surge Current Characteristics</p>							
1SMC5.0A	5.0	6.40	10	9.2	163.0	1000	GDE
1SMC6.0A	6.0	6.67	10	10.3	145.6	1000	GDG
1SMC6.5A	6.5	7.22	10	11.2	133.9	500	GDK
1SMC7.0A	7.0	7.78	10	12.0	125.0	200	GDM
1SMC7.5A	7.5	8.33	1.0	12.9	116.3	100	GDP
1SMC8.0A	8.0	8.89	1.0	13.6	110.3	50	GDR
1SMC9.0A	9.0	10.0	1.0	15.4	97.4	10	GDV
1SMC10A	10	11.1	1.0	17.0	88.2	5.0	GDX
1SMC12A	12	13.3	1.0	19.9	75.3	5.0	GEE
1SMC13A	13	14.4	1.0	21.5	69.7	5.0	GEG
1SMC14A	14	15.6	1.0	23.2	64.7	5.0	GEK
1SMC15A	15	16.7	1.0	24.4	61.5	5.0	GEM
1SMC16A	16	17.8	1.0	26.0	57.7	5.0	GEP
1SMC17A	17	18.9	1.0	27.6	53.3	5.0	GER
1SMC18A	18	20.0	1.0	29.2	51.4	5.0	GET
1SMC20A	20	22.2	1.0	32.4	46.3	5.0	GEV
1SMC22A	22	24.4	1.0	35.5	42.2	5.0	GEX
1SMC24A	24	26.7	1.0	38.9	38.6	5.0	GEZ
1SMC26A	26	28.9	1.0	42.1	35.6	5.0	GFE
1SMC28A	28	31.1	1.0	45.4	33.0	5.0	GFG
1SMC30A	30	33.3	1.0	48.4	31.0	5.0	GFK
1SMC33A	33	36.7	1.0	53.3	28.1	5.0	GFM
1SMC36A	36	40.0	1.0	58.1	25.8	5.0	GFP
1SMC40A	40	44.4	1.0	64.5	23.2	5.0	GFR
1SMC43A	43	47.8	1.0	69.4	21.6	5.0	GFT
1SMC48A	48	53.3	1.0	77.4	19.4	5.0	GFX
1SMC51A	51	56.7	1.0	82.4	18.2	5.0	GFZ
1SMC54A	54	60.0	1.0	87.1	17.2	5.0	GGE
1SMC58A	58	64.4	1.0	93.6	16.0	5.0	GGG
1SMC60A	60	66.7	1.0	96.8	15.5	5.0	GGK
1SMC64A	64	71.1	1.0	103	14.6	5.0	GGM
1SMC70A	70	77.8	1.0	113	13.3	5.0	GGP
1SMC75A	75	83.3	1.0	121	12.4	5.0	GGR
1SMC78A	78	86.7	1.0	126	11.4	5.0	GGT

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C.
3. 10 x 1000 μs exponential decay surge waveform.
4. 1/2 sine wave (or equivalent square pulse, PW = 8.3 ms, duty cycle = 4 pulses per minute).

TVS – IN SURFACE MOUNT (continued)

1.5 SMC Series Unidirectional Overvoltage Transient Suppressors; 1500 W Peak Power @ 1 ms Surge (10 x 1000 μs)

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted) (V_F = 3.5 V Max, I_F = 100 A for all types) (Note 4)

Device	Breakdown Voltage				Working Peak Reverse Voltage V _{RWM} Volts (Note 1)	Maximum Reverse Leakage @ V _{RWM} I _R μA	Maximum Reverse Surge Current I _{PP} Amps (Note 3)	Maximum Reverse Voltage @ I _{PP} (Clamping Voltage) V _C Volts	Temperature Coefficient of V _{BR} %/°C	Device Marking
	V _{BR} @ I _T Volts (Note 2)									
	Min	Nom	Max	mA						
 <p style="text-align: center;">SMC CASE 403 PLASTIC</p> <div style="display: flex; justify-content: space-around; align-items: center;">  </div> <p style="text-align: center;">Surge Current Characteristics</p>										
1.5SMC6.8A 1.5SMC7.5A	6.45 7.13	6.8 7.5	7.14 7.88	10 10	5.8 6.4	1000 500	143 132	10.5 11.3	0.057 0.061	6V8A 7V5A
1.5SMC10A 1.5SMC12A 1.5SMC13A	9.5 11.4 12.4	10 12 13	10.5 12.6 13.7	1 1 1	8.55 10.2 11.1	10 5 5	103 90 82	14.5 16.7 18.2	0.073 0.078 0.081	10A 12A 13A
1.5SMC15A 1.5SMC16A 1.5SMC18A 1.5SMC20A	14.3 15.2 17.1 19	15 16 18 20	15.8 16.8 18.9 21	1 1 1 1	12.8 13.6 15.3 17.1	5 5 5 5	71 67 59.5 54	21.2 22.5 25.2 27.7	0.084 0.086 0.088 0.09	15A 16A 18A 20A
1.5SMC22A 1.5SMC24A 1.5SMC27A 1.5SMC30A	20.9 22.8 25.7 28.5	22 24 27 30	23.1 25.2 28.4 31.5	1 1 1 1	18.8 20.5 23.1 25.6	5 5 5 5	49 45 40 36	30.6 33.2 37.5 41.4	0.092 0.094 0.096 0.097	22A 24A 27A 30A
1.5SMC33A 1.5SMC36A 1.5SMC39A 1.5SMC43A	31.4 34.2 37.1 40.9	33 36 39 43	34.7 37.8 41 45.2	1 1 1 1	28.2 30.8 33.3 36.8	5 5 5 5	33 30 28 25.3	45.7 49.9 53.9 59.3	0.098 0.099 0.1 0.101	33A 36A 39A 43A
1.5SMC47A 1.5SMC51A 1.5SMC56A 1.5SMC62A	44.7 48.5 53.2 58.9	47 51 56 62	49.4 53.6 58.8 65.1	1 1 1 1	40.2 43.6 47.8 53	5 5 5 5	23.2 21.4 19.5 17.7	64.8 70.1 77 85	0.101 0.102 0.103 0.104	47A 51A 56A 62A
1.5SMC68A 1.5SMC75A 1.5SMC82A 1.5SMC91A	64.6 71.3 77.9 86.5	68 75 82 91	71.4 78.8 86.1 95.5	1 1 1 1	58.1 64.1 70.1 77.8	5 5 5 5	16.3 14.6 13.3 12	92 103 113 125	0.104 0.105 0.105 0.106	68A 75A 82A 91A

1. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.
2. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C.
3. 10 x 1000 μs exponential decay surge waveform.
4. 1/2 sine wave (or equivalent square pulse, PW = 8.3 ms, duty cycle = 4 pulses per minute).

TVS/ESD PROTECTION – One Line

ESD11N5 – One Line Low Cap

Single Line TVS/ESD in 0201 DSN; Meets IEC61000–4–2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
BIDIRECTIONAL

Device	Breakdown Voltage		@ I_T (mA)	Reverse Voltage Working Peak V_{RWM} (V)	Max Reverse Leakage Current I_R (μA)	V_C (V) @ I_{PP} = 1 A	Typical Capacitance (pF) Pin 1 to 2 @ 0 V
	V_{BR} (Note 5) (V)						
	Min						
 CASE 152AA DSN2 							
ESD11N5.0ST5G	5.8	1.0		5.0	1.0	12.0	0.6

5. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

ESD11B5 – One Line

Single Line TVS/ESD in 0201 DSN; Meets IEC61000–4–2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
BIDIRECTIONAL

Device	Breakdown Voltage		@ I_T (mA)	Reverse Voltage Working Peak V_{RWM} (V)	Max Reverse Leakage Current I_R (μA)	V_C (V) @ I_{PP} = 1 A	Typical Capacitance (pF) Pin 1 to 2 @ 0 V
	V_{BR} (Note 6) (V)						
	Min						
 CASE 152AA DSN2 							
ESD11B5.0ST5G	5.8	1.0		5.0	1.0	10.0	12.0

6. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

SD05 Series

Single Line TVS/ESD in SOD–323; 350 W Peak Power (8 x 20 μs); Meets IEC61000–4–2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional

Device	Breakdown Voltage				@ I_T (mA)	Reverse Voltage Working Peak V_{RWM} (Volts)	Max Reverse Leakage Current I_R (μA)	Max Reverse Surge Current I_{PP} (A)	Max Reverse Voltage @ I_{PP} (Clamping Voltage) V_C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts
	V_{BR} (Note 7) (V)									
	Min	Nom	Max							
 CASE 477 STYLE 1 SOD–323 										
SD05	6.2	6.75	7.3	1.0	5.0	10	24	14.5	350	
SD12	13.3	14.5	15.75	1.0	12	1.0	15	25	150	

7. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

TVS/ESD PROTECTION – One Line (continued)

SD12C

Single Line TVS/ESD in SOD–323; 350 W Peak Power (8 x 20 μs); Meets IEC61000–4–2, Level 4

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Bidirectional

Device	Breakdown Voltage				Reverse Voltage Working Peak V _{RWM} (Volts)	Max Reverse Leakage Current I _R (μA)	Max Reverse Surge Current I _{PP} (A)	Max Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts
	V _{BR} (Note 8) (V)			@ I _T (mA)					
	Min	Nom	Max						
 CASE 477 STYLE 1 SOD–323 									
SD12C	13.3	–	–	1.0	12	1.0	15	24	64

8. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

ESD5Z Series

Single Line TVS/ESD in SOD–523; 200 W Peak Power (8 x 20 μs); Meets IEC61000–4–2, Level 4

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Unidirectional

Device	Breakdown Voltage				Reverse Voltage Working Peak V _{RWM} (Volts)	Max Reverse Leakage Current I _R (μA)	Max Reverse Surge Current I _{PP} (A)	Max Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts
	V _{BR} (Note 9) (V)			@ I _T (mA)					
	Min	Nom	Max						
 CASE 502 SOD–523 									
ESD5Z2.5	4.0	–	–	1.0	2.5	6.0	11	10.9	145
ESD5Z3.3	5.0	–	–	1.0	3.3	0.05	11.2	14.1	105
ESD5Z5.0	6.2	–	–	1.0	5.0	0.05	9.4	18.6	80
ESD5Z6.0	6.8	–	–	1.0	6.0	0.01	8.8	20.5	70
ESD5Z7.0	7.5	–	–	1.0	7.0	0.01	8.8	22.7	65
ESD5Z12	14.1	–	–	1.0	12	0.01	9.6	25	55

9. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

TVS/ESD PROTECTION – One Line (continued)

ESD5B

Single Line TVS/ESD in SOD-523; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)
Bidirectional

Device	Breakdown Voltage			Reverse Voltage Working Peak V _{RWM} (V)	Max Reverse Leakage Current I _R (μA)	Max Reverse Surge Current I _{PP} (A)	Max Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts
	V _{BR} (V) @ I _T (Note 10)		@ I _T (mA)					
	Min	Max						
 CASE 502 SOD-523 								
ESD5B5.0S	5.8	–	1.0	5.0	1.0	–	–	32

10. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

ESD9X Series

Single Line TVS/ESD in SOD-923; 100 W Peak Power (8 x 20 μs); Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)
Unidirectional

Device	Breakdown Voltage		Reverse Voltage Working Peak V _{RWM} (V)	Max Reverse Leakage Current I _R (μA)	Max Reverse Surge Current I _{PP} (A)	Max Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts	
	V _{BR} (V) @ I _T (Note 11)							@ I _T (mA)
	Min	Max						
 CASE 514AA SOD-923 								
ESD9X3.3S	5.0	1.0	3.3	2.5	9.8	10.4	80	
ESD9X5.0S	6.2	1.0	5.0	1.0	8.7	12.3	65	
ESD9X12S	13.5	1.0	12	1.0	5.9	23.7	30	

11. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

ESD9B Series

Single Line TVS/ESD in SOD-923; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)
Bidirectional

Device	Breakdown Voltage			Reverse Voltage Working Peak V _{RWM} (V)	Max Reverse Leakage Current I _R (μA)	V _C (V) @ I _{PP} = 1 A	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts
	V _{BR} (V) @ I _T (Note 11)		@ I _T (mA)				
	Min	Max					
 CASE 514AB SOD-923 							
ESD9B3.3	5.0	7.0	1.0	3.3	1.0	10.5	15
ESD9B5.0	5.8	7.8	1.0	5.0	1.0	12.5	15

12. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

TVS/ESD PROTECTION – One Line (continued)

ESD9C Series

Single Line TVS/ESD in SOD–923; Meets IEC61000–4–2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional


Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (V)	Max Reverse Leakage Current I_R (μA)	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts
	V_{BR} (V) @ I_T (Note 11)	@ I_T (mA)			
	Min				
 CASE 514AB SOD–923 					
ESD9C3.3	5.0	1.0	3.3	1.0	12.8
ESD9C5.0	11.0	1.0	5.0	0.5	6.0

13. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

NUP1105L – LIN Bus Protector

Single Line TVS/ESD in SOT–23; 350 W Peak Power (8 x 20 μs); Meets IEC61000–4–2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Bidirectional

Device	Breakdown Voltage				Max Reverse Leakage Current		Capacitance (pF) @ 0 V, 1.0 MHz		Max Reverse Surge Current	Max Reverse Voltage @ I_{PP} (Clamping Voltage)	Peak Power Rating (8x20 μsec) (Note 14)
		V_{BR} (V)		@ I_T	I_R	V_{RWM}			I_{PP} (A)	V_C (V)	
	Min	Nom	Max	(mA)	(μA)	(V)	Typ	Max			
 CASE 318 STYLE 27 SOT–23 											
NUP1105L	25.7	–	28.4	1.0	0.1	24	–	30	8.0	44	350


14. Surge waveform 8 x 20 μsec .

TVS/ESD PROTECTION – Two Line

ESD11A3.3 Series – Two Line

Dual Line TVS/ESD in SOT-1123; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional



Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (V)	Max Reverse Leakage Current I_R (μA)	V_C (V) @ $I_{PP} = 1$ A	Typical Capacitance (pF) Pin 1 to 2 @ 0 V
	V_{BR} (Note 15) (V)					
	Min	@ I_T (mA)				
			CASE 524 SOT-1123			
ESD11A3.3DT5G	5.2	1.0	3.3	1.0	7.8	25.0
ESD11A5.0DT5G	6.2	1.0	5.0	0.1	9.5	20.0

15. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

SM05 – Common Anode Series

Two Line TVS/ESD in SOT-23; 300 W Peak Power (8 x 20 μs); Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional


Device	Breakdown Voltage				Reverse Voltage Working Peak V_{RWM} (Volts)	Max Reverse Leakage Current I_R (μA)	Max Reverse Surge Current I_{PP} (A)	Max Reverse Voltage @ I_{PP} (Clamping Voltage) V_C (V)	Typical Capacitance (pF) Pin 1 to 3 @ 0 Volts
	V_{BR} (Note 16) (V)			@ I_T (mA)					
	Min	Nom	Max						
			CASE 318 STYLE 12 LOW PROFILE SOT-23 PLASTIC						
SM05	6.2	6.75	7.3	1.0	5.0	10	17	9.8	225
SM12	13.3	14.5	15.75	1.0	12	1.0	12	19	95

16. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

MA3075WAL

Two Line TVS/ESD in SOT-23; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional

Device	Breakdown Voltage				@ I_T (mA)	Max Reverse Leakage Current I_R (μA @ 5 V)	Maximum Temperature Coefficient of V_{BR} ($\text{mV}/^\circ\text{C}$)
	V_{BR} (Note 17) (V)			Max			
	Min	Nom	Max				
			CASE 318 STYLE 12 LOW PROFILE SOT-23 PLASTIC				
MA3075WAL	7.2	7.5	7.9	5.0	1.0	5.3	



17. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

TVS/ESD PROTECTION – Two Line (continued)

NUP2105L – CAN Bus Protector

Two Line TVS/ESD in SOT-23; 350 W Peak Power (8 x 20 μs); Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)
Bidirectional



Device	Breakdown Voltage				Max Reverse Leakage Current		Capacitance (pF) @ 0 V, 1.0 MHz		Max Reverse Surge Current I _{PP} (A)	Max Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)	Peak Power Rating (8x20 μsec) (Note 18) Watts
	V _{BR} (V)			@ I _T	I _R	V _{RWM}	Typ	Max			
	Min	Nom	Max	(mA)	(μA)	(V)					
 <p style="text-align: center;">CASE 318 SOT-23</p> 											
NUP2105L	26.2	–	32	1.0	0.1	24	30	–	8.0	44	350

18. Surge waveform 8 x 20 μsec.

DF3A6.8FU

Two Line TVS/ESD in SC-70; 150 W Peak Power (8 x 20 μs); Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)
Unidirectional



Device	Breakdown Voltage				@ I _T	Max Reverse Leakage Current		Max Reverse Surge Current I _{PP} (A)	Max Reverse Voltage @ I _{PP} (Clamping Voltage) V _C (V)
	V _{BR} (Note 19) (V)			I _R @ V _R		(μA)	(V)		
	Min	Nom	Max						
 <p style="text-align: center;">CASE 419 SC-70 (SOT-323)</p> 									
DF3A6.8FU	6.4	6.8	7.2	5.0	0.5	5.0	2.0	9.6	

19. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

NZL5V6AXV Series

Two Line ESD Protection in SC-89; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)
Unidirectional

Device	Breakdown Voltage				@ I _T	Max Reverse Leakage Current	
	V _{BR} (Note 20) (V)			I _R @ V _R		(μA)	(V)
	Min	Nom	Max				
 <p style="text-align: center;">CASE 463C SC-89</p> 							
NZL5V6AXV3	5.32	5.6	5.88	5.0	5.0	3.0	
NZL6V8AXV3	6.46	6.8	7.14	5.0	1.0	4.5	
NZL7V5AXV3	7.12	7.5	7.88	5.0	1.0	5.0	



20. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C.

TVS/ESD PROTECTION – Two Line (continued)

μESD3.3D Series

Two Line ESD Protection in SOT-723; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional

Device	Breakdown Voltage				Max Reverse Leakage Current I_R (μA) @ V_{RWM}
	V_{BR} (Note 21) (V)			@ I_T (mA)	
	Min	Nom	Max		
 CASE 631AA STYLE 4 SOT-723 					
μESD3.3D	5.0	–	–	1.0	1.0
μESD5.0D	6.2	–	–	1.0	0.1
μESD6.0D	7.0	–	–	1.0	0.1



21. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

TVS/ESD PROTECTION – Four Line

NUP4000DR2G – Four Line

Four Line TVS/ESD in SO-8; Meets IEC61000-4-C, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Bidirectional



Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (V)	Max Reverse Leakage Current I_R (μA)	V_C (V) @ $I_{PP} = 1\text{ A}$	V_C (V) @ $I_{PP} = 5\text{ A}$	Typical Capacitance (pF) Pin 1 to 2 @ 0 V
	V_{BR} (Note 22) (V)	@ I_T (mA)					
	Min						
 CASE 751 SO-8 							
NUP4000DR2G	16.7	1.0	15.0	1.0	24.0	30.0	75.0

22. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

LOW CAPACITANCE TVS/ESD PROTECTION – One Line



SL05 Series

Single Line Low Cap TVS/ESD in SOT-23; 300 W Peak Power (8 x 20 μ s); Meets IEC61000-4-2, Level 4

Device	Breakdown Voltage				Max Reverse Leakage Current		Capacitance (pF) @ 0 V, 1.0 MHz		Max Reverse Surge Current	Max Reverse Voltage @ I _{PP} (Clamping Voltage)	Peak Power Rating (8x20 μ sec)
		V _{BR} (V)		@ I _T	I _R	V _{RWM}					
	Min	Nom	Max	(mA)	(μ A)	(V)	Typ	Max	I _{PP} (A)	V _C (V)	Watts
 <p>CASE 318 STYLE 26 SOT-23</p> 											
SL05	6.0	-	8.0	1.0	20	5.0	3.5	5.0	17	11	300
SL12	13.3	-	15.0	1.0	1.0	12	3.5	5.0	12	24	300
SL15	16.7	-	18.5	1.0	1.0	15	3.5	5.0	10	30	300
SL24	26.7	-	29	1.0	1.0	24	3.5	5.0	5.0	55	300

NUP1301ML


Single Line Low Capacitance TVS/ESD in SOT-23; Meets IEC61000-4-2, Level 4

Device	Breakdown Voltage		Forward Voltage		Capacitance* (pF) @ 0 V, 1.0 MHz	
	V _{BR} (V)	@ I _{br}	V _f (V)	I _f	Typ	Max
	Min	μ A	Max	mA		
 <p>CASE 318 SOT-23</p> 						
USB 2.0						
NUP1301ML3	70	100	0.855	10	-	0.9

*C_J = Between I/O pin and ground.

NUP2114UC


NUP2114UC: Low Capacitance TVS/ESD Protection

Device	V _{RWM} (V)	Breakdown Voltage	I _R (mA) @ V _{RWM} = 5 V	C (pF)		Clamping Voltage V _C @ I _{PP} = 1 A (V)
	Max	Min	Max	Typ	Max	Max
 <p>CASE 318G TSSOP-6</p> 						
NUP2114UC	5.0	6.0	1.0	0.8	1.0	12

LOW CAPACITANCE TVS/ESD PROTECTION – One Line (continued)

NUP2114UP

NUP2114UP: Low Capacitance TVS/ESD Protection

Device	V_{RWM} (V)	Breakdown Voltage	I_R (mA) @ $V_{RWM} = 5$ V	C (pF)		Clamping Voltage V_C @ $I_{PP} = 1$ A (V)
	Max	Min	Max	Typ	Max	Max
 <div style="display: inline-block; vertical-align: middle; margin-left: 100px;"> CASE 463B SOT-553 </div> 						
NUP2114UP	5.0	6.0	1.0	0.8	1.0	9.1

ESD9L Series

Single Line Unidirectional TVS/ESD in SOD-923; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Unidirectional

Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (V)	Max Reverse Leakage Current I_R (μA)	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts
	V_{BR} (V) @ I_T (Note 11)	@ I_T (mA)			
	Min				
 <div style="display: inline-block; vertical-align: middle; margin-left: 100px;"> CASE 514AB SOD-923 </div> 					
ESD9L3.3S	4.8	1.0	3.3	1.0	0.5
ESD9L5.0S	4.4	1.0	5.0	1.0	0.5

23. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

ESD9R Series

Single Line Low Leakage Unidirectional TVS/ESD in SOD-923; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Unidirectional

Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (V)	Max Reverse Leakage Current I_R (nA)	Typical Capacitance (pF) Pin 1 to 2 @ 0 Volts
	V_{BR} (V) @ I_T (Note 11)	@ I_T (mA)			
	Min				
 <div style="display: inline-block; vertical-align: middle; margin-left: 100px;"> CASE 514AB SOD-923 </div> 					
ESD9R3.3S	4.8	1.0	3.3	1	0.5

24. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

LOW CAPACITANCE TVS/ESD PROTECTION – One Line (continued)

ESD9M Series

Single Line Unidirectional TVS/ESD in SOD-923; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)



Unidirectional

Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (V)	Max Reverse Leakage Current I_R (μA)	Max Capacitance (pF) Pin 1 to 2 @ 0 V
	V_{BR} (V) @ I_T (Note 11)	@ I_T (mA)			
	Min				
	CASE 514AB SOD-923				
ESD9M5.0S	5.8	1.0	5.0	1.0	2.5

25. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

TVS PROTECTION – Low Capacitance Surface Mount for USB 2.0 and 1.1

ESD Protection Meeting IEC 61000-4-2, 4-4, 4-5



Device	Breakdown Voltage				Max Reverse Leakage Current		Capacitance* (pF) @ 0 V, 1.0 MHz		Max Reverse Surge Current I_{PP} (A)	Max Reverse Voltage @ I_{PP} (Clamping Voltage) V_C (V)	Peak Power Rating (8x20 μsec) Watts
	V_{BR} (V)			@ I_T	I_R	V_{RWM}					
	Min	Nom	Max	(mA)	(μA)	(V)	Typ	Max			
	CASE 419B SC-88										
USB 2.0											
NUP2301MW6	70	-	-	-	0.1	2.5	0.8	1.5	-	-	-

LOW CAPACITANCE TVS/ESD PROTECTION – Two Line

ESD7L Series – Common Anode Series

Two Line TVS/ESD in SOT-723; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional


Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (Volts)	V_C (V) @ $I_{PP} = 1$ A	Typical Capacitance (pF) Pin 1 to 2 @ 0 V
	V_{BR} (Note 16) (V)	@ I_T (mA)			
 <p>CASE 631AA SOT-723</p> 	5.4	1.0	5.0	8.4	0.25

26. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

ESD11L – Common Anode Series

Two Line TVS/ESD in SOT-1123; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional



Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (Volts)	Max Reverse Leakage Current I_R (μA)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V
	V_{BR} (Note 16) (V)	@ I_T (mA)			
 <p>CASE 524AA SOT-1123</p> 	5.4	1.0	5.0	1.0	0.25

27. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

ESD7M Series – Common Anode Series

Two Line TVS/ESD in SOT-723; Meets IEC61000-4-2, Level 4

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)
Unidirectional


Device	Breakdown Voltage		Reverse Voltage Working Peak V_{RWM} (Volts)	Max Reverse Leakage Current I_R (μA)	V_C (V) @ $I_{PP} = 1$ A	Max Capacitance (pF) Pin 1 to 3 @ 0 V
	V_{BR} (Note 16) (V)	@ I_T (mA)				
 <p>CASE 631AA SOT-723</p> 	5.4	1.0	5.0	1.0	8.4	2.4

28. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

LOW CAPACITANCE TVS/ESD PROTECTION – Two Line (continued)



NUP4114H

NUP4114H – Low Capacitance TVS/ESD Protection; Meets IEC6100–4–2, Level 4

Device	Max Reverse Voltage V_{RWM} (V)	Breakdown Voltage			Max Reverse Leakage Current I_R (μ A)	Max Clamping Voltage @ I_{PP} = 1 A V_C (V)	Typical Capacitance (pF) @ 0 V
		V_{BR} (V)					
		Min	Nom	Max			
		CASE 318G TSOP-6 STYLE 12					
NUP4114H	5.0	6.0	7.5	1.0	1.0	12.1	0.8

NUP4114UP


NUP4114UP – Low Capacitance TVS/ESD Protection; Meets IEC6100–4–2, Level 4

Device	Max Reverse Voltage V_{RWM} (V)	Breakdown Voltage			Max Reverse Leakage Current I_R (μ A)	Max Clamping Voltage @ I_{PP} = 1 A V_C (V)	Typical Capacitance (pF) @ 0 V
		V_{BR} (V)					
		Min	Nom	Max			
		CASE 463A SOT-563					
NUP4114UP	5.0	6.0		1.0	1.0	11.2	0.4

LOW CAPACITANCE TVS/ESD PROTECTION – Three Line


NUP3115UP

NUP3115UP – Low Capacitance TVS/ESD Protection; Meets IEC6100–4–2, Level 4

Device	Max Reverse Voltage V_{RWM} (V)	Breakdown Voltage				Max Reverse Leakage Current I_R (μ A)	Typ Clamping Voltage @ $I_{PP} = 1$ A V_C (V)	Typical Capacitance (pF) @ 0 V
		V_{BR} (V)			@ I_T (mA)			
		Min	Nom	Max				
		CASE 517AP UDFN6 1.6x1.6						
NUP3115UP	5.5	6.4	6.8	8.0	1.0	1.0	9.4	0.8



ESDR0502N

ESDR0502N – Ultra-Low Capacitance TVS/ESD Protection; Meets IEC61000–4–2, Level 4



Device	Max Reverse Voltage V_{RWM} (V)	Breakdown Voltage				Max Reverse Leakage Current I_R (μ A)	Max Clamping Voltage @ $I_{PP} = 1$ A V_C (V)	Typical Capacitance (pF) @ 0 V
		V_{BR} (V)			@ I_T (mA)			
		Min	Nom	Max				
		CASE 517AA UDFN6						
ESDR0502N	5.5	6.0			1.0	1.0		0.3

LOW CAPACITANCE TVS/ESD PROTECTION – Four Line

Four Line Low Cap TVS/ESD Protection in SOT-563; Meets IEC61000-4-2, Level 4



Device	Breakdown Voltage (D ₁ , D ₂ , and D ₃)				Breakdown Voltage (V _{CC})				Working Peak Reverse Voltage (D ₁ , D ₂ , and D ₃)	Max Reverse Leakage Current (D ₁ , D ₂ , and D ₃)		Max Reverse Leakage Current (V _{CC})		Capacitance (pF) @ 3.0 V, 1.0 MHz		Peak Power Rating (8x20 μsec) (D ₁ , D ₂ , and D ₃)	Peak Power Rating (8x20 μsec) (V _{CC})
	V _{BR} (V)		@ I _T (mA)	V _{BR} (V)	@ I _T (mA)	V _{RWM} (V)	I _R (μA)	V _{RWM} (V)	I _R (μA)	V _R (V)	Typ	Max	Watts	(mW)			
	Min	Nom													Max		
 <p style="text-align: center;">CASE 463A SOT-563</p> 																	
NUP4060AXV6	6.2	6.8	7.2	1.0	15.3	16	17.1	5.0	5.0	0.5	3.0	0.05	11	7.0	10	20	200

Four Line Low Cap Bidirectional TVS/ESD Protection in SOT-563; Meets IEC61000-4-2, Level 4

Device	Breakdown Voltage				Max Reverse Leakage Current		Capacitance* (pF) @ 0 V, 1.0 MHz		Max Reverse Surge Current	Max Reverse Voltage @ I _{pp} (Clamping Voltage)	Peak Power Rating (8x20 μsec)
	V _{BR} (V)		@ I _T (mA)	nA	V _{RWM} (V)	Typ	Max	I _{pp} (A)	V _C (V)	Watts	
	Min	Nom									Max
 <p style="text-align: center;">CASE 463A SOT-563</p> 											
NUP4102XV6	13.6	–	17.8	1.0	100	12	13	15	3.0	25	75

*C_j = Between I/O pin and ground.

Four Line Low Cap TVS/ESD Protection; Meets IEC61000-4-2, Level 4



Device	Breakdown Voltage				Max Reverse Leakage Current		Capacitance* (pF) @ 0 V, 1.0 MHz		Max Reverse Surge Current	Max Reverse Voltage @ I _{pp} (Clamping Voltage)	Peak Power Rating (8x20 μsec)
	V _{BR} (V)		@ I _T (mA)	I _R (μA)	V _{RWM} (V)	Typ	Max	I _{pp} (A)	V _C (V)	Watts	
	Min	Nom									Max
 <p style="text-align: center;">CASE 751 SO-8</p> 											
USB 2.0											
NUP4201DR2	6.0	–	–	1.0	10	5.0	5.0	10	10	12	500
SRDA05-4R2	6.0	–	–	1.0	10	5.0	10	15	10	12	500

*C_j = Between I/O pin and ground.

LOW CAPACITANCE TVS/ESD PROTECTION – Four Line (continued)


NUP4112P

NUP4112P – Quad Low Capacitance TVS/ESD Protection; Meets IEC6100–4–2, Level 4

Device	Max Reverse Voltage V_{RWM} (V)	Breakdown Voltage			V_{BR} (V) @ I_T (mA)	Max Reverse Leakage Current I_R (μ A)	Max Clamping Voltage @ I_{PP} = 1 A V_C (V)	Typical Capacitance (pF) @ 0 V
		V_{BR} (V)						
		Min	Nom	Max				
		CASE 463A SOT–563						
NUP4012P	4.0	5.2	5.5		1.0	1.0	9.5	0.7


NUP4016

NUP4016 – Quad Ultra–Low Capacitance TVS/ESD Protection; Meets IEC6100–4–2, Level 4, 15 kV Contact Discharge

Device	Max Reverse Voltage V_{RWM} (V)	Breakdown Voltage			V_{BR} (V) @ I_T (mA)	Max Reverse Leakage Current I_R (μ A)	Max Clamping Voltage @ I_{PP} = 1 A V_C (V)	Typical Capacitance (pF) @ 0 V
		V_{BR} (V)						
		Min	Nom	Max				
		CASE 527AE SOT–953						
NUP4016	5.0	6.0			1.0	1.0		0.5

ESDR0524P


ESDR0524P – Quad Low Capacitance TVS/ESD Protection; Meets IEC6100–4–2, Level 4

Device	Max Reverse Voltage V_{RWM} (V)	Breakdown Voltage			V_{BR} (V) @ I_T (mA)	Max Reverse Leakage Current I_R (μ A)	Max Clamping Voltage @ I_{PP} = 1 A V_C (V)	Typical Capacitance (pF) @ 0 V
		V_{BR} (V)						
		Min	Nom	Max				
		CASE 517BB UDFN10						
ESDR0524P	5.0	6.0			1.0	1.0		0.5

INTEGRATED COMMON MODE CHOKE WITH TVS/ESD PROTECTION


NUC2401

NUC2401 – Single Pair Common Mode Choke and TVS/ESD Protection; Meets IEC61000-4-2, Level 4, 12 kV discharge

Device	Max Reverse Voltage V_{RWM} (V)	Breakdown Voltage			$@ I_T$ (mA)	Max Reverse Leakage Current I_R (μ A)	Common Mode Cut-Off Freq f_{3dB}	Typical Capacitance (pF) $@ 0$ V
		V_{BR} (V)						
		Min	Nom	Max				
								
NUC2401	5.0	6.0	7.6	8.6	1.0	2.0	40 MHz	0.8

TVS/ESD PROTECTION, COMMON ANODE – One Line

CM1242 – Single Line TVS/ESD; Meets IEC61000-4-2, Level 4,
19 kV contact discharge for CM1242-07CP
30 kV contact discharge for CM1242-33CP

Device	Number of lines	Typ Breakdown Voltage @ 10 mA (V)	Max Channel Leakage Current I_{Leak} (μ A)	Small Signal Clamping Voltage (+ve Clamp) @ $I_{pp} = 10$ mA V_C (V)	Small Signal Clamping Voltage (-ve Clamp) @ $I_{pp} = 10$ mA V_C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
							
CM1242-07CP	1	7.6	0.5	9.0	-9.0	5.8	CSP
CM1242-33CP	1	7.6	0.5	8.6	-8.6	55	CSP

TVS/ESD PROTECTION, COMMON ANODE – Two to Five Lines

CM1218 – Common Anode Series; Meets IEC61000-4-2, Level 4, 15 kV contact discharge

Device	Number of lines	Min Reverse Stand-off Voltage @ 1 mA (V)	Max Reverse Leakage Current I_R (μ A)	Small Signal Clamping Voltage (+ve Clamp) @ $I_{PP} = 10$ mA V_C (V)	Small Signal Clamping Voltage (-ve Clamp) @ $I_{PP} = 10$ mA V_C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
CM1218-02SO	2	6.1	1.0	6.8	-0.8	7	SOT23-3
CM1218-02S7	2	6.1	1.0	6.8	-0.8	7	SC70-3
CM1218-03SR	3	6.1	1.0	6.8	-0.8	7	SOT143
CM1218-04SO	4	6.1	1.0	6.8	-0.8	7	SOT23-5
CM1218-04SE	4	6.1	1.0	6.8	-0.8	7	SOT-553
CM1218-04S7	4	6.1	1.0	6.8	-0.8	7	SC70-5
CM1218-F4SE	4	6.1	1.0	6.8	-0.8	7	SOT-563
CM1218-C4SE	4	6.1	1.0	6.8	-0.8	7	SOT553
CM1218-H4SE	4	6.1	1.0	6.8	-0.8	7	SOT-563
CM1218-05SO	5	6.1	1.0	6.8	-0.8	7	SOT23-6
CM1218-05SE	5	6.1	1.0	6.8	-0.8	7	SOT-563
CM1218-05S7	5	6.1	1.0	6.8	-0.8	7	SC70-6

TVS/ESD PROTECTION, COMMON ANODE – Two to Five Lines (continued)

CM1219 – Common Anode Series; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Min Reverse Stand-off Voltage @ 1 mA (V)	Max Reverse Leakage Current I _R (μA)	Small Signal Clamping Voltage (+ve Clamp) @ I _{PP} = 10 mA V _C (V)	Small Signal Clamping Voltage (-ve Clamp) @ I _{PP} = 10 mA V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
CM1219-02SO	2	6.1	1.0	6.8	-0.8	4	SOT23-3
CM1219-02S7	2	6.1	1.0	6.8	-0.8	4	SC70-3
CM1219-03SR	3	6.1	1.0	6.8	-0.8	4	SOT143
CM1219-04SO	4	6.1	1.0	6.8	-0.8	4	SOT23-5
CM1219-04SE	4	6.1	1.0	6.8	-0.8	4	SOT-553
CM1219-04S7	4	6.1	1.0	6.8	-0.8	4	SC70-5
CM1219-05SO	5	6.1	1.0	6.8	-0.8	4	SOT23-6
CM1219-05SE	5	6.1	1.0	6.8	-0.8	4	SOT-563
CM1219-05S7	5	6.1	1.0	6.8	-0.8	4	SC70-6

CM1240 – Common Anode Series ESD Protection for USB; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Max Reverse Leakage Current LV diode I _R (μA)	Small Signal Clamping Voltage (+ve Clamp) @ I _{PP} = 10 mA V _C (V)	Small Signal Clamping Voltage (-ve Clamp) @ I _{PP} = 10 mA V _C (V)	Typical Capacitance HV diode @ 3 V (pF)	Typical Capacitance LV diode @ 3 V (pF)	Package Type
CM1240-F4SE	3	0.4	6.8	-0.8	25	6	SOT-563

TVS/ESD PROTECTION, COMMON ANODE – Four or Eight Lines

CM1204 – Common Anode Series; Meets IEC61000-4-2, Level 4, 15 kV contact discharge for CM1204 30 kV contact discharge for CM1244

Device	Breakdown Voltage			Max Reverse Leakage Current I _R (μA) @ I _T (mA)	Signal Clamping Voltage (+ve Clamp) @ I _{PP} = 10 mA V _C (V)	Signal Clamping Voltage (-ve Clamp) @ I _{PP} = 10 mA V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V
	Min	Nom	Max				
CM1204-03CP		6.0		0.01	0.1	6.8	27
CM1244-04CP	5.5			0.01	0.1	6.8	27

TVS/ESD PROTECTION, COMMON ANODE – Four or Eight Lines (continued)

CM1249 – Common Anode Series; Meets IEC61000–4–2, Level 4, 8 kV contact discharge


Device	Number of lines	Max Leakage Current I_R (μA)	Small Signal Clamping Voltage (+ve Clamp) @ $I_{PP} = 5\text{ mA}$ V_C (V)	Small Signal Clamping Voltage (-ve Clamp) @ $I_{PP} = 5\text{ mA}$ V_C (V)	Typical Channel Capacitance (pF) @ 0 V	Package Type
<p>CM1249-04</p> <p>The diagram shows a common anode TVS diode array. A central node is labeled V_{IN}. Four diodes are connected to this node: two on the left (lines 1 and 5) and two on the right (lines 3 and 4). The anodes of all four diodes are connected to the central V_{IN} node. The cathodes are connected to lines 1, 2, 3, and 4 respectively.</p>						
CM1249-04S9	4	0.75	8.5 (max)	-0.4	5	SOT-953

CM1250 – Common Anode Series; Meets IEC61000–4–2, Level 4, 8 kV contact discharge


Device	Number of lines	Max Leakage Current I_R (μA)	Small Signal Clamping Voltage (+ve Clamp) @ $I_{PP} = 5\text{ mA}$ V_C (V)	Small Signal Clamping Voltage (-ve Clamp) @ $I_{PP} = 5\text{ mA}$ V_C (V)	Typical Channel Capacitance (pF) @ 0 V	Package Type
<p>The diagram shows a common anode TVS diode array. A central node is labeled V_{IN}. Four diodes are connected to this node: two on the left (lines 1 and 6) and two on the right (lines 3 and 4). The anodes of all four diodes are connected to the central V_{IN} node. The cathodes are connected to lines 1, 2, 3, and 4 respectively.</p>						
CM1250-04QG	4	0.1	8.5 (max)	-0.4 (max)	5	superDFN

PicoGuard®: LOW CAPACITANCE TVS/ESD PROTECTION – One to Four Lines


CM1282 – Low Capacitance Single Line TVS/ESD Protection; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Breakdown Voltage				Max Reverse Leakage Current I_{LEAK} (μ A)	Typical Clamping Voltage @ $I_{PP} = 1$ A V_{CL} (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V
	V_{BR} (V)			@ I_T (mA)			
	Min	Nom	Max				
							
CM1282-01D1	7.5	9.0	11.0	10	1.0	11	0.5

CM1214A series – AC Signal ESD Protection; Meets IEC61000-4-2, Level 4

Device	Number of lines	Operating Supply Voltage (V)		Max Reverse Leakage Current I_R (μ A)	Channel Clamping Voltage @ $I_{PP} = 1$ A V_C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		Nom	Max				
							
CM1214A-01SO	1	7		1.0	11.3	0.6	SOT23
CM1214A-02MR	2	7		1.0	11.3	0.6	MSOP

CM1213A series – Including V_p and V_n Connections; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Operating Supply Voltage (V)		Max Operating Current (μ A)	Max Reverse Leakage Current I_R (μ A)	Channel Clamping Voltage (+ve Transient) @ $I_{PP} = 1$ A V_C (V)	Channel Clamping Voltage (-ve Transient) @ $I_{PP} = 1$ A V_C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		Nom	Max						
									
CM1213A-01SO	1	3.3	5.5	8.0	1.0	10	-1.7	0.85	SOT23-3
CM1213A-02SR	2	3.3	5.5	8.0	1.0	10	-1.7	0.85	SOT143-4
CM1213A-02SO	2	3.3	5.5	8.0	1.0	10	-1.7	0.85	SOT23-5
CM1213A-04SO	4	3.3	5.5	8.0	1.0	10	-1.7	0.85	SOT23-6
CM1213A-04S7	4	3.3	5.5	8.0	1.0	10	-1.7	0.85	SC70-6
CM1213A-04MR	4	3.3	5.5	8.0	1.0	10	-1.7	0.85	MSOP-10

PicoGuard®: LOW CAPACITANCE TVS/ESD PROTECTION – One to Four Lines

(continued)

CM1215 series – Including Vp and Vn Connections; Meets IEC61000-4-2, Level 4, 15 kV contact discharge

Device	Number of lines	Operating Supply Voltage (V)		Max Operating Current (μA)	Max Reverse Leakage Current I _R (μA)	Channel Clamping Voltage (+ve Transient) @ I _{PP} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{PP} = 1 A V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		Nom	Max						
CM1215-01SO	1	3.3	5.5	8	1.0	V _P +1.5	V _N -1.5	1.6	SOT23-3
CM1215-02SR	2	3.3	5.5	8	1.0	V _P +1.5	V _N -1.5	1.6	SOT143
CM1215-02SO	2	3.3	5.5	8	1.0	V _P +1.5	V _N -1.5	1.6	SOT23-5
CM1215-04SO	4	3.3	5.5	8	1.0	V _P +1.5	V _N -1.5	1.6	SOT23-6

CM1224 series – Including Vp and Vn Connections; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Operating Supply Voltage (V)		Max Operating Current (μA)	Max Reverse Leakage Current I _R (μA)	Channel Clamping Voltage (+ve Transient) @ I _{PP} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{PP} = 1 A V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		Nom	Max						
CM1224-02SR	2	3.3	5.5	8	1.0	10.0	-1.8	0.7	SOT143-4
CM1224-04SO	4	3.3	5.5	8	1.0	10.0	-1.8	0.7	SOT23-6
CM1224-04MR	4	3.3	5.5	8	1.0	10.0	-1.8	0.7	MSOP-10

CM1293A series – Including Vp and Vn Connections; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Operating Supply Voltage (V)		Max Operating Current (μA)	Max Reverse Leakage Current I _R (μA)	Channel Clamping Voltage (+ve Transient) @ I _{PP} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{PP} = 1 A V _C (V)	Max Capacitance (pF) @ 0 V	Package Type
		Nom	Max						
CM1293A-02SR	2	3.3	5.5	8	1.0	9.9	-1.6	2.0	SOT143-4
CM1293A-02SO	4	3.3	5.5	8	1.0	9.9	-1.6	2.0	SOT23-5
CM1293A-04SO	2	3.3	5.5	8	1.0	9.9	-1.6	2.0	SOT23-6
CM1293A-04MR	4	3.3	5.5	8	1.0	9.9	-1.6	2.0	MSOP-10

PicoGuard®: LOW CAPACITANCE TVS/ESD PROTECTION – One to Four Lines

(continued)

CM1225 series – Including Vn Connection; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Operating Supply Voltage		Max Reverse Leakage Current I_R (μ A)	Channel Clamping Voltage (+ve Transient) @ $I_{PP} = 1$ A V_C (V)	Channel Clamping Voltage (-ve Transient) @ $I_{PP} = 1$ A V_C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		(V)						
		Nom	Max					
<p style="text-align: center;">CM1224-04DE</p>								
CM1225-04DE	4		5.5	1.0	10.0	-4.5	0.8	uUDFN-10

CM1241 – Dual-Voltage ESD Protection Including Vp and Vn Connections; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Max Reverse Leakage Current LV diode I_R (μ A)	Small Signal Clamping Voltage (+ve Clamp) @ $I_{PP} = 1$ A V_C (V)	Small Signal Clamping Voltage (-ve Clamp) @ $I_{PP} = 1$ A V_C (V)	Typical Capacitance HV diode @ 3 V (pF)	Typical Capacitance LV diode @ 3 V (pF)	Package Type
<p style="text-align: center;">Note: Pins 5 and 6 to 8 are connected to a common substrate.</p>							
CM1241-04D4	3	0.1	9.64	-1.75	53	1.2	TDFN-8

PicoGuard®: LOW CAPACITANCE TVS/ESD PROTECTION – Two, Four, Six or Eight Lines

CM1216 series – Including Vp and Vn Connections; Meets IEC61000-4-2, Level 4, 15 kV contact discharge

Device	Number of lines	Operating Supply Voltage		Max Operating Current (μA)	Max Reverse Leakage Current I _R (μA)	Channel Clamping Voltage (+ve Transient) @ I _{PP} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{PP} = 1 A V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		(V)							
		Nom	Max						
<p style="text-align: center;">CM1216-06MR CM1216-06SM</p> <p style="text-align: center;">CM1216-08MR</p>									
CM1216-06SM	6	3.3	5.5	8	1.0	9.0	-1.5	1.6	SOIC
CM1216-06MR	6	3.3	5.5	8	1.0	9.0	-1.5	1.6	MSOP
CM1216-08MR	8	3.3	5.5	8	1.0	9.0	-1.5	1.6	MSOP

CM1223 series – Including Vp and Vn with Backdrive Protection; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Operating Supply Voltage		Max Operating Current (μA)	Max Reverse Leakage Current I _R (μA)	Channel Clamping Voltage (+ve Transient) @ I _{PP} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{PP} = 1 A V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		(V)							
		Nom	Max						
<p style="text-align: center;">CM1223-02SO CM1223-02SR</p> <p style="text-align: center;">CM1223-04SO CM1223-04MR</p> <p style="text-align: center;">CM1223-08MR</p>									
CM1223-02SO	2	3.3	5.5	8.0	1.0	8.8	-1.4	1.0	SOT23-5
CM1223-02SR	2	3.3	5.5	8.0	1.0	8.8	-1.4	1.0	SOT143-4
CM1223-04SO	4	3.3	5.5	8.0	1.0	8.8	-1.4	1.0	SOT23-6
CM1223-04MR	4	3.3	5.5	8.0	1.0	8.8	-1.4	1.0	MSOP-10
CM1223-08MR	8	3.3	5.5	8.0	1.0	8.8	-1.4	1.0	MSOP-10

PicoGuard®: LOW CAPACITANCE TVS/ESD PROTECTION – Two, Four, Six or Eight Lines

CM1230 series – Including Vp and Vn Connections; Meets IEC61000-4-2, Level 4, 8 kV contact discharge

Device	Number of lines	Operating Supply Voltage		Max Operating Current (μA)	Max Reverse Leakage Current I _R (μA)	Channel Clamping Voltage (+ve Transient) @ I _{pp} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{pp} = 1 A V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		(V)							
		Nom	Max						
CM1230-02CS	2	3.3	5.5	8.0	1.0	9.8	-1.8	0.8	CSP-4
CM1230-04CS	4	3.3	5.5	8.0	1.0	9.8	-1.8	0.8	CSP-6
CM1230-08CS	8	3.3	5.5	8.0	1.0	9.8	-1.8	0.8	CSP-10

CM1263 series – Including Vp and Vn Connections; Meets IEC61000-4-2, Level 4, 15 kV contact discharge

Device	Number of lines	Operating Supply Voltage		Max Operating Current (μA)	Max Reverse Leakage Current I _R (μA)	Channel Clamping Voltage (+ve Transient) @ I _{pp} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{pp} = 1 A V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		(V)							
		Nom	Max						
CM1263-02SE	2	3.3	5.5	8	1.0	9.96	-1.6	0.85	SOT553
CM1263	6	3.3	5.5	8	1.0	9.96	-1.6	0.88	uDFN-12

PicoGuard-XP®: LOW CAPACITANCE TVS/ESD CLAMP PROTECTION – Two Lines

CM1231 series – ESD Clamp Protection Array; Meets IEC61000-4-2, Level 4, 12 kV contact discharge

Device	Number of lines	Operating Supply Voltage		Max Operating Current (μA)	Typical Series Resistance (Ω)	Channel Clamping Voltage (+ve Transient) @ I _{pp} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{pp} = 1 A V _C (V)	Typical Capacitance (pF) Pin 1 to 2 @ 0 V	Package Type
		(V)							
		Nom	Max						
CM1231-02SO	2	5	5.5	1.0	1	9.0	-1.4	1.5	SOT23-6

PicoGuard-XS®: LOW CAPACITANCE TVS/ESD CLAMP PROTECTION – Four Pairs of Differential lines

CM123x series – ESD Clamp Protection Array; Meets IEC61000-4-2, Level 4,
 8 kV contact discharge for CM1233, CM1234, CM1235, CM1236
 20 kV contact discharge for CM1238

Device	Number of Pairs of Differential lines	Operating Supply Voltage		Channel Leakage Current (μA)	Individual Channel Single-ended Impedance (Ω)	Differential Channels Pair Impedance (Ω)	Channel Clamping Voltage (+ve Transient) @ I _{pp} = 1 A V _C (V)	Channel Clamping Voltage (-ve Transient) @ I _{pp} = 1 A V _C (V)	TDFN-16 Package Size (mm x mm)
		(V)							
		Min	Max						
CM1233-08DE	4	-0.5	5.5	1	50	100	10.0	-1.8	4.0 x 6.0
CM1234-08DE	4	-0.5	5.5	1	50	100	9	-1.5	4.0 x 6.0
CM1235-08DE	4	-0.5	5.5	1	50	100	9.2	-1.6	1.7 x 4.0
CM1236-08DE	4	-0.5	5.5	1	50	100	9.2	-1.6	4.0 x 6.0
CM1238-08DE	4	-0.5	5.5	1	50	100	10.0	-1.9	1.6 X 4.0

MediaGuard®: HDMI PORT PROTECTION AND INTERFACE DEVICES

CM20xx series – HDMI Port Source and Sink

Protection and Interface Devices; Meets IEC61000–4–2, Level 4, 8 kV contact discharge

Device	HDMI (Source or Sink ?)	# of pairs of Data Channel	# of pairs of Clock Channel	DDC Active Pull-up	CEC Slew Rate control	Backdrive Protection	Level Shifters	Package Type
<p>The schematic diagram illustrates the internal circuitry of the HDMI port protection and interface devices. It features several key components: <ul style="list-style-type: none"> TMDS Signal Lines: TMDS_D2+, TMDS_D1+, TMDS_D0+, TMDS_GND, TMDS_D2-, TMDS_D1-, TMDS_D0-, TMDS_GND, TMDS_CK+, TMDS_GND, TMDS_D0-, TMDS_CK-. ESD Protection: An ESD_BYP pin and a 5V_SUPPLY pin with a diode to ground. LV SUPPLY Connections: Four LV SUPPLY pins are shown, each with a diode to ground. DDC and Hotplug Lines: CE_REMOTE_IN, CE_REMOTE_OUT, DDC_DAT_IN, DDC_DAT_OUT, DDC_CLK_IN, DDC_CLK_OUT, HOTPLUG_DET_IN, and HOTPLUG_DET_OUT. Overcurrent Protection: A 55mA OVERCURRENT SWITCH connected between 5V_SUPPLY and 5V_OUT. </p>								
CM2020–00TR	Source	3	1	No	No	Yes	Yes	38–TSSOP
CM2020–01TR	Source	3	1	No	No	Yes	Yes	38–TSSOP
CM2021–02TR	Sink	3	1	No	No	Yes	Yes	38–TSSOP
CM2030–A0TR	Source	3	1	Yes	Yes	Yes	Yes	38–TSSOP
CM2031–A0TR	Sink	3	1	Yes	Yes	Yes	Yes	38–TSSOP

VGA PORT PROTECTION AND INTERFACE DEVICES

CM2006 – VGA and DVI-I Port Companion Circuit for TVs and Monitors; Meets IEC61000–4–2, Level 4, 8 kV contact discharge

Device	VGA	# of Video Lines	# of Sync Lines	DDC Data & CLK	CEC Slew Rate control	Backdrive Protection	Level Shifters	Package Type
Electrical Schematic								
CM2006–02QR	Monitors & TVs	3	2	Yes	No	Yes	Yes	16–QSOP

CM2009 – VGA and DVI-I Port Companion Circuit for PCs, Graphics Cards and Set Top Boxes; Meets IEC61000–4–2, Level 4, 8 kV contact discharge

Device	VGA	# of Video Lines	# of Sync Lines	DDC Data & CLK	Backdrive Protection	Level Shifters	R _{OUT}	Package Type
Electrical Schematic								
CM2009–00QR	PCs, Graphics Cards & Set Top Boxes	3	2	Yes	Yes	Yes	65 Ω	16–QSOP
CM2009–02QR	PCs, Graphics Cards & Set Top Boxes	3	2	Yes	Yes	Yes	15 Ω	16–QSOP

Drivers

Drivers

Table of Contents

	Page
Display/LED Drivers	214
Load/Relay Drivers	
Load Drivers – Darlington Transistors Arrays	217
Relay Drivers	217
MOSFET/IGBT Drivers	218
Motor Drivers	219

DISPLAY/LED DRIVERS

Device	Topology	V _I Min (V)	V _I Max (V)	V _O Max (V)	I _O Max (mA)	f _{sw} Typ (kHz)	LEDs in Series, Max #	LEDs in Parallel, Max #	Package
CAT310W	Linear	3	5.5	40	500			10	SOIC-20
CAT3224HV3	Charge Pump	2.5	5.5		4000	800	1	2	TQFN-16
CAT32TDI	Step-Up Boost		5.5	20	25	1200	4		TSOT-23
CAT32ZD4	Step-Up Boost		5.5	20	25	1200	4		TDFN-8
CAT3604HV4	Charge Pump	3	5.5		120	1000		4	TQFN-16
CAT3604VHV4	Charge Pump	2.5	5.5		120	1000		4	TQFN-16
CAT3606HV4	Charge Pump	3	5.5		180	1000		6	TQFN-16
CAT3612HV2	Charge Pump	3	5.5		300	1000		2	TQFN-12
CAT3614HV2	Charge Pump	3	5.5		124	1000		4	TQFN-12
CAT3616HV4	Charge Pump	3	5.5		186	1000		6	TQFN-16
CAT3626HV4	Charge Pump	3	5.5		192	1000		6	TQFN-16
CAT3636HV3	Charge Pump	2.5	5.5		192	1000		6	TQFN-16
CAT3637HV3	Charge Pump	2.5	5.5		180	1000		6	TQFN-16
CAT3643HV2	Charge Pump	2.5	5.5		90	1000		3	TQFN-12
CAT3643HV3	Charge Pump	2.5	5.5		90	1000		3	TQFN-16
CAT3644HV3	Charge Pump	2.5	5.5		100	1000		4	TQFN-16
CAT3647HV3	Charge Pump	2.5	5.5		100	1000		3	TQFN-16
CAT3648HV3	Charge Pump	2.5	5.5		100	1000		4	TQFN-16
CAT37TDI	Step-Up Boost	2	5.5	20	25	1000			TSOT-23
CAT4004VP2	Linear	2.4	5.5		100		4		TDFN-8
CAT4004VP2	Linear	2.4	5.5		100		4		TDFN-8
CAT4008V	Linear	3	5.5		800		8		SOIC-16
CAT4008W	Linear	3	5.5		800		8		SOIC-16
CAT4008Y	Linear	3	5.5		800		8		TSSOP-16
CAT4016HV6	Linear	3	5.5		1600		16		WQFN-24
CAT4016VS	Linear	3	5.5		1600		16		QSOP-24
CAT4016VSR	Linear	3	5.5		1600		16		QSOP-24

DISPLAY/LED DRIVERS

Device	Topology	V _I Min (V)	V _I Max (V)	V _O Max (V)	I _O Max (mA)	f _{sw} Typ (kHz)	LEDs in Series, Max #	LEDs in Parallel, Max #	Package
CAT4016W	Linear	3	5.5		1600		16		SOIC-24
CAT4016Y	Linear	3	5.5		1600		16		TSSOP-24
CAT4026V		4.5	5.5						SOIC-28
CAT4101TV	Linear	3	5.5		1000		8		TO-263
CAT4103V	Linear	3	5.5		525		8	3	SOIC-16
CAT4104V	Linear	3	5.5		700		8	4	SOIC-8
CAT4104VP2	Linear	3	5.5		700		8	4	TDFN-8
CAT4106HV4	Step-Up Boost	3	5.5	40	175	1000	10	4	TQFN-16
CAT4106YP	Step-Up Boost	3	5.5	40	175	1000	10	4	TSSOP-16
CAT4109V	Linear	3	25		525		7	3	SOIC-16
CAT4134HV2	Step-Up Boost	2.8	5.5	16	500	1000	3	2	TDFN-12
CAT4137TD	Step-Up Boost	2.2	5.5	24	30	1000	5		TSOT-23
CAT4139TD	Step-Up Boost	2.2	5.5	24	350	1000	5		TSOT-23
CAT4201TD	Step-Down Buck	7	36		350		7		TSOT-23
CAT4237TD	Step-Up Boost	2.8	5.5	30	100	1000	8		TSOT-23
CAT4238TD	Step-Up Boost	2	5.5	38	100	1000	10		TSOT-23
CAT4240TD	Step-Up Boost	2	5.5	38	350	1000	10		TSOT-23
NCL30000D	Flyback						72		SOIC-8
NCP5005SN	Step-Up	2.7	20	22	50	1200	5		TSOP-5
NCP5006SN	Step-Up	2.7	20	22		1200	5		TSOP-5
NCP5007SN	Step-Up	2.7	20	22	50	1200	5		TSOP-5
NCP5021MU									UGFN-16
NCP5030MT	Step-Up/Step-Down	2.7	5.5	5.5	1200	700	1		WDFN-12
NCP5050MT		2.7	5.5	20	1200	1700	5		WDFN-10
NCP5602MU	Charge Pump	2.7	5.5	5.5	60	1000		2	LLGA-12
NCP5603MN	Charge Pump	2.7	5.5	5.5	350	650	1	10	DFN-10
NCP5604AMT	Charge Pump	2.7	5.5		120	1000	1	4	QFN-16

DISPLAY/LED DRIVERS

Device	Topology	V _I Min (V)	V _I Max (V)	V _O Max (V)	I _O Max (mA)	f _{sw} Typ (kHz)	LEDs in Series, Max #	LEDs in Parallel, Max #	Package
NCP5604BMT	Charge Pump	2.7	5.5		120	1000	1	3	QFN-16
NCP5612MU	Charge Pump		5.5	5.5	60	1000		2	LLGA-12
NCP5623BMU	Charge Pump	2.7	5.5	5.5	80	1000000		3	LLGA-12
NCP5623CMU	Charge Pump				90	1000		3	LLGA-12
NCP5623DTB									TSSOP-14
NCP5680MU					500	1000			UQFN-24
NCP5890MU		2.7	5.5	34	25	1300	10	10	UQFN-16
NLSF595DT	Linear	1.8	7	5.5	8		1	8	TSSOP-16
NLSF595MN	Linear	1.8	7	5.5	8		1	8	QFN-16
NSI45020A	Linear		45		20		80		SOD-123
NSI45020	Linear		45		20		80		SOD-123
NSI45025A	Linear		45		25		80		SOD-123
NSI45025AZ	Linear		45		25		80		SOT-223
NSI45025	Linear		45		25		80		SOD-123
NSI45025Z	Linear		45		25		80		SOT-223
NSI45030A	Linear		45		30		80		SOD-123
NSI45030AZ	Linear		45		30		80		SOT-223
NSI45030	Linear		45		30		80		SOD-123
NSI45030Z	Linear		45		30		80		SOT-223
NSI50010Y	Linear		50		10		80		SOD-123
NUD4001D	Linear	3.6	30	28	500		8		SOIC-8
NUD4011D	Linear	3.6		200	70		100		SOIC-8

LOAD DRIVERS – DARLINGTON TRANSISTOR ARRAYS

Device	Number of Drivers	V _{CC} Max (V)	V _{(BR)GSS} Max (V)	V _{(BR)DSS} Max (V)	I _D Max (A)	r _{DS(on)} Max (Ω)	T _J Max (°C)	Package
MC1413BD	7	50	30	50	0.5	4.6	150	SOIC-16
MC1413BP	7	50	30	50	0.5	4.6	150	PDIP-16
MC1413D	7	50	30	50	0.5	4.6	150	SOIC-16
MC1413P	7	50	30	50	0.5	4.6	150	PDIP-16
NCV1413BD	7	50	30	50	0.5	4.6	150	SOIC-16
ULN2003AD	7	50	-	-	-	4.6	150	SOIC-16
ULQ2003AD	7	50	-	-	-	4.6	150	SOIC-16

RELAY DRIVERS

Device	Type	Number of Drivers	V _{CC} Max (V)	V _{(BR)GSS} Max (V)	V _{(BR)DSS} Max (V)	I _D Max (A)	r _{DS(on)} Max (Ω)	T _J Max (°C)	Package
MDC3105D	Dual 5 V	2	6	6	6.6	0.4	0.64	150	SC-74
MDC3105	Single 5 V	1	6	6	6.6	0.4	0.64	150	SOT-23
NUD3105D	Dual 5 V	2	6	6	6	0.5	0.9	150	SC-74
NUD3105	Single 5 V	1	6	6	6	0.5	0.9	150	SOT-23
NUD3112D	Dual 12 V	2	14	6	14	0.5	0.9	150	SC-74
NUD3112	Single 12 V	1	14	6	14	0.5	0.9	150	SOT-23
NUD3124D	Dual 24 V	2	28	12	28	0.15	0.8	150	SC-74
NUD3124	Single 24 V	1	28	12	28	0.15	0.8	150	SOT-23
NUD3160D	Dual 60 V	2	60	12	60	0.15	1.8	150	SC-74
NUD3160	Single 60 V	1	60	12	60	0.15	1.8	150	SOT-23

MOSFET/IGBT DRIVERS

Device	Configuration	Number of Drivers	V _{CC} Max (V)	Drive Source/ Sink Typ (mA)	Rise Time (ns)	Fall Time (ns)	t _p Max (ns)	Package
ADP3110A	Dual	2	13.2	1000 / 1000	40	20	65	DFN-8, SOIC-8
ADP3120A	Dual	2	13.2	1500 / 1500	20	16	70	DFN-8, SOIC-8
ADP3121	Dual	2	13.2	-	20	20	45	LFCSP-8, SOIC-8
ADP3419	Dual Synchronous	2	6	1000 / 1000	14	11	70	MSOP-10
ADP3611	Dual	-	-	-	-	-	-	DFN-8, Micro-10
MC33151	Dual Inverting	2	18	1500 / 1500	14	16	100	SOIC-8, PDIP-8
MC33152	Dual Non-Inverting	2	18	1500 / 1500	14	15	120	SOIC-8, PDIP-8
MC33153	Single	1	20	1000 / 2000	17	17	300	SOIC-8, PDIP-8
MC34151	Dual Inverting	2	18	1500 / 1500	14	16	100	SOIC-8, PDIP-8
MC34152	Dual Non-Inverting	2	18	1500 / 1500	14	15	120	SOIC-8, PDIP-8
NCP1392B	Half-Bridge	2	16	500/1000	40	20	500	SOIC-8
NCP1393B	Half-Bridge	2	16	500/1000	40	20	500	SOIC-8
NCP3420	Dual	2	13.2	-	16	11	45	DFN-8, SOIC-8
NCP5104	Single	2	20	250 / 500	85	35	170	SOIC-8, PDIP-8
NCP5106A	Dual	2	23	250 / 500	85	35	170	SOIC-8, PDIP-8
NCP5106B	Dual	2	23	250 / 500	85	35	170	SOIC-8, PDIP-8
NCP5111	Single	2	23	250 / 500	85	35	170	SOIC-8, PDIP-8
NCP5181	Dual	2	20	1400 / 2200	40	40	170	SOIC-8, PDIP-8
NCP5304	Dual	2	23	250 / 500	85	35	170	SOIC-8, PDIP-8
NCP5351	Dual	2	6.3	1400 / 2200	10	14	80	SOIC-8, DFN-10
NCP5359	Dual	2	15	1500 / 1500	16	11	35	SOIC-8, DFN-10
NCP5359A	Dual	2	13.2	1500/1500	16	15	30	DFN-8, SOIC-8
NCV7513	Hex Low-Side	6	5.25	1	1400	1400	1000	LQFP-32
NCV7517	Hex Low-Side	6	5.25	100 / 100	277	277	1000	LQFP-32
NCV7702B	Dual H-Bridge	4	16	1000 / 1000	10000	10000	10000	SOIC-24
NCV7703	Triple Half-Bridge	6	40	1500 / 1500	5000	2000	7500	SOIC-14
NCV7708B	Half-Bridge	-	5.25	-	-	-	-	SOIC-28
NCV33152	Dual Non-Inverting	2	18	1500 / 1500	15	36	120	SOIC-8

MOTOR DRIVERS

Device	Type	V _{CC} Min (V)	V _{CC} Max (V)	P _D Max (W)	I _O Max (A)	Package
AMIS30521	Stepper Motor Driver	6	40	1.28	1.6	NQFP-32
AMIS30522	Stepper Motor Driver	6	40	1.28	1.6	NQFP-32
AMIS30532	Stepper Motor Driver	6	30	2.27	3.2	NQFP-32
AMIS30542	Stepper Motor Driver	-	-	-	3.2	NQFP-32
AMIS30621	Stepper Motor Driver	-	-	-	-	NQFP-32, SOIC-20
AMIS30622	Stepper Motor Driver	6	40	0.32	0.8	NQFP-32, SOIC-20
AMIS30623	Stepper Motor Driver and Controller with LIN	6	40	0.32	0.8	SOIC-20, NQFP-32
AMIS30624	Stepper Motor Driver and Controller with I2C	6	40	0.32	0.8	SOIC-20, NQFP-32
CS3351	Alternator Voltage Regulator Darlington Driver	-	27	-	-	SOIC-14
CS3361	Alternator Voltage Regulator FET Driver	-	27	-	-	SOIC-14
CS8190	Precision Air-Core Tach/Speedo Driver with RTZ	8.5	15	-	0.01	SOIC-20, PDIP-16
MC33030	DC Servo Motor Controller	8	36	0.691	1	SOIC-16, PDIP-16
MC33033	Brushless DC 3-Phase Motor Controller	10	30	0.619	0.1	SOIC-20, PDIP-20
MC33035	Brushless DC 3-Phase Motor Controller	10	30	0.65	0.1	SOIC-24, PDIP-24
MC33039	Closed-Loop Brushless Motor Adapter	5.5	9	0.65	0.02	SOIC-8, PDIP-8
NCV33033	Brushless DC 3-Phase Motor Controller	10	30	0.619	0.1	SOIC-20
NCV33035	Brushless DC 3-Phase Motor Controller	10	30	0.65	0.1	SOIC-24
NCV33039	Closed-Loop Brushless Motor Adapter	5.5	9	0.65	0.02	SOIC-8
NCV70521	Stepper Motor Driver	6	40	0.104	1.5	NQFP-32
NCV70522	Stepper Motor Driver	-	-	-	-	NQFP-32
TDA1085C	Universal Motor Controller	15	16	1	0.2	PDIP-16

DSP Systems

DSP Systems

Table of Contents

	Page
Audio DSP Systems	224

AUDIO DSP SYSTEMS

Device	Type	DSP Core (bits)	Coprocessor Type	MIPS	Dynamic Range (dB)	RAM (kB)	I _{standby} Typ (µA)	Audio Inputs	Audio Outputs	Package
0W588-002-XUJP	BelaSigma® 200	16	WOLA	40	83	42	250	2	2	WLCSP-40
0W633-001-XTP	BelaSigma® 250	16	WOLA	60	88	42	50	2	2	LFBGA-57
0W888-002-XTP	BelaSigma® 250	16	WOLA	60	88	42	50	2	2	LFBGA-64
B250W48A106XXG	BelaSigma® 250	16	WOLA	60	88	42	50	2	2	WLCSP-48
B300W35A102XYG	BelaSigma® 300	24	HEAR	240	110	110	40	4	1	WLCSP-35

EMI/RFI Filters

EMI/RFI Filters

Table of Contents

	Page
Audio Filters	228
Data Filters	228
RC Parallel Interface Filters	230
LC Parallel Interface Filters	231
Application Specific Filters	231

ON Semiconductor Selector Guide – EMI/RFI Filters

AUDIO FILTERS

Device	Description	R Typ (Ω)	C Typ (pF)	IR Max (μ A)	V(BR) Typ (V)	VRWM Max (V)	Package
NUF2114MN	2 Line Audio EMI Filter with ESD Protection	8.4	60	0.1	15.7	12	DFN-8
NUF2116MN	2 Line Audio EMI Filter with ESD Protection	64	50	0.1	15.7	12	DFN-8
NUF2441FC	Integrated Passive Filter with ESD Protection	0.28	250	0.1	15	12	Flip-Chip-6
NUF2450MU	2 Line EMI Filter with ESD Protection	1.3	240	0.1	7	5	UDFN-8
NUF4220MN	4 Line Audio EMI Filter with ESD Protection	0.85	205	0.1	7	5	DFN-8
Device	Description	Architecture	F _{CO} (MHz)	Component Values			
CM1418-02CP	Audio Filter, Very Low Insertion Loss	C-L-C	22	100 pF – 3 nH – 100 pF			
CM1483-02DE	Audio Filter, Very Low Insertion Loss	C-L-C	22	100 pF – 3 nH – 100 pF			
CM1411	Audio Filter, Speaker	C-R-C	31	100 pF – 10 Ω – 100 pF			
CM1412	Audio Filter, Microphone	C-R-C	60	100 pF – 68 Ω – 100 pF			

DATA FILTERS

Device	Description	R Typ (Ω)	C Typ (pF)	I _R Max (μ A)	V _{BR} Typ (V)	VRWM Max (V)	Package
NUC2401MN	Integrated Common Mode Choke with ESD Protection	2.2	0.8	2	7.6	5	DFN-8
NUF2042XV6	USB Upstream Terminator with ESD Protection	22	42	0.01	6.8	5.25	SOT-563
NUF2101M	USB 1.1 Down Stream EMI Filter with ESD Protection	30	55	0.1	7	5.25	TSOP-6
NUF2221W1	Zener USB Upstream Terminator with ESD Protection	22	42	0.1	6.8	5.25	SC-88
NUF2222FC	2 Line USB 1.1 Upstream EMI Filter	33	36	0.1	7.6	5.6	Flip-Chip-8
NUF2230XV6	2 Line EMI Filter with ESD Protection	100	16	1	7	5	SOT-563
NUF3101FC	3 Line EMI Filter	47	18	0.1	7	5.6	Flip-Chip-8
NUF3102MU	Low Capacitance 3 Line EMI Filter	100	13	1	7	5	UDFN-8
NUF4000MU	4 Channel, 100 Ω , 17 pF	100	15	0.1	7	5	UDFN-8
NUF4001MU	Low Capacitance 4 Line EMI Filter with ESD Protection	100	13	0.1	7	5	UDFN-8
NUF4010MU	4 Channel, 100 Ω , 8.5 pF	100	7	0.1	7	5	UDFN-8
NUF4107FC	4 Channel EMI Pi-Filter Array with Full USB Filter	22	60	0.1	6.8	3.3	Flip-Chip-17
NUF4211MN	Low Capacitance 4 Line EMI Filter with ESD Protection	100	8.5	0.1	7	5	DFN-8
NUF4310MN	4 Channel EMI Filter with ESD Protection	100	18	0.1	7	5	WDFN-8
NUF4401MN	4 Line EMI Filter with ESD Protection	200	15	0.1	7	5	DFN-8
NUF4402MN	4 Line EMI Filter with ESD Protection	100	12	0.1	7	5	DFN-8

DATA FILTERS

Device	Description	R Typ (Ω)	C Typ (pF)	I _R Max (μ A)	V _{BR} Typ (V)	VRWM Max (V)	Package
NUF4403MN	4 Line EMI Filter with ESD Protection	100	17	0.1	7	5	DFN-8
NUF6001MU	6 Line EMI Filter with ESD Protection	100	17	0.1	7	5	UDFN-12
NUF6005MU	6 channel, 100 Ω , 12 pF	100	10	0.1	7	5	UDFN-12
NUF6010MU	6 Line EMI Filter with ESD Protection	100	7	0.1	6.8	5	UDFN-12
NUF6105FC	6 Channel EMI Pi-Filter Array with ESD Protection	100	53	0.1	7	3.3	Flip-Chip-15
NUF6106FC	6 Channel EMI Pi-Filter Array with ESD Protection	100	21	0.1	7	3.3	Flip-Chip-15
NUF6107MN	4 Channel Data Line EMI Filter	100	30	0.1	6.8	5	DFN-12
NUF6400MN	6 line EMI Filter	100	50	0.1	7	5	DFN-12
NUF6401MN	6 Line EMI Filter with ESD Protection	100	17	1	7	5	DFN-12
NUF6402MN	4 Line EMI Filter with ESD Protection	100	17	1	7	5	DFN-12
NUF6406MN	6 Line EMI Filter with ESD Protection	100	13	1	7	5	DFN-12
NUF6410MN	6 Line EMI Filter with ESD Protection	100	7	0.1	6.8	5	DFN-12
NUF8001MU	Low Capacitance 8 Line EMI Filter with ESD Protection	100	12	0.1	7	5	UDFN-16
NUF8010MU	8 Channel - Low Capacitance	100	7	0.1	7	5	UDFN-16
NUF8152MU	8 Line EMI Filter with ESD Protection	28	20	0.1	7	5	UDFN-16
NUF8401MN	Low Capacitance 8 Line EMI Filter with ESD Protection	100	12	0.1	7	5	DFN-16
NUF8402MN	8 Line EMI Filter with ESD Protection	100	17	0.1	7	5	DFN-16
NUF8410MN	Low Capacitance 8 Line EMI Filter with ESD Protection	100	8.5	0.1	7	5	DFN-16
NUF8600MN	8 Line EMI Filter with ESD	50	17	0.1	7	5	DFN-16
NUF8610MN	8 Line EMI Filter with ESD	50	8.5	0.1	7	6	DFN-16
NUF9001FC	10 Line EMI Filter	200	45	0.1	7	5	Flip-Chip-25
NUF9002FC	Low Capacitance 10 Line EMI Filter with ESD Protection	100	28	0.5	7	5	Flip-Chip-25
NZF220DF	EMI Filter with 6 V TVS Array, 2-Line	100	22	1	7	3	SC-88A
NZF220T	EMI Filter with 6 V TVS Array, 1-Line	100	22	1	7	3	SC-75
STF202-22	Upstream USB Port Filter & 6 V TVS Array, 2-Line	22	68	1	7	5.25	TSOP-6

RC PARALLEL INTERFACE FILTERS

Device	Description	R Typ (Ω)	C Typ (pF) (@ 2.5 V)	I _R Max (μ A)	V _{BR} Typ (V)	V _{CC} (V)	Package
CM1430-04DE	4 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	TDFN
CM1430-06DE	6 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	TDFN
CM1430-08DE	8 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	TDFN
CM1431-04DE	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	TDFN
CM1431-06DE	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	TDFN
CM1431-08DE	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	TDFN
CM1436-04DE	4 Channel EMI Filter Display and Camera	200	30	0.1	6.8	5	TDFN
CM1436-06DE	4 Channel EMI Filter Display and Camera	200	30	0.1	6.8	5	TDFN
CM1436-08DE	4 Channel EMI Filter Display and Camera	200	30	0.1	6.8	5	TDFN
CM1630-04DE	4 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	UDFN
CM1630-06DE	6 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	UDFN
CM1630-08DE	8 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	UDFN
CM1631-04DE	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	UDFN
CM1631-06DE	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	UDFN
CM1631-08DE	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	UDFN
CM1636-04DE	4 Channel EMI Filter Display and Camera	200	30	0.1	6.8	5	UDFN
CM1636-06DE	4 Channel EMI Filter Display and Camera	200	30	0.1	6.8	5	UDFN
CM1636-08DE	4 Channel EMI Filter Display and Camera	200	30	0.1	6.8	5	UDFN
CM1442-04CP	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	CSP
CM1442-06CP	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	CSP
CM1442-08CP	4 Channel EMI Filter Display and Camera	100	30	0.1	6.8	5	CSP
CM1443-04CP	4 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	CSP
CM1443-06CP	6 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	CSP
CM1443-08CP	8 Channel EMI Filter Low Cap	100	17	0.1	6.8	5	CSP

LC PARALLEL INTERFACE FILTERS

Device	Description	L Typ (nH)	C Typ (pF) (@ 2.5 V)	F _{co} (MHz)	Rise/Fall Time (ns)	V _{cc} (V)	Package
CM1693-04DE	LC EMI Filter 700 MHz Stopband	26	22	350	< 4	5	UDFN
CM1693-06DE	LC EMI Filter 700 MHz Stopband	26	22	350	< 4	5	UDFN
CM1693-08DE	LC EMI Filter 700 MHz Stopband	26	22	350	< 4	5	UDFN
CM1692-04DE	LC EMI Filter 800 MHz Stopband	17	24	250	< 5	5	UDFN
CM1692-06DE	LC EMI Filter 800 MHz Stopband	17	24	250	< 5	5	UDFN
CM1692-08DE	LC EMI Filter 800 MHz Stopband	17	24	250	< 5	5	UDFN
CM1690-04DE	LC EMI Filter 800 MHz Stopband	12	32	330	< 7	5	UDFN
CM1690-06DE	LC EMI Filter 800 MHz Stopband	12	32	330	< 7	5	UDFN
CM1690-08DE	LC EMI Filter 800 MHz Stopband	12	32	330	< 7	5	UDFN
CM1460-04DE	LC EMI Filter 800 MHz Stopband	17	30	350	< 8	5	TDFN
CM1460-06DE	LC EMI Filter 800 MHz Stopband	17	30	350	< 8	5	TDFN
CM1460-08DE	LC EMI Filter 800 MHz Stopband	17	30	350	< 8	5	TDFN
CM1461-04DE	LC EMI Filter 800 MHz Stopband	17	20	400	< 6	5	TDFN
CM1461-08DE	LC EMI Filter 800 MHz Stopband	17	20	400	< 6	5	TDFN
CM1457-04CP	LC EMI Filter 700 MHz Stopband	17	15	320	< 4	5	CSP
CM1457-06CP	LC EMI Filter 700 MHz Stopband	17	15	320	< 4	5	CSP
CM1457-08CP	LC EMI Filter 700 MHz Stopband	17	15	320	< 4	5	CSP
CM1453-04CP	LC EMI Filter 800 MHz Stopband	20	18	300	< 4	5	CSP
CM1457-06CP	LC EMI Filter 800 MHz Stopband	20	18	300	< 4	5	CSP
CM1457-08CP	LC EMI Filter 800 MHz Stopband	20	18	300	< 4	5	CSP

APPLICATION SPECIFIC FILTERS

Device	Description	π Filter Structure	F _{co} (MHz)	Rise/Fall Time (ns)	V _{cc} (V)	Package
CM1624-08DE	µSD High Capacity Interface	10 pF – 40 Ω – 20 nH – 10 pF	320	< 4	5	UDFN
CM6304	SIM Card EMI w/ESD	20 pF – 100/47 Ω – 20 pF	–	< 9	5	CSP
CM6300	SIM Card EMI w/ESD	20 pF – 100/47 Ω – 20 pF	–	< 9	5	CSP

IGBTs and FETs

IGBTs and FETs

Table of Contents

	Page
IGBTs	236
JFETs	237
High-Frequency Amplifiers	237
Switches and Choppers	237
MOSFETs	238
Protected MOSFETs	250

ON Semiconductor Selector Guide – IGBTs and FETs

IGBTs

Product	$V_{(BR)CES}$ Typ (V)	I_C Max (A)	$V_{CE(sat)}$ Typ (V)	E_{AS} Typ (μ J)	t_{sc} Min (ms)	P_D Max (W)	Package
NGB15N41CL	410	15	1.9	250000	–	107	D2PAK
NGD15N41CL	410	15	1.9	250000	250	107	DPAK
NGP15N41CL	410	15	1.9	250000	–	107	TO–220
NGB8202N	400	20	1.3	250000	–	150	D2PAK
NGD8201N	400	20	1.3	250000	–	125	DPAK
NGB8204N	400	18	1.8	400000	5	115	D2PAK
NGB18N40CLB	400	18	1.8	400000	0.0015	–	D2PAK
NGD18N40CLB	400	18	1.8	400000	0.04	115	DPAK
NGB8207AN	365	20	1.75	500000	–	165	D2PAK
NGB8207N	365	20	1.5	500000	–	165	D2PAK
NGB8206N	350	20	1.3	250000	–	150	D2PAK
NGD8205N	350	20	1.3	250000	–	125	DPAK

JFETs

HIGH-FREQUENCY AMPLIFIERS

N-Channel	$R_e Y_{fs} $ mmho Min	$R_e Y_{os} $ μmho Max	C_{iss} pF Max	C_{rss} pF Max	NF dB Max	V_{GS} V_{GDO} Volts Min	$V_{GS(off)}$ Volts		I_{DSS} mA		Package
							Min	Max	Min	Max	
J310	12 (Typ)	250 (Typ)	7.5	2.5	1.5 (Typ)	25	2.0	6.5	24	60	 TO-226AA, TO-92 Case 29-11
MMBFJ309L	10	250	5.0	2.5	4.0	25	1.0	4.0	12	30	 TO-236AB, SOT-23 Case 318-08
MMBFJ310L	8.0	250	5.0	2.5	4.0	25	2.0	6.5	24	60	
MMBFU310L	10	250	5.0	2.5	4.0	25	2.5	6.0	24	60	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

SWITCHES AND CHOPPERS

N-Channel	P-Channel	$R_{DS(on)}$ Ω Max	C_{iss} pF Max	C_{rss} pF Max	V_{GS} V_{GDO} Volts Min	$V_{GS(off)}$ Volts		I_{DSS} mA		t_{on} ns Max	t_{off} ns Max	Package
						Min	Max	Min	Max			
J112	-	50	28	5.0	35	1.0	5.0	5.0	-	-	-	 TO-226AA, TO-92 Case 29-11
MPF4393	-	100	10	3.5	30	-	12 (Typ)	5.0	30	15	55	
MMBF4391L	-	30	10	3.5	30	4.0	10	50	150	-	-	 TO-236AB, SOT-23 Case 318-08
MMBF4392L	-	60	10	3.5	30	2.0	5.0	25	75	-	-	
MMBF4393L	-	100	10	3.5	30	0.5	3.0	5.0	30	-	-	
-	MMBFJ175L	125	11	5.5	30	3.0	6.0	7.0	60	-	-	
-	MMBFJ177L	300	-	-	30	0.8	2.5	1.5	20	-	-	

Devices listed in **bold italic** are ON Semiconductor preferred devices.

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		
SOT-963 CASE 527AD									
Complementary									
20		1.5 / 5.0	2.0 / 6.0	3.0 / 7.0		0.16	0.13	NTUD3169C	C
N-Channel									
20		1.500	2.000	3.000		0.22	0.13	NTUD3170N	D
P-Channel									
20		5.000	6.000	7.000		0.20	0.13	NTUD3171P	D
SOT-723 CASE 631AA									
N-Channel									
20		0.550	0.700	0.900	1.50	0.81	0.28	NTK3134N	S
		8.000	13.000	20.000	1.50	0.18	0.31	NTK3043N	S
P-Channel									
20		0.900	1.200	2.000	1.50	0.54	0.28	NTK3139P	S
		3.400	5.300	10.000	1.50	0.26	0.28	NTK3142P	S
SC-75 CASE 463									
N-Channel									
20		0.230	0.275	0.070	1.82	0.92	0.30	NTA4153N	S
		3.000	3.500			0.24	0.30	NTA4001N	S
30		7.000	7.500			0.15	0.30	NTA7002N	S
P-Channel									
20		0.360	0.450	1.000	2.10	0.76	0.30	NTA4151P	S
SC-89 CASE 463C									
N-Channel									
20		0.230	0.275	0.700	1.82	0.92	0.31	NTE4153N	S
P-Channel									
20		0.360	0.450	1.000	2.10	0.76	0.31	NTE4151P	S
SOT-563 CASE 463A									
Complementary									
20		0.55/0.9	0.7/1.2	0.9/2.0	1.5/1.7	0.54 / 0.43	0.28	NTZD3155C	C
		0.55/0.9	0.7/1.2	0.9/2.0	1.5/1.7	0.54 / 0.43	0.28	NTZD3156C	C
N-Channel									
20		0.550	0.070	0.900	1.50	0.54	0.25	NTZD3154N	D
60		1.500			0.50	0.35	0.25	NTZD5110N	D
P-Channel									
20		0.900	1.200	2.000	1.70	0.43	0.28	NTZD3152P	D
		0.150	0.200	0.240	5.60	0.86	0.21	NTZS3151P	S
SC-70 CASE 419									
N-Channel									
20	1.000	1.400			1.40	0.30	0.15	MMBF2201N	S
25		0.350	0.400		1.20	0.75	0.28	NTS4409N	S

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		
SC-70 CASE 419									
N-Channel									
30		1.500	2.000		0.90	0.27	0.33	NTS4001N	S
60	1.000	1.500			0.50	0.35	0.33	2N7002W	S
P-Channel									
8		0.100	0.140	0.210	6.40	1.40	0.33	NTS2101P	S
20	2.200	3.500			2.70	0.30	0.15	MMBF2202P	S
		0.120	0.160		6.40	1.37	0.33	NTS4101P	S
30	0.200	0.200	0.280			1.20	0.29	NTS4173P	S
SC-88 (SOT-363) CASE 419B									
Complementary									
20 / 8		0.375 / 0.3	0.455 / 0.46	0.900	1.3 / 2.2	0.63 / 0.755	0.27	NTJD4105C	C
20 / 20		0.375 / 0.260	0.445 / 0.5		3.00	0.63 / 0.82	0.27	NTJD3158C	C
30 / 20		1.5 / 0.260	2.5 / 0.500		0.9 / 2.2	0.25 / 0.88	0.27	NTJD4158C	C
N-Channel									
20		0.375	0.445		1.30	0.63	0.27	NTJD4401N	D
		0.060	0.070	0.085	6.90	3.20	1.00	NTJS3157N	S
25		0.350	0.040		0.75	1.00	0.63	NTJS4405N	S
30		1.500	2.500		0.90	0.25	0.27	NTJD4001N	D
	0.060	0.085			2.75	2.60	0.62	NTJS4160N	S
60	1.600	2.500			0.70	0.32	0.27	NTJD5121N	D
P-Channel									
8		0.300	0.460	0.900	2.20	0.78	0.27	NTJD2152P	D
12		0.060	0.090	0.160	8.60	3.30	0.63	NTJS3151P	S
20		0.260	0.500	1.000	2.20	0.88	0.35	NTJD4152P	D
		0.060	0.085	0.205	10.00	4.20	1.00	NTJS4151P	S
P-Channel Load Switch									
8		0.175	0.220	0.320		1.30	0.40	NTJD1155L	L
SC-74 (SC-59ML) 6 LEAD CASE 318F-05									
P-Channel									
8	0.055				55.00	3.30	0.83	NTGD1100L	D
UDFN6, 1.6x1.6, 0.5P CASE 517AT									
N-Channel									
30	0.200				1.40	1.50	0.80	NTLUF4189NZ	D
P-Channel									
20	0.085				5.50	3.40	1.50	NTLUS3192PZ	S
	0.250				2.30	1.70	1.00	NTLUD3191PZ	D
30	0.095				3.10	3.00	0.60	NTLUS4195PZ	S

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		
WDFN6 2*2*.75 (μCool™) CASE 506AN									
Complementary									
20	0.065				3.70	4.60	2.30	NTLJD3119C	C
	0.100				4.60	3.20	1.50	NTLJD3183CZ	C
N-Channel									
30	0.070	0.070	0.090	0.125	5.40	3.70	0.71	NTLJD4116N	D
	0.070				5.40	4.00	2.08	NTLJF4156N	F
		0.035	0.045	0.055	8.50	7.80	1.92	NTLJS4114N	S
P-Channel									
8		0.036			15.70	8.10	3.30	NTLJS1102P	S
12		0.040			12.80	7.70	1.90	NTLJS2103P	S
	0.100					0.60	0.96	NUS1204MN	D
20		0.040			13.00	7.70	3.30	NTLJS3113P	S
		0.100	0.135	0.200	5.50	3.30	1.47	NTLJD3115P	D
	0.100				5.50	4.10	2.30	NTLJF3117P	F
TSOP-6 CASE 318G									
Complementary									
20		0.06 / 0.11	0.09 / 0.145	0.15/0. 22	5.20	3.5/2.7	1.10	NTGD3149C	C
30		0.09 / 0.17	0.125 / 0.3		3.70	2.9/2.2	1.10	NTGD4167C	C
N-Channel									
20		0.045	0.055		8.00	5.10	1.00	NTGS3446	S
		0.070	0.100		3.80	3.50	1.10	NTGD3148N	D
		0.024	0.032		13.20	6.20	1.40	NTGS3130N	S
30	0.025	0.035			12.00	7.00	1.00	NTGS4141N	S
P-Channel									
12	0.075				7.00	3.30	2.00	NTGS3433	S
20		0.033	0.040	0.051	18.00	5.80	1.60	NTGS3136P	S
		0.090	0.135		6.20	3.30	1.00	NTGS3441	S
		0.110	0.165		3.25	3.16	0.98	NTGS3441P	S
		0.065	1.000		7.50	4.40	1.00	NTGS3443	S
30	0.160	0.280			5.60	2.30	1.30	NTGD4161P	D
	0.100	0.170			9.00	3.50	1.00	NTGS3455	S
	0.060	0.110			15.25	4.70	1.25	NTGS4111P	S
60	0.110	0.142			18.10	2.90	1.40	NTGS5120P	S

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		
SOT-23 CASE 318									
N-Channel									
20	0.090	0.130			6.00	0.75	0.40	MGSF1N02L	S
		0.085	0.115		3.50	2.80	1.25	MGSF2N02EL	S
	1.100	1.400			1.40	0.30	0.23	MMBF0201NL	S
		0.080	0.105		2.40	3.20	1.25	NTR4501N	S
		0.050	0.063	0.087	7.30	4.00	1.25	NTR3161N	S
30	0.100	0.145			6.00	2.10	0.73	MGSF1N03L	S
		1.500	2.000		1.15	0.56	0.83	NTR4003N	S
	0.110	0.140			3.60	2.50	0.73	NTR4503N	S
	0.055	0.070	0.110		4.76	4.00	1.25	NTR4170N	S
50		3.500	10.000			0.20	0.23	BSS138L	S
60	7.500	7.500				0.12	0.23	2N7002L	S
	1.600	2.500			0.70	0.38	0.42	2N7002K	S
	2.500	3.000			0.81	0.31	0.30	2N7002E	S
	5.000					0.50	0.23	MMBF170L	S
100	6.000				0.17	0.23	BSS123L	S	
P-Channel									
8		0.052	0.072	0.120	12.00	3.70	0.96	NTR2101P	S
20	0.800	1.100			2.18	0.40	0.23	NTR0202PL	S
	0.180	0.280			2.50	1.00	0.40	NTR1P02	S
		0.200	0.350		5.50	1.30	0.40	NTR1P02L	S
		0.850	0.120	0.210	7.50	3.20	1.25	NTR4101P	S
		0.070	0.095	0.120	10.30	3.60	1.25	NTR3162P	S
30	0.075	0.110	0.150		15.60	3.50	1.25	NTR4171P	S
	0.200	0.350			6.00	1.95	1.25	NTR4502P	S
50		10.000			6.00	0.13	0.23	BSS84L	S
ChipFET™ CASE 1206A									
Complementary									
20		0.08 / 0.115	0.115 / 0.240		2.6/3.0	3.1 / 2.1	1.13	NTHC5513	C
		0.080	0.115 / 0.110		2.3/7.4	3.9 / 4.4	1.13	NTHD3100C	C
		0.045 / 0.080	0.050 / 0.110	0.070 / 0.15	7.9/8.9	5.5 / 4.2	1.13	NTHD3102C	C
N-Channel									
20		0.075	0.115		2.60	4.10	1.13	NTHD4508N	D
		0.065	0.105		4.00	4.50	1.13	NTHD5904N	D
		0.030	0.045		12.00	7.20	1.30	NTHS5404	S
30	0.022	0.077			9.20	4.80	1.50	NTHS4166N	S
	0.085	0.140			3.60	3.90	1.13	NTHD4502N	D

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		
ChipFET™ CASE 1206A									
P-Channel									
8		0.058	0.085	0.160	8.00	4.60	1.13	NTHD2102P	D
		0.025	0.036	0.048	15.00	7.50	1.30	NTHS2101P	S
20		0.080	0.110	0.170	7.60	4.10	1.13	NTHD4102P	D
		0.155	0.240		3.00	2.10	1.13	NTHD4401P	D
		0.034	0.040	0.052	25.00	6.70	1.30	NTHS4101P	S
		0.046	0.070		9.70	5.30	1.30	NTHS5441	S
		0.065	0.110		7.50	4.90	1.30	NTHS5443	S
FETKY® P-Channel									
20		0.080	0.110	0.170	7.40	4.40	2.10	NTHD3133P	F
		0.080	0.110	0.170	7.40	4.40	1.13	NTHD3101F	F
		0.155	0.240		3.00	4.40	1.13	NTHD4P02F	F
Micro8™ CASE 846A									
FETKY® P-Channel									
20		0.090	0.150		10.00	3.30	1.42	NTTD4401FR	F
DFN 6 3*3*.85 (μCool™) CASE 506									
N-Channel									
20		0.060			2.90	4.30	1.74	NTLGD3502N	D
P-Channel									
20		0.140	0.225		3.80	3.90	1.60	NTLGF3402P	F
SOT-223 CASE 318E									
N-Channel									
60	1.700				3.20	0.30	0.80	MMFT960	S
	0.110				10.60	3.00	2.10	NTF3055100	S
		0.120			7.60	3.00	2.10	NTF3055L108	S
		0.175			5.10	2.00	2.10	NTF3055L175	S
P-Channel									
20		0.050	0.070		15.00	10.00	8.30	NTF6P02	S
30	0.100	0.150			15.00	5.20	3.13	NTF5P03	S
60	0.170				14.30	2.60	2.30	NTF2955	S
SO-8 (MiniMOS™) CASE 751									
Complementary									
30	0.070 / 0.200	0.075 / 0.300			11.5 / 14.2	4.10	2.00	MMDF2C03HD	C
N-Channel									
20	0.090	0.100			12.50	3.80	2.00	MMDF3N02HD	D
		0.035	0.048		12.00	6.50	2.00	NTMD6N02	D
	0.023	0.028			26.00	6.50	2.50	NTMS7N03	S
25	0.100	0.200			10.60	3.60	2.00	MMDF2N02E	D
28	0.008	0.010			23.00	14.00	2.50	NTMS4503N	S

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		
SO-8 (MiniMOS™) CASE 751									
N-Channel									
30	0.004	0.006			36.00	15.00	1.66	NTMS4802N	S
	0.004	0.006			26.30	17.00	2.12	NTMS4920N	S
	0.005	0.006			45.00	18.00	2.50	NTMS4107N	S
	0.005	0.007			23.30	16.00	2.10	NTMS4935N	S
	0.006	0.008			24.00	9.80	1.55	NTMS4807N	S
	0.007	0.009			17.40	13.60	2.00	NTMS4937N	S
	0.008	0.011			12.40	12.50	2.00	NTMS4939N	S
	0.009	0.013			12.20	9.90	1.41	NTMS4801N	S
	0.010	0.016			9.20	7.20	1.37	NTMS4816N	S
	0.014	0.017			10.00	6.40	1.49	NTMS4872N	S
	0.020	0.027			7.70	5.10	1.28	NTMD4820N	D
	0.020	0.027			7.70	6.40	1.29	NTMS4800N	S
0.024	0.036			5.20	4.40	1.14	NTMD4840N	D	
40	0.080	0.100			13.90	3.40	2.00	MMDF3N04HD	D
	0.034	0.043			20.00	5.80	2.00	NTMD6N04R2	D
50	0.300	0.500			12.50	2.00	2.00	MMDF1N05E	D
80	0.215	0.245			5.00	1.20	1.00	NTMD6601N	D
P-Channel									
16		0.100	0.150		10.00	3.85	2.00	NTMD2P01	D
20	0.160	0.180			15.00	3.30	2.00	MMDF2P02HD	D
	0.075	0.095			33.00	5.60	2.50	MMSF3P02HD	S
		0.033	0.050		20.00	7.80	2.00	NTMD6P02	D
		0.014	0.020		48.00	10.00	2.50	NTMS10P02	S
		0.033	0.048		20.00	7.00	2.50	NTMS5P02	S
30	0.018	0.030			17.00	5.80	1.44	NTMS4176P	S
	0.012	0.019			29.00	7.10	1.52	NTMS4177P	S
	0.035	0.050	35.000		37.90	7.00	2.50	MMSF7P03HD	S
FETKY® N-Channel									
30	0.032	0.040			19.00	6.00	2.00	NTMD6N03	F
	0.032	0.040			19.00	6.00	2.00	NTMSD6N303	F
	0.048	0.070			2.80	3.80	1.60	NTMD4884N	F
	0.012	0.015			10.50	7.20	1.39	NTMS4873N	F
FETKY® P-Channel									
30	0.095	0.165			2.80	2.60	1.60	NTMD4184P	F
	0.085	0.125			16.00	3.86	2.00	NTMSD3P303	F

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		

WDFN8 3.3 x 3.3, 0.65P (U8FL) CASE 511AB

N-Channel									
30	0.004	0.006			20.00	79.00	2.20	NTTFS4932N	S
	0.005	0.007			15.70	75.00	4.60	NTTFS4937N	S
	0.005	0.008			12.60	69.00	2.20	NTTFS4824N	S
	0.006	0.009			12.40	56.00	4.48	NTTFS4939N	S
	0.006	0.011			10.10	46.00	4.42	NTTFS4941N	S
	0.007	0.011			10.50	57.00	2.10	NTTFS4821N	S
	0.007	0.011			9.20	41.00	4.35	NTTFS4943N	S
	0.009	0.013			7.70	34.00	4.30	NTTFS4945N	S
	0.011	0.018			6.50	50.00	2.10	NTTFS4823N	S
	0.012	0.015			15.00	37.00	2.70	NTTFS5820NL	S
	0.020	0.025			7.70	32.00	2.04	NTTFS4800N	S
	0.024	0.036			5.20	26.00	2.04	NTTFS4840N	S

SO-8FL CASE 488

N-Channel									
30	0.002	0.003			39.00	191.00	125.00	NTMFS4833N	S
	0.002	0.003			34.30	155.00	86.20	NTMFS4852N	S
	0.002	0.003			47.00	35.00	6.30	NTMFS4108N	S
	0.003	0.004			25.60	5.80	2.27	NTMFS4845N	S
	0.003	0.004			32.00	130.00	86.20	NTMFS4834N	S
	0.003	0.006			20.00	90.00	55.60	NTMFS4836N	S
	0.003	0.004			22.90	93.00	48.00	NTMFS4935N	S
	0.003	0.005			21.80	20.30	2.25	NTMFS4846N	S
	0.004	0.005			37.00	30.00	6.10	NTMFS4119N	S
	0.004	0.005			22.00	104.00	62.50	NTMFS4835N	S
	0.004	0.006			15.50	79.00	43.00	NTMFS4936N	S
	0.004	0.006			19.20	18.00	2.21	NTMFS4847N	S
	0.005	0.007			15.90	70.00	43.00	NTMFS4937N	S
	0.005	0.008			14.20	74.00	47.20	NTMFS4837N	S
	0.005	0.008			15.00	16.10	2.17	NTMFS4849N	S
	0.005	0.007			24.00	29.00	6.60	NTMFS4121N	S

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		
SO-8FL CASE 488									
N-Channel									
30	0.006	0.010			13.00	66.00	41.70	NTMFS4839N	S
	0.006	0.800			12.70	53.00	30.00	NTMFS4939N	S
	0.006	0.009			13.50	15.00	2.16	NTMFS4851N	S
	0.006	0.009			11.30	47.00	25.50	NTMFS4941N	S
	0.007	10.800			10.70	58.50	5.60	NTMFS4921N	S
	0.007	0.001			10.70	10.00	2.14	NTMFS4821N	S
	0.007	0.011			11.50	57.00	41.70	NTMFS4841N	S
	0.007	0.011			9.20	41.00	22.30	NTMFS4943N	S
	0.009	0.013			7.80	35.00	19.80	NTMFS4945N	S
	0.010	0.014			10.00	11.00	2.20	NTMFS4744N	S
0.011	0.018			6.00	30.00	32.50	NTMFS4823N	S	
N-Channel with Integrated Schottky									
30	0.002	0.003			39.60	171.00	125.00	NTMFS4897NF	F
	0.003	0.005			25.60	117.00	74.00	NTMFS4898NF	F
	0.005	0.008			15.00	75.00	7.18	NTMFS4899NF	F
DPAK (TO252) CASE 369X *									
N-Channel									
24	0.005	0.006			23.60	32.00	110.00	NTD110N02	S
	0.005	0.008			21.00	32.00	86.00	NTD95N02R	S
	0.005	0.007			17.70	32.00	78.10	NTD85N02R	S
	0.006	0.009			30.00	80.00	75.00	NTD80N02	S
25	0.005	0.007			18.00	16.80	2.14	NTD4856N	S
	0.006	0.008			16.00	15.00	2.10	NTD4857N	S
	0.006	0.008			25.50	78.00	64.00	NTD78N03	S
	0.006	0.009			12.80	14.00	2.00	NTD4858N	S
	0.008	0.011			11.00	13.00	2.00	NTD4860N	S
	0.008	0.013			13.20	32.00	62.50	NTD70N03R	S
	0.009	0.014			9.00	11.30	1.95	NTD4863N	S
	0.011	0.013			9.50	32.00	58.00	NTD60N02R	S
	0.011	0.017			7.20	10.50	1.92	NTD4865N	S
	0.017	0.023			5.78	32.00	50.00	NTD40N03R	S
	0.043	0.006			21.80	18.00	2.24	NTD4855N	S
	0.045	0.060			3.76	17.10	22.30	NTD23N03R	S
0.095	0.130			1.80	14.00	20.80	NTD14N03R	S	

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		
DPAK (TO252) CASE 369X *									
N-Channel									
30	0.004	0.006			18.80	79.00	52.00	NTD4904N	S
	0.004	0.006			30.00	117.00	93.75	NTD4804N	S
	0.005	0.007			14.00	67.00	44.00	NTD4905N	S
	0.005	0.007			20.50	88.00	66.00	NTD4805N	S
	0.006	0.008			11.00	54.00	37.50	NTD4906N	S
	0.006	0.009			15.00	76.00	60.00	NTD4806N	S
	0.008	0.012			11.30	63.00	54.60	NTD4808N	S
	0.008	0.012			7.60	41.00	29.40	NTD4909N	S
	0.008	0.013			11.00	55.00	35.70	NTD4960N	S
	0.009	0.014			10.70	58.00	52.00	NTD4809N	S
	0.009	0.013			12.50	58.00	52.00	NTD4809NH	S
	0.009	0.013			6.80	37.00	27.30	NTD4910N	S
	0.010	0.016			9.00	44.00	35.70	NTD4963N	S
	0.010	0.013			55.00	68.00	75.00	NTD4302	S
	0.010	0.016			9.00	54.00	50.00	NTD4810N	S
	0.010	0.017			8.90	54.00	50.00	NTD4810NH	S
	0.011	0.015			6.20	32.00	24.00	NTD4913N	S
	0.013	0.024			6.90	40.00	35.30	NTD4813N	S
	0.013	0.026			7.10	40.00	35.30	NTD4813NH	S
	0.015	0.025			6.00	35.00	32.60	NTD4815N	S
0.015	0.028			6.40	35.00	32.60	NTD4815NH	S	
0.031	0.027			13.80	20.00	74.00	NTD20N03L27	S	
40	0.004	0.008			75.00	78.00	93.75	NTD5802N	S
	0.007	0.010			51.00	75.00	83.00	NTD5803N	S
	0.009	0.012			45.00	69.00	71.00	NTD5804N	S
	0.010	0.016			33.00	51.00	47.00	NTD5805N	S
	0.010	0.017			45.00	70.00	100.00	NTD5406N	S
	0.019	0.026			17.00	33.00	39.00	NTD5806N	S
	0.026	0.040			20.00	38.00	75.00	NTD5407N	S
	0.031	0.370			12.60	23.00	33.00	NTD5807N	S

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		

DPAK (TO252) CASE 369X *

N-Channel									
60	0.060				15.30	18.00	55.00	NTD18N06	S
		0.065			11.00	18.00	55.00	NTD18N06L	S
	0.046				21.20	20.00	60.00	NTD20N06	S
		0.048			16.60	20.00	60.00	NTD20N06L	S
	0.042				24.00	24.00	62.50	NTD24N06	S
		0.045			16.00	24.00	62.50	NTD24N06L	S
	0.094				10.90	12.00	48.00	NTD3055094	S
	0.150				7.10	9.00	28.80	NTD3055150	S
		0.104			7.40	12.00	48.00	NTD3055L104	S
		0.170			4.70	9.00	28.50	NTD3055L170	S
	0.026				35.00	30.00	68.00	NTD5413N	S
	0.037				25.00	24.00	55.00	NTD5414N	S
	0.039				10.00	19.00	30.00	NTD5867NL	S
		0.028			23.00	32.00	93.75	NTD32N06L	S
	0.750				1.00	40.00	MLD1N06CL	S	
62	0.400					2.00	40.00	MLD2N06CL	S
65	0.210					11.00	2.50	NID6002N	S
100	0.037				40.00	32.00	100.00	NTD6414AN	S
	0.052	0.056			20.00	23.00	83.00	NTD6415ANL	S
	0.055				29.00	23.00	83.00	NTD6415AN	S
	0.074	0.080			25.00	19.00	71.00	NTD6416ANL	S
	0.081				20.00	17.00	71.00	NTD6416AN	S
	0.165				14.00	12.00	53.60	NTD12N10	S
		0.146			11.30	12.00	56.60	NTD6600N	S
150	0.300				15.00	6.00	20.00	MTD6N15	S
200	0.700				13.70	6.00	50.00	MTD6N20E	S
500	1.500				18.50	4.70	83.00	NDD05N50Z	S
600	4.800				10.10	2.20	57.00	NDD02N60Z	S
	3.600				12.00	2.60	61.00	NDD03N60Z	S
	2.000				19.00	4.00	28.00	NDD04N60Z	S
P-Channel									
30		0.072			13.00	25.00	75.00	NTD25P03L	S
60	0.450				12.00	5.00	40.00	MTD5P06V	S
		0.150			15.00	15.50	54.00	NTD20P06L	S
	0.180				15.00	12.00	55.00	NTD2955	S

D2PAK (TO264) CASE 418B

N-Channel									
20	0.006	0.009			29.00	90.00	85.00	NTB90N02	S
30	0.008	0.013			13.20	75.00	74.40	NTB75N03R	S
		0.008			57.00	75.00	125.00	NTB75N03L09	S

MOSFETs

MOSFET SURFACE MOUNT									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		

D2PAK (TO264) CASE 418B

N-Channel									
40	4.500	7.000			125.00	136.00	167.00	NTB5404N	S
	5.800	8.000			88.00	116.00	150.00	NTB5405N	S
60	0.010				92.00	80.00	166.00	NTB5411N	S
	0.014				66.00	60.00	125.00	NTB5412N	S
		0.100			7.30	15.00	48.40	NTB18N06L	S
		0.046			16.00	30.00	88.20	NTB30N06L	S
	0.026				33.00	45.00	125.00	NTB45N06	S
		0.028			23.00	45.00	125.00	NTB45N06L	S
	0.014				62.00	60.00	150.00	NTB60N06	S
		0.016			43.20	60.00	150.00	NTB60N06L	S
100	0.095				92.00	75.00	214.00	NTB75N06	S
	0.001				120.00	76.00	188.00	NTB6410AN	S
	0.014				100.00	72.00	188.00	NTB6411AN	S
	0.018				73.00	58.00	187.00	NTB6412AN	S
	0.028				51.00	42.00	136.00	NTB6413AN	S
150	0.030				72.00	52.00	178.00	NTB52N10	S
	0.050				70.00	37.00	178.00	NTB35N15	S
200	0.081				75.00	30.00	214.00	NTB30N20	S
P-Channel									
30			25.000			50.00	125.00	MTB50P03HDL	S
60			80.000			30.00	125.00	MTB30P06V	S
	0.075				33.00	27.50	120.00	NTB25P06	S
500					13.00	18.50	88.00	NTB5605P	S
			6.000			2.00	2.50	MTB2P50E	S

ICEPAK CASE 145AX *

N-Channel									
25	0.002	0.002			51.30	160.00	65.00	NTMKE4894N	S
	0.003	0.004			29.50	129.00	65.00	NTMKE4891N	S
	0.005	0.008			13.10	90.00	65.00	NTMKB4893N	S
30	0.002	0.002			51.70	147.00	65.00	NTMKC4890N	S
	0.002	0.002			51.70	147.00	65.00	NTMKE4890N	S
	0.003	0.005			31.90	126.00	65.00	NTMKE4892N	S
	0.007	0.011			10.00	82.00	65.00	NTMKB4895N	S
	0.008	0.012			10.90	70.00	65.00	NTMKB4896N	S

MOSFETs

MOSFET THROUGH HOLE									
V _{DSS} (V)	R _{DS(on)} MAX (Ω) @ V _{GS} =				Q _g Typ (nC) @ V _{GS} = 4.5 V (5.0 V) / 10 V	Max Rating		Device	Config.
	10 V	4.5 V / 5.0 V	2.5 V / 2.7 V	1.8 V / 1.65 V		I _D (A)	P _D (W)		

TO-92 CASE 29

N-Channel									
60	5.000	6.000				0.20	0.35	2N7000	S
	5.000					0.50	0.35	BS170	S
	7.500					0.15	0.40	VN2222LL	S
200	14.000		28.000			0.25	0.35	BS107	S
	6.000					0.25	0.35	BS107A	S
			10.000			0.25	0.35	BS108	S
240	10.000					0.20	0.35	VN2410L	S

TO-220AB CASE 221A

N-Channel									
40	4.500				125.00	136.00	167.00	NTP5404NR	S
60	6.000				150.00	120.00	214.00	NTP5426N	S
	10.000				92.00	80.00	166.00	NTP5411N	S
	14.000				66.00	60.00	125.00	NTP5412N	S
100	13.000				120.00	76.00	188.00	NTP6410AN	S
	14.000				100.00	72.00	188.00	NTP6411AN	S
	18.200				73.00	58.00	167.00	NTP6412AN	S
	28.000				51.00	42.00	136.00	NTP6413AN	S
150	0.050				70.00	37.00	178.00	NTP35N15	S
	0.130				39.10	20.00	112.00	MTP20N15E	S
P-Channel									
30		0.025			74.00	50.00	125.00	MTP50P03HDL	S
60	0.196				14.00	12.00	62.50	NTP2955	S
500	6.000				19.00	2.00	75.00	MTP2P50E	S

TO-220FP CASE 221D

N-Channel									
500	0.850				31.00	7.50	31.00	NDF08N50ZG	S
	1.500				18.50	5.00	28.00	NDF05N50ZG	S
600	0.750				47.00	10.00	36.00	NDF10N60ZG	S
	1.200				31.00	6.00	31.00	NDF06N60ZG	S
	2.000				19.00	4.00	28.00	NDF04N60ZG	S
	3.600				12.00	3.00	24.00	NDF03N60ZG	S
	4.800				10.10	2.40	23.00	NDF02N60ZG	S
620	2.000				19.00	4.40	28.00	NDF04N62ZG	S

TO-247 CASE 340K

N-Channel									
200	0.075				85.0	32.00	180.00	MTW32N20E	S

PROTECTED MOSFETS

Product	Channel Polarity	$V_{(BR)DSS}$ Min (V)	I_D Typ (A)	$R_{DS(on)}$ Max (m Ω)	P_D Max (W)	Package
MLD1N06CL	N Channel	60		750	40	DPAK-4
NCV8401D	N Channel	42	33	23	1.56	DPAK-4
NCV8402D	N Channel	42	2	165	1.62	SOIC-8
NCV8402	N Channel	42	2	165	8.9	SOT-223
NCV8403	N Channel	42	15	53	1.9	DPAK-4, SOT-223
NCV8405	N Channel	42	6	100	1.7	SOT-223
NCV8440	N Channel	52	2.6	95	1.69	SOT-223
NCV8450	-	45	0.8	1000	1.7	SOT-223
NID5004N	N Channel	36	6.5	130	2.5	DPAK-4
NID6002N	N Channel	65	6.5	210	2.5	DPAK-4
NID9N05CL	N Channel	52	9	181	28.8	DPAK-4
NIF9N05CL	N Channel	52	2.6	125	1.69	SOT-223
NILMS4501N	N Channel	24	9.5	13	2.7	PLLP-4
NIMD6001N	N Channel	60	3	130		SOIC-8
NUD4700SN	-	-	-	-	-	POWERMITE

Interfaces

Interfaces

Table of Contents

	Page
Data Transmitters and Transceivers	254
HART and MAU	254
LIN and CAN Transceivers	254
EIA Transceivers	255
I/O Expanders	256
Modulators/Demodulators	256
Sensor Interfaces	256
SMART and SIM Card Interfaces	257

DATA TRANSMITTERS AND TRANSCEIVERS

HART AND MAU

Device	Description	Data Transmission Standard	V _{CC} Min (V)	V _{CC} Max (V)	t _{PLH} Max (μs)	I _O Max (μA)	I _{IH} Max (mA)	Package
A5191HRT	Industrial HART – Protocol Modem	HART	3	5.5	0.02	670	0.0005	LQFP–32
AMIS–49200	Fieldbus Phys Layer Medium Access Unit (MAU)	MAU	4.75	6.2	4.7	30000	0.001	LQFP–44
AMIS–49250	Fieldbus Phys Layer Medium Access Unit (MAU)	MAU	4.75	6.2	4.7	30000	0.001	NQPP–44

LIN AND CAN TRANSCEIVERS

Device	Description	Data Transmission Standard	V _{CC} Min (V)	V _{CC} Max (V)	t _{PLH} Max (μs)	I _O Max (μA)	I _{IH} Max (mA)	Package
AMIS–30600	LIN Transceiver	LIN	7.3	18	50	40000	0.7	SOIC–8
AMIS–30660	CAN High-Speed Transceiver	CAN	4.75	5.25	1	45000	8	SOIC–8
AMIS–30663	CAN High-Speed Transceiver	CAN	4.75	5.25	1	45000	8	SOIC–8
AMIS–41682	Fault Tolerant CAN Transceiver	CAN	4.75	5.25	8	45000	6.3	SOIC–14
AMIS–41683	Fault Tolerant CAN Transceiver	CAN	4.75	5.25	8	45000	6.3	SOIC–14
AMIS–42665	High-Speed Low Power CAN Transceiver	CAN	4.75	5.25	1	45000	8	SOIC–14
AMIS–42670	High-Speed CAN Transceiver for Long Networks	CAN	4.75	5.25	1	45000	8	SOIC–8
AMIS–42671	High-Speed CAN Transceiver for Long Networks	CAN	4.75	5.25	1	45000	8	SOIC–8
AMIS–42673	High-Speed CAN Transceiver for Long Networks	CAN	4.75	5.25	1	45000	8	SOIC–8
AMIS–42675	High-Speed Low Power CAN Transceiver	CAN	4.75	5.25	1	45000	8	SOIC–8
AMIS–42770	Dual High-Speed Can Transceiver for Long Networks	CAN	4.75	5.25	1	45000	19.5	SOIC–20
NCV7321	Stand Alone LIN Transceiver	LIN	5	27	–	–	–	SOIC–8
NCV7341	High-Speed, Low Power CAN Transceiver	CAN	4.75	5.25	–	–	–	SOIC–14
NCV7356D1	Single Wire CAN	CAN	–0.3	18	6.3	350000	0.05	SOIC–8, SOIC–14
NCV7361A	Voltage Regulator with Integrated LIN Transceiver	LIN	5.25	18	6	120000	0.11	SOIC–8
NCV7420D23	LIN Transceiver with 3.3 V Voltage Regulator	LIN	–	–	–	–	–	SOIC–14
NCV7420D25	LIN Transceiver with 5.0 V Voltage Regulator	LIN	–	–	–	–	–	SOIC–14

DATA TRANSMITTERS AND TRANSCEIVERS (continued)

EIA TRANSCEIVERS

Device	Data Transmission Standard	Number of Drivers	Number of Receivers	V _{CC} Min (V)	V _{CC} Max (V)	t _{PLH} Max (μs)	I _O Max (μA)	I _{IH} Max (mA)	Package
MC1488D	EIA-232D	4	-	9	15	0.35	12000	0.01	SOIC-14
MC1488M	EIA-232D	4	-	9	15	0.35	12000	0.01	SOEIAJ-14
MC1488P	EIA-232D	4	-	9	15	0.35	12000	0.01	PDIP-14
MC1489AD	EIA-232D	-	4	2.5	10	0.085	4000	8.3	SOIC-14
MC1489AM	EIA-232D	-	4	2.5	10	0.083	4000	8.3	SOEIAJ-14
MC1489AP	EIA-232D	-	4	2.5	10	0.085	4000	8.3	PDIP-14
MC1489D	EIA-232D	-	4	2.5	10	0.085	4000	8.3	SOIC-14
MC1489M	EIA-232D	-	4	2.5	10	0.085	4000	8.3	SOEIAJ-14
MC1489P	EIA-232D	-	4	2.5	10	0.085	4000	8.3	PDIP-14
MC26LS30D	EIA-422/423	-	4	-0.5	7	0.01	65000	0.04	SOIC-16
MC3488AD	EIA-423 / EIA-232D	2	-	10.8	13.2	140	150000	0.1	SOIC-8
MC3488AP1	EIA-423 / EIA-232D	2	-	10.8	13.2	140	150000	0.1	PDIP-8
MC75172BDW	EIA-485	4	-	4.75	5.25	0.03	65000	0.02	SOIC-20
MC75174BDW	EIA-485	4	-	4.75	5.25	0.03	65000	0.02	SOIC-20
MC75174BP	EIA-485	4	-	4.75	5.25	0.03	65000	0.02	PDIP-16

I/O EXPANDERS

Product	I/O	Cascadable	V _{CC} Min (V)	V _{CC} Max (V)	Interrupt Output	I/O Pullups	LED Blink/PWM	I _O Min (mA)	Package
CAT9532HV6I	16	8 Slave ID Addresses	2.3	5.5	No	No	Yes	25	TQFN-24
CAT9532WI	16	8 Slave ID Addresses	2.3	5.5	No	No	Yes	25	SOIC-24
CAT9532YI	16	8 Slave ID Addresses	2.3	5.5	No	No	Yes	25	TSSOP-24
CAT9534HV4I	8	8 Slave ID Addresses	2.3	5.5	Yes	No	No	10	TQFN-16
CAT9534WI	8	8 Slave ID Addresses	2.3	5.5	Yes	No	No	10	SOIC-16
CAT9534YI	8	8 Slave ID Addresses	2.3	5.5	Yes	No	No	10	TSSOP-16
CAT9552HV6I	16	8 Slave ID Addresses	2.3	5.5	No	No	Yes	25	TQFN-24
CAT9552WI	16	8 Slave ID Addresses	2.3	5.5	No	No	Yes	25	SOIC-24
CAT9552YI	16	8 Slave ID Addresses	2.3	5.5	No	No	Yes	25	TSSOP-24
CAT9554AHV4I	8	8 Slave ID Addresses	2.3	5.5	Yes	Yes	No	10	TQFN-16
CAT9554AWI	8	8 Slave ID Addresses	2.3	5.5	Yes	Yes	No	10	SOIC-16
CAT9554AYI	8	8 Slave ID Addresses	2.3	5.5	Yes	Yes	No	10	TSSOP-16
CAT9554HV4I	8	8 Slave ID Addresses	2.3	5.5	Yes	Yes	No	10	TQFN-16
CAT9554WI	8	8 Slave ID Addresses	2.3	5.5	Yes	Yes	No	10	SOIC-16
CAT9554YI	8	8 Slave ID Addresses	2.3	5.5	Yes	Yes	No	10	TSSOP-16
JLC1562BF	8	-	4.2	6	No	No	-	-	SOEIAJ-16
JLC1562BN	8	-	4.2	6	No	No	-	-	PDIP-16

MODULATORS/DEMULATORS

Device	Z _{is} Typ (kΩ)	Z _{os} Typ (kΩ)	V _{CFT} Typ (μV)	V _{CS} Typ (mV)	A _{VS} Typ (V)	BW Typ (MHz)	I _B Typ (μA)	ACM Typ (dB)	T _A Min (°C)	T _A Max (°C)	Package
MC1496	200	40	20	65	3.5	300	12	85	0	70	SOIC-14
MC1496B	200	40	20	65	3.5	300	12	85	-40	125	SOIC-14

SENSOR INTERFACES

Device	Channels	V _{CC} Min (V)	V _{CC} Max (V)	I _T Max (mA)	V _I Typ (V)	T _A Min (°C)	T _A Max (°C)	Package
NCV1124	2	4.5	5.5	5	250	-40	125	SOIC-8

SMART AND SIM CARD INTERFACES

Device	Description	V _{CC} Min (V)	V _{CC} Max (V)	I _T Typ (mA)	I _{I(standby)} Max (μA)	f _{Clock} Max (MHz)	Package
NCN4555	SIM Card Power Supply/Level Translator	1.8	5.5	0.03	4	5	QFN-16
NCN4557	Dual SIM / Smart Card Interface	1.8	5.5	0.03	3	5	QFN-16
NCN6001	Compact Smart Card Interface	2.7	6	0.5	60	40	TSSOP-20
NCN6004A	Dual Asynchronous/Synchronous Smart Card Interface	1.8	5.5	–	50	–	TQFP-48
NCN6024	Compact Smart Card Interface	–	–	–	1000	20	TSSOP-28
NCN6804	Dual Smart Card Interface	2.7	5.5	0.1	100	40	QFN-32

Memory

Memory

Table of Contents

	Page
Serial SRAM	262
Parallel SRAM	262
Serial EEPROM	263
Parallel EEPROM	265
Flash	265
NVRAM	265

SERIAL SRAM

Device	Density	Organization (Bits)	Data Transmission Standard	$f_{\text{cycle Max}}$ (MHz)	$V_{\text{cc Min}}$ (V)	$V_{\text{cc Max}}$ (V)	$I_{\text{standby Typ}}$ (μA)	$I_{\text{standby Max}}$ (μA)	Package
N25S818HA	256 kb	32k x 8	SPI	16	1.7	1.95	0.2	0.5	TSSOP-8, SOIC-8
N25S830HA	256 kb	32k x 8	SPI	20	2.7	3.6	1	4	TSSOP-8, SOIC-8
N64S818HA	64 kb	8k x 8	SPI	16	1.7	1.95	0.2	0.5	TSSOP-8, SOIC-8
N64S830HA	64 kb	8k x 8	SPI	20	2.7	3.6	1	4	TSSOP-8, SOIC-8

PARALLEL SRAM

Device	Density	Organization (Bits)	$t_{\text{Acc Max}}$ (ns)	$V_{\text{cc Min}}$ (V)	$V_{\text{cc Max}}$ (V)	$I_{\text{standby Typ}}$ (μA)	$I_{\text{standby Max}}$ (μA)	Package
N08L6182A	8 Mb	512k x 16	70	1.65	2.2	0.5	20	BGA-48
N08L63W2A	8 Mb	512k x 16	70	2.3	3.6	4	20	BGA-48
N04L63W1A	4 Mb	256k x 16	70	2.3	3.6	4	20	BGA-48, TSOP-44
N04L63W2A	4 Mb	256k x 16	70	2.3	3.6	4	20	BGA-48, TSOP-44
N02L6181A	2 Mb	128k x 16	70	1.65	2.2	0.5	10	BGA-48
N02L63W2A	2 Mb	128k x 16	55	2.3	3.6	2	20	BGA-48, TSOP-44
N02L63W3A	2 Mb	128k x 16	55	2.3	3.6	2	20	BGA-48, TSOP-44
N02L83W2A	2 Mb	256k x 8	55	2.3	3.6	2	20	TSOP-32, STSOP-32
N01L83W2A	1 Mb	128k x 8	55	2.3	3.6	2	20	TSOP-32, STSOP-32
N01L6183A	1 Mb	64k x 16	70	1.65	2.2	0.5	10	BGA-48, TSOP-44
N01L63W2A	1 Mb	64k x 16	55	2.3	3.6	2	20	BGA-48, TSOP-44
N01L63W3A	1 Mb	64k x 16	55	2.3	3.6	2	20	BGA-48, TSOP-44

SERIAL EEPROM

Product Type	Device	Density	Organization (bits)	Address Pins	f _{cycle} Max (MHz)	V _{CC} Min (V)	V _{CC} Max (V)	I _{standby} Max (µA)	I _{act} Max (mA)	Package
i ² C Interface	CAT24C256	256 kb	32k x 8	Yes	0.4	1.8	5.5	1.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT24C128	128 kb	16k x 8	Yes	0.4	1.8	5.5	1.0	3.0	TSSOP-8, UDFN-8, SOIC-8, PDIP-8
	CAT24C64	64 kb	8k x 8	Yes	0.4	1.8	5.5	1.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT24C32	32 kb	4k x 8	Yes	0.4	1.7	5.5	1.0	2.0	TSSOP-8, TDFN-8, UDFN-8, SOIC-8, PDIP-8
	CAT24C164	16 kb	2k x 8	Yes	0.4	1.8	5.5	1.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT24C16	16 kb	2k x 8	No	0.4	1.7	5.5	1.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8, TSOT-23-5, MSOP-8
	CAT24AA16	16 kb	2k x 8	No	1.0	1.7	5.5	1.0	1.0	SOIC-8, TSOT-23-5
	CAT24C08	8 kb	1k x 8	Yes	0.4	1.7	5.5	1.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8, TSOT-23-5, MSOP-8
	CAT24AA08	8 kb	1k x 8	No	1.0	1.7	5.5	1.0	1.0	SOIC-8, TSOT-23-5
	CAT24C04	4 kb	512 x 8	Yes	0.4	1.7	5.5	1.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8, TSOT-23-5, MSOP-8
	CAT24AA04	4 kb	512 x 8	No	1.0	1.7	5.5	1.0	1.0	SOIC-8, TSOT-23-5
	CAT24C02	2 kb	256 x 8	Yes	0.4	1.7	5.5	1.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8, TSOT-23-5, MSOP-8
	CAT24AA02	2 kb	256 x 8	No	0.4	1.7	5.5	1.0	1.0	SOIC-8, TSOT-23-5
	CAT24C01	1 kb	128 x 8	Yes	0.4	1.7	5.5	1.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8, TSOT-23-5, MSOP-8
	CAT24AA01	1 kb	128 x 8	No	0.4	1.7	5.5	1.0	1.0	SOIC-8, TSOT-23-5
	CAT24C05	4 kb	512 x 8	-	0.4	1.8	5.5	1.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8, TSOT-23-5
CAT24C03	2 kb	256 x 8	-	0.4	1.8	5.5	1.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8, TSOT-23-5	
CAT24C208	8 kb	1k x 8	-	0.4	2.5	5.5	50	3.0	SOIC-8	
CAT34C02	2 kb	256 x 8	-	0.4	1.7	5.5 (Note 1)	1.0	1.0	TSSOP-8, TDFN-8, UDFN-8	
CAT24C21	1 kb	128 x 8	-	0.4	2.5	5.5	1.0	2.0	TSSOP-8, MSOP-8, TDFN-8, SOIC-8, PDIP-8	

1. The CAT34C02 reversible software write protect feature V_{CC} = 1.7 to 3.6 V.

SERIAL EEPROM

Product Type	Device	Density	Organization (bits)	Address Pins	f _{cycle} Max (MHz)	V _{CC} Min (V)	V _{CC} Max (V)	I _{standby} Max (µA)	I _{act} Max (mA)	Package
SPI Interface	CAT25256	256 kb	32k x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	3.0	4.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT25128	128 kb	16k x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	3.0	4.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT25640	64 kb	8k x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	1.0	3.0	TSSOP-8, TDFN-8, UDFN-8, SOIC-8, PDIP-8
	CAT25320	32 kb	4k x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	2.0	3.0	TSSOP-8, TDFN-8, SOIC-8, UDFN-8, PDIP-8
	CAT25160	16 kb	2k x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	2.0	2.0	TSSOP-8, TDFN-8, SOIC-8, UDFN-8, PDIP-8
	CAT25080	8 kb	1k x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	2.0	2.0	TSSOP-8, TDFN-8, UDFN-8, SOIC-8, PDIP-8
	CAT25040	4 kb	512 x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	2.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT25020	2 kb	256 x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	2.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT25010	1 kb	128 x 8	-	10 @ 2.5 V, 5 @ 1.8 V	1.8	5.5	2.0	2.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT93C86	16 kb	1024 x 16 2048 x 8	-	3 @ 4.5 V, 1 @ 2.5 V, 0.5 @ 1.8 V	1.8	5.5	10.0	3.0	TDFN-8, SOIC-8, PDIP-8
MicroWire Interface	CAT93C76	8 kb	512 x 16 1024 x 8	-	3 @ 2.5 V, 1 @ 1.8 V	1.8	5.5	10.0	3.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT93C66	4 kb	256 x 16 512 x 8	-	2.0	1.8	5.5	4.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT93C56	2 kb	128 x 16 256 x 8	-	2.0	1.8	5.5	4.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT93C57	2 kb	128 x 16 256 x 8	-	2.0	1.8	5.5	4.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT93C46	1 kb	64 x 16 128 x 8	-	2.0	1.8	5.5	2.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8
	CAT93C46R	1 kb	64 x 16 128 x 8	-	2.0	1.8	5.5	2.0	1.0	TSSOP-8, TDFN-8, SOIC-8, PDIP-8

1. The CAT34C02 reversible software write protect feature V_{CC} = 1.7 to 3.6 V.

PARALLEL EEPROM

Device	Density	Organization (Bits)	t _{Acc} Max (ns)	V _{CC} Min (V)	V _{CC} Max (V)	I _{standby} Typ (μA)	I _{act} Max (mA)	Package
CAT28C512	512 kb	64k x 8	120, 150	4.5	5.5	200	50	TSOP-32, PDIP-32, PLCC-32
CAT28C513	512 kb	64k x 8	120, 150	4.5	5.5	200	50	PLCC-32
CAT28C256	256 kb	32k x 8	120, 150	4.5	5.5	150	25	TSOP-28, PDIP-28, PLCC-32
CAT28C257	256 kb	32k x 8	120, 150	4.5	5.5	150	25	PDIP-28, PLCC-32
CAT28LV256	256 kb	32k x 8	200, 250, 300	3.0	3.6	150	15	TSOP-28, PDIP-28, PLCC-32
CAT28C64B	64 kb	8k x 8	90, 120, 150	4.5	5.5	100	25	TSOP-28, SOIC-28, PDIP-28, PLCC-32
CAT28C65B	64 kb	8k x 8	90, 120, 150	4.5	5.5	100	25	TSOP-28, SOIC-28, PDIP-28, PLCC-32
CAT28LV64	64 kb	8k x 8	150, 200, 250	3.0	3.6	100	8	TSOP-28, SOIC-28, PDIP-28, PLCC-32
CAT28LV65	64 kb	8k x 8	150, 200, 250	3.0	3.6	100	8	TSOP-28, SOIC-28, PDIP-28, PLCC-32
CAT28C16A	16 kb	2k x 8	90, 120, 200	4.5	5.5	100	25	SOIC-24, PDIP-24, PLCC-32
CAT28C17A	16 kb	2k x 8	90, 120, 200	4.5	5.5	100	25	SOIC-28, PDIP-28, PLCC-32

FLASH

Device	Type	Density	Organization (Bits)	t _{Acc} Max (ns)	V _{CC} Min (V)	V _{CC} Max (V)	I _{standby} Max (μA)	I _{act} Max (mA)	Package
CAT28F020	Bulk Erase	2 Mb	256k x 8	90, 120	5	12	100	30	TSOP-32, PDIP-32, PLCC-32
CAT28F001	Boot Block	1 Mb	128k x 8	90, 120	5	12	100	30	TSOP-32, PDIP-32, PLCC-32
CAT28F010	Bulk Erase	1 Mb	128k x 8	90, 120	5	12	100	30	TSOP-32, PDIP-32, PLCC-32
CAT28F512	Bulk Erase	512 kb	64k x 8	90, 120, 150	5	12	100	30	TSOP-32, PDIP-32, PLCC-32

NVRAM

Device	Density	Organization (Bits)	t _{Acc} Max (ns)	V _{CC} Min (V)	V _{CC} Max (V)	I _{standby} Max (μA)	I _{act} Max (mA)	Package
CAT22C10	256 b	64 x 4	200, 300	4.5	5.5	30	40	SOIC-16, PDIP-18
CAT24C44	256 b	16 x 16	375	4.5	5.5	30	3	SOIC-8, PDIP-8

Rectifiers

Rectifiers

Table of Contents

	Page
Application Specific Rectifiers	270
Low V_F Schottky	270
Low Leakage Schottky	271
High Voltage Schottky	271
MEGAHERTZ™	271
UltraSoft Rectifiers	271
Energy Rated Rectifiers	271
SCHOTTKY Rectifiers	272
Surface Mount Schottky	272
Axial Lead Schottky	275
TO-220 Type Schottky	276
TO-218 Types and TO-247 Schottky	278
UltraSoft Rectifiers	278
Ultrafast Rectifiers	279
Surface Mount Ultrafast	279
Axial Lead Ultrafast	280
TO-220 Type Ultrafast	281
TO-218 Types and TO-247 Ultrafast	281
Fast Recovery Rectifiers/General Purpose Rectifiers	282

APPLICATION SPECIFIC RECTIFIERS

Table 1. LOW V_F SCHOTTKY RECTIFIERS

Device	I_O (A)	V_{RRM} (V)	Max V_F @ Rated I_O and $T_C = 25^\circ\text{C}$ (V)	Max I_R @ Rated V_{RRM} and $T_C = 25^\circ\text{C}$ (mA) ⁽¹⁾	Package
MBRD835L	8.0	35	0.51	1.4	DPAK
MBRD1035CTL	10	35	0.47	2.0	DPAK
MBRD5H100	5.0	100	0.71	0.0035	DPAK
MBRB2515L	25	15	0.45	15	D ² PAK
MBRB3030CTL	30	30	0.44	2.0	D ² PAK
MBRB2535CTL	25	35	0.47	10	D ² PAK
MBRB30H60CT	30	60	0.62	0.3	D ² PAK
MBRB8H100	8	100	0.71	0.0045	D ² PAK
MBRB20H100CT	20	100	0.77	0.0045	D ² PAK
MBRB41H100CT	40	100	0.8	0.01	D ² PAK
MBRB60H100CT	60	100	0.84	0.01	D ² PAK
MBRB30H30CT-1G	30	30	0.48	0.8	I ² PAK
MBRB3045CT-1G	30	45	0.62	0.2	I ² PAK
MBRB30H60CT-1G	30	60	0.62	0.3	I ² PAK
MBRB41H100CT-1G	40	100	0.80	0.01	I ² PAK
MBRM110L	1.0	10	0.365	0.5	POWERMITE®
MBRA210L	2.0	10	0.35	0.7	SMA
MBRA320	3.0	20	0.50	2.0	SMA
MBRS130L	1.0	30	0.395	1.0	SMB
MBRS230L	2.0	30	0.50	1.0	SMB
MBRS2H100	2.0	100	0.79	0.008	SMB
MBRS410L	4.0	10	0.33	5.0	SMC
MBR0520L	0.5	20	0.385	0.25	SOD-123
MBR120LSF	1.0	20	0.45	0.4	SOD-123 Flat Lead
MBR120VLSF	1.0	20	0.34	0.6	SOD-123 Flat Lead
MBR130LSF	1.0	30	0.38	1.0	SOD-123 Flat Lead
MBR30H30CT	30	30	0.48	0.8	TO-220AB
MBR2535CT	30	35	0.62	0.2	TO-220AB
MBR30L45CT	30	45	0.5	0.65	TO-220AB
MBR3045ST	30	45	0.62	0.2	TO-220AB
MBR40L45CT	40	45	0.5	1.2	TO-220AB
MBR60L45CT	60	45	0.55	1.2	TO-220AB
MBR30H60CT	30	60	0.62	0.3	TO-220AB
MBR20H100CTG	20	100	0.77	0.0045	TO-220AB
MBR10H100CTG	10	100	0.73	0.0035	TO-220AB
MBR20L45CT	20	45	0.5	0.5	TO-220AB
MBR30H100CTG	30	100	0.80	0.0045	TO-220AB
MBR41H100CTG	40	100	0.80	0.01	TO-220AB
MBR60H100CTG	60	100	0.84	0.01	TO-220AB
MBR20H150CT	20	150	0.68 @ 125°C	0.05	TO-220AB
MBR2515L	25	15	0.45	15	TO-220AC
MBR2030CTL	20	30	0.52	5.0	TO-220AC
MBR2535CTL	25	35	0.47	5.0	TO-220AC
MBRF2045CT	20	45	0.84 @ 20A	0.1	TO220FP
MBRF30L45CT	30	45	0.5	0.65	TO220FP
MBRF30H60CTG	30	60	0.62	0.3	TO-220FP
MBRF20H100CT	20	100	0.77	0.0045	TO220FP
MBRF30H100CT	30	100	0.8	0.0045	TO220FP
MBRF20H150CT	20	150	0.68 @ 125°C	0.05	TO220FP
MBRF30H150CT	30	150	0.73 @ 125°C	0.06	TO220FP
MBRF20L45CT	20	45	0.5	0.5	TO220FP
MBRF2545CT	25	45	0.7	0.2	TO220FP
MBR4015LWT	40	15	0.42	5.0	TO-247
MBR60L45WT	60	45	0.55	1.2	TO-247
MBR40H100WTG	40	100	0.80	0.01	TO-247

1. Refers to maximum leakage current per leg on "CT" and "WT" suffix devices.

APPLICATION SPECIFIC RECTIFIERS (continued)

Table 2. LOW LEAKAGE SCHOTTKY RECTIFIERS

Device	I _O (A)	V _{RRM} (V)	Max V _F @ Rated I _O and T _C = 25°C (V)	Max I _R @ Rated V _{RRM} and T _C = 25°C (mA)	Package
MBR120ESF	1.0	20	0.53	0.01	SOD-123 FLAT LEAD
MBRM110E	1.0	10	0.53	0.001	POWERMITE®
MBRM120E	1.0	20	0.53	0.01	POWERMITE®
MBRA210E	2.0	10	0.5	0.05	SMA
MBRA120E	1.0	20	0.53	0.01	SMA
MBRS410E	4.0	10	0.5	0.15	SMC

Table 3. HIGH VOLTAGE SCHOTTKY RECTIFIERS

Device	I _O (A)	V _{RRM} (V)	Max V _F @ Rated I _O and T _C = 25°C (V)	Max I _R @ Rated V _{RRM} and T _C = 25°C (mA) ⁽²⁾	Package
MBRS3200	3.0	200	0.84	1.0	SMB
MBRS3201	3.0	200	0.84	1.0	SMC
MBRS4201	4.0	200	0.86	1.0	SMC
MBRB20200CT	20	200	0.9	1.0	D ² PAK
MBR20200CT	20	200	0.9	1.0	TO-220AB
MBR40250T	40	250	0.97	0.03	TO-220AB
MBR40250	40	250	0.97	0.03	TO-220AC
MBRF20200CT	20	200	0.9	1.0	TO-200FP
MBRF40250T	40	250	0.97	0.03	TO-220FP

2. Refers to maximum leakage current per leg on "CT" and "WT" suffix devices.

Table 4. MEGAHERTZ™ RECTIFIERS

Device	I _O (A)	V _{RRM} (V)	Max V _F @ Rated I _F and T _C = 25°C (V)	Max I _R @ Rated V _{RRM} and T _C = 25°C (mA) ⁽³⁾	t _{rr} (ns)	Package
MURHS160	1.0	600	2.4	0.02	35	SMB
MURHD560	5.0	600	2.7	0.01	30	DPAK
MURHB840CT	8.0	400	2.2	0.01	28	D ² PAK
MURHB860CT	8.0	600	2.8	0.01	35	D ² PAK
MURH840CT	8.0	400	2.2	0.01	28	TO-220AB
MURH860CT	8.0	600	2.8	0.01	35	TO-220AB
MURHF860CT	8.0	600	2.8	0.01	35	TO-220FP

3. Refers to maximum leakage current per leg on "CT" suffix devices.

Table 5. ULTRASOFT RECTIFIERS (For High Speed Rectification)

Device	I _O (A)	V _{RRM} (V)	Max V _F @ I _O Rated and T _C = 25°C (V)	Max t _{rr} (ns)	T _J Max (°C)	Package
MSRD620CT	6.0	200	1.15	55	175	DPAK
MSR860	8.0	600	1.7	120	150	TO-220AC
MSR1560	15	600	1.8	45	150	TO-220AC
MSRF860	8	600	1.7	120	150	TO-220FP
MSRF1560	15	600	1.8	45	150	TO-220FP

Table 6. ENERGY RATED RECTIFIERS

Device	I _O (A)	V _{RRM} (V)	Max V _F @ I _O Rated and T _C = 25°C (V)	Max I _R @ Rated V _{RRM} and T _C = 25°C (μA)	Avalanche Energy (mJ)	Package
MUR180E	1.0	800	1.75	10	10	Case 59-10
MUR1100E	1.0	1000	1.75	10	10	Case 59-10
MUR480E	4.0	800	1.85	25	20	Case 267-05
MUR4100E	4.0	1000	1.85	25	20	Case 267-05
MURS480E	4.0	800	1.85	25	20	SMC
MUR880E	8.0	800	1.8	25	20	TO-220AC
MUR8100E	8.0	1000	1.8	25	20	TO-220AC

SCHOTTKY RECTIFIERS

Table 7. SURFACE MOUNT SCHOTTKY RECTIFIERS

V_{RRM} (V)	I_O (A)	I_O Rating Condition	Device	Max V_F @ I_O $T_C = 25^\circ\text{C}$ (V)	I_{FSM} (A)	T_J Max ($^\circ\text{C}$)	Max $I_R^{(4)}$ $T_J = 25^\circ\text{C}$ (mA)	Max $I_R^{(4)}$ (mA)	Package
20	0.5	$T_L = 90^\circ\text{C}$	<i>MBR0520L</i>	0.385	5.5	125	0.250	8.0 @ 100°C	CASE 425-04 (SOD-123) Cathode = Band 
30	0.5	$T_L = 100^\circ\text{C}$	<i>MBR0530</i>	0.430	5.5	125	0.130	4.0 @ 100°C	
30	2.0	$T_L = 105^\circ\text{C}$	<i>MBR230LSF</i>	0.43	40	125	1.0	25 @ 100°C	
30	1.0	$T_L = 65^\circ\text{C}$	<i>MBR130</i>	0.51	5.5	125	0.06	4.0 @ 125°C	
40	0.5	$T_L = 115^\circ\text{C}$	<i>MBR0540</i>	0.51	5.5	150	0.020	13 @ 100°C	
100	1.0	$T_L = 162^\circ\text{C}$	<i>MBR1H100SF</i>	0.76	50	175	0.04	0.5 @ 125°C	
100	2.0	$T_L = 146^\circ\text{C}$	<i>MBR2H100SF</i>	0.84	50	175	0.04	0.5 @ 125°C	
20	1.0	$T_L = 140^\circ\text{C}$	<i>MBR120ESF</i>	0.53	40	150	0.01	1.6 @ 100°C	CASE 498-01 (SOD-123FL) 
20	1.0	$T_L = 115^\circ\text{C}$	<i>MBR120LSF</i>	0.45	50	125	0.4	25 @ 85°C	
20	1.0	$T_L = 119^\circ\text{C}$	<i>MBR120VLSF</i>	0.34	45	125	0.6	15 @ 85°C	
30	1.0	$T_L = 117^\circ\text{C}$	<i>MBR130LSF</i>	0.38	40	125	1.0	25 @ 100°C	
40	1.0	$T_L = 112^\circ\text{C}$	<i>MBR140SF</i>	0.55	30	125	0.5	25 @ 85°C	
10	1.0	$T_C = 115^\circ\text{C}$	<i>MBRM110E</i>	0.53	50	150	0.001	0.5 @ 100°C	CASE 457-04 (POWERMITE®) 
10	1.0	$T_C = 115^\circ\text{C}$	<i>MBRM110L</i>	0.365	50	125	0.5	60 @ 100°C	
20	1.0	$T_C = 130^\circ\text{C}$	<i>MBRM120E</i>	0.53	50	150	0.01	1.6 @ 100°C	
20	1.0	$T_C = 115^\circ\text{C}$	<i>MBRM120L</i>	0.45	50	125	0.4	25 @ 85°C	
30	1.0	$T_C = 135^\circ\text{C}$	<i>MBRM130L</i>	0.38	50	125	0.41	11 @ 85°C	
40	1.0	$T_C = 110^\circ\text{C}$	<i>MBRM140</i>	0.55	50	125	0.5	25 @ 85°C	
100	1.0	$T_L = 168^\circ\text{C}$	<i>MBRM1H100</i>	0.76	50	175	0.02	1.0 @ 125°C	
100	2.0	$T_L = 160^\circ\text{C}$	<i>MBRM2H100</i>	0.84	50	175	0.02	1.0 @ 125°C	CASE 403D-02 (SMA) Cathode = Notch or Polarity Band 
10	2.0	$T_C = 125^\circ\text{C}$	<i>MBRA210E</i>	0.5	100	150	0.05	0.5 @ 100°C	
10	2.0	$T_L = 110^\circ\text{C}$	<i>MBRA210L</i>	0.35	160	125	0.70	60 @ 100°C	
20	1.0	$T_L = 125^\circ\text{C}$	<i>MBRA120E</i>	0.53	40	150	0.01	1.6 @ 100°C	
20	3.0	$T_L = 100^\circ\text{C}$	<i>MBRA320</i>	0.50	80	125	2.0	20 @ 100°C	
30	1.0	$T_C = 105^\circ\text{C}$	<i>MBRA130L</i>	0.41	25	125	1.0	25 @ 100°C	
40	1.0	$T_C = 95^\circ\text{C}$	<i>MBRA140</i>	0.55	30	125	0.5	10 @ 100°C	
40	3.0	$T_L = 100^\circ\text{C}$	<i>MBRA340</i>	0.45	100	150	0.3	15 @ 100°C	
60	1.0	$T_C = 105^\circ\text{C}$	<i>MBRA160</i>	0.51	60	150	0.2	12 @ 125°C	
100	1.0	$T_L = 167^\circ\text{C}$	<i>MBRA1H100</i>	0.76	50	175	0.04	0.5 @ 125°C	
100	2.0	$T_L = 150^\circ\text{C}$	<i>MBRA2H100</i>	0.79	130	175	0.008	1.5 @ 125°C	

4. At V_{RRM}

SCHOTTKY RECTIFIERS (continued)

Table 7. SURFACE MOUNT SCHOTTKY RECTIFIERS (continued)

V_{RRM} (V)	I_O (A)	I_O Rating Condition	Device	Max V_F @ I_O Rated $T_C = 25^\circ\text{C}$ (V)	I_{FSM} (A)	T_J Max ($^\circ\text{C}$)	Max I_R ⁽⁵⁾ $T_J = 25^\circ\text{C}$ (mA)	Max I_R (mA)	Package
20	1.0	$T_L = 115^\circ\text{C}$	MBRS120	0.6	40	125	1.0	10 @ 100°C	CASE 403A-03 (SMB) Cathode = Notch or Polarity Band 
30	1.0	$T_L = 120^\circ\text{C}$	MBRS130L	0.395	40	125	1.0	10 @ 100°C	
30	1.0	$T_L = 115^\circ\text{C}$	MBRS130	0.6	40	125	1.0	10 @ 100°C	
30	2.0	$T_C = 110^\circ\text{C}$	MBRS230L	0.5	40	125	1.0	75 @ 125°C	
40	1.0	$T_L = 115^\circ\text{C}$	MBRS140	0.6	40	125	1.0	10 @ 100°C	
40	1.5	$T_C = 100^\circ\text{C}$	MBRS1540	0.46	40	125	0.8	5.7 @ 100°C	
40	2.0	$T_C = 100^\circ\text{C}$	MBRS240L	0.43	25	125	2.0	60 @ 100°C	
40	2.0	$T_C = 103^\circ\text{C}$	MBRS2040L	0.43	70	125	0.80	20 @ 100°C	
60	2.0	$T_L = 95^\circ\text{C}$	MBRS260	0.63	60	125	0.2	12 @ 125°C	
90	1.0	$T_L = 163^\circ\text{C}$	MBRS190	0.75	50	175	0.5	5.0 @ 100°C	
100	1.0	$T_L = 163^\circ\text{C}$	MBRS1100	0.75	50	175	0.5	5.0 @ 100°C	
100	2.0	$T_L = 150^\circ\text{C}$	MBRS2H100	0.79	130	175	0.008	1.5 @ 125°C	
200	3.0	$T_L = 120^\circ\text{C}$	MBRS3200	0.84	100	150	1.0	5.0 @ 100°C	
10	4.0	$T_L = 130^\circ\text{C}$	MBRS410E	0.50	250	150	0.15	4.0 @ 100°C	CASE 403-03 (SMC) Cathode = Notch 
10	4.0	$T_L = 110^\circ\text{C}$	MBRS410L	0.33	150	125	5.0	200 @ 100°C	
20	3.0	$T_L = 110^\circ\text{C}$	MBRS320	0.50	80	150	2.0	20 @ 100°C	
30	3.0	$T_L = 110^\circ\text{C}$	MBRS330	0.50	80	150	2.0	20 @ 100°C	
40	3.0	$T_L = 110^\circ\text{C}$	MBRS340	0.5	80	150	2.0	20 @ 100°C	
40	5.0	$T_C = 105^\circ\text{C}$	MBRS540	0.5	190	150	0.3	15 @ 100°C	
60	3.0	$T_L = 137^\circ\text{C}$	MBRS360	0.74	125	175	0.15	10 @ 100°C	
100	3.0	$T_L = 100^\circ\text{C}$	MBRS3100	0.79	130	175	0.05	5.0 @ 125°C	
200	3.0	$T_C = 70^\circ\text{C}$	MBRS3201	0.84	100	150	1.0	5.0 @ 150°C	
200	4.0	$T_L = 70^\circ\text{C}$	MBRS4201	0.86	100	150	1.0	5.0 @ 150°C	

5. At V_{RRM}

SCHOTTKY RECTIFIERS (continued)

Table 7. SURFACE MOUNT SCHOTTKY RECTIFIERS (continued)

V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max V _F @ I _O Rated T _C = 25°C (V)	I _{FSM} (A)	T _J Max (°C)	Max I _R ⁽⁶⁾ T _J = 25°C (mA)	Max I _R ⁽⁶⁾ (mA)	Package	
20	3.0	T _C = 125°C	<i>MBRD320</i>	0.60	75	175	0.2	20 @ 125°C	<p>CASE 369A-13 (DPAK)</p>  <p>1 3 4</p> <p>“CT” Suffix</p>  <p>1 3 4</p> <p>Non-“CT” Suffix</p>  <p>3 4</p> <p>MBRD5H100 ONLY</p>	
20	6.0	T _C = 130°C	<i>MBRD620CT</i>	0.70	75	175	0.1	15 @ 125°C		
30	3.0	T _C = 125°C	<i>MBRD330</i>	0.60	75	175	0.2	20 @ 125°C		
30	6.0	T _C = 130°C	<i>MBRD630CT</i>	0.70	75	175	0.1	15 @ 125°C		
35	8.0	T _C = 88°C	<i>MBRD835L</i>	0.51	75	150	1.4	35 @ 100°C		
35	10	T _C = 115°C	<i>MBRD1035CTL</i>	0.47	50	150	2.0	60 @ 100°C		
40	3.0	T _C = 125°C	<i>MBRD340</i>	0.60	75	175	0.2	20 @ 125°C		
40	6.0	T _C = 130°C	<i>MBRD640CT</i>	0.70	75	175	0.1	15 @ 125°C		
45	10	T _C = 135°C	<i>MBRD1045</i>	0.84	70	175	0.1	15 @ 125°C		
50	3.0	T _C = 125°C	<i>MBRD350</i>	0.60	75	175	0.2	20 @ 125°C		
50	6.0	T _C = 130°C	<i>MBRD650CT</i>	0.70	75	175	0.1	15 @ 125°C		
60	3.0	T _C = 125°C	<i>MBRD360</i>	0.60	75	175	0.2	20 @ 125°C		
60	6.0	T _C = 130°C	<i>MBRD660CT</i>	0.70	75	175	0.1	15 @ 125°C		
100	5.0	T _C = 171°C	<i>MBRD5H100</i>	0.71	105	175	0.0035	4.5 @ 125°C		
15	25	T _C = 90°C	<i>MBRB2515L</i>	0.45	150	100	15	200 @ 70°C		<p>CASE 418B-04 (D²PAK)</p>  <p>1 3 4</p> <p>“CT” Suffix</p>  <p>1 3 4</p> <p>Non-“CT” Suffix</p> 
30	30	T _C = 134°C	<i>MBRB3030CT</i>	0.54	200	175	0.6	145 @ 150°C		
30	30	T _C = 115°C	<i>MBRB3030CTL</i>	0.44	300	125	2.0	195 @ 125°C		
30	40	T _C = 115°C	<i>MBRB4030</i>	0.55	300	175	0.35	150 @ 125°C		
35	25	T _C = 110°C	<i>MBRB2535CTL</i>	0.47	150	125	10	500 @ 125°C		
45	30	T _C = 164°C	<i>MBRB2545CT</i>	0.62	150	175	0.2	25 @ 125°C		
45	10	T _C = 135°C	<i>MBRB1045</i>	0.84	150	175	0.1	15 @ 125°C		
45	15	T _C = 167°C	<i>MBRB1545CT</i>	0.84	150	175	0.1	15 @ 125°C		
45	16	T _C = 163°C	<i>MBRB1645</i>	0.63	150	175	0.2	40 @ 125°C		
60	30	T _C = 159°C	<i>MBRB30H60CT</i>	0.62	260	175	0.3	45 @ 125°C		
60	20	T _C = 110°C	<i>MBRB2060CT</i>	0.95	150	175	0.15	35 @ 125°C		
100	8	T _C = 146°C	<i>MBRB8H100</i>	0.71	250	175	0.0045	5.3 @ 125°C		
100	20	T _C = 162°C	<i>MBRB20H100CT</i>	0.77	250	175	0.0045	6.0 @ 125°C		
100	40	T _C = 150°C	<i>MBRB41H100CT</i>	0.8	350	175	0.01	10 @ 125°C		
100	60	T _C = 155°C	<i>MBRB60H100CT</i>	0.84	350	175	0.01	10 @ 125°C		
100	20	T _C = 110°C	<i>MBRB20100CT</i>	0.85	150	175	0.1	6.0 @ 125°C		
200	20	T _C = 134°C	<i>MBRB20200CT</i>	0.9	150	150	1.0	50 @ 125°C		

6. At V_{RRM}; refers to maximum leakage current per leg on “CT” suffix devices.

SCHOTTKY RECTIFIERS (continued)

Table 8. AXIAL LEAD SCHOTTKY RECTIFIERS

V_{RRM} (V)	I_O (A)	I_O Rating Condition	Device	Max V_F @ I_O Rated $T_C = 25^\circ\text{C}$ (V)	I_{FSM} (A)	T_J Max ($^\circ\text{C}$)	Max I_R @ V_{RRM} $T_A = 25^\circ\text{C}$ (mA)	Max I_R @ V_{RRM} $T_A = 100^\circ\text{C}$ (mA)	Package
20	1.0	$T_A = 55^\circ\text{C}$ $R_{\theta JA} = 80^\circ\text{C/W}$	1N5817	0.45	25	125	1.0	10	<p>CASE 59-10 (DO-41) Plastic</p>  <p>Cathode = Polarity Band</p>
30	1.0	$T_A = 55^\circ\text{C}$ $R_{\theta JA} = 80^\circ\text{C/W}$	1N5818	0.55	25	125	1.0	10	
40	1.0	$T_A = 55^\circ\text{C}$ $R_{\theta JA} = 80^\circ\text{C/W}$	1N5819	0.60	25	125	1.0	10	
50	1.0	$T_A = 55^\circ\text{C}$ $R_{\theta JA} = 80^\circ\text{C/W}$	MBR150	0.75	25	150	0.5	5.0	
60	1.0	$T_A = 55^\circ\text{C}$ $R_{\theta JA} = 80^\circ\text{C/W}$	MBR160	0.75	25	150	0.5	5.0	
100	1.0	$T_A = 120^\circ\text{C}$ $R_{\theta JA} = 50^\circ\text{C/W}$	MBR1100	0.79	50	175	0.5	5.0	
20	3.0	$T_A = 76^\circ\text{C}$ $R_{\theta JA} = 28^\circ\text{C/W}$	1N5820	0.475	80	125	2.0	20	<p>CASE 267-05 (DO-201AD) Plastic</p>  <p>Cathode = Polarity Band</p>
30	3.0	$T_A = 71^\circ\text{C}$ $R_{\theta JA} = 28^\circ\text{C/W}$	1N5821	0.50	80	125	2.0	20	
40	3.0	$T_A = 61^\circ\text{C}$ $R_{\theta JA} = 28^\circ\text{C/W}$	1N5822	0.525	80	125	2.0	20	
40	3.0	$T_A = 65^\circ\text{C}$ $R_{\theta JA} = 28^\circ\text{C/W}$	MBR340	0.60	80	175	0.6	20	
50	3.0	$T_A = 65^\circ\text{C}$ $R_{\theta JA} = 28^\circ\text{C/W}$	MBR350	0.74	80	150	0.6	20	
60	3.0	$T_A = 65^\circ\text{C}$ $R_{\theta JA} = 28^\circ\text{C/W}$	MBR360	0.74	80	150	0.6	20	
100	3.0	$T_A = 100^\circ\text{C}$ $R_{\theta JA} = 28^\circ\text{C/W}$	MBR3100	0.79	150	175	0.6	20	

SCHOTTKY RECTIFIERS (continued)

Table 9. TO-220 AND I²PAK THRU-HOLE SCHOTTKY RECTIFIERS

V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max V _F @ I _O Rated T _C = 25°C (V)	I _{FSM} (A)	T _J Max (°C)	Max I _R ⁽⁷⁾ @ V _{RRM} T _A = 25°C (mA)	Max I _R ⁽⁷⁾ @ V _{RRM} T _A = 125°C (mA)	Package
15	40	T _C = 140°C	MBR4015CTL	0.43	150	150	10	600 @ 125°C	<p>CASE 221A-09 (TO-220AB)</p>
30	20	T _C = 167°C	MBR2030CTL	0.52	150	175	5.0	75 @ 125°C	
30	30	T _C = 138°C	MBR30H30CT	0.48	260	150	0.8	130 @ 125°C	
35	15	T _C = 163°C	MBR1535CT	0.57 @ 125°C	150	175	0.1	15 @ 125°C	
35	25	T _C = 142°C	MBR2535CTL	0.47	150	150	5.0	500 @ 125°C	
35	30	T _C = 160°C	MBR2535CT	0.62	150	175	0.2	25 @ 125°C	
45	15	T _C = 163°C	MBR1545CT	0.57 @ 125°C	150	175	0.1	15 @ 125°C	
45	20	T _C = 141°C	MBR20L45CT	0.5	180	150	0.5	170 @ 125°C	
45	20	T _C = 165°C	MBR2045CT	0.57 @ 125°C	150	175	0.1	15 @ 125°C	
45	25	T _C = 160°C	MBR2545CT	0.62	150	175	0.2	25 @ 125°C	
45	30	T _C = 137°C	MBR30L45CT	0.5	190	150	0.65	250 @ 125°C	
45	30	T _C = 130°C	MBR3045ST	0.62	150	175	0.2	40 @ 125°C	
45	40	T _C = 145°C	MBR40L45CT	0.5	200	175	1.2	275 @ 125°C	
45	60	T _C = 145°C	MBR60L45CT	0.55	200	175	1.2	275 @ 125°C	
60	10	T _C = 140°C	MBR10L60CT	0.66	200	150	0.22	60 @ 125°C	
60	20	T _C = 123°C	MBR20L60CT	0.73	240	150	0.38	96 @ 125°C	
60	20	T _C = 133°C	MBR2060CT	0.85	150	175	0.1	20 @ 125°C	
60	30	T _C = 159°C	MBR30H60CT	0.62	260	175	0.3	45 @ 125°C	
60	30	T _C = 133°C	MBR30L60CT	0.81	240	150	0.35	110 @ 125°C	
60	40	T _C = 130°C	MBR40L60CT	0.81	240	150	0.55	175 @ 125°C	
80	20	T _C = 137°C	MBR20L80CT	0.85	175	150	0.5	50 @ 125°C	
80	20	T _C = 133°C	MBR2080CT	0.85	150	175	0.1	6.0 @ 125°C	
80	30	T _C = 130°C	MBR30H80CT	0.88	240	150	0.25	35 @ 125°C	
90	20	T _C = 133°C	MBR2090CT	0.85	150	175	0.1	6.0 @ 125°C	
100	16	T _C = 166°C	MBR16100CT	0.74	150	175	0.1	5.0 @ 125°C	
100	10	T _C = 168°C	MBR10H100CT	0.75	180	175	0.0035	4.5 @ 125°C	
100	20	T _C = 162°C	MBR20H100CT	0.77	250	175	0.0045	6.0 @ 125°C	
100	20	T _C = 133°C	MBR20100CT	0.85	150	175	0.1	6.0 @ 125°C	
100	30	T _C = 156°C	MBR30H100CT	0.80	250	175	0.0045	6.0 @ 125°C	
100	40	T _C = 150°C	MBR41H100CT	0.80	350	175	0.01	10 @ 125°C	
100	60	T _C = 155°C	MBR60H100CT	0.84	350	175	0.01	10 @ 125°C	
150	20	T _C = 134°C	MBR20H150CT	0.68 @ 125°C	180	150	0.05	30 @ 125°C	
150	30	T _C = 124°C	MBR30H150CT	1.11	200	150	0.06	50 @ 125°C	
200	20	T _C = 161°C	MBR20200CT	0.90	150	175	1.0	50 @ 125°C	
250	40	T _C = 82°C	MBR40250T	0.86	150	150	0.03	30 @ 125°C	

7. Refers to maximum leakage current per leg on "CT" suffix devices.

Ⓜ Indicates UL Recognized – File #E69369

SCHOTTKY RECTIFIERS (continued)

Table 9. TO-220 AND I²PAK THRU-HOLE SCHOTTKY RECTIFIERS



V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max V _F @ I _O Rated T _C = 25°C (V)	I _{FSM} (A)	T _J Max (°C)	Max I _R ⁽⁷⁾ @ V _{RRM} T _A = 25°C (mA)	Max I _R ⁽⁷⁾ @ V _{RRM} T _A = 125°C (mA)	Package
15	25	T _C = 91°C	MBR2515L	0.45	150	100	15	200 @ 70°C	<p>CASE 221B-04 (TO-220AC)</p>
35	7.5	T _C = 164°C	MBR735	0.84	150	175	0.1	15 @ 125°C	
35	10	T _C = 135°C	MBR1035	0.84	150	175	0.1	15 @ 125°C	
35	16	T _C = 163°C	MBR1635	0.63	150	175	0.2	40 @ 125°C	
45	7.5	T _C = 164°C	MBR745	0.84	150	175	0.1	15 @ 125°C	
45	10	T _C = 135°C	MBR1045	0.84	150	175	0.1	15 @ 125°C	
45	16	T _C = 163°C	MBR1645	0.63	150	175	0.2	40 @ 125°C	
60	10	T _C = 133°C	MBR1060	0.80	150	175	0.1	15 @ 125°C	
80	10	T _C = 133°C	MBR1080	0.80	150	175	0.1	6.0 @ 125°C	
90	10	T _C = 133°C	MBR1090	0.80	150	175	0.1	6.0 @ 125°C	
100	10	T _C = 133°C	MBR10100	0.80	150	175	0.1	6.0 @ 125°C	
250	40	T _C = 82°C	MBR40250	0.86	150	150	0.03	30 @ 125°C	
30	30	T _C = 138°C	MBRB30H30CT-1	0.48	260	150	0.8	45 @ 125°C	<p>CASE 418D-01 I²PAK (TO-262)</p>
45	30	T _C = 130°C	MBRB3045CT-1	0.48	150	175	0.2	40 @ 125°C	
60	30	T _C = 159°C	MBRB30H60CT-1	0.62	260	175	0.3	45 @ 125°C	
80	30	T _C = 130°C	MBRB30H80CT-1	0.88	240	150	0.25	35 @ 125°C	
100	40	T _C = 150°C	MBRB41H100CT-1	0.80	350	175	0.01	10 @ 125°C	
45	20	T _C = 141°C	MBRF20L45CT	0.5	180	150	0.5	170 @ 125°C	<p>CASE 221D-03 FULL PAK</p> <p>"CT" Suffix</p>
45	20	T _C = 165°C	MBRF2045CT	0.84 @ 20 A	150	175	0.1	15 @ 125°C	
45	25	T _C = 125°C	MBRF2545CT	0.70	150	175	0.2	40 @ 125°C	
45	30	T _C = 137°C	MBRF30L45CT	0.5	190	150	0.65	250 @ 125°C	
60	10	T _C = 140°C	MBRF10L60CT	0.66	200	150	0.22	60 @ 125°C	
60	20	T _C = 123°C	MBRF20L60CT	0.73	240	150	0.38	96 @ 125°C	
60	20	T _C = 133°C	MBRF2060CT	0.85	150	175	0.15	150 @ 125°C	
60	30	T _C = 133°C	MBRF30L60CT	0.81	240	150	0.35	110 @ 125°C	
60	30	T _C = 159°C	MBRF30H60CT	0.62	260	175	0.3	45 @ 125°C	
80	20	T _C = 137°C	MBRF20L80CT	0.85	175	150	0.5	50 @ 125°C	
100	20	T _C = 162°C	MBRF20H100CT	0.77	250	175	0.0045	6.0 @ 125°C	
100	20	T _C = 133°C	MBRF20100CT	0.85	150	175	0.15	150 @ 125°C	
100	30	T _C = 156°C	MBRF30H100CT	0.8	250	175	0.0045	6.0 @ 125°C	
150	10	T _C = 142°C	MBRF10H150CT	0.69 @ 125°C	150	150	0.045	20 @ 125°C	
150	20	T _C = 134°C	MBRF20H150CT	0.68 @ 125°C	180	150	0.05	30 @ 125°C	
150	30	T _C = 124°C	MBRF30H150CT	0.73 @ 125°C	200	150	0.06	50 @ 125°C	
200	20	T _C = 125°C	MBRF20200CT	0.90	150	150	1.0	50 @ 125°C	
250	40	T _C = 46°C	MBRF40250T	0.86	150	150	0.03	30 @ 125°C	

7. Refers to maximum leakage current per leg on "CT" suffix devices.

Indicates UL Recognized – File #E69369

SCHOTTKY RECTIFIERS (continued)



Table 10. TO-218 AND TO-247 SCHOTTKY RECTIFIERS

V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max V _F @ I _O Rated T _C = 25°C (V)	I _{FSM} (A)	T _J Max (°C)	Max I _R ⁽⁸⁾ @ V _{RRM} T _A = 25°C (mA)	Max I _R ⁽⁸⁾ @ V _{RRM} T _A = 100°C (mA)	Package
45	30	T _C = 105°C	<i>MBR3045PT</i>	0.76 @ 60 A	200	175	1.0	100 @ 125°C	CASE 340D-02 (TO-218AC) 
45	40	T _C = 125°C	<i>MBR4045PT</i>	0.70	400	175	1.0	50 @ 125°C	
45	60	T _C = 125°C	<i>MBR6045PT</i>	0.62	500	175	1.0	50 @ 125°C	
15	40	T _C = 120°C	<i>MBR4015LWT</i>	0.42	120	150	5.0	150 @ 100°C	CASE 340L-02 (TO-247) 
30	70	T _C = 100°C	<i>MBR7030WT</i>	0.55	500	175	5.0	250 @ 100°C	
45	30	T _C = 105°C	<i>MBR3045WT</i>	0.76 @ 60 A	200	175	1.0	100 @ 125°C	
45	40	T _C = 125°C	<i>MBR4045WT</i>	0.70	400	175	1.0	530 @ 100°C	
45	60	T _C = 125°C	<i>MBR6045WT</i>	0.62	500	175	1.0	50 @ 100°C	
45	60	T _C = 165°C	<i>MBR60L45WT</i>	0.55	200	175	1.2	275 @ 125°C	
100	40	T _C = 148°C	<i>MBR40H100WT</i>	0.80	200	175	0.01	10 @ 125°C	

8. Refers to maximum leakage current per leg on "CT" suffix devices.

ULTRASOFT RECTIFIERS






Table 11. ULTRASOFT RECTIFIERS (For High Speed Rectification)

V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max V _F @ I _O T _C = 25°C (V)	t _{rr} (ns)	T _J Max (°C)	Max I _R ⁽⁹⁾ @ V _{RRM} T _A = 25°C (μA)	Max I _R ⁽⁹⁾ @ V _{RRM} T _A = 150°C (μA)	Package
200	6.0	T _C = 137°C	<i>MSRD620CT</i>	1.15	55	175	5.0	200	CASE 369A-13 (DPAK) 
200	6.0	T _C = 162°C	<i>MSRD620CTR</i>	1.3	75	175	1.0	200	
600	8.0	T _C = 125°C	<i>MSR860</i>	1.7	120	150	10	1000	CASE 221B-04 (TO-220AC) 
600	15	T _C = 125°C	<i>MSR1560</i>	1.8	45	150	15	5000	
600	8	T _C = 125°C	<i>MSRF860</i>	1.7	120	150	10	1000	CASE 221D-03 FULL PAK 
600	15	T _C = 125°C	<i>MSRF1560</i>	1.8	45	150	15	5000	

9. Refers to maximum leakage current per leg on "CT" suffix devices.

ULTRAFAST RECTIFIERS

Table 12. SURFACE MOUNT ULTRAFAST RECTIFIERS

V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max t _{rr} (ns)	Max V _F @ I _O Rated T _C = 25°C (V)	I _{FSM} (A)	T _J Max (°C)	Max I _R ⁽¹⁰⁾ @ V _{RRM} T _A = 25°C (μA)	Max I _R ⁽¹⁰⁾ @ V _{RRM} T _A = 150°C (μA)	Package
50	1.0	T _L = 155°C	<i>MURA105</i>	30	0.875	50	175	2.0	50	CASE 403D-02 SMA  Cathode = Polarity Band
50	2.0	T _L = 135°C	<i>MURA205</i>	30	0.94	50	175	2.0	50	
100	1.0	T _L = 155°C	<i>MURA110</i>	30	0.875	50	175	2.0	50	
100	2.0	T _L = 135°C	<i>MURA210</i>	30	0.94	50	175	2.0	50	
150	1.0	T _L = 155°C	<i>MURA115</i>	35	0.875	40	175	2.0	50	
150	2.0	T _L = 135°C	<i>MURA215</i>	35	0.95	40	175	2.0	50	
200	1.0	T _L = 155°C	<i>MURA120</i>	35	0.875	40	175	2.0	50	
200	2.0	T _L = 135°C	<i>MURA220</i>	35	0.95	40	175	2.0	50	
300	1.0	T _L = 150°C	<i>MURA130</i>	65	1.1	35	175	5.0	150	
300	2.0	T _L = 125°C	<i>MURA230</i>	65	1.3	35	175	5.0	150	
400	1.0	T _L = 150°C	<i>MURA140</i>	65	1.1	35	175	5.0	150	
400	2.0	T _L = 125°C	<i>MURA240</i>	65	1.3	35	175	5.0	150	
600	1.0	T _L = 145°C	<i>MURA160</i>	75	1.25	30	175	5.0	150	
600	2.0	T _L = 110°C	<i>MURA260</i>	75	1.45	30	175	5.0	150	
50	1.0	T _L = 155°C	<i>MURS105</i>	35	0.875	40	175	2.0	50	CASE 403A-03 SMB  Cathode = Polarity Band
50	2.0	T _L = 125°C	<i>MURS205</i>	30	0.94	50	175	2.0	50	
100	1.0	T _L = 155°C	<i>MURS110</i>	35	0.875	40	175	2.0	50	
100	2.0	T _L = 125°C	<i>MURS210</i>	30	0.94	50	175	2.0	50	
150	1.0	T _L = 155°C	<i>MURS115</i>	35	0.875	40	175	2.0	50	
200	1.0	T _L = 155°C	<i>MURS120</i>	35	0.875	40	175	2.0	50	
200	2.0	T _L = 145°C	<i>MURS220</i>	35	0.95	40	175	2.0	50	
300	2.0	T _L = 125°C	<i>MURS230</i>	65	1.3	35	175	5.0	150	
400	1.0	T _L = 150°C	<i>MURS140</i>	75	1.25	35	175	5.0	150	
400	2.0	T _L = 125°C	<i>MURS240</i>	65	1.3	35	175	5.0	150	
600	1.0	T _L = 145°C	<i>MURHS160</i>	35	2.4	15	175	20	200 @ 125°C	
600	1.0	T _L = 150°C	<i>MURS160</i>	75	1.25	35	175	5.0	150	
600	2.0	T _L = 125°C	<i>MURS260</i>	75	1.45	35	175	5.0	150	
600	3.0	T _L = 105°C	<i>MURS360B</i>	75	1.25	100	175	3.0	150	
200	3.0	T _L = 140°C	<i>MURS320</i>	35	0.875	75	175	5.0	150	CASE 403-03 SMC Cathode = Notch 
400	3.0	T _L = 130°C	<i>MURS340</i>	75	1.25	75	175	10	250	
600	3.0	T _L = 130°C	<i>MURS360</i>	75	1.25	75	175	10	250	
800	4.0	T _L = 110°C	<i>MURS480E</i>	100	1.85	70	175	25	900	
200	3.0	T _C = 158°C	<i>MURD320</i>	35	0.95	75	175	5.0	500 @ 125°C	
200	6.0	T _C = 140°C	<i>MURD620CT</i>	35	1.0	50	175	5.0	250 @ 125°C	DKPAK  “CT” Suffix  3 0 4 MURD550PF ONLY  1 0 4 3 0 Non-“CT” Suffix
300	3.0	T _C = 160°C	<i>MURD330</i>	50	1.15	75	175	5.0	500	
300	5.0	T _C = 165°C	<i>MURD530</i>	45	1.05	75	175	5.0	100 @ 125°C	
520	5.0	T _C = 160°C	<i>MURD550PF</i>	95	1.15	75	175	5.0	400	
600	5.0	T _C = 159°C	<i>MURHD560</i>	30	2.7	50	175	10	70 @ 125°C	
200	16	T _C = 150°C	<i>MURB1620CT</i>	35	0.975	100	175	5.0	250	D²PAK CASE 418B-04  “CT” Suffix  1 0 4 3 0 Non-“CT” Suffix  1 0 4 3 0 MURB1620CTR ONLY
200	16	T _C = 150°C	<i>MURB1620CTR</i>	35	0.975	100	175	5.0	250	
400	8.0	T _C = 120°C	<i>MURHB840CT</i>	28	2.2	100	175	10	500	
600	8.0	T _C = 120°C	<i>MURHB860CT</i>	35	2.8	100	175	10	500	
600	16	T _C = 150°C	<i>MURB1660CT</i>	60	1.5	100	175	10	500	

10. Refers to maximum leakage current per leg on “CT” suffix devices.




ULTRAFAST RECTIFIERS (continued)

Table 13. AXIAL LEAD ULTRAFAST RECTIFIERS

V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max t _{rr} (ns)	Max V _F @ I _O Rated T _C = 25°C (V)	I _{FSM} (A)	T _J Max (°C)	Max I _R @ V _{RRM} T _A = 25°C (μA)	Max I _R @ V _{RRM} T _A = 150°C (μA)	Package
50	1.0	T _A = 130°C	MUR105	35	0.875	35	175	2.0	50	 <p>CASE 59-10 (DO-41) Plastic Cathode = Polarity Band</p>
100	1.0	T _A = 130°C	MUR110	35	0.875	35	175	2.0	50	
100	2.0	T _A = 100°C	MUR210	30	0.94	35	175	2.0	50	
150	1.0	T _A = 130°C	MUR115	35	0.875	35	175	2.0	50	
200	1.0	T _A = 130°C	MUR120	35	0.875	35	175	2.0	50	
200	2.0	T _A = 90°C	MUR220	35	0.95	35	175	2.0	50	
300	1.0	T _A = 120°C	MUR130	75	1.25	35	175	5.0	150	
400	1.0	T _A = 120°C	MUR140	75	1.25	35	175	5.0	150	
400	2.0	T _A = 85°C	MUR240	65	1.3	35	175	5.0	150	
600	1.0	T _A = 120°C	MUR160	100	1.25	35	175	5.0	150	
600	2.0	T _A = 60°C	MUR260	75	1.35	35	175	5.0	150	
800	1.0	T _A = 95°C	MUR180E	100	1.75	35	175	10	600 @ 100°C	
1000	1.0	T _A = 95°C	MUR1100E	100	1.75	35	175	10	600 @ 100°C	
1000	2.0	T _A = 35°C	MUR2100E	100	2.2	35	175	10	600 @ 100°C	
50	4.0	T _A = 80°C	MUR405	35	0.89	125	175	5.0	150	 <p>CASE 267-05 (DO-201AD) Plastic Cathode = Polarity Band</p>
100	4.0	T _A = 80°C	MUR410	35	0.89	125	175	5.0	150	
150	4.0	T _A = 80°C	MUR415	35	0.89	125	175	5.0	150	
200	4.0	T _A = 80°C	MUR420	35	0.89	125	175	5.0	150	
400	4.0	T _A = 40°C	MUR440	75	1.28	110	175	10	250	
520	5.0	T _A = 65°C	MUR550APF	95	1.15	85	175	5.0	500	
600	4.0	T _A = 40°C	MUR460	75	1.28	110	175	10	400	
800	4.0	T _A = 35°C	MUR480E	100	1.85	70	175	25	900	
1000	4.0	T _A = 35°C	MUR4100E	100	1.85	70	175	25	900	

ULTRAFAST RECTIFIERS (continued)



Table 14. TO-220 ULTRAFAST AND MEGAHERTZ™ RECTIFIERS

V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max t _{rr} (ns)	Max V _F @ I _O Rated T _C = 25°C (V)	I _{FSM} (A)	T _J Max (°C)	Max I _R ⁽¹¹⁾ @ V _{RRM} T _A = 25°C (μA)	Max I _R ⁽¹¹⁾ @ V _{RRM} T _A = 150°C (μA)	Package
100	16	T _C = 150°C	MUR1610CT	35	0.975	100	175	5.0	250	CASE 221A-09 (TO-220AB) 
150	16	T _C = 150°C	MUR1615CT	35	0.975	100	175	5.0	250	
200	6.0	T _C = 130°C	MUR620CT	35	0.975	75	175	5.0	250	
200	16	T _C = 150°C	MUR1620CT	35	0.975	100	175	5.0	250	
200	16	T _C = 160°C	MUR1620CTR	85	1.2	100	175	5.0	500	
400	8.0	T _C = 155°C	MURH840CT	28	2.2	100	175	10	500	
400	16	T _C = 150°C	MUR1640CT	60	1.30	100	175	10	500	
600	8.0	T _C = 120°C	MURH860CT	35	2.8	100	175	10	500	
600	16	T _C = 150°C	MUR1660CT	60	1.5	100	175	10	500	
50	8.0	T _C = 150°C	MUR805	35	0.975	100	175	5.0	250	
100	8.0	T _C = 150°C	MUR810	35	0.975	100	175	5.0	250	CASE 221B-04 (TO-220AC) 
100	15	T _C = 150°C	MUR1510	35	1.05	200	175	10	500	
150	8.0	T _C = 150°C	MUR815	35	0.975	100	175	5.0	250	
150	15	T _C = 150°C	MUR1515	35	1.05	200	175	10	500	
200	8.0	T _C = 150°C	MUR820	35	0.975	100	175	5.0	250	
200	15	T _C = 150°C	MUR1520	35	1.05	200	175	10	500	
200	20	T _C = 125°C	MUR2020R	95	1.10	250	175	50	1000	
400	8.0	T _C = 150°C	MUR840	60	1.30	100	175	10	500	
400	15	T _C = 150°C	MUR1540	60	1.25	150	175	10	500	
520	5.0	T _C = 160°C	MUR550PF	95	1.15	100	175	5.0	400	
600	8.0	T _C = 150°C	MUR860	60	1.50	100	175	10	500	
600	15	T _C = 145°C	MUR1560	60	1.50	150	175	10	1000	
800	8.0	T _C = 150°C	MUR880E	100	1.80	100	175	25	500 @ 100°C	
1000	8.0	T _C = 150°C	MUR8100E	100	1.80	100	175	25	500 @ 100°C	
200	16	T _C = 150°C	Ⓢ MURF1620CT	35	0.975	100	150	5.0	250	CASE 221D-03 (TO-220) FULL PAK 
520	5.0	T _C = 160	MURF550PF	95	1.15	100	175	5.0	400	
600	8.0	T _C = 150	MURF860	60	1.5	100	175	10	500	
600	8.0	T _C = 120°C	Ⓢ MURHF860CT	35	2.8	100	150	10	500	
600	15	T _C = 145	MURF1560	60	45	150	175	10	1000	
600	16	T _C = 150°C	Ⓢ MURF1660CT	60	1.5	100	150	10	500	

Ⓢ Indicates UL Recognized – File #E69369

11. Refers to maximum leakage current per leg on “CT” and “CTR” suffix devices.

Table 15. TO-218 AND TO-247 ULTRAFAST RECTIFIERS

V _{RRM} (V)	I _O (A)	I _O Rating Condition	Device	Max t _{rr} (ns)	Max V _F @ I _O Rated T _C = 25°C (V)	I _{FSM} (A)	T _J Max (°C)	Max I _R ⁽¹²⁾ @ V _{RRM} T _A = 25°C (μA)	Max I _R ⁽¹²⁾ @ V _{RRM} T _A = 150°C (mA)	Package
200	30	T _C = 145°C	MUR3020WT	35	1.05	200	175	10	0.5	CASE 340L-02 (TO-247) 
600	30	T _C = 145°C	MUR3060WT	60	1.70	150	175	10	1.0	
200	30	T _C = 150°C	MUR3020PT	35	1.05	200	175	10	0.5	CASE 340D-02 (TO-218AC) 
400	30	T _C = 150°C	MUR3040PT	60	1.25	200	175	10	0.5	
600	30	T _C = 145°C	MUR3060PT	60	1.50	200	175	10	1.0	

12. Refers to maximum leakage current per leg on “WT” and “PT” suffix devices.

FAST RECOVERY RECTIFIERS/GENERAL PURPOSE RECTIFIERS

Table 16. FAST RECOVERY RECTIFIERS/GENERAL PURPOSE RECTIFIERS

V_{RRM} (V)	I_O (A)	I_O Rating Condition	Device	Max V_F @ I_O Rated $T_J = 25^\circ\text{C}$ (V)	Max t_{rr} (ns)	I_{FSM} (A)	T_J Max ($^\circ\text{C}$)	Max I_R V_{RRM} $T_J = 25^\circ\text{C}$ (μA)	Max I_R V_{RRM} $T_A = 100^\circ\text{C}$ (μA)	Package
300	1.0	$T_L = 150^\circ\text{C}$	<i>MRA4003</i>	1.1	–	30	175	10	50	CASE 403D-02 SMA  Cathode = Notch
400	1.0	$T_L = 150^\circ\text{C}$	<i>MRA4004</i>	1.1	–	30	175	10	50	
600	1.0	$T_L = 150^\circ\text{C}$	<i>MRA4005</i>	1.1	–	30	175	10	50	
800	1.0	$T_L = 150^\circ\text{C}$	<i>MRA4006</i>	1.1	–	30	175	10	50	
1000	1.0	$T_L = 150^\circ\text{C}$	<i>MRA4007</i>	1.1	–	30	175	10	50	
400	1.5	$T_L = 118^\circ\text{C}$	<i>MRS1504</i>	1.04	–	50	150	1.0	340	CASE 403A-03 SMB 
50	1.0	$T_A = 75^\circ\text{C}$	<i>1N4001RL</i>	1.1	–	30	175	10	50	CASE 59-10⁽¹³⁾ (DO-41) Plastic  Cathode = Polarity Band
100	1.0	$T_A = 75^\circ\text{C}$	<i>1N4002RL</i>	1.1	–	30	175	10	50	
200	1.0	$T_A = 75^\circ\text{C}$	<i>1N4003RL</i>	1.1	–	30	175	10	50	
400	1.0	$T_A = 75^\circ\text{C}$	<i>1N4004RL</i>	1.1	–	30	175	10	50	
600	1.0	$T_A = 75^\circ\text{C}$	<i>1N4005RL</i>	1.1	–	30	175	10	50	
800	1.0	$T_A = 75^\circ\text{C}$	<i>1N4006RL</i>	1.1	–	30	175	10	50	
1000	1.0	$T_A = 75^\circ\text{C}$	<i>1N4007RL</i>	1.1	–	30	175	10	50	
50	1.0	$T_A = 75^\circ\text{C}$	<i>1N4933RL</i>	1.2	200	30	150	5.0	100	
100	1.0	$T_A = 75^\circ\text{C}$	<i>1N4934RL</i>	1.2	200	30	150	5.0	100	
200	1.0	$T_A = 75^\circ\text{C}$	<i>1N4935RL</i>	1.2	200	30	150	5.0	100	
400	1.0	$T_A = 75^\circ\text{C}$	<i>1N4936RL</i>	1.2	200	30	150	5.0	100	
600	1.0	$T_A = 75^\circ\text{C}$	<i>1N4937RL</i>	1.2	200	30	150	5.0	100	
50	3.0	$T_L = 105^\circ\text{C}$	<i>1N5400RL</i>	1.0	–	200	150	10	50	
100	3.0	$T_L = 105^\circ\text{C}$	<i>1N5401RL</i>	1.0	–	200	150	10	50	
100	3.0	$T_A = 80^\circ\text{C}$	<i>MR851</i>	1.25	200	100	125	10	150 @ 80°C	
200	3.0	$T_L = 105^\circ\text{C}$	<i>1N5402RL</i>	1.0	–	200	150	10	50	
400	3.0	$T_L = 105^\circ\text{C}$	<i>1N5404RL</i>	1.0	–	200	150	10	50	
600	3.0	$T_L = 105^\circ\text{C}$	<i>1N5406RL</i>	1.0	–	200	150	10	50	
800	3.0	$T_L = 105^\circ\text{C}$	<i>1N5407RL</i>	1.0	–	200	150	10	50	
1000	3.0	$T_L = 105^\circ\text{C}$	<i>1N5408RL</i>	1.0	–	200	150	10	50	
200	3.0	$T_A = 80^\circ\text{C}$	<i>MR852RL</i>	1.25	200	100	125	–	200 @ 80°C	
400	3.0	$T_A = 80^\circ\text{C}$	<i>MR854RL</i>	1.25	200	100	125	–	250 @ 80°C	
600	3.0	$T_A = 80^\circ\text{C}$	<i>MR856RL</i>	1.25	200	100	125	–	300 @ 80°C	

13. Package Size: 0.120" max diameter by 0.260" length.

Standard Logic

Standard Logic

Table of Contents

	Page
Arithmetic Functions	286
Buffers	287
Bus Switches	291
Flip-Flops	292
Inverters	294
Latches and Registers	297
Logic Gates	299
Multiplexers	304
Multivibrators	305
Transceivers	306
Translators	307

ARITHMETIC FUNCTIONS

Device	Description	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	P _D Max (W)	I _o Max (mA)	Package
MC14040B	12-Bit Binary Counter	3.00	18.0	1440.0	0.50	2.25	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74HC4040A	12-Stage Binary Counter	2.00	6.0	31.0	0.75	5.20	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74AC4040D	12-Stage Binary Ripple Counter	2.00	6.0	8.0	0.75	24.00	SOIC-16, PDIP-16, EIAJ-16
MC14020B	14-Bit Binary Counter	3.00	18.0	1725.0	0.50	2.25	SOIC-16, PDIP-16
MC74HC4020A	14-Stage Binary Counter	2.00	6.0	31.0	0.75	5.20	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC14060B	14-Stage Binary Counter/Oscillator	3.00	18.0	1300.0	0.50	2.25	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74HC4060A	14-Stage Binary Ripple Counter With Oscillator	2.00	6.0	250.0	0.75	5.20	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC14521B	24-Stage Frequency Divider	3.00	18.0	4500.0	0.50	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14553B	3-Digit BCD Counter	3.00	18.0	1000.0	0.50	2.25	PDIP-16
MC14008B	4-Bit Full Adder	3.00	18.0	320.0	0.50	2.25	SOIC-16, PDIP-16
MC14585B	4-Bit Magnitude Comparator	3.00	18.0	360.0	0.50	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14024B	7-Segment Ripple Counter	3.00	18.0	750.0	0.50	2.25	SOIC-14, PDIP-14, EIAJ-14
MC14516B	Binary Up/Down Counter	3.00	18.0	260.0	0.50	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14029B	Binary/Decade Up/Down Counter	3.00	18.0	200.0	0.50	2.25	SOIC-16, PDIP-16, EIAJ-16
NL7SZ57	Configurable Multifunction Logic	1.65	5.5	2.5	0.20	32.00	SC-88 / SC-70 / SOT-363
NL7SZ97	Configurable Multifunction Logic	1.65	5.5	2.5	0.20	32.00	SC-88 / SC-70 / SOT-363
NLX1G99	Configurable Multifunction Logic	1.65	5.5	6.7	0.20	32.00	ULLGA-8
NL7SZ58	Configurable Multifunction Logic, Inverting	1.65	5.5	2.5	0.20	32.00	SC-88 / SC-70 / SOT-363
NL7SZ98	Configurable Multifunction Logic, Inverting	1.65	5.5	2.5	0.20	32.00	SC-88 / SC-70 / SOT-363
MC14017B	Decade Counter/Divider	3.00	18.0	460.0	0.50	2.25	SOIC-16, PDIP-16, EIAJ-16
MC74HC393A	Dual 4-Stage Binary Ripple Counter	2.00	6.0	52.0	0.75	5.20	TSSOP-16, SOIC-14, PDIP-14, EIAJ-14
MC74HC390A	Dual 4-Stage Binary Ripple Counter, + 2 and + 5 Sections	2.00	6.0	58.0	0.75	5.20	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC14518B	Dual BCD Up Counter	3.00	18.0	230.0	0.50	2.25	SOIC-16, PDIP-16
MC14520B	Dual BCD Up Counter	3.00	18.0	230.0	0.50	2.25	SOIC-16, PDIP-16
MC14490	Hex Bounce Eliminator	3.00	18.0	320.0	0.50	9.00	SOIC-16, PDIP-16, EIAJ-16
MC14022B	Octal Counter	3.00	18.0	460.0	0.50	2.25	SOIC-16, PDIP-16
MC14018B	Preset Divide By N Counter	3.00	18.0	240.0	0.50	2.25	SOIC-16, PDIP-16
MC14526B	Presettable 4-Bit Down Counters	3.00	18.0	450.0	0.50	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14599B	Programmable Divide-By-N Dual 4-Bit Binary/BCD Down Counter	3.00	18.0	500.0	0.50	2.25	SOIC-16, PDIP-16
MC74HC161A	Synchronous 4-Bit Binary Counter	2.0	6.0	16	0.5	5.2	TSSOP-16
MC74HC163A	Synchronous 4-Bit Binary Counter	2.0	6.0	16	0.5	5.2	TSSOP-16
MC74HC160A	Synchronous BCD Decade Counter	2.0	6.0	16	0.5	5.2	TSSOP-16, SOIC-16
MC74ACT163	Synchronous Presettable Binary Counter, TTL Level	4.50	5.5	11.0	0.35	24.00	SOIC-16, PDIP-16, EIAJ-16
MC74AC161	Synchronous Presettable Binary Counter	2.00	6.0	9.5	0.35	24.00	SOIC-16, PDIP-16, EIAJ-16
MC74AC163	Synchronous Presettable Binary Counter	2.00	6.0	9.5	0.35	24.00	SOIC-16, PDIP-16
MC74ACT161	Synchronous Presettable Binary Counter, TTL Level	4.50	5.5	10.5	0.35	24.00	SOIC-16, PDIP-16, EIAJ-16

BUFFERS

Device	Description	Channels	Vcc Min (V)	Vcc Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
MC74LCX16240	16-Bit Buffer	16	2.00	3.6	4.5	24.0	TSSOP-48
MC74LCX16244	16-Bit Buffer	16	2.00	3.6	4.5	24.0	TSSOP-48
M74LCX16240	16-Bit Noninverting Buffer	16	2.00	3.6	4.5	24.0	TSSOP-48
M74LCX16244	16-Bit Noninverting Buffer	16	2.00	3.6	4.5	24.0	TSSOP-48
74VHCX1245	8-Bit Transceiver	1	2.00	6.0	15.0	6.0	QFN-20
MC14511B	BCD-to-7 Segment Latch/Decoder/Driver	1	3.00	18.0	580.0	25.0	SOIC-16, PDIP 16, EIAJ-16
MC14513B	BCD-to-7 Segment Latch/Decoder/Driver	1	3.00	18.0	580.0	25.0	PDIP-18
MC14543B	BCD-to-7 Segment Latch/Decoder/Driver for Liquid Crystals	1	3.00	18.0	660.0	10.0	SOIC-16, PDIP 16, EIAJ-16
NLX1G99	Configurable Multifunction Logic	1	1.65	5.5	6.7	32.0	ULLGA-8
NL27WZ16	Dual Buffer	2	1.65	5.5	3.8	32.0	TSOP-6, SCJ288
NLU2G16	Dual Buffer	2	1.65	5.5	5.5	8.0	UDFN-6, ULLGA-6
NLX2G16	Dual Buffer	2	1.65	5.5	1.8	24.0	ULLGA-6
NL27WZ17	Dual Buffer Schmitt	2	1.65	5.5	5.9	32.0	SCJ288
NLX2G17	Dual Buffer Schmitt	2	1.65	5.5	3.1	24.0	ULLGA-6
NL27WZ07	Dual Buffer, Open Drain	2	1.65	5.5	3.5	32.0	TSOP-6, SCJ288
NLX2G07	Dual Buffer, Open Drain	2	1.65	5.5	3.5	32.0	ULLGA-6
NL27WZ126	Dual Noninverting Buffer With High Enable, 3-State Outputs	2	1.65	5.5	5.7	24.0	US-8
NL27WZ125	Dual Noninverting Buffer With Low Enable, 3-State Outputs	2	1.65	5.5	5.7	32.0	US-8
NLU2G07	Dual Non-Inverting Buffer, Open Drain Output	2	1.65	5.5	5.5	8.0	UDFN-6, ULLGA-6
NLU2G17	Dual Schmitt-Trigger Buffer	2	1.65	5.5	8.6	8.0	UDFN-6, ULLGA-6
MC74VHC50	Hex Buffer	6	2.00	5.5	7.5	8.0	TSSOP-14, SOIC-14, EIAJ-14
MC74LVX50	Hex Buffer, 3-State Outputs	6	2.00	3.6	9.7	4.0	TSSOP-14, SOIC-14, EIAJ-14
MC74LCX07	Hex Buffer, Open Drain Outputs	6	2.00	5.5	3.0	24.0	TSSOP-14, SOIC-14, EIAJ-14
MC14503B	Hex Noninverting Buffer, 3-State Outputs	6	3.00	18.0	80.0	6.2	SOIC-16, PDIP-16, EIAJ-16
MC74HCT365A	Hex Buffers / Line Drivers, 3-State Outputs, TTL Output	6	4.5	5.5	20	7.8	TSSOP-16, SOIC-16
MC74HCT366A	Hex Buffers / Line Drivers, 3-State Outputs, TTL Output	6	4.5	5.5	20	7.8	TSSOP-16, SOIC-16
MC74HC365A	Hex Buffer/Line Driver, Non-Inverting 3-State	6	2.0	6.0	20	7.8	TSSOP-16, SOIC-16
MC74HC367A	Hex Buffer/Line Driver, Non-Inverting 3-State	6	2.0	6.0	20	7.8	TSSOP-16, SOIC-16
MC74HC368A	Hex Buffer/Line Driver, Non-Inverting 3-State	6	2.0	6.0	20	7.8	TSSOP-16, SOIC-16
MC74VHC150A	Non-inverting Buffer / CMOS Logic Level Shifter, TTL Level	6	4.50	5.5	7.7	8.0	TSSOP-14, SOIC-14, EIAJ-14
NLU1G07	Non-Inverting Buffer, Open Drain Output	1	1.65	5.5	5.5	8.0	UDFN-6, ULLGA-6
NLU1GT50	Non-Inverting Buffer, TTL Level	1	1.65	5.5	6.7	8.0	UDFN-6, ULLGA-6
MC74AC240	Octal Buffer/Line Driver, 3-State Outputs	8	2.00	6.0	6.5	24.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74AC244	Octal Buffer/Line Driver, 3-State Outputs	8	2.00	6.0	7.0	24.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20

BUFFERS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC74ACT240	Octal Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	8.5	24.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74ACT241	Octal Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	9.0	24.0	TSSOP-20, SOIC-20, EIAJ-20
MC74ACT244	Octal Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	9.0	24.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74VHCT244	Octal Bus Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	8.4	8.0	TSSOP-20, SOIC-20, EIAJ-20
MC74LCX244	Octal Bus Transceiver With 3-State Outputs	8	2	3.6	7	24	QFN-20
MC74LCX240	Octal Inverting Buffer, 3-State Outputs	8	2.00	3.6	6.5	24.0	TSSOP-20, SOIC-20
74HC540	Octal Inverting Buffer/Line Driver, 3-State Outputs	8	2.00	6.0	25.0	6.0	TSSOP-20
MC74AC540	Octal Inverting Buffer/Line Driver, 3-State Outputs	8	2.00	6.0	6.0	24.0	SOIC-20, PDIP-20
MC74HC540A	Octal Inverting Buffer/Line Driver, 3-State Outputs	8	2.00	6.0	25.0	6.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74LCX540	Octal Inverting Buffer/Line Driver, 3-State Outputs	8	2.00	3.6	6.5	24.0	TSSOP-20, SOIC-20, EIAJ-20
MC74LVX540	Octal Inverting Buffer/Line Driver, 3-State Outputs	8	2.00	3.6	7.0	4.0	EIAJ-20
MC74VHC240	Octal Inverting Buffer/Line Driver, 3-State Outputs	8	2.00	5.5	7.5	8.0	TSSOP-20, SOIC-20
MC74VHC540	Octal Inverting Buffer/Line Driver, 3-State Outputs	8	2.00	5.5	7.0	8.0	TSSOP-20, SOIC-20
MC74ACT540	Octal Inverting Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	8.0	24.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74VHCT240A	Octal Inverting Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	8.8	8.0	TSSOP-20, SOIC-20, EIAJ-20
MC74VHCT540A	Octal Inverting Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	7.0	8.0	EIAJ-20
MC74HC240A	Octal Inverting Buffer/Line Driver/Line Receiver, 3-State Outputs	8	2.00	6.0	22.0	6.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74LVX240	Octal Inverting Bus Buffer, 3-State Outputs	8	2.00	3.6	9.7	4.0	TSSOP-20, SOIC-20, EIAJ-20
MC74LCX244	Octal Noninverting Buffer, 3-State Outputs	8	2.00	3.6	6.5	24.0	TSSOP-20, SOIC-20, EIAJ-20
74HC541	Octal Noninverting Buffer/Line Driver, 3-State Outputs	8	2.00	6.0	25.0	6.0	TSSOP-20
MC74AC541	Octal Noninverting Buffer/Line Driver, 3-State Outputs	8	2.00	6.0	6.0	24.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74HC541A	Octal Noninverting Buffer/Line Driver, 3-State Outputs	8	2.00	6.0	25.0	6.0	TSSOP-20, SOIC-20, EIAJ-20
MC74LCX541	Octal Noninverting Buffer/Line Driver, 3-State Outputs	8	2.00	3.6	6.5	24.0	TSSOP-20, SOIC-20, EIAJ-20
MC74LVX541	Octal Noninverting Buffer/Line Driver, 3-State Outputs	8	2.00	3.6	7.0	4.0	TSSOP-20, SOIC-20, EIAJ-20
MC74VHC541	Octal Noninverting Buffer/Line Driver, 3-State Outputs	8	2.00	5.5	7.0	8.0	TSSOP-20, SOIC-20, EIAJ-20
MC74HCT241A	Octal Noninverting Buffer/Line Driver, 3-State, TTL Output	8	4.5	5.5	22	7.8	TSSOP-20, SOIC-20
MC74ACT541	Octal Noninverting Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	7.5	24.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74HCT541A	Octal Noninverting Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	30.0	6.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74VHCT541A	Octal Noninverting Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.50	5.5	7.9	8.0	TSSOP-20, SOIC-20, EIAJ-20
74HC244	Octal Noninverting Buffer/Line Driver/Line Receiver, 3-State Outputs	8	2.00	5.5	7.5	8.0	TSSOP-20
MC74HC244A	Octal Noninverting Buffer/Line Driver/Line Receiver, 3-State Outputs	8	2.00	6.0	22.0	6.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74HCT244A	Octal Noninverting Buffer/Line Driver/Line Receiver, 3-State Outputs, TTL Level	8	4.50	5.5	26.0	6.0	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74LVX244	Octal Noninverting Bus Buffer, 3-State Outputs	8	2.00	3.6	10.6	4.0	TSSOP-20, SOIC-20, EIAJ-20

BUFFERS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC74VHC244	Octal Noninverting Bus Buffer, 3-State Outputs	8	2.00	5.5	7.5	8.0	TSSOP-20, SOIC-20, EIAJ-20
MC74LVX257	Quad 2-Channel Multiplexer, 3-State Outputs	4	2.00	3.6	12.0	4.0	TSSOP-16, SOIC-16, EIAJ-16
MC74VHC257	Quad 2-Channel Multiplexer, 3-State Outputs	4	2.00	5.5	7.9	8.0	TSSOP-16, SOIC-16, EIAJ-16
MC74VHCT257A	Quad 2-Channel Multiplexer, 3-State Outputs, TTL Level	4	4.50	5.5	7.9	8.0	TSSOP-16, SOIC-16, EIAJ-16
MC74HC126A	Quad Noninverting Buffer With High Enable, 3-State Outputs	4	2.00	6.0	24.0	6.0	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74LVX126	Quad Noninverting Buffer With High Enable, 3-State Outputs	4	2.00	3.6	9.7	4.0	EIAJ-14
MC74VHC126	Quad Noninverting Buffer With High Enable, 3-State Outputs	4	2.00	5.5	7.5	8.0	TSSOP-14, SOIC-14
M74VHCT126A	Quad Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	4	4.50	5.5	7.5	8.0	TSSOP-14
MC74VHCT126A	Quad Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	4	4.50	5.5	7.5	8.0	SOIC-14, EIAJ-14
NLSF3T126	Quad Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	4	2.00	5.5	7.5	25.0	QFN-16
74HC125	Quad Noninverting Buffer With Low Enable, 3-State Outputs	4	2.00	5.5	7.5	8.0	TSSOP-14, SOIC-14
MC74AC125	Quad Noninverting Buffer With Low Enable, 3-State Outputs	4	2.00	6.0	7.0	24.0	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74HC125A	Quad Noninverting Buffer With Low Enable, 3-State Outputs	4	2.00	6.0	24.0	6.0	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74LCX125	Quad Noninverting Buffer With Low Enable, 3-State Outputs	4	2.00	3.6	6.0	24.0	TSSOP-14, SOIC-14
MC74LVX125	Quad Noninverting Buffer With Low Enable, 3-State Outputs	4	2.00	3.6	9.7	4.0	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC125	Quad Noninverting Buffer With Low Enable, 3-State Outputs	4	2.00	5.5	7.5	8.0	TSSOP-14, SOIC-14, EIAJ-14
NLVLCX125	Quad Noninverting Buffer With Low Enable, 3-State Outputs	4	2.00	3.6	6.0	24.0	TSSOP-14
MC74AC125	Quad Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	4	4.50	5.5	9.0	24.0	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74HCT125A	Quad Noninverting Buffer with Low Enable, 3-State Outputs, TTL Output	4	4.5	5.5	9	24	TSSOP-14, SOIC-14
MC74VHCT125A	Quad Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	4	4.50	5.5	7.5	8.0	TSSOP-14, SOIC-14, EIAJ-14
NLSF3T125	Quad Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	4	2.00	5.5	5.5	25.0	QFN-16
NL17SZ16	Single Buffer	1	1.65	5.5	4.5	24.0	SC ₂ 88A, SOT ₂₃ 553
NL17SZ17	Single Buffer, Schmitt	1	1.65	5.5	4.9	24.0	SC ₂ 88A, SOT ₂₃ 553
MC74VHC1G50	Single Noninverting Buffer	1	2.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
MC74VHC1G126	Single Noninverting Buffer With Enable, 3-State	1	2.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
M74VHCT1G126	Single Noninverting Buffer With High Enable, 3-State Outputs	1	2.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
NL17SZ126	Single Noninverting Buffer With High Enable, 3-State Outputs	1	1.65	5.5	5.0	24.0	SC ₂ 88A, SOT ₂₃ 553
M74VHC1GT126	Single Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	1	3.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
NLU1GT126A	Single Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.0	ULLGA-6

BUFFERS

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
NLU1GT126B	Single Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.0	ULLGA-6
NLU1GT126C	Single Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.0	ULLGA-6
NLU1GT126	Single Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.0	UDFN-6
M74VHC1G125	Single Noninverting Buffer With Low Enable, 3-State Outputs	1	2.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
MC74VHC1G125	Single Noninverting Buffer With Low Enable, 3-State Outputs	1	2.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
NL17SZ125	Single Noninverting Buffer With Low Enable, 3-State Outputs	1	1.65	5.5	5.0	24.0	TSOP-5, SC ₂ 88A, SOT-553
NLX1G125	Single Noninverting Buffer With Low Enable, 3-State Outputs	1	1.65	5.5	2.7	24	uBump-5
M74VHC1GT125	Single Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	1	3.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
MC74VHC1GT125	Single Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	1	3.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
NLU1GT125A	Single Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.0	ULLGA-6
NLU1GT125B	Single Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.0	ULLGA-6
NLU1GT125C	Single Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.0	ULLGA-6
NLU1GT125	Single Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.0	UDFN-6
MC74VHC1G07	Single Noninverting Buffer, Open Drain	1	2.00	5.5	7.5	8.0	TSOP-5, SC ₂ 88A
NL17SZ07	Single Noninverting Buffer, Open Drain	1	1.65	5.5	3.5	24.0	SC ₂ 88A, SOT1553
NL17VHC1G07	Single Noninverting Buffer, Open Drain	1	2.00	5.5	7.5	8.0	TSOP-5
M74VHC1GT50	Single Noninverting Buffer, TTL Level	1	1.65	5.5	7.7	8.0	TSOP-5, SC ₂ 88A
MC74VHC1GT50	Single Noninverting Buffer, TTL Level	1	1.65	5.5	7.7	8.0	TSOP-5, SC ₂ 88A
NL27WZ07	The NL27WZ07 is a high performance dual buffer, open drain	2	1.65	5.5	3.5	32.0	SC ₂ 88
NL37WZ16	Triple Buffer	3	1.65	5.5	3.8	32.0	US-8
NLU3G16	Triple Buffer	3	1.65	5.5	5.5	8.0	UDFN-8, ULLGA-8
NLX3G16	Triple Buffer	3	1.65	5.5	3.8	32.0	ULLGA-8
NL37WZ07	Triple Buffer, Open Drain	3	1.65	5.5	3.5	32.0	US-8
NLX3G14	Triple Inverter, Schmitt	3	1.65	5.5	4.9	32.0	ULLGA-8
NL37WZ17	Triple Noninverting Schmitt Trigger Buffer	3	1.65	5.5	4.9	32.0	US-8
NLU3G17	Triple Noninverting Schmitt Trigger Buffer	3	1.65	5.5	8.6	8.0	UDFN-8, ULLGA-8
NLX3G17	Triple Non-Inverting Schmitt-Trigger Buffer	3	1.65	5.5	2.7	24.0	ULLGA-8

BUS SWITCHES

Device	Product Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	R _{ON} Typical (Ω)	Package
7SB3125	1–Bit Bus Switch	1	1.65	5.5	0.25	<5	SC–88, TSOP–5, UDFN–6, ULLGA–6
7SB3126	1–Bit Bus Switch	1	1.65	5.5	0.25	<5	SC–88, TSOP–5, UDFN–6, ULLGA–6
NL7SB3257	1–Bit Digital Switch	1	4	5.5	0.25	<5	ULLGA–6
7SB384	1–Bit Digital Switch SPST	1	1.65	5.5	0.25	<5	SC–88, TSOP–5, UDFN–6, ULLGA–6
7SB385	1–Bit Digital Switch SPST	1	1.65	5.5	0.25	<5	SC–88, TSOP–5, UDFN–6, ULLGA–6
CBTL1G125	1–Bit Low Voltage Bus Switch	1	0.9	4.5	0.25	<5	ULLGA–6
7SB3257	1–Bit Multiplexer/Demultiplexer Bus Switch	1	1.65	5.5	0.25	<5	SC–88, TSOP–5, UDFN–6, ULLGA–6
CBTL3257	2:1 Multiplexer/Demultiplexer Low Voltage Bus Switch	1	0.9	4.5	0.25	<5	ULLGA–6
7WB3125	2–Bit Bus Switch	2	1.65	5.5	0.25	<5	Micro–8, SOIC–8, ULLGA–8
7WB3126	2–Bit Bus Switch	2	1.65	5.5	0.25	<5	Micro–8, SOIC–8, ULLGA–8
7WB3305	2–Bit Bus Switch	2	1.65	5.5	0.25	<5	Micro–8, SOIC–8, ULLGA–8
7WB3306	2–Bit Bus Switch	2	1.65	5.5	0.25	<5	Micro–8, SOIC–8, ULLGA–8
7WB383	2–Bit Bus Switch	2	1.65	5.5	0.25	<5	Micro–8, SOIC–8, ULLGA–8
CBTL3306	2–Bit Low Voltage Bus Switch	2	0.9	4.5	0.25	<5	ULLGA–6
CBTL383	2–Bit Low Voltage Bus Switch	2	0.9	4.5	0.25	<5	ULLGA–6
7WBD3125	2–Bit Translating Bus Switch	2	4	5.5	0.25	3	Micro–8, SOIC–8, ULLGA–8, US8, UQFN–8
7WBD3126	2–Bit Translating Bus Switch	2	4	5.5	0.25	3	Micro–8, SOIC–8, ULLGA–8, US8, UQFN–8
7WBD3305	2–Bit Translating Bus Switch	2	4	5.5	0.25	3	Micro–8, SOIC–8, ULLGA–8, US8, UQFN–8
7WBD3306	2–Bit Translating Bus Switch	2	4	5.5	0.25	3	Micro–8, SOIC–8, ULLGA–8, US8, UQFN–8
7WBD383	2–Bit Translating Bus Switch	2	4	5.5	0.25	3	Micro–8, SOIC–8, ULLGA–8, US8, UQFN–8
74FST3257	Quad 2:1 Multiplexer/Demultiplexer Bus Switch	4	4	5.5	0.25	4	TSSOP–16, SOIC–16, QFN–16

FLIP-FLOPS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
M74LCX16374	16-Bit D-Type Flip-Flop	16	2.00	3.6	6.2	24.00	TSSOP-48
MC74LCX16374	16-Bit D-Type Flip-Flop	16	2.00	3.6	6.2	24.00	TSSOP-48
MC14013B	Dual D-Type Flip-Flop	2	3.00	18.0	150.0	2.25	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74LCX74	Dual D-Type Flip-Flop	2	2.00	3.6	7.0	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LVX74	Dual D-Type Flip-Flop	2	2.00	3.6	13.6	4.00	TSSOP-14, SOIC-14, EIAJ-14
74HC74	Dual D-Type Flip-Flop, Set and Reset	2	2.00	5.5	9.3	8.00	TSSOP-14, SOIC-14
MC74HC74A	Dual D-Type Flip-Flop, Set and Reset	2	2.00	6.0	20.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74HC174A	Dual D-Type Flip-Flop, Set and Reset, TTL Level	2	4.50	5.5	24.0	4.00	SOIC-14, PDIP-14
MC74VHC174A	Dual D-Type Flip-Flop, Set and Reset, TTL Level	2	4.50	5.5	8.8	8.00	TSSOP-14, SOIC-14
MC74AC74	Dual D-Type Positive Edge Trigger	2	2.00	6.0	9.5	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74ACT74	Dual D-Type Positive Edge Trigger, TTL Level	2	4.50	5.5	10.0	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC14027B	Dual J-K Flip-Flop	2	3.00	18.0	150.0	2.25	SOIC-16, PDIP-16
MC74HC73A	Dual J-K Flip Flop w/ Reset	2	2	6	21	5.2	TSSOP-14, SOIC-14
MC74HC112A	Dual Negative-Edge-Triggered J-K Flip-Flops with Set and Reset	2	2	6	21	5.2	TSSOP-16, SOIC-16
MC14174B	Hex D-Type Flip-Flop	6	3.00	18.0	160.0	2.25	SOIC-16, PDIP-16
MC74HC174A	Hex D-Type Flip-Flop, Clock	6	2.00	6.0	22.0	4.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
NLSF1174	Hex D-Type Flip-Flop, Common Clock and Reset	6	2.00	6.0	19.0	25.00	QFN-16
74HC574	Octal D-Type 3-State Noninverting Flip-Flop	8	2.00	5.5	10.6	8.00	TSSOP-20
MC74HC574A	Octal D-Type 3-State Noninverting Flip-Flop	8	2.00	6.0	32.0	6.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
74HC374	Octal D-Type Flip-Flop	8	2.00	5.5	10.1	8.00	TSSOP-20
MC74AC273	Octal D-Type Flip-Flop	8	2.00	6.0	10.0	24.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74HC273A	Octal D-Type Flip-Flop	8	2.00	6.0	29.0	6.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74HC374A	Octal D-Type Flip-Flop	8	2.00	6.0	25.0	6.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74LCX374	Octal D-Type Flip-Flop	8	2.00	3.6	8.5	24.00	TSSOP-20, SOIC-20, EIAJ-20
MC74LCX574	Octal D-Type Flip-Flop Flow Through Pinout	8	2.00	3.6	8.5	3.60	TSSOP-20, SOIC-20, EIAJ-20
MC74AC374	Octal D-Type Flip-Flop, 3-State Outputs	8	2.00	6.0	9.5	24.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74AC574	Octal D-Type Flip-Flop, 3-State Outputs	8	2.00	6.0	9.5	24.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74LVX374	Octal D-Type Flip-Flop, 3-State Outputs	8	2.00	3.6	14.1	4.00	TSSOP-20, SOIC-20, EIAJ-20
MC74LVX374	Octal D-Type Flip-Flop, 3-State Outputs	8	2.00	3.6	14.1	4.00	EIAJ-20
MC74LVX574	Octal D-Type Flip-Flop, 3-State Outputs	8	2.00	3.6	16.7	4.00	TSSOP-20, SOIC-20, EIAJ-20
MC74VHC374	Octal D-Type Flip-Flop, 3-State Outputs	8	2.00	5.5	10.1	8.00	TSSOP-20, SOIC-20, EIAJ-20
MC74VHC574	Octal D-Type Flip-Flop, 3-State Outputs	8	2.00	5.5	10.6	8.00	TSSOP-20, SOIC-20

FLIP-FLOPS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC74VHC74	Octal D-Type Flip-Flop, 3-State Outputs	2	2.00	5.5	9.3	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC74ACT374	Octal D-Type Flip-Flop, 3-State Outputs, TTL Level	8	4.50	5.5	10.0	24.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74ACT574	Octal D-Type Flip-Flop, 3-State Outputs, TTL Level	8	4.50	5.5	11.0	24.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74AC377	Octal D-Type Flip-Flop, Clock Enable	8	2.00	6.0	10.0	24.00	TSSOP-20, SOIC-20, PDIP-20
MC74ACT377	Octal D-Type Flip-Flop, Clock Enable, TTL Level	8	4.50	5.5	10.0	24.00	SOIC-20, PDIP-20, EIAJ-20
MC74ACT273	Octal D-Type Flip-Flop, TTL Level	8	4.50	5.5	11.0	24.00	TSSOP-20, SOIC-20, PDIP-20
MC74HCT279A	Octal D-Type Flip-Flop, TTL Level	8	4.50	5.5	25.0	6.00	TSSOP-20, SOIC-20, PDIP-20
MC74HC377A	Octal D-Type Flip-Flop w/Enable, Positive-Edge Trigger	8	2	6	32	15	TSSOP-20, SOIC-20
MC74HCT374A	Octal D-Type Noninverting Flip-Flop, 3-State, TTL Level	8	4.50	5.5	31.0	6.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74HCT574A	Octal D-Type Noninverting Flip-Flop, 3-State, TTL Level	8	4.50	5.5	30.0	6.00	TSSOP-20, SOIC-20, PDIP-20
MC74VHC374A	Octal D-Type Noninverting Flip-Flop, 3-State, TTL Level	8	4.50	5.5	10.4	8.00	TSSOP-20, SOIC-20, EIAJ-20
MC74VHC1574A	Octal D-Type Noninverting Flip-Flop, 3-State, TTL Level	8	4.50	5.5	10.4	8.00	TSSOP-20, SOIC-20
MC14175B	Quad D-Type Flip-Flop	4	3.00	18.0	160.0	2.25	SOIC-16, PDIP-16, EIAJ-16
MC74HC175A	Quad D-type Flip-Flop, Common Clock and Reset	4	2.00	6.0	26.0	4.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
NL17SZ74	Single D-Type Flip-Flop	1	1.65	5.5	5.0	24.00	US-8

INVERTERS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
NLX1G99	Configurable Multifunction Logic	1	1.65	5.5	6.7	32.00	ULLGA-8
MC14007UB	Dual Comparator Pair Plus Inverter	3	3.00	18.0	75.0	2.50	SOIC-14, PDIP-14, EIAJ-14
NL27WZ04	Dual Inverter	2	1.65	5.5	3.6	32.00	TSOP-6, SC-88
NLU2G04	Dual Inverter	2	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLX2G04	Dual Inverter	2	1.65	5.5	1.8	24.00	ULLGA-6
NL27WZ06	Dual Inverter, Open Drain	2	1.65	5.5	3.0	32.00	TSOP-6, SC-88
NLX2G06	Dual Inverter, Open Drain	2	1.65	5.5	3.0	32.00	ULLGA-6
NL27WZ14	Dual Inverter, Schmitt	2	1.65	5.5	4.9	32.00	TSOP-6, SC-88
NLX2G14	Dual Inverter, Schmitt	2	1.65	5.5	4.9	32.00	ULLGA-6
NLU2G14	Dual Schmitt-Trigger Inverter	2	1.65	5.5	8.6	8.00	UDFN-6, ULLGA-6
NL27WZU04	Dual Unbuffered Inverter	2	1.65	5.5	5.6	32.00	TSOP-6, SC-88
NLU2GU04	Dual Unbuffered Inverter	2	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLX2GU04	Dual Unbuffered Inverter	2	1.65	5.5	2.7	16.00	ULLGA-6
MC14049B	Hex Buffer	6	3.00	18.0	80.0	16.00	SOIC-16, PDIP-16, EIAJ-16
MC14049UB	Hex Buffer	6	3.00	18.0	65.0	16.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC14050B	Hex Buffer	6	3.00	18.0	80.0	16.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC14572UB	Hex Gate	6	3.00	18.0	100.0	2.25	SOIC-16, PDIP-16
MC14069UB	Hex Inverter	6	3.00	18.0	100.0	2.25	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74AC04	Hex Inverter	6	2.00	6.0	7.0	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74HC04A	Hex Inverter	6	2.00	6.0	15.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74LCX04	Hex Inverter	6	2.00	3.6	5.2	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LVX04	Hex Inverter	6	2.00	3.6	9.7	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC04	Hex Inverter	6	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LVXU04	Hex Inverter (Unbuffered)	6	2.00	3.6	9.7	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74AC05	Hex Inverter Open-Drain	6	2.00	6.0	6.0	24.00	SOIC-14, PDIP-14, EIAJ-14
MC74AC14	Hex Inverter Schmitt Trigger	6	2.00	6.0	10.0	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74ACT14	Hex Inverter Schmitt Trigger, TTL Level	6	4.50	5.5	11.5	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74HC05A	Hex Inverter, Open Drain Outputs	6	2	6	15	5.2	TSSOP-14, SOIC-14
MC74LCX06	Hex Inverter, Open Drain Outputs	6	2.00	3.6	3.7	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74ACT05	Hex Inverter, Open-Drain Outputs, TTL Level	6	4.50	5.5	8.5	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
74HCT04	Hex Inverter, TTL Level	6	4.50	5.5	7.7	8.00	TSSOP-14, SOIC-14
MC74ACT04	Hex Inverter, TTL Level	6	4.50	5.5	8.5	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14

INVERTERS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC74HCT04A	Hex Inverter, TTL Level	6	4.50	5.5	17.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74VHC04A	Hex Inverter, TTL Level	6	4.50	5.5	7.7	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LCX14	Hex Schmitt Inverter	6	2.00	3.6	6.5	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LVX14	Hex Schmitt Inverter	6	2.00	3.6	14.1	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC14	Hex Schmitt Inverter	6	2.00	5.5	10.6	8.00	TSSOP-14, SOIC-14
MC14106B	Hex Schmitt Trigger	6	3.00	18.0	100.0	2.25	TSSOP-14, SOIC-14, PDIP-14
MC14584B	Hex Schmitt Trigger	6	3.00	18.0	100.0	2.25	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
74HC14	Hex Schmitt-Trigger Inverter	6	2.00	5.5	10.6	8.00	TSSOP-14, SOIC-14
MC74HC14A	Hex Schmitt-Trigger Inverter	6	2.00	6.0	15.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
74HCT14	Hex Schmitt-Trigger Inverter, TTL Level	6	4.50	5.5	9.6	8.00	TSSOP-14, SOIC-14
MC74HCT14A	Hex Schmitt-Trigger Inverter, TTL Level	6	4.50	5.5	32.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74VHCT14A	Hex Schmitt-Trigger Inverter, TTL Level	6	4.50	5.5	9.6	8.00	TSSOP-14, SOIC-14, EIAJ-14
74HCU04	Hex Unbuffered Inverter	6	2.00	5.5	7.0	8.00	TSSOP-14, SOIC-14
MC74HCU04A	Hex Unbuffered Inverter	6	2.00	6.0	14.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74VHCU04	Hex Unbuffered Inverter	6	2.00	5.5	7.0	8.00	TSSOP-14, SOIC-14, EIAJ-14
NLU1GT04	Inverting Buffer, TTL Level	1	1.65	5.5	6.7	8.00	UDFN-6, ULLGA-6
NLU1GT14	Schmitt-Trigger Inverter, TTL Level	1	1.65	5.5	8.6	8.00	UDFN-6, ULLGA-6
MC74HC1G04	Single Inverter	1	2.00	6.0	20.0	2.00	TSOP-5, SC ₂ 88A
MC74VHC1G04	Single Inverter	1	2.00	5.5	7.5	8.00	TSOP-5, SC ₂ 88A
NL17SZ04	Single Inverter	1	1.65	5.5	4.3	24.00	SC ₂ 88A, SOT ₂₃ 553
NLU1G04	Single Inverter	1	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
MC74VHC1G05	Single Inverter, Open Drain	1	2.00	5.5	7.5	8.00	TSOP-5, SC ₂ 88A
NL17SZ06	Single Inverter, Open Drain	1	1.65	5.5	3.0	24.00	SC ₂ 88A, SOT ₂₃ 553
MC74HC1G14	Single Inverter, Schmitt Input	1	2.00	6.0	20.0	2.00	TSOP-5, SC ₂ 88A
MC74VHC1G14	Single Inverter, Schmitt Input	1	2.00	5.5	10.6	8.00	TSOP-5, SC ₂ 88A
NL17SZ14	Single Inverter, Schmitt Input	1	1.65	5.5	5.9	24.00	SC ₂ 88A, SOT ₂₃ 553
M74VHC1GT14	Single Inverter, Schmitt Input, TTL Level	1	3.00	5.5	10.6	8.00	TSOP-5, SC ₂ 88A
MC74VHC1GT14	Single Inverter, Schmitt Input, TTL Level	1	3.00	5.5	10.6	8.00	TSOP-5, SC ₂ 88A
M74VHC1GT04	Single Inverter, TTL Level	1	3.00	5.5	7.7	8.00	TSOP-5, SC ₂ 88A
MC74VHC1GT04	Single Inverter, TTL Level	1	3.00	5.5	7.7	8.00	TSOP-5, SC ₂ 88A
NLU1G14	Single Schmitt-Trigger Inverter	1	1.65	5.5	8.6	8.00	UDFN-6, ULLGA-6
M74VHC1GU04	Single Unbuffered Inverter	1	2.00	5.5	7.0	8.00	TSOP-5, SC ₂ 88A

INVERTERS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC74HC1GU04	Single Unbuffered Inverter	1	2.00	6.0	20.0	2.00	TSOP-5, SC ₂ 88A
MC74VHC1GU04	Single Unbuffered Inverter	1	2.00	5.5	7.0	8.00	SC ₂ 88A
NL17SZU04	Single Unbuffered Inverter	1	1.65	5.5	5.0	24.00	SC ₂ 88A, SOT ₂₃ 553
NLU1GU04	Single Unbuffered Inverter	1	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLV17SZU04	Single Unbuffered Inverter	1	1.65	5.5	5.0	24.00	SC ₂ 88A
NL37WZ04	Triple Inverter	3	1.65	5.5	3.6	32.00	US-8
NL37WZ06	Triple Inverter, Open Drain	3	1.65	5.5	3.0	32.00	US-8
NL37WZ14	Triple Inverter, Schmitt	3	1.65	5.5	4.9	32.00	US-8
NLU3G14	Triple Schmitt-Trigger Inverter	3	1.65	5.5	8.6	8.00	UDFN-8, ULLGA-8
MC74LCXU04	Unbuffered Hex Inverter	6	2.00	3.6	3.6	16.00	TSSOP-14, SOIC-14, EIAJ-14

LATCHES AND REGISTERS

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
MC14557B	1 To 64 Bit Variable Length Shift Register	1	3.0	18.0	260.0	2.25	SOIC-16, PDIP-16
M74LXC16373	16-Bit Transparent Latch	16	2.0	3.6	5.4	24.00	TSSOP-48
MC74LXC16373	16-Bit Transparent Latch	16	2.0	3.6	5.4	24.00	TSSOP-48
MC14078B	4-Bit D-Type Register, Three-State Outputs	4	3.0	18.0	250.0	2.25	SOIC-16, PDIP-16
MC74HC599A	8/Bit Shift Register	1	2.0	6.0	40.0	6.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74AC259DG	8-Bit Addressable Latch	8	2.0	6.0	10.0	24.00	SOIC-16, PDIP-16, EIAJ-16
MC74ACT259	8-Bit Addressable Latch, TTL Level	8	4.5	5.5	11.0	24.00	SOIC-16, PDIP-16
MC74HCT259A	8-Bit Addressable Latch, TTL Output	1	4.5	5.5	35	4	TSSOP-16, SOIC-16
MC74LVX259	8-Bit Addressable Latch/1-of-8 Decoder CMOS Logic Level Shifter	1	2.0	3.6	12.0	4.00	TSSOP-16, SOIC-16, EIAJ-16
MC74VHC259	8-Bit Addressable Latch/1-of-8 Decoder CMOS Logic Level Shifter	1	2.0	5.5	10.0	8.00	TSSOP-16, SOIC-16, EIAJ-16
MC74VHC1259A	8-Bit Addressable Latch/1-of-8 Decoder, TTL Level	1	4.5	5.5	10.0	8.00	TSSOP-16, SOIC-16, EIAJ-16
MC74HC259A	8-Bit Addressable Latches	1	2.0	6.0	30	5.2	TSSOP-16, SOIC-16
MC14099B	8-Bit Addressable Latches	1	3.0	18.0	150.0	2.25	SOIC-16, PDIP-16
NLV14099B	8-Bit Addressable Latches	1	3.0	18.0	150.0	2.25	SOIC-16
MC74HC165A	8-Bit Serial or Parallel-Input/Serial Output Shift Register	1	2.0	6.0	30.0	4.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74HC164A	8-Bit Serial-Input/Parallel-Output Shift Register	1	2.0	6.0	32.0	4.00	TSSOP-14, SOIC-14, PDIP-14
MC74HC597A	8-Bit Shift Register	1	2.0	6.0	45	5.2	TSSOP-16, SOIC-16
MC74HCT595A	8-Bit Shift Registers, 3-State Output Registers, TTL Output	1	4.5	5.5	34	4	TSSOP-16, SOIC-16
74HC595	8-Bit Shift Register w/Output Storage Register (3-State)	1	2.0	6.0	28.0	6.00	TSSOP-16, SOIC-16
MC74VHC595	8-Bit Shift Register w/Output Storage Register (3-State)	1	2.0	5.5	10.0	8.00	SOIC-16
MC14094B	8-Bit Shift/Store Register, Three-State Outputs	1	3.0	18.0	250.0	2.25	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC14014B	8-Bit Static S/R	1	3.0	18.0	340.0	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14021B	8-Bit Static Shift Register	1	3.0	18.0	340.0	2.25	SOIC-16, PDIP-16, EIAJ-16
MC74HC4094A	8-Stage Bus Register, 3-State	1	2.0	6.0	33	5.2	TSSOP-16, SOIC-16
MC74HCT4094A	8-Stage Bus Register, 3-State, TTL Output	1	4.5	5.5	36	4	TSSOP-16, SOIC-16
MC14598B	9-Bit Bus-Compatible Latches	8	3.0	18.0	250.0	6.00	PDIP-18
MC14015B	Dual 4-Bit Static Shift Register	2	3.0	18.0	250.0	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14517B	Dual 64-Bit Static Shift Register	2	3.0	18.0	300.0	2.25	SOIC-16, PDIP-16
MC74HCT575A	Octal 3-State Inverter Transceiver/Latch, TTL Level	8	4.5	5.5	30.0	6.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74VHC573	Octal 3-State Non-Inverting D-Type Latch	8	2.0	5.5	8.8	8.00	TSSOP-20, SOIC-20, EIAJ-20
74HC373	Octal 3-State Non-Inverting Transparent Latch	8	2.0	5.5	9.2	8.00	TSSOP-20

LATCHES AND REGISTERS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC74HC373A	Octal 3-State Non-Inverting Transparent Latch	8	2.0	6.0	25.0	6.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74HC573A	Octal 3-State Non-Inverting Transparent Latch	8	2.0	6.0	30.0	6.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74AC573	Octal Buffer/Line Driver, 3-State Outputs	8	2.0	6.0	10.0	24.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74ACT573	Octal Buffer/Line Driver, 3-State Outputs, TTL Level	8	4.5	5.5	10.5	24.00	TSSOP-20, SOIC-20, PDIP-20
MC74LVX573	Octal D-Type Latch 3-State Outputs	8	2.0	3.6	12.8	4.00	TSSOP-20, SOIC-20, EIAJ-20
MC74ACT564	Octal D-Type Latch, 3-State Outputs, TTL Level	8	4.5	5.5	10.5	24.00	SOIC-20, PDIP-20
MC74VHCT573A	Octal D-Type Latch, 3-State Outputs, TTL Level	8	4.5	5.5	9.5	8.00	TSSOP-20, SOIC-20
MC74HCT373A	Octal Latch, TTL Level	8	4.5	5.5	28.0	6.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74LCX373	Octal Transparent Latch	8	2.0	3.6	8.0	24.00	TSSOP-20, SOIC-20, EIAJ-20
MC74LVX373	Octal Transparent Latch 3-State	8	2.0	3.6	12.8	4.00	TSSOP-20, SOIC-20, EIAJ-20
MC74VHC373	Octal Transparent Latch 3-State	8	2.0	5.5	9.2	8.00	TSSOP-20, SOIC-20, EIAJ-20
MC74LCX573	Octal Transparent Latch Flow Through Pinout	8	2.0	3.6	8.0	24.00	TSSOP-20, SOIC-20, EIAJ-20
MC74AC373	Octal Transparent Latch, 3-State Outputs	8	2.0	6.0	9.5	24.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74ACT373	Octal Transparent Latch, 3-State Outputs, TTL Level	8	4.5	5.5	10.0	24.00	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74VHCT373A	Octal Transparent Latch, 3-State Outputs, TTL Level	8	4.5	5.5	9.5	8.00	TSSOP-20, SOIC-20
MC14048B	Quad R-S Latches	4	3.0	18.0	175.0	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14044B	Quad R-S Latches	4	3.0	18.0	175.0	2.25	SOIC-16, PDIP-16
MC14042B	Quad Transparent Latch	4	3.0	18.0	180.0	2.25	SOIC-16, PDIP-16
MC74HC595A	Shift Register 3-State	1	2.0	6.0	28.0	6.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74VHC595	Shift Register 3-State	1	2.0	5.5	10.0	8.00	TSSOP-16
MC74HC595A	Shift Register 3-State	1	2.0	6.0	28.0	6.00	TSSOP-16
MC14548B	Successive Approximation Registers	1	3.0	18.0	420.0	2.25	SOIC-16, PDIP-16

LOGIC GATES

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
NL7SZ57	Configurable Multifunction Logic	3	1.65	5.5	2.5	32.00	SC-88
NLX1G57	Configurable Multifunction Logic	1	1.65	5.5	5.1	24.00	ULLGA-6
NLX1G99	Configurable Multifunction Logic	1	1.65	5.5	6.7	32.00	ULLGA-6
NLX1G97	Configurable Multifunction Logic	1	1.65	5.5	6.3	24.00	ULLGA-6
NL7SZ58	Configurable Multifunction Logic, Inverting	3	1.65	5.5	2.5	32.00	SC-88
NLX1G58	Configurable Multifunction Logic, Inverting	1	1.65	5.5	5.1	24.00	ULLGA-6
NLX1G98	Configurable Multifunction Logic, Inverting	1	1.65	5.5	5.1	24.00	ULLGA-6
NL27WZ08	Dual 2-Input AND Gate	2	1.65	5.5	3.7	32.00	US-8
NLX2G08	Dual 2-Input AND Gate	2	1.65	5.5	4.8	24	ULLGA-8, UQFN-8
NL27WZ86	Dual 2-Input Exclusive OR Gate	2	1.65	5.5	4.2	32.00	US-8
NLX2G86	Dual 2-Input Exclusive OR Gate	2	1.65	5.5	4.8	24	ULLGA-8, UQFN-8
NL27WZ00	Dual 2-Input NAND Gate	2	1.65	5.5	3.6	32.00	US-8
NLX2G00	Dual 2-Input NAND Gate	2	1.65	5.5	4.6	24	ULLGA-8
NL27WZ02	Dual 2-Input NOR Gate	2	1.65	5.5	3.7	32.00	US-8
NLX2G02	Dual 2-Input NOR Gate	2	1.65	5.5	4.8	24	ULLGA-8
NL27WZ32	Dual 2-Input OR Gate	2	1.65	5.5	3.7	32.00	US-8
NLX2G32	Dual 2-Input OR Gate	2	1.65	5.5	4.8	24	ULLGA-8, UQFN-8
MC14082B	Dual 4-Input AND Gate	2	3.00	18.0	130.0	2.25	SOIC-14, PDIP-14
MC14012B	Dual 4-Input NAND Gates	2	3.00	18.0	130.0	2.25	SOIC-14, PDIP-14
MC74HC20A	Dual 4-Input NAND Gate	2	2.0	6.0	26	5.2	TSSOP-14, SOIC-14
MC74AC20	Dual 4-Input NAND Gate	2	2.00	6.0	7.0	24.00	SOIC-14, PDIP-14, EIAJ-14
MC74ACT20	Dual 4-Input NAND Gate, TTL Level	2	4.50	5.5	9.0	24.00	SOIC-14, PDIP-14
MC74HCT20A	Dual 4-Input NAND Gate, TTL Output	2	4.5	5.5	25	4	TSSOP-14, SOIC-14
NLU2G16	Dual Buffer	2	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLU2G04	Dual Inverter	2	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLU2G06	Dual Inverter, Open Drain Output	2	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLU2G07	Dual Non-Inverting Buffer, Open Drain Output	2	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLU2G17	Dual Schmitt-Trigger Buffer	2	1.65	5.5	8.6	8.00	UDFN-6, ULLGA-6
NLU2G14	Dual Schmitt-Trigger Inverter	2	1.65	5.5	8.6	8.00	UDFN-6, ULLGA-6
NLU2GU04	Dual Unbuffered Inverter	2	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
74HC04	Hex Inverter	6	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14
NLU1G07	Non-Inverting Buffer, Open Drain Output	1	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLU1GT50	Non-Inverting Buffer, TTL Level	1	1.65	5.5	6.7	8.00	UDFN-6, ULLGA-6

LOGIC GATES

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
74HC08	Quad 2-Input AND Gate	4	2.00	5.5	7.9	8.00	TSSOP-14, SOIC-14
MC14081B	Quad 2-Input AND Gate	4	3.00	18.0	130.0	2.25	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74AC08	Quad 2-Input AND Gate	4	2.00	6.0	7.5	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74HC08A	Quad 2-Input AND Gate	4	2.00	6.0	15.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74LCX08	Quad 2-Input AND Gate	4	2.00	3.6	5.5	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LVX08	Quad 2-Input AND Gate	4	2.00	3.6	10.6	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC08	Quad 2-Input AND Gate	4	2.00	5.5	7.9	8.00	TSSOP-14, SOIC-14, EIAJ-14
NLSF308	Quad 2-Input AND Gate	4	2.00	5.5	7.9	8.00	QFN-16
74HCT08	Quad 2-Input AND Gate, TTL Level	4	4.50	5.5	7.9	8.00	TSSOP-14, SOIC-14
MC74ACT08	Quad 2-Input AND Gate, TTL Level	4	4.50	5.5	9.0	24.00	TSSOP-14, SOIC-14, PDIP-14
MC74HCT08A	Quad 2-Input AND Gate, TTL Output	4	4.5	5.5	15	4	TSSOP-14, SOIC-14
74HC86	Quad 2-Input Exclusive OR Gate	4	2.00	5.5	8.0	8.00	TSSOP-14, SOIC-14
MC74AC86	Quad 2-Input Exclusive OR Gate	4	2.00	6.0	8.5	24.00	TSSOP-14, SOIC-14, PDIP-14
MC74HC86A	Quad 2-Input Exclusive OR Gate	4	2.00	6.0	20.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74VHC86	Quad 2-Input Exclusive OR Gate	4	2.00	5.5	8.8	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC74ACT86	Quad 2-Input Exclusive-OR Gate, TTL Level	4	4.50	5.5	9.5	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74HCT86A	Quad 2-Input Exclusive-OR Gate, TTL Level	4	4.5	5.5	17	4	TSSOP-14, SOIC-14
74HC00	Quad 2-Input NAND Gate	4	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14
MC14011B	Quad 2-Input NAND Gate	4	3.00	18.0	100.0	2.25	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC14011UB	Quad 2-Input NAND Gate	4	3.00	18.0	100.0	2.25	SOIC-14, PDIP-14
MC74AC00	Quad 2-Input NAND Gate	4	2.00	6.0	8.0	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74HC00A	Quad 2-Input NAND Gate	4	2.00	6.0	15.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74LCX00	Quad 2-Input NAND Gate	4	2.00	3.6	5.2	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LVX00	Quad 2-Input NAND Gate	4	2.00	3.6	9.7	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC00	Quad 2-Input NAND Gate	4	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC74HC03A	Quad 2-Input NAND Gate, Open Drain Outputs	4	2.00	6.0	24.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
74HC132	Quad 2-Input NAND Gate, Schmitt Trigger	4	2.00	5.5	9.7	8.00	TSSOP-14, SOIC-14
MC74ACT00	Quad 2-Input NAND Gate, TTL Level	4	4.50	5.5	9.0	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74VHCT00A	Quad 2-Input NAND Gate, TTL Level	4	3.00	5.5	7.9	8.00	TSSOP-14, SOIC-14
MC74HCT132A	Quad 2-Input NAND Gate, TTL Level	4	4.5	5.5	25	4	TSSOP-14, SOIC-14
MC14098B	Quad 2-Input NAND Schmitt Trigger	4	3.00	18.0	100.0	2.25	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74AC132	Quad 2-Input NAND Schmitt Trigger	4	2.00	6.0	9.0	24.00	SOIC-14, PDIP-14, EIAJ-14
MC74HC132A	Quad 2-Input NAND Schmitt Trigger	4	2.00	6.0	25.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14

LOGIC GATES

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC74LVX132	Quad 2-Input NAND Schmitt Trigger	4	2.00	3.6	15.4	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC132	Quad 2-Input NAND Schmitt Trigger	4	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC74ACT132	Quad 2-Input NAND, Schmitt Trigger, TTL Level	4	4.50	5.5	11.5	24.00	SOIC-14, PDIP-14, EIAJ-14
MC74VHC132A	Quad 2-Input NAND, Schmitt Trigger, TTL Level	4	4.50	5.5	9.7	8.00	TSSOP-14, SOIC-14, EIAJ-14
74HC02	Quad 2-Input NOR Gate	4	2.00	6.0	22.0	4.00	TSSOP-14, SOIC-14
MC14001B	Quad 2-Input NOR Gate	4	3.00	18.0	100.0	2.25	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC14001UB	Quad 2-Input NOR Gate	4	3.00	18.0	100.0	2.25	SOIC-14, PDIP-14
MC74AC02	Quad 2-Input NOR Gate	4	2.00	6.0	6.5	24.00	TSSOP-14, SOIC-14, PDIP-14
MC74HC02A	Quad 2-Input NOR Gate	4	2.00	6.0	15.0	4.00	TSSOP-14, SOIC-14, PDIP-14
MC74LCX02	Quad 2-Input NOR Gate	4	2.00	3.6	5.2	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LVX02	Quad 2-Input NOR Gate	4	2.00	3.6	10.1	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC02	Quad 2-Input NOR Gate	4	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14
NLSF302	Quad 2-Input NOR Gate	4	2.00	5.5	7.5	8.00	QFN-16
MC74ACT02	Quad 2-Input NOR Gate, TTL Level	4	4.50	5.5	9.5	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74VHC02A	Quad 2-Input NOR Gate, TTL Level	4	4.50	5.5	7.5	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC08A	Quad 2-Input NOR Gate, TTL Level	4	4.50	5.5	7.9	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC14071B	Quad 2-Input OR Gate	4	3.00	18.0	130.0	2.25	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74AC32	Quad 2-Input OR Gate	4	2.00	6.0	7.5	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC74LCX32	Quad 2-Input OR Gate	4	2.00	3.6	5.5	24.00	TSSOP-14, SOIC-14, EIAJ-14
MC74LVX32	Quad 2-Input OR Gate	4	2.00	3.6	10.1	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC03A	Quad 2-Input OR Gate / CMOS Logic Level Shifter, TTL Level	4	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC74ACT32	Quad 2-Input OR Gate, TTL Level	4	4.50	5.5	9.0	24.00	TSSOP-14, SOIC-14, PDIP-14
MC74HC03A	Quad 2-Input OR Gate, TTL Level	4	4.5	5.5	15	4	TSSOP-14, SOIC-14
MC74LCX86	Quad 2-Input XOR Gate	4	2.00	3.6	6.5	24.00	TSSOP-14, SOIC-14
MC74LVX86	Quad 2-Input XOR Gate	4	2.00	3.6	12.8	4.00	TSSOP-14, SOIC-14, EIAJ-14
MC74VHC08A	Quad 2-Input XOR Gate / CMOS Logic Level Shifter, TTL Level	4	2.00	5.5	8.8	8.00	TSSOP-14, SOIC-14, EIAJ-14
MC14077B	Quad Exclusive NOR Gate	4	3.00	18.0	150.0	2.25	SOIC-14, PDIP-14, EIAJ-14
74HC32	Quad OR Gate	4	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14
MC74HC32A	Quad OR Gate	4	2.00	6.0	15.0	4.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
74HC03	Quad OR Gate, TTL Level	4	2.00	6.0	22.0	4.00	TSSOP-14, SOIC-14
MC14070B	Quad XOR Gate	4	3.00	18.0	150.0	2.25	SOIC-14, PDIP-14, EIAJ-14
NLU1GT14	Schmitt-Trigger Inverter, TTL Level	1	1.65	5.5	8.6	8.00	UDFN-6, ULLGA-6
MC74VHC32	Single 2-1 Quad OR Gate	4	2.00	5.5	7.5	8.00	TSSOP-14, SOIC-14, EIAJ-14

LOGIC GATES

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
MC74HC1G08	Single 2-Input AND Gate	1	2.00	6.0	20.0	2.00	TSOP-5, SC-88A
MC74VHC1G08	Single 2-Input AND Gate	1	2.00	5.5	7.9	8.00	TSOP-5, SC-88A
NL17SV08	Single 2-Input AND Gate	1	0.90	3.6	1.0	24.00	SOT-553
NL17SZ08	Single 2-Input AND Gate	1	1.65	5.5	4.5	24.00	SC-88A, SOT-553
NLU1G08	Single 2-Input AND Gate	1	1.65	5.5	5.9	8.00	UDFN-6, ULLGA-6
MC74VHC1G09	Single 2-Input AND Gate, Open Drain	1	2.00	5.5	7.9	8.00	TSOP-5, SC-88A
M74VHC1GT08	Single 2-Input AND Gate, TTL Level	1	3.00	5.5	7.9	8.00	TSOP-5, SC-88A
MC74VHC1GT08	Single 2-Input AND Gate, TTL Level	1	3.00	5.5	7.9	8.00	TSOP-5, SC-88A
MC74VHC1G86	Single 2-Input Exclusive OR Gate	1	2.00	5.5	8.8	8.00	TSOP-5, SC-88A
NL17SZ86	Single 2-Input Exclusive OR Gate	1	1.65	5.5	4.2	24.00	SC-88A
NLU1G86	Single 2-Input Exclusive OR Gate	1	1.65	5.5	6.8	8.00	UDFN-6, ULLGA-6
M74VHC1GT86	Single 2-Input Exclusive OR Gate, TTL Level	1	3.00	5.5	8.8	8.00	TSOP-5, SC-88A
MC74VHC1GT86	Single 2-Input Exclusive OR Gate, TTL Level	1	3.00	5.5	8.8	8.00	SC-88A
NLU1GT86	Single 2-Input Exclusive OR Gate, TTL Level	1	1.65	5.5	6.8	8.00	UDFN-6, ULLGA-6
MC74HC1G00	Single 2-Input NAND Gate	1	2.00	6.0	20.0	2.00	TSOP-5, SC-88A
MC74VHC1G00	Single 2-Input NAND Gate	1	2.00	5.5	7.5	8.00	TSOP-5, SC-88A
NL17SV00	Single 2-Input NAND Gate	1	0.90	3.6	2.3	50.00	SOT-553
NL17SZ00	Single 2-Input NAND Gate	1	1.65	5.5	4.3	24.00	SC-88A, SOT-553
NLU1G00	Single 2-Input NAND Gate	1	1.65	5.5	3.5	8.00	ULLGA-6
MC74VHC1G01	Single 2-Input NAND Gate, Open Drain	1	2.00	5.5	7.5	8.00	TSOP-5, SC-88A
M74VHC1G132	Single 2-Input NAND Gate, Schmitt	1	2.00	5.5	9.7	8.00	TSOP-5, SC-88A
MC74VHC1G132	Single 2-Input NAND Gate, Schmitt	1	2.00	5.5	9.7	8.00	TSOP-5, SC-88A
M74VHC1G135	Single 2-Input NAND Gate, Schmitt, Open Drain	1	2.00	5.5	9.7	8.00	TSOP-5, SC-88A
M74VHC1GT00	Single 2-Input NAND Gate, TTL level	1	3.00	5.5	7.9	8.00	TSOP-5, SC-88A
MC74VHC1GT00	Single 2-Input NAND Gate, TTL level	1	3.00	5.5	7.9	8.00	TSOP-5, SC-88A
MC74HC1G02	Single 2-Input NOR Gate	1	2.00	6.0	20.0	2.00	TSOP-5, SC-88A
MC74VHC1G02	Single 2-Input NOR Gate	1	2.00	5.5	7.5	8.00	TSOP-5, SC-88A
NL17SV02	Single 2-Input NOR Gate	1	0.90	3.6	3.3	50.00	SOT-553
NL17SZ02	Single 2-Input NOR Gate	1	1.65	5.5	4.3	24.00	SC-88A, SOT-553
MC74VHC1GT02	Single 2-Input NOR Gate, TTL Level	1	3.00	5.5	7.7	8.00	SC-88A
MC74VHC1G03	Single 2-Input NOR Gate, Open Drain	1	2.00	5.5	7.5	8.00	TSOP-5, SC-88A
M74VHC1GT02	Single 2-Input NOR Gate, TTL Level	1	3.00	5.5	7.7	8.00	TSOP-5, SC-88A
MC74HC1G32	Single 2-Input OR Gate	1	2.00	6.0	20.0	2.00	TSOP-5, SC-88A

LOGIC GATES

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
MC74VHC1G32	Single 2-Input OR Gate	1	2.00	5.5	7.5	8.00	TSOP-5, SC-88A
NL17SV32	Single 2-Input OR Gate	1	0.90	3.6	3.3	50.00	SOT-553
NL17SZ32	Single 2-Input OR Gate	1	1.65	5.5	4.5	24.00	SC-88A, SOT-553
NLU1G32	Single 2-Input OR Gate	1	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
M74VHC1GT32	Single 2-Input OR Gate, TTL Level	1	3.00	5.5	7.5	8.00	TSOP-5, SC-88A
NLU1GT32	Single 2-Input OR Gate, TTL Level	1	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLX1G11	Single 3-Input AND Gate	1	1.65	5.5	2.7	24	ULLGA-6
NLX1G10	Single 3-Input NAND Gate	1	1.65	5.5	2.7	24	ULLGA-6
NLX1G332	Single 3-Input OR Gate	1	1.65	5.5	2.7	24	ULLGA-6
MC74HC30A	Single 8-Input NAND Gate	1	2.0	6.0	30	5.2	TSSOP-14, SOIC-14
NL17SV04	Single Inverter	1	0.09	3.6	2.3	50.00	SOT-553
NL17SV16	Single Noninverting Buffer	1	0.90	4.6	3.3	50.00	SOT-553
NLU1GT126	Single Noninverting Buffer With High Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLU1GT125	Single Noninverting Buffer With Low Enable, 3-State Outputs, TTL Level	1	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
NLU1G14	Single Schmitt-Trigger Inverter	1	1.65	5.5	8.6	8.00	UDFN-6, ULLGA-6
NLU1GU04	Single Unbuffered Inverter	1	1.65	5.5	5.5	8.00	UDFN-6, ULLGA-6
MC14073B	Triple 3-Input AND Gate	3	3.00	18.0	130.0	2.25	SOIC-14, PDIP-14, EIAJ-14
MC74AC11	Triple 3-Input AND Gate	3	2.00	6.0	8.0	24.00	SOIC-14, PDIP-14, EIAJ-14
MC74HC11A	Triple 3-Input AND Gate	3	2.0	6.0	16	5.2	TSSOP-14, SOIC-14
MC74ACT11	Triple 3-Input AND Gate, TTL Level	3	4.50	5.5	9.5	24.00	SOIC-14, PDIP-14, EIAJ-14
MC74HC10A	Triple 3-Input NAND Gate	3	2.0	6.0	16	5.2	TSSOP-14, SOIC-14
MC14023B	Triple 3-Input NAND Gate	3	3.00	18.0	130.0	2.25	SOIC-14, PDIP-14, EIAJ-14
MC74AC10	Triple 3-Input NAND Gate	3	2.00	6.0	7.0	24.00	SOIC-14, PDIP-14
MC74ACT10	Triple 3-Input NAND Gate, TTL Level	3	4.50	5.5	9.0	24.00	TSSOP-14, SOIC-14, PDIP-14, EIAJ-14
MC14025B	Triple 3-Input NOR Gate	3	3.00	18.0	130.0	2.25	SOIC-14, PDIP-14, EIAJ-14
NLU3G16	Triple Buffer	3	1.65	5.5	5.5	8.00	UDFN-8, ULLGA-8
NLU3G17	Triple Noninverting Schmitt Trigger Buffer	3	1.65	5.5	8.6	8.00	UDFN-8, ULLGA-8
NLU3G14	Triple Schmitt-Trigger Inverter	3	1.65	5.5	8.6	8.00	UDFN-8, ULLGA-8

MULTIPLEXERS

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
NL7SZ18	1:2 Digital Demultiplexer Non-Inverting, 3-State Outputs	2	1.65	5.5	4.00	32.00	UDFN-6, SC288
NL7SZ19	1:2 Digital Multiplexer / Demultiplexer	2	1.65	5.5	4.00	50.00	UDFN-6, SC288
74HC138	1-of-8 Decoder/Demultiplexer	1	2.00	5.5	10.10	8.00	TSSOP-16, SOIC-16
MC74AC138	1-of-8 Decoder/Demultiplexer	1	2.00	6.0	9.50	24.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74HC138A	1-of-8 Decoder/Demultiplexer	1	2.00	6.0	27.00	4.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74ACT138	1-of-8 Decoder/Demultiplexer, TTL Level	1	4.50	5.5	10.50	24.00	TSSOP-16, SOIC-16, PDIP-16
MC74HCT138A	1-of-8 Decoder/Demultiplexer, TTL Level	1	4.50	5.5	30.00	4.00	PDIP-16
MC74HCT138A	1-of-8 Decoder/Demultiplexer, TTL Output	1	4.5	5.5	35	4	TSSOP-16, SOIC-16
MC74HC4067A	1-to-16 Multiplexer / Demultiplexer	1	2	6	20	5.2	TSSOP-24, SOIC-24
MC74LXC138	3-to-8 Decoder/Demultiplexer	1	2.00	3.6	6.00	24.00	TSSOP-16, SOIC-16, EIAJ-16
MC74HC238A	3-to-8 Line Decoder/Demultiplexer	1	2	6	35	5.2	TSSOP-16, SOIC-16
MC74LVX138	3-To-8 Line Decoder	1	2.00	3.6	12.30	4.00	TSSOP-16, SOIC-16, EIAJ-16
MC74VHC138	3-To-8 Line Decoder	1	2.00	5.5	10.10	8.00	TSSOP-16, SOIC-16
MC74VHCT138A	3-To-8 Line Decoder, TTL Level	1	3.00	5.5	11.40	8.00	TSSOP-16, SOIC-16
MC14514B	4-Bit Transparent Latch/4-to-16 Line Decoder	1	3.00	18.0	450.00	2.25	SOIC-24
MC14515B	4-Bit Transparent Latch/4-to-16 Line Decoder	1	3.00	18.0	450.00	2.25	SOIC-24
MC14532B	8-Bit Priority Encoder	1	3.00	18.0	220.00	2.25	SOIC-16, PDIP-16
MC14512B	8-Channel Data Selector	1	3.00	18.0	250.00	2.25	SOIC-16, PDIP-16
MC74HC151A	8-Input Multiplexer	1	2	6	43	5.2	TSSOP-16, SOIC-16
MC74HC251A	8-Input Multiplexer, 3-State Outputs	1	2	6	43	5.2	TSSOP-16, SOIC-16
MC74LVX4051	Analog Multiplexer / Demultiplexer	1	2.50	6.0	23.00	4.00	TSSOP-16, SOIC-16, EIAJ-16
MC74LVX4052	Analog Multiplexer / Demultiplexer	2	2.50	6.0	23.00	4.00	TSSOP-16, SOIC-16, EIAJ-16
MC74LVX4053	Analog Multiplexer / Demultiplexer	3	2.50	6.0	23.00	4.00	TSSOP-16, SOIC-16, EIAJ-16
MC74LVXT4051	Analog Multiplexer / Demultiplexer	1	2.50	6.0	23.00	4.00	TSSOP-16, SOIC-16, EIAJ-16
MC74LVXT4052	Analog Multiplexer / Demultiplexer	2	2.50	6.0	23.00	4.00	TSSOP-16, SOIC-16, EIAJ-16
MC74LVXT4053	Analog Multiplexer / Demultiplexer	3	2.50	6.0	23.00	4.00	TSSOP-16, SOIC-16, EIAJ-16
MC74VHC4052	Analog Multiplexer / Demultiplexer	1	2.00	6.0	49.00	8.00	TSSOP-16, SOIC-16, EIAJ-16
MC74VHC4053	Analog Multiplexer / Demultiplexer	1	2.00	6.0	49.00	8.00	TSSOP-16, SOIC-16, EIAJ-16
NLAS4053	Analog Multiplexers/Demultiplexers	2	2.50	5.5	40.00	50.00	TSSOP-16, SOIC-16
MC14028B	BCD-to-Decimal Decoder	1	3.00	18.0	260.00	2.25	SOIC-16, PDIP-16, EIAJ-16
MC74VHC157	Data Selector/Multiplexer 2-Input	4	2.00	5.5	8.40	8.00	TSSOP-16, SOIC-16
MC74HC157A	Data Selector/Multiplexer 2-Input Q	4	2.00	6.0	21.00	6.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74HC139A	Dual 1-of-4 Decoder / Demultiplexer	2	2.00	6.0	23.00	4.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74AC139	Dual 1-of-4 Decoder/Demultiplexer	2	2.00	6.0	8.50	24.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16

MULTIPLEXERS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC74ACT139	Dual 1-of-4 Decoder/Demultiplexer, TTL Level	2	4.50	5.5	9.50	24.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74LCX139	Dual 2-of-4 Decoder/Demultiplexer	2	2.00	3.6	6.20	24.00	TSSOP-16, SOIC-16, EIAJ-16
MC74LVX139	Dual 2-to-4 Decoder/Demultiplexer	2	2.00	3.6	13.00	4.00	TSSOP-16, SOIC-16
MC74VHC139	Dual 2-to-4 Decoder/Demultiplexer	2	2.00	5.5	9.20	8.00	TSSOP-16, SOIC-16
MC74VHCT139A	Dual 2-to-4 Decoder/Demultiplexer, TTL Level	2	4.50	5.5	9.20	8.00	TSSOP-16, SOIC-16, EIAJ-16
MC74HC153A	Dual 4-Input Multiplexers	2	2	6	38	5.2	TSSOP-16, SOIC-16
MC74ACT253	Dual 4-Input Multiplexer, 3-State Outputs, TTL Level	2	4.50	5.5	13.00	24.00	SOIC-16
MC74ACT153	Dual 4-Input Multiplexer, TTL Level	2	4.50	5.5	11.50	24.00	SOIC-16
MC14555B	Dual Binary to 1-of-4 Decoder/Demultiplexer	2	3.00	18.0	190.00	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14558B	Dual Binary to 1-of-4 Decoder/Demultiplexer	2	3.00	18.0	190.00	2250.00	SOIC-16, PDIP-16, EIAJ-16
74FST3257	Quad 2:1 Multiplexer/Demultiplexer Bus Switch	4	4.00	5.5	0.25	-	TSSOP-16, SOIC-16
MC74LVX157	Quad 2-Channel Multiplexer	4	2.00	3.6	11.40	4.00	TSSOP-16, SOIC-16, EIAJ-16
M74VHCT257A	Quad 2-Channel Multiplexer, 3-State Outputs, TTL Level	4	2	5.5	8	8	TSSOP-16
74HCT157	Quad 2-Channel Multiplexer, TTL Level	4	4.50	5.5	8.40	8.00	TSSOP-16, SOIC-16
M74VHCT157A	Quad 2-Channel Multiplexer, TTL Level	4	4.50	5.5	8.40	8.00	TSSOP-16
MC74VHCT157A	Quad 2-Channel Multiplexer, TTL Level	4	4.50	5.5	8.40	8.00	EIAJ-16
MC74AC157	Quad 2-Input Multiplexer	4	2.00	6.0	9.00	24.00	TSSOP-16, SOIC-16, PDIP-16
MC74LCX157	Quad 2-Input Multiplexer	2	2.00	3.6	5.80	24.00	TSSOP-16, SOIC-16
MC74LCX158	Quad 2-Input Multiplexer	4	2.00	3.6	6.50	24.00	TSSOP-16, SOIC-16, EIAJ-16
MC74LCX257	Quad 2-Input Multiplexer	4	2.00	3.6	6.00	24.00	TSSOP-16, SOIC-16, EIAJ-16
MC74LCX258	Quad 2-Input Multiplexer	4	2.00	3.6	6.50	24.00	TSSOP-16, SOIC-16, EIAJ-16
MC74AC257	Quad 2-Input Multiplexer 3-State Output	4	2.00	6.0	7.50	24.00	SOIC-16, PDIP-16, EIAJ-16
MC74ACT257	Quad 2-Input Multiplexer, 3-State Outputs, TTL Level	4	4.50	5.5	10.50	24.00	SOIC-16, PDIP-16, EIAJ-16
MC74ACT157	Quad 2-Input Multiplexer, TTL Level	4	4.50	5.5	9.50	24.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74VHC4316	Quad Analog Multiplexer / Demultiplexer	4	2.00	6.0	8.00	-	TSSOP-16, SOIC-16, EIAJ-16
NLAS4053	Triple 2:1 Analog Switch – Multiplexer	2	2.50	5.5	40.00	50.00	TSSOP-16

MULTIVIBRATORS

Device	Description	Channels	V _{CC} Min (V)	V _{CC} Max (V)	t _{pd} Max (ns)	I _O Max (mA)	Package
MC14528B	Dual Monostable Multivibrator	2	3	18	240	2.25	SOIC-16, PDIP-16, EIAJ-16
MC14538B	Dual Precision Monostable Multivibrator	2	3	18	300	2.25	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74HC4538A	Dual Precision Monostable Multivibrator	2	3	6	35	4.00	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16
MC74HC123A	Dual retriggerable monostable multivibrator with reset	2	2	6	75	5.2	TSSOP-16, SOIC-16

TRANSCIEVERS

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
74VCXH16245	16-Bit Transceiver	16	1.65	3.6	2.5	24	TSSOP-48
M74LCX16245	16-Bit Transceiver	8	2.00	3.6	5.2	24	TSSOP-48
MC74LCX16245	16-Bit Transceiver	8	2.00	3.6	5.2	24	TSSOP-48
74VCXH245	8-Bit Transceiver, Low Voltage	1	2.00	6.0	15.0	6	QFN-20
MC74LVXC3245	Configurable Dual Supply Octal Transceiver	8	2.30	3.6	9.0	24	TSSOP-24, SOIC-24
MC74LVX4245	Dual Supply Octal Translating Transceiver	8	2.70	3.6	10.0	24	TSSOP-24, SOIC-24
74HC245	Octal 3-State Non-Inverting Bus/Transceiver	1	2.00	5.5	7.5	8	TSSOP-20
MC74HC245A	Octal 3-State Non-Inverting Bus/Transceiver	1	2.00	6.0	15.0	6	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74ACT245	Octal Bidirectional Transceiver, 3-State Inputs/Outputs, TTL Level	1	4.50	5.5	8.0	24	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74AC245	Octal Bidirectional Transceiver, 3-State Outputs Inputs/Outputs	1	2.00	2.0	6.5	24	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74LVX245	Octal Bus Transceiver	1	2.00	3.6	10.1	4	TSSOP-20, SOIC-20, EIAJ-20
MC74VHC245	Octal Bus Transceiver	1	2.00	5.5	7.5	8	TSSOP-20, SOIC-20
74HCT245	Octal Bus Transceiver, 3-State Inputs/Outputs, TTL Level	1	4.50	5.5	22.0	6	TSSOP-20
MC74HCT245A	Octal Bus Transceiver, 3-State Inputs/Outputs, TTL Level	1	4.50	5.5	22.0	6	TSSOP-20, SOIC-20, PDIP-20, EIAJ-20
MC74VHCT245A	Octal Bus Transceiver, 3-State Inputs/Outputs, TTL Level	1	4.50	5.5	8.7	8	TSSOP-20, SOIC-20, EIAJ-20
MC74LCX245	Octal Bus Transceiver With 3-State Outputs	8	2	3.6	7	24	QFN-20
MC74ACT640	Octal Inverting Transceiver, 3-State, TTL Level	1	4.50	5.5	8.0	24	SOIC-20, PDIP-20, EIAJ-20
MC74ACT646	Octal Noninverting Transceiver/Register, 3-State Outputs, TTL Level	8	4.50	5.5	14.5	24	SOIC-24, PDIP-24
MC74ACT652	Octal Noninverting Transceiver/Register, 3-State Outputs, TTL Level	8	4.50	5.5	14.5	24	SOIC-24, PDIP-24
MC74LCX245	Octal Transceiver	1	2.00	3.6	7.0	24	TSSOP-20, SOIC-20, EIAJ-20
MC74AC646	Octal Transceiver/Register, 3-State Outputs (Non-inverting)	8	2.00	6.0	12.0	24	SOIC-24
MC74AC652	Octal Transceiver/Register, 3-State Outputs (Non-inverting)	8	2.00	6.0	12.0	24	SOIC-24

TRANSLATORS

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
NLSX5011	1-Bit Auto Sensing Dual-Supply Voltage Level Translator	1	0.9	4.5	8	0.02	UDFN-6, ULLGA-6
NLSV1T34	1 Bit Dual Supply Unidirectional Voltage Level Translator w/o Output Enable	1	0.90	4.5	3.3	50.00	ULLGA-6, SC-88A
NLSV1T244	1-Bit Dual Supply Unidirectional Voltage Level Translator	1	0.90	4.5	3.3	50.00	UDFN-6
NLSV1T240	1-Bit Dual Supply Unidirectional Voltage Level Translator; Inverting	1	0.90	4.5	3.3	50.00	UDFN-6
NLSX3012	2-Bit Auto Sensing Dual-Supply Voltage Level Translator	2	1.30	5.5	7.2	0.02	UDFN-8
NLSX5012	2-Bit Auto Sensing Dual-Supply Voltage Level Translator	2	0.9	4.5	8	0.02	TSSOP-8, SOIC-8, UDFN-8, Micro-8
NLSX3373	2-Bit Auto Sensing Dual-Supply Voltage Level Translator; Open Drain	2	1.20	5.5	30.0	40.00	UDFN-8
NLSX4373	2-Bit Auto Sensing Dual-Supply Voltage Level Translator; Open Drain	2	1.50	5.5	20.0	-	UDFN-8
NLSX4378B	2-Bit Auto Sensing Dual-Supply Voltage Level Translator; Open Drain	4	1.50	5.5	20.0	-	uBump-12
NLSX4378	2-Bit Auto Sensing Dual-Supply Voltage Level Translator; Open Drain	4	1.50	5.5	20.0	-	uBump-12
NLSX4373	2-Bit Auto Sensing Dual-Supply Voltage Level Translator; Open Drain	2	1.5	5.5	20	0.02	SOIC-8, Micro-8
NLSV2T3236	2-Bit Bidirectional Dual-Supply Unidirectional Voltage Level Translator, 26 Ω Series Resistor	2	0.9	4.5	3.3	24	UQFN10
NLSV2T245	2-Bit Bidirectional Dual-Supply Unidirectional Voltage Level Translator, Push-Pull	2	0.9	4.5	3.3	24	UQFN10
NLSV2T244	2-Bit Dual Supply Unidirectional Voltage Level Translator	2	0.90	4.5	3.3	50.00	UDFN-8
NLSV2T244	2-Bit Dual-Supply Unidirectional Voltage Level Translator	2	0.9	4.5	3.3	24	SOIC-8, Micro-8
NLSV2T240	2-Bit Dual Supply Unidirectional Voltage Level Translator; Inverting	2	0.90	4.5	3.3	50.00	UDFN-8
NLSX3014	4-Bit Auto Sensing Dual-Supply Voltage Level Translator	4	0.90	4.5	6.5	0.02	UQFN-12
NLSX4014	4-Bit Auto Sensing Dual-Supply Voltage Level Translator	4	1.30	4.5	17.0	-	UQFN-12
NLSX4014	4-Bit Auto Sensing Dual-Supply Voltage Level Translator	4	0.9	4.5	9	0.02	TSSOP-14, SOIC-14
NLSX5014	4-Bit Auto Sensing Dual-Supply Voltage Level Translator	4	0.9	4.5	8	0.02	TSSOP-14, SOIC-14, UQFN-12
NLSX3378B	4-Bit Auto Sensing Dual-Supply Voltage Level Translator; Open Drain	4	1.20	4.5	15.0	40.00	uBump-12
NLSX3378	4-Bit Auto Sensing Dual-Supply Voltage Level Translator; Open Drain	4	1.20	4.5	15.0	40.00	uBump-12
NLSV4T244	4-Bit Dual-Supply Unidirectional Voltage Level Translator	4	0.9	4.5	3.3	24	TSSOP-14, SOIC-14
NLSV4T2244	4-Bit Dual Supply Unidirectional Voltage Level Translator	4	0.90	4.5	3.3	50.00	UQFN-12
NLSV4T3144	4-Bit Dual Supply Unidirectional Voltage Level Translator	4	0.90	4.5	3.3	50.00	UQFN-12
NLSV4T3234	4-Bit Dual Supply Unidirectional Voltage Level Translator, 26 Ω Output Series Resistor	4	0.90	4.5	5.6	50.00	uBump-11
NLSV4T240	4-Bit Dual Supply Unidirectional Voltage Level Translator; Inverting	4	0.90	4.5	3.3	50.00	UQFN-12

TRANSLATORS

Device	Description	Channels	V _{cc} Min (V)	V _{cc} Max (V)	t _{pd} Max (ns)	I _o Max (mA)	Package
NLSX3013B	8-Bit Auto Sensing Dual-Supply Voltage Level Translator	8	1.30	4.5	6.5	0.02	uBump-20
NLSX3013	8-Bit Auto Sensing Dual-Supply Voltage Level Translator	8	1.30	4.5	6.0	0.02	uBump-20
NLSX3018	8-Bit Auto Sensing Dual-Supply Voltage Level Translator	8	0.90	5.5	6.5	20.00	UDFN-20
NLSX3018	8-Bit Auto Sensing Dual-Supply Voltage Level Translator	8	0.9	4.5	9	0.02	TSSOP-20, SOIC-20
NLSV8T244	8-Bit Dual-Supply Unidirectional Voltage Level Translator	8	0.9	4.5	3.3	24	TSSOP-20, SOIC-20
NLSV8T240	8-Bit Dual Supply Unidirectional Voltage Level Translator; Inverting	8	0.90	4.5	3.3	50.00	UDFN-20
NLSV22T244	Dual 2-Bit Dual-Supply Non-Inverting Level Translator	4	1.65	3.6	3.3	50.00	UQFN-12
PCA9306	Dual Bidirectional Voltage Level Translator	2	1.65	5.5	1		Micro-8, SOIC-8, UQFN-8
MC74LVX4245	Dual Supply Octal Translating Transceiver	8	2.70	3.6	10.0	24.00	TSSOP-24, SOIC-24
MC14504B	Hex Level Shifter	1	3.00	18.0	340.0	2.25	TSSOP-16, SOIC-16, PDIP-16, EIAJ-16

Thermal Management

Thermal Management

Table of Contents

	Page
Fan Controllers	312
Temperature Sensors	313

FAN CONTROLLERS

Device	Data Transmission Standard	I _c Max (mA)	V _{cc} Min (V)	V _{cc} Max (V)	T Min (°C)	T Max (°C)	Package
ADM1024	SMBus	3.5	2.8	5.5	0	100	TSSOP-24
ADM1026	SMBus	4	3	5.5	0	100	QFP-48
ADM1029	SMBus	3	3	5.5	0	100	QSOP-24
ADM1030	SMBus	3	3	5.5	0	100	QSOP-16
ADM1031	SMBus	3	3	5.5	0	100	QSOP-16
ADM1033	SMBus	3	3	5.5	-40	125	QSOP-16
ADM1034	SMBus	3	3	3.6	-40	125	QSOP-16
ADT7460	SMBus	3	3	5.5	-40	120	QSOP-16
ADT7462	SMBus	4	3	5.5	-40	125	LFCSP-32
ADT7463	SMBus	3	3	5.5	-40	120	QSOP-24
ADT7467	SMBus	3	3	5.5	-40	120	QSOP-16
ADT7473	SMBus	3	3	3.6	-40	125	QSOP-16
ADT7475	SMBus	3	3	3.6	-40	125	QSOP-16
ADT7476	SMBus	3	3	3.6	-40	125	QSOP-24
ADT7490	SMBus	5	3	3.6	-40	125	QSOP-24

TEMPERATURE SENSORS

Device	Sensor Type	Data Transmission Standard	I _{cc} Max (mA)	V _{cc} Min (V)	V _{cc} Max (V)	T Min (°C)	T Max (°C)	Temperature Error (°C)	Packages
ADM1021	Local & Remote	SMBus	0.2	3	5.5	-55	125	±3	QSOP-16
ADM1023	Local & Remote	SMBus	0.2	3	5.5	0	120	±1	QSOP-16
ADM1032	Local & Remote	SMBus	0.215	3	5.5	0	120	±1	Micro8™, SOIC-8
ADT7421	Local & Remote	I2C, SMBus	5	3	3.6	-40	125	±1.75	Micro8™, SOIC-8
ADT7461A	Local & Remote	SMBus	0.35	3	3.6	-40	125	±1	Micro8™
ADT7461	Local & Remote	SMBus	0.215	3	5.5	-40	125	±1	Micro8™, SOIC-8
ADT7481	Local & Remote	SMBus	0.35	3	3.6	-40	125	±1	Micro-10
ADT7482	Local & Remote	SMBus	0.35	3	3.6	-40	125	±1	Micro-10
ADT7483	Local & Remote	SMBus	0.35	3	3.6	-40	125	±1	QSOP-16
ADT7484	Local & Remote	SST	5	3	3.6	-40	125	±1	Micro8™, SOIC-8
ADT7485A	-	SST	5	3	3.6	-40	125	±1	Micro-10
ADT7486A	Local & Remote	SST	5	3	3.6	-40	125	±1	Micro-10
ADT7488A	-	SST	5	3	3.6	-40	125	±1	Micro-10
CAT6095	-	-	-	3	3.6	-40	125	±3	TDFN-8



Thyristors

Thyristors

Table of Contents

	Page
Silicon Controlled Rectifiers (SCRs)	318
TRIACs (Bidirectional Devices)	321
Surge Suppressors	325
Triggers	328

SILICON CONTROLLED RECTIFIERS (SCRs)


										
On-State RMS Current $I_{T(RMS)}$ (A)	Blocking Voltage V_{DRM} , V_{RRM} (V)	SOT-23 Case 318 Style 8	TO-92 (Note 1) (TO-226AA) Case 029 Style 10	SOT-223 Case 318E Style 10	TO-225AA (TO-126) Case 077 Style 2	D-PAK Case 369C Style 4 & 5 Case 369D Style 5	Surge Current I_{TSM} (A) 60 Hz	Max I_{GT} (mA)	Max V_{GT} (V)	
0.25	200	NCY0102BL					7.0	0.2	0.8	
0.8	30		2N5060				10	0.2	0.8	
	60		2N5061							
	100		2N5062							
	200		2N5064							
	100		MCR100-3							
	200		MCR100-4							
	400		MCR100-6							
	600		MCR100-8							
	200			MCR08B						
600			MCR08M							
			NYC008-6J (Notes 1 & 5)							
1.5	400		MCR22-6				15	0.2	0.8	
	600		MCR22-8							
	50			NYC222ST						
	400			NYC226ST						
	600			NYC228ST						
4.0	200				C106B		20	0.2	0.8	
	400				C106D					
						C106D1				
	600				C106M					
						C106M1				
	400					MCR106-6	25	0.2	1.0	
	600					MCR106-8				
	100						25	0.1	0.8	
						MCR703A (Note 2)				
	400					MCR706A (Note 2)				
	600					MCR708A (Note 2)				
						MCR708A1 (Note 2 & 4)				
	400					MCR716 (Note 3)				
600					MCR718 (Note 3)					

- See TO-92 data sheets for complete device suffix packaging ordering options.
RLRA, RLRE, RL, & RL1 suffixes: Radial Tape and Reel
RLRM & ZL1 suffixes: Radial Tape and Ammo Pack
- Denotes pkg style 5
- Denotes pkg style 4
- Denotes straight lead package
- Denotes min of 50 V/ μ s for dV/dt

Lead Identification
A = Anode
K = Cathode
G = Gate

Shaded devices denote sensitive gate SCR's

SILICON CONTROLLED RECTIFIERS (SCRs) (continued)



		 CASE 369C  CASE 369D					
On-State RMS Current $I_{T(RMS)}$ (A)	Blocking Voltage V_{DRM} , V_{RRM} (V)	DPAK Case 369C -001 = Case 369D Style 4	TO-220AB Case 221A-09 Style 3	TO-220AB Case 221A-07 Style 3	Surge Current I_{TSM} (A) 60 Hz	Max I_{GT} (mA)	Max V_{GT} (V)
8.0	600	MCR8DSMT4			80	0.2	1.0
	800	MCR8DSNT4					
	600	MCR8DCMT4			80	15	1.0
	800	MCR8DCNT4					
	400		MCR8SD		80	0.2	1.0
	600		MCR8SM				
	800		MCR8SN				
	800		MCR8N		80	15	1.0
	50			C122F1	90	25	1.5
	100			MCR72-3	100	0.2	1.5
	400			MCR72-6			
	600			MCR72-8			
	50			MCR218-2	100	25	1.5
	200			MCR218-4			
400			MCR218-6				
12	400		MCR12LD		100	8.0	0.8
	600		MCR12LM				
	800		MCR12LN				
	800			MCR310-10	100	0.2	1.5
	600	MCR12DSM			100	0.2	1.0
	800	MCR12DSN					
	800	MCR12DSN-001					
	600	MCR12DCM			100	20	1.0
	800	MCR12DCN					
	400		MCR12D		100	30	1.5
	600		MCR12M				
	800		MCR12N				
50			MCR68-2	100	30	1.5	

Shaded devices denote sensitive gate SCR's

Lead Identification





- A = Anode
- K = Cathode
- G = Gate

SILICON CONTROLLED RECTIFIERS (SCRs) (continued)

						
On-State RMS Current $I_{T(RMS)}$ (A)	Blocking Voltage V_{DRM} , V_{RRM} (V)	TO-220AB Case 221A-09 Style 3	TO-220AB Case 221A-07 Style 3	Surge Current I_{TSM} (A) 60 Hz	Max I_{GT} (mA)	Max V_{GT} (V)
12	50		2N6394	100	30	1.5
	100		2N6395			
	400		2N6397			
	800		2N6399			
16	800	MCR16N		160	20	1.0
	50		2N6400	160	30	1.5
	100		2N6401			
	200		2N6402			
	400		2N6403			
	600		2N6404			
	800		2N6405			
25	400	MCR25D		300	30	1.0
	600	MCR25M				
	800	MCR25N				
	50		2N6504	300	30	1.5
	100		2N6505			
	400		2N6507			
	600		2N6508			
	800		2N6509			
	50		MCR69-2			
	100		MCR69-3			

Lead Identification
 A = Anode
 K = Cathode
 G = Gate

TRIACs (Bidirectional Devices)

							Max IGT (mA)				
On-State RMS Current $I_{T(RMS)}$ (A)	Blocking Voltage V_{DRM} , V_{RRM} (V)	TO-92 (Note 6) (TO-226AA) Case 029 Style 12	SOT-223 Case 318E Style 11	TO-225AA (TO-126) Case 077 Style 5	D-PAK Case 369C -001 = Case 369D Style 6	Surge Current I_{TSM} (A) 60 Hz	Q1	Q2	Q3	Q4	
0.6	200	MAC97A4				8.0	5.0	5.0	5.0	7.0	
	400	MAC97A6									
	600	MAC97A8									
0.8	400	MAC997A6				8.0					
		MAC997B6					3.0	3.0	3.0	5.0	
		MAC997A8					5.0	5.0	5.0	7.0	
	600	MAC997B8					3.0	3.0	3.0	5.0	
		MAC08B					10	10	10	10	
		MAC08M									
1.0	600	Z0103MA				8.0	3.0	3.0	3.0	5.0	
		Z0107MA					5.0	5.0	5.0	7.0	
		Z0109MA					10	10	10	10	
	8.0	Z0103MN				8.0	3.0	3.0	3.0	5.0	
		Z0107MN					5.0	5.0	5.0	7.0	
		Z0109MN					10	10	10	10	
2.5	200			T2322B		25	10	10	10	10	
4.0	200			2N6071A		30	5.0	5.0	5.0	10	
				2N6071B			3.0	3.0	3.0	5.0	
				2N6073A			5.0	5.0	5.0	10	
	400			2N6073B			3.0	3.0	3.0	5.0	
				2N6075A			5.0	5.0	5.0	10	
				2N6075B			3.0	3.0	3.0	5.0	
4.0	600			MAC4DLM (Note 7)		40	3.0	3.0	3.0	5.0	
				MAC4DLM-1 (Note 8)							
4.0	600			MAC4DHM (Note 7)		40	5.0	5.0	5.0	10	
				MAC4DHM-1 (Note 8)							
4.0	600			MAC4DSM (Note 7)		40	10	10	10	-	
				MAC4DSMT-1 (Note 8)							
	800			MAC4DSN (Note 7)							
				MAC4DSN-1 (Note 8)							
4.0	600			MAC4DCM (Note 7)		40	35	35	35	-	
				MAC4DCM-1 (Note 8)							
	800			MAC4DCN (Note 7)							
				MAC4DCN-1 (Note 8)							

6. See TO-92 data sheets for complete device suffix packaging ordering options.

RLRA, RLRE, RL, & RL1 suffixes: Radial Tape and Reel

RLRM & ZL1 suffixes: Radial Tape and Ammo Pack




7. Denotes SMT package

8. Denotes straight lead package

Shaded devices denote sensitive gate Triacs

Lead Identification
 MT1 = Main Terminal 1
 MT2 = Main Terminal 2
 G = Gate

TRIACs (Bidirectional Devices) (continued)

									
On-State RMS Current I _{T(RMS)} (A)	Blocking Voltage V _{DRM} , V _{RRM} (V)	TO-220AB Case 221A-09 Style 4	TO-220AB Case 221A-07 Style 4	ISOLATED TO-220 Case 221A-07 Style 12	Surge Current I _{TSM} (A) 60 Hz	Q1	Q2	Q3	Q4
6.0	400		T2500D		60	25	60	25	60
8.0	400	MAC8SD			70	5.0	5.0	5.0	-
	600	MAC8SM							
	800	MAC8SN							
8.0	400	MAC8D			80	35	35	35	-
	600	MAC8M							
	800	MAC8N							
8.0	400	MAC9D			80	50	50	50	-
	600	MAC9M							
	800	MAC9N							
8.0	200		MAC228A4		80	5	5	5	10
	400		MAC228A6						
	600		MAC228A8						
	800		MAC228A10						
8.0	600		BTB08-600CW3G	BTA08-600CW3G	90	35	35	35	-
	800		BTB08-800CW3G	BTA08-800CW3G					
8.0	600		BTB08-600BW3G	BTA08-600BW3G	90	50	50	50	-
	800		BTB08-800BW3G	BTA08-800BW3G					
8.0	600		2N6344		100	50	75	50	75
8.0	400		T2800D		100	25	60	25	60

9. Denotes SMT package
 10. Denotes straight lead package
 UL logo indicates UL Recognized File #E69369

Shaded devices denote sensitive gate Triacs

Lead Identification
 MT1 = Main Terminal 1
 MT2 = Main Terminal 2
 G = Gate
 NC = Not Connected

TRIACs (Bidirectional Devices) (continued)




On-State RMS Current $I_{T(RMS)}$ (A)	Blocking Voltage V_{DRM} , V_{RRM} (V)	Max I_{GT} (mA)				Surge Current I_{TSM} (A) 60 Hz	Q1	Q2	Q3	Q4
		TO-220AB Case 221A-09 Style 4	TO-220AB Case 221A-07 Style 4	ISOLATED TO-220 Case 221A-07 Style 12						
10	600		MAC210A8		100	50	50	50	75	
	800		MAC210A10							
12	600	MAC12SM			90	5.0	5.0	5.0	-	
	800	MAC12SN								
12	400	MAC12HCD			100	50	50	50	-	
	600	MAC12HCM								
	800	MAC12HCN								
12	400	MAC12D			100	35	35	35	-	
	600	MAC12M								
	800	MAC12N								
12	600		MAC212A8		100	50	50	50	75	
	800		MAC212A10							
12	600		BTB12-600TW3G		120	5	5	5	-	
12	600		BTB12-600CW3G	BTA12-600CW3G	120	35	35	35	-	
	600		BTB12H-600CW3G (Note 11)							
	800		BTB12-800CW3G	BTA12-800CW3G						
	600		BTB12-600BW3G	BTA12-600BW3G	120	50	50	50	-	
	800		BTB12-800BW3G	BTA12-800BW3G						
12	600		2N6344A		120	50	75	50	75	
	600		2N6348A			50	75	50	75	
	800		2N6349A			50	75	50	75	
15	400	MAC15SD			120	5.0	5.0	5.0	-	
	600	MAC15SM								
	800	MAC15SN								
15	600	MAC15M			150	35	35	35	-	
	800	MAC15N								
15	400	MAC15A6			150	50	50	50	75	
	600	MAC15A8				50	50	50	75	
	800	MAC15A10				50	50	50	75	

11. Denotes High TJ devices (150°C)
UL logo indicates UL Recognized File #E69369

Shaded devices denote sensitive gate Triacs

Lead Identification
MT1 = Main Terminal 1
MT2 = Main Terminal 2
G = Gate
NC = Not Connected

TRIACs (Bidirectional Devices) (continued)

										
						Max I _{GT} (mA)				
On-State RMS Current I _{T(RMS)} (A)	Blocking Voltage V _{DRM} , V _{RRM} (V)	TO-220AB Case 221A-09 Style 4	TO-220AB Case 221A-07 Style 4	ISOLATED TO-220 Case 221A-07 Style 12	Surge Current I _{TSM} (A) 60 Hz	Q1	Q2	Q3	Q4	
15	400	MAC16D			150	50	50	50	-	
	600	MAC16M								
	800	MAC16N								
16	600	MAC16CM			150	35	35	35	-	
	800	MAC16CN								
16	400	MAC16HCD			150	50	50	50	-	
	600	MAC16HCM								
	800	MAC16HCN								
16	800			BTA16-600SW3G	170	10	10	10	-	
	600			BTA16-800SW3G						
	600		BTB16-600CW3G	BTA16-600CW3G						35
	800		BTB16-800CW3G	BTA16-800CW3G		50	50	50		-
	600		BTB16-600BW3G	BTA16-600BW3G						
	600		BTB16H-600BW3G (Note 11)							
	800		BTB16-800BW3G	BTA16-800BW3G						
25	600			BTA25-600CW3G	250	35	35	35	-	
				BTA25H-600CW3G (Note 11)						
	800			BTA25-800CW3G						
				BTA25H-800CW3G (Note 11)						
30	600			BTA30-600CW3G	300	35	35	35	-	
				BTA30H-600CW3G (Note 11)						
	800			BTA30-800CW3G						
				BTA30H-800CW3G (Note 11)						

11. Denotes High T_J devices (150°C)
UL logo indicates UL Recognized File #E69369

Shaded devices denote sensitive gate Triacs

Lead Identification
MT1 = Main Terminal 1
MT2 = Main Terminal 2
G = Gate
NC = Not Connected

SURGE SUPPRESSORS

ULTRA LOW CAPACITANCE (TSPD)

					
SMB CASE 403C					
Device	V_{DRM}	V_{BO}	$I_{PPS} = 10 \times 1000 \mu s$	$C_O, 2 V, 1 MHz$	General Description
	Offstate Voltage (V)	Breakover Voltage (V)	Surge Current Rating (A)	Capacitance Maximum (pF)	
NP0640SAMC	58	77	50	18	Due to their ultra low off-state capacitance (C_O), these devices offer minimal signal distortion for high speed equipment such as DSL and T1/E1 circuits. The low capacitance translates into extremely low differential capacitance offering superb linearity with applied voltage or frequency, and assists designers in protecting equipment from surge events while maximizing circuit performance.
NP0720SAMC	65	88			
NP0900SAMC	75	98			
NP1100SAMC	90	130			
NP1300SAMC	120	160			
NP1500SAMC	140	180			
NP1800SAMC	170	220			
NP2100SAMC	180	240			
NP2300SAMC	190	260			
NP2600SAMC	220	300			
NP3100SAMC	275	350			
NP3500SAMC	320	400			
NP0640SBMC	58	77	80	21	
NP0720SBMC	65	88			
NP0900SBMC	75	98			
NP1100SBMC	90	130			
NP1300SBMC	120	160			
NP1500SBMC	140	180			
NP1800SBMC	170	220			
NP2100SBMC	180	240			
NP2300SBMC	190	260			
NP2600SBMC	220	300			
NP3100SBMC	275	350			
NP3500SBMC	320	400			
NP0640SCMC	58	77	100	29	
NP0720SCMC	65	88			
NP0900SCMC	75	98			
NP1100SCMC	90	130			
NP1300SCMC	120	160			
NP1500SCMC	140	180			
NP1800SCMC	170	220			
NP2100SCMC	180	240			
NP2300SCMC	190	260			
NP2600SCMC	220	300			
NP3100SCMC	275	350			
NP3500SCMC	320	400			

SURGE SUPPRESSORS (continued)

THYRISTOR SURGE PROTECTION DEVICE (TSPD)

					
SMB CASE 403C					
Device	V _{DRM}	V _{BO}	I _{PPS} = 10x1000 μs	Co, 2 V, 1 Mhz	General Description
	Offstate Voltage (V)	Breakover Voltage (V)	Surge Current Rating (A)	Capacitance Maximum (pF)	
NP0640SA	58	77	50	84	These Thyristor Surge Protector Devices (TSPD) protect telecommunication circuits such as central office, access, and customer premises equipment from over-voltage conditions. These are bidirectional devices so they are able to have functionality of 2 devices in one package, saving valuable space on board layout. These devices will act as a crowbar when over-voltage occurs and will divert the energy away from circuit or device that is being protected. Use of the NP Series in equipment will help meet various regulatory requirements including: GR-1089-CORE, EC 61000-4-5, ITU K.20/21/45, IEC 60950, TIA-968-A, FCC Part 68, EN 60950, UL 1950.
NP0720SA	65	88		79	
NP0900SA	75	98		65	
NP1100SA	90	130		58	
NP1300SA	120	160		46	
NP1500SA	140	180		44	
NP1800SA	170	220		39	
NP2100SA	180	240		37	
NP2300SA	190	260		36	
NP2600SA	220	300		33	
NP3100SA	275	350		31	
NP3500SA	320	400		28	
NP0640SB	58	77		80	
NP0720SB	65	88	123		
NP0900SB	75	98	122		
NP1100SB	90	130	95		
NP1300SB	120	160	75		
NP1500SB	140	180	70		
NP1800SB	170	220	59		
NP2100SB	180	240	59		
NP2300SB	190	260	56		
NP2600SB	220	300	52		
NP3100SB	275	350	47		
NP3500SB	320	400	44		
NP0640SC	58	77	100		
NP0720SC	65	88		198	
NP0900SC	75	98		122	
NP1100SC	90	130		154	
NP1300SC	120	160		120	
NP1500SC	140	180		113	
NP1800SC	170	220		99	
NP2100SC	180	240		97	
NP2300SC	190	260		56	
NP2600SC	220	300		81	
NP3100SC	275	350		76	
NP3500SC	320	400		71	

SURGE SUPPRESSORS (continued)

THYRISTOR SURGE SUPPRESSORS

					
Surge Current IPPS1 10 x 1000 μ sec (A)	Maximum Off State Voltage (V)	SMB Case 403C	Maximum Breakover Voltage V_{BO} (V)	Min. Holding Current I_H (mA)	General Description
50	170	MMT05B230	265	175	These Thyristor Surge Protection devices prevent overvoltage damage to sensitive circuits by lightning, induction and power line crossing. They are breakover triggered crowbar protectors with turn off occurring when the surge current falls below the holding current value.
	200	MMT05B260	320	175	
	270	MMT05B310	365	175	
100	170	MMT10B230	265	175	
	200	MMT10B260	320	175	
	270	MMT10B310	365	175	

LOW VOLTAGE PROTECTOR

					
TSOP-5 CASE 483 SN SUFFIX					
Device	V_{RWM} Offstate Voltage (V)	V_{BR} Breakover Voltage (V)	$I_{PPS} = 8 \times 20 \mu S$ Surge Current Rating (A)	$C_o, 2 V, 1 Mhz$ Capacitance Maximum (pF)	General Description
	NP0080TA	8	9.5	50	
NP0120TA	12	13		11	These low capacitance, low leakage current devices provide superior performance in low voltage high speed applications and assist designers in protecting equipment from surge events while maximizing circuit performance.

VERY LOW VOLTAGE TSPD

					
SMB CASE 403C					
Device	V_{DRM} Offstate Voltage (V)	V_{BO} Breakover Voltage (V)	$I_{PPS} = 10 \times 1000 \mu s$ Surge Current Rating (A)	$C_o, 2 V, 1 Mhz$ Capacitance Max (pF)	General Description
NP0080SAMC	6	25	50	30	The NP-VLV series of Low Capacitance Thyristor Surge Protection Devices (TSPD) protect sensitive electronic equipment from transient overvoltage conditions. Their low turn on voltage allows them to replace much larger TVS devices of the same surge rating.
NP0100SAMC	8	15			
NP0150SAMC	15	30			
NP0220SAMC	15	32			
NP0300SAMC	25	40			
NP0080SCMC	6	25	100		
NP0100SCMC	8	15			
NP0150SCMC	15	30			
NP0220SCMC	15	32			
NP0300SCMC	25	40			

SURGE SUPPRESSORS (continued)

HIGH CURRENT TSPD

					
SMB CASE 403C					
Device	V_{DRM} Offstate Voltage (V)	V_{BO} Breakover Voltage (V)	I_{PPS} = 10 x 1000 μs Surge Current Rating (A)	C_O, 2 V, 1 Mhz Capacitance Max (pF)	General Description
NP0720SDMC	58	77	200	65	The NP–SDMC series of High Current Thyristor Surge Protection Devices (TSPD) protect sensitive electronic equipment from transient overvoltage conditions. The high current withstand of these devices offer protection in extreme environments and provide a solution for GR–1089 balanced “Y” configurations.
NP1100SDMC	65	88			
NP1300SDMC	75	98			
NP1500SDMC	90	130			
NP1800SDMC	170	220			
NP3100SDMC	275	350			

TRIGGERS

THYRISTOR TRIGGERS

					
On–State RMS Current I_{T(RMS)} (A).	DO–41 Case 059A	Surmetic 50 Case 267 Style 2	Range Breakover Voltage V_{BO} (V)	I_{TSM} Surge Current 60 Hz (A)	General Description
0.9	MKP1V120		110–130	4	High voltage trigger devices (used primarily to trigger SCRs and Triacs gates) similar in operation to triacs. Upon reaching the breakover voltage in either direction, the devices switch to a low voltage on state.
	MKP1V130		120–140		
	MKP1V160		150–170		
	MKP1V240		220–250		
1.0		MKP3V120	110–130	20	
		MKP3V240	220–250		

TRANSISTOR TRIGGERS

					
I_P R_G = 10 kΩ (μA Max)	R_G = 1 MΩ (μA Max)	TO–92⁽¹²⁾ (TO226AA) Case 029 Style 2	I_V R_G = 10 kΩ (μA Max)	R_G = 1 MΩ (μA Max)	General Description
5.0	2.0	2N6027	70	50	The only transistors in the Thyristor portfolio. Similar to unijunction transistors, except that I _P , I _V , and intrinsic voltage are programmable (adjustable) by means of external voltage divider. Used primarily to trigger SCR and Triac gates,
1.0	0.15	2N6028	25	25	

12. See TO–92 data sheets for device suffix packaging ordering options.

Voltage and Current Management

Voltage and Current Management

Table of Contents

	Page
Current Protection	332
Voltage Protection	332
Voltage References	333
Voltage Supervisors	334

ON Semiconductor Selector Guide – Voltage and Current Management CURRENT PROTECTION

Device	Type	V _I Max (V)	I _{DS(on)} Max (mΩ)	T _{SD} Typ (°C)	T _{hyst} Typ (°C)	Package
NIS5112D1	Latch Off	18	35	135		SOIC-8
NIS5112D2	Auto-Retry	18	35	135	40	SOIC-8
NIS5132MN1	Latch Off	18	55	175	45	DFN-10
NIS5132MN2	Auto-Retry	18	55	175	45	DFN-10
NIS5135MN1	Latch Off	-	82	175	45	DFN-10
NIS5135MN2	Auto-Retry	-	82	175	45	DFN-10

VOLTAGE PROTECTION

Device	V _{CC} (V) Max	UVLO (V) Typ	OVLO (V) Typ	I _q (µA) Typ	OC _P (A) Typ	R _{DS(on)} (mΩ) Typ	Battery Sense	Flag Status	Enable	Reverse Blocking	Package	Additional Features
NCP360MU	+21	3.00	5.675	24	N.A	210	No	Yes	Yes	No	µDFN-6	-
NCP360SN	+21	3.00	5.675	24	N.A	210	No	Yes	Yes	No	TSOP-5	-
NCP360SNAE	+21	3.00	6.250	24	N.A	210	No	Yes	Yes	No	TSOP-5	-
NCP360SNAF	+21	3.00	7.070	24	N.A	210	No	Yes	Yes	No	TSOP-5	-
NCP360SNAI	+21	3.00	7.200	24	N.A	210	No	Yes	Yes	No	TSOP-5	-
NCP361MU	+21	3.00	5.675	20	0.75	300	No	Yes	Yes	No	µDFN-6	-
NCP361SN	+21	3.00	5.675	20	0.75	300	No	Yes	Yes	No	TSOP-5	-
NCP362AMU	+21	3.00	5.675	20	0.75	300	No	Yes	Yes	No	µDFN-10	TVS for Vbus pin
NCP362BMU	+21	3.00	5.675	20	0.75	300	No	Yes	Yes	No	µDFN-10	TVS for Data lines
NCP362CMU	+21	3.00	5.675	20	0.75	300	No	Yes	Yes	No	µDFN-10	TVS for Both Vbus and data
NCP348MT	+30	3.25	6.40	170	N.A	65	No	Yes	Yes	No	WDFN-10	Soft-start
NCP348AEMT	+30	3.25	6.02	170	N.A	65	No	Yes	Yes	No	WDFN-10	Soft-start
NCP347MTAE	+30	2.95	5.63	170	N.A	65	No	Yes	Yes	No	WDFN-10	Soft-start
NCP347MTAF	+30	2.95	5.90	170	N.A	65	No	Yes	Yes	No	WDFN-10	Soft-start
NCP347MTAH	+30	2.95	7.20	170	N.A	65	No	Yes	Yes	No	WDFN-10	Soft-start
NCP347MTAI	+30	2.95	5.85	170	N.A	65	No	Yes	Yes	No	WDFN-10	Soft-start
NCP349MN	+30	2.95	6.85	140	N.A	65	No	Yes	Yes	No	DFN-6	Soft-start
NCP349MNAE	+30	2.95	5.68	140	N.A	65	No	Yes	Yes	No	DFN-6	Soft-start
NCP349MNBG	+30	3.25	6.02	140	N.A	65	No	Yes	Yes	No	DFN-6	Soft-start
NCP349MNBK	+30	3.25	6.40	140	N.A	65	No	Yes	Yes	No	DFN-6	Soft-start
NCP370MUI	-30 / +30	2.70	6.60	200	1.7, Adj	130	No	Yes	Yes	Yes	LLGA-12	Soft-start, Production mode
NCP372MUI	-30 / +30	2.70	6.30	200	N.A	130	No	Yes	Yes	Yes	LLGA-12	Soft-start

VOLTAGE REFERENCES

Product	Type	V _(BR) Typ (V)	Tolerance (%)	I _Q Typ (mA)	I _R Min (mA)	V _F Max (V)	T _A Min (°C)	T _A Max (°C)	Package
CAT102TDI	Adjustable	0.6	1	0.09	0.1	18	-40	85	TSOT-23
CAT8900B125	Fixed	1.25	0.08	0.45	0.1	6.5	-40	85	SOT-23
CAT8900B204	Fixed	2.048	0.05	0.45	0.1	6.5	-40	85	SOT-23
CAT8900B250	Fixed	2.5	0.04	0.45	0.1	6.5	-40	85	SOT-23
CAT8900C125	Fixed	1.25	0.2	0.45	0.1	6.5	-40	85	SOT-23
CAT8900C204	Fixed	2.048	0.12	0.45	0.1	6.5	-40	85	SOT-23
CAT8900C250	Fixed	2.5	0.1	0.45	0.1	6.5	-40	85	SOT-23
CAT8900D125	Fixed	1.25	0.4	0.45	0.1	6.5	-40	85	SOT-23
CAT8900D204	Fixed	2.048	0.24	0.45	0.1	6.5	-40	85	SOT-23
CAT8900D250	Fixed	2.5	0.2	0.45	0.1	6.5	-40	85	SOT-23
LM285D-1.2	Fixed	1.235	1	-	0.01	-	-40	85	SOIC-8
LM285D-2.5	Fixed	2.5	1.5	-	0.01	-	-40	85	SOIC-8
LM285Z-1.2	Fixed	1.235	1	-	0.01	-	-40	85	TO-92
LM285Z-2.5	Fixed	2.5	1.5	-	0.01	-	-40	85	TO-92
LM385BD-1.2	Fixed	1.235	1	-	0.015	-	0	70	SOIC-8
LM385BD-2.5	Fixed	2.5	1.5	-	0.015	-	0	70	SOIC-8
LM385BZ-1.2	Fixed	1.235	1	-	0.015	-	0	70	TO-92
LM385BZ-2.5	Fixed	2.5	1.5	-	0.015	-	0	70	TO-92
LM385D-1.2	Fixed	1.235	2	-	0.015	-	0	70	SOIC-8
LM385D-2.5	Fixed	2.5	3	-	0.015	-	0	70	SOIC-8
LM385Z-1.2	Fixed	1.235	2	-	0.015	-	0	70	TO-92
LM385Z-2.5	Fixed	2.5	3	-	0.015	-	0	70	TO-92
NCP100	Adjustable	0.696	1.7	0.07	0.1	7	-40	85	TO-92, TSOP-5
NCP4300A	Fixed	2.6	1	-	0.08	36	0	105	SOIC-8
NCS1002	-	-	0.4	0.4	-	-	-	-	SOIC-8
NCV1009	Fixed	2.5	0.2	-	0.4	-	-40	125	SOIC-8
NCV431AI	-	-	-	0.5	-	-	-	-	Micro8™, SOIC-8
NCV431BV	Adjustable	2.495	0.4	-	1	36	-40	125	Micro8™
TL431AC	Adjustable	2.495	1	0.5	1	36	0	70	Micro8™, SOIC-8, TO-92, PDIP-8
TL431AI	Adjustable	2.495	1	0.5	1	36	-40	85	Micro8™, SOIC-8, TO-92, PDIP-8
TL431BC	Adjustable	2.495	0.4	-	1	36	0	70	Micro8™, SOIC-8, TO-92, PDIP-8
TL431BI	Adjustable	2.495	0.4	-	1	36	-40	85	Micro8™, SOIC-8, TO-92, PDIP-8
TL431BV	Adjustable	2.495	0.4	-	1	36	-40	85	Micro8™, SOIC-8, TO-92, PDIP-8
TL431C	Adjustable	2.495	2.2	-	1	36	0	70	Micro8™, SOIC-8, TO-92, PDIP-8
TL431I	Adjustable	2.495	2.2	-	1	36	-40	85	Micro8™, SOIC-8, TO-92, PDIP-8
TLV431A	Adjustable	1.24	1	-	0.08	18	-40	85	TO-92, SOT-23
TLV431B	Adjustable	1.24	0.5	-	0.00055	16	-40	85	TO-92, SOT-23

ON Semiconductor Selector Guide – Voltage and Current Management VOLTAGE SUPERVISORS

Device	Channels	V _{CC} Min (V)	V _{CC} Max (V)	I _{CC} Typ (µA)	Reset Active High	Reset Active Low	Threshold Levels (V)	Package
CAT885	5	1.5	5.5	3		✓	1.68, 2.33, 2.87, 2.95, 4.63, + 3x Adj (0.60 V min)	MSOP-8, SOIC-8
CAT8710	4	1.5	5.5	3		✓	1.67, 2.32, 2.78, 3.08 + 2x Adj (0.62 V min)	SOT-23-6
CAT705/6	2	1.2	5.5	6		✓	4.40 / 1.25, 4.65 / 1.25	SOIC-8
CAT813	2	1.2	5.5	6	✓		4.65 / 1.25	SOIC-8
MC33161, MC34161	2	2	40	450	✓	✓	1.27	Micro8™, SOIC-8, PDIP-8
CAT808N	1	1.2	6.0	3.5		✓	2.7, 3.2, 3.5	TSOT-23-5
CAT811	1	1	5.5	6		✓	2.32, 2.63, 2.93, 3.08, 4.0, 4.38, 4.63	SOT-143-4
CAT812	1	1	5.5	6	✓		2.32, 2.63, 2.93, 3.08, 4.0, 4.38, 4.64	SOT-143-4
CAT823/4/5	1	1	5.5	4	✓	✓	2.19, 2.32, 2.63, 2.93, 3.08, 4.0, 4.38, 4.63	TSOT-23-5, SC-70-5
CAT853/59/63/69	1	1	5.5	6		✓	2.40, 2.93, 3.08, 4.38	SOT-23-3
CAT1232LP	1	1	5.5	35		✓	4.37, 4.62	PDIP-8, MSOP-8, SOIC-8, SOIC-16
CAT1832	1	1	5.5	35		✓	2.55, 2.88	PDIP-8, MSOP-8, SOIC-8
MAX708	1	1	5.5	12		✓	2.63, 2.93, 3.08, 4.38	Micro8™, SOIC-8
MAX803 (Note 13)	1	1	5.5	0.5		✓	1.2, 1.6, 2.32, 2.63, 2.93, 3.08, 4.0, 4.38, 4.63	SC-70-3, SOT-23-3
MAX809 (Note 14)	1	1	5.5	0.5		✓	1.2, 1.6, 2.32, 2.63, 2.93, 3.08, 4.0, 4.38, 4.55, 4.63, 4.9	SC-70-3, SOT-23-3
MAX810 (Note 15)	1	1	5.5	0.5		✓	1.2, 2.63, 2.93, 3.08, 4.38, 4.63	SC-70-3, SOT-23-3
MC33064, MC34064	1	1	6.5	9		✓	4.59	Micro8™, SOIC-8, TSOP-5, TO-92
MC33164, MC34164	1	1	10	9		✓	2.65, 4.27	Micro8™, SOIC-8, TSOP-5, TO-92
NCP300/1	1	0.55	10	0.2	✓	✓	0.9, 1.0, 1.2, 1.6, 1.8, 1.85, 2.0, 2.2, 2.5, 2.6, 2.7, 2.8, 3.0, 3.1, 3.2, 3.3, 3.4, 3.6, 3.9, 4.0, 4.2, 4.4, 4.5, 4.6, 4.7	TSOP-5
NCP302	1	0.55	10	0.2	✓	✓	0.9, 1.5, 1.8, 2.0, 2.7, 3.0, 3.3, 3.8, 4.0, 4.3, 4.5, 4.7	TSOP-5
NCP303	1	0.55	10	0.2		✓	0.9, 1.0, 1.1, 1.3, 1.4, 1.5, 1.6, 1.7, 1.8, 2.0, 2.2, 2.3, 2.4, 2.5, 2.6, 2.7, 2.8, 2.9, 3.0, 3.1, 3.2, 3.3, 3.4, 3.6, 3.8, 4.0, 4.2, 4.5, 4.6, 4.7, 4.9	TSOP-5
NCP304	1	0.55	10	0.8		✓	0.9, 1.5, 1.8, 2.0, 2.2, 2.3, 2.5, 2.7, 2.9, 3.0, 3.3, 3.7, 3.8, 4.0, 4.2, 4.3, 4.5, 4.6, 4.7, 4.9	SC-70-4
NCP305	1	0.55	10	0.8		✓	0.9, 1.1, 1.5, 1.6, 1.7, 1.8, 2.0, 2.2, 2.3, 2.4, 2.5, 2.6, 2.7, 2.8, 2.9, 3.0, 3.1, 3.2, 3.3, 3.4, 3.5, 3.6, 3.7, 4.0, 4.4, 4.5, 4.7, 4.9	SC-70-4

13. See CAT803, MAX803, NCP803

14. See CAT809, MAX809

15. See CAT810, MAX810

Alphanumeric Parts Index

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
0.11 um (SP110)	110	1.5SMC82A	182	1N5375B	158
0.18 um (ONC18)	110	1.5SMC91A	182	1N5377B	158
0.35 um (SC3)	110	1N4001	282	1N5378B	158
0.5 um (SC5)	110	1N4002	282	1N5380B	158
0W588-002-XUP	224	1N4003	282	1N5381B	158
0W633-001-XTP	224	1N4004	282	1N5383B	158
0W888-002-XTP	224	1N4005	282	1N5384B	158
1.5KE10A	170	1N4006	282	1N5386B	158
1.5KE11A	170	1N4007	282	1N5387	158
1.5KE12A	170	1N4933	282	1N5388B	158
1.5KE13A	170	1N4934	282	1N5400	282
1.5KE15A	170	1N4935	282	1N5401	282
1.5KE16A	170	1N4936	282	1N5402	282
1.5KE18A	170	1N4937	282	1N5404	282
1.5KE20A	170	1N5333B	157	1N5406	282
1.5KE24A	170	1N5334B	157	1N5407	282
1.5KE27A	170	1N5335B	157	1N5408	282
1.5KE30A	170	1N5336B	157	1N5817	275
1.5KE33A	170	1N5337B	157	1N5818	275
1.5KE36A	170	1N5338B	157	1N5819	275
1.5KE39A	170	1N5339B	157	1N5820	275
1.5KE43A	170	1N5340B	157	1N5821	275
1.5KE47A	170	1N5341B	157	1N5822	275
1.5KE51A	170	1N5342B	157	1N5913B	157
1.5KE56A	170	1N5343B	157	1N5917B	157
1.5KE6.8A	170	1N5344B	157	1N5919B	157
1.5KE62A	170	1N5345B	157	1N5920B	157
1.5KE68A	170	1N5346B	157	1N5921B	157
1.5KE7.5A	170	1N5347B	157	1N5923B	157
1.5KE75A	170	1N5348B	157	1N5924B	157
1.5KE8.2A	170	1N5349B	157	1N5925B	157
1.5KE82A	170	1N5350B	157	1N5927B	157
1.5KE91A	170	1N5351B	157	1N5929B	157
1.5SMC10A	182	1N5352B	157	1N5931B	157
1.5SMC12A	182	1N5353B	157	1N5932B	157
1.5SMC13A	182	1N5354B	157	1N5934B	157
1.5SMC15A	182	1N5355B	157	1N5935B	158
1.5SMC16A	182	1N5356B	157	1N5937B	158
1.5SMC18A	182	1N5357B	157	1N5938B	158
1.5SMC20A	182	1N5358B	157	1N5940B	158
1.5SMC22A	182	1N5359B	157	1N5941B	158
1.5SMC24A	182	1N5360B	158	1N5942B	158
1.5SMC27A	182	1N5361B	158	1N5946B	158
1.5SMC30A	182	1N5362B	158	1N5948B	158
1.5SMC33A	182	1N5363B	158	1N5953B	158
1.5SMC36A	182	1N5364B	158	1N5955B	158
1.5SMC39A	182	1N5365B	158	1N5956B	158
1.5SMC43A	182	1N5366B	158	1N6267A	170
1.5SMC47A	182	1N5367B	158	1N6271A	170
1.5SMC51A	182	1N5368B	158	1N6274A	170
1.5SMC56A	182	1N5369B	158	1N6275A	170
1.5SMC6.8A	182	1N5370B	158	1N6276A	170
1.5SMC62A	182	1N5371B	158	1N6277A	170
1.5SMC68A	182	1N5372B	158	1N6278A	170
1.5SMC7.5A	182	1N5373B	158	1N6279A	170
1.5SMC75A	182	1N5374B	158	1N6280A	170

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
1N6281A	170	1SMA5.0A	173	1SMB14A	175
1N6282A	170	1SMA54A	173	1SMB14CA	177
1N6283A	170	1SMA58A	173	1SMB150A	176
1N6284A	170	1SMA58CA	174	1SMB15A	175
1N6285A	170	1SMA5913B	164	1SMB15CA	177
1N6286A	170	1SMA5914B	164	1SMB160A	176
1N6287A	170	1SMA5915B	164	1SMB16A	175
1N6288A	170	1SMA5916B	164	1SMB16CA	177
1N6289A	170	1SMA5917B	164	1SMB170A	176
1N6290A	170	1SMA5918B	164	1SMB17A	175
1N6291A	170	1SMA5919B	164	1SMB17CA	177
1N6292A	170	1SMA5920B	164	1SMB18A	175
1N6294A	170	1SMA5921B	164	1SMB18CA	177
1N6295A	170	1SMA5922B	164	1SMB20A	175
1PMT12A	171	1SMA5923B	164	1SMB20CA	177
1PMT16A	171	1SMA5924B	164	1SMB22A	175
1PMT22A	171	1SMA5925B	164	1SMB22CA	177
1PMT26A	171	1SMA5927B	164	1SMB24A	175
1PMT33A	171	1SMA5928B	164	1SMB24CA	177
1PMT5.0A	171	1SMA5929B	164	1SMB26A	175
1PMT7.0A	171	1SMA5930B	164	1SMB26CA	177
1SMA10A	173	1SMA5931B	164	1SMB28A	175
1SMA10CA	174	1SMA5932B	164	1SMB28CA	177
1SMA11A	173	1SMA5933B	164	1SMB30A	175
1SMA12A	173	1SMA5934B	164	1SMB30CA	177
1SMA12CA	174	1SMA5935B	164	1SMB33A	175
1SMA13A	173	1SMA5936B	164	1SMB33CA	177
1SMA13CA	174	1SMA5937B	164	1SMB36A	175
1SMA15A	173	1SMA5938B	164	1SMB36CA	177
1SMA15CA	174	1SMA5939B	164	1SMB40A	175
1SMA16A	173	1SMA5940B	164	1SMB40CA	177
1SMA16CA	174	1SMA5941B	164	1SMB43A	175
1SMA17A	173	1SMA5942B	164	1SMB43CA	177
1SMA18A	173	1SMA5943B	164	1SMB45A	175
1SMA18CA	174	1SMA5945B	164	1SMB45CA	177
1SMA20A	173	1SMA6.0A	173	1SMB48A	175
1SMA20CA	174	1SMA6.5A	173	1SMB48CA	177
1SMA22A	173	1SMA60CA	174	1SMB5.0A	175
1SMA24A	173	1SMA70A	173	1SMB51A	175
1SMA24CA	174	1SMA70CA	174	1SMB51CA	177
1SMA26A	173	1SMA78CA	174	1SMB54A	175
1SMA26CA	174	1SMA8.0A	173	1SMB54CA	177
1SMA28A	173	1SMA8.5A	173	1SMB58A	175
1SMA28CA	174	1SMA9.0A	173	1SMB58CA	177
1SMA30A	173	1SMB100A	175	1SMB5913B	164
1SMA30CA	174	1SMB10A	175	1SMB5914B	164
1SMA33A	173	1SMB10CA	177	1SMB5915B	164
1SMA33CA	174	1SMB110A	176	1SMB5916B	164
1SMA36A	173	1SMB11A	175	1SMB5917B	164
1SMA36CA	174	1SMB11CA	177	1SMB5918B	164
1SMA40A	173	1SMB120A	176	1SMB5919B	164
1SMA40CA	174	1SMB12A	175	1SMB5920B	164
1SMA43A	173	1SMB12CA	177	1SMB5921B	164
1SMA45A	173	1SMB130A	176	1SMB5922B	164
1SMA48A	173	1SMB13A	175	1SMB5923B	164
1SMA48CA	174	1SMB13CA	177	1SMB5924B	164

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
1SMB5925B	164	1SMC22A	181	2N5302	49
1SMB5926B	164	1SMC24A	181	2N5401	64
1SMB5927B	164	1SMC26A	181	2N5550	64
1SMB5928B	164	1SMC28A	181	2N5551	64
1SMB5929B	164	1SMC30A	181	2N5655	45
1SMB5930B	164	1SMC33A	181	2N5657	45
1SMB5931B	164	1SMC36A	181	2N5684	49
1SMB5932B	164	1SMC40A	181	2N5686	49
1SMB5933B	164	1SMC43A	181	2N5883	49
1SMB5934B	164	1SMC48A	181	2N5884	49
1SMB5935B	164	1SMC5.0A	181	2N5885	49
1SMB5936B	164	1SMC51A	181	2N5886	49
1SMB5937B	164	1SMC54A	181	2N6027	328
1SMB5938B	164	1SMC58A	181	2N6028	328
1SMB5939B	164	1SMC6.0A	181	2N6034	50
1SMB5940B	164	1SMC6.5A	181	2N6035	50
1SMB5941B	164	1SMC60A	181	2N6036	50
1SMB5942B	164	1SMC64A	181	2N6038	50
1SMB5943B	164	1SMC7.0A	181	2N6039	50
1SMB5944B	164	1SMC7.5A	181	2N6040	50
1SMB5945B	164	1SMC70A	181	2N6042	50
1SMB5946B	164	1SMC75A	181	2N6043	50
1SMB5947B	165	1SMC78A	181	2N6045	50
1SMB5948B	165	1SMC8.0A	181	2N6052	51
1SMB5949B	165	1SMC9.0A	181	2N6071A	321
1SMB5951B	165	1SS400T1	156	2N6071B	321
1SMB5952B	165	2N3055	48	2N6073A	321
1SMB5953B	165	2N3055A	48	2N6073B	321
1SMB5954B	165	2N3442	48	2N6075A	321
1SMB5955B	165	2N3771	49	2N6075B	321
1SMB5956B	165	2N3772	49	2N6107	47
1SMB6.0A	175	2N3773	49	2N6109	47
1SMB6.5A	175	2N3904	55, 65	2N6111	47
1SMB60A	175	2N3906	55, 65	2N6284	51
1SMB60CA	177	2N4124	55	2N6286	51
1SMB64A	175	2N4401	55, 62, 65	2N6287	51
1SMB64CA	177	2N4403	55, 62, 65	2N6288	47
1SMB7.0A	175	2N4918	45	2N6292	47
1SMB7.5A	175	2N4919	45	2N6338	49
1SMB70A	175	2N4920	45	2N6341	49
1SMB75A	175	2N4921	45	2N6344	322
1SMB75CA	177	2N4922	45	2N6344A	323
1SMB8.0A	175	2N4923	45	2N6348A	323
1SMB8.5A	175	2N5038	49	2N6349A	323
1SMB85A	175	2N5060	318	2N6387	51
1SMB9.0A	175	2N5061	318	2N6388	51
1SMB90A	175	2N5062	318	2N6394	320
1SMC10A	181	2N5064	318	2N6395	320
1SMC12A	181	2N5087	55, 61	2N6397	320
1SMC13A	181	2N5088	55, 61	2N6399	320
1SMC14A	181	2N5089	55, 61	2N6400	320
1SMC15A	181	2N5190	46	2N6401	320
1SMC16A	181	2N5191	46	2N6402	320
1SMC17A	181	2N5192	46	2N6403	320
1SMC18A	181	2N5194	46	2N6404	320
1SMC20A	181	2N5195	46	2N6405	320

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
2N6426	61	7SB384	291	AMIS-30663	254
2N6427	61	7SB385	291	AMIS-41682	254
2N6487	47	7WB3125	291	AMIS-41683	254
2N6488	47	7WB3126	291	AMIS-42665	254
2N6490	47	7WB3305	291	AMIS-42670	254
2N6491	47	7WB3306	291	AMIS-42671	254
2N6504	320	7WB383	291	AMIS-42673	254
2N6505	320	7WBD3125	291	AMIS-42675	254
2N6507	320	7WBD3126	291	AMIS-42770	254
2N6508	320	7WBD3305	291	AMIS30521	219
2N6509	320	7WBD3306	291	AMIS30522	219
2N6520	64	7WBD383	291	AMIS30532	219
2N6667	51	A5191HRT	254	AMIS30542	219
2N7000	249	ADM1021	313	AMIS30621	219
2N7002E	241	ADM1023	313	AMIS30622	219
2N7002K	241	ADM1024	312	AMIS30623	219
2N7002L	241	ADM1026	312	AMIS30624	219
2N7002W	239	ADM1029	312	AMIS49250	254
2SA1020	62	ADM1030	312	ASM3I2579AF-06OR	103
2SA1774	58	ADM1031	312	ASM3I2669AF-06OR	103
2SA2029BM3T5G	58	ADM1032	313	ASM3I2779AF-06OR	103
2SC4617	58	ADM1033	312	ASM3P1819NF-08SR	103
2SC5658BM3T5G	58	ADM1034	312	ASM3P2107AF-08SR	103
2SC5658RM3	58	ADP3110A	218	ASM3P2108AF-08SR	103
74FST3257	291, 305	ADP3120A	218	ASM3P2111BG-08SR	103
74HC00	300	ADP3121	218	ASM3P2180AF-08SR	103
74HC02	301	ADP3210	121	ASM3P2180AF-08ST	103
74HC04	299	ADP3211	121	ASM3P2274AF-06OR	103
74HC08	300	ADP3212	121	ASM3P2474AF-06OR	103
74HC125	289	ADP3290	121, 122	ASM3P2598AF-06OR	103
74HC132	300	ADP3293	121, 122	ASM3P2669AF-06OR	103
74HC138	304	ADP3419	218	ASM3P2760AF-06OR	103
74HC14	295	ADP3611	218	ASM3P2775AF-06OR	103
74HC244	288	ADP4000	121, 122	ASM3P2779AF-06OR	103
74HC245	306	ADP4100	121, 122	ASM3P2780AF-06OR	103
74HC32	301	ADT7421	313	ASM3P2853AG-08SR	103
74HC373	297	ADT7460	312	ASM3P2863AF-06OR	103
74HC374	292	ADT7461	313	ASM3P2872AF-06OR	103
74HC540	288	ADT7461A	313	AU5517	30
74HC541	288	ADT7462	312	B250W48A106XXG	224
74HC574	292	ADT7463	312	B300W35A102XYG	224
74HC595	297	ADT7467	312	BAL99LT1	155
74HC74	292	ADT7473	312	BAS116LT1	155
74HC86	300	ADT7475	312	BAS16DXV6T1	156
74HCT04	294	ADT7476	312	BAS16HT1	156
74HCT08	300	ADT7481	313	BAS16LT1	155
74HCT14	295	ADT7482	313	BAS16TT1	156
74HCT157	305	ADT7483	313	BAS16WT1	155
74HCT245	306	ADT7484	313	BAS16XV2T1	156
74HCT32	301	ADT7485A	313	BAS19LT1	155
74HCU04	295	ADT7486A	313	BAS20HT1	156
74VCXH16245	306	ADT7488A	313	BAS20LT1	155
74VCXH245	287, 306	ADT7490	312	BAS21AH	156
7SB3125	291	AMIS-49200	254	BAS21DW5T1	156
7SB3126	291	AMIS-30600	254	BAS21HT1	156
7SB3257	291	AMIS-30660	254	BAS21LT1	155

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
BAS21M3	156	BC807-25LT1	56	BC858CLT1	57
BAS21SL	155	BC807-40LT1	56	BCP53-10	59, 63
BAS40-04LT1	151	BC808-25L	57	BCP53-16	59, 63
BAS40-06LT1	151	BC817-16LT1	56	BCP53T1	59, 63
BAS40LT1	151	BC817-25LT1	56	BCP56-10	59, 63
BAS70-04LT1	151	BC817-40LT1	56	BCP56-16	59, 63
BAS70LT1	151	BC818-40L	57	BCP56T1	59, 63
BAT54ALT1	151	BC846ALT1	56	BCP68T1	59, 63
BAT54AWT1	152	BC846BDW1T1	60	BCP69T1	59, 63
BAT54CLT1	151	BC846BLT1	56	BCW30LT1	57
BAT54CTT1	152	BC846BM3T5G	58	BCW32LT1	57
BAT54CWT1	152	BC846BPDW1T1	60	BCW33LT1	57
BAT54CXV3T1	152	BC846BWT1	58	BCW65ALT1	57, 63
BAT54HT1	151	BC847ALT1	56	BCW65CLT1	57
BAT54LT1	151	BC847AWT1	58	BCW66GLT1	63
BAT54M3	153	BC847BDW1T1	60	BCW68GLT1	56, 63
BAT54SLT1	151	BC847BLT1	56	BCW70LT1	56
BAT54SWT1	152	BC847BM3T5G	58	BCW72LT1	56
BAT54T1	151	BC847BPDW1T1	60	BCX17LT1	56, 63
BAT54WT1	152	BC847BPDV6T1	60	BCX19LT1	56, 63
BAT54XV2T1	152	BC847BTT1	58	BD135	45
BAV199LT1	155	BC847BWT1	58	BD136	45
BAV23CL	155	BC847CDW1T1	60	BD137	45
BAV70LT1	155	BC847CDXV6T1	60	BD138	45
BAV70M3	156	BC847CLT1	56	BD139	45
BAV70TT1	156	BC847CTT1	58	BD140	45
BAV70WT1	155	BC847CWT1	58	BD159	45
BAV74LT1	155	BC848ALT1	57	BD179	45
BAV99LT1	155	BC848BLT1	57	BD180	45
BAV99RWT1	155	BC848BWT1	58	BD234	45
BAV99WT1	155	BC848CDW1T1	60	BD237	45
BAW56LT1	155	BC848CLT1	57	BD241C	46
BAW56M3	156	BC848CPDW1T1	60	BD242B	46
BAW56TT1	156	BC848CWT1	58	BD242C	46
BAW56WT1	155	BC849BLT1	57	BD243C	47
BC307B	55	BC849CLT1	57	BD244B	47
BC327-25	55, 62	BC850BLT1	56	BD244C	47
BC327-40	55, 62	BC850CLT1	56	BD435	46
BC337	55, 62	BC856ALT1	56	BD436	46
BC337-25	55, 62	BC856BDW1T1	60	BD437	46
BC337-40	55, 62	BC856BLT1	56	BD438	46
BC369	55, 62	BC856BM3T5G	58	BD439	46
BC373	61	BC856BWT1	58	BD440	46
BC517	61	BC857ALT1	56	BD441	46
BC546B	55	BC857BDW1T1	60	BD442	46
BC547B	55	BC857BLT1	56	BD675	50
BC548C	55	BC857BTT1	58	BD675A	50
BC549C	55	BC857BWT1	58	BD676	50
BC550C	55, 61	BC857CDW1T1	60	BD676A	50
BC557B	55	BC857CLT1	56	BD677	50
BC557C	55	BC857CWT1	58	BD677A	50
BC637	55, 62	BC858ALT1	57	BD678	50
BC639	55, 62	BC858AWT1	58	BD678A	50
BC639-16	55, 62	BC858BLT1	57	BD679	50
BC640-016	55	BC858BWT1	58	BD679A	50
BC807-16LT1	56	BC858CDXV6T1	60	BD680	50

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
BD680A	50	BTA30H-800CW3G	324	BZX84C33L	160
BD681	50	BTB08-600BW3G	322	BZX84C36L	160
BD682	50	BTB08-600CW3G	322	BZX84C39L	160
BD787	46	BTB08-800BW3G	322	BZX84C3V0L	160
BD788	46	BTB08-800CW3G	322	BZX84C3V3L	160
BD809	47	BTB12-600BW3G	323	BZX84C3V6L	160
BD810	47	BTB12-600CW3G	323	BZX84C3V9L	160
BDV64B	51	BTB12-600TW3G	323	BZX84C43L	161
BDV65B	51	BTB12-800BW3G	323	BZX84C47L	161
BDW42	51	BTB12-800CW3G	323	BZX84C4V3L	160
BDW46	51	BTB12H-600CW3G	323	BZX84C4V7L	160
BDW47	51	BTB16-600BW3G	324	BZX84C51L	161
BDX33B	51	BTB16-600CW3G	324	BZX84C56L	161
BDX33C	51	BTB16-800BW3G	324	BZX84C5V1L	160
BDX34B	51	BTB16-800CW3G	324	BZX84C5V6L	160
BDX34C	51	BTB16H-600BW3G	324	BZX84C62L	161
BDX53B	50	BU323Z	51	BZX84C68L	161
BDX53C	50	BU406	47	BZX84C6V2L	160
BDX54B	50	BUB323Z	50	BZX84C6V8L	160
BDX54C	50	BUH100	47, 54	BZX84C75L	161
BF720T1	64	BUH150	47, 54	BZX84C7V5L	160
BF721T1	64	BUH50	46, 54	BZX84C8V2L	160
BS107	249	BUL45	46, 54	BZX84C9V1L	160
BS107A	249	BUL45D2	46, 54	C106B	318
BS108	249	BUV21	49	C106D	318
BS170	249	BUV22	49	C106D1	318
BSP16T1	64	BUV26	47	C106M	318
BSP19AT1	64	BUV27	47	C106M1	318
BSP52T1	61	BUX85	46	C122F1	319
BSS123L	241	BZ84B15L	160	C3/D3	110
BSS138L	241	BZX84B12L	160	C5	110
BSS63LT1	56	BZX84B16L	160	CAT102TDI	333
BSS64LT1	56	BZX84B18L	160	CAT1232LP	334
BSS84L	241	BZX84B22L	160	CAT1832	334
BSV52LT1	65	BZX84B24L	160	CAT22C10	265
BTA08-600BW3G	322	BZX84B5V1L	160	CAT24AA01	263
BTA08-600CW3G	322	BZX84B5V6L	160	CAT24AA02	263
BTA08-800BW3G	322	BZX84B6V2L	160	CAT24AA04	263
BTA08-800CW3G	322	BZX84B6V8L	160	CAT24AA08	263
BTA12-600BW3G	323	BZX84B7V5L	160	CAT24AA16	263
BTA12-600CW3G	323	BZX84B8V2L	160	CAT24C01	263
BTA12-800BW3G	323	BZX84B9V1L	160	CAT24C02	263
BTA12-800CW3G	323	BZX84C10L	160	CAT24C03	263
BTA16-600BW3G	324	BZX84C11L	160	CAT24C04	263
BTA16-600CW3G	324	BZX84C12L	160	CAT24C05	263
BTA16-600SW3G	324	BZX84C13L	160	CAT24C08	263
BTA16-800BW3G	324	BZX84C15L	160	CAT24C128	263
BTA16-800CW3G	324	BZX84C16L	160	CAT24C16	263
BTA16-800SW3G	324	BZX84C18L	160	CAT24C164	263
BTA25-600CW3G	324	BZX84C20L	160	CAT24C208	263
BTA25-800CW3G	324	BZX84C22L	160	CAT24C21	263
BTA25H-600CW3G	324	BZX84C24L	160	CAT24C256	263
BTA25H-800CW3G	324	BZX84C27L	160	CAT24C32	263
BTA30-600CW3G	324	BZX84C2V4L	160	CAT24C44	265
BTA30-800CW3G	324	BZX84C2V7L	160	CAT24C64	263
BTA30H-600CW3G	324	BZX84C30L	160	CAT25010	264

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
CAT25020	264	CAT4103V	215	CAT5113YI-50	140
CAT25040	264	CAT4104V	215	CAT5113ZI-00	140
CAT25080	264	CAT4104VP2	215	CAT5113ZI-01	139
CAT25128	264	CAT4106HV4	215	CAT5113ZI-10	139
CAT25160	264	CAT4106YP	215	CAT5113ZI-50	140
CAT25256	264	CAT4109V	215	CAT5113ZI00	140
CAT25320	264	CAT4134HV2	215	CAT5113ZI01	139
CAT25640	264	CAT4137TD	215	CAT5113ZI10	139
CAT28C16A	265	CAT4139TD	215	CAT5113ZI50	140
CAT28C17A	265	CAT4201TD	215	CAT5114LI-00	138
CAT28C256	265	CAT4237TD	215	CAT5114LI-10	136
CAT28C257	265	CAT4238TD	215	CAT5114LI-50	137
CAT28C512	265	CAT4240TD	215	CAT5114VI-00	138
CAT28C513	265	CAT5110SDI-00	138	CAT5114VI-10	136
CAT28C64B	265	CAT5110SDI-10	136	CAT5114VI-50	137
CAT28C65B	265	CAT5110SDI-50	137	CAT5114VP2I-10	136
CAT28F001	265	CAT5110TBI-00	138	CAT5114VP2I00	138
CAT28F010	265	CAT5110TBI-10	136	CAT5114VP2I50	137
CAT28F020	265	CAT5110TBI-50	137	CAT5114YI-00	138
CAT28F512	265	CAT5111LI-00	140	CAT5114YI-10	136
CAT28LV256	265	CAT5111LI-10	139	CAT5114YI-50	137
CAT28LV64	265	CAT5111LI-50	139	CAT5114ZD7I00	138
CAT28LV65	265	CAT5111VI-00	140	CAT5114ZD7I10	136
CAT310W	214	CAT5111VI-10	139	CAT5114ZD7I50	137
CAT3200TDI-GT3	119	CAT5111VI-50	140	CAT5114ZI-00	138
CAT3200ZI-GT3	119	CAT5111YI-00	140	CAT5114ZI-10	136
CAT3224HV3	214	CAT5111YI-10	139	CAT5114ZI-50	137
CAT32TDI	214	CAT5111YI-50	140	CAT5115LI-00	138
CAT32ZD4	214	CAT5111ZI-00	140	CAT5115LI-10	136
CAT34C02	263	CAT5111ZI-10	139	CAT5115LI-50	137
CAT3604HV4	214	CAT5111ZI-50	140	CAT5115VI-00	138
CAT3604VHV4	214	CAT5111ZI00	140	CAT5115VI-10	136
CAT3606HV4	214	CAT5111ZI10	139	CAT5115VI-50	138
CAT3612HV2	214	CAT5111ZI50	140	CAT5115YI-00	138
CAT3614HV2	214	CAT5112LI-00	138	CAT5115YI-10	136
CAT3616HV4	214	CAT5112LI-10	136	CAT5115YI-50	138
CAT3626HV4	214	CAT5112LI-50	137	CAT5115ZI-00	138
CAT3636HV3	214	CAT5112VI-00	138	CAT5115ZI-10	136
CAT3637HV3	214	CAT5112VI-10	136	CAT5115ZI-50	138
CAT3643HV2	214	CAT5112VI-50	137	CAT5115ZI00	138
CAT3643HV3	214	CAT5112YI-00	138	CAT5115ZI10	137
CAT3644HV3	214	CAT5112YI-10	136	CAT5115ZI50	138
CAT3647HV3	214	CAT5112YI-50	137	CAT5116LI	139
CAT3648HV3	214	CAT5112ZI-10	136	CAT5116VI	139
CAT37TDI	214	CAT5112ZI-50	137	CAT5116YI	139
CAT4004VP2	214	CAT5113LI-00	140	CAT5116ZI	139
CAT4008V	214	CAT5113LI-01	139	CAT5118SDI-00	139
CAT4008W	214	CAT5113LI-10	139	CAT5118SDI-10	137
CAT4008Y	214	CAT5113LI-50	140	CAT5118SDI-50	138
CAT4016HV6	214	CAT5113VI-00	140	CAT5118TBI-00	139
CAT4016VS	214	CAT5113VI-01	139	CAT5118TBI-10	137
CAT4016VSR	214	CAT5113VI-10	139	CAT5118TBI-50	138
CAT4016W	215	CAT5113VI-50	140	CAT5119SDI-00	139
CAT4016Y	215	CAT5113YI-00	140	CAT5119SDI-10	137
CAT4026V	215	CAT5113YI-01	139	CAT5119SDI-50	138
CAT4101TV	215	CAT5113YI-10	139	CAT5119TBI-00	139

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
CAT5119TBI-10	137	CAT5241WI00	145	CAT5401YI-10	144
CAT5119TBI-50	138	CAT5241WI10	144	CAT5401YI-25	143
CAT5120SDI-10	136	CAT5241WI25	143	CAT5401YI-50	144
CAT5120SDI-50	136	CAT5241WI50	144	CAT5401YI00	145
CAT5120TBI-10	136	CAT5241YI-00	145	CAT5401YI10	144
CAT5120TBI-50	136	CAT5241YI-10	144	CAT5401YI25	143
CAT5121SDI-10	136	CAT5241YI-25	143	CAT5401YI50	144
CAT5121SDI-50	136	CAT5241YI-50	144	CAT5409WI-00	145
CAT5121TBI-10	136	CAT5241YI00	145	CAT5409WI-10	144
CAT5121TBI-50	136	CAT5241YI10	144	CAT5409WI-25	143
CAT5122SDI-10	136	CAT5241YI25	143	CAT5409WI-50	144
CAT5122SDI-50	136	CAT5241YI50	144	CAT5409WI00	145
CAT5122TBI-10	136	CAT5251WI-00	145	CAT5409WI10	144
CAT5122TBI-50	136	CAT5251WI-50	145	CAT5409WI50	144
CAT5123TBI-10	137	CAT5251WI00	145	CAT5409YI-00	145
CAT5124TBI-50	138	CAT5251WI50	145	CAT5409YI-10	144
CAT5125TBI-10	137	CAT5251YI-00	145	CAT5409YI-25	144
CAT5126VP2I10	137	CAT5251YI-50	145	CAT5409YI-50	144
CAT5126ZI-00	139	CAT5251YI00	145	CAT5409YI00	145
CAT5126ZI-10	137	CAT5251YI50	145	CAT5409YI10	144
CAT5126ZI-50	138	CAT5259WI-00	145	CAT5409YI25	144
CAT5127ZD7I10	137	CAT5259WI-50	145	CAT5409YI50	144
CAT5127ZI-10	137	CAT5259WI00	145	CAT5411WI-00	142
CAT5127ZI10	137	CAT5259WI50	145	CAT5411WI-10	141
CAT5128TBI-10	137	CAT5259YI-00	145	CAT5411WI-25	141
CAT5128TBI-50	138	CAT5259YI-50	145	CAT5411WI-50	142
CAT5129TDI-10	137	CAT5259YI00	145	CAT5411WI00	142
CAT5132ZI-00	141	CAT5259YI50	145	CAT5411WI10	141
CAT5132ZI-10	140	CAT5261WI-00	143	CAT5411WI25	141
CAT5132ZI-50	140	CAT5261WI-50	142	CAT5411WI50	142
CAT5133ZI-10	140	CAT5261WI00	143	CAT5411YI-00	142
CAT5140ZI-00	141	CAT5261WI50	143	CAT5411YI-10	141
CAT5140ZI-50	141	CAT5261YI-00	143	CAT5411YI-25	141
CAT5171TBI-50	141	CAT5261YI-50	143	CAT5411YI-50	142
CAT5172TBI-00	141	CAT5261YI00	143	CAT5411YI00	142
CAT5172TBI-50	141	CAT5261YI50	143	CAT5411YI10	141
CAT5221WI-00	142	CAT5269WI-00	143	CAT5411YI25	141
CAT5221WI-10	141	CAT5269WI-50	143	CAT5411YI50	142
CAT5221WI-25	141	CAT5269WI00	143	CAT5419WI-00	142
CAT5221WI-50	142	CAT5269WI50	143	CAT5419WI-10	141
CAT5221WI00	142	CAT5269YI-00	143	CAT5419WI-25	141
CAT5221WI10	141	CAT5269YI00	143	CAT5419WI-50	142
CAT5221WI25	141	CAT5269YI50	143	CAT5419WI00	142
CAT5221WI50	142	CAT5270YI-00	143	CAT5419WI25	141
CAT5221YI-00	142	CAT5270YI-50	143	CAT5419WI50	142
CAT5221YI-10	141	CAT5271ZI-00	143	CAT5419YI-00	142
CAT5221YI-25	141	CAT5271ZI-50	143	CAT5419YI-10	142
CAT5221YI-50	142	CAT5401WI-00	145	CAT5419YI-25	141
CAT5221YI00	142	CAT5401WI-10	144	CAT5419YI-50	142
CAT5221YI10	141	CAT5401WI-25	143	CAT5419YI00	142
CAT5221YI25	141	CAT5401WI-50	144	CAT5419YI10	142
CAT5221YI50	142	CAT5401WI00	145	CAT5419YI25	141
CAT5241WI-00	144	CAT5401WI10	144	CAT5419YI50	142
CAT5241WI-10	144	CAT5401WI25	143	CAT6095	313
CAT5241WI-25	143	CAT5401WI50	144	CAT660ELA	119
CAT5241WI-50	144	CAT5401YI-00	145	CAT660EVA	119

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
CAT660EVA-T3	119	CBTL3257	291	CM1233-08DE	208
CAT661ELA	119	CBTL3306	291	CM1234-08DE	208
CAT661EVA	119	CBTL383	291	CM1235-08DE	208
CAT661EVA-T3	119	CM1204-03CP	200	CM1236-08DE	208
CAT705	334	CM1205	201	CM1238-08DE	208
CAT706	334	CM1213A-01SO	203	CM1240-F4SE	200
CAT803	334	CM1213A-02SO	203	CM1241-04D4	205
CAT808N	334	CM1213A-02SR	203	CM1242-07CP	198
CAT809	334	CM1213A-04MR	203	CM1242-33CP	198
CAT810	334	CM1213A-04S7	203	CM1244-04CP	200
CAT811	334	CM1213A-04SO	203	CM1248-04QG	201
CAT812	334	CM1214A-01SO	203	CM1248-04S9	201
CAT813	334	CM1214A-02MR	203	CM1248-08DE	201
CAT823	334	CM1215-01SO	204	CM1249-04S9	202
CAT824	334	CM1215-02SO	204	CM1250-04QG	202
CAT825	334	CM1215-02SR	204	CM1263	207
CAT853	334	CM1215-04SO	204	CM1263-02SE	207
CAT859	334	CM1216-06MR	206	CM1282-01D1	203
CAT863	334	CM1216-06SM	206	CM1293A-02SO	204
CAT869	334	CM1216-08MR	206	CM1293A-02SR	204
CAT8710	334	CM1218-02S7	199	CM1293A-04MR	204
CAT885	334	CM1218-02SO	199	CM1293A-04SO	204
CAT8900B125	333	CM1218-03SR	199	CM1411	228
CAT8900B204	333	CM1218-04S7	199	CM1412	228
CAT8900B250	333	CM1218-04SE	199	CM1418-02CP	228
CAT8900C125	333	CM1218-04SO	199	CM1430-04DE	230
CAT8900C204	333	CM1218-05S7	199	CM1430-06DE	230
CAT8900C250	333	CM1218-05SE	199	CM1430-08DE	230
CAT8900D125	333	CM1218-05SO	199	CM1431-04DE	230
CAT8900D204	333	CM1218-C4SE	199	CM1431-06DE	230
CAT8900D250	333	CM1218-F4SE	199	CM1431-08DE	230
CAT93C46	264	CM1218-H4SE	199	CM1436-04DE	230
CAT93C46R	264	CM1219-02S7	200	CM1436-06DE	230
CAT93C56	264	CM1219-02SO	200	CM1436-08DE	230
CAT93C57	264	CM1219-03SR	200	CM1442-04CP	230
CAT93C66	264	CM1219-04S7	200	CM1442-06CP	230
CAT93C76	264	CM1219-04SE	200	CM1442-08CP	230
CAT93C86	264	CM1219-04SO	200	CM1443-04CP	230
CAT9532HV6I	256	CM1219-05S7	200	CM1443-06CP	230
CAT9532WI	256	CM1219-05SE	200	CM1443-08CP	230
CAT9532YI	256	CM1219-05SO	200	CM1453-04CP	231
CAT9534HV4I	256	CM1220-04CP	201	CM1457-04CP	231
CAT9534WI	256	CM1220-08CP	201	CM1457-06CP	231
CAT9534YI	256	CM1223-02SO	206	CM1457-08CP	231
CAT9552HV6I	256	CM1223-02SR	206	CM1460-04DE	231
CAT9552WI	256	CM1223-04MR	206	CM1460-06DE	231
CAT9552YI	256	CM1223-04SO	206	CM1460-08DE	231
CAT9554AHV4I	256	CM1223-08MR	206	CM1461-04DE	231
CAT9554AWI	256	CM1224-02SR	204	CM1461-08DE	231
CAT9554AYI	256	CM1224-04MR	204	CM1483-02DE	228
CAT9554HV4I	256	CM1224-04SO	204	CM1624-08DE	231
CAT9554WI	256	CM1225-04DE	205	CM1630-04DE	230
CAT9554YI	256	CM1230-02CS	207	CM1630-06DE	230
CAT9555WI	256	CM1230-04CS	207	CM1630-08DE	230
CAT9555YI	256	CM1230-08CS	207	CM1631-04DE	230
CBTL1G125	291	CM1231-02SO	208	CM1631-06DE	230

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
CM1631-08DE	230	D45C12	46	EMC5DXV5T5	71
CM1636-04DE	230	D45H11	47	EMD4DXV6T1	71
CM1636-06DE	230	D45H8	47	EMF18XV6	74
CM1636-08DE	230	D45VH10	47	EMF18XV6T5	72
CM1690-04DE	231	DA121TT1	156	EMF5XV6	74
CM1690-06DE	231	DAN222	156	EMF5XV6T5	72
CM1690-08DE	231	DAN222M3T5G	156	EMG2DXV5T5	71
CM1692-04DE	231	DAP222	156	EMT1DXV6	60
CM1692-06DE	231	DAP222M3T5G	156	EMX1DXV6T1	60
CM1692-08DE	231	DF3A6.8FU	188	EMX2DXV6T1	60
CM1693-04DE	231	DTA114EET1	68	EMZ1DXV6T1	60
CM1693-06DE	231	DTA114EM3T5G	68	ESD11A3.3DT5G	187
CM1693-08DE	231	DTA114TET1	68	ESD11A5.0DT5G	187
CM2006-02QR	210	DTA114TM3T5G	68	ESD11B5.0ST5G	183
CM2009-00QR	210	DTA114YET1	68	ESD11L5.0	193
CM2009-02QR	210	DTA114YM3T5G	68	ESD11N5.0ST5G	183
CM2020-00TR	209	DTA115EET1	68	ESD5B5.0S	185
CM2020-01TR	209	DTA115EM3T5G	68	ESD5Z12	184
CM2021-02TR	209	DTA123EM3T5G	68	ESD5Z2.5	184
CM2030-A0TR	209	DTA124EM3T5G	68	ESD5Z3.3	184
CM2031-A0TR	209	DTA124XM3T5G	68	ESD5Z5.0	184
CM6300	231	DTA143EE	68	ESD5Z6.0	184
CM6304	231	DTA143EM3T5G	68	ESD5Z7.0	184
CS3361	219	DTA143TM3T5G	68	ESD7L5.0	193
CS5101EDW16	18	DTA143ZET1	68	ESD7M5.0	193
CS51021A	8, 9, 120	DTA143ZM3T5G	68	ESD9B3.3	185
CS51022A	8, 9, 120	DTA144EET1	68	ESD9B5.0	185
CS51031	114, 118	DTA144EM3T5G	68	ESD9C3.3	186
CS51033	114, 118	DTA144TM3	68	ESD9C5.0	186
CS51221	8, 9, 120	DTA144WM3T5G	68	ESD9L3.3S	191
CS5124	8, 9, 120	DTC114EET1	68	ESD9L5.0S	191
CS51411	114, 115	DTC114EM3T5G	68	ESD9R3.3S	191
CS51412	114, 115	DTC114TET1	68	ESD9X12S	185
CS51413	114, 115	DTC114TM3T5G	68	ESD9X3.3S	185
CS51414	114, 115	DTC114YET1	68	ESD9X5.0S	185
CS5171	114, 115, 117	DTC114YM3T5G	68	ESDR0502N	195
CS5172	114, 115, 117	DTC115EET1	68	ESDR0524P	197
CS5173	114, 115, 117	DTC115EM3T5G	68	FS6128-04	105
CS5174	114, 115, 117	DTC123EM3T5G	68	FS6128-07	105
CS5253	127	DTC123JET1	68	FS6131	105
CS5253B	127	DTC123JM3T5G	68	FS6370	105
CS5253B-1	125	DTC124EET1	68	FS6377	105
CS5253B-8	124	DTC124EM3T5G	68	FS7140	105
CS8101	129, 130	DTC124XET1	68	FS7145	105
CS8126	129, 132	DTC124XM3T5G	68	HN1B01FDW1	60
CS8129	129, 132	DTC143EET1	68	HN1B01FDW1T1	66
CS8151	129, 130	DTC143EM3T5G	68	HN2D02FUTW1T1	156
CS8182	129, 131	DTC143TM3T5G	68	I2T100	110
CS8183	129	DTC143ZET1	68	I2T30, (E)	110
CS8190	219	DTC143ZM3T5G	68	I3T25	110
CS8361	129, 132	DTC144EET1	68	I3T50	110
CS8363	129	DTC144EM3T5G	68	I3T80	110
D44C12	46	DTC144TM3T5G	68	IMH20TR1	70
D44H11	47	DTC144WM3T5G	68	J112	237
D44H8	47	EMC3DXV5T5	71	J310	237
D44VH10	47	EMC4DXV5T5	71	JLC1562BF	256

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
JLC1562BN	256	LP2950CAC	124	MAC15N	323
L4949	124	LP2951AC	125	MAC15SD	323
LM201A	22	LP2951C	124, 125	MAC15SM	323
LM201AV	22	LP2951CAC	124	MAC15SN	323
LM211	28	M1MA141KT1	155	MAC16CM	324
LM224	26	M1MA141WAT1	155	MAC16CN	324
LM239	29	M1MA142WAT1	155	MAC16D	324
LM2574	114, 115	M1MA142WKT1	155	MAC16HCD	324
LM2575	114, 115	M1MA151KT1	155	MAC16HCM	324
LM2576	114, 115	M1MA151WAT1	155	MAC16HCN	324
LM258	24	M1MA151WKT1	155	MAC16M	324
LM2594	114, 116	M1MA152KT1	155	MAC16N	324
LM2595	114, 116	M1MA152WAT1	155	MAC210A10	323
LM2596	114, 116	M1MA152WKT1	155	MAC210A8	323
LM285D-1.2	333	M74HCT4051A	38	MAC212A10	323
LM285D-2.5	333	M74HCT4052A	38	MAC212A8	323
LM285Z-1.2	333	M74HCT4053A	38	MAC228A10	322
LM285Z-2.5	333	M74HCT4851A	38	MAC228A4	322
LM2901	29	M74LCX16240	287	MAC228A6	322
LM2902	26	M74LCX16244	287	MAC228A8	322
LM2902V	26	M74LCX16245	306	MAC4DCM	321
LM2903	28	M74LCX16373	297	MAC4DCM-1	321
LM2904	24	M74LCX16374	292	MAC4DCN	321
LM293	28	M74VHC1G125	290	MAC4DCN-1	321
LM2931	124	M74VHC1G126	289	MAC4DHM	321
LM2931A	124	M74VHC1G132	302	MAC4DHM-1	321
LM2931AC	125	M74VHC1G135	302	MAC4DLM	321
LM2931C	125	M74VHC1GT00	302	MAC4DLM-1	321
LM301A	22	M74VHC1GT02	302	MAC4DSM	321
LM311	28	M74VHC1GT04	295	MAC4DSMT-1	321
LM317	123	M74VHC1GT08	302	MAC4DSN	321
LM317L	123	M74VHC1GT125	290	MAC4DSN-1	321
LM317M	123	M74VHC1GT126	289	MAC8D	322
LM324	26	M74VHC1GT14	295	MAC8M	322
LM337	123	M74VHC1GT32	303	MAC8N	322
LM339	29	M74VHC1GT50	290	MAC8SD	322
LM350	123	M74VHC1GT86	302	MAC8SM	322
LM358	24	M74VHC1GU04	295	MAC8SN	322
LM385BD-1.2	333	M74VHCT126A	289	MAC97A4	321
LM385BD-2.5	333	M74VHCT157A	305	MAC97A6	321
LM385BZ-1.2	333	M74VHCT257A	305	MAC97A8	321
LM385BZ-2.5	333	MA3075WAL	187	MAC997A6	321
LM385D-1.2	333	MAC08B	321	MAC997A8	321
LM385D-2.5	333	MAC08M	321	MAC997B6	321
LM385Z-1.2	333	MAC12D	323	MAC997B8	321
LM385Z-2.5	333	MAC12HCD	323	MAC9D	322
LM393	28	MAC12HCM	323	MAC9M	322
LM833	24	MAC12HCN	323	MAC9N	322
LMV321	22	MAC12M	323	MAX1720EU	114
LMV324	26	MAC12N	323	MAX1720EUTG	119
LMV331	28	MAC12SM	323	MAX708	334
LMV339	29	MAC12SN	323	MAX803	334
LMV358	24	MAC15A10	323	MAX809	334
LMV393	28	MAC15A6	323	MAX810	334
LMV931	22	MAC15A8	323	MBD301	151
LP2950C	124	MAC15M	323	MBD330DWT1	152

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MBD54DWT1	152	MBR30H80CT	276	MBRB30H60CT-1	277
MBD770DWT1	152	MBR30L45CT	270, 276	MBRB30H60CT-1G	270
MBR0520L	270, 272	MBR30L60CT	276	MBRB30H80CT-1	277
MBR0530	272	MBR3100	275	MBRB4030	274
MBR0540	272	MBR340	275	MBRB41H100CT	270, 274
MBR10100	277	MBR350	275	MBRB41H100CT-1	277
MBR1035	277	MBR360	275	MBRB41H100CT-1G	270
MBR1045	277	MBR4015CTL	276	MBRB60H100CT	270, 274
MBR1060	277	MBR4015LWT	278	MBRB8H100	270, 274
MBR1080	277	MBR4015WT	270	MBRD1035CTL	270, 274
MBR1090	277	MBR40250	271, 277	MBRD1045	274
MBR10H100CT	276	MBR40250T	271, 276	MBRD320	274
MBR10H100CTG	270	MBR4045PT	278	MBRD330	274
MBR10L60CT	276	MBR4045WT	278	MBRD340	274
MBR1100	275	MBR40H100WT	278	MBRD350	274
MBR120ESF	271, 272	MBR40H100WTG	270	MBRD360	274
MBR120LSF	270, 272	MBR40L45CT	270, 276	MBRD5H100	270, 274
MBR120VLSF	270, 272	MBR40L60CT	276	MBRD620CT	274
MBR130	272	MBR41H100CT	276	MBRD630CT	274
MBR130LSF	270, 272	MBR41H100CTG	270	MBRD640CT	274
MBR140SF	272	MBR6045PT	278	MBRD650CT	274
MBR150	275	MBR6045WT	278	MBRD660CT	274
MBR1535CT	276	MBR60H100CT	276	MBRD835L	270, 274
MBR1545CT	276	MBR60H100CTG	270	MBRF10H150CT	277
MBR160	275	MBR60L45CT	270, 276	MBRF10L60CT	277
MBR16100CT	276	MBR60L45WT	270, 278	MBRF20100CT	277
MBR1635	277	MBR7030WT	278	MBRF20200CT	271, 277
MBR1645	277	MBR735	277	MBRF2045CT	270, 277
MBR1H100SF	272	MBR745	277	MBRF2060CT	277
MBR20100CT	276	MBRA120E	271, 272	MBRF20H100CT	270, 277
MBR20200CT	271, 276	MBRA130L	272	MBRF20H150CT	270, 277
MBR2030CTL	270, 276	MBRA140	272	MBRF20L45CT	270, 277
MBR2045CT	276	MBRA160	272	MBRF20L60CT	277
MBR2060CT	276	MBRA1H100	272	MBRF20L80CT	277
MBR2080CT	276	MBRA210E	271, 272	MBRF2545CT	270, 277
MBR2090CT	276	MBRA210L	270, 272	MBRF30H100CT	270, 277
MBR20H100CT	276	MBRA2H100	272	MBRF30H150CT	270, 277
MBR20H100CTG	270	MBRA320	270, 272	MBRF30H60CT	277
MBR20H150CT	270	MBRA340	272	MBRF30H60CTG	270
MBR20L45CT	270, 276	MBRB1045	274	MBRF30L45CT	270, 277
MBR20L60CT	276	MBRB1545CT	274	MBRF30L60CT	277
MBR20L80CT	276	MBRB1645	274	MBRF40250T	271, 277
MBR230LSF	272	MBRB20100CT	274	MBRM110E	271, 272
MBR2515L	270, 277	MBRB20200CT	271, 274	MBRM110L	270, 272
MBR2535CT	270, 276	MBRB2060CT	274	MBRM120E	271, 272
MBR2535CTL	270, 276	MBRB20H100CT	270, 274	MBRM120L	272
MBR2545CT	276	MBRB2515L	270, 274	MBRM130L	272
MBR2H100SF	272	MBRB2535CTL	270, 274	MBRM140	272
MBR3045PT	278	MBRB2545CT	274	MBRM1H100	272
MBR3045ST	270, 276	MBRB3030CT	274	MBRM2H100	272
MBR3045WT	278	MBRB3030CTL	270, 274	MBRS1100	273
MBR30H100CT	276	MBRB3045CT-1	277	MBRS120	273
MBR30H100CTG	270	MBRB3045CT-1G	270	MBRS130	273
MBR30H150CT	276	MBRB30H30CT-1	277	MBRS130L	270, 273
MBR30H30CT	270, 276	MBRB30H30CT-1G	270	MBRS140	273
MBR30H60CT	270, 276	MBRB30H60CT	270, 274	MBRS1540	273

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MBRS190	273	MC100E457	89	MC100EP16VS	91
MBRS2040L	273	MC100EL01	87	MC100EP16VT	91
MBRS230L	270, 273	MC100EL04	87	MC100EP17	92
MBRS240L	273	MC100EL05	87	MC100EP195	93
MBRS260	273	MC100EL07	88	MC100EP195B	93
MBRS2H100	270, 273	MC100EL11	83	MC100EP196	93
MBRS3100	273	MC100EL12	81	MC100EP196B	93
MBRS320	273	MC100EL13	83	MC100EP210S	82
MBRS3200	271, 273	MC100EL14	82	MC100EP29	84
MBRS3201	271, 273	MC100EL15	82	MC100EP31	84
MBRS330	273	MC100EL16	91	MC100EP32	79
MBRS340	273	MC100EL1648	105	MC100EP33	79
MBRS360	273	MC100EL17	92	MC100EP35	85
MBRS410E	271, 273	MC100EL29	84	MC100EP40	101
MBRS410L	270, 273	MC100EL30	84	MC100EP445	93
MBRS4201	271, 273	MC100EL31	84	MC100EP446	93
MBRS540	273	MC100EL32	79	MC100EP451	86
MBT2222ADW1T1	60, 66	MC100EL33	79	MC100EP51	84
MBT35200M	59	MC100EL34	79	MC100EP52	85
MBT3904DW1T1	60, 66	MC100EL35	85	MC100EP56	89
MBT3906DW1T1	60, 66	MC100EL38	79	MC100EP57	90
MBT3946DW1T1	60, 66	MC100EL39	79	MC100EP58	89
MBT6429DW1T1	60	MC100EL51	84	MC100EP809	81
MC100E016	78	MC100EL52	85	MC100EP90	94
MC100E101	87	MC100EL56	89	MC100EP91	94
MC100E104	87	MC100EL57	90	MC100EPT20	94
MC100E107	88	MC100EL58	89	MC100EPT21	94
MC100E111	81	MC100EL59	89	MC100EPT22	94
MC100E112	81	MC100EL90	94	MC100EPT23	94
MC100E116	92	MC100EL91	94	MC100EPT24	94
MC100E131	85	MC100ELT20	94	MC100EPT25	94
MC100E136	78	MC100ELT21	94	MC100EPT26	94
MC100E137	78	MC100ELT22	94	MC100EPT622	95
MC100E142	86	MC100ELT23	94	MC100H600	95
MC100E143	86	MC100ELT24	94	MC100H601	95
MC100E150	86	MC100ELT25	94	MC100H602	95
MC100E151	86	MC100ELT28	94	MC100H603	95
MC100E157	89	MC100EP01	87	MC100H604	95
MC100E158	89	MC100EP016A	78	MC100H605	95
MC100E163	90	MC100EP05	87	MC100H606	95
MC100E164	90	MC100EP08	88	MC100H607	95
MC100E171	90	MC100EP101	88	MC100H640	82
MC100E175	86	MC100EP105	87	MC100H641	81, 82
MC100E195	93	MC100EP11	83	MC100H642	82
MC100E196	93	MC100EP116	92	MC100H643	82
MC100E210	81	MC100EP131	85	MC100H646	82
MC100E211	82	MC100EP139	79	MC100H680	92
MC100E241	86	MC100EP14	82	MC100LVE111	81
MC100E310	82	MC100EP140	101	MC100LVE164	90
MC100E404	87	MC100EP142	86	MC100LVE210	81
MC100E416	92	MC100EP16	91	MC100LVE222	81
MC100E431	85	MC100EP16F	91	MC100LVE310	82
MC100E445	93	MC100EP16T	91	MC100LVEL01	88
MC100E446	93	MC100EP16VA	91	MC100LVEL05	87
MC100E451	86	MC100EP16VB	91	MC100LVEL11	83
MC100E452	86	MC100EP16VC	91	MC100LVEL12	81

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MC100LVEL13	83	MC10E171	90	MC10EP33	79
MC100LVEL14	82	MC10E175	86	MC10EP35	85
MC100LVEL16	91	MC10E195	93	MC10EP445	93
MC100LVEL17	92	MC10E196	93	MC10EP446	93
MC100LVEL29	84	MC10E211	82	MC10EP451	86
MC100LVEL30	84	MC10E404	87	MC10EP51	84
MC100LVEL31	84	MC10E411	82	MC10EP52	85
MC100LVEL32	79	MC10E416	92	MC10EP56	89
MC100LVEL33	79	MC10E431	85	MC10EP57	90
MC100LVEL34	79	MC10E445	93	MC10EP58	89
MC100LVEL37	79	MC10E446	93	MC10EP89	91
MC100LVEL38	79	MC10E451	86	MC10EP90	95
MC100LVEL39	79	MC10E452	86	MC10EPT20	94
MC100LVEL40	101	MC10E457	89	MC10H016	78
MC100LVEL51	84	MC10EL01	88	MC10H100	87
MC100LVEL56	89	MC10EL04	87	MC10H101	88
MC100LVEL58	89	MC10EL05	87	MC10H102	87
MC100LVEL59	89	MC10EL07	88	MC10H103	87
MC100LVEL90	95	MC10EL11	83	MC10H104	87
MC100LVEL91	95	MC10EL12	81	MC10H105	88
MC100LVEL92	95	MC10EL15	82	MC10H106	87
MC100LVELT20	94	MC10EL16	91	MC10H107	88
MC100LVELT22	94	MC10EL31	84	MC10H109	88
MC100LVELT23	94	MC10EL32	79	MC10H113	88
MC100LVPEP05	87	MC10EL33	79	MC10H115	92
MC100LVPEP11	83	MC10EL34	79	MC10H116	92
MC100LVPEP111	81	MC10EL35	85	MC10H117	88
MC100LVPEP14	82	MC10EL51	84	MC10H121	88
MC100LVPEP16	91	MC10EL52	85	MC10H123	81
MC100LVPEP210	82	MC10EL57	90	MC10H124	95
MC100LVPEP34	79	MC10EL58	89	MC10H125	95
MC10E016	78	MC10EL89	91	MC10H130	86
MC10E101	88	MC10ELT20	94	MC10H131	85
MC10E104	87	MC10ELT21	94	MC10H135	85
MC10E107	88	MC10ELT22	94	MC10H136	78
MC10E111	82	MC10ELT24	94	MC10H141	86
MC10E112	81	MC10ELT28	94	MC10H158	89
MC10E116	92	MC10EP01	88	MC10H159	89
MC10E122	81	MC10EP016	78	MC10H161	90
MC10E131	85	MC10EP05	87	MC10H162	90
MC10E136	78	MC10EP08	88	MC10H164	90
MC10E137	78	MC10EP101	88	MC10H165	90
MC10E141	86	MC10EP105	87	MC10H166	80
MC10E142	86	MC10EP11	83	MC10H171	90
MC10E143	86	MC10EP116	92	MC10H172	90
MC10E150	86	MC10EP131	85	MC10H174	90
MC10E151	86	MC10EP139	79	MC10H175	86
MC10E154	89	MC10EP142	86	MC10H176	85
MC10E155	89	MC10EP16	91	MC10H180	78
MC10E156	90	MC10EP16T	91	MC10H186	85
MC10E157	89	MC10EP16VA	91	MC10H188	81
MC10E158	89	MC10EP17	92	MC10H189	81
MC10E163	90	MC10EP195	93	MC10H209	88
MC10E164	90	MC10EP29	84	MC10H210	87
MC10E166	80	MC10EP31	84	MC10H211	87
MC10E167	89	MC10EP32	79	MC10H330	92

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MC10H332	92	MC14046B	105	MC14598B	297
MC10H334	92	MC14049B	294	MC1488D	255
MC10H350	95	MC14049UB	294	MC1488M	255
MC10H351	95	MC14050B	294	MC1488P	255
MC10H352	95	MC14051B	37	MC1489AD	255
MC10H424	95	MC14052B	37	MC1489AM	255
MC10H600	95	MC14053B	37	MC1489AP	255
MC10H601	95	MC14060B	286	MC1489D	255
MC10H602	95	MC14066B	37	MC1489M	255
MC10H603	95	MC14067B	37	MC1489P	255
MC10H604	95	MC14069UB	294	MC1496	256
MC10H605	95	MC14070B	301	MC1496B	256
MC10H606	95	MC14071B	301	MC26LS30D	255
MC10H607	95	MC14073B	303	MC3302	29
MC10H640	82	MC14076B	297	MC33023	8, 9
MC10H641	82	MC14077B	301	MC33025	8, 12, 120
MC10H642	82	MC14081B	300	MC3303	26
MC10H643	82	MC14082B	299	MC33030	219
MC10H645	82	MC14093B	300	MC33033	219
MC10H646	82	MC14094B	297	MC33035	219
MC10H680	92	MC14099B	297	MC33039	219
MC10LVPEP11	83	MC14106B	295	MC33060A	8, 9, 120
MC10LVPEP16	91	MC1413BD	217	MC33063	114, 117
MC10SX1130	91	MC1413BP	217	MC33064	334
MC10SX1189	91	MC1413D	217	MC33067	8, 11
MC10SX1190	91	MC1413P	217	MC33071	22
MC12026A	80	MC14174B	292	MC33072	24
MC12080	80	MC14175B	293	MC33074	26
MC12093	80	MC14490	286	MC33077	24
MC12095	80	MC14503B	287	MC33078	24
MC14001B	301	MC14504B	308	MC33079	26
MC14001UB	301	MC14511B	287	MC33151	218
MC14007UB	294	MC14512B	304	MC33152	218
MC14008B	286	MC14513B	287	MC33153	218
MC14011B	300	MC14514B	304	MC33160	123
MC14011UB	300	MC14515B	304	MC33161	334
MC14012B	299	MC14516B	286	MC33163	117
MC14013B	292	MC14517B	297	MC33164	334
MC14014B	297	MC14518B	286	MC33166	114, 115, 117
MC14015B	297	MC14520B	286	MC33167	114, 115, 117
MC14016B	37	MC14521B	286	MC33171	22
MC14017B	286	MC14526B	286	MC33172	24
MC14018B	286	MC14528B	305	MC33172V	24
MC14020B	286	MC14532B	304	MC33174	26
MC14021B	297	MC14538B	305	MC33174V	26
MC14022B	286	MC14543B	287	MC33178	24
MC14023B	303	MC14549B	298	MC33179	26
MC14024B	286	MC14551B	37	MC33201	22
MC14025B	303	MC14553B	286	MC33202	25
MC14027B	292	MC14555B	305	MC33204	27
MC14028B	304	MC14556B	305	MC33204V	27
MC14029B	286	MC14557B	297	MC33262	16, 17
MC14040B	286	MC14569B	286	MC33269,	124, 125, 126
MC14042B	298	MC14572UB	294	MC33272A	25
MC14043B	298	MC14584B	295	MC33274A	27
MC14044B	298	MC14585B	286	MC33275	124, 126

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MC33341	132	MC74AC245	306	MC74HC02A	301
MC33363	14, 15	MC74AC257	305	MC74HC03A	300
MC33364	11	MC74AC259DG	297	MC74HC04A	294
MC33364	8	MC74AC273	292	MC74HC05A	294
MC33368	16, 17	MC74AC32	301	MC74HC08A	300
MC33375	124, 126	MC74AC373	298	MC74HC10A	303
MC33501	22	MC74AC374	292	MC74HC112A	292
MC33502	25	MC74AC377	293	MC74HC11A	303
MC33503	22	MC74AC4040D	286	MC74HC123A	305
MC33565	123	MC74AC540	288	MC74HC125A	289
MC33567	125, 128	MC74AC541	288	MC74HC126A	289
MC33761	124	MC74AC573	298	MC74HC132A	300
MC33762	125, 128	MC74AC574	292	MC74HC138A	304
MC33765	125, 128	MC74AC646	306	MC74HC139A	304
MC34023	8, 9	MC74AC652	306	MC74HC14A	295
MC34025	8, 12, 120	MC74AC74	292	MC74HC151A	304
MC3403	27	MC74AC86	300	MC74HC153A	305
MC34060A	8, 9, 120	MC74ACT00	300	MC74HC157A	304
MC34063	114, 117	MC74ACT02	301	MC74HC161A	286
MC34064	334	MC74ACT04	294	MC74HC163A	286
MC34067	8, 11	MC74ACT05	294	MC74HC164A	297
MC34071	23	MC74ACT08	300	MC74HC165A	297
MC34072	25	MC74ACT10	303	MC74HC174A	292
MC34074	27	MC74ACT11	303	MC74HC175A	293
MC34074A	27	MC74ACT125	289	MC74HC1G00	302
MC34074V	27	MC74ACT132	301	MC74HC1G02	302
MC34151	218	MC74ACT138	304	MC74HC1G04	295
MC34152	218	MC74ACT139	305	MC74HC1G08	302
MC34160	123	MC74ACT14	294	MC74HC1G14	295
MC34161	334	MC74ACT153	305	MC74HC1G32	302
MC34163	114, 117	MC74ACT157	305	MC74HC1GU04	296
MC34164	334	MC74ACT161	286	MC74HC20A	299
MC34166	114, 115, 117	MC74ACT163	286	MC74HC238A	304
MC34167	114, 115, 117	MC74ACT20	299	MC74HC240A	288
MC34262	16, 17	MC74ACT240	288	MC74HC244A	288
MC34268	124, 126	MC74ACT241	288	MC74HC245A	306
MC3488AD	255	MC74ACT245	306	MC74HC251A	304
MC3488AP1	255	MC74ACT253	305	MC74HC259A	297
MC74AC00	300	MC74ACT257	305	MC74HC273A	292
MC74AC02	301	MC74ACT259	297	MC74HC30A	303
MC74AC04	294	MC74ACT273	293	MC74HC32A	301
MC74AC05	294	MC74ACT32	301	MC74HC365A	287
MC74AC08	300	MC74ACT373	298	MC74HC367A	287
MC74AC10	303	MC74ACT374	293	MC74HC368A	287
MC74AC11	303	MC74ACT377	293	MC74HC373A	298
MC74AC125	289	MC74ACT540	288	MC74HC374A	292
MC74AC132	300	MC74ACT541	288	MC74HC377A	293
MC74AC138	304	MC74ACT564	298	MC74HC390A	286
MC74AC139	304	MC74ACT573	298	MC74HC4020A	286
MC74AC14	294	MC74ACT574	293	MC74HC4040A	286
MC74AC157	305	MC74ACT640	306	MC74HC4046A	105
MC74AC161	286	MC74ACT646	306	MC74HC4051A	37
MC74AC163	286	MC74ACT652	306	MC74HC4052A	37
MC74AC20	299	MC74ACT74	292	MC74HC4053A	38
MC74AC240	287	MC74ACT86	300	MC74HC4060A	286
MC74AC244	287	MC74HC00A	300	MC74HC4066A	38

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MC74HC4067A	37, 304	MC74LCX16244	287	MC74LVXT4066	38
MC74HC4094A	297	MC74LCX16245	306	MC74LVXT8051	38
MC74HC4316A	38	MC74LCX16373	297	MC74LVXT8053	38
MC74HC4538A	305	MC74LCX16374	292	MC74LVXU04	294
MC74HC4851A	38	MC74LCX240	288	MC74VHC00	300
MC74HC4852	38	MC74LCX244	288	MC74VHC02	301
MC74HC540A	288	MC74LCX245	306	MC74VHC04	294
MC74HC541A	288	MC74LCX257	305	MC74VHC08	300
MC74HC573A	298	MC74LCX258	305	MC74VHC125	289
MC74HC574A	292	MC74LCX32	301	MC74VHC126	289
MC74HC589A	297	MC74LCX373	298	MC74VHC132	301
MC74HC595A	298	MC74LCX374	292	MC74VHC138	304
MC74HC597A	297	MC74LCX540	288	MC74VHC139	305
MC74HC73A	292	MC74LCX541	288	MC74VHC14	295
MC74HC74A	292	MC74LCX573	298	MC74VHC157	304
MC74HC86A	300	MC74LCX574	292	MC74VHC1G00	302
MC74HCT04A	295	MC74LCX74	292	MC74VHC1G01	302
MC74HCT08A	300	MC74LCX86	301	MC74VHC1G02	302
MC74HCT125A	289	MC74LCXU04	296	MC74VHC1G03	302
MC74HCT132A	300	MC74LVX00	300	MC74VHC1G04	295
MC74HCT138A	304	MC74LVX02	301	MC74VHC1G05	295
MC74HCT14A	295	MC74LVX04	294	MC74VHC1G07	290
MC74HCT20A	299	MC74LVX08	300	MC74VHC1G08	302
MC74HCT241A	288	MC74LVX125	289	MC74VHC1G09	302
MC74HCT244A	288	MC74LVX126	289	MC74VHC1G125	290
MC74HCT245A	306	MC74LVX132	301	MC74VHC1G126	289
MC74HCT259A	297	MC74LVX138	304	MC74VHC1G132	302
MC74HCT273A	293	MC74LVX139	305	MC74VHC1G14	295
MC74HCT32A	301	MC74LVX14	295	MC74VHC1G32	303
MC74HCT365A	287	MC74LVX157	305	MC74VHC1G50	289
MC74HCT366A	287	MC74LVX240	288	MC74VHC1G66	38
MC74HCT373A	298	MC74LVX244	288	MC74VHC1G86	302
MC74HCT374A	293	MC74LVX245	306	MC74VHC1GT00	302
MC74HCT4094A	297	MC74LVX257	289	MC74VHC1GT02	302
MC74HCT4851A	38	MC74LVX259	297	MC74VHC1GT04	295
MC74HCT4852A	38	MC74LVX32	301	MC74VHC1GT08	302
MC74HCT541A	288	MC74LVX373	298	MC74VHC1GT125	290
MC74HCT573A	297	MC74LVX374	292	MC74VHC1GT14	295
MC74HCT574A	293	MC74LVX4051	304	MC74VHC1GT50	290
MC74HCT595A	297	MC74LVX4052	304	MC74VHC1GT66	38
MC74HCT74A	292	MC74LVX4053	304	MC74VHC1GT86	302
MC74HCT86A	300	MC74LVX4066	38	MC74VHC1GU04	296
MC74HCU04A	295	MC74LVX4245	306, 308	MC74VHC240	288
MC74LCX00	300	MC74LVX50	287	MC74VHC244	289
MC74LCX02	301	MC74LVX540	288	MC74VHC245	306
MC74LCX04	294	MC74LVX541	288	MC74VHC257	289
MC74LCX06	294	MC74LVX573	298	MC74VHC259	297
MC74LCX07	287	MC74LVX574	292	MC74VHC32	301
MC74LCX08	300	MC74LVX74	292	MC74VHC373	298
MC74LCX125	289	MC74LVX8051	38	MC74VHC374	292
MC74LCX138	304	MC74LVX8053	38	MC74VHC4051	38
MC74LCX139	305	MC74LVX86	301	MC74VHC4052	304
MC74LCX14	295	MC74LVXC3245	306	MC74VHC4053	304
MC74LCX157	305	MC74LVXT4051	304	MC74VHC4066	38
MC74LCX158	305	MC74LVXT4052	304	MC74VHC4316	305
MC74LCX16240	287	MC74LVXT4053	304	MC74VHC50	287

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MC74VHC540	288	MCR100-8	318	MJ11032	51
MC74VHC541	288	MCR106-6	318	MJ11033	51
MC74VHC573	297	MCR106-8	318	MJ14002	49
MC74VHC574	292	MCR12D	319	MJ15001	48
MC74VHC595	297, 298	MCR12DCM	319	MJ15002	48
MC74VHC74	293	MCR12DCN	319	MJ15003	49, 52
MC74VHC86	300	MCR12DSM	319	MJ15004	49, 52
MC74VHCT00A	300	MCR12DSN	319	MJ15015	48, 52
MC74VHCT02A	301	MCR12DSN-001	319	MJ15016	48, 52
MC74VHCT04A	295	MCR12LD	319	MJ15023	49
MC74VHCT08A	301	MCR12LM	319	MJ15024	49, 53
MC74VHCT125A	289	MCR12LN	319	MJ15025	49, 53
MC74VHCT126A	289	MCR12M	319	MJ21193	49, 53
MC74VHCT132A	301	MCR12N	319	MJ21194	49, 53
MC74VHCT138A	304	MCR16N	320	MJ21195	49
MC74VHCT139A	305	MCR218-2	319	MJ21196	49
MC74VHCT14A	295	MCR218-4	319	MJ2955	48
MC74VHCT157A	305	MCR218-6	319	MJ4502	49
MC74VHCT240A	288	MCR22-6	318	MJ802	49
MC74VHCT244	288	MCR22-8	318	MJB41CT4	45
MC74VHCT245A	306	MCR25D	320	MJB42CT4	45
MC74VHCT257A	289	MCR25M	320	MJB44H11T4	45
MC74VHCT259A	297	MCR25N	320	MJB45H11T4	45
MC74VHCT32A	301	MCR310-10	319	MJD112T4	50
MC74VHCT373A	298	MCR68-2	319	MJD117T4	50
MC74VHCT374A	293	MCR69-2	320	MJD122T4	50
MC74VHCT50A	287	MCR69-3	320	MJD127T4	50
MC74VHCT540A	288	MCR703A	318	MJD148T4	45
MC74VHCT541A	288	MCR706A	318	MJD200T4	45
MC74VHCT573A	298	MCR708A	318	MJD210T4	45
MC74VHCT574A	293	MCR708A1	318	MJD243T4	45
MC74VHCT74A	292	MCR716	318	MJD253T4	45
MC74VHCT86A	301	MCR718	318	MJD2955T4	45
MC74VHCU04	295	MCR72-3	319	MJD3055T4	45
MC75172BDW	255	MCR72-6	319	MJD31CT4	45
MC75174BDW	255	MCR72-8	319	MJD31T4	45
MC75174BP	255	MCR8DCMT4	319	MJD32CT4	45
MC78FCxx	124	MCR8DCNT4	319	MJD32T4	45
MC78LCxx	124	MCR8DSMT4	319	MJD340T4	45
MC78LxxA	123	MCR8DSNT4	319	MJD350T4	45
MC78Mxx	123	MCR8N	319	MJD41CT4	45
MC78MxxA	123	MCR8SD	319	MJD42CT4	45
MC78PC	124	MCR8SM	319	MJD44E3T4	50
MC78xx	123	MCR8SN	319	MJD44H11T4	45
MC78xxA	123	MDC3105	217	MJD45H11T4	45
MC79LxxA	123	MDC3105D	217	MJD47T4	45
MC79Mxx	123	MGSF1N02L	241	MJD50T4	45
MC79xx	123	MGSF1N03L	241	MJD5731T4	45
MC79xxA	123	MGSF2N02EL	241	MJD6039T4	50
MCH12140	101	MJ11012	51	MJE13005	46
MCK12140	101	MJ11015	51	MJE13007	47
MCR08B	318	MJ11016	51	MJE13009	47
MCR08M	318	MJ11021	51	MJE15028	47
MCR100-3	318	MJ11022	51	MJE15029	47
MCR100-4	318	MJ11028	51	MJE15030	47, 52
MCR100-6	318	MJ11030	51	MJE15031	47, 52

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MJE15032	47, 52	MJH11017	51	MM3Z39V	159
MJE15033	47, 52	MJH11019	51	MM3Z3V0	159
MJE15034	46, 52	MJH11020	51	MM3Z3V3	159
MJE15035	46, 52	MJH11021	51	MM3Z3V3S	159
MJE170	45	MJH11022	51	MM3Z3V6	159
MJE171	45	MJH6284	51	MM3Z3V9	159
MJE172	45	MJH6287	51	MM3Z3V9S	159
MJE180	45	MJL1302A	48, 52	MM3Z43V	159
MJE18002	46, 54	MJL21193	48, 52	MM3Z4V3	159
MJE18004	46, 54	MJL21194	48, 52	MM3Z4V3S	159
MJE18006	47, 54	MJL21195	48, 52	MM3Z4V7	159
MJE18008	47, 54	MJL21196	48, 52	MM3Z4V7S	159
MJE181	45	MJL3281A	48, 52	MM3Z5V1	159
MJE182	45	MJL4281A	48, 53	MM3Z5V1S	159
MJE200	46	MJL4302A	48, 53	MM3Z5V6	159
MJE210	46	MJW0281A	48, 52	MM3Z5V6S	159
MJE243	46	MJW0302A	48, 52	MM3Z6V2	159
MJE253	46	MJW1302A	48, 53	MM3Z6V2S	159
MJE270	50	MJW18020	48	MM3Z6V8	159
MJE271	50	MJW21191	48, 52	MM3Z6V8S	159
MJE2955T	47	MJW21192	48, 52	MM3Z7V5	159
MJE3055T	47	MJW21193	48, 52	MM3Z7V5S	159
MJE340	45	MJW21194	48, 52	MM3Z8V2	159
MJE3439	45	MJW21195	48, 52	MM3Z8V2S	159
MJE344	45	MJW21196	48, 52	MM3Z9V1	159
MJE350	45	MJW3281A	48, 53	MM3Z9V1S	159
MJE371	46	MKP1V120	328	MM5Z10V	159
MJE4343	48	MKP1V130	328	MM5Z12V	159
MJE4353	48	MKP1V160	328	MM5Z15V	159
MJE5730	46	MKP1V240	328	MM5Z16V	159
MJE5731	46	MKP3V120	328	MM5Z18V	159
MJE5731A	46	MKP3V240	328	MM5Z20V	159
MJE5742	50	MLD1N06CL	247, 250	MM5Z24V	159
MJE5850	47	MLD2N06CL	247	MM5Z27V	159
MJE5851	47	MM3Z10V	159	MM5Z2V4	159
MJE5852	47	MM3Z10VS	159	MM5Z2V4S	159
MJE700	50	MM3Z11V	159	MM5Z2V7	159
MJE702	50	MM3Z12V	159	MM5Z30V	159
MJE703	50	MM3Z12VS	159	MM5Z36V	159
MJE800	50	MM3Z13V	159	MM5Z3V0	159
MJE802	50	MM3Z15V	159	MM5Z3V3	159
MJE803	50	MM3Z15V5	159	MM5Z3V6	159
MJF122	51	MM3Z16V	159	MM5Z4V7	159
MJF127	51	MM3Z16VS	159	MM5Z4V7S	159
MJF15030	48	MM3Z18V	159	MM5Z5V1	159
MJF15031	48	MM3Z18VS	159	MM5Z5V1S	159
MJF18004	48, 54	MM3Z20V	159	MM5Z5V6	159
MJF18008	48, 54	MM3Z22V	159	MM5Z5V6S	159
MJF2955	48	MM3Z22VS	159	MM5Z6V2	159
MJF3055	48	MM3Z24V	159	MM5Z6V2S	159
MJF31C	48	MM3Z27V	159	MM5Z6V8	159
MJF32C	48	MM3Z27VS	159	MM5Z6V8S	159
MJF44H11	48	MM3Z2V4	159	MM5Z7V5	159
MJF45H11	48	MM3Z2V7	159	MM5Z8V2	159
MJF47	48	MM3Z33VS	159	MM5Z8V2S	159
MJF6388	51	MM3Z36V	159	MM5Z9V1	159

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MM5Z9V1S	159	MMBT4401M3	58	MMBZ5223BL	160
MMBD101LT1	151	MMBT4401WT1	58, 66	MMBZ5225BL	160
MMBD2835LT1	155	MMBT4403LT1	57, 63, 65	MMBZ5226BL	160
MMBD2836LT1	155	MMBT4403M3	58	MMBZ5227BL	160
MMBD2837LT1	155	MMBT4403WT1	58, 66	MMBZ5228BL	160
MMBD2838LT1	155	MMBT489L	57	MMBZ5229BL	160
MMBD301LT1	151	MMBT5087LT1	56, 61	MMBZ5230BL	160
MMBD301M3	153	MMBT5088LT1	57, 61	MMBZ5231BL	160
MMBD330T1	152	MMBT5089LT1	57, 61	MMBZ5231EL	160
MMBD352LT1	151	MMBT5401LT1	64	MMBZ5232BL	160
MMBD352WT1	152	MMBT5550L	56	MMBZ5232EL	160
MMBD353LT1	151	MMBT5550LT1	63, 64	MMBZ5233BL	160
MMBD354LT1	151	MMBT5551LT1	64	MMBZ5234BL	160
MMBD355LT1	151	MMBT5551M3	58	MMBZ5234EL	160
MMBD452LT1	151	MMBT589L	57	MMBZ5235BL	160
MMBD6050LT1	155	MMBT6427LT1	61	MMBZ5236BL	160
MMBD6100LT1	155	MMBT6428LT1	56, 61	MMBZ5237BL	160
MMBD7000LT1	155	MMBT6429LT1	56, 61	MMBZ5237EL	160
MMBD701LT1	151	MMBT6517LT1	64	MMBZ5238BL	160
MMBD717LT1	152	MMBT6520LT1	64	MMBZ5239BL	160
MMBD770T1	152	MMBT6521L	57	MMBZ5239EL	160
MMBD914LT1	155	MMBT8099LT1	56, 63	MMBZ5240BL	160
MMBF0201NL	241	MMBT918LT1	65	MMBZ5240EL	160
MMBF170L	241	MMBTA05LT1	56, 63	MMBZ5241BL	160
MMBF2201N	238	MMBTA06LT1	56, 63	MMBZ5242BL	160
MMBF2202P	239	MMBTA06WT1	58	MMBZ5242EL	160
MMBF4391LT1	237	MMBTA13LT1	61	MMBZ5243BL	160
MMBF4392LT1	237	MMBTA14LT1	61	MMBZ5243EL	160
MMBF4393LT1	237	MMBTA42LT1	64	MMBZ5244BL	160
MMBFJ175LT1	237	MMBTA55LT1	56, 63	MMBZ5245BL	160
MMBFJ177LT1	237	MMBTA56LT1	56, 63	MMBZ5245EL	160
MMBFJ309LT1	237	MMBTA56WT1	58	MMBZ5246BL	160
MMBFJ310LT1	237	MMBTA63LT1	61	MMBZ5246EL	160
MMBFU310LT1	237	MMBTA64LT1	61	MMBZ5247BL	160
MMBT2131	59	MMBTA70LT1	57	MMBZ5248BL	160
MMBT2222ALT1	56, 63, 65	MMBTA92LT1	64	MMBZ5248EL	160
MMBT2222AM3	58	MMBTH10-4L	65	MMBZ5249BL	160
MMBT2222ATT1	58, 63, 66	MMBTH10LT1	65	MMBZ5250BL	160
MMBT2222AWT1	58, 63, 66	MMBTH10M3	65	MMBZ5251BL	160
MMBT2222LT1	57, 63	MMBV105GLT1	150	MMBZ5252BL	160
MMBT2369ALT1	65	MMBV2105LT1	150	MMBZ5252EL	160
MMBT2369LT1	65	MMBV3102LT1	150	MMBZ5253BL	160
MMBT2484LT1	56, 61	MMBV3401LT1	154	MMBZ5253EL	160
MMBT2907ALT1	56, 63, 65	MMBV3700LT1	154	MMBZ5254BL	160
MMBT2907AM3T5G	58	MMBV609LT1	150	MMBZ5255BL	160
MMBT2907AWT1	58, 63, 66	MMBZ12VAL	166	MMBZ5256BL	160
MMBT3416L	57	MMBZ15VAL	166	MMBZ5257BL	160
MMBT3904LT1	56, 65	MMBZ15VDL	165	MMBZ5257EL	160
MMBT3904TT1	58, 66	MMBZ18VAL	166	MMBZ5258BL	160
MMBT3904WT1	58, 66	MMBZ20VAL	166	MMBZ5259BL	160
MMBT3906LT1	57, 65	MMBZ27VAL	166	MMBZ5260BL	161
MMBT3906TT1	58, 66	MMBZ27VAW	167	MMBZ5261BL	161
MMBT3906WT1	58, 66	MMBZ27VCL	165, 167	MMBZ5261EL	161
MMBT4124LT1	57	MMBZ33VAL	166	MMBZ5263BL	161
MMBT4126LT1	57	MMBZ5221BL	160	MMBZ5264BL	161
MMBT4401LT1	57, 63, 65	MMBZ5222BL	160	MMBZ5268BL	161

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MMBZ5270BL	161	MMSZ4687	162	MMSZ5240E	162
MMBZ5V6AL	166	MMSZ4688	162	MMSZ5241B	162
MMBZ6V2AL	166	MMSZ4689	162	MMSZ5242B	162
MMBZ6V8AL	166	MMSZ4690	162	MMSZ5242E	162
MMBZ9V1AL	166	MMSZ4691	162	MMSZ5243B	162
MMDF1N05E	243	MMSZ4692	162	MMSZ5244B	162
MMDF2C03HD	242	MMSZ4693	162	MMSZ5244E	162
MMDF2N02E	242	MMSZ4694	162	MMSZ5245B	162
MMDF2P02HD	243	MMSZ4696	162	MMSZ5245E	162
MMDF3N02HD	242	MMSZ4697	162	MMSZ5246B	162
MMDF3N04HD	243	MMSZ4698	162	MMSZ5246E	162
MMDL101T1	151	MMSZ4699	162	MMSZ5247B	162
MMDL301T1	151	MMSZ47	163	MMSZ5248B	162
MMDL6050T1	156	MMSZ4700	162	MMSZ5248E	162
MMDL770T1	151	MMSZ4701	162	MMSZ5249B	162
MMDL914T1	156	MMSZ4702	162	MMSZ5250B	162
MMFT960	242	MMSZ4703	162	MMSZ5250E	162
MMJT350T1	45	MMSZ4704	162	MMSZ5251B	162
MMSD103T1	155	MMSZ4705	162	MMSZ5251E	162
MMSD301T1	151	MMSZ4706	162	MMSZ5252B	162
MMSD4148T1	155	MMSZ4707	162	MMSZ5252E	162
MMSD701T1	151	MMSZ4708	162	MMSZ5253B	162
MMSD914T1	155	MMSZ4709	162	MMSZ5254B	163
MMSF3P02HD	243	MMSZ4710	162	MMSZ5254E	163
MMSF7P03HD	243	MMSZ4711	163	MMSZ5255B	163
MMSZ10	162	MMSZ4713	163	MMSZ5256B	163
MMSZ11	162	MMSZ4714	163	MMSZ5256E	163
MMSZ12	162	MMSZ4715	163	MMSZ5257B	163
MMSZ13	162	MMSZ4717	163	MMSZ5257E	163
MMSZ15	162	MMSZ4V3	162	MMSZ5258B	163
MMSZ16	162	MMSZ4V7	162	MMSZ5259B	163
MMSZ18	162	MMSZ51	163	MMSZ5259E	163
MMSZ20	162	MMSZ5221B	162	MMSZ5260B	163
MMSZ22	162	MMSZ5221E	162	MMSZ5261B	163
MMSZ24	162	MMSZ5222B	162	MMSZ5262B	163
MMSZ27	163	MMSZ5223B	162	MMSZ5263B	163
MMSZ2V4	162	MMSZ5223E	162	MMSZ5264B	163
MMSZ2V7	162	MMSZ5225B	162	MMSZ5265B	163
MMSZ30	163	MMSZ5226B	162	MMSZ5266B	163
MMSZ33	163	MMSZ5226E	162	MMSZ5267B	163
MMSZ36	163	MMSZ5227B	162	MMSZ5268B	163
MMSZ39	163	MMSZ5228B	162	MMSZ5270B	163
MMSZ3V0	162	MMSZ5229B	162	MMSZ5272B	163
MMSZ3V3	162	MMSZ5230B	162	MMSZ56	163
MMSZ3V6	162	MMSZ5231B	162	MMSZ5V1	162
MMSZ3V9	162	MMSZ5232B	162	MMSZ5V6	162
MMSZ43	163	MMSZ5233B	162	MMSZ6V2	162
MMSZ4678	162	MMSZ5234B	162	MMSZ6V8	162
MMSZ4679	162	MMSZ5235B	162	MMSZ7V5	162
MMSZ4680	162	MMSZ5235E	162	MMSZ8V2	162
MMSZ4681	162	MMSZ5236B	162	MMSZ9V1	162
MMSZ4682	162	MMSZ5237B	162	MMT05B230	327
MMSZ4683	162	MMSZ5237E	162	MMT05B260	327
MMSZ4684	162	MMSZ5238B	162	MMT05B310	327
MMSZ4685	162	MMSZ5239B	162	MMT10B230	327
MMSZ4686	162	MMSZ5240B	162	MMT10B260	327

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MMT10B310	327	MR851	282	MUN5111T1	67
MMUN2111LT1	67	MR852	282	MUN5112T1	67
MMUN2112LT1	67	MR854	282	MUN5113DW1T1	69
MMUN2113LT1	67	MR856	282	MUN5113T1	67
MMUN2114LT1	67	MRA4003	282	MUN5114DW1T1	69
MMUN2115LT1	67	MRA4004	282	MUN5114T1	67
MMUN2116LT1	67	MRA4005	282	MUN5115DW1T1	69
MMUN2132LT1	67	MRA4006	282	MUN5116DW1T1	69
MMUN2133LT1	67	MRA4007	282	MUN5131T1	67
MMUN2211LT1	67	MRS1504	282	MUN5132T1	67
MMUN2212LT1	67	MSA1162GT1	57	MUN5133DW1T1	69
MMUN2213LT1	67	MSA1162YT1	57	MUN5133T1	67
MMUN2214LT1	67	MSB1218A-RT1	58	MUN5135DW1T1	69
MMUN2215LT1	67	MSB709-RT1	57	MUN5135T1	67
MMUN2216LT1	67	MSB710-RT1	57	MUN5211DW1T1	69
MMUN2231LT1	67	MSB92ASW	63, 64	MUN5211T1	67
MMUN2232LT1	67	MSB92AWT1	64	MUN5212DW1T1	69
MMUN2233LT1	67	MSB92WT1	64	MUN5212T1	67
MMUN2234LT1	67	MSC2712GT1	57	MUN5213DW1T1	69
MMUN2238LT1	67	MSD1328-RT1	57	MUN5213T1	67
MMVL3401T1	154	MSD1819A-RT1	58	MUN5214DW1T1	69
MPF4393	237	MSD42WT1	64	MUN5214T1	67
MPS2222	55, 62	MSD601-RT1	57	MUN5215DW1T1	69
MPS2222A	55, 62, 65	MSD602-RT1	57	MUN5215T1	67
MPS2907A	55, 62, 65	MSR1560	271, 278	MUN5216DW1T1	69
MPS4124	55	MSR860	271, 278	MUN5230DW1T1	69
MPS5172	55	MSRD620CT	271, 278	MUN5230T1	67
MPS650	62	MSRD620CTR	278	MUN5232DW1T1	69
MPS651	55, 62	MSRF1560	271, 278	MUN5232T1	67
MPS6652	55, 62	MSRF860	271, 278	MUN5233DW1T1	69
MPS6726	55, 62	MTB2P50E	248	MUN5233T1	67
MPS751	55, 62	MTB30P06V	248	MUN5235DW1T1	69
MPS8099	55, 62	MTB50P03HDL	248	MUN5235T1	67
MPSA05	55, 62	MTD5P06V	247	MUN5237DW1	69
MPSA06	55, 62	MTD6N15	247	MUN5311DW1T1	70
MPSA13	61	MTD6N20E	247	MUN5312DW1T1	70
MPSA14	61	MTP20N15E	249	MUN5313DW1T1	70
MPSA27	61	MTP50P03HDL	249	MUN5314DW1T1	70
MPSA29	61	MTW32N20E	249	MUN5315DW1T1	70
MPSA42	64	MUN2111T1	67	MUN5316DW1T1	70
MPSA44	64	MUN2112T1	67	MUN5330DW1T1	70
MPSA55	55, 62	MUN2113T1	67	MUN5333DW1T1	70
MPSA56	55, 62	MUN2114T1	67	MUN5334DW1	70
MPSA92	64	MUN2211T1	67	MUN5335DW1T1	70
MPSH10	65	MUN2212T1	67	MUR105	280
MPSW01	55, 62	MUN2213T1	67	MUR110	280
MPSW01A	55, 62	MUN2214T1	67	MUR1100E	271, 280
MPSW05	55, 62	MUN2215T1	67	MUR115	280
MPSW06	55, 62	MUN2216T1	67	MUR120	280
MPSW42	64	MUN2230T1	67	MUR130	280
MPSW45	61	MUN2232T1	67	MUR140	280
MPSW45A	61	MUN2233T1	67	MUR1510	281
MPSW51	55, 62	MUN2234T1	67	MUR1515	281
MPSW51A	55, 62	MUN2237T1	67	MUR1520	281
MPSW56	55, 62	MUN2240T1	67	MUR1540	281
MPSW92	64	MUN5111DW1T1	69	MUR1560	281

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
MUR160	280	MURD330	279	NB100LVEP91	94
MUR1610CT	281	MURD550PF	279	NB2304A	105
MUR1615CT	281	MURD620CT	279	NB2305A	105
MUR1620CT	281	MURF1560	281	NB2308A	105
MUR1620CTR	281	MURF1620CT	281	NB2309A	105
MUR1640CT	281	MURF1660CT	281	NB3L553	82
MUR1660CT	281	MURF550PF	281	NB3N2304NZ	82
MUR180E	271, 280	MURF860	281	NB3N3001	102
MUR2020R	281	MURH840CT	271, 281	NB3N3002	102
MUR210	280	MURH860CT	271, 281	NB3N3011	102
MUR2100E	280	MURHB840CT	271, 279	NB3N502	102
MUR220	280	MURHB860CT	271, 279	NB3N508S	102
MUR240	280	MURHD560	271, 279	NB3N551	82
MUR260	280	MURHF860CT	271, 281	NB3N5573	101
MUR3020PT	281	MURHS160	279	NB4L16M	91
MUR3020WT	281	MURS105	279	NB4L339	83
MUR3040PT	281	MURS110	279	NB4L52	85
MUR3060PT	281	MURS115	279	NB4L6254	83, 84
MUR3060WT	281	MURS120	279	NB4L7210	84
MUR405	280	MURS140	279	NB4L858M	84
MUR410	280	MURS160	279	NB4N111K	81
MUR4100E	271, 280	MURS205	279	NB4N1158	90
MUR415	280	MURS210	279	NB4N11M	83
MUR420	280	MURS220	279	NB4N121K	81
MUR440	280	MURS230	279	NB4N316M	81, 92
MUR460	280	MURS240	279	NB4N441	102
MUR480E	271, 280	MURS260	279	NB4N507A	102
MUR550APF	280	MURS320	279	NB4N527S	81
MUR550PF	281	MURS340	279	NB4N7132	90
MUR620CT	281	MURS360	279	NB4N840M	84
MUR805	281	MURS360B	279	NB4N855S	81, 83, 92
MUR810	281	MURS480E	271, 279	NB6HQ14M	82
MUR8100E	271, 281	MV2105	150	NB6L11	83
MUR815	281	N01L6183A	262	NB6L11M	83
MUR820	281	N01L63W2A	262	NB6L11S	83
MUR840	281	N01L63W3A	262	NB6L14	83
MUR860	281	N01L83W2A	262	NB6L14M	82
MUR880E	271, 281	N02L6181A	262	NB6L16	91
MURA105	279	N02L63W2A	262	NB6L239	79
MURA110	279	N02L63W3A	262	NB6L295M	93
MURA115	279	N02L83W2A	262	NB6L572M	83
MURA120	279	N04L63W1A	262	NB6L611	83
MURA130	279	N04L63W2A	262	NB6L72	84
MURA140	279	N08L6182A	262	NB6L72M	84
MURA160	279	N08L63W2A	262	NB6LQ572M	83
MURA205	279	N25S818HA	262	NB6N11S	83
MURA210	279	N25S830HA	262	NB6N14S	83
MURA215	279	N64S818HA	262	NB6N239S	79
MURA220	279	N64S830HA	262	NB7HQ14M	83
MURA230	279	NB100ELT23L	94	NB7L111M	81
MURA240	279	NB100EP223	81	NB7L11M	83
MURA260	279	NB100LVEP17	91	NB7L14M	83
MURB1620CT	279	NB100LVEP221	81	NB7L216	92
MURB1620CTR	279	NB100LVEP222	81	NB7L32M	79
MURB1660CT	279	NB100LVEP224	81	NB7L572	90
MURD320	279	NB100LVEP56	89	NB7L585R	83

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NB7L86M	87, 89	NCN6024	257	NCP1393	8, 12, 120
NB7N017M	79	NCN6804	257	NCP1393B	218
NB7V72M	84	NCP100	333	NCP1395	8, 12
NB7VQ1006M	82, 92	NCP1010	14, 15	NCP1395A	120
NBC12429	102	NCP1011	14, 15	NCP1395B	120
NBC12429A	102	NCP1012	14, 15	NCP1396	8, 12, 120
NBC12430	102	NCP1013	14, 15	NCP1397	8, 12
NBC12430A	102	NCP1014	14, 15	NCP1400	114, 116
NBC12439	102	NCP1015	14, 15	NCP1402	114, 116
NBC12439A	102	NCP102	127	NCP1403	114, 116
NBSG11	83	NCP1027	14, 15	NCP1406	114, 116
NBSG14	82	NCP1028	14, 15	NCP1410	114, 116
NBSG16	91	NCP1030	120	NCP1421	114, 115
NBSG16M	91	NCP1031	120	NCP1422	114, 115
NBSG16VS	91	NCP1034	114, 118	NCP1423	114, 116
NBSG53A	85	NCP1050	14, 15	NCP1450	114, 118
NBSG72A	84	NCP1051	14, 15	NCP1521B	114, 115
NBSG86A	87, 89	NCP1052	14, 15	NCP1522B	114, 115
NBXDBA009	100	NCP1053	14, 15	NCP1523B	114, 116
NBXDBA012	100	NCP1054	14, 15	NCP1529	114, 115
NBXDBA014	100	NCP1055	14, 15	NCP1532	114, 115
NBXDBA015	100	NCP1086	124, 125, 127	NCP1562	8, 10, 120
NBXDBA017	100	NCP1117	124, 125, 126	NCP1571	114, 118
NBXDBA018	100	NCP1200	9, 120	NCP1575	114, 118
NBXDBA019	100	NCP1200	8	NCP1587	114, 121, 122
NBXDBB017	100	NCP1203	8, 9, 120	NCP1587A	122
NBXDBB018	100	NCP1207A	8, 11	NCP1589	121
NBXDDA016	100	NCP1207B	8	NCP1595A	114, 115
NBXDPA012	100	NCP1208B	11	NCP1596	121
NBXDPA017	100	NCP1212	120	NCP1601	16, 18
NBXDPA018	100	NCP1216	8, 9, 120	NCP1605	16, 18
NBXDPA019	100	NCP1216A	8, 9, 120	NCP1605A	18
NBXHBA017	100	NCP1217	8, 9, 120	NCP1606	16, 17
NBXHBA019	100	NCP1217A	8, 9, 120	NCP1607	16, 17
NBXSBA007	100	NCP1218	8, 10	NCP1608	16
NBXSBA008	100	NCP1219	8, 9	NCP1631	16, 17
NBXSBA010	100	NCP1230	8, 9, 120	NCP1650	16, 17
NBXSBA017	100	NCP1237	8, 10	NCP1651	16, 18
NBXSBA019	101	NCP1238	8, 10	NCP1652	16, 18
NBXSBA020	101	NCP1252	8, 10	NCP1653	16, 17
NBXSBA021	101	NCP1271	8, 10, 120	NCP1654	16, 17
NBXSBA022	101	NCP1280	120	NCP1729SN35	114
NBXSBA023	101	NCP1282	120	NCP1729SN35T1G	119
NBXSBA024	101	NCP1288	8, 10	NCP1835B	132
NBXSBA025	101	NCP1294	120	NCP2809	30
NBXSBA030	101	NCP1308	8, 11	NCP2811	30
NBXSBA031	101	NCP1337	8, 11	NCP2820	30
NBXSBA045	101	NCP1338	8, 11	NCP2823	30
NBXSBA046	101	NCP1351	8, 11	NCP2830	30
NBXSPA008	101	NCP1377	8, 11	NCP2860	124, 125, 126
NBXSPA022	101	NCP1379	8, 11	NCP2890	30
NCL30000D	215	NCP1380	8, 11	NCP2892	30
NCN4555	257	NCP1381	8, 11	NCP2990	30
NCN4557	257	NCP1382	8, 11	NCP2991	30
NCN6001	257	NCP1392	8, 12, 120	NCP300	334
NCN6004A	257	NCP1392B	218	NCP301	334

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NCP3011	114, 118	NCP4894	30	NCP5667	124, 127
NCP302	334	NCP500	124	NCP5680MU	216
NCP3020	114, 118	NCP5005SN	215	NCP582	124
NCP303	334	NCP5006SN	215	NCP583	124
NCP304	334	NCP5007SN	215	NCP584	124, 126
NCP305	334	NCP502	124	NCP585	124, 126
NCP3063	114, 117	NCP5021MU	215	NCP5890MU	216
NCP3063B	117	NCP5030	114, 115	NCP590	125, 128
NCP3064	114, 117	NCP5030MT	215	NCP600	124, 125
NCP3065	114, 117	NCP5050MT	215	NCP603	124, 125, 126
NCP3066	114, 117	NCP5104	218	NCP605	124, 125, 126
NCP3101	114, 115	NCP5106A	218	NCP606	124, 125, 126
NCP3102	114	NCP5106B	218	NCP612	124
NCP3120	114, 115	NCP511	124	NCP623	124
NCP3121	114, 115	NCP5111	218	NCP629	124
NCP3122	114, 115	NCP512	124	NCP630	124, 125, 127
NCP3123	114, 115	NCP5181	218	NCP631	124, 127
NCP3125	114, 116	NCP5208	121, 122	NCP662	124
NCP3126	114, 116	NCP5210	121, 122	NCP663	124
NCP3127	114, 116	NCP5212	121	NCP698	124, 126
NCP3163	114, 117	NCP5217	121	NCP699	124, 126
NCP3334	125, 126	NCP5252	114, 115	NCP803	334
NCP3335	124	NCP5304	218	NCS1002	333
NCP3335A	125, 126	NCP5351	218	NCS2001	23
NCP3420	218	NCP5359	218	NCS2002	23
NCP347MTAE	332	NCP5359A	218	NCS2200	28
NCP347MTAF	332	NCP5380	121	NCS2201	28
NCP347MTAH	332	NCP5386	121, 122	NCS2202	28
NCP347MTAI	332	NCP5392	121, 122	NCS2203	28
NCP348AEMT	332	NCP5393	121	NCS2211	30
NCP348MT	332	NCP5395	121	NCS2553	31
NCP349MN	332	NCP5422	114, 118	NCS2554	31
NCP349MNAE	332	NCP5425	114, 118	NCS2561	31
NCP349MNBG	332	NCP5426	124, 126	NCS2563	31
NCP349MNBK	332	NCP5500	124, 126	NCS2564	31
NCP3520	127	NCP5501	126	NCS2566	31
NCP3521	127	NCP5504	125, 128	NCS6415	40
NCP360MU	332	NCP551	124	NCS6416	40
NCP360SN	332	NCP553	124	NCS6433	40
NCP360SNAE	332	NCP5602MU	215	NCS7101	23
NCP360SNAF	332	NCP5603MN	215	NCV1009	333
NCP360SNAI	332	NCP5604AMT	215	NCV1117	129, 132
NCP361MU	332	NCP5604BMT	216	NCV1124	256
NCP361SN	332	NCP561	124	NCV1413BD	217
NCP362AMU	332	NCP5612MU	216	NCV2931	129, 130
NCP362BMU	332	NCP562	124	NCV2931A	129, 130
NCP362CMU	332	NCP5623BMU	216	NCV2951	129, 130
NCP370MUA	332	NCP5623CMU	216	NCV2951A	129, 130
NCP372MUA	332	NCP5623DTB	216	NCV317	129, 132
NCP400	124	NCP563	124	NCV317L	129, 130
NCP4200	121	NCP565	124, 125, 126	NCV317M	129, 131
NCP4300A	333	NCP566	124, 127	NCV33033	219
NCP4303	18	NCP5661	124, 125, 126	NCV33035	219
NCP4330	18	NCP5662	124, 125, 127	NCV33039	219
NCP4523	125, 128	NCP5663	124, 125, 127	NCV33152	218
NCP4672	125, 128	NCP5666	124, 127	NCV33269	129, 132

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NCV33274A	27	NCV8502	129, 130	NGP15N41CL	236
NCV33275	129, 131	NCV8503	129, 131	NID5004N	250
NCV33375	129, 131	NCV8504	129, 131	NID6002N	247, 250
NCV4264	130	NCV8505	129, 131	NID9N05CL	250
NCV4264-2	130	NCV8506	129, 131	NIF9N05CL	250
NCV4269	129, 130	NCV8508	129, 131	NILMS4501N	250
NCV4274	129, 131	NCV8509	129, 132	NIMD6001N	250
NCV4274A	129, 131	NCV8512	129, 130	NIS5112D1	332
NCV4275	129	NCV8518	129	NIS5112D2	332
NCV4275A	129, 131	NCV8518A	129, 131	NIS5132MN1	332
NCV4276	129, 131	NCV8535	129, 131	NIS5132MN2	332
NCV4276A	129, 131	NCV8560	129, 131	NIS5135MN1	332
NCV4279	129, 130	NCV8660	129, 131	NIS5135MN2	332
NCV4299	129, 130	NCV8664	131	NJD2873	74
NCV431AI	333	NCV8665	129, 131	NJD2873T4	45
NCV431BV	333	NCV8674	129, 131	NJD35N04	50
NCV4949	129, 130	NCV8675	129, 131	NJL0281D	48, 52
NCV5500	129, 131	NCY0102BL	318	NJL0302D	48, 52
NCV5501	129, 131	NCY226ST	318	NJL1302D	48, 53
NCV5504	129, 132	NCY228ST	318	NJL21193D	48
NCV551	129, 130	NDD02N60Z	247	NJL21194D	48
NCV553	129, 130	NDD03N60Z	247	NJL3281D	48, 53
NCV565	129, 132	NDD04N60Z	247	NJL4281D	48, 53
NCV5661	129, 132	NDD05N50Z	247	NJL4302D	48, 53
NCV5662	129, 132	NDF02N60ZG	249	NJT4030P	45
NCV5663	129, 132	NDF03N60ZG	249	NJT4031N	45
NCV612	129, 130	NDF04N60ZG	249	NJW0281	48
NCV662	129, 130	NDF04N62ZG	249	NJW0302	48
NCV663	129, 130	NDF05N50ZG	249	NJW1302	48, 53
NCV70521	219	NDF06N60ZG	249	NJW21193	48, 52
NCV70522	219	NDF08N50ZG	249	NJW21194	48, 52
NCV7321	254	NDF10N60ZG	249	NJW3281	48, 53
NCV7341	254	NE5230	23	NL17SV00	302
NCV7356D1	254	NE5517	30	NL17SV02	302
NCV7361A	254	NE5517A	30	NL17SV04	303
NCV7420D23	254	NE5532	25	NL17SV08	302
NCV7513	218	NE5532A	25	NL17SV16	303
NCV7517	218	NE5534	23	NL17SV32	303
NCV7702B	218	NE5534A	23	NL17SZ00	302
NCV7703	218	NE570	31	NL17SZ02	302
NCV7708B	218	NE592	25	NL17SZ04	295
NCV78LxxA	129, 130	NE592D14	31	NL17SZ06	295
NCV78Mxx	129, 131	NE592D8	31	NL17SZ07	290
NCV78MxxA	129, 131	NE592N14	31	NL17SZ08	302
NCV78xx	129, 132	NE592N8	31	NL17SZ125	290
NCV78xxA	129, 132	NGB15N41CL	236	NL17SZ126	289
NCV8141	129, 131	NGB18N40CLB	236	NL17SZ14	295
NCV8184	129, 130	NGB8202N	236	NL17SZ16	289
NCV8401D	250	NGB8204N	236	NL17SZ17	289
NCV8402	250	NGB8206N	236	NL17SZ32	303
NCV8402D	250	NGB8207AN	236	NL17SZ74	293
NCV8403	250	NGB8207N	236	NL17SZ86	302
NCV8405	250	NGD15N41CL	236	NL17SZU04	296
NCV8440	250	NGD18N40CLB	236	NL17VHC1G07	290
NCV8450	250	NGD8201N	236	NL27WZ00	299
NCV8501	129, 130	NGD8205N	236	NL27WZ02	299

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NL27WZ04	294	NLAS5223	36, 39	NLSX5011	307
NL27WZ06	294	NLAS52231	36	NLSX5012	307
NL27WZ07	287, 290	NLAS5223B	36	NLSX5014	307
NL27WZ08	299	NLAS5223BL	36	NLU1G00	302
NL27WZ125	287	NLAS5223L	39	NLU1G04	295
NL27WZ126	287	NLAS7213	37	N, LU1G07	287, 299
NL27WZ14	294	NLAS7222A	37	NLU1G08	302
NL27WZ16	287	NLAS7222B	37	NLU1G14	295, 303
NL27WZ17	287	NLAS7222C	37	NLU1G32	303
NL27WZ32	299	NLAS7223B	37	NLU1G86	302
NL27WZ86	299	NLAS7223C	37	NLU1GT04	295
NL27WZU04	294	NLAS7242	37	NLU1GT125	303
NL37WZ04	296	NLAS8252	37	NLU1GT125A	290
NL37WZ06	296	NLAS9431	39	NLU1GT125B	290
NL37WZ07	290	NLASB3157	39	NLU1GT125C	290
NL37WZ14	296	NLAST4051	39	NLU1GT126	290, 303
NL37WZ16	290	NLAST4053	39	NLU1GT126A	289
NL37WZ17	290	NLAST44599	39	NLU1GT126B	290
NL7SB3257	291	NLAST4501	39	NLU1GT126C	290
NL7SZ18	304	NLAST4599	39	NLU1GT14	295, 301
NL7SZ19	304	NLAST9431	39	NLU1GT32	303
NL7SZ57	286, 299	NLMD5820	30, 36	NLU1GT50	287, 299
NL7SZ58	286, 299	NLSF1174	292	NLU1GT86	302
NL7SZ97	286	NLSF302	301	NLU1GU04	296, 303
NL7SZ98	286	NLSF308	300	NLU2G04	294, 299
NL7WB66	38	NLSF3T125	289	NLU2G06	299
NLAS1053	38	NLSF3T126	289	NLU2G07	287, 299
NLAS2066	38	NLSF595DT	216	NLU2G14	294, 299
NLAS3158	38	NLSF595MN	216	NLU2G16	287, 299
NLAS323	38	NLSV1T240	307	NLU2G17	287, 299
NLAS324	38	NLSV1T244	307	NLU2GU04	294, 299
NLAS325	39	NLSV1T34	307	NLU3G14	296, 303
NLAS3699	36	NLSV22T244	308	NLU3G16	303
NLAS3699B	36	NLSV2T240	307	NLU3G17	290, 303
NLAS3799	36, 39	NLSV2T244	307	NLV14099B	297
NLAS3799B	36	NLSV2T245	307	NLV17SZU04	296
NLAS3799BL	36	NLSV2T3236	307	NLVLCX125	289
NLAS3799L	36	NLSV4T2244	307	NLX1G10	303
NLAS3899B	36, 37, 39	NLSV4T240	307	NLX1G11	303
NLAS4051	39	NLSV4T244	307	NLX1G125	290
NLAS4051S	39	NLSV4T3144	307	NLX1G332	303
NLAS4053	39, 304, 305	NLSV4T3234	307	NLX1G57	299
NLAS4157	36	NLSV8T240	308	NLX1G58	299
NLAS44599	39	NLSV8T244	308	NLX1G97	299
NLAS4501	39	NLSX3012	307	NLX1G98	299
NLAS4599	39	NLSX3013	308	NLX1G99	286, 287, 294, 299
NLAS4684	36	NLSX3013B	308	NLX2G00	299
NLAS4717	37	NLSX3014	307	NLX2G02	299
NLAS4717EP	37, 39	NLSX3018	308	NLX2G04	294
NLAS4783	36	NLSX3373	307	NLX2G06	294
NLAS4783B	36	NLSX3378	307	NLX2G07	287
NLAS5113	36, 39	NLSX3378B	307	NLX2G08	299
NLAS5123	36, 39	NLSX4014	307	NLX2G14	294
NLAS5157	36	NLSX4373	307	NLX2G16	287
NLAS5213A	36	NLSX4378	307	NLX2G17	287
NLAS5213B	36	NLSX4378B	307	NLX2G32	299

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NLX2G86	299	NP1500SDMC	328	NSBA114YF3	70
NLX2GU04	294	NP1800SA	326	NSBA115EDXV6T1	69
NLX3G14	290	NP1800SAMC	325	NSBA115TDP6	69
NLX3G16	290	NP1800SB	326	NSBA115TF3	68
NLX3G17	290	NP1800SBMC	325	NSBA1223TDP6	69
NP0080SAMC	327	NP1800SC	326	NSBA123JDP6	69
NP0080SCMC	327	NP1800SCMC	325	NSBA123JDXV6T1	69
NP0080TA	327	NP1800SDMC	328	NSBA123JF3	68
NP0100SAMC	327	NP2100SA	326	NSBA123TF3	68
NP0100SCMC	327	NP2100SAMC	325	NSBA124EDP6	69
NP0120TA	327	NP2100SB	326	NSBA124EF3	68
NP0150SAMC	327	NP2100SBMC	325	NSBA143EDP6	69
NP0150SCMC	327	NP2100SC	326	NSBA143EF3	68
NP0220SAMC	327	NP2100SCMC	325	NSBA143ZDP6	69
NP0220SCMC	327	NP2300SA	326	NSBA143ZF3	68
NP0300SAMC	327	NP2300SAMC	325	NSBA144EDP6	69
NP0300SCMC	327	NP2300SB	326	NSBA144EDXV6T1	69
NP0640SA	326	NP2300SBMC	325	NSBA144EF3	68
NP0640SAMC	325	NP2300SC	326	NSBA144WDP6	69
NP0640SB	326	NP2300SCMC	325	NSBA144WF3	68
NP0640SBMC	325	NP2600SA	326	NSBC114EDP6	69
NP0640SC	326	NP2600SAMC	325	NSBC114EDXV6T1	69
NP0640SCMC	325	NP2600SB	326	NSBC114EF	68
NP0720SA	326	NP2600SBMC	325	NSBC114EPD6	72
NP0720SAMC	325	NP2600SC	326	NSBC114EPDXV6	71
NP0720SB	326	NP2600SCMC	325	NSBC114TDP6	69
NP0720SBMC	325	NP3100SA	326	NSBC114TDXV6T1	69
NP0720SC	326	NP3100SAMC	325	NSBC114TF3	68
NP0720SCMC	325	NP3100SB	326	NSBC114YDP6	69
NP0720SDMC	328	NP3100SBMC	325	NSBC114YDXV6T1	69
NP0900SA	326	NP3100SC	326	NSBC114YF3	70
NP0900SAMC	325	NP3100SCMC	325	NSBC114YPDP6	72
NP0900SB	326	NP3100SDMC	328	NSBC114YPDXV6	71
NP0900SBMC	325	NP3500SA	326	NSBC115EDXV6T1	69
NP0900SC	326	NP3500SAMC	325	NSBC115TDP6	69
NP0900SCMC	325	NP3500SB	326	NSBC115TF3	68
NP1100SA	326	NP3500SBMC	325	NSBC115TPDP6	72
NP1100SAMC	325	NP3500SC	326	NSBC123JDP6	69
NP1100SB	326	NP3500SCMC	325	NSBC123JF3	68
NP1100SBMC	325	NS2029M3	58	NSBC123JPDP6	72
NP1100SC	326	NS5B1G384	39	NSBC123JPDV6	71
NP1100SCMC	325	NS5B1G385	39	NSBC123TDP6	69
NP1100SDMC	328	NS5S1153	36, 37	NSBC123TF3	68
NP1300SA	326	NS9F18VS	159	NSBC124EDP6	69
NP1300SAMC	325	NSB1010XV5T5	71	NSBC124EDXV6T1	69
NP1300SB	326	NSB1011XV6T1	71	NSBC124EF3	68
NP1300SBMC	325	NSB1706DMW5T1	70	NSBC124EPDXV6	71
NP1300SC	326	NSB4904DW1	70	NSBC143EDP6	69
NP1300SCMC	325	NSB9435	74	NSBC143EF3	68
NP1300SDMC	328	NSBA114EDP6	69	NSBC143TPDXV6	71
NP1500SA	326	NSBA114EDXV6T1	69	NSBC143ZDP6	69
NP1500SAMC	325	NSBA114EF3	68	NSBC143ZDXV6T1	69
NP1500SB	326	NSBA114TDP6	69	NSBC143ZF3	68
NP1500SBMC	325	NSBA114TF3	68	NSBC143ZPDP6	72
NP1500SC	326	NSBA114YDP6	69	NSBC143ZPDV6	71
NP1500SCMC	325	NSBA114YDXV6T1	69	NSBC144EDP6	69

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NSBC144EDXV6T1	69	NSS12200L	73	NST847BDP6	60
NSBC144EF3	68	NSS12200W	74	NST848BF3	59
NSBC144EPDP6	72	NSS12201L	73	NST856BF3	59
NSBC144EPDXV6	71	NSS12500UW3	73	NST857BDP6	60
NSBC144WDP6	69	NSS12501UW3	73	NST857BF3	59
NSBC144WF3	68	NSS12601CF8	73	NSTB1002DXV5	71
NSD16F3	156	NSS1C200L	73	NSTB1005DXV5	71
NSD914F3	156	NSS1C200MZ4	45, 74	NTA4001N	238
NSD914XV2T1	156	NSS1C201L	73	NTA4151P	238
NSDEMP11XV6T1	156	NSS1C201MZ4	45, 74	NTA4153N	238
NSI45020	216	NSS20101J	73	NTA7002N	238
NSI45020A	216	NSS20200L	73	NTB18N06L	248
NSI45025	216	NSS20201L	73	NTB25P06	248
NSI45025A	216	NSS20201MR6	73	NTB30N06L	248
NSI45025AZ	216	NSS20300MR6	73	NTB30N20	248
NSI45025Z	216	NSS20500UW3	73	NTB35N15	248
NSI45030	216	NSS20501UW3	73	NTB45N06	248
NSI45030A	216	NSS20601CF8	73	NTB45N06L	248
NSI45030AZ	216	NSS30070MR6	73	NTB52N10	248
NSI45030Z	216	NSS30071MR6	73	NTB5404N	248
NSI50010Y	216	NSS30100L	73	NTB5405N	248
NSL12AW	59	NSS30101L	73	NTB5411N	248
NSR0130P2	153	NSS30201MR6	73	NTB5412N	248
NSR0140P2	153	NSS35200CF8	73	NTB5605P	248
NSR01F30NX	153	NSS35200MR6	73	NTB60N06	248
NSR01L30NX	153	NSS40200L	73	NTB60N06L	248
NSR0230M2	153	NSS40200UW6	74	NTB6410AN	248
NSR0230P2	153	NSS40201L	73	NTB6411AN	248
NSR0240H	151	NSS40300MZ4	45	NTB6412AN	248
NSR0240P2	153	NSS40300MZ4T1G	74	NTB6413AN	248
NSR0240V2	152	NSS40301MD	60, 74	NTB75N03L09	247
NSR02F30NX	153	NSS40301MZ4	45	NTB75N03R	247
NSR02L30NX	153	NSS40301MZ4T1G	74	NTB75N06	248
NSR0320MW2T1	151	NSS40500UW3	73	NTB90N02	247
NSR0320XV6T1	152	NSS40501UW3	73	NTD110N02	245
NSR0340H	151	NSS40600CF8	73	NTD12N10	247
NSR0340P2	153	NSS40601CF8	73	NTD14N03R	245
NSR0340V2	152	NSS60200L	73	NTD18N06	247
NSR0520V2	152	NSS60201L	73	NTD18N06L	247
NSR0530P2	153	NSS60600MZ4	45, 74	NTD20N03L27	246
NSR05F20NX	153	NSS60601MZ4	45, 74	NTD20N06	247
NSR05F30NX	153	NST30010MXV6	60	NTD20N06L	247
NSR05F40NX	153	NST3904DP6	60	NTD20P06L	247
NSR0620P2	153	NST3904DXV6T1	60	NTD23N03R	245
NSR1020MW2	151	NST3904F3	59	NTD24N06	247
NSR10F20NX	153	NST3906DP6	60	NTD24N06L	247
NSR10F30NX	153	NST3906DXV6T1	60	NTD25P03L	247
NSR10F40NX	153	NST3906F3	59	NTD2955	247
NSR20F20NX	153	NST3946DP6	60	NTD3055094	247
NSR20F30NX	153	NST3946DXV6T1	60	NTD3055150	247
NSR30CM3T5G	153	NST45010MW6	60	NTD3055L104	247
NSRLL30XV2	152	NST45011MW6	60	NTD3055L170	247
NSRLV20MW2	151	NST489AM	59	NTD32N06L	247
NSS12100M3	73	NST846BF3	59	NTD40N03R	245
NSS12100UW3	73	NST847BDP6	60	NTD4302	246
NSS12100XV6	74	NST847BF3	59	NTD4804N	246

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NTD4805N	246	NTF6P02	242	NTLJD3119C	240
NTD4806N	246	NTGD1100L	239	NTLJD3183CZ	240
NTD4808N	246	NTGD3148N	240	NTLJD4116N	240
NTD4809N	246	NTGD3149C	240	NTLJF3117P	240
NTD4809NH	246	NTGD4161P	240	NTLJF4156N	240
NTD4810N	246	NTGD4167C	240	NTLJS1102P	240
NTD4810NH	246	NTGS3130N	240	NTLJS2103P	240
NTD4813N	246	NTGS3136P	240	NTLJS3113P	240
NTD4813NH	246	NTGS3433	240	NTLJS4114N	240
NTD4815N	246	NTGS3441	240	NTLUD3191PZ	239
NTD4815NH	246	NTGS3441P	240	NTLUF4189NZ	239
NTD4855N	245	NTGS3443	240	NTLUS3192PZ	239
NTD4856N	245	NTGS3446	240	NTLUS4195PZ	239
NTD4857N	245	NTGS3455	240	NTMD2P01	243
NTD4858N	245	NTGS4111P	240	NTMD4184P	243
NTD4860N	245	NTGS4141N	240	NTMD4820N	243
NTD4863N	245	NTGS5120P	240	NTMD4840N	243
NTD4865N	245	NTHC5513	241	NTMD4884N	243
NTD4904N	246	NTHD2102P	242	NTMD6601N	243
NTD4905N	246	NTHD3100C	241	NTMD6N02	242
NTD4906N	246	NTHD3101F	242	NTMD6N03	243
NTD4909N	246	NTHD3102C	241	NTMD6N04R2	243
NTD4910N	246	NTHD3133P	242	NTMD6P02	243
NTD4913N	246	NTHD4102P	242	NTMFS4108N	244
NTD4960N	246	NTHD4401P	242	NTMFS4119N	244
NTD4963N	246	NTHD4502N	241	NTMFS4121N	244
NTD5406N	246	NTHD4508N	241	NTMFS4744N	245
NTD5407N	246	NTHD4P02F	242	NTMFS4821N	245
NTD5413N	247	NTHD5904N	241	NTMFS4823N	245
NTD5414N	247	NTHS2101P	242	NTMFS4833N	244
NTD5802N	246	NTHS4101P	242	NTMFS4834N	244
NTD5803N	246	NTHS4166N	241	NTMFS4835N	244
NTD5804N	246	NTHS5404	241	NTMFS4836N	244
NTD5805N	246	NTHS5441	242	NTMFS4837N	244
NTD5806N	246	NTHS5443	242	NTMFS4839N	245
NTD5807N	246	NTJD1155L	239	NTMFS4841N	245
NTD5867NL	247	NTJD2152P	239	NTMFS4845N	244
NTD60N02R	245	NTJD3158C	239	NTMFS4846N	244
NTD6414AN	247	NTJD4001N	239	NTMFS4847N	244
NTD6415AN	247	NTJD4105C	239	NTMFS4849N	244
NTD6415ANL	247	NTJD4152P	239	NTMFS4851N	245
NTD6416AN	247	NTJD4158C	239	NTMFS4852N	244
NTD6416ANL	247	NTJD4401N	239	NTMFS4897NF	245
NTD6600N	247	NTJD5121N	239	NTMFS4898NF	245
NTD70N03R	245	NTJS3151P	239	NTMFS4899NF	245
NTD78N03	245	NTJS3157N	239	NTMFS4921N	245
NTD80N02	245	NTJS4151P	239	NTMFS4935N	244
NTD85N02R	245	NTJS4160N	239	NTMFS4936N	244
NTD95N02R	245	NTJS4405N	239	NTMFS4937N	244
NTE4151P	238	NTK3043N	238	NTMFS4939N	245
NTE4153N	238	NTK3134N	238	NTMFS4941N	245
NTF2955	242	NTK3139P	238	NTMFS4943N	245
NTF3055100	242	NTK3142P	238	NTMFS4945N	245
NTF3055L108	242	NTLGD3502N	242	NTMKB4893N	248
NTF3055L175	242	NTLGF3402P	242	NTMKB4895N	248
NTF5P03	242	NTLJD3115P	240	NTMKB4896N	248

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NTMKC4890N	248	NTTFS4823N	244	NUF6105FC	229
NTMKE4890N	248	NTTFS4824N	244	NUF6106FC	229
NTMKE4891N	248	NTTFS4840N	244	NUF6107MN	229
NTMKE4892N	248	NTTFS4932N	244	NUF6400MN	229
NTMKE4894N	248	NTTFS4937N	244	NUF6401MN	229
NTMS10P02	243	NTTFS4939N	244	NUF6402MN	229
NTMS4107N	243	NTTFS4941N	244	NUF6406MN	229
NTMS4176P	243	NTTFS4943N	244	NUF6410MN	229
NTMS4177P	243	NTTFS4945N	244	NUF8001MU	229
NTMS4503N	242	NTTFS5820NL	244	NUF8010MU	229
NTMS4800N	243	NTUD3169C	238	NUF8152MU	229
NTMS4801N	243	NTUD3170N	238	NUF8401MN	229
NTMS4802N	243	NTUD3171P	238	NUF8402MN	229
NTMS4807N	243	NTZD3152P	238	NUF8410MN	229
NTMS4816N	243	NTZD3154N	238	NUF8600MN	229
NTMS4872N	243	NTZD3155C	238	NUF8610MN	229
NTMS4873N	243	NTZD3156C	238	NUF9001FC	229
NTMS4920N	243	NTZD5110N	238	NUF9002FC	229
NTMS4935N	243	NTZS3151P	238	NUP1105L	186
NTMS4937N	243	NUC2401	198	NUP1301ML3	190
NTMS4939N	243	NUC2401MN	228	NUP2105L	188
NTMS5P02	243	NUD3105	217	NUP2114UC	190
NTMS7N03	242	NUD3105D	217	NUP2114UP	191
NTMSD3P303	243	NUD3112	217	NUP2301MW6	192
NTMSD6N303	243	NUD3112D	217	NUP3115UP	195
NTP2955	249	NUD3124	217	NUP4000DR2G	189
NTP35N15	249	NUD3124D	217	NUP4012P	197
NTP5404NR	249	NUD3160	217	NUP4060AXV6	196
NTP5411N	249	NUD3160D	217	NUP4102XV6	196
NTP5412N	249	NUD4001D	216	NUP4114H	194
NTP5426N	249	NUD4011D	216	NUP4114UP	194
NTP6410AN	249	NUD4700SN	250	NUP4201DR2	196
NTP6411AN	249	NUF2042XV6	228	NUS1204MN	240
NTP6412AN	249	NUF2101M	228	NYC222ST	318
NTP6413AN	249	NUF2114MN	228	NZ9F10V	159
NTR0202PL	241	NUF2116MN	228	NZ9F10VS	159
NTR1P02	241	NUF2221W1	228	NZ9F11V	159
NTR1P02L	241	NUF2222FC	228	NZ9F11VS	159
NTR2101P	241	NUF2230XV6	228	NZ9F12V	159
NTR3161N	241	NUF2441FC	228	NZ9F12VS	159
NTR3162P	241	NUF2450MU	228	NZ9F13V	159
NTR4003N	241	NUF3101FC	228	NZ9F13VS	159
NTR4101P	241	NUF3102MU	228	NZ9F15V	159
NTR4170N	241	NUF4000MU	228	NZ9F15VS	159
NTR4171P	241	NUF4001MU	228	NZ9F16V	159
NTR4501N	241	NUF4010MU	228	NZ9F16VS	159
NTR4502P	241	NUF4107FC	228	NZ9F18V	159
NTR4503N	241	NUF4211MN	228	NZ9F20V	159
NTS2101P	239	NUF4220MN	228	NZ9F22V	159
NTS4001N	239	NUF4310MN	228	NZ9F24V	159
NTS4101P	239	NUF4401MN	228	NZ9F2V4	159
NTS4173P	239	NUF4402MN	228	NZ9F2V7	159
NTS4409N	238	NUF4403MN	229	NZ9F2V7S	159
NTTD4401FR	242	NUF6001MU	229	NZ9F2Y4S	159
NTTFS4800N	244	NUF6005MU	229	NZ9F3V0	159
NTTFS4821N	244	NUF6010MU	229	NZ9F3V0S	159

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
NZ9F3V3	159	P6KE20A	169	P6SMB51A	178
NZ9F3V6	159	P6KE22A	169	P6SMB51CA	179
NZ9F3V6S	159	P6KE24A	169	P6SMB56A	178
NZ9F3V9	159	P6KE27A	169	P6SMB56CA	179
NZ9F3V9S	159	P6KE30A	169	P6SMB6.8A	178
NZ9F3Y3S	159	P6KE33A	169	P6SMB62A	178
NZ9F4V3	159	P6KE36A	169	P6SMB62CA	179
NZ9F4V3S	159	P6KE39A	169	P6SMB68A	178
NZ9F4V7	159	P6KE43A	169	P6SMB68CA	179
NZ9F4V7S	159	P6KE47A	169	P6SMB7.5A	178
NZ9F5V1	159	P6KE51A	169	P6SMB75A	178
NZ9F5V1S	159	P6KE56A	169	P6SMB8.2A	178
NZ9F5V6	159	P6KE6.8A	169	P6SMB82A	178
NZ9F5V6S	159	P6KE62A	169	P6SMB82CA	179
NZ9F6V2	159	P6KE68A	169	P6SMB9.1A	178
NZ9F6V2S	159	P6KE7.5A	169	P6SMB91A	178
NZ9F6V8	159	P6KE75A	169	PCA9306	308
NZ9F6V8S	159	P6KE82A	169	PCS3P2042BG-08TR	104
NZ9F7V5	159	P6SMB100A	178	PCS3P2042BG-08TT	104
NZ9F7V5S	159	P6SMB10A	178	PCS3P2537AG-08CR	104
NZ9F8V2	159	P6SMB11CA	179	PCS3P25811AG08SR	104
NZ9F8V2S	159	P6SMB120A	178	PCS3P7303AG-08CR	104
NZ9F9V1	159	P6SMB12A	178	PCS3P7303AG-08TR	104
NZ9F9V1S	159	P6SMB12CA	179	PCS3P7303AG-08TT	104
NZF220DF	229	P6SMB130A	178	PCS3P73U00AG08TR	104
NZF220T	229	P6SMB13A	178	PCS3P8504AG-08CR	104
NZL5V6AXV3	188	P6SMB150A	178	PCS3PS550AG-08CR	104
NZL6V8AXV3	188	P6SMB15A	178	PN2222A	55, 62
NZL7V5AXV3	188	P6SMB15CA	179	PZT2222AT1	59, 63
ONBCD25	110	P6SMB160A	178	PZT2907AT1	59, 63
ONC18G/R	110	P6SMB16A	178	PZT651T1	59, 63
ONC25	110	P6SMB16CA	179	PZT751T1	59, 63
P1708CF-08SR	103	P6SMB180A	178	PZTA42T1	64
P1708CF-08TR	103	P6SMB18A	178	PZTA92T1	64
P1727AF-08SR	103	P6SMB18CA	179	PZTA96S	64
P2N2222A	62, 65	P6SMB200A	178	RB520S30T1	152
P3P18S19BF-08SR	103	P6SMB20A	178	RB521S30T1	152
P3P18S19BF-08ST	103	P6SMB20CA	179	RB751S40T1	152
P3P73U00AG-08-ST	103	P6SMB22A	178	RB751V40T1	151
P3P73U00AG-08-TT	103	P6SMB22CA	179	SA10A	168
P3P73U00AG-08CR	103	P6SMB24A	178	SA12A	168
P3P73U00AG-08SR	103	P6SMB24CA	179	SA13A	168
P3P73Z01BWG-08CR	104	P6SMB27A	178	SA15A	168
P3P73Z01BWG-08TR	104	P6SMB27CA	179	SA16A	168
P3P73Z01BWG-08TT	104	P6SMB30A	178	SA17A	168
P6KE100A	169	P6SMB30CA	179	SA18A	168
P6KE10A	169	P6SMB33A	178	SA20A	168
P6KE12A	169	P6SMB33CA	179	SA24A	168
P6KE13A	169	P6SMB36A	178	SA26A	168
P6KE150A	169	P6SMB36CA	179	SA28A	168
P6KE15A	169	P6SMB39A	178	SA30A	168
P6KE160A	169	P6SMB39CA	179	SA33A	168
P6KE16A	169	P6SMB43A	178	SA36A	168
P6KE180A	169	P6SMB43CA	179	SA5.0A	168
P6KE18A	169	P6SMB47A	178	SA5230	23
P6KE200A	169	P6SMB47CA	179	SA5532	25

Alphabetical Parts Listing

Device Number	Page	Device Number	Page	Device Number	Page
SA5534	23	TIP107	50	TL594	8, 12, 114, 120
SA5534A	23	TIP110	50	TLV431A	333
SA571	31	TIP111	50	TLV431B	333
SA572D	31	TIP112	50	UC2842B	8, 13
SA575D	31	TIP115	50	UC2843B	8, 13
SA6.0A	168	TIP116	50	UC2844B	8, 13
SA7.0A	168	TIP117	50	UC2845B	8, 13
SD05	183	TIP120	50	UC3842B	8, 13
SD12	183	TIP121	50	UC3842BV	8, 13
SD12C	184	TIP122	50	UC3843B	8, 13
SE5532	25	TIP125	50	UC3843BV	8, 13
SE5532A	25	TIP126	50	UC3844B	8, 13
SE5534	23	TIP127	50	UC3844BV	8, 13
SE5534A	23	TIP131	50	UC3845B	8, 13
SG3525	114, 118	TIP132	50	UC3845BV	8, 13
SG3525A	8, 12	TIP140	51	uESD3.3D	189
SG3535A	120	TIP141	51	ULN2003AD	217
SL05	190	TIP142	51	ULQ2003AD	217
SL12	190	TIP147	51	UMC3NT1	70
SL15	190	TIP2955	48	UMC5NT1	70
SL24	190	TIP29A	46	UMZ1NT1	60
SM05	187	TIP29B	46	VN2222LL	249
SM12	187	TIP29C	46	VN2410L	249
SMBJ12AON	180	TIP3055	48	XPressArray-II	110
SMF10A	172	TIP30C	46	Z0103MA	321
SMF11A	172	TIP31	46	Z0103MN	321
SMF12A	172	TIP31A	46	Z0107MA	321
SMF13A	172	TIP31B	46	Z0107MN	321
SMF14A	172	TIP31C	46	Z0109MA	321
SMF15A	172	TIP32	46	Z0109MN	321
SMF18A	172	TIP32A	46		
SMF20A	172	TIP32B	46		
SMF22A	172	TIP32C	46		
SMF24A	172	TIP33C	48		
SMF26A	172	TIP35A	48		
SMF28A	172	TIP35C	48		
SMF30A	172	TIP36A	48		
SMF33A	172	TIP36C	48		
SMF36A	172	TIP41A	47		
SMF5.0A	172	TIP41B	47		
SMF6.0A	172	TIP41C	47		
SMF7.0A	172	TIP42	47		
SMF7.5A	172	TIP42A	47		
SMF8.0A	172	TIP42B	47		
SMF9.0A	172	TIP42C	47		
STF202-22	229	TIP47	46		
T2322B	321	TIP48	46		
T2500D	322	TIP50	46		
T2800D	322	TL431AC	333		
TCA0372	25	TL431AI	333		
TCA0372B	25	TL431BC	333		
TDA1085C	219	TL431BI	333		
TIP100	50	TL431BV	333		
TIP101	50	TL431C	333		
TIP102	50	TL431I	333		
TIP106	50	TL494	8, 12, 114, 118, 120		

Sales and Design Assistance from ON Semiconductor

ON Semiconductor Distribution Partners

AMSC Co.	www.amsco.jp	(81) 422 54 6622
Arrow Electronics	www.arrow.com	(800) 777-2776
Avnet	www.em.avnet.com	(800) 332-8638
Digi-Key	www.digikey.com	(800) 344-4539
EBV Elektronik	www.ebv.com/en/locations.html	(49) 8121 774-0
Fuji Electric Co.	www.fujiele.co.jp	(81) 3 3814 1411
Future & FAI Electronics	www.futureelectronics.com/contact	1-800-FUTURE1 (388-8731)
KH Electronics Inc.	www.khelec.com/kor	(82) 42 471 8521
Marubun	www.marubun.co.jp	(81) 3 3639 5630
Mitsui Electronics Inc.	www.btel.co.jp	(81) 3 6403 5900
Mouser Electronics	www.mouser.com	(800) 346-6873
Newark/Farnell	www.farnell.com/onsemi	(800) 4-NEWARK
Promate Electronic Co.	www.promate.com.tw	(886) 2 2659 0303
Segyung Bristestone Co.	www.bristestone.com	(82) 2 3218 1511
Serial Microelectronics, HK	www.serialsys.com.hk	(852) 2790 8220
Tokyo Electron Device Co.	hwww.teldevice.co.jp	(81) 45 443 4000
World Peace Industries Co.	www.wpi-group.com	(852) 2365 4860
WT Microelectronics Co.	www.wtmec.com	(852) 2950 0820
Yosun Electronics	www.yosun.com.tw	(886) 2 2659 8168

INTERNATIONAL

GREATER CHINA	Beijing	86-10-8518-2323
	Chengdu	86-28-8678-4078
	Hong Kong	852-2689-0088
	Nanjing	86-25-8453-5879
	Shanghai	86-21-6123-8798
	Shenzhen	86-755-8209-1128
	Taipei, Taiwan	886-2-8797-8110
FRANCE	Paris	33 (0) 1 39-26-41-00
GERMANY	Munich	49 (0) 89-93-0808-0
INDIA	Bangalore	91-80-4113-9553
ISRAEL	Raanana	972 (0) 9-9609-111
ITALY	Milan	39 02 9239311
JAPAN	Tokyo	81-3-5773-3850
KOREA	Seoul	82-31-786-3700
MALAYSIA	Penang	60-4-226-9368
SINGAPORE	Singapore	65-6555-8260
SLOVAKIA	Piestany	421 33 790 2450
UNITED KINGDOM	Slough	44 (0) 1753 70 1676

For a comprehensive listing of
ON Semiconductor Sales Offices, please visit:
www.onsemi.com/salesupport

AMERICAS REP FIRMS

Alabama	Huntsville	e-Components	(256) 533-2444
Brazil	Countrywide	Ammon & Rizos	(+55) 11-4688-1960
California	Bay Area	L2	(408) 433-9388
Canada	Eastern Canada	Astec	(905) 607-1444
	Western Canada	Sifore	(503) 977-6267
Connecticut	Statewide	Genesis Associates	(781) 270-9540
Florida	Statewide	e-Components	(888) 468-2444
Georgia	Atlanta	e-Components	(888) 468-2444
	Palatine (North)	HLC Ltd.	(847) 358-6500
Illinois	St. Charles (South)	Stan Clothier Company	(847) 781-4010
	Palatine (North)	HLC Ltd.	(847) 358-6500
Indiana	Fishers	Bear VAI	(317) 570-0707
Iowa	Cedar Rapids	Essig & Associates	(319) 363-8703
Kansas	Overland Park	Stan Clothier Company	(913) 894-1675
Maryland	Columbia	Third Wave Solutions	(410) 290-5990
Massachusetts	Burlington	Genesis Associates	(781) 270-9540
Mexico	Countrywide	Ammon & Rizos	(+55) 11-4688-1960
Michigan	St. Joseph	Bear VAI	(440) 526-1991
Minnesota	Eden Prairie	Stan Clothier Company	(952) 944-3456
Missouri	St. Charles	Stan Clothier Company	(636) 916-3777
New Jersey	Statewide	S.J. Metro	(516) 942-3232
New York	Binghamton	TriTech - Full Line Rep	(607) 722-3580
	Jericho	S.J. Metro	(516) 942-3232
	Rochester	TriTech - Full Line Rep	(585) 385-6500
North Carolina	Raleigh	e-Components	(888) 468-2444
Ohio	Brecksville	Bear VAI Technology	(440) 526-1991
Oregon	Portland	SiFore Technical	(503) 977-6267
Puerto Rico	Countrywide	e-Components	(888) 468-2444
Washington	Bellevue	SiFore Technical	(425) 990-4701
Wisconsin	Eden Prairie (NW)	Stan Clothier Company	(608) 882-0686
	Milwaukee (SE)	HLC Ltd.	(847) 358-6500



ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada.

Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local
Sales Representative